




| REVISION | DATE | BY | DATE | BY |
|----------|------|----|----------|----|
| | | | 16/02/24 | PP |
| | | | | |
| | | | | |

Confidential - Property of
Siemens Industry, Inc.

| | |
|-----------|----------------|
| CUSTOMER | |
| ORDER NO. | DWG. NO. |
| | 3F3Y015FLN3D16 |
| | SH 1 OF 2 |


SIEMENS

| | | |
|---|--|---|
| CATALOG NO. 3F3Y015FLN3D16 SERIAL NO. SERIES H 15 kVA 60 Hz 3 PHASE 4.3 % IMP AT 135 °C | |  <p>VOLTS CONNECT</p> <p>504 1 492 2 480 3 468 4 456 5 444 6 432 7</p> |
| 115 °C RISE 30 °C AVG. AMBIENT 220 °C TEMP CLASS 40 °C MAX. AMBIENT PRIMARY (H1 H2 H3) 480V V 10 kV BIL SECONDARY(X0 X1 X2 X3) 208Y/120V V 10 kV BIL | WINDING MATERIAL AL ENCLOSURE TYPE 3R WEIGHT 205 LBS ENERGY EFFICIENCY EXCEEDS CSA C802.2-2012 DOE 10 CFR PART 431:2016 SPACINGS BETWEEN ANY VENTILATED ENCLOSURE PANEL AND ANY ADJACENT WALL SHALL BE A MINIMUM OF 3 INCHES SOUND LEVEL IS 3 DB LOWER THAN NEMA ST20 REQUIREMENTS | |
| SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS BEFORE HANDLING, INSTALLING AND OPERATING; SEE INSTRUCTION MANUAL NEMA Class ANN Dry Type Transformer | | TYPE K   <p>SEISMIC QUALIFICATIONS, FLOOR MOUNT ONLY OSP-0136-10 IBC 2012/ASCE 7-10 SDS<=2.0g z/h=1 p=1.5</p> |




3F3Y015FLN3D16

FRONT VIEW



SIDE VIEW



All Dimensions in inches

ENCLOSURE COLOR : ANSI-61 GREY PAINT OUTDOOR

H.V.1. TERMINAL DETAIL

L.V.1. TERMINAL DETAIL

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR #14-2 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR #14-2 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT

Confidential - Property of
Siemens Industry, Inc.

| REVISION | DATE | BY | DATE | BY |
|----------|------|---------|----------|----|
| | | DRAWN | 16/02/24 | PP |
| | | CHEK'D | | |
| | | VERIF'D | | |

CUSTOMER

ORDER NO.

DWG. NO.

3F3Y015FLN3D16

SH 2 OF 2