




3F3Y150FD16 - Three-Phase Ventilated-USA-DOE

PRODUCT DETAILS			
KVA:	150.00	Enclosure:	NEMA 3R Ventilated
UPC#:	804766148347	Phase:	Three-Phase
Line Voltage	480V-Delta	Load Voltage	208Y/120V
E/S Shielded:	No	Windings:	Aluminum
Temp. rise:	115°	Hertz:	60 Hz
Taps:	2 - 2.5% FCAN; 4 - 2.5% FCBN	Approvals:	UL, cUL, DOE
		Wall Bracket:	n/a
WEIGHT AND DIMENSIONS			
Height(A):	42.00"	Width(B):	33.00"
Depth(C):	32.50"	Shipping Weight:	1250 lbs
ADDITIONAL INFORMATION			
How to Buy: Contact Siemens Distributor, Siemens Sales Rep or Configure in COMPAS Configuration Tool			

Wiring Diagram

T480E Wiring Diagram & Connections



Connections		
Primary Volts	On Each Coil Jumper Taps To	Primary Lines Connect To
504	1	H1, H2, H3
492	2	H1, H2, H3
480	3	H1, H2, H3
468	4	H1, H2, H3
456	5	H1, H2, H3
444	6	H1, H2, H3
432	7	H1, H2, H3
Sec. Volts	Secondary Lines Connect To	
208	X1, X2, X3	
120	Between X0 and X1 or X2 or X3	
1 phase		

Dimensional Drawing

Figure 24

