

# SIEMENS

## SIPROTEC 7SL82

Combined line differential and distance protection relay

[www.siemens.com/siprotec](http://www.siemens.com/siprotec)

### Description

The combined SIPROTEC 7SL82 line differential and distance protection has been designed particularly for the cost-optimized and compact protection of lines in medium-voltage and high-voltage systems. With its flexibility and the powerful DIGSI 5 engineering tool, SIPROTEC 7SL82 offers future-oriented for protection, control, automation, monitoring, and Power Quality – Basic

Main function	Differential protection and distance protection for medium-voltage and high voltage applications Interoperability of SIPROTEC 4 and SIPROTEC 5 line protection devices
Tripping	3-pole, minimum tripping time: 19 ms
Inputs and outputs	4 current transformers, 4 voltage transformers (optional), 11 or 23 binary inputs, 9 or 16 binary outputs
Hardware flexibility	Different hardware quantity structures for binary inputs and outputs are available in the 1/3 base module. Adding 1/6 expansion modules is not possible; available with large or small display.
Housing width	1/3 × 19 inches

### Applications

- Line protection for all voltage levels with 3-pole tripping
- Phase-selective protection of overhead lines and cables with single-ended and multi-ended infeed of all lengths with up to 6 line ends
- Transformers and compensating coils in the protection zone
- Detection of ground faults in isolated or arc-suppression-coilground power systems in star, ring, or meshed arrangement
- Serial protection communication with SIPROTEC 5 and SIPROTEC 4 devices over different distances and physical media, such as optical fiber, two-wire connections, and communication networks



Combined line differential and distance protection relay  
SIPROTEC 7SL82 (housing width 1/3 x 19")

- Phasor Measurement Unit (PMU)
- Detection and recording of power-quality data in the medium-voltage and subordinate low-voltage power system

### Functions

DIGSI 5 permits all functions to be configured and combined as required.

- Minimum tripping time: 19 ms
- Main protection function is differential protection with adaptive algorithm for maximum sensitivity and stability even with the most different transformer errors, current-transformer saturation and capacitive charging currents
- Several distance-protection functions selectable as backup protection or secondary main protection: Classic, reactance method (RMD), impedance protection for transformers
- Directional backup protection and various additional functions
- Ground-fault detection using the pulse detection method
- Adaptive power-swing blocking

# Compact and efficient

- Detection of ground faults of any type in compensated or isolated electrical power systems using the following functions:  $3I_0$ ,  $V_0$ , transient ground fault,  $\cos \phi$ ,  $\sin \phi$ , dir. detection of intermittent ground faults, harmonic detection, and admittance measurement
- Detection of current-transformer saturation for fast tripping with high accuracy
- Fault locator plus for accurate fault location with inhomogenous line sections and targeted automatic overhead-line section reclosing (AREC)
- Arc protection
- Automatic frequency relief for underfrequency load shedding, taking changed infeed conditions due to decentralized power generation into consideration
- Directional reactive-power undervoltage protection (QU protection)
- Detection of current and voltage signals up to the 50th harmonic with high accuracy for selected protection functions (such as thermal overload protection) and operational measured values
- PQ – Basic: Voltage unbalance; voltage changes: overvoltage, dip, interruption; TDD, THD, and harmonics
- Control, synchrocheck, and switchgear interlocking protection
- Graphical logic editor to create high-performance automation functions in the device
- Single-line representation in the small or large display
- Fixed integrated electrical Ethernet RJ45 interface for DIGSI 5 and IEC 61850 (reporting and GOOSE)
- 2 optional pluggable communication modules, usable for different and redundant protocols (IEC 61850, IEC 60870-5-103, IEC 60870-5-104, Modbus TCP, DNP3 serial and TCP, PROFINET IO)
- Serial protection communication via optical fibers, two-wire connections, and communication networks (IEEE C37.94 and others), including automatic switch-over between ring and chain topology.
- Reliable data transmission via PRP and HSR redundancy protocols
- Extensive cybersecurity functionality, such as role-based access control (RBAC), logging of security-related events, signed firmware, or authenticated IEEE 802.1X network access
- Simple, fast, and secure access to the device via a standard Web browser to display all information and diagnostic data, vector diagrams, single-line and device display pages
- Phasor Measurement Unit (PMU) for synchrophasor measured values and IEEE C37.118 protocol
- Time synchronization using IEEE 1588
- High-performance fault recording (buffer for a max. record time of 80 s at 8 kHz or 320 s at 2 kHz)
- Auxiliary functions for simple tests and commissioning

## Benefits

- Compact and low-cost line differential and distance protection
- Safety due to powerful protection functions
- Purposeful and easy handling of devices and software thanks to a user-friendly design
- Cybersecurity in accordance with NERC CIP and BDEW Whitepaper requirements
- Highest availability even under extreme environmental conditions by standard coating of the modules
- Full compatibility between IEC 61850 Editions 1, 2.0, and 2.1



Siemens  
Smart Infrastructure  
Electrification &  
Automation  
Mozartstraße 31 C  
91052 Erlangen,  
Germany

For the U.S. published by  
Siemens Industry Inc.

100 Technology Drive  
Alpharetta, GA 30005  
United States

Customer Support: <http://www.siemens.com/csc>

© Siemens 2020. Subject to changes and errors.

For all products using security features of OpenSSL, the following shall apply:

This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit ([www.openssl.org](http://www.openssl.org)), cryptographic software written by Eric Young ([eay@cryptsoft.com](mailto:eay@cryptsoft.com)) and software developed by Bodo Moeller.