



3F1Y030FCTP1

SIEMENS


CATALOG NO. 3F1Y030FCTP1 SERIAL NO. SERIES H 30 kVA 60 Hz 3 PHASE 4.7 % IMP AT 135 °C		<p>VOLTS 504 492 480 468 456 444 432</p> <p>CONNECT 1 2 3 4 5 6 7</p>
115 °C RISE 30 °C AVG. AMBIENT 200 °C TEMP CLASS 40 °C MAX. AMBIENT PRIMARY (H1 H2 H3) 480 V SECONDARY(X1 X2 X3) 240 V WINDING MATERIAL CU ENCLOSURE TYPE NEMA-3R WEIGHT 360 LBS ENERGY EFFICIENCY NEMA TP 1-2002		
SPACINGS BETWEEN ANY VENTILATED ENCLOSURE PANEL AND ANY ADJACENT WALL SHALL BE A MINIMUM OF 3 INCHES X6 = 120V CT, 5% OF KVA RATING MAXIMUM DO NOT INSTALL IN AREAS ACCESSIBLE TO PUBLIC NE PAS INSTALLER DANS DES ENDROITS ACCESSIBLES AU PUBLIC SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION MANUAL NEMA Class ANN Dry Type Transformer Siemens Industry, Inc. Norcross, GA		
		TYPE K

dsu0082e

REVISION	DATE	BY	DATE	BY
1	10/01/19	RM	07/06/08	CY

Confidential - Property of Siemens Industry, Inc. Building Technologies Division		
CUSTOMER		
ORDER NO.	DWG. NO.	1
	3F1Y030FCTP1	SH 1 OF 2

1:1 messam 2013/05/06 20:37



All Dimensions in inches

ENCLOSURE COLOR : ANSI 61 GREY – OUTDOOR

H.V.1. TERMINAL DETAIL

L.V.1. TERMINAL DETAIL

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR #14-4 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR #2/0-6 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT

Confidential – Property of
Siemens Industry, Inc.
Building Technologies Division

REVISION	DATE	BY	DATE	BY	CUSTOMER
		DRAWN	07/06/08	CY	
		CHEK'D			
1	HCN: 33300	10/01/19	RM	VERIF'D	ORDER NO. DWG. NO. 1
					3F1Y030FCTP1 SH 2 OF 2

1:1 messam 2013/05/06 20:37