





REVISION	DATE	BY	DATE	BY
		DRAWN	06/06/05	JW
		CHEK'D		
		VERIF'D		

Confidential - Property of Siemens Industry, Inc. Building Technologies Division		
CUSTOMER		
ORDER NO.	DWG. NO.	
	3F1Y030TP1	SH 1 OF 2

SIEMENS

CATALOG NO. 3F1Y030TP1 SERIAL NO. 30 kVA 60 Hz 3 PHASE 5.3 % IMP AT 170 °C 150 °C RISE °C AVG. AMBIENT 220 °C TEMP CLASS °C MAX. AMBIENT PRIMARY (H1 H2 H3) 480V V SECONDARY(X1 X2 X3) 240V V WINDING MATERIAL AL ENCLOSURE TYPE NEMA-3R WEIGHT 310 LBS ENERGY EFFICIENCY NEMA TP 1-2002	 <p style="text-align: center;">VOLTS</p> <p style="text-align: center;">1 2 3 4 5 6 7</p>	<div style="text-align: center;">  <p>UL LISTED</p> </div> <div style="text-align: center;"> <p>DRY TYPE TRANSFORMER</p> <p>77105 E112313</p> <p>TYPE K</p> </div> <div style="text-align: center;">  <p>VERIFIED Energy Performance</p> <p>VERIFIE' Performance Energetique</p> </div> <p style="font-size: small;">SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION MANUAL</p> <p style="font-size: x-small;">NEMA Class ANN Dry Type Transformer Siemens Industry, Inc. Norcross, GA dsu0082e</p>
--	---	---





All Dimensions in inches

ENCLOSURE COLOR : ANSI 61 GREY – OUTDOOR

H.V.1. TERMINAL DETAIL

L.V.1. TERMINAL DETAIL

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR #14-4 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR #2/0-6 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT

Confidential – Property of
Siemens Industry, Inc.
Building Technologies Division

REVISION	DATE	BY	DATE	BY
		DRAWN	06/06/05	JW
		CHEK'D		
		VERIF'D		

CUSTOMER

ORDER NO.

DWG. NO.

3F1Y030TP1

SH 2 OF 2

0.1 root 2011/01/11 12:52