



ELECTRONICALLY CONFIGURABLE

The new **SIRIUS signaling columns** can do much more than just shine a pretty light

Thanks to their professional signaling technology, the SIRIUS signaling columns ensure optimal visibility of your plant and thus increase its availability. They reliably signal different states and offer a variety of signaling levels and functions. In addition to making individual settings, you can also implement variable fill level displays or signaling over a wide area. The integrated acoustic element with volume control also makes it possible to use the system in zones where visibility is limited. The columns can be easily configured by IO-Link or via a USB interface. They can be mounted and deployed universally in industrial settings or buildings, on machines, assembly stations, charging points, ramps, shipping and packaging stations, conveyor belts and much more.

Your benefits:

- Maximum flexibility
- Efficient engineering
- Optimal visibility
- Extremely robust
- Increases plant value
- Easy selection for ordering



SIEMENS

The SIRIUS signaling columns can be individually configured:
color, light intensity and type, levels, and acoustics

Two sizes – eight variants:

Without acoustics 15 segments		Without acoustics 9 segments		With acoustics 15 segments		With acoustics 9 segments	
IO-Link				IO-Link			
8WD4615-5HH47		8WD4613-5HH47		8WD4615-5JH47		8WD4613-5JH47	
M12 plug, 4-pole		M12 plug, 4-pole		M12 plug, 4-pole		M12 plug, 4-pole	
24V standard				24V standard			
8WD4615-5HH37		8WD4613-5HH37		8WD4615-5JH37		8WD4613-5JH37	
M12 plug, 8-pole		M12 plug, 8-pole		M12 plug, 8-pole		M12 plug, 8-pole	

Suitable for outdoor and indoor use in protection classes IP66, IP69K, NEMA 4, 4X, 12, 13

Wide range of signaling variants:

- The individual mode allows to activate each of the segments separately
- Multicolor LEDs allow to set more than 1 M colors
- Different light effects: Continuous, Blinking (3/2/1 Hz), Flashing (1x/2x/3x), Rotating light (70 RPM)
- Signaling modes: autoscale, filling level, signal column, and individual
- Acoustic element: 10 adjustable tones, volume settable up to max. 105 dB



Further information: www.siemens.com/sirius-signaling-columns and www.siemens.com/sirius-command

Published by Siemens AG

Smart Infrastructure
 Electrical Products
 Werner-von-Siemens-Str. 48–50
 92224 Amberg, Germany

For the U.S. published by Siemens Industry Inc.

100 Technology Drive
 Alpharetta, GA 30005
 United States
 Article No.: SIEP-B10241-00-7600
 WS 07222.0
 © Siemens 2022

Subject to changes and errors. The information provided in this document contains descriptions or performance characteristics which, in case of actual use, do not always apply as described or which may change as a result of further development of the products. The desired performance characteristics are only binding if expressly agreed in the contract. Availability and technical specifications are subject to change without notice.

All product designations may be trademarks or product names of Siemens AG or supplier companies, the use of which by third parties for their own purposes may violate the rights of the owners.