

SPS IPC Drives 2018, Hall 11

New Sinamics G120X converter series specializing in infrastructure applications

- **New Sinamics converter family series optimized for pump and fan infrastructure applications**
- **0.75 to 630 kW power range allows operation with any motor**
- **Stable running under any network conditions thanks to integrated DC link reactor**
- **Sinamics G120X is digitalization-ready and can be linked directly to the cloud with Sinamics Connect 300**

Siemens will be presenting a brand new converter series at this year's SPS IPC Drives. The converters of the new Sinamics G120X series are especially suited for use in pump and fan applications in industries such as water/wastewater, building technology or also in industrial environments. With a power range of 0.75 to 630 kW, Sinamics G120X converters can be operated with any motor. The converters are at their most effective running with synchronous reluctance motors from Siemens. Sinamics G120X are configured throughout for cost-optimized and resource-saving operation across all voltages and supply networks, and their characteristic compact design saves space in the control cabinet. Although not featuring an additional output reactor, the converters enable motor cable lengths of up to 150 meters. The integrated safety functions are certified to SIL3.

Simple, reliable and efficient

The Sinamics G120X series offers outstanding ease of operation and is simple to commission using the Sinamics Smart Access Module and the IOP-2 operator panel. The converters can be selected and ordered using only a single purchase order number in the Siemens drive technology configurator. Their integrated DC link reactor enables Sinamics G120X converters to run with the utmost stability under all

network conditions. This robust, drip-proof new series comes in the form of a painted module as standard, with an additional 3C3 contaminant-resistant coating as an optional extra. A high C2 (optionally C1) EMC category and a protection rating of IP20 (optionally IP21 in UL open type) ensure that the converter can be reliably used in any kind of industrial environment. Sinamics G120X converters are in compliance with all relevant EU energy-saving standards, and offer an operating efficiency level of over 98 percent. Their comprehensive range of integrated application-specific functions such as Flux Reduction for adjustment in line with the actual load, Eco Mode which ensures best possible performance and minimal losses coupled with low dynamic loads and optimized output power, or Keep Running Mode to reduce speed prior to a shutdown.

Ready for digitalization

Sinamics G120X converters can be linked to MindSphere over Sinamics Connect 300, offering users the opportunity to analyze valuable operating data gathered from the converter, the drive train and the machine using the MindSphere app Analyze MyDrives. This enables the visualization and analysis of status information, providing users with valuable data which can be used as the basis for optimizing processes and maintenance strategies.



Siemens will be presenting a brand new converter series at this year's SPS IPC Drives. The converters of the new Sinamics G120X series are especially suited for use in pump and fan applications in sectors such as water/wastewater, building technology or also in industrial environments.

This press release and press pictures are available at www.siemens.com/press/PR2018110042DFEN

More information on Sinamics G120X is available at www.siemens.com/sinamics-g120x

More information on Siemens at the SPS IPC Drives 2018 is available at www.siemens.com/sps-ipc-drives and www.siemens.com/press/sps2018

Contact for journalists

Katharina Lamsa

Phone: +49 911 895-7975

E-mail: katharina.lamsa@siemens.com

Follow us on **social media**:

Twitter: www.twitter.com/MediaServiceInd and www.twitter.com/siemens_press

Blog: <https://blogs.siemens.com/mediaservice-industries-en>

Siemens AG (Berlin and Munich) is a global technology powerhouse that has stood for engineering excellence, innovation, quality, reliability and internationality for more than 170 years. The company is active around the globe, focusing on the areas of electrification, automation and digitalization. One of the largest producers of energy-efficient, resource-saving technologies, Siemens is a leading supplier of efficient power generation and power transmission solutions and a pioneer in infrastructure solutions as well as automation, drive and software solutions for industry. With its publicly listed subsidiary Siemens Healthineers AG, the company is also a leading provider of medical imaging equipment – such as computed tomography and magnetic resonance imaging systems – and a leader in laboratory diagnostics as well as clinical IT. In fiscal 2018, which ended on September 30, 2018, Siemens generated revenue of €83.0 billion and net income of €6.1 billion. At the end of September 2018, the company had around 379,000 employees worldwide. Further information is available on the Internet at www.siemens.com.