



REVISION	DATE	BY	DATE	BY
		DRAWN	08/03/17	CY
		CHEK'D		
		VERIF'D		

Confidential - Property of <b>Siemens Industry, Inc.</b> Building Technologies Division		
CUSTOMER		
ORDER NO.	DWG. NO.	
	1D1Y015FCTP1	SH 1 OF 2

SIEMENS

<p>CATALOG NO. 1D1Y015FCTP1</p> <p>SERIAL NO.</p> <p>15 kVA    60 Hz    1 PHASE</p> <p>3.4 % IMP AT 135 °C</p> <p>115 °C RISE    °C AVG. AMBIENT</p> <p>220 °C TEMP CLASS    °C MAX. AMBIENT</p> <p>PRIMARY ( H1 H3 H2 H4 )    240X480 V</p> <p>SECONDARY(X4 X2 X3 X1 )    120/240 V</p> <p>WINDING MATERIAL    CU</p> <p>ENCLOSURE TYPE NEMA-3R    WEIGHT 295 LBS</p> <p>ENERGY EFFICIENCY NEMA    TP 1-2002</p> <p>SPACINGS BETWEEN ENCLOSURE AND ANY ADJACENT WALL SHALL BE A MINIMUM OF 6 INCHES</p> <p>SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS DO NOT INSTALL IN AREAS ACCESSIBLE TO PUBLIC FOR INSTALLATION SEE INSTRUCTION MANUAL</p> <p>NEMA Class <b>ANN</b> Dry Type Transformer Siemens Industry, Inc. Norcross, GA</p>	<p>SERIES H</p> <p>1 PHASE</p> <p>°C AVG. AMBIENT</p> <p>°C MAX. AMBIENT</p> <p>240X480 V</p> <p>120/240 V</p> <p>CU</p> <p>TP 1-2002</p> <p>LISTED DISTRIBUTION TRANSFORMER 77US TYPE F</p> <p>UL LR 3902</p> <p>E112313</p>	 <p style="text-align: center;">HAM1006</p> <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th>VOLTS</th> <th>INPUT LINE ON H1 &amp; H4 CONNECT</th> </tr> </thead> <tbody> <tr> <td>504</td> <td>H2-1, H3-2</td> </tr> <tr> <td>492</td> <td>H3-2, H2-3</td> </tr> <tr> <td>480</td> <td>H2-3, H3-4</td> </tr> <tr> <td>468</td> <td>H3-4, H2-5</td> </tr> <tr> <td>456</td> <td>H2-5, H3-6</td> </tr> <tr> <td>444</td> <td>H3-6, H2-7</td> </tr> <tr> <td>432</td> <td>H2-7, H3-8</td> </tr> <tr> <td>252</td> <td>H2-1, H3-2</td> </tr> <tr> <td>240</td> <td>H2-3, H3-4</td> </tr> <tr> <td>228</td> <td>H2-5, H3-6</td> </tr> <tr> <td>216</td> <td>H2-7, H3-8</td> </tr> </tbody> </table> <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th>VOLTS</th> <th>CONNECT</th> <th>OUTPUT LINE</th> </tr> </thead> <tbody> <tr> <td>120</td> <td>X1-X3, X2-X4</td> <td>X1-X4</td> </tr> <tr> <td>240</td> <td>X2-X3</td> <td>X1-X4</td> </tr> <tr> <td>240/120</td> <td>X2-X3</td> <td>X1-X2-X4</td> </tr> </tbody> </table> <p style="text-align: center;">CONNECT H1 TO H3 AND H2 TO H4 FOR PARALLEL PRIMARY</p> <p style="text-align: center;">CONNECT H1 TO H3 AND H2 TO H4 FOR PARALLEL PRIMARY</p>	VOLTS	INPUT LINE ON H1 & H4 CONNECT	504	H2-1, H3-2	492	H3-2, H2-3	480	H2-3, H3-4	468	H3-4, H2-5	456	H2-5, H3-6	444	H3-6, H2-7	432	H2-7, H3-8	252	H2-1, H3-2	240	H2-3, H3-4	228	H2-5, H3-6	216	H2-7, H3-8	VOLTS	CONNECT	OUTPUT LINE	120	X1-X3, X2-X4	X1-X4	240	X2-X3	X1-X4	240/120	X2-X3	X1-X2-X4
VOLTS	INPUT LINE ON H1 & H4 CONNECT																																					
504	H2-1, H3-2																																					
492	H3-2, H2-3																																					
480	H2-3, H3-4																																					
468	H3-4, H2-5																																					
456	H2-5, H3-6																																					
444	H3-6, H2-7																																					
432	H2-7, H3-8																																					
252	H2-1, H3-2																																					
240	H2-3, H3-4																																					
228	H2-5, H3-6																																					
216	H2-7, H3-8																																					
VOLTS	CONNECT	OUTPUT LINE																																				
120	X1-X3, X2-X4	X1-X4																																				
240	X2-X3	X1-X4																																				
240/120	X2-X3	X1-X2-X4																																				





All Dimensions in inches

ENCLOSURE COLOR : ANSI 61 GREY – OUTDOOR

H.V.1. TERMINAL DETAIL

L.V.1. TERMINAL DETAIL

MECHANICAL TYPE LUGS INCLUDED  
SUITABLE FOR #14-2 CU/AL  
CONDUCTORS  
1 CONDUCTOR PER PHASE

MECHANICAL TYPE LUGS INCLUDED  
SUITABLE FOR #2/0-6 CU/AL  
CONDUCTORS  
1 CONDUCTOR PER PHASE

CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT

Confidential – Property of  
**Siemens Industry, Inc.**  
Building Technologies Division

REVISION	DATE	BY	DATE	BY	CUSTOMER
		DRAWN	08/03/17	CY	
		CHEK'D			
		VERIF'D			
					ORDER NO.
					DWG. NO. 1D1Y015FCTP1
					SH 2 OF 2

0.2 jwen 2010/01/21 13:27