



SIEMENS

CATALOG NO. 3F3Y225ESTP1 SERIAL NO. SERIES H 225 kVA 60 Hz 3 PHASE 4.8 % IMP AT 170 °C		<p>VOLTS 504 492 480 468 456 444 432</p> <p>CONNECT 1 2 3 4 5 6 7</p>
150 °C RISE °C AVG. AMBIENT 220 °C TEMP CLASS °C MAX. AMBIENT PRIMARY (H1 H2 H3) 480V V SECONDARY(X0 X1 X2 X3) 208Y/120V V WINDING MATERIAL AL ENCLOSURE TYPE NEMA-3R WEIGHT 1600 LBS ENERGY EFFICIENCY NEMA TP 1-2002		
SPACINGS BETWEEN ENCLOSURE AND ANY ADJACENT WALL SHALL BE A MINIMUM OF 6 INCHES ELECTROSTATIC SHIELD		<p>DRY TYPE TRANSFORMER 77105 E112313 LISTED</p> <p>TYPE K</p>
SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION MANUAL NEMA Class ANN Dry Type Transformer Siemens Industry, Inc. Norcross, GA		<p>VERIFIED Energy Performance Certification Energetique</p> <p>VERIFIE</p> <p>SEE INSTRUCTION MANUAL</p>



dsu0082e

REVISION	DATE	BY	DATE	BY
		DRAWN	06/04/19	RB
		CHEK'D		
		VERIF'D		

Confidential - Property of
Siemens Industry, Inc.
 Building Technologies Division

CUSTOMER	
ORDER NO.	DWG. NO.
	3F3Y225ESTP1
SH 1 OF 2	

0.2_jwen 2010/03/10 13:47




All Dimensions in inches

ENCLOSURE COLOR :ANSI 61 GREY – OUTDOOR

H.V.1. TERMINAL DETAIL

L.V.1. TERMINAL DETAIL

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR 350MCM-6 CU/AL
CONDUCTORS
2 CONDUCTORS PER PHASE



CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT COIL FACE

Confidential – Property of
Siemens Industry, Inc.
Building Technologies Division

REVISION	DATE	BY	DATE	BY
		DRAWN	06/04/19	RB
		CHEK'D		
		VERIF'D		

CUSTOMER	
ORDER NO.	DWG. NO. 3F3Y225ESTP1
SH 2 OF 2	

0.2 jwen 2010/03/10 13:47