



ENERGY AUTOMATION PRODUCTS

SICAM A8000 - Automation and remote terminal units

siemens.com/sicam-a8000

The SICAM A8000 is a modular device series designed specifically for telecontrol and automation applications. It provides a comprehensive solution for remote monitoring, control, and automation of energy systems across industries and infrastructure. The platform is highly versatile, offering integration of hardware and software with modular designs that allow customization based on specific use cases. The SICAM A8000 supports up to 200,000 data points, making it ideal for managing large-scale energy networks efficiently.

Highlights

- ✓ Increased EMC stability of up to 5 kV (IEC 60255), making it suitable for direct use in substations
- 🔍 Integrated short-circuit indicator functionality allows network monitoring
- 🧩 Modular design allows tailored application solutions
- 💡 Detachable display for maximum flexibility (applies to device CP-8010/12)
- ☁️ Cloud connectivity enables secure real-time data transfer for monitoring and analytics



Benefits

- High investment security through the use of international standards such as IEC 61850, IEC 60870 5 101/103/104
- Fulfils high cybersecurity requirements with the integrated crypto chip and IPSec encryption for secure data communication
- Time and cost savings thanks to easy installation and maintenance – plug and play
- Reduction in inventory costs due to the modular platform with versatile application options
- Adaptability to existing communication infrastructures using multiple interfaces and integrated LTE modem available

SIEMENS

SICAM A8000 – module types

- Processor modules (up to 14 interfaces)
- Power supplies (DC 24-60 V; 110-220 V; AC 230 V)
- Ethernet communication modules
- Expansion modules for max. 16 I/O lines
- Digital input module (DC 24 V; 48/60 V; 110 V; 220 V)
- Digital output module (DC 24-220 V; AC 110/230 V)
- Transistor output (DC 24-60 V)
- Analog input module
(-20/+20 mA; -10/+10 V; Pt 100)
- Analog output module
(-20/+20 mA; -10/+10 mA; -10/+10 V)
- Input current/voltage (1A / 5 A; LoPo; up to 250 V)

The universal digital and analog input/output modules can be plugged in any order and are suitable for the smallest spaces due to their module width of 30 mm.

Communication interfaces and protocols

- IEC 60870-5-101/-103/-104, Modbus RTU / TCP
- IEC 61850 Ed1/Ed2 Client & Server incl. GOOSE
- DNP3 Master/Slave serial, TCP/IP
- Further protocols on request
- CP-8010
 - 3xRJ45 (Eth) and 3x serial interfaces
 - Integrated ZigBee module to connect sensors
- CP-8012
 - 3xRJ45 (Eth) and 3x serial interfaces
 - Integrated LTE modem with GPRS fallback
 - Integrated ZigBee module to connect sensors
- CP-8031
 - 2x RJ45 (Eth) and 2x serial interfaces
- CP-8050
 - 2x RJ45 (Eth), 1x RS232 (RJ45), 1x RS485, 10x RJ45 (Eth) with CI-modules

Auxiliary voltage

- DC 24-60 V (12 W or 45 W)
- DC 110-220 V (12 W or 45 W)
- AC 230 V (45 W)
- Redundancy possible

Real-time clock

- +/- 2 ppm, time synchronization via NTP, SNTP

Inputs / outputs

- CP-8050: max. 2048 I/Os with up to 16 I/O lines, 8 expansion modules each

Electromagnetic compatibility

- IEC 60870-2-1, IEC 61010, IEC 60255-5, IEC 61000-4, EN 55022, CE marking

Temperature range

- From -40°C to +70°C

Housing specification

- Plastic housing for DIN rail mounting
- Dimensions CP-8010/12:
153x160x123 mm (W / H / D)
- Dimensions CP-8031/50, CI, PS and expansion modules: 30x132x124 mm (W / H / D)

Special features

- Data storage via SD memory card (storage of parameters and device firmware)
- Freely programmable user programs as per IEC 61131-3

Security standards

- IEC 62351 series
- BDEW white paper conformity
- IEC 62443-4-2 certified

Security features

- Integrated crypto chip
- IPsec encryption
- https protocol
- Firmware signature
- Security logbook

 [Online shop - Industry Mall](#)

 [Catalog: SICAM Substation Automation](#)

 [Webinar series: SICAM 8 - Power Automation Platform](#)

Siemens AG

Smart Infrastructure

Electrification & Automation

Mozartstrasse 31c

91052 Erlangen, Germany

Siemens Industry Inc.

3617 Parkway Lane

Peachtree Corners, GA 30092

United States

© Siemens 2025

Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract. For all products using security features of OpenSSL, the following shall apply: This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (www.openssl.org), cryptographic software written by Eric Young (eay@cryptsoft.com) and software developed by Bodo Moeller.