

Surge Protection Device (SPD) Externally mounted to Electrical Distribution Equipment

TPS 14

Transient Protection System for High Exposure
Applications - Externally Mounted Edition of
Field Proven, Integral TPS6

UL 1449 2nd Edition Revision (Feb 2007)
(UL 1449 Rev 2.5)
200kA SCCR
UL 1283

APPLICATIONS

- Service entrance High Exposure protection for externally generated surges
- 320kA is used for increased redundancy and is applicable for service entrance, distribution panel, and branch panel locations.
- 400kA is used for maximum redundancy and is applicable for service entrance, distribution panel, and branch panel locations.

SPECIFICATIONS

- Modes of Protection

Model	L-N	L-G	N-G
320kA	160kA	160kA	160kA
400kA	200kA	200kA	200kA
- EMI/RFI filtering: Active tracking up to -50db from 100kHz to 100MHz
- Less than 1/2 nanosecond response time
- Pulse life of 5,000 Category C impulses
- 200,000 AIC fuses
- UL 1449 2nd Edition listed for 200kA SCCR applications or below. In compliance with NEC Article 285.6



- Single TPS6 Style Replaceable Module
- Fast acting 40mm MOV's
- Relative humidity range: 0 - 95% non-condensing
- Operating frequency: 47 - 63Hz
- Operating temperature: -40°C to +65°C

SIEMENS

SPD FEATURES

- UL 1449 Second Edition Revision Effective Feb 9, 2007 (aka UL 1449 Rev 2.5)
- Designed and tested in accordance with IEEE C62.41.1, C62.41.2, and C62.45
- Patented TranSafe™ Circuitry Design incorporating thermal cutouts and surge rated fuses
- Multistage protection circuit
- Fast acting 40mm MOV's
- 5 Year Warranty

SPD FEATURES

- NEMA 12 Standard Enclosure:
 - Standard 18.0" x 14.5" x 6.5"
 - W/Disconnect 18.0" x 14.5" x 6.5"
 - Flushmount 14.0" x 14.0" x 6.0"
- Weight: 35 lbs.

STANDARD MONITORING

- LED Indicators
- Audible Alarm with Silence and Test Buttons
- Dry Contacts

AVAILABLE OPTIONS

- Surge Counter
- Flush Mount
- Remote Monitor
- Internal Disconnect
- NEMA3R, 4, and 4X (may increase enclosure size)

KEY BID SPECIFICATION ITEMS

SPD

UL 1449 Rev. 2.5, UL 1283, and cUL Listed
EMI/RFI Filtering
UL Suppression of 330V/700V
Modes of Protection L-N, L-G, N-G, and L-L

Surge Capacity:

Per Phase =	L-N	+	L-G
320kA	160kA		160kA
400kA	200kA		200kA

Category C High Tested

ORDERING INFORMATION


Catalog# **TPS 14**

Voltage Code

- A = 120/240V 1Ø 3W
- B = 240/120V 3Ø 4W
- C = 208Y/120V 3Ø 4W
- D = 240V 3Ø 3W
- E = 480Y/277V 3Ø 4W
- F = 480V 3Ø 3W
- G = 600V 3Ø 3W
- K = 380Y/220V 3Ø 4W
- L = 600Y/347V 3Ø 4W
- S = 400Y/230V 3Ø 4W

Surge Current (kA)

- 320
- 400



Options (*)

- R = Remote Monitor
- D = Disconnect
- 00 = NEMA 12
- 03 = NEMA 3R
- 04 = NEMA 4
- 4X = NEMA 4X
- F = Flush Mount
- S = Surge Counter

Example: TPSC14320S000D0 = 120/208 TVSS with a surge capacity of 320kA/Phase and surge counter and disconnect.

* When an option is not selected, include a zero (0) in the option field

Service Voltage and UL 1449 Rev. 2.5 Suppression Ratings

VOLTAGE CODE	SERVICE VOLTAGE	L-N	L-G	N-G	L-L	MCOV
A	120/240V 1Ø 3W	400	400	400	800	150
B	240/120V 3Ø 4W	400/800	400/800	400	800/1000	150/275
C	208Y/120V 3Ø 4W	330	330	330	600	150
D	240V 3Ø 3W		600		700	275
E	480Y/277V 3Ø 4W	600	600	600	1200	320
F	480V 3Ø 3W		1500		1200	640
G	600V 3Ø 3W		1800		1800	840
K	380Y/220V 3Ø 4W	600	600	600	1500	320
L	600Y/347V 3Ø 4W	1000	1000	1000	1800	420
S	400Y/230V 3Ø 4W	600	600	600	1200	320

Siemens Energy & Automation, Inc.
3333 Old Milton Parkway
Alpharetta, GA 30005

888.333.3545
info.sea@siemens.com

www.sea.siemens.com/power

©2008 Siemens Energy & Automation, Inc. All Rights Reserved
Siemens is a registered trademark of Siemens AG. Product names mentioned may be trademarks or registered trademarks of their respective companies. Specifications are subject to change without notice.