


SIEMENS

DRY TYPE TRANSFORMERS

NOTES:

1. ALL UNITS ARE UL LISTED AND DESIGNED IN ACCORDANCE WITH ANSI, NEMA, AND CSA STANDARDS.
2. THESE TRANSFORMERS UTILIZE A UL RECOGNIZED 180°C INSULATION SYSTEM, TEMPERATURE RISE AS INDICATED IN THE TABLE.
3. TRANSFORMERS ARE ENCAPSULATED WITH ELECTRICAL GRADE RESIN IN A NEMA 3R-RATED ENCLOSURE. BUILT IN ACCORDANCE WITH NEMA, ANSI, UL, AND CSA STANDARDS.
4. TRANSFORMERS FLOOR MOUNTED FOR INDOOR / OUTDOOR USE.
5. PAINT COLOR IS ANSI #61 GRAY.



KVA	TEMP. RISE C°	NET WT. LBS. ALUM. UNITS	NET WT. LBS. COPPER UNITS	HOUSING DIMENSIONS										
				A	B	C	D	E	F	G				
30	135	800	820	37.00	25.25	12.75	10.50	22.50	3.00	1.50				
45	135	805	830	37.00	25.25	12.75	10.50	22.50	3.00	1.50				
75	135	1005	1100	37.00	25.25	12.75	10.50	22.50	3.00	1.50				

KVA	QTY.	CATALOG NO.	VOLTAGE		TAPS	DRAWING
			PRIMARY	SECONDARY		
						<input type="checkbox"/> APPROVAL
						<input type="checkbox"/> RECORD
						<input type="checkbox"/> OTHER

CUST.	DWN. BY:	Siemens Industry, Inc.
	DATE:	
JOB	CHK. BY:	GENERAL PURPOSE TRANSFORMERS THREE-PHASE, 600 VOLTS CLASS, 60 HZ. RUGGED DUTY, ALUMINUM & COPPER WOUND
P.O.	DATE:	
TIE	APVD. BY:	
S.O.	DATE:	DWG. NO. J-22
		REV. C DATE 06/22/10