


New Siemens Compact Non-fusible Safety Switch

Features and Benefits

- 30 - 800A ratings
- Compact size reduces panel footprint requirement
- Meets UL 98 requirements
- All switches are able to be panel mounted. Catalog numbers CNFS361N, CNFS362N, and CNFS363N can also be DIN-rail mounted and can either be front or side operated with standard pistol handles.
- All short circuit protection ratings require the use of Class J fuses in the circuit.
- Quick make and break operation
- Options to have door mounted pistol handles with defeatable cover interlock or direct mounted handles.
- Handles are available in Type 1, 3R, 4/4X & 12 ratings
- All external handles and direct handles for 600-800A switches are padlockable with up to (3) padlocks with 5/16" hasps in the OFF position. Direct handles for 30-100A switches are padlockable with (1) padlock with 3/16" hasps in the OFF position.
- Load break and horsepower rated
- UL Listed under file #E201138 & CSA Certified under file #112964 or #703166

Type CNFS compact non-fusible switches

Switch Ampere Rating	Catalog Number	Max Horsepower Ratings			Short Circuit Rating	
		240V 3Ø AC	480V 3Ø AC	600V 3Ø AC	@ 480VAC	@ 600VAC
30	CNFS361N	10	20	25	100	100
60	CNFS362N	20	40	50	100	100
100	CNFS363N	20	50	50	100	25
200	CNFS364N	75	150	200	200	200
400	CNFS365N	125	250	350	200	200
600	CNFS366N	200	400	350	200	200
800	CNFS367N	200	500	500	100	100



**Published by
Siemens 2020**

Siemens Industry, Inc.
5400 Triangle Parkway
Norcross, GA 30092

Siemens Technical Support:
1-800-333-7421
info.us@siemens.com

Printed in USA-CP
Order No. SSFL-CNFS1-0320
All Rights Reserved
© 2020, Siemens Industry, Inc.
usa.siemens.com/switches

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.