

SPECIFICATIONS

GENERAL

SERVICE: 3PH 3W
 VOLTAGE: 480
 FREQUENCY: 60 Hz

STRUCTURE

NEMA TYPE: 1A
 PAINT: ANSI 61 GRAY

BUSBRACING:

65K AIC SYM

HORIZONTAL BUS

RATING: 1200A (3/8 X 2)
 MATERIAL: COPPER
 PLATING: TIN

VERTICAL BUS

RATING: 300A ISOLATED
 MATERIAL: COPPER
 PLATING: TIN

HORIZONTAL GROUND BUS

RATING: 300A (1/4 X 1)
 MATERIAL: COPPER
 PLATING: UNPLATED

INCOMING


SPLICE TO EXISTING

UL LABELS:

ALL UNITS/SECTIONS

GENERAL OPTIONS

NONE



| | | | | | |
|---|------------------|--|---|---------------------------------|--------------|
| A) RELEASED FOR PRODUCTION ECN 61769 RWB 10/16/14 | | | | NEXT ASS'Y *** | |
| AB) P5A00121347 RWB 04/23/15 | | | | TOOL NO. | TYPE OF TOOL |
| | | | | *** | *** |
| | | | | *** | *** |
| | | | | *** | *** |
| This print is the confidential property of Siemens Industry, Inc. It is not to be used or reproduced in any manner, nor submitted to any other parties for examination without prior approval of Siemens Industry, Inc. | DRAWN BY: RWB | SCALE: N/A | TITLE: FRONT ELEVATION 1200A H - 300A V BUS 12" BLANK SPACES | | |
| | CHKD BY: RWB | DATE: 10/16/14 | DWG. NO. D46752007 | | REV. AB |
| | APPRD BY: RWB | TOLERANCE UNLESS OTHERWISE SHOWN XX OR XXX ± .015 ANGULAR ± 2° | | F/N: X:\STD\D46\752007-A.DWG | |
| Siemens Industry, Inc. West Chicago, IL 60185-1655 | | | STYLE: **** | SHEET # 1 | |