



Totally Integrated Power

## Switchgear Type 8DJH for Secondary Distribution Systems up to 24 kV, Gas-Insulated



The 8DJH switchgear will impress you with its extensive scope of functions and diverse deployment possibilities. Simple transformer substations, customer transfer substations, and even circuit-breaker switchgear in industrial applications can be implemented easily with this switchgear type.



Flexibility during switchgear configuration is a decisive factor in secondary distribution. The modular switchgear design enables a variable configuration of functions – both within a panel block and also with more complex switchgear layouts. All of the individual panels and panel blocks can be extended as an option. Thus, with the 8DJH switchgear, practically any switching configuration can be implemented.



The hermetically sealed welded stainless steel switchgear vessel makes the parts of the 8DJH switchgear carrying high voltage insensitive to salty air, air humidity, dust and condensation. It prevents the ingress of dust and dirt, liquids, humidity and small animals. Additional test requirements, e. g. for


climate resistance and seismic safety verifies the overall high resilience of the switchgear.

### Your advantages

- Independent of environment and climate
- Maintenance-free
- Compact
- Safe for operators
- Cost-efficient
- Ecological
- Reliable and safe operation

## 8DJH, Medium-Voltage Switchgear

Product range (The following selection is not complete)



### Technical data of 8DJH

Rated						
Voltage	kV	7.2	12	15	17.5	24
Frequency	Hz	50/60	50/60	50/60	50/60	50/60
Short-duration power-frequency withstand voltage	kV	20	28*	36	38	50
Lightning impulse withstand voltage	kV	60	75	95	95	125
Normal current for ring-main feeders	A	400 or 630				
Normal current for busbar	A	630				
Normal current for circuit-breaker feeders	A	250 or 630				
Normal current for transformer feeders	A	200**				
Short-time withstand current, 1 s	50 Hz	max. kA	25	25	25	20
Short-time withstand current, 3 s		max. kA	20	20	20	20
Peak withstand current		max. kA	63	63	63	50
Short-circuit making current for ring-main feeders	50 Hz	max. kA	63	63	63	50
for circuit-breaker feeders		max. kA	63	63	63	50
for transformer feeders		max. kA	63	63	63	50
Short-time withstand current, 1 s	60 Hz	max. kA	25	25	25	21
Short-time withstand current, 3 s		max. kA	21	21	21	21
Peak current		max. kA	65	65	65	55
Short-circuit making current for ring-main feeders	60 Hz	max. kA	65	65	65	55
for circuit-breaker feeders		max. kA	65	65	65	55
for transformer feeders		max. kA	65	65	65	55

\* 42 kV according to some national requirements \*\* Depending on HV HRC fuse-link

### Performance features

- Type-tested according to IEC 62271-200
- Sealed pressure system with SF<sub>6</sub> filling for the entire service life
- Safe-to-touch enclosure and standardized connections for plug-in cable terminations
- 3-pole, gas-insulated switchgear vessel for switching devices and busbar
- Panel blocks and single panels available (optionally extensible)
- Switching devices: three-position switch-disconnector (OPEN – CLOSED – EARTHED), switch-fuse combination for distribution transformer protection, vacuum circuit-breaker with three-position disconnector
- Earthing function of switching devices generally make-proof
- Metal-enclosed, partition class PM
- Loss of service continuity category for switchgear: LSC 2
- Internal arc classification (option):
  - IAC A FL 21 kA, 1 s
  - IAC A FLR 21 kA, 1 s

### Dimensions of 8DJH

Dimensions			Dimensions in mm
Width	W	Ring-main feeders Transformer feeders Circuit-breaker feeders RRT / RRL block	310 or 500 430 430 or 500 1,050
Height	H	Panels without low-voltage compartment Panels with low-voltage compartment (option) Switchgear with pressure absorber (option)	1,200 / 1,400 / 1,700 1,400–2,600 1,800–2,600
Depth	D	Standard switchgear Switchgear with pressure absorber (option)	775 890

© 2016 Siemens. Subject to changes and errors.  
The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.

Siemens AG  
Energy Management  
Medium Voltage & Systems  
Postfach 3240  
91050 Erlangen, Germany  
[www.siemens.com/8DJH](http://www.siemens.com/8DJH)

Article No. IC1000-G320-A253-V7-7600  
Printed in Germany  
01.16 1.0 | 1400/74871

Read the  
QR code  
to see further  
typicals of this  
switchgear!

