



Standard Dimensions in Millimeters (Inches)

SHAFT DIA	TOLERANCE	
200 (7.87)	+0.037 +0.017	(+0.0015) (+0.0007)

Notes:

1. The FS1.5 conduit boxes is rotatable and has a removable bottom plate.
2. L (C) = Length of motor from drive end of shaft to end of non-drive end of motor.
3. Machines operate in one direction only.
4. Shims may be necessary under motor feet for direct connection.
5. The standard shaft seal is rated IP55.

Standard Dimensions in Millimeters (Inches) \*IEC Designations (NEMA)

Frame	Speed	A (2E)	B (2F)	C (BA)	L (C)	- (LE)	E (N-W)	- (R)	- (S)	- (T)	D (U)	- (ES)	Approx. Max. Wt. kgs (lbs)
630/2	6 Pole +	1320 (51.96)	1600 (62.99)	335 (13.19)	3140 (123.62)	2900 (114.17)	280 (11.02)	185 (7.28)	45 (1.77)	25 (0.98)	200 (7.87)	232.5 (9.15)	11900 (26200)
634/6	6 Pole +	1320 (51.96)	1800 (70.87)	335 (13.19)	3380 (133.07)	3140 (123.62)	280 (11.02)	185 (7.28)	45 (1.77)	25 (0.98)	200 (7.87)	232.5 (9.15)	13750 (30300)

**Certification:** Customer \_\_\_\_\_ P.O. \_\_\_\_\_ S.O. \_\_\_\_\_ Item \_\_\_\_\_  
 HP \_\_\_\_\_ RPM \_\_\_\_\_ Frame \_\_\_\_\_ PH/HZ/Volts 3/ \_\_\_\_\_ / \_\_\_\_\_ Terminal Box Size FS1.5   
 Customer Tag # \_\_\_\_\_ By \_\_\_\_\_ Date \_\_\_\_\_  
 Comments \_\_\_\_\_  
 Not for construction, installation or application purposes unless certified.