



**SIEMENS**  
Ingenuity for life

## Technical data

Selection data, synchronous-reluctance drive system with SINAMICS G120 for 50 Hz and 400 V line voltage



SIMOTICS reluctance motor (VSD4000 line)

SINAMICS G120 frequency converter

Rated power (kW)	Frame size	Torque (Nm)	Rated current (A)	Rated speed (rpm)	Max. speed SIMOTICS GP/ SIMOTICS SD (rpm)	Motor code	Motor Article No.			Frame size	Power Module Article No.*		
							1FP1	5	14-...		Frame size	Power Module Article No.*	...
0.55	80M	3.5	1.6	1,500	3,200/3,200	60017	1FP1	■	14-0DB22-1 ...	A	6SL3210-1PE11-8	■	L1
		4.8	2.2	1,500	3,200/3,200	60018	1FP1	■	14-0DB32-1 ...			A	6SL3210-1PE12-3
0.75	80M	2.4	2.1	3,000	- /6,000	60019	1FP1	5	14-ODF22-1 ...	A	6SL3210-1PE12-3		
		7.0	2.8	1,500	3,200/3,200	60021	1FP1	■	14-0EB02-1 ...			A	6SL3210-1PE13-2
1.1	80M	3.5	3.0	3,000	- /6,000	60020	1FP1	5	14-ODF32-1 ...	A	6SL3210-1PE13-2		
		9.5	3.8	1,500	3,200/3,200	60022	1FP1	■	14-0EB42-1 ...			A	6SL3210-1PE14-3
1.5	90M	4.8	4.0	3,000	- /6,000	60023	1FP1	5	14-0EF02-1 ...	A	6SL3210-1PE14-3		
		14.0	5.3	1,500	3,200/3,200	60025	1FP1	■	14-1BB02-1 ...			A	6SL3210-1PE16-1
2.2	90L	7.0	5.8	3,000	- /6,000	60024	1FP1	5	14-0EF42-1 ...	A	6SL3210-1PE16-1		
		19.1	7.1	1,500	3,200/3,200	60026	1FP1	■	14-1BB12-1 ...			A	6SL3210-1PE18-0
3.0	112M	9.5	7.2	3,000	- /6,000	60027	1FP1	5	14-1BF12-1 ...	A	6SL3210-1PE18-0		
		25.5	10.0	1,500	3,200/3,200	60028	1FP1	■	14-1BB22-1 ...			A	6SL3210-1PE21-1
4.0	112M	12.7	9.8	3,000	- /6,000	60029	1FP1	5	14-1BF22-1 ...	A	6SL3210-1PE21-1		
		35.0	12.6	1,500	3,200/3,200	60030	1FP1	■	14-1CB02-1 ...			B	6SL3210-1PE21-4
5.5	132S	17.5	12.9	3,000	- /5,600	60032	1FP1	5	14-1CF02-1 ...	B	6SL3210-1PE21-4		



SIMOTICS reluctance motor (VSD4000 line)

SINAMICS G120 frequency converter

Rated power (kW)	Frame size	Torque (Nm)	Rated current (A)	Rated speed (rpm)	Max. speed SIMOTICS GP/ SIMOTICS SD (rpm)	Motor code	Motor Article No.		Frame size	Power Module Article No.*			
							1	2		1	2		
7.5	132M	47.5	17.1	1,500	3,200/3,200	60031	1FP1	■	14-1CB22-1 ...	B	6SL3210-1PE21-8	■	LO
	132S	23.8	17.3	3,000	- / 5,600	60033		5	14-1CF12-1 ...				
11	160M	70.0	25.0	1,500	3,000/3,200	60034	1FP1	■	14-1DB22-1 ...	C	6SL3210-1PE22-7	■	LO
		35.0	24.5	3,000	- / 4,800	60036		5	14-1DF22-1 ...				
15	160L	95.0	34.0	1,500	3,000/3,200	60035	1FP1	■	14-1DB42-1 ...	C	6SL3210-1PE23-3	■	LO
	160M	47.5	34.0	3,000	- / 4,800	60037		5	14-1DF32-1 ...				
18.5	180M	118.0	42.0	1,500	2,610/3,000	60011	1FP1	■	14-1EB22-1 ...	D	6SL3210-1PE23-8	■	LO
	160L	59.0	41.5	3,000	- / 4,800	60038		5	14-1DF42-1 ...				
22	180L	140.0	49.0	1,500	2,610/3,000	60012	1FP1	■	14-1EB42-1 ...	D	6SL3210-1PE24-5	■	LO
		70.0	50.0	3,000	- / 4,600	60014		5	14-1EF22-1 ...				
30	200L	191.0	68.0	1,500	2,610/3,000	60013	1FP1	■	14-2AB52-1 ...	D	6SL3210-1PE26-0	■	LO
		96.0	68.0	3,000	- / 4,500	60015		5	14-2AF42-1 ...				
37	225S	235.0	79.0	1,500	- / 3,000	60039	1FP1	5	14-2BB02-1 ...	E	6SL3210-1PE28-8	■	LO
	200L	118.0	82.0	3,000	- / 4,500	60016			14-2AF52-1 ...				
45	225M	286.0	96.0	1,500	- / 3,000	60040	1FP1	5	14-2BB22-1 ...	E	6SL3210-1PE31-1	■	LO
		143.0	99.0	3,000	- / 4,500	60041			14-2BF22-1 ...				

Motor series	■
SIMOTICS GP – aluminum frame	0
SIMOTICS SD – cast iron frame	5

EMV filter	■
Non-filtered	U
Class A filter	A

\* In addition to the Power Module, the Control Unit and possibly further components are required

Other converters in the SINAMICS family perfectly coordinated with the SIMOTICS reluctance motor:



SINAMICS S120 SINAMICS G120X SINAMICS G110M SINAMICS G120D

Published by

Siemens AG

Digital Industries

Motion Control

P.O. Box 31 80

91050 Erlangen, Germany

For the U.S. published by

Siemens Industry Inc.

Large Drives Applications

100 Technology Drive

Alpharetta, GA 30005, United States

siemens.com/reluctancedrivesystem

Article No. PDLT-T10138-00-7600

TH 455-181163 DA 0319

© Siemens 2019

Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract. All other designations in this document may represent trademarks whose use by third parties for their own purposes may violate the proprietary rights of the owner.