



Notes:

1. Main conduit box may be rotated in steps of 90°. A removable bottom plate is supplied on the FS1 conduit box. A 5.0 N.P.T. is supplied on the CI2 and CI3 conduit boxes.
2. C = Length of motor from drive end of shaft to end of standard fan housing.
3. V = (N-W)-0.25" = length of shaft available for coupling.
4. Machines may rotate in either direction.
5. Shims may be necessary under motor feet for direct connection.
6. Short shaft is for direct connection.
7. Adding a rotating labyrinth seal to the drive end does not change any dimensions.
8. Adding a ground brush increases BA & C by:
4 Pole & Slower: 2.50"
9. Adding a ground brush with rotating labyrinth seals increases BA & C by:
4 Pole & Slower: 2.50"

Standard Dimensions in Inches

Shaft	Frame	Speed	B	BA _{8,9}	C _{8,9}	E	2F	N ₇	(N-W)	R	S	U	V ₃	ES	Approx. Ship Wt. (Lbs)
Short	880	4 Pole & Slower	66.1	12.0	112.0	18.7	55.13	10.4	10.0	4.803	1.25	5.5	9.75	8.0	20000

Certification: Customer _____ P.O. _____ S.O. _____ Item _____
 HP _____ RPM _____ Frame _____ PH/Hz/Volts 3/_____/_____
 By _____ Date _____
 Comments _____

CGZA0_880_4plusPL_AF_ROT
Revision 00
03/04/13