

**RECIPROCATING PRODUCTS****HHE-VG****Reciprocating Process Compressor**

**Our first HHE-class compressor was installed more than 50 years ago. Continuous advancements in technology have allowed us to enhance the HHE's reputation as a highly reliable, heavy-duty process compressor. With more than 3,000 units serving in applications around the world, the HHE process compressor has proven to be an outstanding choice for a variety of applications.**

**Rugged Performer**

Designed to API-618 specifications, the HHE-VG is available in standard stroke sizes from 10 to 15 inches (254-381 mm) with up to 10 throws.

For long-lasting reliability, the HHE-VG frame is engineered to the highest standards. The fine-grain, cast iron frame provides maximum stability through the use of internally ribbed walls and integral cross-member bearing saddle supports located between each crankthrow. The frame's rigid design is further enhanced with precision spacer blocks and tie rods at each bearing point. This greatly

reduces distortion caused by gas and inertia forces. To ensure precise bearing alignment, the bearing saddles are bored in a single set-up.

**Optimized Design, Precision-Built**

Every HHE-VG is built with optimized crank angles and a minimum number of crank throws, resulting in minimal unbalanced forces and moments on the foundation. Available with up to ten throws, the design flexibility doesn't limit the HHE to an even number of crank throws. The result of this variable crank angle design is a compressor that requires minimum foundation size and expense, reduced drive-train torsional stresses, and reduced motor current pulsation and power costs. The crankshaft is forged from high tensile strength alloy steel that is fully stress-relieved and heat-treated. All journals and crankpins are precision-ground and polished to exacting tolerances.

Rugged, precision-machined tri-metal main and crankpin bearings are generously sized and micro-babbit coated for best run-in and long-lasting service. Bearings are provided on both

sides of each crankthrow and doubled on the drive end. All bearings are forced-lubricated per API-618 specifications. Connecting rods are die-forged steel with rifle-drilled passages for positive lubrication of the crosshead pin and bearings.

The flanged crosshead is designed for error-free assembly, ensuring maximum reliability through the hydraulic pre-stressing of the critical piston-to-crosshead bolting. Hydraulic tensioning reduces labor and maintenance downtime while increasing safety and reliability. The crosshead flange is firmly secured to the piston rod by a hydraulically tensioned nut and the flange is then attached to the crosshead using six hydraulically tensioned studs. The design employs an adjusting ring on the nose of the crosshead to facilitate adjustment of piston rod run-out without having to re-shim the crosshead shoes. A spacer provides a simple, one-time adjustment of piston-to-cylinder end clearance. The hydraulics are located in the tensioning tool instead of the piston nut where an O-ring failure might otherwise

necessitate torching through the rod to disassemble the joint. An air-motor driven hydraulic pump, tensioning devices and piston rod alignment tools are provided.

All frame and distance piece inspection and service openings are extra large to permit easy access. Bolting for frame-to-frame extension, and distance piece-to-cylinder is external, making tensioning easy and accurate.

### Outstanding Cylinder Design and Selection

Each cylinder is designed with the capability of loading the frames maximum allowable continuous rod load. All cylinder bolting, piston nut, and valve differential pressures meet this design criteria. This will permit future flexibility if process conditions change or the compressor is reapplied for another application.

With experience in virtually every type of service, our cylinders provide outstanding service and reliability. Our engineering expertise will ensure that each cylinder built for your application will provide maximum performance and reliability with minimum maintenance cost. Cylinder materials include nodular iron, cast steel, fabricated carbon or stainless steel, and forged steel. Most cylinders are available for either lubricated or non-lubricated service.

### Dimensions


Dimensions provided are typical, basis API Type B distance pieces. For Types C & D distance pieces, add 32 inches (81 cm) to the width dimension and 16 inches (41 cm) to the rod removal distance.

## Specifications

Maximum HP	13,125 (9,787 kW)
Standard Strokes	10 to 15 inch (254 to 381 mm)
Number of Throws	Up to 10
Cylinder Bore Range	5 to 44.5 inch (127 to 1,130 mm) max bore
Standard Double-Acting	

### HHE-VG Typical Length (L) Dimension

Throws	1	2	3	4	5	6	7	8	9	10
Inches	69	95	122	149	175	202	228	255	281	308
Centimeters	174	241	309	377	445	512	579	646	714	781



For a complete list of products and services, visit [dresser-rand.com](http://dresser-rand.com) or contact the following:

**Dresser-Rand Reciprocating Compressor Engineering Center of Excellence**  
100 Chemung Street  
Painted Post, NY 14870 USA  
Tel: (Int'l +1) 607-937-2011  
Fax: (Int'l +1) 607-937-2905

**Dresser-Rand High Speed Reciprocating Compressor Business Unit**  
West Memorial Place 1  
15375 Memorial Drive, Suite 700  
Houston, Texas 77079 USA  
Tel: (Int'l +1) 713-354-6100  
Fax: (Int'l +1) 713-354-5822  
Email: [GFC@dresser-rand.com](mailto:GFC@dresser-rand.com)

### Regional Headquarters

**The Americas**  
West Memorial Place 1  
15375 Memorial Drive, Suite 700  
Houston, Texas 77079 USA  
Tel: (Int'l +1) 713-354-6100  
Fax: (Int'l +1) 713-354-5822

**EMEA**  
(Europe, Middle East & Africa)  
Dresser-Rand S.A.  
31 Boulevard Winston Churchill  
Cedex 7013  
Le Havre 76080, France  
Tel: (Int'l +33) 2-35-25-5225  
Fax: (Int'l +33) 2-35-25-5366/5367

**Asia-Pacific**  
Dresser-Rand Asia Pacific Sdn Bhd  
Unit 9-4, 9th Floor  
Bangunan Malaysian Re  
17 Lorong Dungun  
Damansara Heights  
50490 Kuala Lumpur, Malaysia  
Tel: (Int'l +60) 3-2093-6633  
Fax: (Int'l +60) 3-2093-2622

This brochure comprises a general overview of the Dresser-Rand business products described herein. It is solely for informational purposes, does not represent a warranty or guarantee of the information contained herein, and is not to be construed as an offer to sell or solicitation to buy. Contact Dresser-Rand business for detailed design and engineering information suitable to your specific applications. Dresser-Rand business reserves the right to modify its products and related product information at any time without prior notice.