

A Siemens Inspiro Sofia metro train is shown from a front-quarter perspective, traveling on a track. The train is white with a light blue accent on the front. The background shows a clear sky and some trees. A white sign with the number '04' is visible on the right side of the track.

SIEMENS

Ingenuity for life

Inspiro Sofia

20 three-car metro trains


In September 2015, the operator of Bulgaria's Sofia Metro, MEAD, awarded an order to Siemens AG to supply 20 metro trains. The order includes the option for an additional ten trains.

The three-car trains are manufactured in collaboration with partner Newag SA and are intended for use on the new Line 3. The trains are expected to go into operation from 2019.

The vehicles are from the proven Inspiro family, which is already in operation in Warsaw. The Inspiro platform was developed with a special emphasis on low energy consumption, optimized maintenance, disabled friendliness, and environmental considerations. At the end of its service life, up to 95 percent of the rolling stock can be recycled.

The driver's cabin and passenger area are air-conditioned for maximum comfort.

The open and bright design of the interior area guarantees a pleasant ride. Logitudinal seats and four wide doors on each side of the car ensure maximum passenger capacity and rapid boarding and exiting at the stations.



Technical data

Train configuration	Mc-T-Mc
Wheel arrangement	Bo'Bo'+ 2'2'+ Bo'Bo'
Car body material	Aluminum
Track gauge	1,435 mm
Train length over couplers	60,008 mm
Width of car over door sill	2,650 mm
Floor height above top of rail	1,100 mm
Maximum axle load	Approx. 12 t
Vehicle capacity (at 6 passengers/m ²)	617, including 110 seated
Passenger doors per car	2 x 4 sliding-plug doors
Door width	1,400 mm
Max. operating speed	80 km/h
Power supply	1,500 V DC / pantograph

- Car bodies are made of welded aluminum profiles in a lightweight design.
- The rolling stock complies with stringent fire safety regulations per EN 45545 and is equipped with a fire alarm system in the passenger area and the equipment cabinets.
- The floor is a weight-saving, sound-absorbent composite cork-aluminum plate.
- Two compact air-conditioning units per car ensure comfortable air-conditioning in the passenger area. Separate air-conditioning systems are provided for both drivers' cabs.
- To ensure a high level of availability, the vehicles are equipped with a bogie-oriented traction system and mechanical brake system.

- The state-of-the-art traction system can provide electrodynamic braking almost down to standstill. This feature provides a non-wearing service brake under normal operating conditions and also improves stopping accuracy in the stations.
- Train control is assured by a reliable MVB bus based on the proven Sibas 32[®] system.
- Each train is equipped with an event recorder.

Published by
Siemens Mobility GmbH

Otto-Hahn-Ring 6
81739 Munich
Germany

contact.mobility@siemens.com

Article No. MOUT-B10025-01-7600
Printed in Germany
Dispo 21720, SIMC-0000-50868
TH 325-180788 DA 08180.5

Subject to changes and errors.

The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.

Inspiro[®] is a trademark of Siemens AG.
Any unauthorized use is prohibited. All other designations in this document may represent trademarks whose use by third parties for their own purposes may violate the proprietary rights of the owner.