



SIEMENS

Ingenuity for life

Avenio M tram – Ulm, Germany

Twelve five-section,
100 percent low-floor vehicles

Siemens is one of the leading suppliers of integrated mobility solutions for urban areas and of vehicles for local, regional, and main-line transportation.

Ulm's municipal utility (Stadtwerke Ulm) ordered twelve trams from Siemens for its local line network. The new trams will be used on the future Line 2. This new Avenio M tram series profits from the reliable multi-articulated concept and the proven experiences with Avenio trams in The Haag and Munich. In both cities, the trams are already in successful operation.

Each of the trams delivered from April 2018 consists of five modules, meaning three bogies and two intermediate vehicle modules. Combined, the modules build a bright walk through passenger area. The trams are equipped with a driver's cabin as well as an assistant driver's cabin each.

Avenio M also set new benchmark regarding safety – the tram meets all the actual fire protection norms and is equipped with for the upcoming crash requirements. The coalition warning system „Siemens Tram Assistant“ supports the driver to avoid accidents.

In July 2018, Avenio M Ulm tram was honored with the Red Dot Award in the category Product Design 2018.



Technical data

Vehicle type / platform	100% low-floor, tram vehicle / Avenio M
Configuration	5-car (uni-directional operation)
Wheel arrangement	Bo' 2' Bo'
Car body material	Aluminum welded
Length	31,470 mm
Width	2,400 mm
Entrance height / floor height	305 mm / 380 mm above bogies
Motor power rating	4 x 120 kW
Power supply	DC 750 V
Maximum speed	70 km/h
Track gauge	1,000 mm
Capacity (4 P/m ²)	185 incl. 69 seats
Tare weight	approx. 38 tons

Technical properties / special features

- Excellent passenger comfort achieved by open, bright interior with seats and handrails optimally designed according to ergonomic criteria, air-conditioning for driver's cab and passenger area, and optimized running characteristics with three suspension stages
- Convenient access for passengers with large multi-function areas for wheelchairs and strollers and quick passenger flow ensured by wide doors (four double doors 1,300 mm, two single doors 800 mm)
- Weight-optimized vehicle design compliant with limited axle load in existing networks, also ensures a maximum passenger capacity (welded aluminum car body)
- Perfect riding comfort and optimized wheel-track wear achieved by bogies with installation of drive unit and mechanical coupling of the wheels in longitudinal direction, minimal unsprung masses, and optimized bogie-to-car-body coupling
- Highest safety ensured by four independent brake systems enhanced by a special braking assistance system in the vehicles to safely run on the long slopes in Ulm's networks, providing a fallback layer in the event of vehicle power supply failure
- Compliant with newest safety standards (EN15227, EN 45545)
- Electro-dynamic brakes to provide comfortable and smooth braking to standstill
- Redundant design of traction equipment provides maximum reliability and fail-safe performance (two IGBT pulse inverters, two traction control units SIBAS® 32)



Driver's cabin providing a vast view



Wide gangways



Bright passenger area

Published by
Siemens Mobility GmbH

Otto-Hahn-Ring 6
81739 Munich
Germany

contact.mobility@siemens.com

Article No. MOUT-B10001-01-7600
Printed in Germany
Dispo 21720 SIMC-0000-50799
gB 180232 07180.5

Avenio® and SIBAS® are registered trademarks of Siemens AG.

Subject to changes and errors.
The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.