

SIEMENS

SIPROTEC

Voltage and Frequency Protection 7RW80

V4.6

IEC 61850

PIXIT

Preface, Table of Contents

Applications

1

Basics

2

Mapping

3

Literature, Index

Disclaimer of Liability

We have checked the text of this manual against the hardware and software described. However, deviations from the description cannot be completely ruled out, so that no liability can be accepted for any errors or omissions contained in the information given.

The information given in this document is reviewed regularly and any necessary corrections will be included in subsequent editions. We appreciate any suggestions for improvement.

We reserve the right to make technical improvements without notice.

Document Release V04.10.01
Edition 10.2011

Copyright

Copyright © Siemens AG 2010

Dissemination or reproduction of this document, or evaluation and communication of its contents, is not authorized except where expressly permitted. Violations are liable for damages. All rights reserved, particularly for the purposes of patent application or trademark registration.

Registered Trademarks

SIPROTEC, SINAUT, SICAM and DIGSI are registered trademarks of Siemens AG. Other designations in this manual might be trademarks whose use by third parties for their own purposes would infringe the rights of the owner.

Preface

Purpose of this manual

In this Manual, you will find the

- ❑ Specification of the applications of the IEC 61850 interface
- ❑ General information about the effects of configuration of your device to the different Logical Nodes and DOIs
- ❑ Mapping of device relevant information to Logical Nodes as part of protocol IEC61850

Target audience

This manual is intended mainly for all persons who configure, parameterize and operate a SIPROTEC Devices 7RW80.

Scope of validity of this Manual

SIPROTEC 7RW80, Version 4.6

Standards

This document has been created according to the ISO 9001 quality standards.

Further Support

If you have questions about SIPROTEC IEC 61850 interface, please contact your Siemens sales representative.

Table of contents

1	Applications	7
1.1	General	8
1.2	Association model	9
1.3	Server model	10
1.4	Data set model	11
1.5	Substitution model	12
1.6	Setting group control model	13
1.7	Reporting model	14
1.7.1	Unbuffered Report	14
1.7.2	Buffered Report	15
1.8	Logging model	17
1.9	Generic substation model	18
1.10	Transmission of sample values model	20
1.11	Control model	21
1.12	Time and time synchronisation model	23
1.13	File transfer model	24
1.14	General items	25
1.15	TISSUES	26
2	Basics	29
2.1	General	30
2.2	Effects of Configuration on the Logical Nodes	32
2.2.1	Function parameters	32
2.2.2	Function Parameters	32
2.3	Allocation of Logical Nodes to Logical Devices	34
2.4	Logical Node LLN0	37
2.4.1	Logical Device PROT	37
2.4.2	Logical Devices MEAS, DR and EXT	38
2.4.3	Logical Device CTRL	39
2.5	DOI Behavior	40
2.5.1	Logical Device PROT	40
2.5.2	Logical Devices MEAS, CTRL, DR and EXT	41

3	Mapping	43
3.1	Device (LPHD1, CALH1)	44
3.1.1	Error with a summary alarm and Alarm summary event	45
3.2	Oscillographic Fault Records (RDRE1)	46
3.3	Overexcitation (Volt/Hertz) Protection (PVPH1, PVPH2)	48
3.4	Jump of Voltage Vector (GAPC1)	51
3.5	Voltage Protection 27, 59 (PTUVx, PTOVx)	53
3.5.1	Undervoltage Protection 27 (PTUV1)	53
3.5.2	Undervoltage Protection 27 (PTUV2)	55
3.5.3	Undervoltage Protection $V_{p<}$ (PTUV3)	57
3.5.4	Overvoltage Protection 59 (PTOV1)	59
3.5.5	Overvoltage Protection 59 (PTOV2)	61
3.5.6	Overvoltage Protection $V_{p>}$ (PTOV3)	63
3.6	Frequency protection 81 O/U (PTUFx, PTOFx)	65
3.6.1	Frequency protection 81-1 U (PTUF1)	65
3.6.2	Frequency protection 81-2 U (PTUF2)	67
3.6.3	Frequency protection 81-3 U (PTUF3)	69
3.6.4	Frequency protection 81-4 U (PTUF4)	71
3.6.5	Frequency protection 81-1 O (PTOF1)	73
3.6.6	Frequency protection 81-2 O (PTOF2)	75
3.6.7	Frequency protection 81-3 O (PTOF3)	77
3.6.8	Frequency protection 81-4 O (PTOF4)	79
3.7	Synchronism and Voltage Check 25 (RSYNx)	81
3.8	Three-pole tripping 52 Breaker (XCBR1)	83
3.9	Tripping Logic of the Entire Device (PTRC1)	86
3.10	Measurement (MMXU1, MSQ11)	88
3.10.1	Measures (MMXU1)	88
3.10.2	Measured values, symmetrical components (MSQ11)	91

Literature

Index

Applications

Contents

This chapter specifies the protocol implementation extra information for testing (PIXIT) of the IEC 61850 interface in SIPROTEC 7RW80 V4.6.

1.1	General	8
1.2	Association model	9
1.3	Server model	10
1.4	Data set model	11
1.5	Substitution model	12
1.6	Setting group control model	13
1.7	Reporting model	14
1.8	Logging model	17
1.9	Generic substation model	18
1.10	Transmission of sample values model	20
1.11	Control model	21
1.12	Time and time synchronisation model	23
1.13	File transfer model	24
1.14	General items	25
1.15	TISSUES	26

1.1 General

This chapter specifies the protocol implementation extra information for testing (PIXIT) of the IEC 61850 interface in SIPROTEC 7RW80 V4.6.

It is based on the service subset definition given in the protocol implementation conformance statement (PICS), which is specified within the user manual *SIPROTEC 4 Ethernet Module EN 100 IEC 61850 Electrical Interface 100 MBit, Manual /1/*.

The following applicable ACSI service models are specified:

- Association model
- Server model
- Data set model
- Substitution model
- Setting group control model
- Reporting model
- Logging model
- Generic substitution model
- Transmission of sample values model
- Control model
- Time and time synchronisation model
- File transfer model
- General items

Together with the PICS and the MICS the PIXIT forms the basis for a conformance test according to IEC 61850-10.

The mapping between the IEC 61850 server data model and the SIPROTEC specific data is specified in Chapter 3.

1.2 Association model

Description	Value / Clarification
Maximum number of clients that can set-up an association simultaneously	5 with IEC 61850 Protocol Update Version EN100 V04.02 and lower 6 with IEC 61850 Protocol Update Version EN100 V04.03 and higher
Lost connection detection time range (default range of TCP_KEEPALIVE is 1 – 20 seconds)	10 seconds
Is authentication supported	N
What called association parameters are necessary for successful association ?	Transport selector Y Session selector Y Presentation selector Y AP Title ANY AE Qualifier ANY Where Y means: as defined within the ICD-File ANY means: any value accepted
What is the maximum and minimum MMS PDU size ?	Max MMS PDU size 32768 Min MMS PDU size
What is the typical startup time after a power supply interrupt ?	15 SECONDS
<additional items>	

1.3 Server model

Description	Value / Clarification
Which analogue value (MX) quality bits are supported (can be set by server) ?	Validity: Y Good, Y Invalid, N Reserved, Y Questionable Y Overflow Y OutofRange N BadReference N Oscillatory Y Failure Y OldData N Inconsistent Y Inaccurate Source: Y Process N Substituted Y Test Y OperatorBlocked
Which status value (ST) quality bits are supported (can be set by server) ?	Validity: Y Good, Y Invalid, N Reserved, Y Questionable N BadReference Y Oscillatory Y Failure Y OldData N Inconsistent N Inaccurate Source: Y Process Y Substituted Y Test Y OperatorBlocked
What is the maximum number of data values in one GetDataValues request ?	Not restricted; depends on the max. MMS PDU size given above.
What is the maximum number of data values in one SetDataValues request ?	Not restricted; depends on the max. MMS PDU size given above. No Data Attribute within our object directory is writable with the service SetDataValues.
<additional items>	

1.4 Data set model

Description	Value / Clarification
Maximum number of data elements in one data set	Not limited by an internal configuration parameter. It depends on the available memory.
How many persistent data sets can be created by one or more clients ?	64 data sets for each LD. It depends on the available memory.
How many non-persistent data sets can be created by one or more clients ?	10 data sets. It depends on the available memory.
additional items:	
Maximum number of data sets	Could not be defined, it depends on the available memory space. In principle, this information it not necessary from type conformance testing standpoint.

1.5 Substitution model

This service will not be supported (see also *SIPROTEC 4 Ethernet Module EN 100 IEC 61850 Electrical Interface 100 MBit, Manual /1/*).

1.6 Setting group control model

Description	Value / Clarification
What is the number of supported setting groups for each logical device ?	Setting groups available for LLN0 only in LD PROT. The number of supported setting groups is 1 or 4, it depends on the given configuration. Specified in the ICD-File.
What is the effect of when and how the non-volatile storage is updated ? (compare IEC 61850-8-1 §16.2.4)	Just SelectActiveSG service will supported according to PICS.
<additional items>	

1.7 Reporting model

1.7.1 Unbuffered Report

Description	Value / Clarification
The supported trigger conditions are	Y Integrity Y Data change Y Quality change Y Data update Y General Interrogation
The supported optional fields are	Y Sequence-number Y Report-time-stamp Y Reason-for-inclusion Y Data-set-name Y Data-reference N Buffer-overflow N EntryID Y Conf-rev Y Segmentation
Can the server send segmented reports ?	Y
Mechanism on second internal data change notification of the same analogue data value within buffer period (Compare IEC 61850-7-2 §14.2.2.9)	Send report immediately
Multi client URCB approach (Compare IEC 61850-7-2 §14.2.1)	All clients can access all URCB's
additional items:	
Interrupt of general interrogation	Running GI could not be interrupted. If a new GI request occurs during a running GI, the current GI will be finished first before the second GI request will be processed.
Integrity period	Configurable ≥ 1 second;
Dynamic URCB reservation after an abort of the client/server association	Reservation of the URCB is lost. After a re-establishment of the association the URCB reservation has to be done by the client before. This behavior is implemented to avoid unnecessary memory residuals if temporarily client associations (e.g. for maintenance) are established.
Configured URCB reservation after an abort of the client/server association	Reservation of the URCB is not lost.

1.7.2 Buffered Report

Description	Value / Clarification
The supported trigger conditions are	Y Integrity Y Data change Y Quality change Y Data update Y General Interrogation
The supported optional fields are	Y Sequence-number Y Report-time-stamp Y Reason-for-inclusion Y Data-set-name Y Data-reference Y Buffer-overflow Y EntryID Y Conf-rev Y Segmentation
Can the server send segmented reports ?	Y
Mechanism on second internal data change notification of the same analogue data value within buffer period (Compare IEC 61850-7-2 §14.2.2.9)	Buffer the Entry Send report if the report is enabled
Multi client BRCB approach (Compare IEC 61850-7-2 §14.2.1)	All clients can access all BRCB's
What is the format of EntryID ?	First 2 Byte : Integer Last 6 Bytes: BTime6 time stamp
What is the buffer size for each BRCB or how many reports can be buffered ?	About 1 MB are available for the buffering. Each BRCB has an extension attribute Memory that display the percentage of those 1 MB that have been reserved/forseen for its own entries. Default amount 1 MB/(2*Number of logical devices)
additional items:	
Interrupt of general interrogation	Running GI could not be interrupted. If a new GI request occurs during a running GI, the current GI will be finished first before the second GI request will be processed.
Integrity period	Configurable >=1 second;
Dynamic BRCB reservation after an abort of the client/server association	Reservation of the BRCB has been fixed with TISSUE 453. The value of the attribute ResvTms delivers the time interval during which the reservation is still active after the connection has been lost. In case a BRCB is still reserved, and a client connects with the same IP address as the one used during the reservation, then the BRCB attribute can be written by this client without prior setting the ResvTms attribute as long as the reservation timer has not expired.

<p>Configured BRCB reservation after an abort of the client/server association</p>	<p>Reservation of the BRCB is not lost for BRCBs that have been pre-associated to a specific client (pre-association defined with means of the CLientLN element with the BRCB instantiation in the SCD file). Reservation of a BRCB is lost for BRCBs, that have not been pre-associated to a specific client, after the expiration of the reservation timer set with the ResvTms attribute. In case ResvTms is not set (backward compatibility), ResvTms will get a default value for all preconfigured BRCBs that are not pre-associated to a specific client.</p>
<p>Optional use of a flow control for transmitting history of a BRCB</p>	<p>As specified in the IEC61850-7-2, transmission of entries may required some times, depending of the amount of entries that have to be transmitted. Therefore, the SIPROTEC has an optional flow control feature to accelerate the transmission of the entries: each BRCB has an extended attribute MaxOutReports that can be set from the associated-client to change the transmission strategy of the entries. The number ordered will then be transmitted as long as they exist in the buffer; the server then reset the attribute to 0 and wait for the client to set it again in order to continue the history transmission with MaxOutReports entries. The attribute only influences the flow control of entries while dealing with the history, and not after the history transmission has completed.</p>

1.8 Logging model

This service will not be supported (see also *SIPROTEC 4 Ethernet Module EN 100 IEC 61850 Electrical Interface 100 MBit, Manual /1/*).

1.9 Generic substation model

Description	Value / Clarification
What is the behavior when one subscribed GOOSE message isn't received or syntactically incorrect ?	The telegram will be discarded (i.e not forwarded to the application) since it is corrupt or syntactically incorrect and therefore not readable. The data objects will be declared as invalid after a timeout detection since no telegram have been received by the application.
What is the behavior when a subscribed GOOSE message is out-of-order ?	Error message will be stored into the error buffer (could be accessed by EN100 web-server).
What is the behavior when a subscribed GOOSE message is duplicated ?	The sequence number given in the GOOSE-message is out-of-order. Error message will be stored into the error buffer (could be accessed by EN100 web-server).
additional items:	
Maximum number of GOOSE messages which could be sent	<= 16 ; It depends on the available memory.
Maximum number of GOOSE messages which could be received	<= 128 ; It depends on the available memory.
Interpretation of GOOSE messages at subscriber side	<ol style="list-style-type: none"> 1. Received GOOSE data objects without assigned quality attribute are interpreted as invalid. 2. Received GOOSE data objects which quality attribute are set to questionable are changed to invalid.
GOOSE subscriber behavior in case of missing GOOSE messages	<p>After a GOOSE multicast application association has been interrupted, the reception of a valid GOOSE telegram is required to validate the state of this GOOSE association again.</p> <p>However, the IED tolerates a missing telegram as long as the next telegram (expected n, received n+1) is received within the time allowed to live time out detection (the time allowed to live timeout detection occurs after 2*TAL).</p>
GOOSE subscriber behaviour in case of multiple GOOSE messages	If a message is received twice or more, the IED already reports an error after the second reception. Therefore, network configuration error can be more easily tracked.
What is the behavior when a GOOSE header parameter is mismatching with the expected one? (datSet, goID, confRev, numDatSetEntries, number of allData)	Error message will be stored into the error buffer (could be accessed by EN100 web-server). The received telegram with the mismatched attribute will be discarded: It has not been subscribed.
What is the behavior when a timeAllowedToLive is 0?	Error message will be stored into the error buffer (could be accessed by EN100 web-server) since the timeAllowedToLive expired. All expected data objects will be declared as invalid.

What is the behavior when there is an out-of-order entry in the allData?	The confRev attribute in the header guarantees that the allData entries are in the correct order. Therefore, it's necessary to check the confRev attribute. There is no chance to detect such an out-of-order.
What is the behavior when no telegram is received within a TAL timeout?	To avoid an incorrect timeout detection, the subscriber detects a timeout after a period of 2×TAL. The information is then declared as questionable, oldData.
What is the behavior when a GOOSE header parameter goCBRef is mismatching with the expected one?	Since the goCBRef shall be unique stationwide, the received telegram with the mismatched goCBRef will be discarded: it has not been published. In that case only the timeout detection will set the data to invalid.
What is the behavior when a GOOSE header parameter APPID is mismatching with the expected one?	The APPID is a link layer parameter. It is used as a filter on link layer. If the APPID is mismatching, the telegram will therefore be discarded on link layer without notifying the application. Only the timeout detection will set the data to invalid.
What is the behavior when a GOOSE header parameter t is not increasing?	The t parameter is not checked. Therefore it doesn't lead to any error detection.
What is the behavior when numDatSetEntries and number of allData are inconsistent?	The telegram is discarded since it is corrupt (not well formed). After the timeout detection (no telegram forwarded to the application) the data objects are declared invalid.

1.10 Transmission of sample values model

Compare the "Implementation Guidelines for Electrical Current and Voltage Transducers according to IEC 60044-7/8 with Digital Output according to IEC 61850-9-2; Version 1.0; as specified by ABB, Areva, Landis+Gyr, OMICRON and SIEMENS

This service will not be supported (see also *SIPROTEC 4 Ethernet Module EN 100 IEC 61850 Electrical Interface 100 MBit, Manual /1/*).

1.11 Control model

Description	Value / Clarification
What control models are supported ?	Y Status-only Y Direct-with-normal-security N Sbo-with-normal-security Y Direct-with-enhanced-security Y Sbo-with-enhanced-security
Is Time activated operate (operTm) supported	N
What is the behavior when the test attribute is set in the SelectWithValue and/or Operate request ?	Will be acknowledged with negative response. The AddCause attribute will be set to "not supported"
What are the conditions for the time (T) attribute in the SelectWithValue and/or Operate request ?	Time attribute is not relevant.
Is "operate-many" supported ?	N
Is pulse configuration supported ?	N
What check conditions are supported ?	Y Synchrocheck Y Interlock-check
What service error types are supported ?	Y Instance-not-available Y Instance-in-use Y Access-violation Y Access-not-allowed-in-current-state Y Parameter-value-inappropriate Y Parameter-value-inconsistent Y Class-not-supported Y Instance-locked-by-other-client Y Control-must-be-selected Y Type-conflict Y Failed-due-to-communications Y Constraint failed-due-to-server-constraint

What additional cause diagnosis are supported ?	N Blocked-by-switching-hierarchy Y Select-failed Y Invalid-position Y Position-reached Y Parameter-change-in-execution Y Step-limit Y Blocked-by-Mode Y Blocked-by-process Y Blocked-by-interlocking Y Blocked-by-synchrocheck Y Command-already-in-execution N Blocked-by-health Y 1-of-n-control Y Abortion-by-cancel Y Time-limit-over N Abortion-by-trip Y Object-not-selected
additional items:	
What additional cause diagnosis extensions are supported ?	Y Plausibility_error Y Parameter_setting_invalid Y Hardware_error Y System_overload Y Internal_fault Y Command_sequence_error
Changing the control services by configuration	N
Inconsistency between Select and (Oper or cancel)	Oper or cancel will be acknowledged with negative response if inconsistencies to the select request are detected. The following attributes will not be checked in this case: T (Time)
Cancel request could be sent after an operate request.	Y
Format of the control time stamp attribute ?	TimeStamp instead of EntryTime acc. to the 7-2 Errata List.
Negative response for select request could be performed only	If test mode is activated or If the selection is always done.

1.12 Time and time synchronisation model

Description	Value / Clarification
What kind of quality bits are supported ?	N LeapSecondsKnown Y ClockFailure Y ClockNotSynchronized
What kind of quality accuracy bits are supported ?	Y Invalid N Unspecified
What is the behavior when the time synchronization signal/messages are lost ?	The quality attribute "ClockFailure" will be set to TRUE after a configured time period.
What is the behaviour when the time synchronisation messages indicate that the stratum is greater than 3?	A stratum with a value greater than 3 with the SNTP time synchronization messages indicates that the time server has a questionable synchronisation. It might also indicate that no GPS connection are available. Therefore the time quality attribute "ClockNotSynchronized" will be set to TRUE as long as the stratum content is greater than 3.
additional items:	
What is the behavior at start up time when a time synchronization via SNTP is configured ?	The "ClockNotSynchronized" attribute is set to TRUE as long as no time synchronization is established.

1.13 File transfer model

Description	Value / Clarification
What is structure of files and directories?	Directory name / COMTRADE / *; Directory name / LD / *; Files according to the comtrade standard.
What is the resulting behavior if no file specification is present in the file directory request?	If no file specification is present in the directory request, all files are returned - not only the files in the root directory.
Is the IETF FTP protocol also implemented ?	N
Directory names are separated from the file name by	"/"
The maximum file name size including path (default 64 chars)	64
Are directory/file name case sensitive	Case sensitive
Maximum file size	Not limited by implementation or configuration. Depends on available memory.
additional items:	
Maximum number of clients that can use the FTP service simultaneously	1
Maximum number of files that can be accessed simultaneously	1

1.14 General items

Description	Value / Clarification
IED behavior when the Logical Device is blocked : LLN0.Mod.stVal = blocked	Unlike the definition of the Data Objects "Mod/Beh" in IEC 61850-7-4, outputs to the process will be generated. Details to this behavior are specified in <i>SIPROTEC 4 Ethernet Module EN 100 IEC 61850 Electrical Interface 100 MBit, Manual /1/</i>
additional items:	
GOOSE Proxy object	To be able to subscribe Data over GOOSE, Proxy Objects are added into the object directory. Typically, they are Data of GGIO logical nodes: SPCSOxx, DPCSOxx, ISCSOxx. The Data Attributes of those Data are ctlVal, q and t. The control model associated to those Data is status-only. They are not controllable from an IEC61850 client, and their function is only to enable the GOOSE subscribing.
What is the type of the attribute actVal in the BCR (Binary Counter Reading) CDC?	The type is integer 32 (INT32).

1.15 TISSUES

Topic	TISSUE -No.	Link	Description	Impact of Interoper.
Object Model	120	http://tissue.iec61850.com/tissue.aspx?issueid=120	Type - Mod.stVal and Mod.ctlVal	-
	146	http://tissue.iec61850.com/tissue.aspx?issueid=146	CtxInt	-
	173	http://tissue.iec61850.com/tissue.aspx?issueid=173	Ctl modelling harmonization	-
	234	http://tissue.iec61850.com/tissue.aspx?issueid=234	New type CtxInt	x
Services	377	http://tissue.iec61850.com/tissue.aspx?issueid=377	DeleteDataSet response-	-
	276	http://tissue.iec61850.com/tissue.aspx?issueid=276	File Services Negative Responses	-
	183	http://tissue.iec61850.com/tissue.aspx?issueid=183	GetNameList error handling	x
	165	http://tissue.iec61850.com/tissue.aspx?issueid=165	Improper Error Response for GetDataSetValues	x
	116	http://tissue.iec61850.com/tissue.aspx?issueid=116	GetNameList with empty response?	x
Reporting	474	http://tissue.iec61850.com/tissue.aspx?issueid=474	GI for URCB	-
	453	http://tissue.iec61850.com/tissue.aspx?issueid=453	Reporting & Logging model revision	x
	438	http://tissue.iec61850.com/tissue.aspx?issueid=438	EntryTime base should be GMT	-
	349	http://tissue.iec61850.com/tissue.aspx?issueid=349	BRCB TimeOfEntry has two definitions	x
	348	http://tissue.iec61850.com/tissue.aspx?issueid=348	URCB class and report	x

Reporting	344	http://tissue.iec61850.com/tissue.msp?issueid=344	TimeOfEntry misspelled	-
	335	http://tissue.iec61850.com/tissue.msp?issueid=335	Clearing of BufOvl	x
	332	http://tissue.iec61850.com/tissue.msp?issueid=332	Ambiguity in use of trigger options	x
	329	http://tissue.iec61850.com/tissue.msp?issueid=329	Reporting and BufOvl	x
	322	http://tissue.iec61850.com/tissue.msp?issueid=322	Write Configuration attribute of BRCBs	
	301	http://tissue.iec61850.com/tissue.msp?issueid=301	SqNum in Buffered Reports	-
	300	http://tissue.iec61850.com/tissue.msp?issueid=300	Attribute Resv in BRCB	x
	298	http://tissue.iec61850.com/tissue.msp?issueid=298	Type of SqNum	x
	297	http://tissue.iec61850.com/tissue.msp?issueid=297	Sequence number	x
	278	http://tissue.iec61850.com/tissue.msp?issueid=278	EntryId not valid for a server	x
	275	http://tissue.iec61850.com/tissue.msp?issueid=275	Confusing statement on GI usage	x
	191	http://tissue.iec61850.com/tissue.msp?issueid=191	BRCB: Integrity and buffering reports	x
	190	http://tissue.iec61850.com/tissue.msp?issueid=190	BRCB: EntryId and TimeOfEntry	x
	177	http://tissue.iec61850.com/tissue.msp?issueid=177	Ignoring OptFlds bits for URCB	-
	52	http://tissue.iec61850.com/tissue.msp?issueid=52	Ambiguity GOOSE SqNum	x
49	http://tissue.iec61850.com/tissue.msp?issueid=49	BRCB TimeOfEntry?	x	
Control Model	46	http://tissue.iec61850.com/tissue.msp?issueid=46	Synchro check cancel	x
	44	http://tissue.iec61850.com/tissue.msp?issueid=44	AddCause - Object not sel	x
	30	http://tissue.iec61850.com/tissue.msp?issueid=30	control parameter T	x

Basics

Contents

This chapter contains general information about the effects of device configuration on Logical Nodes and DOIs.

2.1	General	30
2.2	Effects of Configuration on the Logical Nodes	32
2.3	Allocation of Logical Nodes to Logical Devices	34
2.4	Logical Node LLN0	37
2.5	DOI Behavior	40

2.1 General

The protocol IEC 61850 was developed to define a standard that can be internationally employed for the transmission of power automation system data.

This cross national standard enables an interoperability between automation systems and devices made by different manufacturers.

The devices and high voltage bay control units of the SIPROTEC 4 series can be equipped with an Ethernet module EN100 via which the protocol IEC 61850 is interpreted.

The configuration of the protocol and the integration of the device with redundant IEC 61850 interfaces in your network are performed via the configuration system DIGSI.

For details please refer to the manuals:

- ❑ *SIPROTEC 4 Ethernet Module EN 100 IEC 61850 Electrical Interface 100 MBit, Manual /1/ and*
- ❑ *SIPROTEC 4 System Description /2/.*



Note

The following definitions are taken mainly from standard IEC 61850, Technical Specification IEC TS 61850-2.

Logical Devices

LD Logical Devices represent a functional structuring of the LN Logical Nodes of a SIPROTEC device.

The following Logical Devices are present:

- ❑ Logical Device Protection PROT
- ❑ Logical Device Measurement MEAS
- ❑ Logical Device Disturbance Recorder DR
- ❑ Logical Device Control CTRL
- ❑ Logical Device Extended EXT

Each LD contains LN LLN0 and LN LPHD1.

The allocation of the Logical Nodes to the Logical Devices is listed in Chapter 2.3.

Logical Node LN

Smallest part of a function that exchanges data. A logical node is an object defined by its data and methods.

Data object instance DOI

A Data object is part of a logical node object representing specific information for example status of measurement. From an object-oriented point of view, a data object is an instance of a data class. Specific data classes carry the semantic within a logical node.

Data attribute instance DAI

A Data attribute defines the name (semantic), format, range of possible values, and representation of values while being communicated.

Annunciation types via GOOSE

Generic Object Oriented Substation Event

A GOOSE report enables high speed trip signals to be issued with a high probability of delivery.

The following types of information can be configured via GOOSE.

- External single point indication O/O
- External single point indication I/O
- External double point indication
- External double point indication, fast
- External operational measured values
- External metered values

2.2 Effects of Configuration on the Logical Nodes

2.2.1 Function parameters

Depending on the configuration of the function parameters the functions of the SIPROTEC are enabled or disabled. If a function is disabled, the corresponding Logical Node is not available.

The following Logical Nodes are always available:

Logical Device Protection: LLN0, LPHD1, XCBR1, PTRC1

Logical Device Measurement: LLN0, LPHD1, MMXU1, MSQ1

Logical Device Control: LLN0, LPHD1, CALH1

2.2.2 Function Parameters

The following table shows which Logical Nodes are available when setting the corresponding function parameter.

The setting (-) implies that no corresponding LN is available.

Table 2-1 SIPROTEC 7RW80 - Effects of Function parameters to the Logical Nodes

No.	Function	Setting	Logical Nodes
103	Setting Group Change Option		No effect
104	Oscillographic Fault Records	Disabled	-
		Enabled	RDRE1
143	24 Overexcit. Protection (Volt/Hertz)	Disabled	-
		Enabled	PVPH1, PVPH2
146	Jump of Voltage Vector	Disabled	-
		Enabled	GAPC5
150	27, 59 Under/Overvoltage Protection	Disabled	-
		Enabled	PTUV1, PTUV2, PTUV3 PTOV1, PTOV2, PTOV3
152	VT broken wire supervision		No effect

Table 2-1 SIPROTEC 7RW80 - Effects of Function parameters to the Logical Nodes (Forts.)

No.	Function	Setting	Logical Nodes
154	81 Over/Underfrequency Protection	Disabled	-
		Enabled	PTOF1 – PTOF4, PTUF1 – PTUF4
145	Load Restoration		No effect
161	25 Function group 1 Synchronism and Voltage Check	Disabled	-
		SYNCHROCHECK	RSYN1
182	74TC Trip Circuit Supervision	Disabled	-
		2 Binary Inputs	DOI CirSpv, LN XCBR LD PROT
		1 Binary Input	DOI CirSpv, LN XCBR LD PROT
617	Port B usage		No effect

2.3 Allocation of Logical Nodes to Logical Devices

All Logical Nodes (LN) are allocated to Logical Devices (LD). The following tables show this allocation and the DOIs available for each LN.

LD PROT

The Logical Device PROT (Protection) contains the following LNs:

Table 2-2 LD PROT - Logical Nodes

LN	Function	DOI
LLN0	General	Mod, Beh, Health, NamPlt, OpTmh
PTRC1	General device pickup General OFF	Mod, Beh, Health, NamPlt, Str,Tr,FinTr
XCBR1	52 Breaker Three-pole tripping	Mod, Beh, Health, NamPlt, Loc, OpCnt, Pos BlkOpn, BlkCls, CBOpCap SumSwARs1, SumSwARs2, SumSwARs3
PTUV1 PTUV2 PTUV3	27 Undervoltage Protection	Mod, Beh, Health, NamPlt, Str, Op
PTOV1 PTOV2 PTOV3	59 Overvoltage Protection	Mod, Beh, Health, NamPlt, Str, Op
PTUF1 PTUF2 PTUF3 PTUF4	81 Underfrequency Protection	Mod, Beh, Health, NamPlt, Str, Op, BlkV
PTOF1 PTOF2 PTOF3 PTOF4	81 Overfrequency Protection	Mod, Beh, Health, NamPlt, Str, Op, BlkV
PVPH1 PVPH2	Overexcitation Protection (U/f)	Mod, Beh, Health, NamPlt, Str, Op
GAPC5	Jump of Voltage Vector	Mod, Beh, Health, NamPlt, Str, Op
LPHD1	Device	PhyNam, PhyHealth, Proxy

LD MEAS

The Logical Device MEAS (Measurement) contains the following LNs:

Table 2-3 LD MEAS - Logical Nodes

LN	Function	DOIs
LLN0	General	Mod, Beh, Health, NamPlt
MMXU1	Operational measured values	Mod, Beh, Health, NamPlt, Hz, PPV, PhV
MSQI1	Measured values, symmetrical components	Mod, Beh, Health, NamPlt, SeqV
LPHD1	Device	PhyNam, PhyHealth, Proxy

LD DR

The Logical Device DR (Disturbance Recorder) contains the following LNs:

Table 2-4 LD DR - Logical Nodes

LN	Function	DOIs
LLN0	General	Mod, Beh, Health, NamPlt
RDRE1	Oscillographic Fault Records	Mod, Beh, Health, NamPlt, RcdMade, RcdStr FltNum, GriFltNum
LPHD1	Device	PhyNam, PhyHealth, Proxy

LD CTRL

The Logical Device CTRL (Control) contains the following LNs:

Table 2-5 LD CTRL - Logical Nodes

LN	Function	DOIs
LLN0	General	Mod, Beh, Health, NamPlt, LEDRs, Loc
RSYN1	25 Function group 1	Mod, Beh, Health, NamPlt, Rel, VInd, AngInd, HzInd, SynPrg, DifVClc, DifHzClc, DifAngClc
CALH1	Error with a summary alarm and Alarm summary event	Mod, Beh, Health, NamPlt, GrAlm, GrWrn, ErrBoard1, ErrBoard2, ErrBoard3, ErrBoard4, ErrBoard5, ErrBoard6, ErrBoard7
LPHD1	Device	PhyNam, PhyHealth, Proxy, CtlNum, DevStr

LD EXT

The Logical Device EXT (Extended) contains the following LNs:

Table 2-6 LD EXT - Logical Nodes

LN	Function	DOIs
LLN0	General	Mod, Beh, Health, NamPlt, LEDRs, Loc
LPHD1	Device	PhyNam, PhyHealth, Proxy, CtlNum

The Logical Nodes of the switching (and userdefined) objects will be created by DIGSI during the parameterization of your SIPROTEC device.

MICS, Model Implementation Conformance Statement, shows the assignment of the DOIs; you can use DIGSI to print the MICS.

2.4 Logical Node LLN0

2.4.1 Logical Device PROT

LLN0.Mod

No.	Information					
52	At Least 1 Protection Funct. is Active (ProtActive)	0	1	1	1	1
	Test mode (Test mode)	x	0	0	1	1
	Stop data transmission (DataStop)	x	0	1	0	1
LLN0.Mod.stVal		5	1	2	3	4

device annunciation / setting: 1 - ON / TRUE
0 - OFF / FALSE
x - irrelevant

IEC Status Mod.stVal: 1 - ON
2 - BLOCKED
3 - TEST
4 - TEST/BLOCKED
5 - OFF

LLN0.Beh

No.	Information					
52	At Least 1 Protection Funct. is Active (ProtActive)	0	1	1	1	1
	Test mode (Test mode)	x	0	0	1	1
	Stop data transmission (DataStop)	x	0	1	0	1
LLN0.Beh.stVal		5	1	2	3	4

device annunciation / setting: 1 - ON / TRUE
0 - OFF / FALSE
x - irrelevant

IEC Status Beh.stVal: 1 - ON
2 - BLOCKED
3 - TEST
4 - TEST/BLOCKED
5 - OFF

LLN0.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
LLN0.Health.stVal		3	1

device annunciation: 1 - ON
0 - OFF

IEC Status Health.stVal: 1 - OK
2 - WARNING
3 - ALARM

2.4.2 Logical Devices MEAS, DR and EXT

LLN0.Mod

No.	Information				
51	Device is Operational and Protecting (Device OK)	x	x	x	x
	Test mode (Test mode)	1	1	0	0
	Stop data transmission (DataStop)	1	0	1	0
LLN0.Mod.stVal		4	3	2	1

device annunciation / setting: 1 - ON / TRUE
0 - OFF / FALSE
x - irrelevant

IEC Status Mod.stVal: 1 - ON
2 - BLOCKED
3 - TEST
4 - TEST/BLOCKED
5 - OFF

LLN0.Beh

No.	Information					
51	Device is Operational and Protecting (Device OK)	0	1	1	1	1
	Test mode (Test mode)	x	0	0	1	1
	Stop data transmission (DataStop)	x	0	1	0	1
LLN0.Beh.stVal		5	1	2	3	4

device annunciation / setting: 1 - ON / TRUE
0 - OFF / FALSE
x - irrelevant

IEC Status Beh.stVal: 1 - ON
2 - BLOCKED
3 - TEST
4 - TEST/BLOCKED
5 - OFF

LLN0.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
LLN0.Health.stVal		3	1

device annunciation: 1 - ON
0 - OFF

IEC Status Health.stVal: 1 - OK
2 - WARNING
3 - ALARM

2.4.3 Logical Device CTRL

LLN0.Mod

No.	Information					
55	Reset Device (Reset Device)	1	1	1	1	1
51	Device is Operational and Protecting (Device OK)	1	1	1	1	0
	Test mode (Test mode)	1	1	0	0	0
	Stop data transmission (DataStop)	1	0	1	0	0
LLN0.Mod.stVal		4	3	2	1	5

device annunciation / setting: 1 - ON / TRUE
0 - OFF / FALSE
x - irrelevant

IEC Status Mod.stVal:

1 - ON
2 - BLOCKED
3 - TEST
4 - TEST/BLOCKED
5 - OFF

LLN0.Beh

No.	Information					
55	Reset Device (Reset Device)	1	1	1	1	1
51	Device is Operational and Protecting (Device OK)	1	1	1	1	0
	Test mode (Test mode)	1	1	0	0	0
	Stop data transmission (DataStop)	1	0	1	0	0
LLN0.Beh.stVal		4	3	2	1	5

device annunciation / setting: 1 - ON / TRUE
0 - OFF / FALSE
x - irrelevant

IEC Status Beh.stVal:

1 - ON
2 - BLOCKED
3 - TEST
4 - TEST/BLOCKED
5 - OFF

LLN0.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
LLN0.Health.stVal		3	1

device annunciation: 1 - ON
0 - OFF

IEC Status Health.stVal:

1 - OK
2 - WARNING
3 - ALARM

2.5 DOI Behavior

2.5.1 Logical Device PROT

For the Logical Nodes of the PROT Logical Device, **LNx.Beh.stVal** is formed from **LNx.Mod.stVal** of the Logical Node and the status of the following device messages:

- Test mode (Test mode),
- Stop data transmission and
- At Least 1 Protection Funct. is Active.

No.	Information								
	Test mode (Test mode)	x	0	1	0	1	0	1	x
	Stop data transmission (DataStop)	x	0	0	1	1	x	x	x
52	At Least 1 Protection Funct. is Active (ProtActive)	x	1	1	1	1	1	1	0
	LNx .Mod.stVal	5	1	1	1	1	2	2	x
LNx.Beh.stVal		5	1	3	2	4	2	4	5

device annunciation / setting: 1 - ON / TRUE IEC Status stVal:
 0 - OFF / FALSE
 x - irrelevant

1 - ON
 2 - BLOCKED
 3 - TEST
 4 - TEST/BLOCKED
 5 - OFF

2.5.2 Logical Devices MEAS, CTRL, DR and EXT

For the Logical Nodes of the MEAS, CTRL, DR and EXT Logical Devices, **LNx.Beh.stVal** is formed from **LNx.Mod.stVal** of the Logical Node and the status of the following device messages:

- Test mode (Test mode),
- Stop data transmission.

No.	Information								
	Test mode (Test mode)	x	0	1	0	1	0	1	
	Stop data transmission (DataStop)	x	0	0	1	1	x	x	
	LNx .Mod.stVal	5	1	1	1	1	2	2	
	LNx.Beh.stVal	5	1	3	2	4	2	4	

device annunciation / setting: 1 - ON / TRUE
0 - OFF / FALSE
x - irrelevant

IEC Status stVal:

1 - ON
2 - BLOCKED
3 - TEST
4 - TEST/BLOCKED
5 - OFF

Mapping

Contents

This chapter shows the mapping of the information relevant to the device on the Logical Node of protocol IEC61850. It is structured according to function. In Chapter 2 you can find what consequences non-configured functions have on the Logical Nodes as well as general information about IEC 61850 mapping of information.

3.1	Device (LPHD1, CALH1)	44
3.2	Oscillographic Fault Records (RDRE1)	46
3.3	Overexcitation (Volt/Hertz) Protection (PVPH1, PVPH2)	48
3.4	Jump of Voltage Vector (GAPC1)	51
3.5	Voltage Protection 27, 59 (PTUVx, PTOVx)	53
3.6	Frequency protection 81 O/U (PTUFx, PTOFx)	65
3.7	Synchronism and Voltage Check 25 (RSYNx)	81
3.8	Three-pole tripping 52 Breaker (XCBR1)	83
3.9	Tripping Logic of the Entire Device (PTRC1)	86
3.10	Measurement (MMXU1, MSQI1)	88

3.1 Device (LPHD1, CALH1)

LPHD1.DevStr

No.	Information				
56	Initial Start of Device (Initial Start)	0	0	1	1
67	Resume (Resume)	0	1	0	1
LPHD1.DevStr.stVal		T	2	1	T

device annunciation: 1 - ON IEC Status DevStr.stVal: 1 - Initial Start
 0 - OFF 2 - Resume
 T - toggle between 1 and 2

LPHD1.Proxy

No.	Information		
55	Reset Device (Reset Device)	0	1
LPHD1.Proxy.stVal		1	0

device annunciation: 1 - ON IEC Status Proxy.stVal: 0 - DEVICE is not a PROXY
 0 - OFF 1 - DEVICE is a PROXY

LPHD1.PhyHealth

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
LPHD1.PhyHealth.stVal		3	1

device annunciation: 1 - ON IEC Status PhyHealth.stVal: 1 - OK
 0 - OFF 2 - WARNING
 3 - ALARM

3.1.1 Error with a summary alarm and Alarm summary event

CALH1.Mod

No.	Information		
51	Device is Operational and Protecting (Device OK)	1	0
CALH1.Mod.stVal		1	5

device annunciation: 1 - ON
0 - OFF

IEC Status Mod.stVal: 1 - ON
2 - BLOCKED
3 - TEST
4 - TEST/BLOCKED
5 - OFF

CALH1.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
CALH1.Health.stVal		3	1

device annunciation: 1 - ON
0 - OFF

IEC Status Health.stVal: 1 - OK
2 - WARNING
3 - ALARM

CALH1.GrAlm

No.	Information		
140	Error with a summary alarm (Error Sum Alarm)	1	0
CALH1.GrAlm.stVal		1	0

device annunciation: 1 - ON
0 - OFF

IEC Status GrAlm.stVal: 0 - FALSE
1 - TRUE

CALH1.GrWrn

No.	Information		
160	Alarm Summary Event (Alarm Sum Event)	1	0
CALH1.GrWrn.stVal		1	0

device annunciation: 1 - ON
0 - OFF

IEC Status GrWrn.stVal: 0 - FALSE
1 - TRUE

3.2 Oscillographic Fault Records (RDRE1)

RDRE1.Mod

No.	Information	
55	Reset Device (Reset Device)	x
RDRE1.Mod.stVal		1

device annunciation: 1 - ON
0 - OFF
x - irrelevant

IEC Status Mod.stVal: 1 - ON
2 - BLOCKED
3 - TEST
4 - TEST/BLOCKED
5 - OFF

RDRE1.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
RDRE1.Health.stVal		3	1

device annunciation: 1 - ON
0 - OFF

IEC Status Health.stVal: 1 - OK
2 - WARNING
3 - ALARM

RDRE1.RcdMade

No.	Information		
30053	Fault recording is running (Fault rec. run.)	0	1
RDRE1.RcdMade.stVal		1	0

device annunciation: 1 - ON
0 - OFF

IEC Status RodMade.stVal: 0 - FALSE
1 - TRUE
(Recording complete)

RDRE1.FltNum

No.	Information	Value	
302	Fault Event (Fault Event)	RDRE1.FltNum.stVal	Present fault number

RDRE1.GriFltNum

No.	Information	Value	
301	Power System fault (Pow.Sys.Flt.)	RDRE1.GriFltNum.stVal	Network fault number

RDRE1.RcdStr

No.	Information		
30053	Fault recording is running (Fault rec. run.)	0	1
RDRE1.RcdStr.stVal		0	1

device annunciation:

1 - ON
0 - OFF

IEC Status RcdStr.stVal:

0 - FALSE
1 - TRUE

3.3 Overexcitation (Volt/Hertz) Protection (PVPH1, PVPH2)

PVPH1.Mod

No.	Information			
5363	24 is ACTIVE (24 ACTIVE)	x	0	1
5361	24 is swiched OFF (24 OFF)	1	0	0
PVPH1.Mod.stVal		5	2	1

device annunciation / setting: 1 - ON / TRUE IEC Status Mod.stVal: 1 - ON
0 - OFF / FALSE 2 - BLOCKED
x - irrelevant 3 - TEST
4 - TEST/BLOCKED
5 - OFF

PVPH1.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
PVPH1.Health.stVal		3	1

device annunciation: 1 - ON IEC Status Health.stVal: 1 - OK
0 - OFF 2 - WARNING
3 - ALARM

PVPH1.Str

No.	Information		
5370	24-1 V/f> picked up (24-1 picked up)	0	1
PVPH1.Str.general		0	1

device annunciation: 1 - ON IEC Status Str.general: 0 - FALSE
 0 - OFF 1 - TRUE

PVPH1.Op

No.	Information		
5372	24 TRIP of th. stage (24 th.TRIP)	0	1
PVPH1.Op.general		0	1

device annunciation: 1 - ON IEC Status Op.general: 0 - FALSE
 0 - OFF 1 - TRUE

PVPH2.Mod

No.	Information			
5363	24 is ACTIVE (24 ACTIVE)	x	0	1
5361	24 is swiched OFF (24 OFF)	1	0	0
PVPH2.Mod.stVal		5	2	1

device annunciation / setting: 1 - ON / TRUE IEC Status Mod.stVal: 1 - ON
0 - OFF / FALSE 2 - BLOCKED
x - irrelevant 3 - TEST
4 - TEST/BLOCKED
5 - OFF

PVPH2.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
PVPH2.Health.stVal		3	1

device annunciation: 1 - ON IEC Status Health.stVal: 1 - OK
0 - OFF 2 - WARNING
3 - ALARM

PVPH2.Str

No.	Information		
5373	24-2 V/f>> picked up (24-2 picked up)	0	1
PVPH2.Str.general		0	1

device annunciation: 1 - ON IEC Status Str.general: 0 - FALSE
0 - OFF 1 - TRUE

PVPH2.Op

No.	Information		
5371	24-2 TRIP of V/f>> stage (24-2 TRIP)	0	1
PVPH2.Op.general		0	1

device annunciation: 1 - ON IEC Status Op.general: 0 - FALSE
0 - OFF 1 - TRUE

3.4 Jump of Voltage Vector (GAPC1)

GAPC1.Mod

No.	Information			
5584	Vector Jump is ACTIVE (VEC JUMP ACTIVE)	x	0	1
5582	Vector Jump is switched OFF (VEC JUMP OFF)	1	0	0
GAPC1.Mod.stVal		5	2	1

device annunciation / setting: 1 - ON / TRUE IEC Status Mod.stVal: 1 - ON
 0 - OFF / FALSE 2 - BLOCKED
 x - irrelevant 3 - TEST
 4 - TEST/BLOCKED
 5 - OFF

GAPC1.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
GAPC1.Health.stVal		3	1

device annunciation: 1 - ON IEC Status Health.stVal: 1 - OK
 0 - OFF 2 - WARNING
 3 - ALARM

GAPC1.Str

No.	Information		
5586	Vector Jump picked up (VEC JUMP pickup)	0	1
GAPC1.Str.general		0	1

device annunciation: 1 - ON IEC Status Str.general: 0 - FALSE
 0 - OFF 1 - TRUE

GAPC1.Op

No.	Information		
5587	Vector Jump TRIP (VEC JUMP TRIP)	0	1
GAPC1.Op.general		0	1

device annunciation: 1 - ON IEC Status Op.general: 0 - FALSE
 0 - OFF 1 - TRUE

3.5 Voltage Protection 27, 59 (PTUVx, PTOVx)

3.5.1 Undervoltage Protection 27 (PTUV1)

PTUV1.Mod

No.	Information			
6532	27 Undervoltage protection is ACTIVE (27 ACTIVE)	x	x	x
6531	27 Undervoltage protection is BLOCKED (27 BLOCKED)	x	1	0
6530	27 Undervoltage protection switched OFF (27 OFF)	1	0	0
PTUV1.Mod.stVal		5	2	1

device annunciation: 1 - ON
0 - OFF
x - irrelevant

IEC Status Mod.stVal: 1 - ON
2 - BLOCKED
3 - TEST
4 - TEST/BLOCKED
5 - OFF

PTUV1.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
PTUV1.Health.stVal		3	1

device annunciation: 1 - ON
0 - OFF

IEC Status Health.stVal: 1 - OK
2 - WARNING
3 - ALARM

PTUV1.Str

No.	Information		
6533	27-1 Undervoltage picked up (27-1 picked up)	0	1
PTUV1.Str.general		0	1

device annunciation: 1 - ON IEC Status Str.general: 0 - FALSE
 0 - OFF 1 - TRUE
 x - irrelevant

PTUV1.Op

No.	Information		
6539	27-1 Undervoltage TRIP (27-1 TRIP)	0	1
PTUV1.Op.general		0	1

device annunciation: 1 - ON IEC Status Op.general: 0 - FALSE
 0 - OFF 1 - TRUE

3.5.2 Undervoltage Protection 27 (PTUV2)

PTUV2.Mod

No.	Information			
6532	27 Undervoltage protection is ACTIVE (27 ACTIVE)	x	x	x
6531	27 Undervoltage protection is BLOCKED (27 BLOCKED)	x	1	0
6530	27 Undervoltage protection switched OFF (27 OFF)	1	0	0
PTUV2.Mod.stVal		5	2	1

device annunciation: 1 - ON
0 - OFF
x - irrelevant

IEC Status Mod.stVal: 1 - ON
2 - BLOCKED
3 - TEST
4 - TEST/BLOCKED
5 - OFF

PTUV2.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
PTUV2.Health.stVal		3	1

device annunciation: 1 - ON
0 - OFF

IEC Status Health.stVal: 1 - OK
2 - WARNING
3 - ALARM

PTUV2.Str

No.	Information		
6537	27-2 Undervoltage picked up (27-2 picked up)	0	1
PTUV2.Str.general		0	1

device annunciation: 1 - ON IEC Status Str.general: 0 - FALSE
0 - OFF 1 - TRUE
X - irrelevant

PTUV2.Op

No.	Information		
6540	27-2 Undervoltage TRIP (27-2 TRIP)	0	1
PTUV2.Op.general		0	1

device annunciation: 1 - ON IEC Status Op.general: 0 - FALSE
0 - OFF 1 - TRUE

3.5.3 Undervoltage Protection Vp< (PTUV3)

PTUV3.Mod

No.	Information			
6532	27 Undervoltage protection is ACTIVE (27 ACTIVE)	x	x	x
6531	27 Undervoltage protection is BLOCKED (27 BLOCKED)	x	1	0
6530	27 Undervoltage protection switched OFF (27 OFF)	1	0	0
PTUV3.Mod.stVal		5	2	1

device annunciation: 1 - ON IEC Status Mod.stVal: 1 - ON
 0 - OFF 2 - BLOCKED
 x - irrelevant 3 - TEST
 4 - TEST/BLOCKED
 5 - OFF

PTUV3.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
PTUV3.Health.stVal		3	1

device annunciation: 1 - ON IEC Status Health.stVal: 1 - OK
 0 - OFF 2 - WARNING
 3 - ALARM

PTUV3.Str

No.	Information		
17372	Vp< Undervoltage picked up (Vp< picked up)	0	1
PTUV3.Str.general		0	1

device annunciation: 1 - ON IEC Status Str.general: 0 - FALSE
0 - OFF 1 - TRUE
x - irrelevant

PTUV3.Op

No.	Information		
17374	Vp< Undervoltage TRIP (Vp< TRIP)	0	1
PTUV3.Op.general		0	1

device annunciation: 1 - ON IEC Status Op.general: 0 - FALSE
0 - OFF 1 - TRUE

3.5.4 Overvoltage Protection 59 (PTOV1)

PTOV1.Mod

No.	Information				
6567	59-Overvoltage protection is ACTIVE (59 ACTIVE)	x	x	x	x
6566	59-Overvoltage protection is BLOCKED (59 BLOCKED)	x	x	1	0
6565	59-Overvoltage protection switched OFF (59 OFF)	1	0	0	0
	Frequency range is exceeded	x	1	x	0
PTOV1.Mod.stVal		5	2	2	1

device annunciation / setting: 1 - ON / TRUE
0 - OFF / FALSE
x - irrelevant

IEC Status Mod.stVal:

1 - ON
2 - BLOCKED
3 - TEST
4 - TEST/BLOCKED
5 - OFF

PTOV1.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
PTOV1.Health.stVal		3	1

device annunciation: 1 - ON
0 - OFF

IEC Status Health.stVal:

1 - OK
2 - WARNING
3 - ALARM

PTOV1.Str

No.	Information		
6568	59 picked up (59-1 picked up)	0	1
PTOV1.Str.general		0	1

device annunciation: 1 - ON
0 - OFF

IEC Status Str.general:

0 - FALSE
1 - TRUE

PTOV1.Op

No.	Information		
6570	59 TRIP (59-1 TRIP)	0	1
PTOV1.Op.general		0	1

device annunciation: 1 - ON
 0 - OFF

IEC Status Op.general: 0 - FALSE
 1 - TRUE

3.5.5 Overvoltage Protection 59 (PTOV2)

PTOV2.Mod

No.	Information				
6567	59-Overvoltage protection is ACTIVE (59 ACTIVE)	x	x	x	x
6566	59-Overvoltage protection is BLOCKED (59 BLOCKED)	x	x	1	0
6565	59-Overvoltage protection switched OFF (59 OFF)	1	0	0	0
	Frequency range is exceeded	x	1	x	0
PTOV2.Mod.stVal		5	2	2	1

device annunciation / setting: 1 - ON / TRUE IEC Status Mod.stVal: 1 - ON
 0 - OFF / FALSE 2 - BLOCKED
 x - irrelevant 3 - TEST
 4 - TEST/BLOCKED
 5 - OFF

PTOV2.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
PTOV2.Health.stVal		3	1

device annunciation: 1 - ON IEC Status Health.stVal: 1 - OK
 0 - OFF 2 - WARNING
 3 - ALARM

PTOV2.Str

No.	Information		
6571	59-2 Overvoltage V>> picked up (59-2 picked up)	0	1
PTOV2.Str.general		0	1

device annunciation: 1 - ON IEC Status Str.general: 0 - FALSE
 0 - OFF 1 - TRUE

PTOV2.Op

No.	Information		
6573	59-2 Overvoltage V>> TRIP (59-2 TRIP)	0	1
PTOV2.Op.general		0	1

device annunciation: 1 - ON
 0 - OFF

IEC Status Op.general: 0 - FALSE
 1 - TRUE

3.5.6 Overvoltage Protection $V_{p>}$ (PTOV3)

PTOV3.Mod

No.	Information				
6567	59-Overvoltage protection is ACTIVE (59 ACTIVE)	x	x	x	x
6566	59-Overvoltage protection is BLOCKED (59 BLOCKED)	x	x	1	0
6565	59-Overvoltage protection switched OFF (59 OFF)	1	0	0	0
	Frequency range is exceeded	x	1	x	0
PTOV3.Mod.stVal		5	2	2	1

device annunciation / setting: 1 - ON / TRUE
0 - OFF / FALSE
x - irrelevant

IEC Status Mod.stVal:

1 - ON
2 - BLOCKED
3 - TEST
4 - TEST/BLOCKED
5 - OFF

PTOV3.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
PTOV3.Health.stVal		3	1

device annunciation: 1 - ON
0 - OFF

IEC Status Health.stVal:

1 - OK
2 - WARNING
3 - ALARM

PTOV3.Str

No.	Information		
17373	$V_{p>}$ Overvoltage picked up ($V_{p>}$ picked up)	0	1
PTOV3.Str.general		0	1

device annunciation: 1 - ON
0 - OFF

IEC Status Str.general:

0 - FALSE
1 - TRUE

PTOV3.Op

No.	Information		
17375	Vp> Overvoltage TRIP (Vp> TRIP)	0	1
PTOV3.Op.general		0	1

device annunciation: 1 - ON
 0 - OFF

IEC Status Op.general: 0 - FALSE
 1 - TRUE

3.6 Frequency protection 81 O/U (PTUFx, PTOFx)

3.6.1 Frequency protection 81-1 U (PTUF1)

PTUF1.Mod

No.	Information						
5213	81 ACTIVE (81 ACTIVE)	x	x	x	x	x	x
5212	81 BLOCKED (81 BLOCKED)	x	x	x	x	1	0
5206	>BLOCK 81-1 (>BLOCK 81-1)	x	x	x	1	x	0
5214	81 Under Voltage Block (81 Under V Blk)	x	x	1	x	x	0
5211	81 OFF (81 OFF)	x	1	0	0	0	0
	81-1 PICKUP (P5403/5404) < Rated Frequency (P214)	0	1	1	1	1	1
PTUF1.Mod.stVal		5	5	2	2	2	1

device annunciation / setting: 1 - ON / TRUE IEC Status Mod.stVal: 1 - ON
 0 - OFF / FALSE 2 - BLOCKED
 x - irrelevant 3 - TEST
 4 - TEST/BLOCKED
 5 - OFF

PTUF1.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
PTUF1.Health.stVal		3	1

device annunciation: 1 - ON IEC Status Health.stVal: 1 - OK
 0 - OFF 2 - WARNING
 3 - ALARM

3.6.2 Frequency protection 81-2 U (PTUF2)

PTUF2.Mod

No.	Information						
5213	81 ACTIVE (81 ACTIVE)	x	x	x	x	x	x
5212	81 BLOCKED (81 BLOCKED)	x	x	x	x	1	0
5207	>BLOCK 81-2 (>BLOCK 81-2)	x	x	x	1	x	0
5214	81 Under Voltage Block (81 Under V Blk)	x	x	1	x	x	0
5211	81 OFF (81 OFF)	x	1	0	0	0	0
	81-2 PICKUP (P5406/5407) < Rated Frequency (P214)	0	1	1	1	1	1
PTUF2.Mod.stVal		5	5	2	2	2	1

device annunciation / setting: 1 - ON / TRUE
0 - OFF / FALSE
x - irrelevant

IEC Status Mod.stVal:

1 - ON
2 - BLOCKED
3 - TEST
4 - TEST/BLOCKED
5 - OFF

PTUF2.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
PTUF2.Health.stVal		3	1

device annunciation: 1 - ON
0 - OFF

IEC Status Health.stVal:

1 - OK
2 - WARNING
3 - ALARM

PTUF2.Str

No.	Information				
5233	81-2 picked up (81-2 picked up)	0	0	1	1
	81-2 PICKUP (P5406/5407) < Rated Frequency (P214)	0	1	0	1
PTUF2.Str.general		0	0	0	1

device annunciation / setting: 1 - ON / TRUE IEC Status Str.general: 0 - FALSE
 0 - OFF / FALSE 1 - TRUE

PTUF2.Op

No.	Information				
5237	81-2 TRIP (81-2 TRIP)	0	0	1	1
	81-2 PICKUP (P5406/5407) < Rated Frequency (P214)	0	1	0	1
PTUF2.Op.general		0	0	0	1

device annunciation / setting: 1 - ON / TRUE IEC Status Op.general: 0 - FALSE
 0 - OFF / FALSE 1 - TRUE

PTUF2.BlkV

No.	Information				
5214	81 Under Voltage Block (81 Under V Blk)	0	0	1	1
	81-2 PICKUP (P5406/5407) < Rated Frequency (P214)	0	1	0	1
PTUF2.BlkV.stVal		0	0	0	1

device annunciation / setting: 1 - ON / TRUE IEC Status BlkV.stVal: 0 - FALSE
 0 - OFF / FALSE 1 - TRUE

PTUF3.Str

No.	Information				
5234	81-3 picked up (81-3 picked up)	0	0	1	1
	81-3 PICKUP (P5409/5410) < Rated Frequency (P214)	0	1	0	1
PTUF3.Str.general		0	0	0	1

device annunciation / setting: 1 - ON / TRUE IEC Status Str.general: 0 - FALSE
0 - OFF / FALSE 1 - TRUE

PTUF3.Op

No.	Information				
5238	81-3 TRIP (81-3 TRIP)	0	0	1	1
	81-3 PICKUP (P5409/5410) < Rated Frequency (P214)	0	1	0	1
PTUF3.Op.general		0	0	0	1

device annunciation / setting: 1 - ON / TRUE IEC Status Op.general: 0 - FALSE
0 - OFF / FALSE 1 - TRUE

PTUF3.BlkV

No.	Information				
5214	81 Under Voltage Block (81 Under V Blk)	0	0	1	1
	81-3 PICKUP (P5409/5410) < Rated Frequency (P214)	0	1	0	1
PTUF3.BlkV.stVal		0	0	0	1

device annunciation / setting: 1 - ON / TRUE IEC Status BlkV.stVal: 0 - FALSE
0 - OFF / FALSE 1 - TRUE

PTUF4.Str

No.	Information				
5235	81-4 picked up (81-4 picked up)	0	0	1	1
	81-4 PICKUP (P5412/5413) < Rated Frequency (P214)	0	1	0	1
PTUF4.Str.general		0	0	0	1

device annunciation / setting: 1 - ON / TRUE IEC Status Str.general: 0 - FALSE
0 - OFF / FALSE 1 - TRUE

PTUF4.Op

No.	Information				
5239	81-4 TRIP (81-4 TRIP)	0	0	1	1
	81-4 PICKUP (P5412/5413) < Rated Frequency (P214)	0	1	0	1
PTUF4.Op.general		0	0	0	1

device annunciation / setting: 1 - ON / TRUE IEC Status Op.general: 0 - FALSE
0 - OFF / FALSE 1 - TRUE

PTUF4.BIkV

No.	Information				
5214	81 Under Voltage Block (81 Under V Blk)	0	0	1	1
	81-4 PICKUP (P5412/5413) < Rated Frequency (P214)	0	1	0	1
PTUF4.BIkV.stVal		0	0	0	1

device annunciation / setting: 1 - ON / TRUE IEC Status BlkV.stVal: 0 - FALSE
0 - OFF / FALSE 1 - TRUE

3.6.5 Frequency protection 81-1 O (PTOF1)

PTOF1.Mod

No.	Information							
5213	81 ACTIVE (81 ACTIVE)	x	x	x	x	x	x	x
5212	81 BLOCKED (81 BLOCKED)	x	x	x	x	x	1	0
5206	>BLOCK 81-1 (>BLOCK 81-1)	x	x	x	x	1	x	0
5214	81 Under Voltage Block (81 Under V Blk)	x	x	x	1	x	x	0
5211	81 OFF (81 OFF)	x	x	1	0	0	0	0
	81-1 PICKUP (P5403/5404) \leq Rated Frequency (P214)	x	1	x	0	0	0	0
PTOF1.Mod.stVal		5	5	5	2	2	2	1

device annunciation / setting: 1 - ON / TRUE IEC Status Mod.stVal: 1 - ON
 0 - OFF / FALSE 2 - BLOCKED
 x - irrelevant 3 - TEST
 4 - TEST/BLOCKED
 5 - OFF

PTOF1.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
PTOF1.Health.stVal		3	1

device annunciation: 1 - ON IEC Status Health.stVal: 1 - OK
 0 - OFF 2 - WARNING
 3 - ALARM

PTOF2.Str

No.	Information				
5233	81-2 picked up (81-2 picked up)	0	0	1	1
	81-2 PICKUP (P5406/5407) < Rated Frequency (P214)	0	1	0	1
PTOF2.Str.general		0	0	1	0

device annunciation / setting: 1 - ON / TRUE IEC Status Str.general: 0 - FALSE
0 - OFF / FALSE 1 - TRUE

PTOF2.Op

No.	Information				
5237	81-2 TRIP (81-2 TRIP)	0	0	1	1
	81-2 PICKUP (P5406/5407) < Rated Frequency (P214)	0	1	0	1
PTOF2.Op.general		0	0	1	0

device annunciation / setting: 1 - ON / TRUE IEC Status Op.general: 0 - FALSE
0 - OFF / FALSE 1 - TRUE

PTOF2.BlkV

No.	Information				
5214	81 Under Voltage Block (81 Under V Blk)	0	0	1	1
	81-2 PICKUP (P5406/5407) < Rated Frequency (P214)	0	1	0	1
PTOF2.BlkV.stVal		0	0	1	0

device annunciation / setting: 1 - ON / TRUE IEC Status BlkV.stVal: 0 - FALSE
0 - OFF / FALSE 1 - TRUE

3.6.7 Frequency protection 81-3 O (PTOF3)

PTOF3.Mod

No.	Information								
5213	81 ACTIVE (81 ACTIVE)	x	x	x	x	x	x	x	x
5212	81 BLOCKED (81 BLOCKED)	x	x	x	x	x	1	0	
5208	>BLOCK 81-3 (>BLOCK 81-3)	x	x	x	x	1	x	0	
5214	81 Under Voltage Block (81 Under V Blk)	x	x	x	1	x	x	0	
5211	81 OFF (81 OFF)	x	x	1	0	0	0	0	
	81-3 PICKUP (P5409/5410) ≤ Rated Frequency (P214)	x	1	x	0	0	0	0	
PTOF3.Mod.stVal		5	5	5	2	2	2	1	

device annunciation / setting: 1 - ON / TRUE IEC Status Mod.stVal: 1 - ON
0 - OFF / FALSE 2 - BLOCKED
x - irrelevant 3 - TEST
4 - TEST/BLOCKED
5 - OFF

PTOF3.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
PTOF3.Health.stVal		3	1

device annunciation: 1 - ON IEC Status Health.stVal: 1 - OK
0 - OFF 2 - WARNING
3 - ALARM

3.6.8 Frequency protection 81-4 O (PTOF4)

PTOF4.Mod

No.	Information								
5213	81 ACTIVE (81 ACTIVE)	x	x	x	x	x	x	x	x
5212	81 BLOCKED (81 BLOCKED)	x	x	x	x	x	1	0	
5209	>BLOCK 81-4 (>BLOCK 81-4)	x	x	x	x	1	x	0	
5214	81 Under Voltage Block (81 Under V Blk)	x	x	x	1	x	x	0	
5211	81 OFF (81 OFF)	x	x	1	0	0	0	0	
	81-4 PICKUP (P5412/5413) ≤ Rated Frequency (P214)	x	1	x	0	0	0	0	
PTOF4.Mod.stVal		5	5	5	2	2	2	1	

device annunciation / setting: 1 - ON / TRUE IEC Status Mod.stVal: 1 - ON
 0 - OFF / FALSE 2 - BLOCKED
 x - irrelevant 3 - TEST
 4 - TEST/BLOCKED
 5 - OFF

PTOF4.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
PTOF4.Health.stVal		3	1

device annunciation: 1 - ON IEC Status Health.stVal: 1 - OK
 0 - OFF 2 - WARNING
 3 - ALARM

3.7 Synchronism and Voltage Check 25 (RSYNx)

RSYN1.Mod

No.	Information			
170.0051	25-group 1 is BLOCKED (25-1 BLOCK)	0	1	x
170.2101	Sync-group 1 is switched OFF (25-1 OFF)	0	0	1
RSYN1.Mod.stVal		1	2	5

device annunciation: 1 - ON IEC Status Mod.stVal: 1 - ON
 0 - OFF 2 - BLOCKED
 x - irrelevant 3 - TEST
 4 - TEST/BLOCKED
 5 - OFF

RSYN1.Health

No.	Information				
170.0050	25 Synchronization Error (25 Sync. Error)	x	x	1	0
51	Device is Operational and Protecting (Device OK)	x	x	1	1
170.2096	25 Multiple selection of func-groups (25 FG-Error)	1	x	0	0
170.2097	25 Setting error (25 Set-Error)	x	1	0	0
RSYN1.Health.stVal		3	3	2	1

device annunciation: 1 - ON IEC Status Health.stVal: 1 - OK
 0 - OFF 2 - WARNING
 x - irrelevant 3 - ALARM

RSYN1.Rel

No.	Information		
170.0049	25 Sync. Release of CLOSE Command (25 CloseRelease)	0	1
RSYN1.Rel.stVal		0	1

device annunciation: 1 - ON IEC Status Rel.stVal: 0 - FALSE
 0 - OFF 1 - TRUE

RSYN1.VInd

No.	Information		
170.2030	25 Voltage difference (Vdiff) okay (25 Vdiff ok)	0	1
RSYN1.VInd.stVal		1	0

device annunciation: 1 - ON IEC Status VInd.stVal: 0 - FALSE
 0 - OFF 1 - TRUE

RSYN1.AngInd

No.	Information		
170.2032	25 Angle difference (alphadiff) okay (25 α diff ok)	0	1
RSYN1.AngInd.stVal		1	0

device annunciation: 1 - ON IEC Status AngInd.stVal: 0 - FALSE
 0 - OFF 1 - TRUE

RSYN1.HzInd

No.	Information		
170.2031	25 Frequency difference (fdiff) okay (25 fdiff ok)	0	1
RSYN1.HzInd.stVal		1	0

device annunciation: 1 - ON IEC Status HzInd.stVal: 0 - FALSE
 0 - OFF 1 - TRUE

RSYN1.SynPrg

No.	Information		
170.2022	25-group 1: measurement in progress (25-1 meas.)	0	1
RSYN1.SynPrg.stVal		0	1

device annunciation: 1 - ON IEC Status SynPrg.stVal: 0 - FALSE
 0 - OFF 1 - TRUE

3.8 Three-pole tripping 52 Breaker (XCBR1)

XCBR1.Mod

No.	Information		
52	At Least 1 Protection Funct. is Active (ProtActive)	1	0
XCBR1.Mod.stVal		1	5

device annunciation: 1 - ON 0 - OFF IEC Status Mod.stVal: 1 - ON 2 - BLOCKED 3 - TEST 4 - TEST/BLOCKED 5 - OFF

XCBR1.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
XCBR1.Health.stVal		3	1

device annunciation: 1 - ON 0 - OFF x - irrelevant IEC Status Health.stVal: 1 - OK 2 - WARNING 3 - ALARM

XCBR1.Loc

No.	Information		
55	Reset Device (Reset Device)	1	0
XCBR1.Loc.stVal		1	0

device annunciation: 1 - ON 0 - OFF IEC Status Loc.stVal: 0 - FALSE 1 - TRUE

XCBR1.OpCnt

No.	Information	Value		
	Number of TRIPs= (#of TRIPs=)	XCBR1.OpCnt.stVal	Metered value	Absolute value

XCBR1.Pos

No.	Information				
4601	>52-a contact (OPEN, if bkr is open) (>52-a)	0	1	0	1
4602	>52-b contact (OPEN, if bkr is closed) (>52-b)	0	0	1	1
XCBR1.Pos.stVal - if spontan information		11	01	10	11
XCBR1.Pos.stVal - if command is running		00	01	10	00

device annunciation: 1 - ON IEC Status Pos.stVal: 00 - INTERMEDIATE STATE
 0 - OFF 01 - OFF
 10 - ON
 11 - BAD STATE

XCBR1.BlkOpn

No.	Information		
55	Reset Device (Reset Device)	1	0
XCBR1.BlkOpn.stVal		0	1

device annunciation: 1 - ON IEC Status BlkOpn.stVal: 0 - FALSE
 0 - OFF 1 - TRUE

XCBR1.BlkCls

No.	Information		
55	Reset Device (Reset Device)	1	0
XCBR1.BlkCls.stVal		0	1

device annunciation: 1 - ON IEC Status BlkCls.stVal: 0 - FALSE
 0 - OFF 1 - TRUE

XCBR1.CBOPCap

No.	Information	
XCBR1.CBOPCap.stVal		1

device annunciation: IEC Status CBOpCap.stVal: 1 - NONE

XCBR1.CirSpv

No.	Information		
6865	74TC Failure Trip Circuit (74TC Trip cir.)	0	1
XCBR1.CirSpv.stVal		0	1

device annunciation:

1 - ON
0 - OFF

IEC Status CirSpv.stVal:

0 - FALSE
1 - TRUE

3.9 Tripping Logic of the Entire Device (PTRC1)

PTRC1.Mod

No.	Information		
52	At Least 1 Protection Funct. is Active (ProtActive)	1	0
PTRC1.Mod.stVal		1	5

device annunciation: 1 - ON
0 - OFF

IEC Status Mod.stVal: 1 - ON
2 - BLOCKED
3 - TEST
4 - TEST/BLOCKED
5 - OFF

PTRC1.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
PTRC1.Health.stVal		3	1

device annunciation: 1 - ON
0 - OFF

IEC Status Health.stVal: 1 - OK
2 - WARNING
3 - ALARM

PTRC1.Str

No.	Information		
501	Relay PICKUP (Relay PICKUP)	0	1
PTRC1.Str.general		0	1

device annunciation: 1 - ON
0 - OFF

IEC Status Str.general: 0 - FALSE
1 - TRUE

PTRC1.Tr

No.	Information		
511	Relay GENERAL TRIP command (Relay TRIP)	0	1
PTRC1.Tr.general		0	1

device annunciation:

1 - ON
0 - OFF

IEC Status Tr.general:

0 - FALSE
1 - TRUE

3.10 Measurement (MMXU1, MSQI1)

3.10.1 Measures (MMXU1)

MMXU1.Mod

No.	Information	
55	Reset Device (Reset Device)	x
MMXU1.Mod.stVal		1

device annunciation: 1 - ON
 0 - OFF
 x - irrelevant

IEC Status Mod.stVal: 1 - ON
 2 - BLOCKED
 3 - TEST
 4 - TEST/BLOCKED
 5 - OFF

MMXU1.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
MMXU1.Health.stVal		3	1

device annunciation: 1 - ON
 0 - OFF

IEC Status Health.stVal: 1 - OK
 2 - WARNING
 3 - ALARM

MMXU1.Hz

No.	Information	Value		
644	Frequency (Freq=)	MMXU1.Hz.mag.f	Measured value	Absolute value
		MMXU1.Hz.units.SIUnit	33	Hz
		MMXU1.Hz.units.multiplier	0	1

MMXU1.PPV

No.	Information	Value		
624	Va-b (Va-b=)	MMXU1.PPV.phsAB.cVal.mag.f	Measured value	Absolute value
		MMXU1.PPV.phsAB.units.SIUnit	29	V (Volt)
		MMXU1.PPV.phsAB.units.multiplier	3	Kilo

No.	Information	Value		
625	Vb-c (Vb-c=)	MMXU1.PPV.phsBC.cVal.mag.f	Measured value	Absolute value
		MMXU1.PPV.phsBC.units.SIUnit	29	V (Volt)
		MMXU1.PPV.phsBC.units.multiplier	3	Kilo

No.	Information	Value		
626	Vc-a (Vc-a=)	MMXU1.PPV.phsCA.cVal.mag.f	Measured value	Absolute value
		MMXU1.PPV.phsCA.units.SIUnit	29	V (Volt)
		MMXU1.PPV.phsCA.units.multiplier	3	Kilo

MMXU1.PhV

No.	Information	Value		
621	Va (Va =)	MMXU1.PhV.phsA.cVal.mag.f	Measured value	Absolute value
		MMXU1.PhV.phsA.units.SIUnit	29	V (Volt)
		MMXU1.PhV.phsA.units.multiplier	3	Kilo
No.	Information	Value		
622	Vb (Vb =)	MMXU1.PhV.phsB.cVal.mag.f	Measured value	Absolute value
		MMXU1.PhV.phsB.units.SIUnit	29	V (Volt)
		MMXU1.PhV.phsB.units.multiplier	3	Kilo
No.	Information	Value		
623	Vc (Vc =)	MMXU1.PhV.phsC.cVal.mag.f	Measured value	Absolute value
		MMXU1.PhV.phsC.units.SIUnit	29	V (Volt)
		MMXU1.PhV.phsC.units.multiplier	3	Kilo
No.	Information	Value		
627	VN (VN =)	MMXU1.PhV.neut.cVal.mag.f	Measured value	Absolute value
		MMXU1.PhV.neut.units.SIUnit	29	V (Volt)
		MMXU1.PhV.neut.units.multiplier	3	Kilo

3.10.2 Measured values, symmetrical components (MSQI1)

MSQI1.Mod

No.	Information	
55	Reset Device (Reset Device)	x
MSQI1.Mod.stVal		1

device annunciation: 1 - ON
0 - OFF
x - irrelevant

IEC Status Mod.stVal: 1 - ON
2 - BLOCKED
3 - TEST
4 - TEST/BLOCKED
5 - OFF

MSQI1.Health

No.	Information		
51	Device is Operational and Protecting (Device OK)	0	1
MSQI1.Health.stVal		3	1

device annunciation: 1 - ON
0 - OFF

IEC Status Health.stVal: 1 - OK
2 - WARNING
3 - ALARM

MSQI1.SeqV

No.	Information	Value		
629	V1 (positive sequence) (V1 =)	MSQI1.SeqV.c1.cVal.mag.f	Measured value	Absolute value
		MSQI1.SeqV.c1.units.SIUnit	29	V (Volt)
		MSQI1.SeqV.c1.units.multiplier	3	Kilo
No.	Information		Value	
630	V2 (negative sequence) (V2 =)	MSQI1.SeqV.c2.cVal.mag.f	Measured value	Absolute value
		MSQI1.SeqV.c2.units.SIUnit	29	V (Volt)
		MSQI1.SeqV.c2.units.multiplier	3	Kilo
No.	Information		Value	
832	Vo (zero sequence) (Vo =)	MSQI1.SeqV.c3.cVal.mag.f	Measured value	Absolute value
		MSQI1.SeqV.c3.units.SIUnit	29	V (Volt)
		MSQI1.SeqV.c3.units.multiplier	3	Kilo

Literature

- /1/ SIPROTEC 4 Ethernet Module EN 100 IEC 61850 Electrical Interface 100 MBit, Manual
C54000-G1176-C167
- /2/ SIPROTEC 4 System Description
E50417-H1176-C151
- /3/ SIPROTEC DIGSI, StartUP
E50417-G1176-C152
- /4/ DIGSI CFC, Manual
E50417-H1176-C098
- /5/ SIPROTEC SIGRA 4, Manual
E50417-H1176-C1100-C070
- /6/ SIPROTEC Voltage and Frequency Protection 7RW80, Manual
C53000-G1140-C234

Index

C

CALH1 32, 36, 45
ErrBoard5 45
GrAlm 45
GrWrn 45
Health 45
Mod 45

D

DOI 31

F

Function parameters 32

G

GAPC5 32, 34
Health 51
Mod 51
Op 52
Str 52

L

LD
CTRL (Control) 32, 36
DR (Disturbance Recorder) 35
EXT (Extended) 36
Logical Device 30
MEAS (Measurement) 32, 35
PROT (Protection) 32, 34
LLN0 30, 32, 34, 35, 36
Beh 37, 38, 39
Health 37, 38, 39
Mod 38, 39
OpTmh 37
Logical Node 31, 32, 34
LPHD1 30, 32, 34, 35, 36, 44
DevStr 44
PhyHealth 44
Proxy 44

M

MMXU1 32, 35, 88
Health 88
Hz 89
Mod 88
PhV 90
PPV 89
MSQI1 32, 35, 91
Health 91
Mod 91
SeqV 91

P

PTOF1 33, 34, 73

BikV 74
Health 73
Mod 73, 75
Op 74
Str 74
PTOF2 75
BikV 76
Health 75
Mod 75
Op 76
Str 76
PTOF3 77
BikV 78
Health 77
Mod 77
Op 78
Str 78
PTOF4 79
BikV 80
Health 79
Mod 79
Op 80
Str 80
PTOV1 32, 34, 59
Health 59
Mod 59, 63
Op 60
Str 59
PTOV2 32, 61
Health 61
Mod 61
Op 62
Str 61
PTOV3 32, 63
Health 63
Mod 63
Op 64
Str 63
PTRC1 32, 34, 86
FinTr 88
Health 86
Mod 86
Str 86
Tr 87
PTUF1 33, 34, 65
BikV 66
Health 65
Mod 65
Op 66
Str 66
PTUF2 67
BikV 68
Health 67
Mod 67

- Op 68
- Str 68
- PTUF3 69
 - BlkV 70
 - Health 69
 - Mod 69
 - Op 70
 - Str 70
- PTUF4 71
 - BlkV 72
 - Health 71
 - Mod 71
 - Op 72
 - Str 72
- PTUV1 32, 34, 53
 - Health 53
 - Mod 53
 - Op 54
 - Str 54
- PTUV2 32, 55
 - Health 55
 - Mod 55
 - Op 56
 - Str 56
- PTUV3 32, 57
 - Health 57
 - Mod 57
 - Op 58
 - Str 58
- PVPH1 32, 34
 - Health 48
 - Mod 48
 - Op 49
 - Str 49
- PVPH2 32
 - Health 50
 - Mod 50
 - Op 50
 - Str 50

R

- RDRE1 32, 35, 46
 - FltNum 47
 - GriFltNum 47
 - Health 46
 - Mod 46
 - RcdMade 46, 47
 - RcdStr 47
- RSYN1 33, 36, 81
 - AngInd 82
 - DifVClc 83
 - Health 81
 - HziInd 82
 - Mod 81
 - Rel 81
 - SynPrg 82
 - VInd 82

X

- XCBR1 32, 34, 83
 - BlkCls 84
 - BlkOpn 84
 - CBOpCap 84
 - CirSpv 85
 - Health 83
 - Loc 83
 - Mod 83
 - OpCnt 83
 - Pos 84