

RFID systems for the HF range



2/2	Introduction	2/102	RF300
2/4	Transponders (ISO mode)	2/104	RF300 readers
2/4	Introduction	2/105	RF310R
2/8	MDS D165	2/107	RF340R
2/8	MDS D261	2/109	RF350R
2/10	MDS D100	2/112	RF380R
2/12	MDS D200	2/115	RF382R
2/14	MDS D400	2/117	RF350M mobile handheld terminal
2/16	MDS D421	2/120	MOBY D
2/18	MDS D521	2/122	MOBY D readers
2/20	MDS D422	2/123	SLG D11 / SLG D11S basic units
2/22	MDS D522	2/126	SLG D12 / SLG D12S
2/24	MDS D423	2/129	MOBY D Configuring instructions
2/26	MDS D124	2/130	HF antennas
2/28	MDS D324	2/130	Introduction
2/30	MDS D424	2/131	ANT 1 for RF350R
2/32	MDS D524	2/132	ANT 3 for RF250R, RF350R and RF350M
2/34	MDS D425	2/133	ANT 3S for RF250R, RF350R and RF350M
2/36	MDS D525	2/134	ANT 8 for RF250R and RF350M
2/38	MDS D126	2/136	ANT 12 for RF250R, RF350R and RF350M
2/40	MDS D426	2/137	ANT 18 for RF250R, RF350R and RF350M
2/42	MDS D526	2/138	ANT 30 for RF250R, RF350R and RF350M
2/44	MDS D117	2/139	ANT D1 for RF290R
2/46	MDS D127	2/140	ANT D2 for SLG D11 / SLG D11S
2/48	MDS D428	2/141	ANT D5 for RF290R and SLG D11 / D11S
2/50	MDS D528	2/143	ANT D6 for RF290R
2/52	MDS D139	2/145	ANT D10 for RF290R
2/54	MDS D339		
2/56	MDS D160		
2/58	MDS D460		
2/60	Transponders (RF300 mode)		
2/60	Introduction		
2/61	RF320T		
2/63	RF330T		
2/65	RF340T		
2/67	RF350T		
2/69	RF360T		
2/71	RF370T		
2/73	RF380T		
2/76	RF200		
2/78	RF200 readers		
2/79	RF210R		
2/82	RF210M mobile handheld terminal		
2/83	RF220R		
2/86	RF240R		
2/90	RF250R		
2/95	RF260R		
2/99	RF290R		
2/117	RF350M mobile handheld terminal		

RFID systems for the HF range

Introduction

Overview



As the world's leading supplier of identification systems, with SIMATIC Ident Siemens offers a unique integrated and scalable range of RFID and optical identification systems for flexible and cost-effective identification solutions.

RFID systems are offered for the most diverse requirements on performance, range, frequency range as well as HF and UHF. This section provides you an overview of our RFID systems in the HF range.

Easy integration of the RFID systems via communication modules and pre-configured software blocks in the world of Totally Integrated Automation (TIA) significantly reduces the work and costs necessary for commissioning, diagnostics and maintenance. Thanks to many years of experience in the area of RFID, Siemens is a competent partner for implementation of the most diverse solutions in all sectors, but especially in the areas of production and logistics.

RFID systems for the HF frequency range

Siemens offers the following two RFID systems for the HF range:

- **SIMATIC RF200:**
The compact and economical RFID system according to ISO 15693. Readers with an IO-Link interface are provided for particularly simple and open identification solutions.
- **SIMATIC RF300:**
For the most demanding requirements in terms of speed, data volume and diagnostics functionality, the RF300 mode with separate transponders is available. The high-performance RFID system can be operated with ISO 15693 transponders to meet average performance requirements.

Meaningful data from the outset

The RFID systems ensure that meaningful data accompanies a product or object from the very beginning. The transponders are attached to the product, product carrier, object or its transport or packing unit and are recorded, read and written by non-contact methods. This means that all the application-specific data is located on the transponder. This is true whether you are dealing with vehicle body parts in the automotive industry or order picking boxes. Up to 64 KB of data can be stored and individually read and supplemented when required at the various workstations or manufacturing stations. This all means that the flow of material and data is synchronized optimally.

Contactless data transfer and a high degree of industrial compatibility

Powerful readers (write/read devices) in various rugged designs ensure fast and reliable data transfer between the transponders and the higher-level systems (e.g. PLC, PC).

The data and power are transmitted inductively by an electromagnetic alternating field. This principle of contactless data transfer also works in the presence of contamination or through numerous non-metallic materials.

Perfectly matched components

The RFID systems consist of perfectly matched individual components:

- Transponder
- Readers
- Antennas
- Communication modules for connection to the automation system (e.g. PROFIBUS, PROFINET)
- Software for system integration

For a wide range of applications in all sectors

- Production control
- Asset management
- Tracking & tracing

Wide range of transponders

A wide range of different transponders is available using a variety of storage technologies and geometric designs. Their strength is not only their high level of data security but also the excellent high degree of protection against ambient conditions such as contamination, temperature fluctuations, washing water or shock load.

Benefits

get Designed for Industry

- Flexible and economic solutions thanks to the complete and scalable portfolio for the field of industrial identification.
- Simplified engineering, commissioning, diagnostics and maintenance through seamless integration into Totally Integrated Automation:
 - Integrated bus connection to an automation system, such as SIMATIC, SIMOTION or SINUMERIK via communication modules with PROFIBUS and PROFINET.
 - Simple S7 software integration via ready-to-use function blocks.
 - Extensive status and diagnostic functions.
- High degree of investment protection thanks to:
 - Open standards (e.g. ISO 15693).
 - Software compatibility between the RFID and optical reading systems of Siemens.
 - Standardized communication interfaces.
- Openness through connection possibilities to different bus systems from different manufacturers and PC environments via communication modules.
- Worldwide Service and Support.

Integration

A wide range of communication modules, function blocks, as well as high-performance drivers and function libraries permits easy and quick integration into the application. And best of all: SIMATIC RF is part of Totally Integrated Automation (TIA) and can be integrated easily and cost-effectively into the SIMATIC world. For more details on the connection possibilities, see the section "Communication Modules".

SIMATIC Ident Configuration Guide

Here is a compact configuration tool for setting up RFID systems:

<http://support.automation.siemens.com/WW/view/en/67384964>












RFID systems for the HF range

Transponders (ISO mode)

Introduction

Overview











The following transponders can be used with the SIMATIC RF200, RF300 or MOBY D RFID systems:

Transponder	Features	Page	Transponder	Features	Page
MDS D165 	SmartLabel, (PET) similar to credit card format. Applications range from simple identification such as electronic barcode substitution or supplementation, to storage and distribution logistics, right up to product identification.. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 • RF300 • MOBY D 	2/8	MDS D421 	Transponder for the tool coding according to DIN 69873. It can be used wherever very small data media and exact positioning are required (e.g. for tool identification). Usable for RFID systems: <ul style="list-style-type: none"> • RF200 • RF300 • MOBY D 	2/16
MDS D261 	SmartLabel, (PET) in compact design. Applications range from simple identification such as electronic barcode substitution or supplementation, to storage and distribution logistics, right up to product identification. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 • RF300 • MOBY D 	2/8	MDS D521 	The MDS D521 is designed for tool coding according to DIN 69873. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 	2/18
MDS D100 	Universal transponder in credit card format with 112 bytes EEPROM, suitable for the identification of transport units in production-related logistics. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 • RF300 • MOBY D 	2/10	MDS D422 	Transponder for the identification of metallic workpiece holders, workpieces or containers. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 • RF300 	2/20
MDS D200 	Universal transponder in credit card format with 256 bytes EEPROM, suitable for the identification of transport units in production-related logistics. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 • RF300 • MOBY D 	2/12	MDS D522  	Transponder for the identification of metallic workpiece holders, workpieces or containers. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 	2/22
MDS D400 	Universal transponder in credit card format with 2 000 bytes FRAM, suitable for the identification of transport units in production-related logistics. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 • RF300 • MOBY D 	2/14	MDS D423 	Rugged transponder for use in production and distribution logistics as well as in assembly and production lines. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 • RF300 	2/24

RFID systems for the HF range

Transponders (ISO mode)



Introduction

Transponder	Features	Page	Transponder	Features	Page
MDS D124 	Heat-resistant transponder for use in applications with high thermal stress. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 • RF300 • MOBY D 	2/26	MDS D525 	It is designed for use in assembly and production lines as well as in the powertrain sector. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 	2/36
MDS D324 	Rugged transponder for use in harsh industrial environments and under extreme environmental conditions. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 • RF300 • MOBY D 	2/28	MDS D126 	Compact and rugged transponder for identification of transport units in production-related logistics. The transponder can also be used in harsh environments. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 • RF300 • MOBY D 	2/38
MDS D424 	Rugged transponder for use in production and distribution logistics as well as in assembly and production lines. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 • RF300 • MOBY D 	2/30	MDS D426 	Compact and rugged transponder for identification of transport units in production-related logistics. The transponder can also be used in harsh environments. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 • RF300 • MOBY D 	2/40
MDS D524 	The transponder is designed for use in production and distribution logistics as well as in assembly and production lines. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 	2/32	MDS D526 	It is designed for the identification of transport units in production-related logistics. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 	2/42
MDS D425 	Compact and rugged transponder suitable for screw mounting. For use in assembly and production lines in the powertrain sector. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 • RF300 	2/34	MDS D117 	Extremely small, ISO-15693-compatible transponder that can be flush-mounted on metal with adhesive. Transponder for direct identification of metallic workpiece holders, small workpieces, or containers. Usable for RFID systems: <ul style="list-style-type: none"> • RF200 • RF300 	2/44

RFID systems for the HF range

Transponders (ISO mode)

Introduction

Transponder	Features	Page	Transponder	Features	Page
MDS D127 	<p>Extremely small, ISO 15693-compatible transponder that can be screwed flush into metal.</p> <p>Transponder for direct identification of metallic workpiece holders, small workpieces, or containers</p> <p>Usable for RFID systems:</p> <ul style="list-style-type: none"> • RF200 • RF300 	2/46	MDS D160 	<p>Special transponder for harsh environments in the laundry and cleaning industry.</p> <p>Usable for RFID systems:</p> <ul style="list-style-type: none"> • RF200 • RF300 • MOBY D 	2/56
MDS D428 	<p>Compact and rugged transponder for screw mounting; for use in assembly and production lines in the powertrain area.</p> <p>Usable for RFID systems:</p> <ul style="list-style-type: none"> • RF200 • RF300 • MOBY D 	2/48	MDS D460 	<p>Rugged transponder for use in assembly lines.</p> <p>Usable for RFID systems:</p> <ul style="list-style-type: none"> • RF200 • RF300 • MOBY D 	2/58
MDS D528 	<p>It is designed for use in assembly and production lines as well as in the powertrain sector.</p> <p>Usable for RFID systems:</p> <ul style="list-style-type: none"> • RF200 	2/50	<p>Customer-specific transponders</p> <p>Customer-specific transponders (packaging, temperature range, geometry, etc.) on request.</p>		
MDS D139 	<p>Heat-resistant transponder for use in paint shops or applications with high thermal stress.</p> <p>Usable for RFID systems:</p> <ul style="list-style-type: none"> • RF200 • RF300 • MOBY D 	2/52			
MDS D339 	<p>Heat-resistant transponder for use in paint shops or applications with high thermal stress..</p> <p>Usable for RFID systems:</p> <ul style="list-style-type: none"> • RF200 • RF300 • MOBY D 	2/54			

Benefits

The comprehensive portfolio of ISO 15693 transponders offers the right solution for every requirement in production and production logistics:

- Large memory of up to 8 192 bytes (FRAM)
- Low-cost transponders can, if necessary, be mounted on metal with a spacer.
- Extremely rugged transponder for high temperature ranges up to 220 °C with ATEX approval for use in paint shops.
- Extremely small transponder for exact positioning, e.g. for tool identification.
- Screw-fit transponders for automatic attachment by means of robots.
- Screw-fit transponders for flush-mounting in metal for identifying workpieces or workpiece holders.
- Customized solutions for SmartLabels and transponders on request.

Technical specifications***Field data (operating/limit distance) of transponders and readers (all specifications in mm)***


The the field data (unaffected by metal) for all ISO transponders (MDS Dxxx) in connection with RF200 readers is listed in the technical specifications of the RFID overview. The listed technical data are typical values and are valid for a room temperature of +25 °C.

RFID systems for the HF range

Transponder (ISO mode)

MDS D165/D261

Overview



The SmartLabels MDS D165 and MDS D261 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

SmartLabels permit numerous flexible constructions to ensure optimum dimensioning for many different applications.

Thanks to their very reasonable price, the SmartLabels can be used universally as "electronic barcode substitutes or supplements" or "delivery notes".



6GT2600-1AB00-0AX0¹⁾



6GT2600-1AA01-0AX0

Technical specifications

Article number	6GT2600-1AB00-0AX0	6GT2600-1AA01-0AX0
Product type designation	MDS D165 SmartLabel	MDS D261 SmartLabel
Suitability for operation	RF200, RF300, MOBY D	RF200, RF300, MOBY D
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	500 mm range is reader dependent: observe http://support.automation.siemens.com/WW/view/en/67384964	450 mm
Protocol with radio transmission	ISO 15693	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s
Product feature multitag-capable	Yes	Yes
Product component Backup battery	No	No
Memory		
Type of memory	EEPROM	EEPROM
Storage capacity of the user memory	112 byte	256 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 112 bytes, configuration memory 8 bytes	UID (fixed code) 8 bytes, user memory 256 bytes, configuration memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000	1 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y	10 y
Property of memory	Block-by-block write protection of the user memory	Block-by-block write protection of the user memory
Type of transponder chip used	NXP I-Code SLI	STM LRI2K
Mechanical data		
Material	Top side + inlay: PET, antenna aluminum	Top side + inlay: PET, antenna aluminum
Color	white	white
Mounting distance relating to metal surfaces recommended minimum	25 mm	25 mm

¹⁾ Explanation of symbols: See page 1/8.

RFID systems for the HF range

Transponder (ISO mode)

MDS D165/D261

Article number	6GT2600-1AB00-0AX0	6GT2600-1AA01-0AX0
Product type designation	MDS D165 SmartLabel	MDS D261 SmartLabel
Suitability for operation	RF200, RF300, MOBY D	RF200, RF300, MOBY D
Permitted ambient conditions		
Ambient temperature		
• during read/write access	-25 ... +85 °C	-25 ... +85 °C
• outside the read/write area	-25 ... +85 °C	-25 ... +85 °C
• during storage	20 ... 30 °C	20 ... 30 °C
Protection class IP	IP65	IP65
Resistance to mechanical stress	Maximum storage period: 2 years (determined by durability of the adhesive)	Maximum storage period: 2 years (determined by durability of the adhesive)
Design, dimensions and weight		
Width	54 mm	55 mm
Height	0.3 mm	0.3 mm
Depth	86 mm	55 mm
Net weight	1 g	1 g
Mounting type	one-side adhesible	one-side adhesible
Product properties, functions, components general		
Product feature		
• printable	Yes	Yes
Printing process	Thermal transfer process	Thermal transfer process

Selection and ordering data


	Article No.
MDS D165 SmartLabel	6GT2600-1AB00-0AX0
112 bytes EEPROM	
Ordering quantity 1 000 units or a multiple thereof.	
MDS D261 SmartLabel	6GT2600-1AA01-0AX0
256 bytes EEPROM	
Ordering quantity 1 000 units or a multiple thereof.	

RFID systems for the HF range

Transponder (ISO mode)

MDS D100

Overview



The transponder in credit card format can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application




Applications range from simple identification such as electronic bar code substitution or supplementation, to storage and distribution logistics, up to product identification.


This transponder can even be used problem-free under extreme environmental conditions (e.g. when subjected to temperatures up to +80 °C).

Technical specifications

Article number	6GT2600-0AD10
Product type designation	MDS D100 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	650 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	112 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 112 bytes, configuration memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	NXP I-Code SLI
Mechanical data	
Material	PC laminated plastic
Color	white / petrol
Mounting distance relating to metal surfaces recommended minimum	20 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +80 °C
• outside the read/write area	-25 ... +80 °C
• during storage	-25 ... +80 °C
Protection class IP	IP68
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Resistance to mechanical stress	Shock and vibration according to ISO 10373 / ISO 7810, torsion and twisting according to ISO 10373 / ISO 7816-3
Design, dimensions and weight	
Width	54 mm
Height	0.9 mm
Depth	85.6 mm
Net weight	5 g
Mounting type	Gluing, mounting bag (see accessories)
Product properties, functions, components general	
Product feature	
• printable	Yes
Printing process	Printable on both sides
Standards, specifications, approvals	
MTBF	228 y
Accessories	
Accessories	Fixing strap, holder, spacer

Selection and ordering data

	Article No.
MDS D100 transponder 112 bytes EEPROM Ordering quantity 50 units or a multiple thereof.	6GT2600-0AD10
Accessories	
Fixing pocket For MDS D100, usable together with spacer 6GT2190-0AA00. Ordering quantity 50 units or a multiple thereof.	6GT2190-0AB00
	
Spacer For fixing pocket (6GT2190-0AB00), thickness 20 mm The purpose of the spacer is to maintain the recommended distance to the metal when installing the transponder. Ordering quantity 50 units or a multiple thereof.	6GT2190-0AA00
	
Holder For MDS D100. Ordering quantity 50 units or a multiple thereof.	6GT2390-0AA00
	

Dimensional drawings



MDS D100 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D200

Overview



The MDS D200 is a mobile, passive, maintenance-free transponder based on ISO 15693.

The MDS D200 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application




From simple identification, e.g. as electronic barcode replacement or supplementation, through warehouse and distribution logistics, up to product identification.


Technical specifications

Article number	6GT2600-1AD00-0AX0
Product type designation	MDS D200 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	600 mm; range is reader dependent: observe
http://support.automation.siemens.com/WWW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No

Article number	6GT2600-1AD00-0AX0
Product type designation	MDS D200 transponder
Suitability for operation	RF200, RF300, MOBY D
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	256 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 256 bytes, configuration memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	TI Tag-it HFI
Mechanical data	
Material	PVC laminated plastic
Color	white
Mounting distance relating to metal surfaces recommended minimum	25 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-20 ... +60 °C
• outside the read/write area	-20 ... +60 °C
• during storage	-20 ... +60 °C
Protection class IP	IP67
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Resistance to mechanical stress	Shock and vibration according to ISO 10373 / ISO 7810, torsion and twisting according to ISO 10373 / ISO 7816-3
Design, dimensions and weight	
Width	54 mm
Height	0.8 mm
Depth	85 mm
Net weight	5 g
Mounting type	Gluing, mounting bag (see accessories)
Product properties, functions, components general	
Product feature	
• printable	Yes
Printing process	Printable on both sides
Standards, specifications, approvals	
MTBF	228 y
Accessories	
Accessories	Fixing strap, holder, spacer

Selection and ordering data

	Article No.
MDS D200 transponder 256 bytes EEPROM Ordering quantity 250 units or a multiple thereof.	6GT2600-1AD00-0AX0
Accessories	
Fixing pocket For MDS D200, usable together with spacer 6GT2190-0AA00. Ordering quantity 50 units or a multiple thereof.	6GT2190-0AB00
	
Spacer For fixing pocket (6GT2190-0AB00), thickness 20 mm The purpose of the spacer is to maintain the recommended distance to the metal when installing the transponder. Ordering quantity 50 units or a multiple thereof.	6GT2190-0AA00
	
Holder For MDS D200. Ordering quantity 50 units or a multiple thereof.	6GT2390-0AA00
	

Dimensional drawings


MDS D200 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D400

Overview



The MDS D400 is a passive, maintenance-free transponder based on the ISO standard 15693 with FRAM technology.




The MDS D400 transponder can be used for the RFID system MOBY D as well as for SIMATIC RF300 (ISO mode) and SIMATIC RF200.


Application

ISO transponder, suitable for the identification of transport units in production-related logistics.

Technical specifications

Article number	6GT2600-4AD00
Product type designation	MDS D400 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	650 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	2 000 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 2 000 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R118
Mechanical data	
Material	PVC laminated plastic
Color	white
Mounting distance relating to metal surfaces recommended minimum	20 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-20 ... +60 °C
• outside the read/write area	-20 ... +60 °C
• during storage	-20 ... +60 °C
Protection class IP	IP67
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Resistance to mechanical stress	acc. to ISO 10373/ ISO 7816-1
Design, dimensions and weight	
Width	54 mm
Height	0.8 mm
Depth	85.6 mm
Net weight	5 g
Mounting type	gluing, mounting bag (see accessories)
Product properties, functions, components general	
Product feature	
• printable	Yes
Printing process	Printable on both sides
Standards, specifications, approvals	
MTBF	228 y
Accessories	
Accessories	Fixing strap, holder, spacer

Selection and ordering data	
	Article No.
MDS D400 transponder 2 000 bytes EEPROM.	6GT2600-4AD00
Accessories	
Fixing pocket For MDS D400, usable together with spacer 6GT2190-0AA00. Ordering quantity 50 units or a multiple thereof.	6GT2190-0AB00
	
Spacer For fixing pocket (6GT2190-0AB00), thickness 20 mm The purpose of the spacer is to maintain the recommended distance to the metal when installing the transponder. Ordering quantity 50 units or a multiple thereof.	6GT2190-0AA00
	
Holder For MDS D400. Ordering quantity 50 units or a multiple thereof.	6GT2390-0AA00
	



MDS D400 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D421

Overview



The MDS D421 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

Note

This transponder is used exclusively with the following readers/antennas:

- RF210R
- RF250R with ANT 8, ANT 12 or ANT 18
- RF350R with ANT 12 or ANT 18
- RF350M with external antenna

Application

The MDS D421 is designed for tool coding according to DIN 69873.

It can be used wherever small transponders and exact positioning are required, for example, for tool identification or on workpiece holders.


Technical specifications

Article number	6GT2600-4AE00
Product type designation	MDS D421 transponder
Suitability for operation	RF200, RF300
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	8 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	2 000 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 2 000 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R118
Mechanical data	
Material	Epoxy resin
Color	black
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +100 °C
• during storage	-40 ... +100 °C
Protection class IP	IP67 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	4.5 mm
Diameter	10 mm
Net weight	1 g
Mounting type	gluing
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
• printable	No

Selection and ordering data

	Article No.
MDS D421 transponder 2 000 bytes FRAM Ordering quantity 10 units or a multiple thereof.	6GT2600-4AE00

Dimensional drawings



MDS D421 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D521

Overview



8 Kbyte



METAL



ISO

The MDS D521 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The transponder can only be operated with the SIMATIC RF200 RFID system.

Application

The MDS D521 is designed for tool coding according to DIN 69873.


It can be used wherever small transponders and exact positioning are required, for example, for tool identification or on workpiece holders.

Technical specifications

Article number	6GT2600-5AE00
Product type designation	MDS D521 transponder
Suitability for operation	RF200
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	5 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	8 192 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 8 192 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R112
Mechanical data	
Material	Epoxy resin
Color	black
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +100 °C
• during storage	-40 ... +100 °C
Protection class IP	IP67 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	4.5 mm
Diameter	10 mm
Net weight	1 g
Mounting type	gluing
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
• printable	No

Selection and ordering data

	Article No.
MDS D521 transponder 8 192 byte FRAM Ordering quantity 10 units or a multiple thereof.	6GT2600-5AE00

Dimensional drawings

MDS D521 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D422

Overview



The MDS D422 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The transponder can be operated with the SIMATIC RF200 and SIMATIC RF300 (ISO mode) RFID systems.

When operated with a mobile reader, the RF350M must be used with an external antenna.

Application


Identification of metallic workpiece holders, workpieces or containers.

Technical specifications

Article number	6GT2600-4AF00
Product type designation	MDS D422 transponder
Suitability for operation	RF200, RF300
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	19 mm; range is reader dependent: observe http://support.automation.siemens.com/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	2 000 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 2 000 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R118
Mechanical data	
Material	PA6.6 GF / brass, nickel-plated
Color	black / silver
Tightening torque of the screw for securing the equipment maximum	1 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +100 °C
• during storage	-40 ... +100 °C
Protection class IP	IP68
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	6 mm
Diameter	20 mm
Net weight	13 g
Mounting type	gluing, screwing
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
• printable	No
Standards, specifications, approvals	
MTBF	228 y

Selection and ordering data

	Article No.
MDS D422 transponder 2 000 bytes FRAM One installation tool is included in each packing unit. Ordering quantity 5 units or a multiple thereof.	6GT2600-4AF00

Dimensional drawings


MDS D422 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D522

Overview



The MDS D522 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The transponder can only be operated with the RFID system SIMATIC RF200.

Operation with a mobile reader is currently only possible with RF210M.

Application

Identification of metallic workpiece holders, workpieces or containers.

Technical specifications

Article number	6GT2600-5AF00	6GT2600-5AF00-0AX0
Product type designation	MDS D522 transponder For gluing or screwing	MDS D522 transponder For clipping
Suitability for operation	RF200	RF200
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	35 mm; range is reader dependent: observe	35 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964		
Protocol with radio transmission	ISO 15693	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s
Product feature multitag-capable	Yes	Yes
Product component Backup battery	No	No
Memory		
Type of memory	FRAM	FRAM
Storage capacity of the user memory	8 192 byte	8 192 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 8 192 bytes, configuration memory 40 bytes	UID (fixed code) 8 bytes, user memory 8 192 bytes, configuration memory 48 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y	10 y
Property of memory	Block-by-block write protection of the user memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R112	Fujitsu MB89R112
Mechanical data		
Material	PA6.6 GF / brass, nickel-plated	PA6.6 GF
Color	black / silver	black
Tightening torque of the screw for securing the equipment maximum	1 Nm	-
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm
Permitted ambient conditions		
Ambient temperature		
• during read/write access	-25 ... +85 °C	-25 ... +85 °C
• outside the read/write area	-40 ... +100 °C	-40 ... +100 °C
• during storage	-40 ... +100 °C	-40 ... +100 °C
Protection class IP	IP68	IP68
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²

RFID systems for the HF range

Transponder (ISO mode)


MDS D522

Article number	6GT2600-5AF00	6GT2600-5AF00-0AX0
Product type designation	MDS D522 transponder For gluing or screwing	MDS D522 transponder For clipping
Suitability for operation	RF200	RF200
Design, dimensions and weight		
Height	6 mm	5.2 mm
Diameter	20 mm	18 mm
Net weight	13 g	1.2 g
Mounting type	gluing, screwing	Clip into the pre-milled contour according to the operating instructions
Product properties, functions, components general		
Product feature		
• silicon-free	Yes	Yes
• printable	No	No
Standards, specifications, approvals		
MTBF	228 y	200 y


Selection and ordering data

	Article No.
MDS D522 transponder	
For SIMATIC RF200	
8 192 byte FRAM	
Ordering quantity 10 units or a multiple thereof.	
• For attachment with glue or screws onto metal.	
One screw-in aid is included in each packing unit.	6GT2600-5AF00
• for clipping onto metal	6GT2600-5AF00-0AX0

Dimensional drawings



MDS D522 transponder for gluing or screwing (6GT2600-5AF00)



MDS D522 transponder for clip attachment (6GT2600-5AF00-0AX0)

RFID systems for the HF range

Transponder (ISO mode)

MDS D423

Overview



The MDS D423 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The transponder can be operated with the SIMATIC RF200 and SIMATIC RF300 (ISO mode) RFID systems.

Application

The particularly compact transponder of small design can be flush-mounted in metal and is thus suitable for identifying metallic workpiece holders, workpieces or containers.


As a result of its high IP68 / IPx9K degree of protection, it is suitable for use in particularly harsh environments such as the passage through washers.

Technical specifications

Article number	6GT2600-4AA00
Product type designation	MDS D423 transponder
Suitability for operation	RF200, RF300
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	80 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	2 000 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 2 000 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R118
Mechanical data	
Material	PPS
Color	black
Tightening torque of the screw for securing the equipment maximum	1 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +100 °C
• during storage	-40 ... +100 °C
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	8 mm
Diameter	30 mm
Net weight	15 g
Mounting type	M4 countersunk screw
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
• printable	No
Standards, specifications, approvals	
MTBF	228 y
Accessories	
Accessories	mounting hood

Selection and ordering data

	Article No.
MDS D423 transponder 2 000 bytes FRAM Ordering quantity 10 units or a multiple thereof.	6GT2600-4AA00
Accessories	
Mounting cover Length = 50 mm, height = 10 mm, temperature range up to 100 °C, ordering quantity 10 units or a multiple thereof.	6GT2690-0AE00


Dimensional drawings




MDS D423 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D124

Overview



The MDS D124 is a mobile, passive, maintenance-free transponder based on the ISO 15693 standard.

The MDS D124 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

This transponder can even be used problem-free under extreme environmental conditions (e.g. when subjected to temperatures up to +180 °C).

Technical specifications

Article number	6GT2600-0AC10
Product type designation	MDS D124 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	300 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No


Article number	6GT2600-0AC10
Product type designation	MDS D124 transponder
Suitability for operation	RF200, RF300, MOBY D
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	112 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 112 bytes, configuration memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	NXP I-Code SLI
Mechanical data	
Material	PPS
Color	black
Tightening torque of the screw for securing the equipment maximum	1 Nm
Mounting distance relating to metal surfaces recommended minimum	15 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +125 °C
• outside the read/write area	-40 ... +180 °C
• during storage	-40 ... +125 °C
Ambient condition for operation	Operating temperature permanent up to 100 °C, at 180 °C: up to 5 000 hours or 3 000 temperature cycles
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	4 mm
Diameter	27 mm
Net weight	5 g
Mounting type	M3 screw, gluing
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
• printable	No
Standards, specifications, approvals	
Certificate of suitability	Ex: II 1 G Ex ia IIC T3/T6 Ga / II 1 D Ex ia IIC T80°C/T180°C
MTBF	171 y
Accessories	
Accessories	Mounting support and spacer

Selection and ordering data

	Article No.
MDS D124 transponder 112 bytes EEPROM Ordering quantity 20 units or a multiple thereof.	6GT2600-0AC10
Accessories	
Mounting support and spacer For MDS D124, MDS D324, MDS D424, MDS D524 and RF320T. Necessary for mounting onto metal surfaces. Diameter = 35 mm, height = 15 mm Ordering quantity 20 units or a multiple thereof.	6GT2690-0AK00



Dimensional drawings




MDS D124 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D324

Overview



The MDS D324 is a passive (maintenance-free) transponder based on ISO 15693.

The MDS D324 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

The MDS D324 was developed for applications in production and distribution logistics as well as product identification.

For the user, the usable application memory amounts to 992 byte.

This transponder can also be easily used in harsh environments under extreme environmental conditions (e.g. with higher thermal stress).

Technical specifications


Article number	6GT2600-3AC00
Product type designation	MDS D324 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	280 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	992 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 992 bytes, configuration memory 24 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Infineon My-D SRF 55V10P
Mechanical data	
Material	Epoxy resin
Color	black
Tightening torque of the screw for securing the equipment maximum	1 Nm
Mounting distance relating to metal surfaces recommended minimum	15 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +125 °C
• outside the read/write area	-40 ... +140 °C
• during storage	-40 ... +140 °C
Protection class IP	IP67
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	4 mm
Diameter	27 mm
Net weight	5 g
Mounting type	M3 screw, gluing
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
• printable	No
Standards, specifications, approvals	
MTBF	171 y
Accessories	
Accessories	Mounting support and spacer

Selection and ordering data

	Article No.
MDS D324 transponder 992 bytes EEPROM Ordering quantity 20 units or a multiple thereof.	6GT2600-3AC00
Accessories	
Mounting support and spacer For MDS D124, MDS D324, MDS D424, MDS D524 and RF320T. Necessary for mounting onto metal surfaces. Diameter = 35 mm, height = 15 mm Ordering quantity 20 units or a multiple thereof.	6GT2690-0AK00



Dimensional drawings



MDS D324 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D424

Overview



The MDS D424 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The MDS D424 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application


The MDS D424 was developed for applications in production and distribution logistics as well as for use in assembly and production lines.

Technical specifications

Article number	6GT2600-4AC00
Product type designation	MDS D424 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	300 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	2 000 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 2 000 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R118
Mechanical data	
Material	Epoxy resin
Color	black
Tightening torque of the screw for securing the equipment maximum	1 Nm
Mounting distance relating to metal surfaces recommended minimum	15 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +100 °C
• during storage	-40 ... +100 °C
Protection class IP	IP67 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	4 mm
Diameter	27 mm
Net weight	5 g
Mounting type	M3 screw, gluing
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
• printable	No
Standards, specifications, approvals	
MTBF	171 y
Accessories	
Accessories	Mounting support and spacer

Selection and ordering data

	Article No.
MDS D424 transponder 2 000 bytes FRAM Ordering quantity 20 units or a multiple thereof.	6GT2600-4AC00
Accessories	
Mounting support and spacer For MDS D124, MDS D324, MDS D424, MDS D524 and RF320T. Necessary for mounting onto metal surfaces. Diameter = 35 mm, height = 15 mm Ordering quantity 20 units or a multiple thereof.	6GT2690-0AK00


Dimensional drawings


MDS D424 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D524

Overview



The MDS D524 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The transponder can only be operated with the SIMATIC RF200 RFID system.

Application


The transponder is designed for use in production and distribution logistics as well as in assembly and production lines.

Technical specifications

Article number	6GT2600-5AC00
Product type designation	MDS D524 transponder
Suitability for operation	RF200
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	300 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	8 192 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 8 192 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R112
Mechanical data	
Material	Epoxy resin
Color	black
Tightening torque of the screw for securing the equipment maximum	1 Nm
Mounting distance relating to metal surfaces recommended minimum	15 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +100 °C
• during storage	-40 ... +100 °C
Protection class IP	IP67 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	4 mm
Diameter	27 mm
Net weight	5 g
Mounting type	M3 screw, gluing
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
• printable	No
Standards, specifications, approvals	
MTBF	171 y
Accessories	
Accessories	Mounting support and spacer

Selection and ordering data

	Article No.
MDS D524 transponder 8 192 byte FRAM Ordering quantity 20 units or a multiple thereof.	6GT2600-5AC00
Accessories	
Mounting support and spacer For MDS D124, MDS D324, MDS D424, MDS D524 and RF320T. Necessary for mounting onto metal surfaces. Diameter = 35 mm, height = 15 mm Ordering quantity 20 units or a multiple thereof.	6GT2690-0AK00


Dimensional drawings



MDS D524 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D425

Overview



The MDS D425 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The MDS D425 can be operated with the SIMATIC RF200 and SIMATIC RF300 (ISO mode) RFID systems.

Application

The MDS D425 is a compact and rugged ISO transponder suitable for screw mounting.

It has been designed for applications in assembly and production lines in the powertrain sector.

Technical specifications

Article number	6GT2600-4AG00
Product type designation	MDS D425 transponder
Suitability for operation	RF200, RF300
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	45 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	2 000 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 2 000 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R118
Mechanical data	
Material	PA6.6 GF / stainless steel
Color	black / silver
Tightening torque of the screw for securing the equipment maximum	6 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +125 °C
• during storage	-40 ... +125 °C
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	10 mm
Diameter	24 mm
Net weight	35 g
Mounting type	screwing (M6)
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
• printable	No
Standards, specifications, approvals	
MTBF	228 y

RFID systems for the HF range


Transponder (ISO mode)

MDS D425

Selection and ordering data

	Article No.
MDS D425 transponder	6GT2600-4AG00
2 000 bytes FRAM	
Ordering quantity 5 units or a multiple thereof.	

Dimensional drawings



MDS D425 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D525

Overview



The MDS D525 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The transponder can only be operated with the SIMATIC RF200 RFID system.

Application

The MDS D525 is a compact and rugged ISO transponder suitable for screw mounting.

It is designed for use in assembly and production lines as well as in the powertrain sector.

Technical specifications

Article number	6GT2600-5AG00
Product type designation	MDS D525 transponder
Suitability for operation	RF200
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	50 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	8 192 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 8 192 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R112
Mechanical data	
Material	PA6.6 GF / stainless steel
Color	black / silver
Tightening torque of the screw for securing the equipment maximum	6 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +125 °C
• during storage	-40 ... +125 °C
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	10 mm
Diameter	24 mm
Net weight	35 g
Mounting type	screwing (M6)
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
• printable	No
Standards, specifications, approvals	
MTBF	228 y

RFID systems for the HF range


Transponder (ISO mode)

MDS D525

Selection and ordering data

	Article No.
MDS D525 transponder	6GT2600-5AG00
8 192 byte FRAM	
Order quantity 5 units or a multiple thereof.	

Dimensional drawings




MDS D525 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D126

Overview



The MDS D126 is a passive (maintenance-free) transponder based on ISO 15693.

The MDS D126 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application


The MDS D126 is a compact and rugged ISO transponder suitable for the identification of transport units in production-related logistics.

The transponder can also be used in harsh environments.

Technical specifications

Article number	6GT2600-0AE00
Product type designation	MDS D126 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	500 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	112 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 112 bytes, configuration memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	NXP I-Code SLI
Mechanical data	
Material	PA6.6 GF
Color	black
Tightening torque of the screw for securing the equipment maximum	1 Nm
Mounting distance relating to metal surfaces recommended minimum	25 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +100 °C
• during storage	-40 ... +100 °C
Protection class IP	IP68
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	3.6 mm
Diameter	50 mm
Net weight	13 g
Mounting type	M4 screw
Product properties, functions, components general	
Product feature	
• printable	No
Standards, specifications, approvals	
MTBF	171 y
Accessories	
Accessories	Mounting support and spacer

Selection and ordering data	
	Article No.
MDS D126 transponder 112 bytes EEPROM Ordering quantity 250 units or a multiple thereof.	6GT2600-0AE00
Accessories	
Mounting support and spacer For MDS D126, necessary for mounting onto metal surfaces. Diameter = 60 mm, height = 30 mm. Ordering quantity 50 units or a multiple thereof.	6GT2690-0AL00



MDS D126 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D426

Overview



The MDS D426 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The MDS D426 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

The MDS D426 is a compact and rugged ISO transponder suitable for the identification of transport units in production-related logistics.

The transponder can also be used in harsh environments.

Technical specifications


Article number	6GT2600-4AH00
Product type designation	MDS D426 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	400 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	2 000 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 2 000 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R118
Mechanical data	
Material	PA6.6 GF
Color	black
Tightening torque of the screw for securing the equipment maximum	1 Nm
Mounting distance relating to metal surfaces recommended minimum	25 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +100 °C
• during storage	-40 ... +100 °C
Protection class IP	IP68
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	3.6 mm
Diameter	50 mm
Net weight	13 g
Mounting type	M4 screw
Product properties, functions, components general	
Product feature	
• printable	No
Standards, specifications, approvals	
MTBF	228 y
Accessories	
Accessories	Mounting support and spacer

Selection and ordering data

	Article No.
MDS D426 transponder 2 000 bytes FRAM Ordering quantity 50 units or a multiple thereof.	6GT2600-4AH00
Accessories	
Mounting support and spacer For MDS D426, necessary for mounting onto metal surfaces. Diameter = 60 mm, height = 30 mm Ordering quantity 50 units or a multiple thereof.	6GT2690-0AL00



Dimensional drawings




MDS D426 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D526

Overview



The MDS D526 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The transponder can only be operated with the SIMATIC RF200 RFID system.

Application

The MDS D526 is a compact and rugged ISO transponder which can also be used under harsh environmental conditions.

It is designed for the identification of transport units in production-related logistics.

Technical specifications


Article number	6GT2600-5AH00
Product type designation	MDS D526 transponder
Suitability for operation	RF200
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	400 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	8 192 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 8 192 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R112
Mechanical data	
Material	PA6.6 GF
Color	black
Tightening torque of the screw for securing the equipment maximum	1 Nm
Mounting distance relating to metal surfaces recommended minimum	25 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +100 °C
• during storage	-40 ... +100 °C
Protection class IP	IP68
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	3.6 mm
Diameter	50 mm
Net weight	13 g
Mounting type	M4 screw
Product properties, functions, components general	
Product feature	
• printable	No
Standards, specifications, approvals	
MTBF	228 y
Accessories	
Accessories	Mounting support and spacer

Selection and ordering data

	Article No.
MDS D526 transponder 8 192 byte FRAM Ordering quantity 50 units or a multiple thereof.	6GT2600-5AH00
Accessories	
Mounting support and spacer For MDS D526, necessary for mounting onto metal surfaces. Diameter = 60 mm, height = 30 mm Ordering quantity 50 units or a multiple thereof.	6GT2690-0AL00



Dimensional drawings




MDS D526 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D117

Overview




The MDS D117 is a passive, maintenance-free transponder based on ISO 15693. It is small and compact and can be mounted on metal using adhesive.

The mobile data memory can be operated with the SIMATIC RF300 (ISO mode) and SIMATIC RF200 RFID systems. When operated with the RF350M mobile handheld terminal, an external antenna must be used.

Application

For direct identification of small metallic workpieces and workpiece holders.




Size comparison of match to MDS D117

Technical specifications

Article number	6GT2600-0AG00
Product type designation	MDS D117 transponder
Suitability for operation	RF200, RF300
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	4 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	112 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 112 bytes, configuration memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	NXP I-Code SLI
Mechanical data	
Material	PPS
Color	black
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +125 °C
• during storage	-40 ... +125 °C
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	5.2 mm
Diameter	4 mm
Net weight	1 g
Mounting type	gluing
Product properties, functions, components general	
Product feature	
• printable	No
Standards, specifications, approvals	
MTBF	228 y

Selection and ordering data

	Article No.
MDS D117 transponder 112 bytes EEPROM Ordering quantity 10 units or a multiple thereof.	6GT2600-0AG00

Dimensional drawings

MDS D117 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D127

Overview



The MDS D127 is a passive, maintenance-free transponder based on ISO 15693. It is small and compact and can be screwed into metal.

The mobile data memory can only be operated with the SIMATIC RF300 (ISO mode) and SIMATIC RF200 RFID systems. When operated with the RF350M mobile handheld terminal, an external antenna must be used.

Application

For direct identification of small metallic workpieces, workpiece holders, or containers.


Technical specifications

Article number	6GT2600-0AF00
Product type designation	MDS D127 transponder
Suitability for operation	RF200, RF300
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	5 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	112 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 112 bytes, configuration memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	NXP I-Code SLI
Mechanical data	
Material	PA6
Color	black
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +100 °C
• outside the read/write area	-40 ... +125 °C
• during storage	-40 ... +125 °C
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	5.8 mm
Diameter	6 mm
Net weight	1 g
Mounting type	gluing, screwing
Product properties, functions, components general	
Product feature	
• printable	No
Standards, specifications, approvals	
MTBF	228 y

Selection and ordering data

	Article No.
MDS 127 transponder 112 bytes EEPROM Ordering quantity 10 units or a multiple thereof.	6GT2600-0AF00

Dimensional drawings



MDS D127 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D428

Overview



2 Kbyte



METAL



ISO

The MDS D428 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The MDS D428 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

The MDS D428 is a compact and rugged ISO transponder suitable for screw mounting.

It has been designed for applications in assembly and production lines in the powertrain sector.

Technical specifications

Article number	6GT2600-4AK00-0AX0
Product type designation	MDS D428 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	160 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	2 000 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 2 000 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R118
Mechanical data	
Material	PA6.6 GF / stainless steel
Color	black / silver
Tightening torque of the screw for securing the equipment maximum	6 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +125 °C
• during storage	-40 ... +125 °C
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	20 mm
Diameter	24 mm
Net weight	35 g
Mounting type	screwing (M8)
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
• printable	No

Selection and ordering data

Article No.

MDS D428 transponder


2 000 bytes FRAM

With surface protection plate to prevent scratching of the screw-in surface.

Ordering quantity 5 units or a multiple thereof.

6GT2600-4AK00-0AX0

Dimensional drawings



MDS D428 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D528

Overview



8 Kbyte



METAL



ISO

The MDS D528 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The transponder can only be operated with the SIMATIC RF200 RFID system.

Application

The MDS D528 is a compact and rugged ISO transponder suitable for screw mounting.


It is designed for use in assembly and production lines as well as in the powertrain sector.

Technical specifications

Article number	6GT2600-5AK00
Product type designation	MDS D528 transponder
Suitability for operation	RF200
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	160 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	8 192 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 8 192 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R112
Mechanical data	
Material	PA6.6 GF / stainless steel
Color	black / silver
Tightening torque of the screw for securing the equipment maximum	6 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +125 °C
• during storage	-40 ... +125 °C
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	20 mm
Diameter	18 mm
Net weight	35 g
Mounting type	screwing (M8)
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
• printable	No

Selection and ordering data
Article No.
MDS D528 transponder

8 192 bytes of FRAM user memory
 With surface protection plate to
 prevent scratching of the screw-in
 surface.
 Ordering quantity 5 units or a
 multiple thereof.

6GT2600-5AK00
Dimensional drawings



MDS D528 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D139

Overview



The MDS D139 is a passive (maintenance-free), heat-resistant transponder based on the ISO 15693 standard.

The MDS D139 can be used both for the MOBY D RFID system as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application




Applications in production logistics and in assembly lines subject to high temperatures (up to +200 °C, e.g. in a paint shop).


Technical specifications

Article number	6GT2600-0AA10
Product type designation	MDS D139 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	600 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No

Article number	6GT2600-0AA10
Product type designation	MDS D139 transponder
Suitability for operation	RF200, RF300, MOBY D
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	112 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 112 bytes, configuration memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	NXP I-Code SLI
Mechanical data	
Material	PPS
Color	black
Tightening torque of the screw for securing the equipment maximum	1.5 Nm
Mounting distance relating to metal surfaces recommended minimum	30 mm
Permitted ambient conditions	
Ambient temperature	-25 ... +100 °C
• during read/write access	-40 ... +220 °C
• outside the read/write area	-40 ... +100 °C
• during storage	-40 ... +100 °C
Ambient condition for operation	Operating temperature permanent up to 100 °C, at 220 °C: up to 2 000 hours or 1 500 temperature cycles, at 200 °C: up to 5 000 hours or 3 000 temperature cycles
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	15 mm
Diameter	85 mm
Net weight	50 g
Mounting type	M5 screw
Product properties, functions, components general	
Product feature	Yes
• silicon-free	No
• printable	No
Standards, specifications, approvals	
Certificate of suitability	Ex: II 3 G Ex nA II T2, II 3 D Ex tD A22 IP68 T 210°C
MTBF	228 y
Accessories	
Accessories	Spacer, quick-change holder

Selection and ordering data

	Article No.
MDS D139 transponder 112 bytes EEPROM Ordering quantity 10 units or a multiple thereof.	6GT2600-0AA10
Accessories	
Spacer Necessary for mounting onto metal surfaces. Ordering quantity 10 units or a multiple thereof.	6GT2690-0AA00
	
Quick change holder For MDS D139, stainless steel, diameter = 22 mm, height = 48 mm. Fixing with M8 nut. Ordering quantity 10 units or a multiple thereof.	6GT2690-0AH00
	
Quick change holder For MDS D139, stainless steel, diameter = 22 mm, height = 48 mm. With M10 female thread Ordering quantity 10 units or a multiple thereof.	6GT2690-0AH10
	

Dimensional drawings


MDS D139 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D339

Overview



The MDS D339 is a passive (maintenance-free), heat-resistant transponder based on ISO 15693.

The MDS D339 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application




Applications in production logistics and in assembly lines subject to high temperatures (up to +220 °C, e.g. in a paint shop).


Technical specifications

Article number	6GT2600-3AA10
Product type designation	MDS D339 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	480 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No

Article number	6GT2600-3AA10
Product type designation	MDS D339 transponder
Suitability for operation	RF200, RF300, MOBY D
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	992 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 992 bytes, configuration memory 24 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Infineon My-D SRF 55V10P
Mechanical data	
Material	PPS
Color	black
Tightening torque of the screw for securing the equipment maximum	1.5 Nm
Mounting distance relating to metal surfaces recommended minimum	30 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +100 °C
• outside the read/write area	-40 ... +220 °C
• during storage	-40 ... +100 °C
Ambient condition for operation	Operating temperature permanent up to 100 °C, at 220 °C: up to 2 000 hours or 1 500 temperature cycles, at 200 °C: up to 5 000 hours or 3 000 temperature cycles
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	15 mm
Diameter	85 mm
Net weight	50 g
Mounting type	M5 screw
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
• printable	No
Standards, specifications, approvals	
Certificate of suitability	Ex: II 3 G Ex nA II T2, II 3 D Ex tD A22 IP68 T 210°C
MTBF	228 y
Accessories	
Accessories	Spacer, quick-change holder

Selection and ordering data

	Article No.
MDS D339 transponder 992 bytes EEPROM Ordering quantity 10 units or a multiple thereof.	6GT2600-3AA10
Accessories	
Spacer Necessary for mounting onto metal surfaces. Ordering quantity 10 units or a multiple thereof.	6GT2690-0AA00
	
Quick change holder For MDS D339, stainless steel, diameter = 22 mm, height = 48 mm. Fixing with M8 nut. Ordering quantity 10 units or a multiple thereof.	6GT2690-0AH00
	
Quick change holder For MDS D339, stainless steel, diameter = 22 mm, height = 48 mm. With M10 female thread Ordering quantity 10 units or a multiple thereof	6GT2690-0AH10
	

Dimensional drawings




MDS D339 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D160

Overview



The MDS D160 is a passive, maintenance-free and rugged transponder based on the ISO 15693 standard.

The MDS D160 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

Typical applications are, for example:

- Rented work clothing
- Hotel laundry
- Surgical textiles
- Hospital clothing
- Dirt collection mats
- Clothing for nursing homes/hostels

Technical specifications

Article number	6GT2600-0AB10
Product type designation	MDS D160 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	180 mm; range is reader dependent: observe
http://support.automation.siemens.com/WWW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No


Article number	6GT2600-0AB10
Product type designation	MDS D160 transponder
Suitability for operation	RF200, RF300, MOBY D
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	112 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 112 bytes, configuration memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	NXP I-Code SLI
Mechanical data	
Material	PPS
Color	beige
Mounting distance relating to metal surfaces recommended minimum	10 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +175 °C
• during storage	-25 ... +100 °C
Ambient condition for operation	Operating temperature permanent up to 100 °C, up to 175 °C min. 100 washing cycles, one time up to 220 °C for 30 s
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	400 m/s ²
Vibrational acceleration	100 m/s ²
Design, dimensions and weight	
Height	3 mm
Diameter	16 mm
Net weight	1.2 g
Mounting type	patch, sewing, gluing
Product properties, functions, components general	
Product feature	
• printable	No
Standards, specifications, approvals	
MTBF	228 y
Accessories	
Accessories	Mounting support and spacer

Selection and ordering data

	Article No.
MDS D160 transponder 112 bytes EEPROM Ordering quantity 100 units or a multiple thereof.	6GT2600-0AB10
Accessories	
Spacer for MDS D160 For MDS D160, necessary for mounting onto metal surfaces. Diameter = 20 mm, height = 15 mm. Ordering quantity 50 units or a multiple thereof.	6GT2690-0AG00



Dimensional drawings



MDS D160 transponder

RFID systems for the HF range

Transponder (ISO mode)

MDS D460

Overview



The MDS D460 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The MDS D460 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

The MDS D460 has been designed for identification tasks in small assembly lines.

Technical specifications


Article number	6GT2600-4AB00
Product type designation	MDS D460 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	160 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	2 000 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 2 000 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R118
Mechanical data	
Material	Epoxy resin
Color	black
Mounting distance relating to metal surfaces recommended minimum	10 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +100 °C
• during storage	-40 ... +100 °C
Protection class IP	IP67 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	3 mm
Diameter	16 mm
Net weight	3 g
Mounting type	patching, gluing
Product properties, functions, components general	
Product feature	
• printable	No
Standards, specifications, approvals	
MTBF	228 y
Accessories	
Accessories	Mounting support and spacer

Selection and ordering data

	Article No.
MDS D460 transponder 2 000 bytes FRAM Ordering quantity 50 units or a multiple thereof.	6GT2600-4AB00
Accessories	
Spacer For MDS D460, necessary for mounting onto metal surfaces. Diameter = 20 mm, height = 15 mm Ordering quantity 50 units or a multiple thereof.	6GT2690-0AG00



Dimensional drawings



MDS D460 transponder

RFID systems for the HF range

Transponder (RF300 mode)

Introduction

Overview

The following RF300 mode transponders can be used with the SIMATIC RF300 RFID system:

Transponder	Features	Page	Transponder	Features	Page
RF320T 	Small, compact, universal transponder. 20 byte EEPROM	2/61	RF370T 	Universal transponder with 32 KB or 64 KB memory, for mounting directly on metal, suitable for longer ranges.	2/71
RF330T 	Transponder, can be directly flush-mounted on metal. For directly identifying metallic workpieces or containers. 32 KB FRAM	2/63	RF380T 	Heat-resistant transponder, designed for skid identification in paint shops, for mounting directly on metal. Temperature range to +220 °C. 32 KB FRAM	2/73
RF340T 	Universal transponder, for mounting directly on metal, e.g. workpiece holders. 8 or 32 KB FRAM	2/65	<div>  Designed for Industry </div> <p>The comprehensive portfolio of SIMATIC RF300 transponders offers the right solution for every requirement in production:</p> <ul style="list-style-type: none"> • For high-performance applications. • Large memory up to 64 KB. • IP68 / IPx9K degree of protection. • Extremely rugged transponder for high temperature ranges up to 220 degrees with ATEX approval for use in paint shops. • Customized solutions for SmartLabels and transponders on request. 		
RF350T 	Universal transponder, for mounting directly on metal, suitable for longer ranges. 32 KB FRAM	2/67			
RF360T 	Universal transponder in credit card format. For mounting onto metal with spacer. 8 or 32 KB FRAM	2/69			

Benefits

get Designed for Industry

The comprehensive portfolio of SIMATIC RF300 transponders offers the right solution for every requirement in production:


- For high-performance applications.
- Large memory up to 64 KB.
- IP68 / IPx9K degree of protection.
- Extremely rugged transponder for high temperature ranges up to 220 degrees with ATEX approval for use in paint shops.
- Customized solutions for SmartLabels and transponders on request.

Technical specifications

Field data (operating/limit distance) of transponders and readers (all specifications in mm)

The field data (unaffected by metal) of the RF300 transponders in connection with RF300 readers is listed in the technical specifications of the RFID overview. The listed technical data are typical values and are valid for a room temperature of +25 °C.

For detailed descriptions and ordering data of these RF300 transponders: Refer to the following product nodes.

Overview


Universal, compact transponder (20 bytes EEPROM + 4 bytes serial number) in button format. Dimensions Ø x H (mm): 27 x 4.

2

Technical specifications

Article number	6GT2800-1CA00
Product type designation	RF320T transponder
Suitability for operation	RF300
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	60 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	RF300-specific
Transfer rate with radio transmission maximum	106 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	20 byte
Type of memory organization	UID (fixed code) 4 bytes, user memory 20 bytes, 100 000 000 000 000
Number of read cycles at ambient temperature < 40 °C maximum	
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Mechanical data	
Material	Epoxy resin
Color	black
Mounting distance relating to metal surfaces recommended minimum	20 mm

Article number	6GT2800-1CA00
Product type designation	RF320T transponder
Suitability for operation	RF300
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +125 °C
• outside the read/write area	-40 ... +140 °C
• during storage	-40 ... +140 °C
Protection class IP	IP67 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	4 mm
Diameter	27 mm
Net weight	5 g
Mounting type	M3 screw, gluing
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
• printable	No
Standards, specifications, approvals	
MTBF	1 800 y
Accessories	
Accessories	Mounting support and spacer

RFID systems for the HF range

Transponder (RF300 mode)


RF320T

Selection and ordering data

	Article No.
SIMATIC RF320T transponder 20 bytes EEPROM Ordering quantity 20 units or a multiple thereof.	6GT2800-1CA00
Accessories	
Spacer For MDS D124, MDS D324, MDS D424, MDS D524 and RF320T. Necessary for mounting onto metal surfaces. Diameter = 35 mm, height = 15 mm. Ordering quantity 20 units or a multiple thereof.	6GT2690-0AK00



Dimensional drawings




SIMATIC RF320T transponder

RFID systems for the HF range

Transponder (RF300 mode)

RF330T

Overview



The SIMATIC RF330T is a universal transponder. This compact transponder can be flush-mounted in and on metal. It is thus suitable for directly identifying metallic workpiece holders, workpieces or containers. Thanks to its high IP68/IPx9K degree of protection, it is suitable for use in particularly harsh environments such as the passage through washers.

Technical specifications

Article number	6GT2800-5BA00
Product type designation	RF330T transponder
Suitability for operation	RF300
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	52 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	RF300-specific
Transfer rate with radio transmission maximum	106 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM/EEPROM
Storage capacity of the user memory	32 765 byte
Type of memory organization	UID (fixed code) 4 bytes, user memory 32 765 bytes, OTP memory 20 bytes
Number of read cycles at ambient temperature < 40 °C maximum	10 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	10 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the OTP memory

Article number	6GT2800-5BA00
Product type designation	RF330T transponder
Suitability for operation	RF300
Mechanical data	
Material	PPS
Color	black
Tightening torque of the screw for securing the equipment maximum	1.2 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +100 °C
• during storage	-40 ... +100 °C
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	8 mm
Diameter	30 mm
Net weight	15 g
Mounting type	M4 countersunk screw
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
• printable	No
Standards, specifications, approvals	
MTBF	1 200 y
Accessories	
Accessories	mounting hood

RFID systems for the HF range

Transponder (RF300 mode)


RF330T

Selection and ordering data

	Article No.
SIMATIC RF330T transponder 32 KB FRAM Ordering quantity 10 units or a multiple thereof.	6GT2800-5BA00
Accessories	
Mounting cover Length = 50 mm, height = 10 mm, temperature range up to 100 °C, ordering quantity 10 units or a multiple thereof.	6GT2690-0AE00



Dimensional drawings



SIMATIC RF330T transponder

Overview



Universal transponder, especially suitable for small workpiece holders. The transponder can be mounted directly onto metal surfaces.

 8 Kbyte	 METAL	 RF300	 Speed	6GT2800-4BB00
 32 Kbyte	 METAL	 RF300	 Speed	6GT2800-5BB00

Technical specifications

Article number	6GT2800-4BB00	6GT2800-5BB00
Product type designation	RF340T transponder	RF340T transponder
Suitability for operation	RF300	RF300
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	105 mm; range is reader dependent: observe http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	RF300-specific	RF300-specific
Transfer rate with radio transmission maximum	106 kbit/s	106 kbit/s
Product feature multitag-capable	Yes	Yes
Product component Backup battery	No	No
Memory		
Type of memory	FRAM/EEPROM	FRAM/EEPROM
Storage capacity of the user memory	8 189 byte	32 765 byte
Type of memory organization	UID (fixed code) 4 bytes, user memory 8 189 bytes, OTP memory 20 bytes	UID (fixed code) 4 bytes, user memory 32 765 bytes, OTP memory 20 bytes
Number of read cycles at ambient temperature < 40 °C maximum	10 000 000 000	10 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	10 000 000 000	10 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y	10 y
Property of memory	Block-by-block write protection of the OTP memory	Block-by-block write protection of the OTP memory

RFID systems for the HF range

Transponder (RF300 mode)


RF340T

Article number	6GT2800-4BB00	6GT2800-5BB00
Product type designation	RF340T transponder	RF340T transponder
Suitability for operation	RF300	RF300
Mechanical data		
Material	PA12	PA12
Color	anthracite	anthracite
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm
Permitted ambient conditions		
Ambient temperature		
• during read/write access	-25 ... +85 °C	-25 ... +85 °C
• outside the read/write area	-40 ... +85 °C	-40 ... +85 °C
• during storage	-40 ... +85 °C	-40 ... +85 °C
Protection class IP	IP67 / IPx9K	IP67 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²
Design, dimensions and weight		
Width	25 mm	25 mm
Height	15 mm	15 mm
Depth	48 mm	48 mm
Net weight	25 g	25 g
Mounting type	2 x M3 screws	2 x M3 screws
Product properties, functions, components general		
Product feature		
• silicon-free	Yes	Yes
• printable	No	No
Standards, specifications, approvals		
MTBF	1 200 y	1 200 y

Selection and ordering data

	Article No.
SIMATIC RF340T transponder	
• 8 KB FRAM Ordering quantity 5 units or a multiple thereof.	6GT2800-4BB00
• 32 KB FRAM Order quantity 5 units or a multiple thereof.	6GT2800-5BB00

Dimensional drawings



SIMATIC RF340T transponder

RFID systems for the HF range

Transponder (RF300 mode)

RF350T

Overview



Universal transponder. The transponder can be mounted directly onto metal surfaces.

Technical specifications

Article number	6GT2800-5BD00
Product type designation	RF350T transponder
Suitability for operation	RF300
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	125 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	RF300-specific
Transfer rate with radio transmission maximum	106 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM/EEPROM
Storage capacity of the user memory	32 765 byte
Type of memory organization	UID (fixed code) 4 bytes, user memory 32 765 bytes, OTP memory 20 bytes
Number of read cycles at ambient temperature < 40 °C maximum	10 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	10 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the OTP memory

Article number	6GT2800-5BD00
Product type designation	RF350T transponder
Suitability for operation	RF300
Mechanical data	
Material	PA12
Color	anthracite
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +85 °C
• during storage	-40 ... +85 °C
Protection class IP	IP68
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Width	50 mm
Height	20 mm
Depth	50 mm
Net weight	25 g
Mounting type	2 x M4 screws
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
• printable	No
Standards, specifications, approvals	
MTBF	1 200 y

Selection and ordering data


	Article No.
SIMATIC RF350T transponder	6GT2800-5BD00
32 Kbyte FRAM	

RFID systems for the HF range

Transponder (RF300 mode)

RF350T

Dimensional drawings



Overview



Universal transponder in credit card format. The transponder can be mounted on metal with spacers.

			6GT2800-4AC00
8 Kbyte	RF300	Speed	
			6GT2800-5AC00
32 Kbyte	RF300	Speed	

Technical specifications

Article number	6GT2800-4AC00	6GT2800-5AC00
Product type designation	RF360T transponder	RF360T transponder
Suitability for operation	RF300	RF300
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	150 mm; range is reader dependent: observe http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	RF300-specific	RF300-specific
Transfer rate with radio transmission maximum	106 kbit/s	106 kbit/s
Product feature multitag-capable	Yes	Yes
Product component Backup battery	No	No
Memory		
Type of memory	FRAM/EEPROM	FRAM/EEPROM
Storage capacity of the user memory	8 189 byte	32 765 byte
Type of memory organization	UID (fixed code) 4 bytes, user memory 8 189 bytes, OTP memory 20 bytes	UID (fixed code) 4 bytes, user memory 32 765 bytes, OTP memory 20 bytes
Number of read cycles at ambient temperature < 40 °C maximum	10 000 000 000	10 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	10 000 000 000	10 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y	10 y
Property of memory	Block-by-block write protection of the OTP memory	Block-by-block write protection of the OTP memory
Mechanical data		
Material	Epoxy resin	Epoxy resin
Color	anthracite	anthracite
Mounting distance relating to metal surfaces recommended minimum	20 mm	20 mm



RFID systems for the HF range

Transponder (RF300 mode)


RF360T

Article number	6GT2800-4AC00	6GT2800-5AC00
Product type designation	RF360T transponder	RF360T transponder
Suitability for operation	RF300	RF300
Permitted ambient conditions		
Ambient temperature		
• during read/write access	-25 ... +75 °C	-25 ... +75 °C
• outside the read/write area	-40 ... +85 °C	-40 ... +85 °C
• during storage	-40 ... +85 °C	-40 ... +85 °C
Protection class IP	IP67	IP67
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²
Resistance to mechanical stress	Continuous torsion and bending stress not permissible	Continuous torsion and bending stress not permissible
Design, dimensions and weight		
Width	55 mm	55 mm
Height	2.5 mm	2.5 mm
Depth	86 mm	86 mm
Net weight	25 g	25 g
Mounting type	2 x M3 screws, mounting bag (see accessories)	2 x M3 screws, mounting bag (see accessories)
Product properties, functions, components general		
Product feature		
• silicon-free	Yes	Yes
• printable	No	No
Standards, specifications, approvals		
MTBF	1 200 y	1 200 y
Accessories	Fixing strap, holder	Fixing strap, holder

Selection and ordering data

	Article No.
SIMATIC RF360T transponder	
• 8 Kbyte FRAM Ordering quantity 10 units or a multiple thereof..	6GT2800-4AC00
• 32 Kbyte FRAM Ordering quantity 10 units or a multiple thereof.	6GT2800-5AC00
Accessories	
Fixing pocket	
For SIMATIC RF360T, only usable together with spacer 6GT2190-0AA00. Ordering quantity 50 units or a multiple thereof.	6GT2190-0AB00
	
Spacer	
For fixing pocket (6GT2190-0AB00), thickness 20 mm. The purpose of the spacer is to maintain the recommended distance to the metal when installing the transponder. Ordering quantity 50 units or a multiple thereof.	6GT2190-0AA00
	

Dimensional drawings



SIMATIC RF360T transponder

Overview



Universal transponder in cuboid form. The transponder can be mounted directly onto metal surfaces.

 32 Kbyte	 METAL	 RF300	 Speed	6GT2800-5BE00
 64 Kbyte	 METAL	 RF300	 Speed	6GT2800-6BE00

Technical specifications

Article number	6GT2800-5BE00	6GT2800-6BE00
Product type designation	RF370T transponder	RF370T transponder
Suitability for operation	RF300	RF300
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	135 mm; range is reader dependent: observe http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	RF300-specific	RF300-specific
Transfer rate with radio transmission maximum	106 kbit/s	106 kbit/s
Product feature multitag-capable	Yes	Yes
Product component Backup battery	No	No
Memory		
Type of memory	FRAM/EEPROM	FRAM/EEPROM
Storage capacity of the user memory	32 765 byte	65 277 byte
Type of memory organization	UID (fixed code) 4 bytes, user memory 32 765 bytes, OTP memory 20 bytes	UID (fixed code) 4 bytes, user memory 65 277 bytes, OTP memory 20 bytes
Number of read cycles at ambient temperature < 40 °C maximum	10 000 000 000	10 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	10 000 000 000	10 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y	10 y
Property of memory	Block-by-block write protection of the OTP memory	Block-by-block write protection of the OTP memory

RFID systems for the HF range

Transponder (RF300 mode)


RF370T

Article number	6GT2800-5BE00	6GT2800-6BE00
Product type designation	RF370T transponder	RF370T transponder
Suitability for operation	RF300	RF300
Mechanical data		
Material	PA12	PA12
Color	anthracite	anthracite
Tightening torque of the screw for securing the equipment maximum	1.2 Nm	1.2 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm
Permitted ambient conditions		
Ambient temperature		
• during read/write access	-25 ... +85 °C	-25 ... +85 °C
• outside the read/write area	-40 ... +85 °C	-40 ... +85 °C
• during storage	-40 ... +85 °C	-40 ... +85 °C
Protection class IP	IP68	IP68
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²
Design, dimensions and weight		
Width	75 mm	75 mm
Height	41 mm	41 mm
Depth	75 mm	75 mm
Net weight	200 g	200 g
Mounting type	2 x M5 screws	2 x M5 screws
Product properties, functions, components general		
Product feature		
• silicon-free	Yes	Yes
• printable	No	No
Standards, specifications, approvals		
MTBF	1 200 y	1 200 y

Selection and ordering data

	Article No.
SIMATIC RF370T transponder	
• 32 KB FRAM	6GT2800-5BE00
• 64 KB FRAM	6GT2800-6BE00

Dimensional drawings



SIMATIC RF370T transponder

Overview



Heat-resistant transponder, designed for skid identification in paint shops, temperature range up to +220 °C (cyclic).

Application

Typical applications are:

- Primer application, cataphoresis with the associated drying ovens
- Outer paint coating area with drying ovens
- Washing area with temperatures > +85 °C

2

Mode of operation

Cyclic operation of the transponder at temperatures > 100 °C

At ambient temperatures between +110 °C and +220 °C, care must be taken to ensure that the internal temperature of the SIMATIC RF380T does not exceed the critical threshold of +110 °C. Each heating phase must therefore be followed by a cooling phase. Some limit cycles are listed in the table below.

Heating up		Cooling down	
Temperature	Time	Temperature	Time
200 °C	2 h	25 °C	> 8 h
200 °C	1 h	25 °C	> 2 h
190 °C	2 h	25 °C	> 7 h
190 °C	1 h	25 °C	> 1 h 45 min
180 °C	2 h	25 °C	> 5 h 30 min
180 °C	2 h	25 °C	> 4 h 30 min

A temperature calculation tool computes the temperature curve for the heat-proof SIMATIC RF380T transponder (see DVD "RFID Systems Software & Documentation", Article No. 6GT2080-2AA20).

RFID systems for the HF range

Transponder (RF300 mode)


RF380T

Technical specifications


Article number	6GT2800-5DA00
Product type designation	RF380T transponder
Suitability for operation	RF300
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	160 mm; range is reader dependent: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	RF300-specific
Transfer rate with radio transmission maximum	106 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM/EEPROM
Storage capacity of the user memory	32 765 byte
Type of memory organization	UID (fixed code) 4 bytes, memory 32 765 bytes, OTP memory 20 bytes
Number of read cycles at ambient temperature < 40 °C maximum	10 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	10 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the OTP memory
Mechanical data	
Material	PPS
Color	brown
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
• during read/write access	-25 ... +110 °C
• outside the read/write area	-40 ... +220 °C
• during storage	-40 ... +110 °C
Ambient condition for operation	Cyclic operation at ambient temperature > 110 °C
Protection class IP	IP68
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	83 mm
Diameter	114 mm
Net weight	900 g
Mounting type	mount (see accessories)
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
• printable	No
Standards, specifications, approvals	
Certificate of suitability	Ex: II 3G Ex nC IIB T5
MTBF	1 200 y
Accessories	
Accessories	Skid holder, shrouding cover, universal holder

Selection and ordering data


	Article No.
Transponder SIMATIC RF380T	6GT2800-5DA00
With 32 KB FRAM	
Accessories	
Skid support for SIMATIC RF380T	6GT2090-0QA00
Short type	
	
Universal support	6GT2590-0QA00
For SIMATIC RF380T, e.g. for attaching to the body.	
	
Shrouding cover	6GT2090-0QB00
For skid support.	
	

Dimensional drawings



SIMATIC RF380T transponder



Universal holder for RF380T



Skid holder for RF380T



Skid holder, shrouding cover for RF380T

RFID systems for the HF range

SIMATIC RF200

Introduction

Overview



The RFID system SIMATIC RF200 is, thanks to its compact and low-cost reader, particularly suitable for use in industrial production in the areas of small assembly lines and intralogistics.

With RF200, identification tasks of medium-performance in the RF range (13.56 MHz, ISO 15693) can be implemented extremely cost effectively. RF200 readers can be operated with all ISO transponders.

The communication modules that can be used for all MOBY and SIMATIC RF systems (ASM 456, ASM 475, SIMATIC RF1xxC) are available for connecting to SIMATIC S7, PROFIBUS, PROFINET, Ethernet/IP and TCP/IP (XML).

IO-Link

For simple identification tasks (e.g. reading an identification number) the RF210R/RF220R/RF240R/RF250R/RF260R readers are available in an interface version for IO-Link. With the help of this standardized interface it is extremely easy and economical to integrate the data automatically read by the reader into the automation level. The SIMATIC RF200 readers can be connected to the controllers of many well-known suppliers of automation solutions through an appropriate IO-Link master module.

Siemens offers IO-Link master modules for S7-1200, ET 200S, ET 200SP, ET 200AL and ET 200eco PN. In this way, IO-Link is seamlessly integrated into the established PROFIBUS and PROFIBUS field buses and into the world of Totally Integrated Automation (TIA Portal).

The Siemens master modules allow up to four SIMATIC RF200 IO-Link readers to be connected.

The essential features of IO-Link are:

- Ease of use: No RFID-specific programming is necessary, ideal for RFID beginners.
- Particularly low channel costs per reading point (reader + IO-Link master interface).
- Openness through standardization: Many well-known manufacturers offer IO-Link masters.

The SIMATIC RF200 identification system offers the following features:

- 13.56 MHz operating frequency (operation according to ISO 15693).
- Passive (without battery), maintenance-free transponders (MDS Dxxx) with memory capacities up to 8 KB FRAM.
- Rugged, compact components with IP67 degree of protection.
- Easy integration into SIMATIC, PROFIBUS, PROFINET and TCP/IP.
- Reader versions with RS422, RS232 or IO-Link.

Benefits

get Designed for Industry

- Price-optimized and compact, space-saving components.
- Operation with the attractively priced and battery-free ISO 15693 transponders for low investment and operating costs.
- Flexible and economic solutions thanks to the complete and scalable portfolio for the field of industrial identification.
- Simplified engineering, commissioning, diagnostics and maintenance through seamless integration into Totally Integrated Automation:
 - Integrated bus connection to an automation system, such as SIMATIC, SIMOTION or SINUMERIK via communication modules with PROFIBUS and PROFINET.
 - Simple S7 software integration via ready-to-use function blocks.
- High investment security thanks to:
 - Open ISO 15693 standard.
 - Software compatibility between the RFID systems of Siemens.
 - Standardized communication interfaces.
- Openness through connection options to various bus systems from different manufacturers and PC environments via communication modules, RS232 or IO-Link.
- Worldwide Service and Support.
- tionsmodule, RS232 oder IO-Link.
- Weltweiter Service und Support.

Application

The RFID system SIMATIC RF200 is primarily used for non-contact identification of containers, pallets and workpiece holders where the demands on performance (data transmission rate, memory volume) satisfy the ISO 15693 standard.

The main application areas for SIMATIC RF200 are:

- Assembly and handling systems, assembly lines (identification of workpiece carriers), especially small assembly lines.
- Production logistics (material flow control, identification of containers and other vessels), intralogistics.
- Parts identification (the transponder is attached to the products or pallets).
- Conveyor systems (e.g. suspended monorail).

Design

Due to their compact design and the integrated antenna, SIMATIC RF200 readers are suitable for mounting in confined spaces, e.g. in small assembly lines or in intralogistics.

The high IP67 degree of protection of the SIMATIC RF200 reader enables it to be used in harsh industrial environments.

Each SIMATIC RF200 reader has a multicolor LED which indicates the function and status of the reader on-site, as well as the presence of a transponder.

The interface to the automation level can be implemented by means of communication modules. For quick and easy cabling, pre-assembled cables with M12 plug-in connectors are available in various lengths.

Transponders compliant with ISO 15693 are used as mobile data carriers.

Transponders suitable for a wide variety of different requirements can be selected from an extensive range: For example, low-cost SmartLabels in rugged credit card format, or screw-fit transponders that can be attached by robots.

The transponders are attached to the object to be identified, e.g. by means of screws, adhesive or pre-assembled spacer.

Function

All of the SIMATIC RF200 readers are suitable for reliable reading and writing tasks in the HF range of 13.56 MHz. The SIMATIC RF200 IO-Link readers are designed for simple identification tasks.

The readers are connected (via an RS422 interface) to the automation level (e.g. SIMATIC S7) by means of communication modules over standard fieldbuses (e.g. PROFIBUS or PROFINET).

User-friendly function blocks are available for the S7 programming.

In the event of an error, the S7 application receives a detailed error message from the communication module via the function block.

In addition, there are the SIMATIC RF240R, RF250R and RF260R readers with an RS232 interface for connection to the PC or to SIMATIC S7-1200.

The SIMATIC RF210R, RF220R, RF240R, RF250R and RF260R readers are available as versions with IO-Link interface.

Integration

A wide range of communication modules, function blocks, as well as high-performance drivers and function libraries permits easy and quick integration into the application.

And best of all: SIMATIC RF200 is part of Totally Integrated Automation (TIA) and can be integrated easily and cost-effectively into the SIMATIC world.

The IO-Link versions of the RF200 readers are integrated into the control level with the help of standardized IO-Link masters.

For more details on the connection possibilities, see Chapter 5 "Communication Modules".

SIMATIC Ident Configuration Guide

Here is a compact configuration tool for setting up RFID systems:

<http://support.automation.siemens.com/WW/view/en/67384964>

Technical specifications

RFID system	SIMATIC RF200
Transmission frequency	13.56 MHz
Maximum range	650 mm
Protocol (air interface)	<ul style="list-style-type: none"> • ISO 15693 • ISO 18000-3
Approvals ¹⁾	<ul style="list-style-type: none"> • EN 300330, 301489, CE • FCC Part 15 • UL/CSA
Memory capacity	max. 992 bytes (EEPROM) / 8 192 bytes (FRAM)
Data transfer rate, reader – transponder (not for IO-Link)	
<ul style="list-style-type: none"> • Read • Write 	Max. 1.5 kbyte/s Max. 1.5 kbyte/s
Transmission time per byte for user data (IO-Link versions)	Typ. 40 ms
Multitag/Bulk capability	With RF290R reader only
Special features	<ul style="list-style-type: none"> • Particularly compact designs • For particularly low-cost RFID solutions • IO-Link for simple identification tasks









¹⁾ All current wireless approvals can be found on the Internet at:
<http://www.siemens.com/rfid-approvals>

RFID systems for the HF range

SIMATIC RF200 readers

Introduction

Overview

Readers	Feature	Page	Readers	Feature	Page
RF210R 	M18 reader with integrated antenna.	2/79	RF250R 	Extremely small compact reader for connecting external antennas (ANT 3, 8, 12, 18 and 30).	2/90
RF210M 	Handheld reader with integrated RF210R reader.	2/82	RF260R 	Compact reader with integrated antenna.	2/95
RF220R 	M30 reader with integrated antenna.	2/83	RF290R 	High-performance reader for connecting external antennas (ANT D5, D6, D10).	2/99
RF240R 	Very small compact reader with integrated antenna..	2/86	RF350M 	Handheld terminal with integrated or external read/write antenna.	2/117

Overview




SIMATIC RF210R is an M18 reader with integrated antenna. Its extremely compact design makes it ideal for use on small assembly lines.

This reader has either

- an RS422 interface with 3964R transmission procedure for connection to RFID communication modules (see Chapter 5),
- or a standardized IO-Link interface for connection to IO-Link master modules from Siemens or third parties.

Thanks to its high degree of protection and rugged design, the SIMATIC RF210R reader enables problem-free use even under the toughest industrial conditions. Connection is by means of either an 8-pin M12 plug-in connector (RS422 version) or a 4-pin M12 plug-in connector (IO-Link version).

The reader is operated with ISO 15693-compatible transponders.



6GT2821-1AC10



6GT2821-1AC32

Design

Minimum distance from reader to reader

SIMATIC RF210R	≥ 100 mm
----------------	----------

Technical specifications

Article number	6GT2821-1AC10	6GT2821-1AC32
Product type designation	RF210R reader	RF210R reader IO-Link
Suitability for operation	ISO 15693 transponders (MDS Dxxx), for connecting to communication modules	ISO 15693 transponders (MDS Dxxx), for connecting to an IO-Link master
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	20 mm; Range is dependent on transponder type: observe http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s
Product feature multitag-capable	No	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s	38.4 kbit/s
Transmission time for user data		
• for write access per byte typical	0.6 ms	40 ms
• for read access per byte typical	0.6 ms	40 ms
Interfaces		
Standard for interfaces for communication	RS422	IO-Link
Type of electrical connection	M12, 8-pin	M12, 4-pin
Mechanical data		
Material	Brass, nickel-plated / PBT	Brass, nickel-plated / PBT
Color	silver/pastel turquoise	silver/pastel turquoise
Tightening torque of the screw for securing the equipment maximum	20 Nm	20 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm

RFID systems for the HF range

SIMATIC RF200 readers

RF210R

Article number	6GT2821-1AC10	6GT2821-1AC32
Product type designation	RF210R reader	RF210R reader IO-Link
Supply voltage, current consumption, power loss		
Supply voltage		
• at DC Rated value	24 V	24 V
• at DC	20.4 ... 28.8 V	20.4 ... 28.8 V
Consumed current at 24 V DC		
• typical	0.05 A	0.05 A
Permitted ambient conditions		
Ambient temperature		
• during operation	-20 ... +70 °C	-20 ... +70 °C
• during storage	-25 ... +80 °C	-25 ... +80 °C
• during transport	-25 ... +80 °C	-25 ... +80 °C
Protection class IP	IP67	IP67
Shock resistance	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²
Design, dimensions and weight		
Height	83 mm	83 mm
Diameter	18 mm	18 mm
Net weight	0.065 kg	0.065 kg
Mounting type	2 x M18 nuts (included in scope of supply)	2 x M18 nuts (included in scope of supply)
Cable length		
• for RS422 interface maximum	1 000 m	
• between master and IO-Link device maximum		20 m
Product properties, functions, components general		
Display version	3-color LED	3-color LED
Product feature silicon-free	Yes	Yes
Standards, specifications, approvals		
Certificate of suitability	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA
MTBF	505 y	505 y
Accessories		
Accessories		IO-Link master, IO-Link connecting cables






RFID systems for the HF range

SIMATIC RF200 readers

RF210R

2

Selection and ordering data

	Article No.
SIMATIC RF210R reader (RS422)	6GT2821-1AC10
SIMATIC RF210R reader (IO-Link)	6GT2821-1AC32
Accessories Note: All connection options can be found in Chapter 5, "Communication Modules".	
IO-Link master SM 1278 For SIMATIC S7-1200, for 4 readers.	6ES7278-4BD32-0XB0
	
IO-Link master 4SI For SIMATIC ET 200S, for 4 readers.	6ES7138-4GA50-0AB0
	
IO-Link master For SIMATIC ET 200eco PN, for 4 readers.	6ES7148-6JA00-0AB0
	
IO-Link master For ET 200SP, for 4 readers.	6ES7137-6BD00-0BA0
	
IO-Link master For ET 200AL, for 4 readers.	6ES7147-5JD00-0BA0
	

Article No.


IO-Link connecting cables



- between IO-Link master and reader, with M12 plug on the IO-Link master, open end, 4-pole, 5 m
- between IO-Link master and reader, with M12 plug on the IO-Link master, open end, 4-pole, 10 m
- between IO-Link master and reader, with M12 plug at both ends, 4-pole, 5 m
- between IO-Link master and reader, with M12 plug at both ends, 4-pole, 10 m

6GT2891-4LH50**6GT2891-4LN10****6GT2891-4MH50****6GT2891-4MN10**
DVD „RFID-Systems Software & Documentation“
6GT2080-2AA20

Dimensional drawings



SIMATIC RF210R reader

More information

All current wireless approvals can be found on the Internet at:

<http://www.siemens.com/rfid-approvals>

RFID systems for the HF range

SIMATIC RF200 readers

RF210M mobile handheld terminal

Overview



The field-proven RF210R M18 reader is integrated into the SIMATIC RF210M mobile handheld reader. It has been designed for manual workplaces and reworking stations for commissioning, as well as for tracking and tracing tasks and tool identification.

The handheld reader has an RS422 interface with 3964R transmission procedure for connection to RFID communication modules. Connection is via an 8-pole M12 plug-in connector (RS422 variant).

The handheld reader is operated with ISO 15693-compatible transponders.

Article number	6GT2823-0AA00
Product type designation	RF210M hand-held reader
Design, dimensions and weight	
Depth	26 mm
Height	140 mm
Width	195 mm
Net weight	0.46 kg
Product properties, functions, components general	
Design of the display	3 color LED
Design of the interface	M12 8-pole with RS422 at spiral cable, which is permanently fixed to the reader
Product functions management, configuration	
Product function of the software	Function blocks for execution of ISO15693 transponders
Type of programming	Function blocks FB 45/55, ident profile
Standards, specifications, approvals	
Certificate of suitability	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA


Selection and ordering data

	Article No.
SIMATIC RF210M handheld reader (RS422)	6GT2823-0AA00
Accessories	
Note: All connection options can be found in Chapter 5, "Communication Modules".	
DVD „RFID-Systems Software & Documentation“	6GT2080-2AA20

Technical specifications

Article number	6GT2823-0AA00
Product type designation	RF210M hand-held reader
Suitability for operation	RF200/ISO 15693 transponders, to connect to communication modules via spiral cable with usable length of 2 m to 3.5 m
Range	0 ... 20 mm
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Protocol with radio transmission	ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	No
Supply voltage, current consumption, power loss	
Type of current supply	24 V via communication module
Type of battery	-
Permitted ambient conditions	
Ambient temperature	
• during operation	-20 ... +50 °C
• during storage	-25 ... +60 °C
Height of fall maximum	1.5 m
Protection class IP	IP54

Dimensional drawings




SIMATIC RF210M handheld reader

More information

All current wireless approvals can be found on the Internet at:
<http://www.siemens.com/rfid-approvals>

Overview




SIMATIC RF220R is an M30 reader with integrated antenna. Its compact design makes it ideal for use in small assembly lines which require a slightly higher range.

This reader has either

- an RS422 interface with 3964R transmission procedure for connection to RFID communication modules (see Chapter 5),
- or a standardized IO-Link interface for connection to IO-Link master modules from Siemens or third parties.

Thanks to its high degree of protection and rugged design, the SIMATIC RF220R reader enables problem-free use even under the toughest industrial conditions. Connection is by means of either an 8-pin M12 plug-in connector (RS422 version) or a 4-pin M12 plug-in connector (IO-Link version).

The reader is operated with ISO 15693-compatible transponders.



6GT2821-2AC10



6GT2821-2AC32

Design

Minimum distance from reader to reader

SIMATIC RF220R	≥ 150 mm
----------------	----------

Technical specifications

	6GT2821-2AC10	6GT2821-2AC32
Article number	RF220R reader	RF220R reader IO-Link
Product type designation	ISO 15693 transponders (MDS Dxxx), for connecting to communication modules	ISO 15693 transponders (MDS Dxxx), for connecting to an IO-Link Master
Suitability for operation		
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	35 mm; Range is dependent on transponder type: observe http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s
Product feature multitag-capable	No	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s	38.4 kbit/s
Transmission time for user data		
• for write access per byte typical	0.6 ms	40 ms
• for read access per byte typical	0.6 ms	40 ms
Interfaces		
Standard for interfaces for communication	RS422	IO-Link
Type of electrical connection	M12, 8-pin	M12, 4-pin
Mechanical data		
Material	Brass, nickel-plated / PBT	Brass, nickel-plated / PBT
Color	silver/pastel turquoise	silver/pastel turquoise
Tightening torque of the screw for securing the equipment maximum	40 Nm	40 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm

RFID systems for the HF range

SIMATIC RF200 readers

RF220R

Article number	6GT2821-2AC10	6GT2821-2AC32
Product type designation	RF220R reader	RF220R reader IO-Link
Supply voltage, current consumption, power loss		
Supply voltage		
• at DC Rated value	24 V	24 V
• at DC	20.4 ... 28.8 V	20.4 ... 28.8 V
Consumed current at DC at 24 V		
• typical	0.05 A	0.05 A
Permitted ambient conditions		
Ambient temperature		
• during operation	-20 ... +70 °C	-20 ... +70 °C
• during storage	-25 ... +80 °C	-25 ... +80 °C
• during transport	-25 ... +80 °C	-25 ... +80 °C
Protection class IP	IP67	IP67
Shock resistance	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²
Design, dimensions and weight		
Height	83 mm	83 mm
Diameter	30 mm	30 mm
Net weight	0.14 kg	0.14 kg
Mounting type	2 x M30 nuts (included in scope of supply)	2 x M30 nuts (included in scope of supply)
Cable length		
• for RS422 interface maximum	1 000 m	
• between master and IO-Link device maximum		20 m
Product properties, functions, components general		
Display version	3-color LED	3-color LED
Product feature silicon-free	Yes	Yes
Standards, specifications, approvals		
Certificate of suitability	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA
MTBF	501 y	501 y
Accessories		
Accessories		IO-Link master, IO-Link connecting cables






RFID systems for the HF range

SIMATIC RF200 readers

RF220R

2

Selection and ordering data

	Article No.
SIMATIC RF220R reader (RS422)	6GT2821-2AC10
SIMATIC RF220R reader (IO-Link)	6GT2821-2AC32
Accessories Note: All connection options can be found in Chapter 5, "Communication Modules".	
IO-Link master SM 1278 For SIMATIC S7-1200, for 4 readers.	6ES7278-4BD32-0XB0
	
IO-Link master 4SI For SIMATIC ET 200S, for 4 readers.	6ES7138-4GA50-0AB0
	
IO-Link master For SIMATIC ET 200eco PN, for 4 readers.	6ES7148-6JA00-0AB0
	
IO-Link master For ET 200SP, for 4 readers.	6ES7137-6BD00-0BA0
	
IO-Link master For ET 200AL, for 4 readers.	6ES7147-5JD00-0BA0
	

Article No.

IO-Link connecting cables




- between IO-Link master and reader, with M12 plug on the IO-Link master, open end, 4-pole, 5 m
- between IO-Link master and reader, with M12 plug on the IO-Link master, open end, 4-pole, 10 m
- between IO-Link master and reader, with M12 plug at both ends, 4-pole, 5 m
- between IO-Link master and reader, with M12 plug at both ends, 4-pole, 10 m

6GT2891-4LH50**6GT2891-4LN10****6GT2891-4MH50****6GT2891-4MN10**

DVD „RFID-Systems Software & Documentation“

6GT2080-2AA20

Dimensional drawings



SIMATIC RF220R reader

More information

All current wireless approvals can be found on the Internet at:
<http://www.siemens.com/rfid-approvals>

RFID systems for the HF range

SIMATIC RF200 readers

RF240R

Overview




SIMATIC RF240R is a reader with an integrated antenna. Its extra compact design makes it ideal for use in small assembly lines.

This reader has either

- an RS422 interface with 3964R transmission procedure for connection to RFID communication modules (see Chapter 5),
- or an RS232 interface with ASCII protocol for connection to S7-1200, PC-based systems or third-party controllers,
- or a standardized IO-Link interface for connection to IO-Link Master modules from Siemens or third parties.

Thanks to its high degree of protection and rugged design, the SIMATIC RF240R reader enables problem-free use even under the toughest industrial conditions. Connection is made either with an 8-pin M12 plug-in connector (RS422/RS232 version) or a 4-pin M12 plug-in connector (IO-Link version).

The reader is operated with ISO 15693-compatible transponders.



CM



ISO

6GT2821-4AC10



RS232



ISO

6GT2821-4AC40



IO-Link



ISO

6GT2821-4AC32

Design

Minimum distance from reader to reader	
SIMATIC RF240R	≥ 120 mm

Technical specifications

Article number	6GT2821-4AC10	6GT2821-4AC40	6GT2821-4AC32
Product type designation	RF240R reader	RF240R reader ASCII	RF240R reader IO-Link
Suitability for operation	ISO 15693 transponders (MDS Dxxx), for connecting to communication modules	ISO 15693 transponders (MDS Dxxx), for connecting to PC- and control systems	ISO 15693 transponders (MDS Dxxx), for connecting to an IO-Link Master
Wireless frequencies			
Operating frequency Rated value	13.56 MHz	13.56 MHz	13.56 MHz
Electrical data			
Range maximum	65 mm; Range is dependent on transponder type: observe http://support.automation.siemens.com/WW/view/en/67384964	65 mm; Range is dependent on transponder type: observe	65 mm; Range is dependent on transponder type: observe
Protocol with radio transmission	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s	26.5 kbit/s
Product feature multitag-capable	No	No	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s	115.2 kbit/s	38.4 kbit/s
Transmission time for user data			
• for write access per byte typical	0.6 ms	1.2 ms	40 ms
• for read access per byte typical	0.6 ms	1.2 ms	40 ms
Interfaces			
Standard for interfaces for communication	RS422	RS232	IO-Link
Type of electrical connection	M12, 8-pin	M12, 8-pin	M12, 4-pin

RFID systems for the HF range

SIMATIC RF200 readers

RF240R

Article number	6GT2821-4AC10	6GT2821-4AC40	6GT2821-4AC32
Product type designation	RF240R reader	RF240R reader ASCII	RF240R reader IO-Link
Mechanical data			
Material	PA6.6	PA6.6	PA6.6
Color	anthracite	anthracite	anthracite
Tightening torque of the screw for securing the equipment maximum	1.5 Nm	1.5 Nm	1.5 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm	0 mm
Supply voltage, current consumption, power loss			
Supply voltage			
• at DC Rated value	24 V	24 V	24 V
• at DC	20.4 ... 28.8 V	20.4 ... 28.8 V	20.4 ... 28.8 V
Consumed current at DC at 24 V			
• typical	0.05 A	0.05 A	0.05 A
Permitted ambient conditions			
Ambient temperature			
• during operation	-20 ... +70 °C	-20 ... +70 °C	-20 ... +70 °C
• during storage	-25 ... +80 °C	-25 ... +80 °C	-25 ... +80 °C
• during transport	-25 ... +80 °C	-25 ... +80 °C	-25 ... +80 °C
Protection class IP	IP67	IP67	IP67
Shock resistance	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²	200 m/s ²
Design, dimensions and weight			
Width	50 mm	50 mm	50 mm
Height	30 mm	30 mm	30 mm
Depth	50 mm	50 mm	50 mm
Net weight	0.06 kg	0.06 kg	0.06 kg
Mounting type	2 x M5 screws	2 x M5 screws	2 x M5 screws
Cable length			
• with RS232 interface maximum		30 m	
• for RS422 interface maximum	1 000 m		
• between master and IO-Link device maximum			20 m
Product properties, functions, components general			
Display version	3-color LED	3-color LED	3-color LED
Product feature silicon-free	Yes	Yes	Yes
Standards, specifications, approvals			
Certificate of suitability	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA
MTBF	430 y	430 y	430 y
Accessories			
Accessories	Connecting cables	Connecting cables	IO-Link master, IO-Link connecting cables










2


RFID systems for the HF range

SIMATIC RF200 readers

RF240R

Selection and ordering data

	Article No.		Article No.
SIMATIC RF240R reader (RS422)	6GT2821-4AC10	IO-Link master For ET 200AL, for 4 readers.	6ES7147-5JD00-0BA0
SIMATIC RF240R reader (RS232 - ASCII)	6GT2821-4AC40		
SIMATIC RF240R reader (IO-Link)	6GT2821-4AC32	RS232 connecting cable Between reader and PC (RS232), 5 m long, material: PUR, CMG approval. <ul style="list-style-type: none">• 24 V connection with M12 plug	6GT2891-4KH50
Accessories Note: All connection options can be found in Chapter 5, "Communication Modules".			
IO-Link master SM 1278 For SIMATIC S7-1200, for 4 readers.	6ES7278-4BD32-0XB0	<ul style="list-style-type: none">• 24 V connection with open ends	6GT2891-4KH50-0AX0
			
IO-Link master 4SI For SIMATIC ET 200S, for 4 readers.	6ES7138-4GA50-0AB0	IO-Link connecting cables	
			
IO-Link master For SIMATIC ET 200eco PN, for 4 readers.	6ES7148-6JA00-0AB0		
		<ul style="list-style-type: none">• between IO-Link Master and reader, with M12 connector on the IO-Link Master, open end, 4-pin, 5 m	6GT2891-4LH50
IO-Link master For ET 200SP, for 4 readers.	6ES7137-6BD00-0BA0	<ul style="list-style-type: none">• between IO-Link Master and reader, with M12 connector on the IO-Link Master, open end, 4-pin, 10 m	6GT2891-4LN10
		<ul style="list-style-type: none">• between IO-Link Master and reader, with M12 connector at both ends, 4-pin, 5 m	6GT2891-4MH50
		<ul style="list-style-type: none">• between IO-Link Master and reader, with M12 connector at both ends, 4-pin, 10 m	6GT2891-4MN10
		DVD „RFID-Systems Software & Documentation“	6GT2080-2AA20

Dimensional drawings

SIMATIC RF240R reader

More information

All current wireless approvals can be found on the Internet at:


<http://www.siemens.com/rfid-approvals>

RFID systems for the HF range

SIMATIC RF250R readers

RF250R

Overview



6GT2821-5AC10

6GT2821-5AC40

6GT2821-5AC32

SIMATIC RF250R is a reader for operation with external antennas. Thanks to the different antenna designs (ANT 3, ANT 3S, ANT 8, ANT 12, ANT 18 and ANT 30), the potential applications in the areas of tool identification and small assembly lines are extremely varied.

This reader has either

- an RS422 interface with 3964R transmission procedure for connection to RFID communication modules (see Chapter 5),
- or an RS232 interface with ASCII protocol for connection to S7-1200, PC-based systems or third-party controllers,
- or a standardized IO-Link interface for connection to IO-Link Master modules from Siemens or third parties.

Thanks to its high degree of protection and rugged design, the SIMATIC RF250R reader enables problem-free use even under the toughest industrial conditions.

Connection is made either with an 8-pin M12 plug-in connector (RS422/RS232 version) or a 4-pin M12 plug-in connector (IO-Link version).

The reader is operated with ISO 15693-compatible transponders.

Connectable antennas

One of each of the following antennas can be operated on a SIMATIC RF250R reader:

- ANT 3, due to its slimline, compact design, this antenna can still be precisely positioned even in cramped conditions. The dimensions are L x W x H (mm): 50 x 28 x 10.
- ANT 3S, same as ANT 3, except suitable exclusively for processing of MDS D117, MDS D127, MDS D421 and MDS D521 transponders. The dimensions are L x W x H (mm): 50 x 28 x 10.
- ANT 8, this cylindrical antenna is mainly intended for the field of tool identification. The extremely small design of the antenna enables extremely accurate positioning, dimensions Ø x L (mm) M8 x 38.
- ANT 12, universal round antenna in M12 design for assembly lines with extremely small workpiece holders, dimensions Ø x L (mm) M12 x 40.
- ANT 18, universal round antenna in M18 design for assembly lines with small workpiece holders, dimensions Ø x L (mm) M18 x 55.
- ANT 30, universal round antenna for assembly lines with small workpiece holders, dimensions Ø x L (mm) M30 x 58.

Design

Connectable antennas	ANT 3	ANT 3S	ANT 8	ANT 12	ANT 18	ANT 30
See page	2/132	2/133	2/134	2/136	2/137	2/138
Inductive interface to the transponder	13.56 MHz					
Range, max.	50 mm	17 mm	4 mm	17 mm	37 mm	60 mm

Minimum distance between antennas

RF250R with antenna	ANT 3	ANT 3S	ANT 8	ANT 12	ANT 18	ANT 30
Minimum distance (mm) from antenna to antenna (D)						
• ANT 3	60	-	-	-	-	-
• ANT 3S	-	80	-	-	-	-
• ANT 8	-	-	60	-	-	-
• ANT 12	-	-	-	80	-	-
• ANT 18	-	-	-	-	125	-
• ANT 30	-	-	-	-	-	200

RFID systems for the HF range

SIMATIC RF200 readers

RF250R

Technical specifications

Article number	6GT2821-5AC10	6GT2821-5AC40	6GT2821-5AC32
Product type designation	RF250R reader	RF250R reader ASCII	RF250R reader IO-Link
Suitability for operation	ISO 15693 transponders (MDS Dxxx), for connecting to communication modules	ISO 15693 transponders (MDS Dxxx), for connecting to PC- and control systems	ISO 15693 transponders (MDS Dxxx), for connecting to an IO-Link Master
Wireless frequencies			
Operating frequency Rated value	13.56 MHz	13.56 MHz	13.56 MHz
Electrical data			
Range maximum	60 mm; Range is dependent on transponder type: observe http://support.automation.siemens.com/WW/view/en/67384964	60 mm; Range is dependent on transponder type: observe	60 mm; Range is dependent on transponder type: observe
Protocol with radio transmission	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s	26.5 kbit/s
Product feature multitag-capable	No	No	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s	115.2 kbit/s	38.4 kbit/s
Transmission time for user data			
• for write access per byte typical	0.6 ms	1.2 ms	40 ms
• for read access per byte typical	0.6 ms	1.2 ms	40 ms
Interfaces			
Number of external antennas	1	1	1
Standard for interfaces for communication	RS422	RS232	IO-Link
Type of electrical connection			
• for external antenna(s)	M8, 4-pin	M8, 4-pin	M8, 4-pin
• for communications interface	M12, 8-pin	M12, 8-pin	M12, 4-pin
Mechanical data			
Material	PA6.6	PA6.6	PA6.6
Color	anthracite	anthracite	anthracite
Tightening torque of the screw for securing the equipment maximum	1.5 Nm	1.5 Nm	1.5 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm	0 mm
Supply voltage, current consumption, power loss			
Supply voltage			
• at DC Rated value	24 V	24 V	24 V
• at DC	20.4 ... 28.8 V	20.4 ... 28.8 V	20.4 ... 28.8 V
Consumed current at DC at 24 V			
• typical	0.05 A	0.05 A	0.05 A
Permitted ambient conditions			
Ambient temperature			
• during operation	-20 ... +70 °C	-20 ... +70 °C	-20 ... +70 °C
• during storage	-25 ... +80 °C	-25 ... +80 °C	-25 ... +80 °C
• during transport	-25 ... +80 °C	-25 ... +80 °C	-25 ... +80 °C
Protection class IP	IP65	IP65	IP65
Shock resistance	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²	200 m/s ²

2

RFID systems for the HF range






SIMATIC RF200 readers

RF250R

Article number	6GT2821-5AC10	6GT2821-5AC40	6GT2821-5AC32
Product type designation	RF250R reader	RF250R reader ASCII	RF250R reader IO-Link
Design, dimensions and weight			
Width	50 mm	50 mm	50 mm
Height	30 mm	30 mm	30 mm
Depth	50 mm	50 mm	50 mm
Net weight	0.06 kg	0.06 kg	0.06 kg
Mounting type	2 x M5 screws	2 x M5 screws	2 x M5 screws
Cable length			
• with RS232 interface maximum		30 m	
• for RS422 interface maximum	1 000 m		
• between master and IO-Link device maximum			20 m
Product properties, functions, components general			
Display version	3-color LED	3-color LED	3-color LED
Product feature silicon-free	Yes	Yes	Yes
Standards, specifications, approvals			
Certificate of suitability	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA
MTBF	430 y	430 y	430 y
Accessories			
Accessories	Various antennas are available, connecting cables	Various antennas are available, connecting cables	Various antennas are available, IO-Link master, IO-Link connecting cables

Selection and ordering data

	Article No.
SIMATIC RF250R reader (RS422 - 3964R) Without antenna, for connecting external antennas.	6GT2821-5AC10
SIMATIC RF250R reader (RS232 - ASCII) Without antenna, for connecting external antennas.	6GT2821-5AC40
SIMATIC RF250R reader (IO-Link) Without antenna, for connecting external antennas.	6GT2821-5AC32
Accessories Note: All connection options can be found in Chapter 5, "Communication Modules".	
Antennas	
External antenna ANT 3 For RF250R reader, with antenna connecting cable (3 m, double ended (plug M8 straight / M8 angled)). See page 2/132.	6GT2398-1CD40-0AX0
External antenna ANT 3S For RF350R reader, with antenna connecting cable (3 m, double ended (plug M8 straight / M8 angled)). See page 2/133.	6GT2398-1CD60-0AX0
External antenna ANT 8 For RF250R reader, with antenna connecting cable (3 m), double ended (plug M8 straight / M8 angled). See page 2/134.	6GT2398-1CF10
External antenna ANT 12 For RF250R readers, with antenna connecting cable. See page 2/136.	6GT2398-1CC00
External antenna ANT 18 For RF250R readers, with antenna connecting cable. See page 2/137.	6GT2398-1CA00
External antenna ANT 30 For RF250R readers, with antenna connecting cable. See page 2/138.	6GT2398-1CD00

	Article No.
IO-Link master IO-Link master SM 1278 For SIMATIC S7-1200, for 4 readers.	6ES7278-4BD32-0XB0
	
IO-Link master 4SI For SIMATIC ET 200S, for 4 readers.	6ES7138-4GA50-0AB0
	
IO-Link master For SIMATIC ET 200eco PN, for 4 readers.	6ES7148-6JA00-0AB0
	
IO-Link master For ET 200SP, for 4 readers.	6ES7137-6BD00-0BA0
	
IO-Link master For ET 200AL, for 4 readers.	6ES7147-5JD00-0BA0
	

RFID systems for the HF range

SIMATIC RF200 readers

RF250R

Article No.

Connecting cables

RS232 connecting cable

Between reader and PC (RS232),
5 m, material: PUR, CMG approval.
CMG-Zulassung.

- 24 V connection with M12 plug



6GT2891-4KH50

- 24 V connection with open ends



6GT2891-4KH50-0AX0

IO-Link connecting cables



- between IO-Link Master and reader, with M12 connector on the IO-Link Master, open end, 4-pin, 5 m

6GT2891-4LH50

- between IO-Link Master and reader, with M12 connector on the IO-Link Master, open end, 4-pin, 10 m

6GT2891-4LN10

- between IO-Link Master and reader, with M12 connector at both ends, 4-pin, 5 m

6GT2891-4MH50


- between IO-Link Master and reader, with M12 connector at both ends, 4-pin, 10 m

6GT2891-4MN10

DVD "RFID-Systems Software & Documentation"

6GT2080-2AA20

Dimensional drawings



SIMATIC RF250R reader

More information

All current wireless approvals can be found on the Internet at:

<http://www.siemens.com/rfid-approvals>

Overview



SIMATIC RF260R is a reader with an integrated antenna. Its compact design makes it ideal for use in assembly lines.

This reader has either:

- an RS422 interface with 3964R transmission procedure for connection to the RFID communication modules (see Chapter 5),
- an RS232 interface with ASCII protocol for connection to S7-1200, PC-based systems or third-party controllers,
- or a standardized IO-Link interface for connection to IO-Link master modules from Siemens or third parties.

Thanks to its high degree of protection and rugged design, the SIMATIC RF260R reader enables problem-free use even under the toughest industrial conditions.

Connection is by means of either an 8-pin M12 plug-in connector (RS422/RS232 version) or a 4-pin M12 plug-in connector (IO-Link version).

The reader is operated with ISO 15693-compatible transponders.



6GT2821-6AC10

6GT2821-6AC40

6GT2821-6AC32

Design

Minimum distance from reader to reader	
SIMATIC RF260R	≥ 150 mm

Technical specifications

	6GT2821-6AC10	6GT2821-6AC40	6GT2821-6AC32
Article number	RF260R reader	RF260R ASCII reader	RF260R IO-Link reader
Product type designation	ISO 15693 transponders (MDS Dxxx), for connecting to communication modules	ISO 15693 transponders (MDS Dxxx), for connecting to PC- and control systems	ISO 15693 transponders (MDS Dxxx), for connecting to an IO-Link Master
Suitability for operation			
Wireless frequencies			
Operating frequency Rated value	13.56 MHz	13.56 MHz	13.56 MHz
Electrical data			
Range maximum	135 mm; Range is dependent on transponder type: observe http://support.automation.siemens.com/WW/view/en/67384964		
Protocol with radio transmission	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s	26.5 kbit/s
Product feature multitag-capable	No	No	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s	115.2 kbit/s	38.4 kbit/s
Transmission time for user data			
• for write access per byte typical	0.6 ms	1.2 ms	40 ms
• for read access per byte typical	0.6 ms	1.2 ms	40 ms
Interfaces			
Standard for interfaces for communication	RS422	RS232	IO-Link
Type of electrical connection	M12, 8-pin	M12, 8-pin	M12, 4-pin






RFID systems for the HF range




SIMATIC RF200 readers

RF260R

Article number	6GT2821-6AC10	6GT2821-6AC40	6GT2821-6AC32
Product type designation	RF260R reader	RF260R ASCII reader	RF260R IO-Link reader
Mechanical data			
Material	PA6.6	PA6.6	PA6.6
Color	anthracite	anthracite	anthracite
Tightening torque of the screw for securing the equipment maximum	1.5 Nm	1.5 Nm	1.5 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm	0 mm
Supply voltage, current consumption, power loss			
Supply voltage			
• at DC Rated value	24 V	24 V	24 V
• at DC	20.4 ... 28.8 V	20.4 ... 28.8 V	20.4 ... 28.8 V
Consumed current at DC at 24 V			
• typical	0.05 A	0.05 A	0.05 A
Permitted ambient conditions			
Ambient temperature			
• during operation	-20 ... +70 °C	-20 ... +70 °C	-20 ... +70 °C
• during storage	-25 ... +80 °C	-25 ... +80 °C	-25 ... +80 °C
• during transport	-25 ... +80 °C	-25 ... +80 °C	-25 ... +80 °C
Protection class IP	IP67	IP67	IP67
Shock resistance	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²	200 m/s ²
Design, dimensions and weight			
Width	75 mm	75 mm	75 mm
Height	41 mm	41 mm	41 mm
Depth	75 mm	75 mm	75 mm
Net weight	0.2 kg	0.2 kg	0.2 kg
Mounting type	2 x M5 screws	2 x M5 screws	2 x M5 screws
Cable length			
• with RS232 interface maximum		30 m	
• for RS422 interface maximum	1 000 m		
• between master and IO-Link device maximum			20 m
Product properties, functions, components general			
Display version	3-color LED	3-color LED	3-color LED
Product feature silicon-free	Yes	Yes	Yes
Standards, specifications, approvals			
Certificate of suitability	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA
MTBF	480 y	430 y	480 y
Accessories			
Accessories	Connecting cables	Connecting cables	IO-Link master, IO-Link connecting cables

Selection and ordering data

	Article No.
SIMATIC RF260R reader (RS422)	6GT2821-6AC10
SIMATIC RF260R reader (RS232 - ASCII)	6GT2821-6AC40
SIMATIC RF260R reader (IO-Link)	6GT2821-6AC32
Accessories Note: All connection options can be found in section 5, "Communication Modules".	
IO-Link master	
IO-Link master SM 1278 For SIMATIC S7-1200, for 4 readers.	6ES7278-4BD32-0XB0
	
IO-Link master 4SI For SIMATIC ET 200S, for 4 readers	6ES7138-4GA50-0AB0
	
IO-Link master For SIMATIC ET 200eco PN, for 4 readers	6ES7148-6JA00-0AB0
	
IO-Link master For ET 200SP, for 4 readers.	6ES7137-6BD00-0BA0
	
IO-Link master For ET 200AL, for 4 readers.	6ES7147-5JD00-0BA0
	


	Article No.
Connecting cables	
RS232 connecting cable	
Between reader and PC (RS232), 5 m, material: PUR, CMG approval. CMG-Zulassung.	
<ul style="list-style-type: none"> 24 V connection with M12 plug 	6GT2891-4KH50
	
<ul style="list-style-type: none"> 24 V connection with open ends 	6GT2891-4KH50-0AX0
	
IO-Link connecting cables	
	
	6GT2891-4LH50
	
<ul style="list-style-type: none"> between IO-Link Master and reader, with M12 connector on the IO-Link Master, open end, 4-pin, 5 m 	6GT2891-4LN10
<ul style="list-style-type: none"> between IO-Link Master and reader, with M12 connector on the IO-Link Master, open end, 4-pin, 10 m 	6GT2891-4MH50
<ul style="list-style-type: none"> between IO-Link Master and reader, with M12 connector at both ends, 4-pin, 5 m 	6GT2891-4MN10
DVD „RFID-Systems Software & Documentation“	6GT2080-2AA20

RFID systems for the HF range

SIMATIC RF200 readers

RF260R

Dimensional drawings



SIMATIC RF260R reader

More information

All current wireless approvals can be found on the Internet at:

<http://www.siemens.com/rfid-approvals>

Overview



The SIMATIC RF290R reader is a compact long-range reader for the upper performance range and ranges of up to 60 cm. Intended for operation with external antennas ANT D1, ANT D5, ANT D6 and ANT D10. The application range for RF290R lies in the area of production control and intralogistics through to gate applications in which longer ranges for HF-RFID are required.

The reader is equipped with a combined RS422/RS232 interface, which is switched over when the corresponding connecting cable is used.

In RS422 mode, the reader can be connected to SIMATIC S7, PROFIBUS, PROFINET or Ethernet TCP/IP via the communication modules (see Chapter 5). Please note that due to the current consumption of the reader on the ASM 456 and RF160C, only one RF290R can be connected.

In the RS232 mode, the reader is suitable for integration into PC-based control systems. Trigger and alarm signals can be connected via digital inputs/outputs.

Furthermore, bulk detection of several hundred transponders is possible.

The antenna switch or the multiplexer enables several individual antennas or portal solutions to be implemented with only one RF290R. The RF260X antenna multiplexer supports the connection of up to 6 antennas to one reader and operates in quasi-parallel mode.

Connectable antennas

One of each of the following antennas can be operated on a SIMATIC RF290R:

- ANT D1
Dimensions L x W x H (mm): 75 x 75 x 20.
- ANT D5
Dimensions L x W x H (mm): 380 x 380 x 110.
- ANT D6
Dimensions L x W x H (mm): 580 x 480 x 110.
- ANT D10
Dimensions L x W x H (mm): 1150 x 365 x 115.

ANT D1

The ANT D1 is a universal antenna for the production and logistics areas that can also be used in dynamic applications. The high degree of protection (IP67) means the antenna can also be used under harsh industrial conditions.

ANT D5

Universal antenna for warehouse, logistics and distribution applications. The high degree of protection (IP65) enables the antenna to be used under harsh industrial conditions.

ANT D6

Antenna in the upper performance range, designed especially for warehouse, logistics and distribution applications. It can be used wherever high speeds are required together with a large write/read distance.

ANT D10

The ANT D10 is suitable for use in warehouses, logistics and distribution. An antenna with this geometry is required in the clothing industry and laundries in particular.

Design

Connectable antennas	ANT D1	ANT D5	ANT D6	ANT D10
See page	2/139	2/141	2/143	2/145
Inductive interface to the transponder	13.56 MHz			
Range	250 mm	480 mm	650 mm	480 mm

SIMATIC RF290R with antenna	ANT D1	ANT D5	ANT D6	ANT D10
Minimum distance (m) from antenna to antenna (D)				
• ANT D1	0,5	-	-	-
• ANT D5	-	2	-	-
• ANT D6	-	-	2	-
• ANT D10	-	-	-	2

RFID systems for the HF range

SIMATIC RF200 readers

RF290R

Technical specifications

Article number	6GT2821-0AC12
Product type designation	RF290R reader
Suitability for operation	ISO 15693 transponders (MDS Dxxx), for connecting to communication modules and PC systems
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	650 mm; Range adjustable in reader via transmission power, range is dependent on transponder type: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s
Transmission time for user data	
• for write access per byte typical	0.6 ms
• for read access per byte typical	0.6 ms
Interfaces	
Number of external antennas	1
Standard for interfaces for communication	RS422/RS232
Type of electrical connection	M12, 8-pin
• for external antenna(s)	TNC
• for supply voltage	M12, 8-pin
• for communications interface	M12, 8-pin
• at the digital inputs/outputs	M12, 4-pin, female connector
Number of digital inputs	1
Number of digital outputs	1
Mechanical data	
Material	aluminum
Color	silver/anthracite
Tightening torque of the screw for securing the equipment maximum	1.5 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm
Supply voltage, current consumption, power loss	
Supply voltage	
• at DC Rated value	24 V
• at DC	21.6 ... 26.4 V
Consumed current at DC at 24 V	
• typical	0.4 A
• maximum	0.5 A
Permitted ambient conditions	
Ambient temperature	
• during operation	-20 ... +55 °C
• during storage	-25 ... +85 °C
• during transport	-25 ... +85 °C
Protection class IP	IP65
Shock resistance	EN 60721-3-7 Class 7 M2
Shock acceleration	300 m/s ²
Vibrational acceleration	20 m/s ²





Article number	6GT2821-0AC12
Product type designation	RF290R reader
Design, dimensions and weight	
Width	200 mm
Height	80 mm
Depth	140 mm
Net weight	1.8 kg
Mounting type	4 x M6 screws
Cable length	
• of antenna cable minimum	3.3 m
• of antenna cable maximum	25 m
• with RS232 interface maximum	30 m
• for RS422 interface maximum	1 000 m
Product properties, functions, components general	
Display version	4 LEDs
Standards, specifications, approvals	
Certificate of suitability	CE, FCC, IC (Canada)
MTBF	18 y
Accessories	
Accessories	Various antennas are available, antenna combiners, antenna multiplexer, mounting set for top-hat rail mounting

RFID systems for the HF range

SIMATIC RF200 readers

RF290R

Selection and ordering data

	Article No.
SIMATIC RF290R reader Without antenna	6GT2821-0AC12
Antennas for SIMATIC RF290R reader Including antenna cable	
• Antenna ANT D1	6GT2698-5AC00
• Antenna ANT D5	6GT2698-5AA10
• Antenna ANT D6	6GT2698-5AB00
• Antenna ANT D10 Cover included in scope of delivery.	6GT2698-5AF00
Accessories Note: All connection options can be found in Chapter 5, "Communication Modules".	
Antenna switch For connecting several antennas (ANT D5, ANT D6 or ANT D10) to one reader.	6GT2690-0AC00
	
SIMATIC RF260X antenna multiplexer Antenna multiplexer for RF290R reader when connected via RS232; 6 x antenna outputs (for ANT D5, ANT D6 and ANT D10); IP65; 240 mm x 150 mm x 70 mm; including antenna connecting cable, cable length 0.4 m.	6GT2894-0EA00
	
Covering hood for ANT D6 Serves as protection against contact.	6GT2690-0AD00
RS232 connecting cable Between reader and PC (RS232), 5 m long, material: PUR, CMG approval.	
• 24 V connection with M12 plug	6GT2891-4KH50
	
• 24 V connection with open ends	6GT2891-4KH50-0AX0
	

Article No.

Accessories for antenna switch and antenna multiplexer

Antenna connecting cable

Between antenna and reader or antenna switch/multiplexer, PVC material.

- Length 3.3 m
- Length 10 m

6GT2691-0CH33**6GT2691-0CN10**

Extension cable

For 6GT2691-0CH33, PVC material. Length 7.2 m.

6GT2691-0DH72


Standard rail mounting

6GK5798-8ML00-0AB3

DVD „RFID Systems Software & Documentation“

6GT2080-2AA20

Dimensional drawings



SIMATIC RF290R reader

More information

All current wireless approvals can be found on the Internet at:

<http://www.siemens.com/rfid-approvals>

RFID systems for the HF range

SIMATIC RF300

Introduction

Overview



The RFID system SIMATIC RF300 is particularly suitable for use in industrial production in the areas of production control, assembly lines and conveyors.

SIMATIC RF300 is used to implement identification tasks with medium to high performance in the HF range (13.56 MHz).

Depending on the performance of the identification system, two versions of the system are available:

- Medium performance: System configuration with SIMATIC RF300 readers in ISO 15693 mode and low-cost MOBY D transponders.
- High performance: System configuration with SIMATIC RF300 readers in RF300 mode and SIMATIC RF300 transponders.

The SIMATIC RF300 identification system offers the following features:

- 13.56 MHz operating frequency
- For operating with ISO 15693 mode or RF300 mode
- Passive (without battery), maintenance-free transponder (MDS Dxxx and RF3xxT) with memory up to 64 KB
- Rugged, compact components with IP67 / IP68 degree of protection
- Very high immunity to noise
- Extensive diagnostic functions
- Extremely fast data transmission
- Easy integration into SIMATIC, PROFIBUS, PROFINET and TCP/IP.

Benefits

get Designed for Industry

- Rugged, compact components with high degree of protection (up to IP68).
- Data communication that is highly resistant to interference with a high degree of data security.
- Maintenance-free data carriers with up to 64 KB.
- Extremely high-speed data transmission between reader and transponder (up to 7.8 KB/s).
- Flexible and economic solutions thanks to the complete and scalable portfolio for the field of industrial identification.
- Simplified engineering, commissioning, diagnostics and maintenance through seamless integration into Totally Integrated Automation (TIA):
 - Integrated bus connection to an automation system, such as SIMATIC, SIMOTION or SINUMERIK via communication modules with PROFIBUS and PROFINET.
 - Simple S7 software integration via ready-to-use function blocks.
 - Extensive status and diagnostic functions.
- High investment security thanks to:
 - Open standard in accordance with ISO standard 15693.
 - Software compatibility between the RFID systems of Siemens.
 - Standardized communication interfaces.
- Openness through connection possibilities to various bus systems from different manufacturers and PC environments via communication modules.
- Worldwide service and support.

Application

The RFID system SIMATIC RF300 is used primarily for contact-free identification of containers, pallets and workpiece holders in a closed production cycle. This means that the data carriers (transponders, tags) remain in the production chain and are not shipped out with the products. Thanks to the compact enclosure dimensions of the transponders as well as of the read/write devices, SIMATIC RF300 is particularly suitable for (small) assembly lines where space is at a premium.

The main application areas of SIMATIC RF300 are:

- Assembly and handling systems, assembly lines (identification of workpiece carriers)
- Production logistics (material flow control, identification of containers and other vessels)
- Parts identification (e.g. transponder is attached to product or pallet)
- Conveyor systems (e.g. overhead monorail conveyors)

Design

The high IP68 degree of protection of the SIMATIC RF300 reader enables it to be used in harsh industrial environments.

The SIMATIC RF310R, RF340R and RF380R devices have an integrated antenna. The SIMATIC RF350R reader is operated with an external antenna.

Each SIMATIC RF300 reader has a multicolor LED which locally indicates the function and status of the reader as well as of the transponder.

The interface to the automation level can be implemented by means of communication modules. For quick and easy cabling, pre-assembled cables with M12 plug-in connectors are available in various lengths.

All readers can be operated either according to the RFID standard ISO 15693, or in high-performance RF300 mode.

Depending on the mode of the reader, a comprehensive range of transponders is available for a wide variety of requirements.

For use in accordance with the ISO 15693 standard there are various versions available, e.g. low-cost SmartLabels for simple identification tasks, rugged credit card formats or screw-fit transponders that can be automatically attached by robots.

Additional transponders are available for selection for the high-performance RF300 mode, e.g. particularly heat-resistant transponders for temperatures up to +220 °C, or particularly compact rectangular designs for use on small workpiece holders.

The transponders are attached to the object to be identified, e.g. by means of screws, adhesive or pre-assembled spacer.

Function

All of the SIMATIC RF300 readers are suitable for reliable reading and writing tasks in the HF range of 13.56 MHz. In the ISO 15693 operating mode, identification tasks in the medium-performance range are possible.

The RF300 mode permits high-performance operation with a high-speed data transmission of up to 7.8 kbytes/s and is therefore one of the fastest RFID systems in the HF range.

Connection of readers to the automation level (e.g. SIMATIC S7) via standard fieldbuses (e.g. PROFIBUS or PROFINET) is by means of communication modules to which the readers can be connected via an RS422 interface.

User-friendly function blocks are available for the S7 programming.

In the event of an error, the S7 application receives a detailed error message from the communication module via the function block.

In addition, there is the option of the SIMATIC RF380R readers with an RS232 interface for the connection to the PC or to SIMATIC S7-1200.

The SIMATIC RF380R, RF382R and RF310R readers are available as scan mode variants (read only) for identification tasks without special command control. In these variants, the reader reads each detected transponder (UID or user data) automatically and outputs this data via the serial interface to be received by a PC, for example.

Extended diagnostics functions in RF300 mode, such as the field strength measured variable or the signature error counter, enable the HF field or the quality of the air interface to be measured.

Integration

A wide range of communication modules, function blocks, as well as high-performance drivers and function libraries permits easy and quick integration into the application.

And best of all: SIMATIC RF300 is part of Totally Integrated Automation (TIA) and can be integrated easily and cost-effectively into the SIMATIC world.

For more details on the connection possibilities, see Chapter 5 "Communication Modules".

SIMATIC Ident Configuration Guide

Here is a compact configuration tool for setting up RFID systems:

<http://support.automation.siemens.com/WW/view/en/67384964>

Technical specifications

RFID system	SIMATIC RF300
Transmission frequency	13.56 MHz
Maximum range	210 mm
Protocol (air interface)	<ul style="list-style-type: none"> • ISO 15693 • ISO 18000-3 • RF300 (proprietary)
Approvals ¹⁾	<ul style="list-style-type: none"> • EN 300330, 301489, CE • FCC Part 15 • UL/CSA • ATEX
Memory capacity	Max. 64 KB
Data transmission rate reader – transponder	
• Read	Max. 7.8 kbyte/s
• Write	Max. 7.8 kbyte/s
Multitag/Bulk capability	No
Special features	<ul style="list-style-type: none"> • High data transfer rate • Extended diagnostic possibilities • High memory capacity







¹⁾ All current wireless approvals can be found on the Internet at:
<http://www.siemens.com/rfid-approvals>

RFID systems for the HF range


SIMATIC RF300 readers

Introduction

Overview

Readers	Features	Page	Readers	Features	Page
RF310R 	Ideal for use on small assembly lines. The reader has an integrated antenna.	2/105	RF380R 	Ideal for use in assembly lines in which long ranges are required. The reader has an integrated antenna.	2/112
RF340R 	Ideal for use on assembly lines. Reader for connecting external antennas	2/107	RF382R 	Ideal for use in assembly lines in which transponders must be read from the side. Reader with integrated special antenna. Scan mode (read only).	2/115
RF350R 	Ideal for use on assembly lines. Reader for connecting external antennas (ANT 1, 3, 3S, 12, 18, 30).	2/109	RF350M 	Mobile handheld terminal with integrated or external read/write antenna.	2/117

Overview



6GT2801-1AB10

Due to its small, compact design, the SIMATIC RF310R reader can be used to considerable advantage in small assembly lines.

This reader is available with an RS422 interface for the RFID communication modules (see Chapter 5).

The SIMATIC RF310R is also available as a scan mode variant (automatic read mode, without command control). This automatic read-only mode does not require a special command control, but supplies the autonomously read transponder data directly to the connected host system.



6GT2801-1AB20-0AX1

Due to the high degree of protection and the use of high-quality materials, the SIMATIC RF310R ensures problem-free operation even under the harshest industrial conditions. It is connected via an 8-pole M12 plug-in connector.

The reader can process the high-speed RF300 transponders and the ISO-15693-compatible transponders (see RFID systems field data table on page 1/10).

Design

Minimum distance from reader to reader

SIMATIC RF310R	≥ 100 mm
----------------	----------

Technical specifications

Article number	6GT2801-1AB10	6GT2801-1AB20-0AX1
Product type designation	RF310R reader	RF310R reader
Suitability for operation	RF300 and ISO 15693 transponders (MDS Dxxx), for connecting to communication modules	RF300 and ISO 15693 transponders (MDS Dxxx), for serial connection to control systems (Scan Mode)
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	60 mm; Range is dependent on transponder type: observe http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	RF300-specific, ISO 15693, ISO 18000-3	RF300-specific, ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	106 kbit/s	106 kbit/s
Product feature multitag-capable	No	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s	115.2 kbit/s
Transmission time for user data		
• for write access per byte typical	0.13 ms	
• for read access per byte typical	0.13 ms	0.13 ms
Interfaces		
Standard for interfaces for communication	RS422	RS422
Type of electrical connection	M12, 8-pin	M12, 8-pin

RFID systems for the HF range

SIMATIC RF300 readers

RF310R

Article number	6GT2801-1AB10	6GT2801-1AB20-0AX1
Product type designation	RF310R reader	RF310R reader
Mechanical data		
Material	PA 12	PA 12
Color	anthracite	anthracite
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm
Supply voltage, current consumption, power loss		
Supply voltage		
• at DC Rated value	24 V	24 V
• at DC	20.4 ... 28.8 V	20.4 ... 28.8 V
Consumed current at DC at 24 V		
• typical	0.05 A	0.05 A
Permitted ambient conditions		
Ambient temperature		
• during operation	-25 ... +70 °C	-25 ... +70 °C
• during storage	-40 ... +85 °C	-40 ... +85 °C
• during transport	-40 ... +85 °C	-40 ... +85 °C
Protection class IP	IP67	IP67
Shock resistance	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²
Design, dimensions and weight		
Width	55 mm	55 mm
Height	30 mm	30 mm
Depth	75 mm	75 mm
Net weight	0.2 kg	0.2 kg
Mounting type	4 x M5 screws	4 x M5 screws
Cable length		
• for RS422 interface maximum	1 000 m	1 000 m
Product properties, functions, components general		
Display version	3-color LED	3-color LED
Product feature silicon-free	Yes	Yes
Standards, specifications, approvals		
Certificate of suitability	Wireless according to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, UL/CSA	Wireless according to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, UL/CSA
MTBF	154 y	170 y


Selection and ordering data

	Article No.
SIMATIC RF310R reader	
• With RS422 interface (3964R protocol)	6GT2801-1AB10
• as a scan mode variant (RS422)	6GT2801-1AB20-0AX1
Accessories	
Note: All connection options can be found in the chapter 5 "Communication Modules".	
DVD „RFID-Systems Software & Documentation“	6GT2080-2AA20

More information

All current wireless approvals can be found on the Internet at:
<http://www.siemens.com/rfid-approvals>

Dimensional drawings



SIMATIC RF310R reader without Scan Mode

G_FS10_XX_00034

RFID systems for the HF range

SIMATIC RF300 readers

RF340R

Overview



The SIMATIC RF340R is a reader with integrated antenna for the medium performance range and can be used to great advantage in assembly lines thanks to its compact design. This reader is also particularly suitable for dynamic applications, in which the transponder does not stop during the read/write process.

This reader has an RS422 interface with 3964R transmission procedure for connection to RFID communication modules (see Chapter 5).

Thanks to the high degree of protection and the use of high-quality materials, the SIMATIC RF340R ensures problem-free use even under the toughest industrial conditions. It is connected via an 8-pole M12 plug-in connector.

The reader can process the high-speed RF300 transponders and the ISO-15693-compatible transponders (see RFID systems field data table on page 1/10).

Design

Minimum distance from reader to reader

SIMATIC RF340R	≥ 200 mm
----------------	----------

Technical specifications

Article number	6GT2801-2AB10
Product type designation	RF340R reader
Suitability for operation	RF300 and ISO 15693 transponders (MDS Dxxx), for connecting to communication modules

Wireless frequencies

Operating frequency Rated value	13.56 MHz
---------------------------------	-----------

Article number	6GT2801-2AB10
Product type designation	RF340R reader
Elektrische Daten	
Range maximum	140 mm; Range is dependent on transponder type: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	RF300-specific, ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	106 kbit/s
Product feature multitag-capable	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s
Transmission time for user data	
• for write access per byte typical	0.13 ms
• for read access per byte typical	0.13 ms
Interfaces	
Standard for interfaces for communication	RS422
Type of electrical connection	M12, 8-pin
Mechanical data	
Material	PA 12
Color	anthracite
Mounting distance relating to metal surfaces recommended minimum	0 mm
Supply voltage, current consumption, power loss	
Supply voltage	
• at DC Rated value	24 V
• at DC	20.4 ... 28.8 V
Consumed current at DC at 24 V	
• typical	0.1 A
Permitted ambient conditions	
Ambient temperature	
• during operation	-25 ... +70 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
Protection class IP	IP67
Shock resistance	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Width	75 mm
Height	41 mm
Depth	75 mm
Net weight	0.25 kg
Mounting type	2 x M5 screws
Cable length	
• for RS422 interface maximum	1 000 m
Product properties, functions, components general	
Display version	3-color LED
Product feature silicon-free	Yes
Standards, specifications, approvals	
Certificate of suitability	Wireless according to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, UL/CSA, Ex: II 3G Ex nA nC IIB T5, II 3D Ex tD A22 IP6x T80°C
MTBF	140 y

2

SIMATIC RF300 readers

Selection and ordering data

Accessories

Note:
All connection options can be
found in section 5,
"Communication Modules".

More information

All current wireless approvals can be found on the Internet at:

<http://www.siemens.com/rfid-approvals>

Overview



SIMATIC RF350R is a universal reader for operation with external antennas. Due to the different, pluggable antenna designs (flat antenna, round antennas), there are many possible applications in the area of industrial production, especially in assembly lines.

This reader has an RS422 interface with 3964R transmission procedure for connection to RFID communication modules (see Chapter 5).

Due to the high degree of protection and the use of high-quality materials, the SIMATIC RF350R ensures problem-free operation even under the harshest industrial conditions. It is connected via an 8-pole M12 plug-in connector.

The reader can process the high-speed RF300 transponders and the ISO-15693-compatible transponders (see RFID systems field data table on page 1/10).

Connectable antennas

One of each of the following antennas can be operated on an RF350R:

- ANT 1, universal flat antenna, also for dynamic applications, dimensions L x W x H (mm): 75 x 75 x 20
- Due to its slimline, compact design, the ANT 3 can still be precisely positioned even in cramped conditions.
Dimensions L x W x H (mm): 50 x 28 x 10
- ANT 3S, same as ANT 3, except suitable exclusively for processing of MDS D117, MDS D127, MDS D421 and MDS D521 transponders. The dimensions are L x W x H (mm): 50 x 28 x 10.
- ANT 12, universal round antenna in M12 design for assembly lines with extremely small workpiece holders.
Dimensions Ø x L (mm): M12 x 40
- ANT 18, universal round antenna in M18 design for assembly lines with small workpiece holders.
Dimensions Ø x L (mm): M18 x 55
- ANT 30, universal round antenna for assembly lines with small workpiece holders.
Dimensions Ø x L (mm): M30 x 58

Design

Connectable antennas	ANT 1	ANT 3	ANT 3S	ANT 12	ANT 18	ANT 30
See page	2/131	2/132	2/133	2/136	2/137	2/138
Inductive interface to the transponder	13.56 MHz					
Range, max	140 mm	45 mm	16 mm	16 mm	35 mm	55 mm

Minimum distance between antennas

RF350R with antenna	ANT 1	ANT 3	ANT 3S	ANT 12	ANT 18	ANT 30
Minimum distance (mm) from antenna to antenna (D)						
• ANT 1	800	-	-	-	-	-
• ANT 3	-	200	-	-	-	-
• ANT 3S	-	-	80	-	-	-
• ANT 12	-	-	-	80	-	-
• ANT 18	-	-	-	-	125	-
• ANT 30	-	-	-	-	-	200

RFID systems for the HF range

SIMATIC RF300 readers

RF350R


Technical specifications

Article number	6GT2801-4AB10
Product type designation	RF350R reader
Suitability for operation	RF300 and ISO 15693 transponders (MDS Dxxx), for connecting to communication modules
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	140 mm; Range is dependent on transponder type: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	RF300-specific, ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	106 kbit/s
Product feature multitag-capable	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s
Transmission time for user data	
• for write access per byte typical	0.13 ms
• for read access per byte typical	0.13 ms
Interfaces	
Number of external antennas	1
Standard for interfaces for communication	RS422
Type of electrical connection	
• for external antenna(s)	M8, 4-pin
• for communications interface	M12, 8-pin
Mechanical data	
Material	PA 12
Color	anthracite
Mounting distance relating to metal surfaces recommended minimum	0 mm
Supply voltage, current consumption, power loss	
Supply voltage	
• at DC Rated value	24 V
• at DC	20.4 ... 28.8 V
Consumed current at DC at 24 V	
• typical	0.1 A
Permitted ambient conditions	
Ambient temperature	
• during operation	-25 ... +70 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
Protection class IP	IP65
Shock resistance	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Width	75 mm
Height	41 mm
Depth	75 mm
Net weight	0.25 kg
Mounting type	2 x M5 screws
Cable length	
• of antenna cable fixed value	3 m
• for RS422 interface maximum	1 000 m

Article number	6GT2801-4AB10
Product type designation	RF350R reader
Product properties, functions, components general	
Display version	3-color LED
Product feature silicon-free	Yes
Standards, specifications, approvals	
Certificate of suitability	Wireless according to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, UL/CSA, Ex: II 3G Ex nA nC IIB T5, II 3D Ex tD A22 IP6x T80°C
MTBF	140 y
Accessories	Various antennas are available

Selection and ordering data

	Article No.
SIMATIC RF350R reader	6GT2801-4AB10
Without antenna	
Antennas	
External antenna ANT 1	6GT2398-1CB00
For RF350R reader, with antenna connecting cable (3 m, permanently connected to antenna ANT 1). See page 2/131.	
External antenna ANT 3	6GT2398-1CD40-0AX0
For RF350R reader, with antenna connecting cable (3 m, double ended (plug M8 straight / M8 angled)). See page 2/132.	
External antenna ANT 3S	6GT2398-1CD60-0AX0
For RF350R reader, with antenna connecting cable (3 m, double ended (plug M8 straight / M8 angled)). See page 2/133.	
External antenna ANT 12	6GT2398-1CC00
For RF350R readers, with antenna connecting cable. See page 2/136.	
External antenna ANT 18	6GT2398-1CA00
For RF350R readers, with antenna connecting cable. See page 2/137.	
External antenna ANT 30	6GT2398-1CD00
For RF350R readers, with antenna connecting cable. See page 2/138.	
Accessories	
Note: All connection options can be found in the chapter 5 "Communication Modules".	
DVD "RFID-Systems Software & Documentation"	6GT2080-2AA20

Dimensional drawings


SIMATIC RF350R reader

More information

All current wireless approvals can be found on the Internet at:

<http://www.siemens.com/rfid-approvals>

RFID systems for the HF range

SIMATIC RF300 readers

RF380R


Overview



6GT2801-3AB10

SIMATIC RF380R is a reader with an integral antenna for the top-end performance range and its compact construction makes it ideal for use in assembly lines in which long ranges are required (e.g. bodyshop/paintshop in the automotive industry). This reader is also particularly suitable for dynamic applications, in which the transponder does not stop during the read/write process (e.g. baggage conveyors in airports).

This reader has both an RS422 and an RS232 interface with a 3964R transmission procedure for connection to RFID communication modules (see Communication modules) as well as to non-Siemens controllers or the PC.



6GT2801-3AB20-0AX1

The RF380R is also available as a scan mode variant (automatic read mode, without command control). This automatic read-only mode does not require a special command control, but supplies the autonomously read transponder data directly to the connected host system.

Due to the high degree of protection and the use of high-quality materials, the SIMATIC RF380R facilitates problem-free operation even under the harshest industrial conditions. It is connected via an 8-pole M12 plug-in connector.

The reader can process the high-speed RF300 transponders and the ISO-15693-compatible transponders (see RFID systems field data table on page 1/10).

Design

Minimum distance from reader to reader

SIMATIC RF380R	≥ 400 mm
----------------	----------

RFID systems for the HF range

SIMATIC RF300 readers

RF380R

2

Technical specifications



Article number	6GT2801-3AB10	6GT2801-3AB20-0AX1
Product type designation	RF380R reader	RF380R reader (ISO scan mode)
Suitability for operation	RF300 and ISO 15693 transponders (MDS Dxxx), for connecting to communication modules and PC systems	RF300 and ISO 15693 transponders (MDS Dxxx), for serial connection to control systems (Scan Mode)
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	200 mm; Range adjustable in reader via transmission power, range is dependent on transponder type: observe http://support.automation.siemens.com/WW/view/en/67384964	200 mm
Protocol with radio transmission	RF300-specific, ISO 15693, ISO 18000-3	RF300-specific, ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	106 kbit/s	106 kbit/s
Product feature multitag-capable	No	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s	115.2 kbit/s
Transmission time for user data		
• for write access per byte typical	0.13 ms	
• for read access per byte typical	0.13 ms	0.13 ms
Interfaces		
Standard for interfaces for communication	RS422/RS232	RS422/RS232
Type of electrical connection	M12, 8-pin	M12, 8-pin
Mechanical data		
Material	PA 12	PA 12
Color	anthracite	anthracite
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm
Supply voltage, current consumption, power loss		
Supply voltage		
• at DC Rated value	24 V	24 V
• at DC	20.4 ... 28.8 V	20.4 ... 28.8 V
Consumed current at DC at 24 V		
• typical	0.16 A	0.16 A
Permitted ambient conditions		
Ambient temperature		
• during operation	-25 ... +70 °C	-25 ... +70 °C
• during storage	-40 ... +85 °C	-40 ... +85 °C
• during transport	-40 ... +85 °C	-40 ... +85 °C
Protection class IP	IP67	IP67
Shock resistance	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²
Design, dimensions and weight		
Width	80 mm	80 mm
Height	41 mm	41 mm
Depth	160 mm	160 mm
Net weight	0.6 kg	0.6 kg
Mounting type	4 x M5 screws	4 x M5 screws
Cable length		
• with RS232 interface maximum	30 m	30 m
• for RS422 interface maximum	1 000 m	1 000 m
Product properties, functions, components general		
Display version	3-color LED	3-color LED
Product feature silicon-free	Yes	Yes
Standards, specifications, approvals		
Certificate of suitability	Wireless according to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, UL/CSA, Ex: II 3G Ex nC IIB T5	Wireless according to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, UL/CSA, Ex: II 3G Ex nC IIB T5
MTBF	109 y	109 y

RFID systems for the HF range


SIMATIC RF300 readers

RF380R

Selection and ordering data

	Article No.		Article No.
SIMATIC RF380R reader <ul style="list-style-type: none"> RF300 and ISO15693 modes scan mode 	6GT2801-3AB10 6GT2801-3AB20-0AX1	Accessories Note: All connection options can be found in section 5, "Communication Modules".	
		RS232 connecting cable Between reader and PC (RS232), 5 m long, material: PUR, CMG approval. <ul style="list-style-type: none"> 24 V connection with M12 plug 	6GT2891-4KH50
		<ul style="list-style-type: none"> 24 V connection with open ends 	6GT2891-4KH50-0AX0
		DVD "RFID-Systems Software & Documentation"	6GT2080-2AA20

Dimensional drawings



FS10_00285

SIMATIC RF380R reader

More information

All current wireless approvals can be found on the Internet at:

<http://www.siemens.com/rfid-approvals>

RFID systems for the HF range

SIMATIC RF300 readers

RF382R

Overview



SIMATIC RF382R is a reader with an integral special antenna for the top-end performance range and its compact construction makes it ideal for implementation in conveyor systems in which transponders have to be read from the side (e.g. in the clothing industry or laundry applications). This reader is also particularly suitable for dynamic applications, in which the transponder does not stop during the read/write process.

The reader has both an RS422 interface and an RS232 interface with scan mode functionality. This automatic read-only mode does not require a special command control, but supplies the autonomously read transponder data directly to the connected host system.

Due to the high degree of protection and the use of high-quality materials, the SIMATIC RF382R facilitates problem-free operation even under the harshest industrial conditions. It is connected via an 8-pole M12 plug-in connector.

The reader can process the high-speed RF300 transponders and the ISO-15693-compatible transponders (see RFID systems field data table on page 1/10).

2

Design

Minimum distance from reader to reader

SIMATIC RF382R	≥ 200 mm
----------------	----------

Technical specifications

Article number	6GT2801-3AB20-0AX0
Product type designation	RF382R reader
Suitability for operation	RF300 and ISO 15693 transponders (MDS Dxxx), lateral antenna field, for serial connection to control systems (Scan Mode)
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	75 mm; Range adjustable in reader via transmission power, range is dependent on transponder type: observe
http://support.automation.siemens.com/WW/view/en/67384964	
Protocol with radio transmission	RF300-specific, ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	106 kbit/s
Product feature multitag-capable	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s
Transmission time for user data	
• for read access per byte typical	0.13 ms
Interfaces	
Standard for interfaces for communication	RS422/RS232
Type of electrical connection	M12, 8-pin
Mechanical data	
Material	PA 12
Color	anthracite
Mounting distance relating to metal surfaces recommended minimum	0 mm

Article number	6GT2801-3AB20-0AX0
Product type designation	RF382R reader
Supply voltage, current consumption, power loss	
Supply voltage	
• at DC Rated value	24 V
• at DC	20.4 ... 28.8 V
Consumed current at DC at 24 V	
• typical	0.16 A
Permitted ambient conditions	
Ambient temperature	
• during operation	-25 ... +70 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
Protection class IP	IP67
Shock resistance	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²

RFID systems for the HF range

SIMATIC RF300 readers

RF382R


Article number	6GT2801-3AB20-0AX0
Product type designation	RF382R reader
Design, dimensions and weight	
Width	80 mm
Height	41 mm
Depth	160 mm
Net weight	0.6 kg
Mounting type	4 x M5 screws
Cable length	
• with RS232 interface maximum	30 m
• for RS422 interface maximum	1 000 m
Product properties, functions, components general	
Display version	3-color LED
Product feature silicon-free	Yes
Standards, specifications, approvals	
Certificate of suitability	Wireless according to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, UL/CSA
MTBF	109 y
Accessories	
Accessories	RS232 connecting cables

Selection and ordering data

	Article No.
SIMATIC RF382R reader RF300 and ISO15693 modes.	6GT2801-3AB20-0AX0
Accessories	
RS232 connecting cable Between reader and PC (RS232), 5 m long, material: PUR, CMG approval.	
• 24 V connection with M12 plug	6GT2891-4KH50
• 24 V connection with open ends	6GT2891-4KH50-0AX0
DVD "RFID-Systems Software & Documentation"	6GT2080-2AA20



Dimensional drawings



SIMATIC RF382R reader

Overview



The SIMATIC RF350M is a powerful mobile handheld terminal for applications in the field of production logistics, distribution and service. In addition, it is an indispensable tool for commissioning and testing. The RF350M is equipped either with an integral antenna or with a socket for connecting external antennas.

Design

The SIMATIC RF350M mobile handheld terminal consists of a basic unit (Basis Nordic ID Merlin) and an integrated read/write device for RF300 transponders and transponders of the MDS D-family according to the ISO15693 standard. The read/write device is equipped either with an integrated antenna or with a socket for connecting external antennas.

The SIMATIC RF350M has a splash-proof enclosure (IP54), a color QVGA color touchscreen with a resolution of 320 x 240 pixels, TFT portrait format, an alphanumeric keyboard and various interfaces e.g. for SD memory cards, battery charging and WLAN.

Integral read/write unit, inductive interface to transponder	For SIMATIC RF300 / RF200, MOBY D (ISO)
Read/write distance to the transponder (with integrated antenna)	<ul style="list-style-type: none"> RF300: up to 50 mm ISO: up to 80 mm
Read/write distance to the transponder (with external antenna)	<ul style="list-style-type: none"> RF300: up to 30 mm ISO: up to 60 mm
Energy/data transmission frequency	13.56 MHz
Serial interface (internal, to basic unit)	RS232, 3964R protocol
Functionality of the software application	Standard user interface for reading/writing of transponders, etc.

Function

The supplied and pre-installed software provides the following service and test functions for RF300 and MDS Dxxx transponders¹⁾:

- Reading data from the transponder
- Writing data to the transponder
- Reading and displaying the ID number of the transponder
- Displaying and editing the data in hexadecimal, ASCII, decimal and binary formats

Based on the operating system and communication standard (WIN CE), the unit ensures simple integration into existing or planned infrastructures. Various optional development tools for the PC and a wide selection of accessories are available.

Connectable antennas

One of each of the following antennas can be operated on a SIMATIC RF350M for external antennas:

- ANT 3,
Dimensions L x W x H (mm): 28 x 50 x 10
- ANT 3S,
Dimensions L x W x H (mm): 28 x 50 x 10
- ANT 8,
Dimensions Ø x L (mm): M8 x 38
- ANT 12,
Dimensions Ø x L (mm): M12 x 40
- ANT 18,
Dimensions Ø x L (mm): M18 x 55
- ANT 30,
Dimensions Ø x L (mm): M30 x 58

¹⁾ Exception: The MDS D421, MDS D422, MDS D127 and MDS D117 transponders can only be operated with the SIMATIC RF350M mobile handheld terminal with external antenna..

RFID systems for the HF range


SIMATIC RF300 readers

RF350M mobile handheld terminal

Technical specifications

Article number	6GT2803-1BA00	6GT2803-1BA10
Product type designation	RF350M mobile hand-held terminal	RF350M mobile hand-held terminal for external antenna
Suitability for operation	RF300- and RF200/ISO 15693 transponders	RF300- and RF200/ISO 15693 transponders, in particular for small transponders
Range	80 mm	80 mm
Range note		dependent of the type of external antenna
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Protocol with radio transmission	RF300-specific, ISO 15693, ISO 18000-3	RF300-specific, ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	106 kbit/s	106 kbit/s
Product feature multitag-capable	No	No
Supply voltage, current consumption, power loss		
Type of current supply	Battery operation or mains operation via docking station	Battery operation or mains operation via docking station
Type of battery	Lithium ion accumulator, fast charging capability	Lithium ion accumulator, fast charging capability
Type of battery as back-up battery Integrated	Lithium ion battery, permanently installed, cannot be replaced by customer	Lithium ion battery, permanently installed, cannot be replaced by customer
Battery capacity	2.6 Ah	2.6 Ah
Operating period with standard battery typical	8 h	8 h
Permitted ambient conditions		
Ambient temperature		
• during operation	-20 ... +55 °C	-20 ... +55 °C
• during storage	-20 ... +60 °C	-20 ... +60 °C
Relative humidity at 25 °C without condensation during operation maximum	95 %	95 %
Height of fall maximum	1.2 m	1.2 m
Protection class IP	IP54	IP54
Design, dimensions and weight		
Width	90 mm	90 mm
Height	250 mm	250 mm
Depth	47 mm	47 mm
Net weight	0.6 kg	0.6 kg
Product properties, functions, components general		
Design of the display	QVGA color touch screen 3.5 inch, 240 x 320 pixels	QVGA color touch screen 3.5 inch, 240 x 320 pixels
Operator element version	Alphanumeric	Alphanumeric
Design of acoustic signaling element	Speakers	Speakers
Design of the interface	WLAN, USB and Ethernet via charging station	WLAN, USB and Ethernet via charging station
Storage capacity		
• of the RAM	256 Mibyte	256 Mibyte
• of the data and program memory	288 Mibyte	288 Mibyte
• of the data memory can be used	256 Mibyte	256 Mibyte
Product functions management, configuration		
Operating system pre-installed	Windows Embedded CE 6.0	Windows Embedded CE 6.0
Product function of the software	RF350M.exe for execution of RF300 and ISO15693 (RF200, MOBY D) transponders	RF350M.exe for execution of RF300 and ISO15693 (RF200, MOBY D) transponders
Standards, specifications, approvals		
Certificate of suitability	EMC: EN 55022, EN 301 489, EN 300 330, EN 300 328, EN 301 893, safety: EN 60950	EMC: EN 55022, EN 301 489, EN 300 330, EN 300 328, EN 301 893, safety: EN 60950
Accessories		
Accessories	Charging/docking station with USB- and Ethernet interface, changeable accumulator Li-ion 2600 mAh / 7.4 V	Charging/docking station with USB- and Ethernet interface, changeable accumulator Li-ion 2600 mAh / 7.4 V external antenna ANT 3, ANT 3S, ANT 8, ANT 12, ANT 18, ANT 30

Selection and ordering data

	Article No.
SIMATIC RF350M mobile handheld terminal <ul style="list-style-type: none"> Basic unit with integrated RFID read/write unit (RF300 and ISO 15693), integrated antenna, battery, standard software pre-installed, without charging/docking station. Basic unit with integrated RFID read/write unit (RF300 and ISO 15693), for external antennas, battery, standard software pre-installed, without charging/docking station, without external antenna. 	6GT2803-1BA00 6GT2803-1BA10
External antennas for 6GT2803-1BA10	
External antenna ANT 3 For RF350M mobile handheld terminal (6GT2803-1BA10), without antenna connecting cable. See page 2/132.	6GT2398-1CD30-0AX0
External antenna ANT 3S For RF350M mobile handheld terminal (6GT2803-1BA10), without antenna connecting cable. See page 2/133.	6GT2398-1CD50-0AX0
External antenna ANT 8 For RF350M mobile handheld terminal (6GT2803-1BA10), without antenna connecting cable. See page 2/134.	6GT2398-1CF00
Antenna adapter for ANT 3, ANT 3S and ANT 8 For direct connection of ANT 3, ANT 3S and ANT 8 to RF350M (6GT2803-1BA10). <ul style="list-style-type: none"> Length 0.1 m 	6GT2898-0EA00
 <ul style="list-style-type: none"> Length 3 m 	6GT2391-0AH30
External antenna ANT 12 For RF350M mobile handheld terminal, with antenna connecting cable. See page 2/136.	6GT2398-1CC00
External antenna ANT 18 For RF350M mobile handheld terminal, with antenna connecting cable. See page 2/137.	6GT2398-1CA00
External antenna ANT 30 For RF350M mobile handheld terminal, with antenna connecting cable. See page 2/138.	6GT2398-1CD00

Accessories


Note:
All connection options can be found in Chapter 5, "Communication Modules".

Charging/docking station

For a mobile handheld terminal as well as a spare battery, including wide-range plug-in power supply 100 to 240 V AC and country-specific adapters as well as USB cable.


Spare battery

For basic device, 2600 mAh, Li-ion batteries.

DVD „RFID-Systems Software & Documentation“
Article No.
6GT2803-0BM00
6GT2803-0CA00
6GT2080-2AA20
Dimensional drawings


Docking station for SIMATIC RF350M handheld terminal

More information

All current wireless approvals can be found on the Internet at:
<http://www.siemens.com/rfid-approvals>

RFID systems for the HF range

MOBY D

Introduction

Overview



The MOBY D RFID system is particularly suitable for use in industrial production in the areas of production control, asset management and tracking & tracing.

MOBY D is used for implementing identification tasks with medium performance (ISO 15693) in the HF range (13.56 MHz).

MOBY D offers a comprehensive portfolio of ISO 15693 transponders for a whole variety of requirements - from low-cost SmartLabels for simple identification tasks through rugged credit card formats, right up to transponders for use in especially harsh environments such as paint shops or in the laundry and cleaning industry.

The communication modules that can be used for all MOBY and SIMATIC RF systems (ASM 456, ASM 475, SIMATIC RF1xxC) are available for connecting to SIMATIC S7-300, PROFIBUS, PROFINET and TCP/IP (XML).

Depending on the read/write distance, different readers are available with integrated or remote antennas.

The MOBY D identification system boasts the following performance features:

- 13.56 MHz operating frequency.
- Operation according to ISO 15693.
- Passive (without battery), maintenance-free transponder (MDS Dxxx) with memory of up to 2 000 bytes FRAM.
- Rugged, compact components with IP68 / IPx9K degree of protection.
- Simple integration in SIMATIC, PROFIBUS, PROFINET and TCP/IP with the help of tried and tested function blocks (FC 45, FB 45).

Benefits



- High-performance reader with bulk detection capability and a range of up to 0.35 m.
- Cost-effective and battery-free ISO 15693 transponders up to 2 KB with IP68 degree of protection and 220 °C temperature range, with ATEX approval.
- Flexible and economic solutions thanks to the complete and scalable portfolio for the field of industrial identification.

- Simplified engineering, commissioning, diagnostics and maintenance through seamless integration into Totally Integrated Automation (TIA):
 - Integrated bus connection to an automation system, such as SIMATIC, SIMOTION or SINUMERIK via communication modules with PROFIBUS and PROFINET.
 - Simple S7 software integration via ready-to-use function blocks.
- High security of investment thanks to:
 - Open ISO 15693 standard.
 - Software compatibility between the RFID systems of Siemens.
 - Standardized communication interfaces.
- Openness through connection possibilities to different bus systems from different manufacturers and PC environments via communication modules.
- Worldwide Service and Support.

Application

- High-performance reader with bulk detection capability and a range of up to 0.35 m.
- Cost-effective and battery-free ISO 15693 transponders up to 2 KB with IP68 degree of protection and 220 °C temperature range, with ATEX approval.
- Flexible and economic solutions thanks to the complete and scalable portfolio for the field of industrial identification.
- Simplified engineering, commissioning, diagnostics and maintenance through seamless integration into Totally Integrated Automation (TIA):
 - Integrated bus connection to an automation system, such as SIMATIC, SIMOTION or SINUMERIK via communication modules with PROFIBUS and PROFINET.
 - Simple S7 software integration via ready-to-use function blocks.
- High security of investment thanks to:
 - Open ISO 15693 standard.
 - Software compatibility between the RFID systems of Siemens.
 - Standardized communication interfaces.
- Openness through connection possibilities to different bus systems from different manufacturers and PC environments via communication modules.
- Worldwide Service and Support.

Design

The MOBY D readers are available in different designs. In addition to the SLG D12 and SLG D12S readers with integrated antennas, the SLG D11 and SLG D11S readers permit the connection of various external antennas with which extended ranges of up to 380 mm can be achieved.

The high degree of protection of up to IP65 enables the MOBY D readers to be used in harsh, industrial environments.

The interface to the automation level can be implemented by means of communication modules. For quick and easy cabling, pre-assembled cables with M12 plug-in connectors are available in various lengths.

The MOBY D transponders compliant with ISO 15693 are used as mobile data carriers.

Transponders suitable for a wide variety of different requirements can be selected from an extensive range: From low-cost SmartLabels for simple identification tasks, through rugged credit card formats, right up to screw-fit transponders that can be automatically attached by robots.

The transponders are attached to the object to be identified, e.g. by means of screws, adhesive or pre-assembled spacer.

Function

All MOBY D readers are suitable for reliable reading and writing tasks in the HF range.

The readers are equipped either with an RS232 interface for the connection to the PC or to SIMATIC S7-1200 or with an RS422 interface for the connection via communication modules to the automation level (e.g. SIMATIC S7) via standard fieldbuses (e.g. PROFIBUS or PROFINET).

User-friendly function blocks are available for the S7 programming.

In the event of an error, the S7 application receives a detailed error message from the communication module via the function block.

Integration

A wide range of communication modules, function blocks, as well as high-performance drivers and function libraries permits easy and quick integration into the application.

And best of all: MOBY D is part of Totally Integrated Automation (TIA) and can be integrated easily and cost-effectively into the SIMATIC world.

For more details on the connection possibilities, see the section 5 "Communication Modules".

SIMATIC Ident Configuration Guide

Here is a compact configuration tool for setting up RFID systems:

<http://support.automation.siemens.com/WW/view/en/67384964>

Technical specifications



RFID system	MOBY D
Transmission frequency	13.56 MHz
Range	Max. 380 mm
Protocol (air interface)	<ul style="list-style-type: none"> • ISO 15693 • ISO 18000-3
Approvals	<ul style="list-style-type: none"> • EN 300330, 301489, CE • FCC Part 15 • UL/CSA
Memory capacity	992 bytes (EEPROM) / 2 000 bytes (FRAM)
Data transmission rate reader – transponder	
<ul style="list-style-type: none"> • Read • Write 	Max. 1.5 kbyte/s Max. 0.5 kbyte/s
Multitag/Bulk capability	Yes
Special features	<ul style="list-style-type: none"> • SIMATIC or PC/IT integration • Long sensing ranges with excellent interference immunity • External antennas for industrial applications



RFID systems for the HF range

MOBY D readers

Introduction

Overview

Readers	Features	Page
SLG D11 basic unit 	Reader for connection of an external antenna (ANT D2 / ANT D5). With RS232 interface for connection to PC/PLC.	2/123
SLG D11S basic unit 	Like SLG D11, but with RS422 interface for connection to SIMATIC S7 / PROFIBUS / PROFINET / Ethernet TCP/IP via ASM 456, ASM 475, SIMATIC RF120C, RF160C, RF170C, RF180C or RF182C.	2/123

Readers	Features	Page
SLG D12 	Universal reader with integrated antenna. With RS232 interface for connection to PC/PLC.	2/126
SLG D12S 	Like SLG D12, but with RS422 interface for connection to SIMATIC S7 / PROFIBUS / PROFINET / Ethernet TCP/IP via ASM 456, ASM 475, SIMATIC RF120C, RF160C, RF170C, RF180C or RF182C.	2/126

Overview


The SLG D11/SLG D11S basic units are readers in the mid-performance range and can be operated with the ANT D2 and ANT D5 antennas.

SLG D11

Equipped with RS232 serial interface for connection to PC/PLC.

SLG D11S

Equipped with an RS422 serial interface, which permits communication via the communication modules ASM 456, ASM 475, SIMATIC RF120C, RF160C, RF170C and SIMATIC RF180C, or RF182C to SIMATIC S7, PROFIBUS/PROFINET or Ethernet TCP/IP.

Connectable antennas
ANT D2

The ANT D2 antenna is designed for transponders that are directed sideways past the antenna. This antenna is specially designed for high speeds, e.g. in overhead conveyors, assembly lines, production and order picking. It can be mounted directly onto metal surfaces. Description see page 2/140.

ANT D5

The ANT D5 is a universal antenna designed for warehouse, logistics and distribution applications. The high degree of protection (IP65) enables the antenna to be used under harsh industrial conditions. A spacer kit is required for mounting on metal surfaces. Description see page 2/141.


Technical specifications

Article number	6GT2698-1AC00	6GT2698-2AC00
Product type designation	SLG D11 reader	SLG D11S reader
Suitability for operation	ISO 15693 transponders (MDS Dxxx), for connecting to PC systems	ISO 15693 transponders (MDS Dxxx), for connecting to communication modules
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	380 mm; Range is dependent on transponder type: observe http://support.automation.siemens.com/WWW/view/en/67384964	
Protocol with radio transmission	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s
Product feature multitag-capable	Yes	No
Transfer rate at the point-to-point connection serial maximum	38.4 kbit/s	19.2 kbit/s
Transmission time for user data		
• for write access per byte typical	2.5 ms	2.5 ms
• for read access per byte typical	2.5 ms	2.5 ms
Interfaces		
Number of external antennas	1	1
Standard for interfaces for communication	RS232	RS422
Type of electrical connection		
• for external antenna(s)	TNC	TNC
• for supply voltage	M12, 4-pin, female connector	M12, 4-pin, female connector
• for communications interface	Sub-D, 9-pin, male	Sub-D, 9-pin, male
Mechanical data		
Material	PA 12	PA 12
Color	anthracite	anthracite
Tightening torque of the screw for securing the equipment maximum	2 Nm	2 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm

RFID systems for the HF range

MOBY D readers

SLG D11/SLG D11S basic unit for ANT D2 and ANT D5 antennas




Article number	6GT2698-1AC00	6GT2698-2AC00
Product type designation	SLG D11 reader	SLG D11S reader
Supply voltage, current consumption, power loss		
Supply voltage		
• at DC Rated value	24 V	24 V
• at DC	20 ... 30 V	20 ... 30 V
Consumed current at DC at 24 V		
• typical	0.2 A	0.2 A
• maximum	0.6 A	0.6 A
Permitted ambient conditions		
Ambient temperature		
• during operation	-25 ... +55 °C	-25 ... +55 °C
• during storage	-25 ... +70 °C	-25 ... +70 °C
• during transport	-25 ... +70 °C	-25 ... +70 °C
Protection class IP	IP65	IP65
Shock resistance	EN 60721-3-7 Class 7 M2	EN 60721-3-7 Class 7 M2
Shock acceleration	300 m/s ²	300 m/s ²
Vibrational acceleration	15 m/s ²	15 m/s ²
Design, dimensions and weight		
Width	80 mm	80 mm
Height	40 mm	40 mm
Depth	160 mm	160 mm
Net weight	0.26 kg	0.26 kg
Mounting type	2 x M5 screws	2 x M5 screws
Cable length		
• of antenna cable minimum	3.3 m	3.3 m
• of antenna cable maximum	10.5 m	10.5 m
• with RS232 interface maximum	30 m	
• for RS422 interface maximum		300 m
Standards, specifications, approvals		
Certificate of suitability	CE, FCC, IC (Canada), UL 60950, safe for cardiac pacemakers	CE, FCC, IC (Canada), UL 60950, safe for cardiac pacemakers
MTBF	23 y	23 y
Accessories		
Accessories	Various antennas are available, Wide-range power supply, connectors and cables	Various antennas are available, Wide-range power supply, connectors and cables

RFID systems for the HF range


MOBY D readers

SLG D11/SLG D11S basic unit for ANT D2 and ANT D5 antennas

Selection and ordering data

	Article No.
SLG D11 reader Basic unit (without antenna) with RS232 serial interface for connection to PC/PLC.	6GT2698-1AC00
SLG D11S reader Basic unit (without antenna) with RS422 serial interface for connection to SIMATIC S7/PROFIBUS/PROFINET via communication module.	6GT2698-2AC00
Accessories Note: All connection options can be found in section 5, "Communication Modules".	
Antenna ANT D2 For SLG D11 / SLG D11S basic units, incl. antenna cable, PVC, length 3.3 m. See page 2/140.	6GT2698-5BB00
Antenna ANT D5 For SLG D11 / SLG D11S basic units. See page 2/141.	6GT2698-5AA10
Wide-range power supply 100 V ... 240 V AC / 24 V DC, 3 A With no-load protection, with continuous short-circuit protection <ul style="list-style-type: none"> • With EU plug • With UK plug • With US plug 	6GT2898-0AA00 6GT2898-0AA10 6GT2898-0AA20
Connecting cable for 24 V DC For wide-range power supply, PUR, length 5 m. 	6GT2491-1HH50
24 V connector (M12 socket) For SLG D1x reader. 	6GT2390-1AB00
RS232 cable for SLG D11, PUR 	
5 m	6GT2691-4BH50
20 m	6GT2691-4BN20
DVD „RFID-Systeme Software & Dokumentation“	6GT2080-2AA20

Dimensional drawings



SLG D11 / SLG D11S reader - basic unit

More information

All current wireless approvals can be found on the Internet at:

<http://www.siemens.com/rfid-approvals>

RFID systems for the HF range

MOBY D readers

SLG D12 / SLG D12S

Overview



The SLG D12 / SLG D12S basic devices are universal readers in the medium performance range with integral antennas.

SLG D12

Equipped with RS232 serial interface for connection to PC/PLC.

SLG D12S

Equipped with an RS422 serial interface, which permits communication via the communication modules ASM 456, ASM 475, SIMATIC RF120C, RF160C, RF170C and SIMATIC RF180C, or RF182C to SIMATIC S7, PROFIBUS/PROFINET or Ethernet TCP/IP.




RS232



ISO

6GT2601-0AB00



CM



ISO

6GT2602-0AB00 and
6GT2602-0AB10-0AX0

Technical specifications

Article number	6GT2601-0AB00	6GT2602-0AB00	6GT2602-0AB10-0AX0
Product type designation	SLG D12 reader	SLG D12S reader	SLG D12S reader
Suitability for operation	ISO 15693 transponders (MDS Dxxx), for connecting to PC systems	ISO 15693 transponders (MDS Dxxx), for connecting to communication modules	ISO 15693 transponders (MDS Dxxx), for connecting to communication modules
Wireless frequencies			
Operating frequency Rated value	13.56 MHz	13.56 MHz	13.56 MHz
Electrical data			
Range maximum	220 mm; Range is dependent on transponder type: observe http://support.automation.siemens.com/WW/view/en/67384964		
Protocol with radio transmission	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s	26.5 kbit/s
Product feature multitag-capable	Yes	No	No
Transfer rate at the point-to-point connection serial maximum	38.4 kbit/s	19.2 kbit/s	19.2 kbit/s
Transmission time for user data			
• for write access per byte typical	2.5 ms	2.5 ms	2.5 ms
• for read access per byte typical	2.5 ms	2.5 ms	2.5 ms
Interfaces			
Standard for interfaces for communication	RS232	RS422	RS422
Type of electrical connection	Data: Sub-D, 9-pin, male, voltage: M12, 4-pin, female connector	Data: Sub-D, 9-pin, male, voltage: M12, 4-pin, female connector	M12, 8-pin
Mechanical data			
Material	PA 12	PA 12	PA 12
Color	anthracite	anthracite	anthracite
Tightening torque of the screw for securing the equipment maximum	2 Nm	2 Nm	2 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm	0 mm
Supply voltage, current consumption, power loss			
Supply voltage			
• at DC Rated value	24 V	24 V	24 V
• at DC	20 ... 30 V	20 ... 30 V	20 ... 30 V
Consumed current at DC at 24 V			
• typical	0.15 A	0.15 A	0.15 A
• maximum	0.6 A	0.6 A	0.6 A





RFID systems for the HF range

MOBY D readers

SLG D12 / SLG D12S

Article number	6GT2601-0AB00	6GT2602-0AB00	6GT2602-0AB10-0AX0
Product type designation	SLG D12 reader	SLG D12S reader	SLG D12S reader
Permitted ambient conditions			
Ambient temperature			
• during operation	-25 ... +55 °C	-25 ... +55 °C	-25 ... +55 °C
• during storage	-25 ... +70 °C	-25 ... +70 °C	-25 ... +70 °C
• during transport	-25 ... +70 °C	-25 ... +70 °C	-25 ... +70 °C
Protection class IP	IP65	IP65	IP65
Shock resistance	EN 60721-3-7 Class 7 M2	EN 60721-3-7 Class 7 M2	EN 60721-3-7 Class 7 M2
Shock acceleration	300 m/s ²	300 m/s ²	300 m/s ²
Vibrational acceleration	15 m/s ²	15 m/s ²	15 m/s ²
Design, dimensions and weight			
Width	80 mm	80 mm	80 mm
Height	40 mm	40 mm	40 mm
Depth	160 mm	160 mm	160 mm
Net weight	0.23 kg	0.23 kg	0.23 kg
Mounting type	2 x M5 screws	2 x M5 screws	2 x M5 screws
Cable length			
• with RS232 interface maximum	30 m		
• for RS422 interface maximum		300 m	300 m
Standards, specifications, approvals			
Certificate of suitability	CE, FCC, IC (Canada), UL 60950, safe for cardiac pacemakers	CE, FCC, IC (Canada), UL 60950, safe for cardiac pacemakers	CE, FCC, IC (Canada), UL 60950, safe for cardiac pacemakers
MTBF	23 y	23 y	23 y
Accessories			
Accessories	Wide-range power supply, connectors, cables	Wide-range power supply, connectors, cables	Wide-range power supply, connectors, cables

Selection and ordering data


	Article No.		Article No.
SLG D12 reader	6GT2601-0AB00	Connector for reader	6GT2490-1AA00
With RS232 serial interface and integrated antenna.		IP65 degree of protection, 9-pin Sub-D connector.	
SLG D12S reader	6GT2602-0AB00		
With RS422 serial interface and integrated antenna for connection to SIMATIC S7 / PROFIBUS / PROFINET or Ethernet TCP/IP.		Wide-range power supply	
SLG D12S reader, for single-cable connection	6GT2602-0AB10-0AX0	Primary side: AC 100 ... 240 V, secondary side: 24 V DC, 3 A, with no-load protection and continuous short-circuit protection.	
With RS422 serial interface and integrated antenna. Only one connector for data and voltage supply. Power supply via communication module.		• EU connector version	6GT2898-0AA00
Connector: M12, 8-pin (male)		• UK connector version	6GT2898-0AA10
Accessories		• US connector version	6GT2898-0AA20
Note: All connection options can be found in section 5, "Communication Modules".		Cable for wide-range power supply	6GT2491-1HH50
RS232 connecting cable		24 V DC, PUR, length 5 m.	
Between PC and SLG D12, PUR.			
		24 V connector (M12 socket)	6GT2390-1AB00
5 m	6GT2691-4BH50	for SLG D1x readers	
20 m	6GT2691-4BN20		
		DVD „RFID-Systems Software & Documentation“	6GT2080-2AA20

RFID systems for the HF range

MOBY D readers

SLG D12 / SLG D12S

Dimensional drawings



SLG D12 / SLG D12S reader, basic unit

More information

All current wireless approvals can be found on the Internet at:

<http://www.siemens.com/rfid-approvals>

Overview


Note

Detailed configuration and commissioning data is contained in the "Manual for Configuration, Assembly and Service".

Transmission window

The reader generates an inductive alternating field. The field is at its strongest near the antenna and declines considerably as the distance from the antenna increases. The distribution of the field depends on the structure and geometry of the antennas in the reader and transponder.

A prerequisite for the function of the transponder is a minimum field strength at the transponder that is achieved at a distance S_g from the reader. The picture below shows the transmission window between the transponder and reader:



S_a : Operating distance between transponder and reader

S_g : Limit distance (maximum clear distance between upper surface of antenna and transponder, at which the transmission can still function under normal conditions)

L: Length of a transmission window

SP: Intersection of the axes of symmetry of the transponder

The transmittable quantity of information between reader and transponder depends on:

- the speed at which the transponder passes the antenna ("passing speed")
- Length of the inductive alternating field of the reader, through which the transponder moves ("transmission window").

Communication between reader and transponder

Communication between the reader and transponder is asynchronous.

Data transfer, reader - transponder	
Read	≥ 3.5 ms/byte
Write	≥ 9.5 ms/byte (EEPROM)
Transmission time of ID number	
<ul style="list-style-type: none"> SLG D12S ANT D5, ANT D6, ANT D10 	90 ms (8 bytes at 19.2 Kbit/s)
<ul style="list-style-type: none"> SLG D11S ANT D5 	
<ul style="list-style-type: none"> SLG D12 ANT D5, ANT D6, ANT D10 	60 ms (8 bytes at 38.4 Kbit/s)
<ul style="list-style-type: none"> SLG D11 ANT D5 	

Traversing speed for SLG D1x / ANT Dx (with one transponder in the field)

Reader	SLG D11		SLG D12	SLG D11S		SLG D12S
Antenna	ANT D2	ANT D5		ANT D2	ANT D5	
UID number (8 bytes)	≤ 1.2	≤ 3.5	≤ 2.5	≤ 0.4	≤ 1.0	≤ 0.8
ISO transponder, e.g. MDS D100						
Read (with 4 bytes of user data / 1 block)	≤ 1.2	≤ 1.6	≤ 1.2	≤ 0.4	≤ 3.0	≤ 1.4
Write (with 4 bytes of user data / 1 block)	≤ 0.2	≤ 1.2	≤ 1.0	≤ 0.3	≤ 2.8	≤ 1.2
Read (with 112 bytes of complete user data)	≤ 0.4	≤ 1.4	≤ 0.8	≤ 0.2	≤ 2.2	≤ 1.0
Write (with 112 bytes of complete user data)	≤ 0.1	≤ 0.4	≤ 0.2	≤ 0.1	≤ 0.5	≤ 0.2

All values in the table in m/s.






RFID systems for the HF range

HF antennas

Introduction

Overview

Antennas	Features	Page
ANT 1 	<p>The ANT 1 is a universal flat antenna, also designed for dynamic applications.</p> <p>Usable for readers:</p> <ul style="list-style-type: none"> • RF350R 	2/131
ANT 3 	<p>Due to its slimline, compact design, the ANT 3 antenna can still be precisely positioned even in cramped conditions.</p> <p>Usable for readers:</p> <ul style="list-style-type: none"> • RF250R • RF350R • RF350M 	2/132
ANT 3S 	<p>Due to its slimline, compact design, the ANT 3S antenna can still be precisely positioned even in cramped conditions.</p> <p>The ANT 3S is suitable only for use with transponders MDS D117, MDS D127, MDS D421 and MDS D521.</p> <p>Usable for readers:</p> <ul style="list-style-type: none"> • RF250R • RF350R • RF350M 	2/133
ANT 8 	<p>The ANT 8 antenna is a cylindrical antenna and is intended predominantly for the area of tool identification.</p> <p>The extremely small design of the antenna allows extremely accurate positioning.</p> <p>Usable for readers:</p> <ul style="list-style-type: none"> • RF250R • RF350M 	2/134
ANT 12 	<p>The ANT 12 antenna is a universal round antenna in M12 design for assembly lines with extremely small workpiece holders.</p> <p>Usable for readers:</p> <ul style="list-style-type: none"> • RF250R • RF350R • RF350M 	2/136
ANT 18 	<p>The ANT 18 antenna is a universal round antenna in M18 design for assembly lines with small workpiece holders.</p> <p>Usable for readers:</p> <ul style="list-style-type: none"> • RF250R • RF350R • RF350M 	2/137
ANT 30 	<p>The ANT 30 antenna is a universal round antenna in M30 design for assembly lines with small workpiece holders.</p> <p>Usable for readers:</p> <ul style="list-style-type: none"> • RF250R • RF350R • RF350M 	2/138

Antennen	Merkmale	Page
ANT D1 	<p>The ANT D1 is a universal antenna for the areas of production and logistics that can also be used in dynamic applications.</p> <p>Usable for readers:</p> <ul style="list-style-type: none"> • RF290R 	2/139
ANT D2 	<p>The ANT D2 antenna is specially designed for high speeds with a small antenna size, e.g. in overhead conveyors, assembly lines, production and order picking.</p> <p>The ANT D2 can be mounted directly onto metal surfaces.</p> <p>The antenna is designed for transponders that are directed sideways past the antenna.</p> <p>Usable for readers:</p> <ul style="list-style-type: none"> • SLG D11 / SLG D11S 	2/140
ANT D5 	<p>The ANT D5 is a universal antenna designed for warehouse, logistics and distribution applications.</p> <p>The high degree of protection (IP65) enables the antenna to be used under harsh industrial conditions.</p> <p>The antenna is designed for transponders that are directed sideways past the antenna.</p> <p>Usable for readers:</p> <ul style="list-style-type: none"> • RF290R • SLG D11 / SLG D11S 	2/141
ANT D6 	<p>The ANT D6 is a universal antenna designed for warehouse, logistics and distribution applications.</p> <p>The high degree of protection (IP65) enables the antenna to be used under harsh industrial conditions.</p> <p>Usable for readers:</p> <ul style="list-style-type: none"> • RF290R 	2/143
ANT D10 	<p>The ANT D10 is a universal antenna. It has been designed for warehouse, logistics and distribution applications, and is especially suitable for the clothing industry and laundries. It possesses an advantageous geometry for use with small transponders and a long transmission field.</p> <p>The high degree of protection (IP65) enables the antenna to be used under harsh industrial conditions.</p> <p>Usable for readers:</p> <ul style="list-style-type: none"> • RF290R 	2/145

Overview




The ANT 1 is a universal flat antenna, also designed for dynamic applications.

The dimensions are L x W x H (mm): 75 x 75 x 20.

Selection and ordering data

	Article No.
ANT 1 external antenna for RF350R readers. The antenna cable (3m long) is permanently connected to the antenna.	6GT2398-1CB00

Dimensional drawings



ANT 1 antenna

Technical specifications


Article number	6GT2398-1CB00
Product type designation	ANT 1 antenna
Suitability for operation	RF350R / MOBY E
Wireless frequencies	
Transmission frequency Rated value	13.56 MHz
Electrical data	
Type of electrical connection of the antenna	M8, 4-pin
Design of plug-in connection	male
Mechanical data	
Material	PA 12
Color	Anthracite
Tightening torque of the screw for securing the equipment maximum	2 Nm
Mounting distance	
• relating to metal surfaces recommended minimum	0.02 m
Permitted ambient conditions	
Ambient temperature	
• during operation	-25 ... +70 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
Protection class IP	IP67
Resistance to mechanical stress	no bending or torsion permitted
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Width	75 mm
Height	75 mm
Depth	20 mm
Net weight	225 g
Mounting type	2 screws M5
Cable length of antenna cable	3 m
Standards, specifications, approvals	
Certificate of suitability	CE, FCC, IC, cULus, Ex approval only together with reader 6GT2801-4AB10

RFID systems for the HF range

HF antennas

ANT 3 for RF250R, RF350R and RF350M

Overview



Due to its slimline, compact design, the ANT 3 antenna can still be precisely positioned even in cramped conditions.

The dimensions are L x W x H (mm): 50 x 28 x 10.

Technical specifications


Article number	6GT2398-1CD30-0AX0	6GT2398-1CD40-0AX0
Product type designation	ANT 3 antenna	ANT 3 antenna incl. antenna cable (3 m)
Suitability for operation	RF250R / RF350R / RF350M	RF250R / RF350R
Wireless frequencies		
Transmission frequency Rated value	13.56 MHz	
Electrical data		
Type of electrical connection of the antenna	M8, 4-pin	
Design of plug-in connection	female	male
Mechanical data		
Material	PA6 V0	
Color	black	
Tightening torque of the screw for securing the equipment maximum	1 Nm	
Mounting distance		
• relating to metal surfaces recommended minimum	0 m	
Permitted ambient conditions		
Ambient temperature		
• during operation	-25 ... +70 °C	
• during storage	-40 ... +85 °C	
• during transport	-40 ... +85 °C	
Protection class IP	IP67	
Shock resistance	according to EN 60721-3-7 Class 7M2	
Shock acceleration	500 m/s²	
Vibrational acceleration	200 m/s²	

Article number	6GT2398-1CD30-0AX0	6GT2398-1CD40-0AX0
Design, dimensions and weight		
Width	28 mm	
Height	50 mm	
Depth	10 mm	
Net weight	35 g	160 g
Mounting type	2 x M4 screws	2 x M4 screws
Cable length of antenna cable	-	3 m
Standards, specifications, approvals		
Certificate of suitability	CE, FCC, IC, cULus	
Accessories		
	Antenna cable	Included: 6GT23910-AH30 (antenna cable)

Selection and ordering data

	Article No.
ANT 3 external antenna	
• Without antenna connecting cable For RF250R, RF350R and RF350M readers.	6GT2398-1CD30-0AX0
• With antenna connecting cable included in the scope of delivery; can be connected at both ends (connector M8 straight / M8 angled), length 3 m. For RF250R and RF350R readers.	6GT2398-1CD40-0AX0
Accessories	
Antenna connecting cable for ANT 3 / ANT 3S / ANT 8 For direct connection of ANT 3, ANT 3S and ANT 8 to RF350M	
• Length 0.1 m (figure see page 2/119)	6GT2898-0EA00
• Length 3 m	6GT2391-0AH30

Dimensional drawings



ANT 3 antenna


G_FS10_XX_01140

RFID systems for the HF range

HF antennas

ANT 3S for RF250R, RF350R and RF350M

Overview



Due to its slimline, compact design, the ANT 3S antenna can still be precisely positioned even in cramped conditions.

The ANT 3S is suitable only for use with transponders MDS D117, MDS D127, MDS D421 and MDS D521.

The dimensions of the antenna are L x W x H (mm): 50 x 28 x 10.

Technical specifications


Article number	6GT2398-1CD50-0AX0	6GT2398-1CD60-0AX0
Product type designation	ANT 3S antenna	ANT 3S antenna including antenna cable (3 m)
Suitability for operation	RF250R / RF350R / RF350M	RF250R / RF350R
Wireless frequencies		
Transmission frequency Rated value	13.56 MHz	
Electrical data		
Type of electrical connection of the antenna	M8, 4-pin	
Design of plug-in connection	female	male
Mechanical data		
Material	PA6 V0	
Color	black	
Tightening torque of the screw for securing the equipment maximum	1 Nm	
Mounting distance	0 m	
• relating to metal surfaces recommended minimum		
Permitted ambient conditions		
Ambient temperature		
• during operation	-25 ... +70 °C	
• during storage	-40 ... +85 °C	
• during transport	-40 ... +85 °C	
Protection class IP	IP67	
Shock resistance	according to EN 60721-3-7 Class 7M2	
Shock acceleration	500 m/s²	
Vibrational acceleration	200 m/s²	

Article number	6GT2398-1CD50-0AX0	6GT2398-1CD60-0AX0
Design, dimensions and weight		
Width	28 mm	
Height	50 mm	
Depth	10 mm	
Net weight	35 g	160 g
Mounting type	2 x M4 screws	2 x M4 screws
Cable length of antenna cable	-	3 m
Standards, specifications, approvals		
Certificate of suitability	CE, FCC, IC, cULus	
Accessories	Antenna cable	Included: 6GT23910-AH30 (antenna cable)

Selection and ordering data

	Article No.
ANT 3S external antenna	
• Without antenna connecting cable For RF250R, RF350R and RF350M readers.	6GT2398-1CD50-0AX0
• With antenna connecting cable included in the scope of delivery; can be connected at both ends (connector M8 straight / M8 angled), length 3 m. For RF250R and RF350R readers.	6GT2398-1CD60-0AX0
Accessories	
Antenna connecting cable for ANT 3 / ANT 3S / ANT 8	
For direct connection of ANT 3, ANT 3S and ANT 8 to RF350M (6GT2803-1BA10).	
• Length 0.1 m (figure see page 2/119)	6GT2898-0EA00
• Length 3 m	6GT2391-0AH30

Dimensional drawings




ANT 3S antenna

RFID systems for the HF range


HF antennas

ANT 8 for RF250R and RF350M

Overview



The ANT 8 antenna is a cylindrical antenna and is intended predominantly for the area of tool identification. The extremely small design of the antenna allows extremely accurate positioning. Dimensions Ø x L (mm): M8 x 38.



Technical specifications


Article number	6GT2398-1CF00	6GT2398-1CF10
Product type designation	ANT 8 antenna	ANT 8 antenna incl. antenna cable
Suitability for operation	RF250R / RF350M	RF250R
Wireless frequencies		
Transmission frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Type of electrical connection of the antenna	M8, 4-pin	M8, 4-pin
Design of plug-in connection	female	male
Mechanical data		
Material	Stainless steel V2A	Stainless steel V2A
Color	Silver	Silver
Tightening torque of the screw for securing the equipment maximum	3 Nm	3 Nm
Mounting distance		
• relating to metal surfaces recommended minimum	0 m	0 m
Permitted ambient conditions		
Ambient temperature		
• during operation	-25 ... +70 °C	-25 ... +70 °C
• during storage	-40 ... +85 °C	-40 ... +85 °C
• during transport	-40 ... +85 °C	-40 ... +85 °C
Protection class IP	IP67, front	IP67, front
Shock resistance	according to EN 60721-3-7 Class 7M2	according to EN 60721-3-7 Class 7M2
Shock acceleration	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²
Design, dimensions and weight		
Depth	40 mm	40 mm
Diameter	8 mm	8 mm
Net weight	10 g	140 g
Mounting type	2 stainless steel cscrew nuts M8 x 1.0 (included)	2 stainless steel cscrew nuts M8 x 1.0 (included)
Cable length of antenna cable		3 m
Standards, specifications, approvals		
Certificate of suitability	CE, FCC, IC, cULus	CE, FCC, IC, cULus
Accessories		
Accessories	Antenna cable	Included: 6GT23910-AH30 (antenna cable, length 3 m)

RFID systems for the HF range


HF antennas

ANT 8 for RF250R and RF350M

Selection and ordering data

	Article No.
ANT 8 external antenna <ul style="list-style-type: none"> Without antenna connecting cable For RF250R and RF350M readers. 	6GT2398-1CF00
<ul style="list-style-type: none"> With antenna connecting cable. The antenna connecting cable is included in the scope of delivery of the antenna and can be connected at both ends (M8 connector straight / M8 angled). Length 3 m. For RF250R readers. 	6GT2398-1CF10
Accessories	
Antenna connecting cable for ANT 3 / ANT 3S / ANT 8 For direct connection of ANT 3, ANT 3S and ANT 8 to RF350M (6GT2803-1BA10).	
<ul style="list-style-type: none"> Length 0.1 m 	6GT2898-0EA00
 <ul style="list-style-type: none"> Length 3 m 	6GT2391-0AH30

Dimensional drawings



ANT 8 antenna


G_FS10_XX_01142

RFID systems for the HF range

HF antennas

ANT 12 for RF250R, RF350R and RF350M

Overview



The ANT 12 antenna is a universal round antenna in M12 design for assembly lines with extremely small workpiece holders. Dimensions $\varnothing \times L$ (mm): M12 x 40.

Technical specifications


Article number	6GT2398-1CC00
Product type designation	ANT 12 antenna
Suitability for operation	RF250R / RF350R / RF350M / MOBY E
Wireless frequencies	
Transmission frequency Rated value	13.56 MHz
Electrical data	
Type of electrical connection of the antenna	M8, 4-pin
Design of plug-in connection	male
Mechanical data	
Material	Crastin
Color	Pastel turquoise
Tightening torque of the screw for securing the equipment maximum	3 Nm
Mounting distance	
• relating to metal surfaces recommended minimum	0 m

Article number	6GT2398-1CC00
Product type designation	ANT 12 antenna
Permitted ambient conditions	
Ambient temperature	
• during operation	-25 ... +70 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
Protection class IP	IP67, front
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Depth	40 mm
Diameter	12 mm
Net weight	145 g
Mounting type	2 plastic csrew nuts M12 x 1.0
Cable length of antenna cable	3 m
Standards, specifications, approvals	
Certificate of suitability	CE, FCC, IC, cULus, Ex approval only together with RF350R reader 6GT2801-4AB10

Selection and ordering data

	Article No.
ANT 12 external antenna for readers RF250R, RF350R and RF350M.	6GT2398-1CC00

Dimensional drawings



ANT 12 antenna


G_KT01_XX_00182

RFID systems for the HF range

HF antennas

ANT 18 for RF250R, RF350R and RF350M

Overview



The ANT 18 antenna is a universal round antenna in M18 design for assembly lines with small workpiece holders. Dimensions Ø x L (mm): M18 x 55.

Article number	6GT2398-1CA00
Product type designation	ANT 18 antenna
Permitted ambient conditions	
Ambient temperature	
• during operation	-25 ... +70 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
Protection class IP	IP67, front
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Depth	55 mm
Diameter	18 mm
Net weight	130 g
Mounting type	2 plastic cscrew nuts M18 x 1.0
Cable length of antenna cable	3 m
Standards, specifications, approvals	
Certificate of suitability	CE, FCC, IC, cULus, Ex approval only together with RF350R reader 6GT2801-4AB10


Technical specifications

Article number	6GT2398-1CA00
Product type designation	ANT 18 antenna
Suitability for operation	RF250R / RF350R / RF350M / MOBY E
Wireless frequencies	
Transmission frequency Rated value	13.56 MHz
Electrical data	
Type of electrical connection of the antenna	M8, 4-pin
Design of plug-in connection	male
Mechanical data	
Material	Crastin
Color	Pastel turquoise
Tightening torque of the screw for securing the equipment maximum	3 Nm
Mounting distance	
• relating to metal surfaces recommended minimum	0 m

Selection and ordering data

	Article No.
ANT 18 external antenna for readers RF250R, RF350R and RF350M.	6GT2398-1CA00

Dimensional drawings



ANT 18 antenna

RFID systems for the HF range

HF antennas

ANT 30 for RF250R, RF350R and RF350M

Overview



The ANT 30 antenna is a universal round antenna in M30 design for assembly lines with small workpiece holders. Dimensions Ø x L (mm): M30 x 58

Technical specifications


Article number	6GT2398-1CD00
Product type designation	ANT 30 antenna
Suitability for operation	RF250R / RF350R / RF350M / MOBY E
Wireless frequencies	
Transmission frequency Rated value	13.56 MHz
Electrical data	
Type of electrical connection of the antenna	M8, 4-pin
Design of plug-in connection	male
Mechanical data	
Material	Crastin
Color	Pastel turquoise
Tightening torque of the screw for securing the equipment maximum	3 Nm
Mounting distance	
• relating to metal surfaces recommended minimum	0 m

Article number	6GT2398-1CD00
Product type designation	ANT 30 antenna
Permitted ambient conditions	
Ambient temperature	
• during operation	-25 ... +70 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
Protection class IP	IP67, front
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Depth	58 mm
Diameter	30 mm
Net weight	180 g
Mounting type	2 plastic cscrew nuts M30 x 1.5
Cable length of antenna cable	3 m
Standards, specifications, approvals	
Certificate of suitability	CE, FCC, IC, cULus, Ex approval only together with RF350R reader 6GT2801-4AB10

Selection and ordering data

	Article No.
ANT 30 external antenna for readers RF250R, RF350R and RF350M.	6GT2398-1CD00


Dimensional drawings



ANT 30 antenna

G_KT01_XX_00184

Overview




The ANT D1 is a universal antenna for the areas of production and logistics that can also be used in dynamic applications. The high degree of protection (IP67) means the antenna can also be used under harsh industrial conditions.

Selection and ordering data

	Article No.
ANT D1 antenna For RF290R readers, including antenna cable, PVC, length 3.3 m	6GT2698-5AC00
Accessories	
Cable extension Length 7.2 m	6GT2691-0DH72

Dimensional drawings



ANT D1 antenna

Technical specifications

Article number	6GT2698-5AC00
Product type designation	ANT D1 antenna
Suitability for operation	RF290R
Wireless frequencies	
Transmission frequency Rated value	13.56 MHz
Electrical data	
Type of electrical connection of the antenna	1-pol. TNC-Stecker
Design of plug-in connection	female
Mechanical data	
Material	PA 12
Color	Anthracite
Mounting distance	
• relating to metal surfaces recommended minimum	0.02 m
Permitted ambient conditions	
Ambient temperature	
• during operation	-20 ... +55 °C
• during storage	-25 ... +70 °C
• during transport	-25 ... +70 °C
Protection class IP	IP67
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Width	75 mm
Height	75 mm
Depth	20 mm
Net weight	270 g
Mounting type	2 screws M5
Cable length of antenna cable	3.3 m
Accessories	Antenna cable

RFID systems for the HF range

HF antennas

ANT D2 for SLG D11 / SLG D11S

Overview



The ANT D2 antenna is designed for transponders that are directed sideways past the antenna. This antenna is specially designed for high speeds with a small antenna size, e.g. in overhead conveyors, assembly lines, production and order picking. It can be mounted directly onto metal surfaces.


Technical specifications

Article number	6GT2698-5BB00
Product type designation	ANT D2 antenna
Suitability for operation	MOBY D with SLG D11
Wireless frequencies	
Transmission frequency Rated value	13.56 MHz
Electrical data	
Type of electrical connection of the antenna	1-pol. TNC-Stecker
Design of plug-in connection	female
Mechanical data	
Material	PA 12
Color	Anthracite
Tightening torque of the screw for securing the equipment maximum	2 Nm
Mounting distance	
• relating to metal surfaces recommended minimum	0 m
Permitted ambient conditions	
Ambient temperature	
• during operation	-25 ... +70 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
Protection class IP	IP65
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	500 m/s ²
Vibrational acceleration	100 m/s ²
Design, dimensions and weight	
Width	75 mm
Height	75 mm
Depth	40 mm
Net weight	260 g
Mounting type	2 screws M5, mounting dependent on direction
Cable length of antenna cable	3.3 m
Standards, specifications, approvals	
Certificate of suitability	CE, FCC, IC, cULus

Selection and ordering data

Article No.
ANT D2 antenna
For SLG D11 / SLG D11S basic units, lateral antenna field, incl. PVC antenna cable (length 3.3 m).
6GT2698-5BB00

Dimensional drawings



ANT D2 antenna


G_FS10_XX_00205

RFID systems for the HF range

HF antennas

ANT D5 for RF290R and SLG D11 / D11S

Overview



The ANT D5 is a universal antenna designed for warehouse, logistics and distribution applications. The high degree of protection (IP65) enables the antenna to be used under harsh industrial conditions. The antenna is designed for transponders that are directed sideways past the antenna.

Technical specifications


Article number	6GT2698-5AA10
Product type designation	ANT D5 antenna
Suitability for operation	RF290R, MOBY D with SLG D10, D11
Wireless frequencies	
Transmission frequency Rated value	13.56 MHz
Electrical data	
Type of electrical connection of the antenna	1-pol. TNC-Stecker
Design of plug-in connection	female
Mechanical data	
Material	Aluminum/plastic
Color	black/gray
Mounting distance	
• relating to metal surfaces recommended minimum	0 m
Permitted ambient conditions	
Ambient temperature	
• during operation	-20 ... +55 °C
• during storage	-25 ... +70 °C
• during transport	-25 ... +70 °C
Protection class IP	IP65
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	300 m/s ²
Vibrational acceleration	10 m/s ²

Article number	6GT2698-5AA10
Product type designation	ANT D5 antenna
Design, dimensions and weight	
Width	380 mm
Height	380 mm
Depth	110 mm
Net weight	2 kg
Mounting type	4 screws M6
Cable length of antenna cable	3.3 m
Standards, specifications, approvals	
Certificate of suitability	CE, FCC
Accessories	
Antenna cables 3.3 m, 10 m, extension 7.2 m	

Selection and ordering data


	Article No.
ANT D5 antenna for RF290R readers and SLG D11 / SLG D11S basic units, including antenna cable, PVC, length 3.3 m	6GT2698-5AA10
Accessories	
Antenna switch For connecting several antennas (ANT D5 or ANT D6) to one RF290R reader, IP65, -25 °C to +65 °C	6GT2690-0AC00
	
SIMATIC RF260X antenna multiplexer Antenna multiplexer for RF290R reader when connected via RS232. 6 x antenna outputs (for ANT D5, ANT D6 and ANT D10); IP65; 240 mm x 150 mm x 70 mm; including antenna connecting cable, cable length 0.4 m.	6GT2894-0EA00
	
Accessories for antenna switch and antenna multiplexer	
Antenna connecting cable Between antenna and reader or antenna switch/multiplexer, PVC material.	
• Length 3.3 m	6GT2691-0CH33
• Length 10 m	6GT2691-0CN10
Extension cable For 6GT2691-0CH33, PVC material. Length 7.2 m.	6GT2691-0DH72

Dimensional drawings



ANT D5 antenna

Overview



The ANT D6 is a universal antenna designed for warehouse, logistics and distribution applications. The high degree of protection (IP65) enables the antenna to be used under harsh industrial conditions.

Technical specifications

Article number	6GT2698-5AB00
Product type designation	ANT D6 antenna
Suitability for operation	RF290R, MOBY D with SLG D10
Wireless frequencies	
Transmission frequency Rated value	13.56 MHz
Electrical data	
Type of electrical connection of the antenna	1-pol. TNC-Stecker
Design of plug-in connection	female
Mechanical data	
Material	Aluminum/plastic
Color	gray / black
Mounting distance	
• relating to metal surfaces recommended minimum	0 m
Permitted ambient conditions	
Ambient temperature	
• during operation	-20 ... +55 °C
• during storage	-25 ... +70 °C
• during transport	-25 ... +70 °C
Protection class IP	IP65
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	300 m/s ²
Vibrational acceleration	10 m/s ²
Design, dimensions and weight	
Width	480 mm
Height	580 mm
Depth	110 mm
Net weight	3.3 kg
Mounting type	4 screws M6
Cable length of antenna cable	3.3 m
Standards, specifications, approvals	
Certificate of suitability	CE, FCC, cULus
Accessories	
Accessories	Antenna cables 3.3 m, 10 m, extension 7.2 m

Selection and ordering data


	Article No.
ANT D6 antenna for RF290R readers, including antenna cable, PVC, length 3.3 m	6GT2698-5AB00
Accessories	
Shrouding cover Serves as contact protection for ANT D6	6GT2690-0AD00
Antenna switch For connecting several antennas (ANT D5 or ANT D6) to one RF290R reader, IP65, -25 °C to +65 °C	6GT2690-0AC00
	
SIMATIC RF260X antenna multiplexer Antenna multiplexer for RF290R reader when connected via RS232. 6 x antenna outputs (for ANT D5, ANT D6 and ANT D10); IP65; 240 mm x 150 mm x 70 mm; including antenna connecting cable, cable length 0.4 m.	6GT2894-0EA00
	
Accessories for antenna switch and antenna multiplexer	
Antenna connecting cable Between antenna and reader or antenna switch/multiplexer, PVC material.	
• Length 3.3 m	6GT2691-0CH33
• Length 10 m	6GT2691-0CN10
Extension cable For 6GT2691-0CH33, PVC material. Length 7.2 m.	6GT2691-0DH72

RFID systems for the HF range


HF antennas

ANT D6 for RF290R

Dimensional drawings



ANT D6 antenna

Overview


The ANT D10 is a universal antenna designed for warehouse, logistics and distribution applications. The high degree of protection (IP65) enables the antenna to be used under harsh industrial conditions.

Technical specifications



Article number	6GT2698-5AF00
Product type designation	ANT D10 antenna
Suitability for operation	RF290R, MOBY D with SLG D10
Wireless frequencies	
Transmission frequency Rated value	13.56 MHz
Electrical data	
Type of electrical connection of the antenna	1-pol. TNC-Stecker
Design of plug-in connection	female
Mechanical data	
Material	Aluminum/plastic
Color	Transparent (cover), gray/black (antenna)
Mounting distance	0 m
• relating to metal surfaces recommended minimum	
Permitted ambient conditions	
Ambient temperature	-20 ... +55 °C
• during operation	
• during storage	
• during transport	-25 ... +70 °C
Protection class IP	IP65
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	300 m/s ²
Vibrational acceleration	10 m/s ²
Design, dimensions and weight	
Width	365 mm
Height	1 150 mm
Depth	115 mm
Net weight	10 kg
Mounting type	4 screws M6
Cable length of antenna cable	3.3 m
Standards, specifications, approvals	
Certificate of suitability	CE, FCC, cULus
Accessories	
Accessories	Antenna cables 3.3 m, 10 m, extension 7.2 m

RFID systems for the HF range


HF antennas

ANT D10 for RF290R

Selection and ordering data

	Article No.
ANT D10 antenna For the RF290R reader, incl. antenna cable, PVC, length 3.3 m.	6GT2698-5AF00
Accessories	
Antenna switch For connecting multiple antennas (ANT D5, ANT D6 or ANT D10) to one reader	6GT2690-0AC00
	
SIMATIC RF260X antenna multiplexer Antenna multiplexer for RF290R reader when connected via RS232. 6 x antenna outputs (for ANT D5, ANT D6 and ANT D10); IP65; 240 mm x 150 mm x 70 mm; including antenna connecting cable, cable length 0.4 m	6GT2894-0EA00
	
Accessories for antenna switch and antenna multiplexer	
Antenna connecting cable Between antenna and reader or antenna switch/multiplexer, PVC material.	
<ul style="list-style-type: none"> Length 3.3 m 	6GT2691-0CH33
<ul style="list-style-type: none"> Length 10 m 	6GT2691-0CN10
Extension cable For 6GT2691-0CH33, PVC material. Length 7.2 m.	6GT2691-0DH72

Dimensional drawings



ANT D10 antenna

G_FS10_XX_00238