


SIEMENS

PIPING AND CABLING MANUAL

VersiCharge Ultra 175™

175 kW DC fast charger

usa.siemens.com/versicharge



Index

1. Introduction	3
2. Overview of conduits for VersiCharge 175 kW Fast Charger system	4
3. Conduit requirements	5
4. Cabling requirements	6
4.1 Conduit A – Worldwide 400V 50Hz	6
4.2 Conduit A – USA 480V 60Hz / Canada 480V 60Hz	6
4.3 Conduit A – Canada 600V 60Hz	7
4.4 Conduit B – Worldwide	7
4.5 Conduit B – USA / Canada	8
4.6 Remarks	8
5. Appendix 1: Reference specification for AC link – Worldwide 400VAC	9
6. Appendix 2: Reference specification for AC link – USA / Canada 480VAC	10
7. Appendix 3: Reference specification for AC link – Canada 600VAC	11
8. Appendix 4: Reference specification for DC link – Worldwide	12
9. Appendix 5: Reference specification for DC link – USA / Canada	13
10. Revision record	14

SECTION 1

Introduction

This document defines the cabling and piping of the VersiCharge 175 kW Fast Charger system. It serves as an aid to install the infrastructure required to put the VersiCharge 175 kW Fast Charger system into operation.

This document describes the minimum requirements.



IMPORTANT! All local regulations and requirements **MUST** be met: Prior to installation of the piping and wiring, a professional review of local regulations and requirements must be performed to ensure adherence to all local laws and regulations. As a result, deviation from the requirements of this documentation may be required.

Siemens recommends the use of copper cables.

Ensure correct fit for all cables used for installation.

SECTION 2

Overview of conduits for VersiCharge 175 kW Fast Charger system




Figure 1: Bird's-eye view of the system with underground conduits.

SECTION 3

Conduit requirements


Conduit	Diameter [mm]	From - To	Sub Conduit	Termination above ground [mm]		Quantity	Comments
				From side	To side		
A	125	Power unit – LV Distribution Board	-	Note 1	Note 2	1	
B	110	Power unit – User unit	1 x 25 1 x 32	Note 1	50	1	

Installation notes:

1. Conduits to and from the power unit must end within the foundation cavity to allow ample length for cables to bend and align with the cable glands in the base of the power unit.
2. Required termination height at the Low Voltage (LV) distribution panel must be confirmed with the LV distribution panel supplier.

SECTION 4


Cabling requirements



IMPORTANT! Cabling requirements are specified for USA and Canada. Ensure that the correct cabling requirements for your location are used.

4.1 Conduit A – Worldwide 400V 50Hz

STOP
Important: This section is for all locations **except** USA and Canada.



Ø 125mm

A

All cables are double insulated and must conform with all relevant local regulations

- Marking of AC power cables: “Lyz”, where:
y: Phase number
z: Cable number


For example: L21 (Phaseline 2, cable 1)

Note: The calculations in this table are based on site conditions, as described in the appendices. Ensure that the correct calculations for your site are used.

Cable#	Quantity	Description	Minimum recommended cable type	Marking	Termination above ground [mm]		Usage	Notes
					LV Distribution Board	Power Unit		
1	7	AC cable, 450/750V, min pairs of 70mm ² , different colours for 3 phases and earth	Flexible Copper Conductor, SDI, X-90 Insulated, 70mm ²	1)	TBD	350	3-phase plus earth	Appendix 1: Key specification AC cable
2	1	AC Cable, 0.6 / 1kV, single core earth cable.	Flexible Copper Conductor, SDI, X-90 Insulated, 2.5mm ²	2)	TBD	NA	IMI Earth Reference	Continues unbroken to User Unit

4.2 Conduit A – USA 480V 60Hz / Canada 480V 60Hz

STOP
Important: This section is for USA and Canada.



Ø 125mm

A

All cables are double insulated and must conform with all relevant local regulations

- Marking of AC power cables: “Lyz”, where:
y: Phase number
z: Cable number

For example: L21 (Phaseline 2, cable 1)

Note: The calculations in this table are based on site conditions as described in the appendices. Ensure that the correct calculations for your site are used.

Cable#	Quantity	Description	Minimum recommended cable type	Marking	Termination above ground [mm]		Usage	Notes
					LV Distribution Board	Power Unit		
1	7	AC cable, 0.6/1kV, min pairs of 3/0AWG, different colours for 3 phases and earth	Flexible Copper Conductor, SDI, X-90 Insulated, 3/0AWG	1.	TBD	350	3-phase plus earth	Appendix 2: Key specification AC cable
2	1	AC Cable, 0.6 / 1kV, single core earth cable.	Flexible Copper Conductor, SDI, X-90 Insulated, 14 AWG	2)	TBD	950	IMI Earth Reference	-

4.3 Conduit A – Canada 600V 60Hz

STOP

Important: This section is for Canada only.

Ø 125mm

A

All cables are double insulated and must conform with all relevant local regulations

1. Marking of AC power cables: “Lyz”, where:
y: Phase number
z: Cable number

For example: L21 (Phaseline 2, cable 1)

Note: The calculations in this table are based on site conditions, as described in the appendices. Ensure that the correct calculations for your site are used.

Cable#	Quantity	Description	Minimum recommended cable type	Marking	Termination above ground [mm]		Usage	Notes
					LV Distribution Board	Power Unit		
1	7	AC cable, 0.6/1kV, min pairs of 1/0AWG, different colours for 3 phases and earth	Flexible Copper Conductor, SDI, X-90 Insulated, 1/0AWG	1.	TBD	350	3-phase plus earth	Appendix 3: Key specification AC cable
2	1	AC Cable, 0.6 / 1kV, single core earth cable.	Flexible Copper Conductor, SDI, X-90 Insulated, 14 AWG	2)	TBD	950	IMI Earth Reference	-

4.4 Conduit B – Worldwide

STOP

Important: This section is for all locations **except** USA and Canada.

Ø 110mm


B

All cables are double insulated and must conform with all relevant local regulations


Note: The calculations in this table are based on site conditions, as described in the appendices. Ensure that the correct calculations for your site are used.

Cable#	Quantity	Description	Minimum recommended cable type	Marking	Termination above ground [mm]		Usage	Notes
					User Unit	Power Unit		
1	2	DC Cable class X-90 (2 DC cables), min 70mm ² , different colours for positive, negative and earth	Flexible Copper Conductor, SDI, V-90 Insulated, 70mm ²	-	550	1800		Appendix 4: Key specification DC cable
2	1	1 earth conductor, min 35mm ²	Flexible Copper Conductor, SDI, V-90 Insulated, 35mm ²	-	250	450	Protective Earth	
3	1	Copper flex cable 2 cores, min 0.5mm ²	Flexible Copper, V-70 insulated, 2 core 2x0.5mm ²	-	450	950	Safety Loop	Sub conduit 1
4	1	Copper flex cable 3 cores (2C+E), min 2.5mm ²	Flexible Copper, V-70 insulated, 3 core (2C+E), 3x2.5mm ²	-	500	950	Single phase supply and IMI Earth Reference	Sub conduit 1
5	1	Ethernet cable, shielded fully twisted pair	Cat 6a sftp	-	500	1550		Sub conduit 2
6	1	Fibre Optic Cable	OM3 Multi Mode 2 Core	-	500	1550	Fibre is optional	

4.5 Conduit B – USA / Canada



Important: This section is for USA and Canada.



All cables are double insulated and must conform with all relevant local regulations

Note: The calculations in this table are based on site conditions, as described in the appendices. Ensure that the correct calculations for your site are used.

Cable#	Quantity	Description	Minimum recommended cable type	Marking	Termination above ground [mm]		Usage	Notes
					User Unit	Power Unit		
1	2	DC Cable class X-90 (2 DC cables), min 2/0AWG, different colours for positive, negative and earth	Flexible Copper Conductor, SDI, V-90 Insulated, 2/0AWG	-	550	1800		Appendix 5: Key specification DC cable
2	1	1 earth conductor, min 1AWG	Flexible Copper Conductor, SDI, V-90 Insulated, 1AWG	-	250	450	Protective Earth	
3	1	Copper flex cable 2 cores, min 0.5mm ²	Flexible Copper, V-70 insulated, 2 core 2x20AWG	-	450	950	Safety Loop	Sub conduit 1
4	1	Copper flex cable 3 cores (2C+E), min 2.5mm ²	Flexible Copper, V-70 insulated, 3 core (2C+E), 3x14AWG	-	500	950	Single phase supply and IMI Earth Reference	Sub conduit 1
5	1	Ethernet cable, shielded fully twisted pair	Cat 6a sftp	-	500	1550		Sub conduit 2
6	1	Fibre Optic Cable	OM3 Multi Mode 2 Core	-	500	1550	Fibre is optional	Sub conduit 2

4.6 Remarks

The cross section (in mm²) of all conductors in the site is location specific according to relevant local laws and regulations. Verification against these regulations should be performed by the customer prior to installation.

SECTION 5

Appendix 1: Reference specification for AC link

– Worldwide 400VAC

**Important:**

- This section is for all locations **except** USA and Canada.
- The calculations in this document are based on site conditions that match the values in the following table. Ensure that the correct calculations for your site are used.

	Value	Units	Comments
Voltage (Line-to-Line) (nominal)	400	V _{RMS}	
Voltage (line to neutral) (nominal)	230	V _{RMS}	
Rated power	185	kVA	
Power factor	0.99		
Maximum line current at low line level	297	A	Low line level 400V -10%
Over Current Protection Device Rating	320	A	
Soil thermal resistivity	1.0	K.m/W	
Soil temperature	20	C	
Depth of laying	1.0	m	
Conductor material	Copper		
Conductor insulation	XLPE / EPR		
Conductor temperature (maximum)	90	C	
Conductor temperature (minimum)	-40	C	
Minimum Active Conductor CSA ¹	2 x 70	mm ²	
Minimum Earth Conductor CSA	1 x 70	mm ²	
Current carrying capacity	328	A	
Maximum diameter	20	mm	
Maximum bend radius	4 x Diameter		

¹⁾ Buried cable sizing as per IEC 60364 for configuration D1 – buried conduit

SECTION 6

Appendix 2: Reference specification for AC link – USA / Canada 480VAC



Important:

- This section is for USA and Canada.
- The calculations in this document are based on site conditions that match the values in the following table. Ensure that the correct calculations for your site are used.

	Value	Units	Comments
Voltage (Line-to-Line) (nominal)	480	V _{RMS}	
Voltage (line to neutral) (nominal)	277	V _{RMS}	
Rated power	185	kVA	
Power factor	0.99		
Maximum current at low line level	248	A	Low line level 480V -10%
Over Current Protection Device Rating	320	A	Based on 125% rule
Soil thermal resistivity	0.9	K.m/W	
Soil temperature	20	C	
Depth of laying	1.0	m	
Conductor material	Copper		
Conductor insulation	XLPE / EPR		
Conductor temperature (maximum)	90	C	
Conductor temperature (minimum)	-40	C	
Minimum Active Conductor CSA ¹	2 x 3/0	AWG	
Minimum Earth Conductor CSA	1 x 3/0	AWG	
Current carrying capacity	347	A	
Maximum diameter	20	mm	
Maximum bend radius	4 x Diameter		

¹⁾ Buried cable sizing as per NEC – buried conduit

SECTION 7

Appendix 3: Reference specification for AC link – Canada 600VAC

**Important:**

- This section is for Canada **only**.
- The calculations in this document are based on site conditions that match the values in the following table. Ensure that the correct calculations for your site are used.

	Value	Units	Comments
Voltage (Line-to-Line) (nominal)	600	V _{RMS}	
Voltage (line to neutral) (nominal)	347	V _{RMS}	
Rated power	185	kVA	
Power factor	0.99		
Maximum current at low line level	198	A	Low line level 480V -10%
Over Current Protection Device Rating	250	A	Based on 125% rule
Soil thermal resistivity	0.9	K.m/W	
Soil temperature	20	C	
Depth of laying	1.0	m	
Conductor material	Copper		
Conductor insulation	XLPE / EPR		
Conductor temperature (maximum)	90	C	
Conductor temperature (minimum)	-40	C	
Minimum Active Conductor CSA ¹	2 x 1/0	AWG	
Minimum Earth Conductor CSA	1 x 1/0	AWG	
Current carrying capacity	266	A	
Maximum diameter	20	mm	
Maximum bend radius	4 x Diameter		

¹⁾ Buried cable sizing as per NEC – buried conduit

SECTION 8

Appendix 4: Reference specification for DC link – Worldwide

**Important:**

- This section is for all locations **except** USA and Canada.
- The calculations in this document are based on site conditions that match the values in the following table. Ensure that the correct calculations for your site are used.

	Value	Units	Comments
Voltage (nominal)	950	V _{DC}	
Rated power	180	kW	
Maximum current	189	A	
Soil thermal resistivity	1.0	K.m/W	
Soil temperature	20	C	
Depth of laying	1.0	m	
Conductor material	Copper		
Conductor insulation	XLPE / EPR		
Conductor temperature (maximum)	90	C	
Conductor temperature (minimum)	-40	C	
Minimum Active Conductor CSA ¹	1 x 70	mm ²	
Minimum Earth Conductor CSA	1 x 35	mm ²	
Current carrying capacity	232	A	
Maximum diameter	20	mm	
Maximum bend radius	4 x Diameter		

¹⁾ Buried cable sizing as per IEC 60364 table B.52.3 for configuration D1 – buried conduit

SECTION 9

Appendix 5: Reference specification for DC link – USA / Canada

**Important:**

- This section is for USA and Canada.
- The calculations in this document are based on site conditions that match the values in the following table. Ensure that the correct calculations for your site are used.

	Value	Units	Comments
Voltage (nominal)	950	V _{DC}	
Rated power	180	kW	
Maximum current	189	A	
Soil thermal resistivity	0.9	K.m/W	
Soil temperature	20	C	
Depth of laying	1.0	m	
Conductor material	Copper		
Conductor insulation	XLPE / EPR		
Conductor temperature (maximum)	90	C	
Conductor temperature (minimum)	-40	C	
Minimum Active Conductor CSA ¹	1 x 2/0	AWG	
Minimum Earth Conductor CSA	1 x 1	AWG	
Current carrying capacity	190	A	
Maximum diameter	20	mm	
Maximum bend radius	4 x Diameter		

¹⁾ Buried cable sizing as per NEC – buried conduit

SECTION 10

Revision record

Rev	Date	TC #	Change
1	4 February 2020	TC-1409	Document release (J. Pierce, S. Taylor)

Legal Manufacturer

Siemens Industry, Inc.
3617 Parkway Ln.
Peachtree Corners, GA 30092
United States of America

Telephone: +1 (800) 333-7421
helpline.sii@siemens.com
www.usa.siemens.com/versicharge
Engineering No. P3REC000100058
Article No. SIDS-T40110-00-4AUS

This document contains a general description of available technical options only, and its effectiveness will be subject to specific variables including field conditions and project parameters. Siemens does not make representations, warranties, or assurances as to the accuracy or completeness of the content contained herein. Siemens reserves the right to modify the technology and product specifications in its sole discretion without advance notice.