

1 IF IN DOUBT ASK
DO NOT SCALE


EU EXPORT CONTROLS

ECCN: N

AL: N

This document is not Export Controlled unless sending to Critical Countries.

| Sr. no. | Parts |
|---------|--------------------------------------|
| 1 | Transparent cover with gasket inside |
| 2 | Relay Mounting Screw Kit |



NOTE:
THE $\phi 4.5$ HOLES TO BE CLEARANCE AND RELAYS MOUNTED USING
M4x20 ROUND SS STUDS (4 nos.), M4 KNURLED SCREWS (4 nos.),
LOCK WASHERS(4 nos.) and NUT (4 nos.)

MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.

Machine where marked ✓

For explanation of dimensions, tolerances, notes etc. see B.S.308.

Limit on untoleranced unmachined-dimensions \pm _____

Limits on untoleranced machined-dimensions, to B.S.4500;
i.e. up to 6 \pm 0.1; over 30 to 120 \pm 0.3; over 315 \pm 0.8;

over 6 to 30 \pm 0.2; over 120 to 315 \pm 0.5;

General unmachined angular tolerance \pm _____

Finish:

Treatment:

Title:

7SR45 V3 WITH TRANSPARENT COVER ASSEMBLY

Copyright ©

Siemens Protection Devices Ltd. Hebburn

First used on:

Similar Articles:

Supersedes:

Original Scale.

: NTS

Drng. No.

2995X10026

| ISSUE | DATE | CHANGE NOTED |
|-------|----------|--------------|
| 1A | 01/11/19 | |

**NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED**

| | | | | | | | | | | | | | | | | |
|-------|------|---------|-----------|----------|------|------|----------|----|-----|-----|--------------|----|-----|----|-----|----|
| DRAWN | AMAR | CHECKED | VENKATESH | APPROVED | MANI | DATE | 01/11/19 | IE | OPS | PCP | Purch. Spec. | TQ | EAC | CE | STD | A3 |
|-------|------|---------|-----------|----------|------|------|----------|----|-----|-----|--------------|----|-----|----|-----|----|