

Compliance Certificate

7SG16 - Ohmega 406

Apparatus: Ohmega 406 is a 4 zone distance relay. In addition to the impedance functions it has the following features, High Set O/C, DEF (Dual), UV/OV, 1 & 3 pole Auto Reclose, PSB, VTS and SOTF. Permissive U/R 1 & 3 pole tripping. Permissive over-reach and blocking scheme.


Manufacturer: Siemens Protection Devices Ltd, Hebburn, Tyne & Wear.

Tested by: Has been Type Tested in accordance with the relevant clauses of British and International Standards BS142 and IEC255 (series).

15 July 2009



Alan Manson
Manager
R&D



Ken Short
Manager
Quality

Energy Distribution

Answers for energy.

SIEMENS