



SIEMENS

Ingenuity for life



Pedestrian signals

Advanced functionality with modern good looks

siemens.co.uk/traffic

The Siemens Helios range of pedestrian signals offers a superior level of functionality and modern good looks. Manufactured in high precision die cast aluminium, the range incorporates a complete set of nearside and wait style signals utilising both standard and narrow field of view optics.

Maximum user choice is offered with both LED optics and traditional 48V incandescent lamps being available on selected units across the range. Additionally, both two part and combined nearside units are available, ensuring that whatever the style preference, this can be met from within the product range.

Puffin style signals

Typically at Puffin style crossing sites, at least two nearside displays and their associated demand units are installed. The signals are mounted upstream of passing traffic, making them visible solely to pedestrians, who view them by looking in the direction of the oncoming traffic.

Crossing layouts may sometimes need to be more sophisticated, particularly at crossings which are subject to heavy use. The separate nature of the Siemens nearside display and demand unit allows additional instances of either to be installed when required. For example, when additional demand units are necessary these can easily be located on downstream poles.

If improved visibility of the signals is needed, additional display units may be installed above those located in their normal position, to act as repeaters.

Where a more integrated aesthetic appearance is desired, a combined version of the nearside signal is also available, encapsulating both demand and display elements within a single attractive enclosure.

Excellent optical performance

Advanced optical design provides exceptional visibility of the signals in all lighting conditions. In particular, the enhanced illumination on the demand unit offers an extremely clear and positive indication to the user, once the demand button has been activated.

For sites where signal 'see-through' is a particular problem, 'narrow field of view' versions of the Puffin, Toucan and Equestrian display units are available.

- Complete range of pedestrian signals
 - Puffin, Toucan and Equestrian nearside units
 - traditional wait indicators
- Choice of illumination type
 - long-life, low power consumption LED light sources
 - traditional incandescent lamps
- Support for ELV and Plus+ lamp drive systems
- Excellent all weather visibility
- Regular and 'narrow field of view' options
- Lamp monitorable by Siemens controllers
- Optional touch-sensitive vandal-resistant demand button
- Available with audible and tactile units
- Registered to TOPAS 2511

Pelican style signals

For use in traditional Pelican and intersection pedestrian applications, wait indicators are available which match the styling of the nearside units.

Both 48V incandescent and LED illuminated options are available. The LED versions offer long-life and reduce power consumption eliminating the need for regular lamp changing and increasing the service interval at the site.

Vandal-resistant, touch-sensitive demand button

All units are fitted as standard with a robust mechanical switch, designed to give a long and reliable service life.

Where sites are particularly prone to vandal damage all unit styles may be fitted with a reliable touch sensitive button that has no moving parts.

Lamp monitoring compatibility

All incandescent units are able to be lamp monitored directly by any Siemens intersection or pedestrian controller that offers integral lamp monitoring facilities.

LED based units are able to be lamp monitored by both the ST9XX ELV and the ST750 ELV ensuring that failures of cabling or pole top connections can be detected automatically, allowing the installation to be returned to full operation with the minimum of delay.

Plus+ versions are all directly monitored by the Plus+ system.

Technical specification

Construction (all types)

Casting: Precision cast aluminum alloy
Signal screen: UV resistant polycarbonate

Environmental (all types)

Operating temperature: -15°C to +60°C
Water penetration: IPX5

Supply Voltage (all types)

Bright operation: 48V AC/DC*
Dim operation: 32V AC or 27.5

*Correct operational voltage is selected automatically when driven by the ST750 ELV or the ST9XX ELV. For Plus+ versions power is derived directly from the Plus+ network.

Two part nearside display unit

Dimensions: 360mm (H) x 225mm (W) x 130mm (D) Weight: 4.8Kg

Optical performance:

- Red symbol (typical): 29cd
- Green symbol (typical): 34cd (Reduces to approximately 20% intensity when dimmed)
- Viewing angle (NFV version): +/-25° (approx)

Typical power consumption (bright state): 16 Watts

Two part nearside demand unit

Dimensions: 180mm (H) x 225mm (W) x 130mm (D)
Weight: 3.2Kg

Optical performance:

- Demand accept LED ring: 24cd (Reduces to approximately 20% intensity when dimmed)

Typical power consumption (bright state): 6 Watts

Single part nearside units

Dimensions: 448mm (H) x 225mm (W) x 133mm (D)
Weight: 6.5Kg

Optical performance:

- Red symbol (typical): 29cd
- Green symbol (typical): 34cd
- Demand accept LED ring: 24cd
- (Reduces to approximately 20% intensity when dimmed)
- Viewing angle (NFV version): +/-25° (approx)

Typical power consumption (bright state): 16 Watts (Display)

Typical power consumption (bright state): 6 Watts (Demand ring)

Wait indicators

Dimensions: 360mm (H) x 225mm (W) x 130mm (D)

Weight: 4.8 Kg

Typical power consumption (at 48V):

- LED version 6 Watts
- Incandescent version 40 Watts



Siemens Mobility Limited

Sopers Lane, Poole, Dorset, BH17 7ER

Tel: +44 (0) 1202 782000

Email: sales.stc@siemens.com

siemens.co.uk/traffic

© Siemens 2020. All rights reserved.

This publication is issued to provide outline information only, which (unless agreed by the Company in writing) may not be used, applied or reproduced for any purpose or form part of any order or contract or be regarded as a representation relating to the products or service concerned. The Company reserves the right to alter without notice this specification, design, price or conditions of supply of any product or service.