

SHUNT TRIP FLEXIBLE 110-127 V AC 50/60 HZ ACCESSORY  
FOR 3VA4/5/6



Model	
Product brand name	SETRON
Product designation	Accessories
Design of the product	Auxiliary release
accessories	Auxiliary release
General technical data	
Degree of pollution	3
Overvoltage category	III
Apparent power consumption / maximum	810 V·A
Voltage	
Tension assignée d'isolement Ui	690 V
Surge voltage resistance	4 kV
Mechanical Design	
Height	65.1 mm
Width	21.7 mm
Number of slots	3
Depth	31.2 mm
Net weight	91 g

Tightening torque / with screw-type terminals / minimum	0.4 N·m
Tightening torque / with screw-type terminals / maximum	0.5 N·m






### Connections according IEC

Wire stripping length	10 mm
Connectable conductor cross-section	
• minimum	0.5 mm <sup>2</sup>
• maximum	1.5 mm <sup>2</sup>
AWG number / as coded connectable conductor cross section / for auxiliary contacts	
• minimum	20
• maximum	16

### Connections according UL

Wire stripping length [in]	0.4 in
Tightening torque [lbf·in] / with screw-type terminals / minimum	3.5 lbf·in
Tightening torque [lbf·in] / with screw-type terminals / maximum	4.4 lbf·in

### Certificates

General Product Approval	EMC	Declaration of Conformity	other
 CSA	 UL		 RCM
		 EG-Konf.	<a href="#">Miscellaneous</a>

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9978-0BA22>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9978-0BA22>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**



[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA9978-0BA22](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9978-0BA22)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



**last modified:**

11/17/2017