

# SIEMENS

## Rainproof Combination Metering

Catalog Number

**MC0606L1200RA**

Series

Enclosure

**Type 3R**

Panelboard Rating:  
200 Amps Max.  
120/240 V AC 1 Phase, 3 Wire  
208Y/120 V AC 1 Phase, 3 Wire  
(Derived from 3 phase - 4 wire system)  
Meter Socket Rating:  
200 Amps. Continuous

### Suitable For Use Only As Service Equipment

Install not more than 6 main  
disconnect means.

All circuit breakers are service disconnects.

Line Terminals A and B have wire connectors  
installed for overhead and underground  
service.

### Use Copper or Aluminum Wire

Line Terminals A, B, and N  
Suitable for 60°/75° C Conductors.  
Wire Size #4 AWG-250 kcmil  
Torque Terminals to 250 Lb.-Ins.

Neutral Bar Wire Size  
Suitable for 60°/75° C Conductors. Wire Size  
Small Terminals:  
14-10 AWG 20 Lb.-Ins.  
8 AWG 25 Lb.-Ins.  
6 AWG 35 Lb.-Ins.  
Large Terminals:  
14-10 AWG 35 Lb.-Ins.  
8 AWG 40 Lb.-Ins.  
6 AWG 45 Lb.-Ins.  
4-1/0 AWG 45 Lb.-Ins.

Refer to Branch Breaker markings for  
wire size, rating and torque. Branch  
Breaker Terminals Suitable for 60°/75° C  
Conductors. Left side suitable for 60A  
breakers with CU wire, 50A breakers  
with AL wire, right side suitable for 150A  
breakers with CU wire and accessory  
kit: ECLK2.

For installation by a qualified person in accordance with all local electrical codes and/or the National  
Electrical Code®.

© The National Electrical Code is a registered trademark of the National Fire Protection Association.

© 2005 COPYRIGHT SIEMENS ENERGY & AUTOMATION, INC. ALPHARETTA, GA. U.S.A.

All unused neutral branch terminals can be  
used as equipment grounding wire terminals.  
These terminals can be identified by the green  
or bare grounding wire and will accept the  
wire sizes listed under "Equipment Ground  
Bar Terminals".

#### Accessories:

Filler Plate Cat. No. QF3 or ECQF3

2/0-#4 wire range lug kit: ECLK2

5th Jaw Assembly: EC5J2

Mechanical Breaker Interlock: ECQML12

Meter Socket Jumper: ECJS

Equipment Grounding Bars Cat. No. ECGB20

Tighten Equipment Ground Bar Terminals to  
the torque shown in Neutral bar table for the  
wire installed.

Ground Bar Wire Size

Copper

One #14-#4 AWG or Two or Three #14-#10 AWG

Aluminum

One #12-#4 AWG or Two or Three #12-#10 AWG

If a RX Hub is required on Top End Wall, the  
catalog nos. listed below may be used on this  
enclosure.

1 1/4" .....	EC38597
1 1/2" .....	EC38598
2" .....	EC38599
2 1/2" .....	EC38600

If a HC Hub is required on the bottom end wall,  
the catalog nos. listed below may be used on this  
enclosure.


2" .....	ECHC200
2-1/2 .....	ECHC250
3 .....	ECHC300

#### General Information:

Remove twistouts from trim only where breakers  
will be installed. All openings must be filled with  
breakers or filler plates.

Circuit breaker overload trip position is indicated  
by handle position midway between ON and  
OFF. To reset, move handle to OFF position  
then turn ON.

## Use Two Pole Breakers Only



**Short Circuit Current Rating** (Wattour Meter not included in short circuit current rating) This panelboard has a maximum short circuit rating of 10,000 RMS symmetrical amperes, 240 volts maximum. Any circuit breaker installed, replaced or added in this panelboard must be manufactured by Siemens and must be of the types listed below.

BRANCH BREAKER	THE MAXIMUM SHORT CIRCUIT CURRENT RATING IN RMS SYMMETRICAL AMPERES, 120/240~ IS:
QP, QPH, QPHF, HGP, QT, QAF, QAFH, QPF, QN	10,000

### WARNING:

This equipment has been designed for use only with circuit breakers listed above. Use of other circuit breakers in this equipment could result in personal injury or property damage and will void the warranty.

### IMPORTANT:

Do not allow petroleum based (hydrocarbon) sprays, chemicals, solvents or any paint to contact interior components. Petroleum based chemicals can cause degradation of electrical insulating materials.

© 2005 COPYRIGHT SIEMENS ENERGY & AUTOMATION, INC. ALPHARETTA, GA. U.S.A.

DH1

49310871