



PRICE GUIDE


# 2021 Siemens Rail Infrastructure

Valid March 1st, 2021–February 28th, 2022

**SIEMENS**

# Siemens Rail Infrastructure office locations in the United States

Siemens Rail Infrastructure has office locations throughout the United States to support all customer needs.



# Contact us

## **Freight Products**

Phone: 1 (800) 793-7233 Option 2

Fax: 1 (502) 371-0701

Ordering Email: [ra.csorders.ic@siemens.com](mailto:ra.csorders.ic@siemens.com)

Repair Email: [ra.csrepairorders.ic@siemens.com](mailto:ra.csrepairorders.ic@siemens.com)

Estimating Email: [ra.estimateding.ic@siemens.com](mailto:ra.estimateding.ic@siemens.com)

## **Carborne Productions**

Phone: 1 (800) 793-7233 Option 2

Fax: 1 (855) 434-8436

Customer Service Email: [carbsys-custserv.mobility@siemens.com](mailto:carbsys-custserv.mobility@siemens.com)

## **Technical Assistance**

Phone: 1 (800) 793 7233 Option 1

Email: [RA.RailTechSupport.ic@siemens.com](mailto:RA.RailTechSupport.ic@siemens.com)

## **We value your feedback!**

Please send any questions, comments, or concerns to [RA.CustomerFeedback.lc@siemens.com](mailto:RA.CustomerFeedback.lc@siemens.com)

## **Trademarks**

All product designations may be registered trademarks or product names of Siemens AG or other supplying companies.

Third parties using these trademarks or product names for their own purposes may infringe upon the rights of the trademark owners.

Further information about rail automation products: [usa.siemens.com/mobility](http://usa.siemens.com/mobility)

*Revision date:*

*April 2, 2021*

# Standard terms and conditions of sale

## Siemens Mobility, Inc. Products July 1, 2016 (Rev. 1.1)

**1. Applicable Terms.** This Agreement governs the sale of equipment, components, parts, and materials provided by Siemens ("Products").

Any applicable addenda, these terms, Siemens proposal, price quote, purchase order, or acknowledgement issued by Siemens form the parties' final agreement ("Agreement"). In the event of a conflict between these documents, precedence shall apply in accordance with the order listed in the previous sentence.

Siemens' proposal, offer or acceptance is conditioned on Buyer's acceptance of this Agreement. Any additional or conflicting terms in Buyer's request for proposal, specifications, purchase order or any other written or oral communication are not binding on Siemens unless separately signed by Siemens.

Siemens' failure to object to Buyer's additional or conflicting terms does not operate as a waiver of any terms contained in this Agreement.

**2. Pricing & Payment.** Prices and payment terms are: (i) as stated in Siemens' proposal, or if none are stated; (ii) Siemens' standard prices in effect when Siemens receives Buyer's purchase order; or if neither (i) or (ii) apply, then Siemens' standard prices in effect when the Products ship.

(a) Payment. Unless stated in Siemens' proposal, all payments are due net thirty (30) days from the invoice date in United States Dollars.

(b) Credit Approval. All orders are subject to credit approval by Siemens. Siemens may modify, suspend or withdraw the credit amount or payment terms at any time. If there is doubt as to Buyer's financial condition, Siemens may withhold manufacturing or shipment, require cash payments, or require other satisfactory security. Siemens may recover shipped Products from the carrier pending such assurances.

(c) Installment Shipment. Where Products are delivered in shipments or only part of a shipment fails to comply with this Agreement, the Buyer may only reject the non-compliant portion. Buyer will separately pay for each shipment. If Siemens holds or stores Products for Buyer, it shall do so at Buyer's sole risk and expense.

(d) Taxes, Shipping, Packing, Handling. Unless stated in writing by Siemens, Siemens' prices exclude charges for freight, unloading, storage, insurance, taxes, excises, fees, duties or other government charges related to the Products. Buyer will pay these amounts or reimburse Siemens. If Buyer claims a tax or other exemption or direct payment permit, Buyer will provide a valid exemption certificate or permit and indemnify, defend and hold Siemens harmless from any taxes, costs and penalties arising from same. Siemens' prices include the costs of its standard domestic packing only. Any packing deviation, including

U.S. Government sealed packing, will be charged to Buyer. Increases, changes (including in application), adjustments or surcharges which may be incurred are for Buyer's account.

(e) Late Payments. Late payments shall bear interest at an annual percentage rate of twelve percent (12%) or the highest rate allowed by law, whichever is lower.

(f) Disputed Invoice. If Buyer disputes all or any portion of an invoice, it must first deliver written notice to Siemens of the disputed amount and the basis for the dispute within twenty-one (21) days of receiving the invoice. Failure of Buyer to timely notify Siemens of any dispute constitutes a waiver of Buyer's claim. If Buyer only disputes a portion of the invoice, Buyer must pay the undisputed portion in accordance with Article 2(a). Upon resolution of the dispute, Buyer must pay the invoice or the remainder of the invoice, plus any accrued interest on the late payment.

(g) Suspension/Termination Right. Siemens may suspend work if an undisputed invoice is more than thirty (30) days past due. Siemens may terminate this Agreement if an undisputed invoice is more than sixty (60) days past due. Unless prohibited by law, Siemens may also terminate this Agreement immediately in the event of a material adverse change in Buyer's financial condition including, but not limited to, bankruptcy, insolvency, liquidation or similar financial condition.

**3. Delivery; Title; Risk of Loss.** Products will be delivered F.O.B. Siemens point of shipment with title and risk of loss or damage passing to Buyer at that point. Buyer is responsible for all transportation, insurance and related expenses. The related expenses shall include any taxes, duties or documentation fees. Siemens may make partial shipments. Any shipping, delivery and installation dates are estimated dates only. Siemens is not liable for any loss or expense incurred by Buyer or Buyer's customers if Siemens fails to meet its delivery schedule.

**4. Deferment and Cancellation.** Buyer has no right to defer shipment but may cancel this Agreement on thirty (30) days written notice if Siemens has not already performed. If Buyer cancels this Agreement, it shall pay all cancellation charges including, without limitation:

(i) the full price for any finished Product;

(ii) for partially completed product, the portion of the price determined to be due by Siemens based on its percentage of completion of the Product;

(iii) reasonable overhead and profit; and (iv) any payments due subcontractors and/or suppliers for any materials, components or products ordered which cannot be cancelled, refunded, or redirected for other beneficial use.

**5. Transportation and Storage.** (a) When Products are ready for shipment, Siemens will: (i) inform Buyer, and Buyer will then promptly give shipping instructions to Siemens; (ii) determine the method of transportation and shipment routing; and (iii) ship the Products with freight prepaid by normal transportation. If Buyer fails to provide timely shipping instructions, Siemens will ship the Products by normal transportation means to Buyer or to a storage location selected by Siemens. Buyer will pay or reimburse any excess transportation charges for special or expedited transportation.

(b) If Products are placed into storage, delivery occurs and risk of loss transfers to Buyer when the Products are placed on the carrier for shipment to the storage location. If the Products are to be stored in the facility where manufactured, delivery occurs and risk of loss transfers to Buyer when placed in the storage location. Buyer will pay all Siemens' storage expenses, including but not limited to, preparation for and placement into storage, handling, freight, storage, inspection, preservation, maintenance, taxes and insurance, upon receipt of an invoice(s) from Siemens. When conditions permit and upon payment to Siemens of all amounts due, Buyer must arrange, at its expense, to remove the Products from storage. Buyer bears the risk of loss, damage or destruction to Products in storage.

**6. Force Majeure / Delays.** If Siemens' performance is delayed by any cause beyond its reasonable control (regardless of whether the cause was foreseeable), including without limitation acts of God, strikes, labor shortage or disturbance, fire, accident, war or civil disturbance, delays of carriers, cyber-attacks, terrorist attacks, failure of normal sources of supply, or acts or inaction of government, Siemens' time of performance will be extended by a period equal to the length of the delay plus any consequences of the delay. Siemens will notify Buyer within a reasonable time after becoming aware of any such delay.

**7. Buyer's Requirements.** Siemens' performance is contingent upon Buyer timely fulfilling all of its obligations under this Agreement. These obligations include the Buyer supplying all documents and approvals needed for Siemens to perform, including but not limited to technical information and data, drawing and document approvals, and necessary commercial documentation. Siemens may request a change order for an equitable adjustment in prices and times for performance, as well as for any additional costs or any delay resulting from the failure of Buyer or Buyer's contractors, successors or assigns to meet these obligations.

**8. Indemnity.** Siemens and Buyer (each as an "Indemnitor") shall indemnify the other ("Indemnatee") from and against all third party claims alleging bodily injury, death or damage to a third party's tangible property, but only to the extent caused by the Indemnitor's negligent acts or omissions. If the injury or damage is caused by the parties' joint or contributory negligence, the loss and/or expenses shall be borne by each party in proportion to its degree of fault. No part of the Product(s) or Buyer's site is considered third party property. Indemnatee shall provide the Indemnitor with prompt written notice of any third party claims covered by this Article. Indemnitor has the unrestricted right to select and hire counsel and the exclusive right to conduct the legal defense and/or settle the claim on the Indemnatee's behalf. The Indemnatee shall not make any admission(s) which might be prejudicial to the Indemnitor and shall not enter into a settlement without the express permission of the Indemnitor.

**9. Warranties.** (a) Warranties. Siemens warrants that: (i) each Product is free from defects in material and workmanship; (ii) each Product materially conforms to Siemens' specifications that are attached to, or expressly incorporated into this Agreement; and (iii) at the time of delivery, Siemens has title to each Product free and clear of liens and encumbrances (collectively, the "Warranties"). The Warranties do not apply to software furnished by Siemens. The sole and exclusive warranties for any software are set forth in the applicable Software License/Warranty Addendum.

(b) Conditions to the Warranties. The Warranties are conditioned on: (i) no repairs, modifications or alterations being made to the Product other than by Siemens or its authorized representatives; (ii) Buyer handling, using, storing, installing, operating and maintaining the Product in compliance with any parameters or instructions in any specifications attached to, or incorporated into this Agreement; (iii) compliance with all generally accepted industry standards; (iv) Buyer discontinuing use of the Product after it has, or should have had, knowledge of any defect; (v) Buyer providing prompt written notice of any warranty claims within the warranty period described below; (vi) at Siemens' discretion, Buyer either removing and shipping the Product or non-conforming part thereof to Siemens, at Buyer's expense, or granting Siemens reasonable access to the Products to assess the warranty claims; (vii) Product not having been subjected to accident (including force majeure), alteration, abuse or misuse; and (viii) Buyer not being in default of any payment obligation.

(c) Exclusions from Warranty Coverage. The Warranties do not apply to any equipment not provided by Siemens under this Agreement.

Any Product that is described as being experimental, developmental, prototype, or pilot is specifically excluded from the Warranties and is provided to Buyer "as is" with no warranties of any kind. Normal wear and tear is excluded, including any expendable items that comprise part of the Product (such as fuses, light bulbs and lamps). Siemens does not warrant or guarantee that any Product will be secure from cyber threats, hacking or similar malicious activity. Products that are networked, connected to the internet, or otherwise connected to computers or other devices must be appropriately protected by Buyer and/or end user against unauthorized access.

(d) Warranty Period. Buyer must provide written notice of any claims for breach of Warranties by the earlier of twelve (12) months from initial operation of the Product or eighteen (18) months from shipment. Additionally, absent written notice within the warranty period, any use or possession of the Product after expiration of the warranty period is conclusive evidence that the Warranties have been satisfied.

(e) Remedies. Buyer's sole and exclusive remedies for breach of the Warranties are limited, at Siemens' discretion, to repair or replacement of the Product, or its non-conforming parts, within a reasonable time period, or refund of all or part of the purchase price. The warranty on repaired or replaced parts is limited to the remainder of the original warranty period. Unless Siemens agrees otherwise in writing, Buyer will be responsible for any costs associated with: (i) gaining

access to the Product; (ii) removal, disassembly, replacement, installation, or reinstallation of any equipment, materials or structures to permit Siemens to perform its warranty obligations; (iii) transportation to and from the Siemens factory or repair facility; and (iv) damage to equipment components or parts resulting in whole or in part from non-compliance by the Buyer with Article 9(b) or from their deteriorated condition. All exchanged Products replaced under this Warranty will become the property of Siemens.

(f) Transferability. The Warranties are only transferable during the warranty period and only to the Product's initial end-user.

(g) THE WARRANTIES IN THIS ARTICLE 9 ARE SIEMENS' SOLE AND EXCLUSIVE WARRANTIES AND ARE SUBJECT TO THE LIMITS OF LIABILITY IN ARTICLE 10 BELOW. SIEMENS MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, COURSE OF DEALING AND USAGE OF TRADE.

- 10. LIMITATION OF LIABILITY.** NOTWITHSTANDING ANYTHING IN THIS AGREEMENT TO THE CONTRARY, SIEMENS IS NOT LIABLE, WHETHER BASED IN CONTRACT, WARRANTY, TORT (INCLUDING NEGLIGENCE), STRICT LIABILITY, INDEMNITY OR ANY OTHER LEGAL OR EQUITABLE THEORY, FOR: LOSS OF USE, REVENUE, SAVINGS, PROFIT, INTEREST, GOODWILL OR OPPORTUNITY, COSTS OF CAPITAL, COSTS OF REPLACEMENT OR SUBSTITUTE USE OR PERFORMANCE, LOSS OF INFORMATION AND DATA, LOSS OF POWER, VOLTAGE IRREGULARITIES OR FREQUENCY FLUCTUATION, CLAIMS ARISING FROM BUYER'S THIRD PARTY CONTRACTS, OR FOR ANY TYPE OF INDIRECT, SPECIAL, LIQUIDATED, PUNITIVE, EXEMPLARY, COLLATERAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES, OR FOR ANY OTHER LOSS OR COST OF A SIMILAR TYPE.

SIEMENS' MAXIMUM LIABILITY UNDER THIS AGREEMENT IS THE ACTUAL PURCHASE PRICE RECEIVED BY SIEMENS FOR THE PRODUCT THAT GAVE RISE TO THE CLAIM.

BUYER AGREES THAT THE EXCLUSIONS AND LIMITATIONS IN THIS ARTICLE 10 WILL PREVAIL OVER ANY CONFLICTING TERMS AND CONDITIONS IN THIS AGREEMENT AND MUST BE GIVEN FULL FORCE AND EFFECT, WHETHER OR NOT ANY OR ALL SUCH REMEDIES ARE DETERMINED TO HAVE FAILED OF THEIR ESSENTIAL PURPOSE. THESE LIMITATIONS OF LIABILITY ARE EFFECTIVE EVEN IF SIEMENS HAS BEEN ADVISED BY BUYER OF THE POSSIBILITY OF SUCH DAMAGES. THE WAIVERS AND DISCLAIMERS OF LIABILITY, RELEASES FROM LIABILITY AND LIMITATIONS ON LIABILITY EXPRESSED IN THIS ARTICLE 10 EXTEND TO SIEMENS' AFFILIATES, PARTNERS, PRINCIPALS, SHAREHOLDERS, DIRECTORS, OFFICERS, EMPLOYEES, SUPPLIERS, AGENTS, AND SUCCESSORS AND ASSIGNS.

- 11. Patent and Copyright Infringement.** Siemens will, at its option and expense, defend or settle any suit or proceeding brought against Buyer based on an allegation that any Product or use thereof for its intended purpose constitutes an infringement of any Patent Cooperation Treaty country member's patent or misappropriation of a third party's trade secret or copyright in the country where the Product is delivered by Siemens. Buyer will promptly give Siemens written notice of the suit or proceeding and the authority, information, and assistance needed to defend the claims. Siemens shall have the full and exclusive authority to defend and settle such claim(s) and will pay the damages and costs awarded in any suit or proceeding so defended. Buyer shall not make any admission(s) which might be prejudicial to Siemens and shall not enter into a settlement without Siemens' consent. Siemens is not responsible for any settlement made without its prior written consent. If the Product, or any part thereof, as a result of any suit or proceeding so defended is held to constitute infringement or its use by Buyer is enjoined, Siemens will, at its option and expense, either: (i) procure for Buyer the right to continue using said Product; (ii) replace it with substantially equivalent non-infringing Product; or (iii) modify the Product so it is non-infringing.

Siemens will have no duty or obligation under this Article 11 if the Product is: (i) supplied according to Buyer's design or instructions and compliance therewith has caused Siemens to deviate from its normal course of performance; (ii) modified by Buyer or its contractors after delivery; or (iii) combined by Buyer or its contractors with devices, methods, systems or processes not furnished hereunder and by reason of said design, instruction, modification, or combination a suit is brought against Buyer. In addition, if by reason of such design, instruction, modification or combination, a suit or proceeding is brought against Siemens, Buyer must protect Siemens in the same manner and to the same extent that Siemens has agreed to protect Buyer under this Article 11.

THIS ARTICLE 11 IS AN EXCLUSIVE STATEMENT OF SIEMENS' DUTIES AND BUYER'S REMEDIES RELATING TO PATENTS, TRADE SECRETS AND COPYRIGHTS, AND DIRECT OR CONTRIBUTORY INFRINGEMENT THEREOF.

- 12. Confidentiality.** (a) Both during and after the term of this Agreement, the parties will treat as confidential all information obtained from the disclosing party and all information compiled or generated by the disclosing party under this Agreement for the receiving party, including but not limited to business information, manufacturing information, technical data, drawings, flow charts, program listings, software code, and other software, plans and projections. Neither party may disclose or refer to the work to be performed under this Agreement in any manner that identifies the other party without advance written permission. However, Siemens has the right to share confidential information with its affiliates and subcontractors, provided those recipients are subject to the same confidentiality obligations set forth herein. (b) Nothing in this Agreement requires a party to treat as confidential any information which: (i) is or becomes generally known to the public, without the fault of the receiving party; (ii) is disclosed to the receiving party, without obligation of confidentiality, by a third party having the right to make such disclosure; (iii) was previously known to the receiving party, without obligation of confidentiality, which fact can be demonstrated by means of documents which are in the possession of the receiving party upon the date of this Agreement; (iv) was independently developed by receiving party or its representatives, as evidenced by written records, without the use of discloser's confidential information; or (v) is required to be disclosed by law, except to the extent eligible for special treatment under an appropriate protective order, provided that the party required to disclose by law will promptly advise the originating party of any requirement to make such disclosure to allow the originating party the opportunity to obtain a protective order and assist the originating party in so doing. (c) It is Siemens' policy not to unlawfully or improperly receive or use confidential information, including trade secrets, belonging to others. This policy precludes Siemens from obtaining, directly or indirectly from any employee, contractor, or other individual

rendering services to Siemens confidential information of a prior employer, client or any other person which such employee, contractor, or individual is under an obligation not to disclose.

Buyer agrees to abide by this policy.

13. **Compliance With Laws.** The parties agree to comply with all applicable laws and regulations, including but not limited to those relating to the manufacture, purchase, resale, exportation, transfer, assignment or use of the Products.
14. **Changes In Work.** No change will be made to the scope of work unless Buyer and Siemens agree in writing to the change and any resulting price, schedule or other contractual modifications. If any change to any law, rule, regulation, order, code, standard or requirement impacts Siemens' obligations or performance under this Agreement, Siemens may request a change order for an equitable adjustment in the price and time of performance.
15. **Non-Waiver.** Any waiver by a party of strict compliance with this Agreement must be in writing, and any failure by the parties to require strict compliance in one instance will not waive its right to insist on strict compliance thereafter.
16. **Modification of Terms.** This Agreement may only be modified by a written instrument signed by authorized representatives of both parties.
17. **Assignment.** Neither party may assign all or part of this Agreement, or any rights or obligations under this Agreement, without the prior written consent of the other; but either party may assign its rights and obligations, without recourse or consent, to any parent, wholly owned subsidiary, or affiliate or affiliate's successor organization (whether as a result of reorganization, restructuring or sale of substantially all of a party's assets). However, Buyer shall not assign this Agreement to: a competitor of Siemens; an entity in litigation with Siemens; or an entity lacking the financial capability to satisfy Buyer's obligations.  
  
Any assignee expressly assumes the performance of any obligation assigned. Siemens may grant a security interest in this Agreement and/or assign proceeds of this Agreement without Buyer's consent.
18. **Applicable Law and Jurisdiction.** This Agreement is governed by and construed in accordance with the laws of the State of Delaware, without regard to its conflict of laws principles. The application of the United Nations Convention on Contracts for the International Sale of Goods is excluded. BOTH SIEMENS AND BUYER KNOWINGLY, VOLUNTARILY AND IRREVOCABLY WAIVE ALL RIGHTS TO A JURY TRIAL IN ANY ACTION OR PROCEEDING RELATED IN ANY WAY TO THIS AGREEMENT. Each party agrees that claims and disputes arising out of this Agreement must be decided exclusively in a federal or state court of competent jurisdiction located in a state in which either Buyer or Siemens maintains its principal place of business. Each party submits to the personal jurisdiction of such courts for the purpose of litigating any claims or disputes.
19. **Severability.** If any provision of this Agreement is held invalid, illegal or unenforceable, the remaining provisions will not in any way be affected or impaired. A court may modify the invalid, illegal or unenforceable provision to reflect, as closely as possible, the parties' original intent.
20. **Export / Import Compliance.** Buyer acknowledges that Siemens is required to comply with applicable export /import laws and regulations relating to the sale, export, import, transfer, assignment, disposal and use of the Products, including any export / import license requirements. Buyer agrees that Products will not at any time directly or indirectly be used, exported, imported, sold, transferred, assigned or otherwise disposed of in a manner which will result in non-compliance with any export / import laws and regulations. Siemens' continuing performance hereunder is conditioned on compliance with such export / import laws and regulations at all times.
21. **Product Returns.** Prior to the return of any Product to Siemens, Buyer must identify the Product or portion thereof and obtain written authorization and shipping instructions from Siemens. Siemens has the right, in its sole discretion, to permit or reject any such return. Siemens' authorization to return any Product to Siemens does not relieve Buyer of its obligation to pay for such Product. Upon receipt, inspection, and acceptance of the Product by Siemens, Siemens will issue a credit memo to Buyer, less applicable re-stocking fees. Siemens reserves the right to reject any hazardous material.
22. **Nuclear.** Unless expressly authorized in writing by Siemens, the Products must not be used in or in connection with a nuclear facility or application. If Buyer uses any Product in connection with any nuclear facility or activity, it does so at its own risk and Buyer will indemnify, defend and hold Siemens harmless, and waives and will require its insurers to waive all right of recovery against Siemens for any damage, loss, destruction, injury or death resulting from a "nuclear incident," as defined in the Atomic Energy Act of 1954, as amended, whether or not due to Siemens' negligence. Siemens' consent to Buyer's use of the Product in connection with any nuclear facility or application will be subject to additional terms and conditions that Siemens deems necessary to protect its interests.
23. **Survival.** The articles titled "Patent and Copyright Infringement," "Limitation of Liability," "Confidentiality," "Delivery; Title; Risk of Loss," "Export / Import Compliance," and "Nuclear" survive termination, expiration or cancellation of this Agreement.

Grade Crossing Control Systems Products			Price	
NYK:80008090500000	Wayguard® GCP 5000 Empty Five Track Non-Redundant	A14	\$	3,267.00
NYK:81018090500216	Wayguard® GCP 5000 Comprehensive Five Track Non-Redundant	A14	\$	26,465.00
NYK:80008090200000	Wayguard® GCP 5000 Empty Two Track Redundant	A15	\$	3,407.00
NYK:82028090200220	Wayguard® GCP 5000 Comprehensive Two Track Redundant	A15	\$	35,413.00
NYK:80008090700000	Wayguard® GCP 5000 Empty Three Track Redundant	A16	\$	3,407.00
NYK:82038090700220	Wayguard® GCP 5000 Comprehensive Three Track Redundant	A16	\$	50,913.00
NYK:80008090000000	Wayguard® GCP 5000 Empty Six Track Redundant	A17	\$	7,391.00
NYK:82028090000220	Wayguard® GCP 5000 Comprehensive Six Track Redundant	A17	\$	48,241.00
NYK:80008074000000	Wayguard® GCP 3000+ Empty Two Track Redundant	--	\$	11,023.00
NYK:8004807400011	Wayguard® GCP 3000+ Comprehensive Single Track Non-Redundant	--	\$	14,158.00
NYK:8001807400001	Wayguard® GCP 3000+ Comprehensive Single Track Redundant	--	\$	19,555.00
NYK:8105807400001	Wayguard® GCP 3000+ Comprehensive Two Track Non-Redundant	--	\$	24,249.00
NYK:8102807400001	Wayguard® GCP 3000+ Comprehensive Two Track Redundant	--	\$	33,637.00
NYK:80008049500000	Wayguard® SGCP 4000 / MS 4000 Empty Narrow	A2	\$	2,456.00
NYK:84108049500000	Wayguard® SGCP 4000 / MS 4000 Comprehensive Narrow Non-Redundant	A2	\$	10,459.00
NYK:80008049000001	Wayguard® SGCP 4000 / MS 4000 Empty Wide	A3	\$	2,312.00
NYK:81108049000001	Wayguard® SGCP 4000 / MS 4000 Basic Wide Non-Redundant	A3	\$	11,448.00
NYK:84218049000001	Wayguard® SGCP 4000 / MS 4000 Comprehensive Wide Redundant	A3	\$	18,093.00
NYK:80008044500000	Wayguard® GCP 4000 Empty Single Track Non-Redundant	A6	\$	1,612.00
NYK:84108044500000	Wayguard® GCP 4000 Comprehensive Single Track Non-Redundant	A6	\$	11,264.00
NYK:80008044000000	Wayguard® GCP 4000 Empty Five Track Non-Redundant	A7	\$	3,378.00
NYK:811080440002J3	Wayguard® GCP 4000 Comprehensive Five Track Non-Redundant	A7	\$	24,145.00
NYK:80008045500000	Wayguard® GCP 4000 Empty Single Basic Crossing Non-Redundant	A8	\$	2,747.00
NYK:81108045500280	Wayguard® GCP 4000 Comprehensive Single Basic Crossing Non-Redundant	A8	\$	19,260.00
NYK:80008046500000	Wayguard® GCP 4000 Empty Two Track Redundant	A9	\$	3,513.00
NYK:822080465002U9	Wayguard® GCP 4000 Comprehensive Two Track Redundant	A9	\$	34,976.00
NYK:80008046000000	Wayguard® GCP 4000 Empty Six Track Redundant	A10	\$	6,954.00
NYK:822080460000Y2	Wayguard® GCP 4000 Comprehensive Six Track Redundant	A10	\$	29,216.00
NYK:8000809034022	GCP CPU III Module Without Echelon - GCP3000+	--	\$	4,075.00
NYK:8000809034021	GCP CPU III Module With Echelon - GCP3000+	--	\$	4,545.00
NYK:8000809032021	GCP CPU III Module With Echelon - GCP4000/5000	--	\$	4,828.00
NYK:8000809031011	GCP CPU III Module With Echelon - GEO	--	\$	4,828.00
NYK:8000804030001	GCP CPU II+ Module	A19	Call For Pricing	
NYK:8000804180001	GCP Track Module	A19	\$	5,102.00
NYK:8000804050001	GCP SSCC Illi Module	A19	\$	2,754.00
NYK:8000804850001	GCP Display Module	A19	\$	2,642.00
NYK:8000804060001	GCP Transfer Module, Wide	A20	\$	1,695.00
NYK:8000804060002	GCP Transfer Module, Narrow	A20	\$	1,695.00
NYK:8000804680001	GCP Transfer Module, Chassis	A20	\$	1,695.00
NYK:8000804100001	GCP SEAR Illi Module w/o Cable	A21	\$	4,493.00
NYK:8000804100003	GCP SEAR Illi Module w/ Cable	A22	\$	4,380.00

Grade Crossing Control Systems Products			Price
NYK:8000804280001	GCP Phase Shift Overlay (PSO) Module	A23	\$ 3,764.00
NYK:8000804280002	GCP Phase Shift Overlay (PSO) Module	A23	\$ 3,764.00
NYK:8000804130001	GCP Relay Input /Output (RIO) Module	A23	\$ 2,187.00
NYK:Z610393250001	Blank Module Filler Plate, Narrow	A24	\$ 25.00
NYK:Z610393260001	Blank Module Filler Plate, Wide	A24	\$ 155.00
NYK:Z610393590001	Blank Module Filler Plate, SEAR	A24	\$ 35.00
NYK:8000804350001	GCP SPI / ECD Module, 4mb	A25	\$ 242.00
NYK:525-0202-01	EGMS, 4 Loop Assembly w/ Communications Module	A29	\$ 40,752.00
NYK:525-0202-02	EGMS, 8 Loop Assembly w/ Communications Module	A29	\$ 50,196.00
NYK:525-0202-03	EGMS, 12 Loop Assembly w/ Communications Module	A29	\$ 60,833.00
NYK:525-0202-04	EGMS, 16 Loop Assembly w/ Communications Module	A29	\$ 69,084.00
NYK:017-100-0001	E1400S (4) Channel Presence Detector	A30	Call For Pricing
NYK:017-101-0001	P1400S (4) Channel Presence Detector	A30	Call For Pricing
NYK:010-101-0006	EGMS Power Supply Module	A31	\$ 5,464.00
NYK:010-101-0002	EGMS Display Module	A31	\$ 5,464.00
NYK:010-101-0003	EGMS CPU Module	A31	\$ 5,413.00
NYK:010-101-0004	EGMS Vital Input Module	A31	\$ 4,655.00
NYK:PLC-24-50	EGMS Cable 24' long x 50' wide	A32	\$ 1,166.00
NYK:PLC-26-50	EGMS Cable 26' long x 50' wide	A32	\$ 1,193.00
NYK:PLC-28-50	EGMS Cable 28' long x 50' wide	A32	\$ 1,220.00
NYK:PLC-30-50	EGMS Cable 30' long x 50' wide	A32	\$ 1,247.00
NYK:PLC-32-50	EGMS Cable 32' (9.8 m) long x 50' wide	A32	\$ 1,274.00
NYK:PLC-34-50	EGMS Cable 34' long x 50' wide	A32	\$ 1,301.00
NYK:PLC-36-50	EGMS Cable 36' long x 50' wide	A32	\$ 1,328.00
NYK:PLC-38-50	EGMS Cable 38' long x 50' wide	A32	\$ 1,356.00
NYK:PLC-40-50	EGMS Cable 40' long x 50' wide	A32	\$ 1,382.00
NYK:PLC-50-50	EGMS Cable 50' long x 50' wide	A32	\$ 1,517.00
NYK:07-020-011	Ø3/4" 4C #18 AWG RR-418 cable, triple jacketed, per linear foot	A32	\$ 9.65
NYK:03-094-005	EGMS Home run cable	A32	\$ 16.39
NYK:03-083-003	EGMS, TB-2 Wago® terminal strip for 1st and 2nd presence detectors	A33	\$ 675.00
NYK:03-083-004	EGMS, TB-4 Wago® terminal strip for 3rd and 4th presence detectors	A33	\$ 345.00
NYK:07-020-006	EGMS, Presence detector cable harness kit	A33	\$ 3,053.00
NYK:018-100-0001	EGMS, Aluminum foundation mounted junction box	A33	\$ 822.00
NYK:018-101-0001	EGMS, Aluminum pedestal mounted junction box	A33	\$ 1,017.00
NYK:04-004-005	EGMS, 1" NPT hub gland plate	---	\$ 45.10
NYK:8000810000001	Wayside Inspector Unit	A34	\$ 3,950.00
NYK:Z921004070000	WiMag VSN240-F Sensor	A34	Call For Pricing
NYK:Z927004220000	WiMag Repeater Unit	A34	Call For Pricing
NYK:Z927004210000	Access Point Base Station	A34	Call For Pricing
NYK:9000911651101	SSCC IIIA, 20 Amp, 19" Mounting Plate	A36	\$ 4,403.00
NYK:9000911601101	SSCC IIIA, 40 Amp, 19" Mounting Plate	A36	\$ 5,305.00
NYK:9000911650101	SSCC IIIA, 20 Amp, 23" Mounting Plate	A36	\$ 4,403.00
NYK:9000911600101	SSCC IIIA, 40 Amp, 23" Mounting Plate	A36	\$ 5,305.00
NYK:9000911951101	SSCC III Plus, 20 Amp, 19" Mounting Plate	A37	\$ 6,264.00
NYK:9000911901101	SSCC III Plus, 40 Amp, 19" Mounting Plate	A37	\$ 7,547.00
NYK:9000911950101	SSCC III Plus, 20 Amp, 23" Mounting Plate	A37	\$ 6,264.00
NYK:9000911900101	SSCC III Plus, 40 Amp, 23" Mounting Plate	A37	\$ 7,547.00

Grade Crossing Control Systems Products			Price	
NYK:9000912151101	SSCC IV, 20 Amp, 19" Mounting Plate	A38	\$	7,266.00
NYK:9000912101101	SSCC IV, 40 Amp, 19" Mounting Plate	A38	\$	8,754.00
NYK:9000912150101	SSCC IV, 20 Amp, 23" Mounting Plate	A38	\$	7,266.00
NYK:9000912100101	SSCC IV, 40 Amp, 23" Mounting Plate	A38	\$	8,754.00
NYK:8000803110001	ARGUS, w/o GPS, Proprietary Silk Screen	A42	\$	2,176.00
NYK:8000803110003	ARGUS, w/o GPS, Non Proprietary Silk Screen	A42	\$	2,176.00
NYK:8000803110004	ARGUS, w/ GPS, Proprietary Silk Screen	A42	\$	2,687.00
NYK:8000803110006	ARGUS, w/ GPS, Non Proprietary Silk Screen	A42	\$	2,687.00
NYK:8000267600001	ARGUS, (2) 6' Antenna / Surge cables, (1) SMA/M adapter, (1) DC Arrester	A43	\$	924.00
NYK:8000267600002	ARGUS, (1) 6' Antenna / Surge cable, (1) 15' Antenna / Surge cable, (1) SMA/M adapter, (1) DC Arrester	A43	\$	924.00
NYK:8000267600003	ARGUS, (1) 6' Antenna / Surge cable, (1) 30' Antenna / Surge cable, (1) SMA/M adapter, (1) DC Arrester	A43	\$	924.00
NYK:8000267600004	ARGUS, (1) 6' Antenna / Surge cable, (1) 50' Antenna / Surge cable, (1) SMA/M adapter, (1) DC Arrester	A43	\$	924.00
NYK:8000267600006	ARGUS, (2) 15' Antenna / Surge cable, (1) SMA/M adapter, (1) DC Arrester	A43	\$	924.00
NYK:8000267600007	ARGUS, (1) 15' Antenna / Surge cable, (1) 30' Antenna / Surge cable, (1) SMA/M adapter, (1) DC Arrester	A43	\$	924.00
NYK:8000267600008	ARGUS, (1) 15' Antenna / Surge cable, (1) 50' Antenna / Surge cable, (1) SMA/M adapter, (1) DC Arrester	A43	\$	924.00
NYK:8000267600011	ARGUS, (2) 30' Antenna / Surge cables, (1) SMA/M adapter, (1) DC Arrester	A43	\$	950.00
NYK:8000267600012	ARGUS, (1) 30' Antenna / Surge cable, (1) 50' Antenna / Surge cable, (1) SMA/M adapter, (1) DC Arrester	A43	\$	950.00
NYK:8000267600016	ARGUS, (2) 50' Antenna / Surge cables, (1) SMA/M adapter, (1) DC Arrester	A43	\$	950.00
NYK:8000802730001	SEAR w/o Internal Expansion Module	A46	\$	4,470.00
NYK:8000802550001	SEAR Analog I/O Expansion Card Module	A47	\$	454.00
NYK:8000802580001	SEAR Digital I/O Expansion Module	A47	\$	5,517.00
NYK:8000802580002	SEAR Analog I/O Expansion Module	A47	\$	3,425.00
NYK:8000802610001	Analog Input Module	A47	\$	1,944.00
NYK:8000800630001	GCP to Echelon® Interface Module	A48	\$	278.00
NYK:8000802910001	SEAR Communications Isolator Module	A48	\$	1,477.00
NYK:8000802760001	VHF Communicator, SEAR Transmit / Receive	A48	\$	2,392.00
NYK:8000802760002	VHF Communicator, Console Transmit / Receive	A48	\$	2,451.00
NYK:8000802850001	MTSS, Mini Track Side Sensor	A49	\$	823.00
NYK:8000802710001	iLOD, Intelligent Lights Out Detector	A50	\$	809.00
NYK:8000810100001	GFT II, Ground Fault Tester, 12V or 16V	A52	Call for Pricing	
NYK:8000810100002	GFT II, Ground Fault Tester, 24V or 30V	A52	Call for Pricing	

Grade Crossing Auxiliary Systems Products			Price	
NYK:6000627750086	NBS, Narrow Band Shunt, Copper Wire, Standard, 86 Hz	A54	\$	739.00
NYK:6000627750114	NBS, Narrow Band Shunt, Copper Wire, Standard, 114 Hz	A54	\$	753.00
NYK:6000627750156	NBS, Narrow Band Shunt, Copper Wire, Standard, 156 Hz	A54	\$	739.00
NYK:6000627750211	NBS, Narrow Band Shunt, Copper Wire, Standard, 211 Hz	A54	\$	739.00
NYK:6000627750285	NBS, Narrow Band Shunt, Copper Wire, Standard, 285 Hz	A54	\$	653.00
NYK:6000627750348	NBS, Narrow Band Shunt, Copper Wire, Standard, 348 Hz	A54	\$	653.00
NYK:6000627750430	NBS, Narrow Band Shunt, Copper Wire, Standard, 430 Hz	A54	\$	670.00
NYK:6000627750525	NBS, Narrow Band Shunt, Copper Wire, Standard, 525 Hz	A54	\$	619.00
NYK:6000627750645	NBS, Narrow Band Shunt, Copper Wire, Standard, 645 Hz	A54	\$	619.00
NYK:6000627750790	NBS, Narrow Band Shunt, Copper Wire, Standard, 790 Hz	A54	\$	619.00
NYK:6000627750970	NBS, Narrow Band Shunt, Copper Wire, Standard, 970 Hz	A54	\$	634.00
NYK:6E00627750086	NBS, Narrow Band Shunt, Erico® Bondstrand, Standard, 86 Hz	A54	\$	767.00
NYK:6E00627750114	NBS, Narrow Band Shunt, Erico® Bondstrand, Standard, 114 Hz	A54	\$	767.00
NYK:6E00627750156	NBS, Narrow Band Shunt, Erico® Bondstrand, Standard, 156 Hz	A54	\$	770.00
NYK:6E00627750211	NBS, Narrow Band Shunt, Erico® Bondstrand, Standard, 211 Hz	A54	\$	752.00
NYK:6E00627750285	NBS, Narrow Band Shunt, Erico® Bondstrand, Standard, 285 Hz	A54	\$	665.00
NYK:6E00627750348	NBS, Narrow Band Shunt, Erico® Bondstrand, Standard, 348 Hz	A54	\$	665.00
NYK:6E00627750430	NBS, Narrow Band Shunt, Erico® Bondstrand, Standard, 430 Hz	A54	\$	665.00
NYK:6E00627750525	NBS, Narrow Band Shunt, Erico® Bondstrand, Standard, 525 Hz	A54	\$	629.00
NYK:6E00627750645	NBS, Narrow Band Shunt, Erico® Bondstrand, Standard, 645 Hz	A54	\$	645.00
NYK:6E00627750790	NBS, Narrow Band Shunt, Erico® Bondstrand, Standard, 790 Hz	A54	\$	645.00
NYK:6E00627750970	NBS, Narrow Band Shunt, Erico® Bondstrand, Standard, 970 Hz	A54	\$	629.00
NYK:6000627780086	NBS, Narrow Band Shunt, Copper Wire, High Impedance, 86 Hz	A54	\$	1,235.00
NYK:6000627780114	NBS, Narrow Band Shunt, Copper Wire, High Impedance, 114 Hz	A54	\$	1,235.00
NYK:6000627780156	NBS, Narrow Band Shunt, Copper Wire, High Impedance, 156 Hz	A54	\$	691.00
NYK:6000627780211	NBS, Narrow Band Shunt, Copper Wire, High Impedance, 211 Hz	A54	\$	691.00
NYK:6000627780285	NBS, Narrow Band Shunt, Copper Wire, High Impedance, 285 Hz	A54	\$	691.00
NYK:6000627780348	NBS, Narrow Band Shunt, Copper Wire, High Impedance, 348 Hz	A54	\$	691.00
NYK:6000627780430	NBS, Narrow Band Shunt, Copper Wire, High Impedance, 430 Hz	A54	\$	691.00
NYK:6000627780525	NBS, Narrow Band Shunt, Copper Wire, High Impedance, 525 Hz	A54	\$	691.00
NYK:6000627780645	NBS, Narrow Band Shunt, Copper Wire, High Impedance, 645 Hz	A54	\$	691.00
NYK:6000627780790	NBS, Narrow Band Shunt, Copper Wire, High Impedance, 790 Hz	A54	\$	691.00
NYK:6000627780970	NBS, Narrow Band Shunt, Copper Wire, High Impedance, 970 Hz	A54	\$	691.00
NYK:6E00627780086	NBS, Narrow Band Shunt, Erico® Bondstrand, High Impedance, 86 Hz	A55	\$	1,257.00
NYK:6E00627780114	NBS, Narrow Band Shunt, Erico® Bondstrand, High Impedance, 114 Hz	A55	\$	1,257.00
NYK:6E00627780156	NBS, Narrow Band Shunt, Erico® Bondstrand, High Impedance, 156 Hz	A55	\$	703.00
NYK:6E00627780211	NBS, Narrow Band Shunt, Erico® Bondstrand, High Impedance, 211 Hz	A55	\$	703.00
NYK:6E00627780285	NBS, Narrow Band Shunt, Erico® Bondstrand, High Impedance, 285 Hz	A55	\$	703.00
NYK:6E00627780348	NBS, Narrow Band Shunt, Erico® Bondstrand, High Impedance, 348 Hz	A55	\$	703.00
NYK:6E00627780430	NBS, Narrow Band Shunt, Erico® Bondstrand, High Impedance, 430 Hz	A55	\$	703.00
NYK:6E00627780525	NBS, Narrow Band Shunt, Erico® Bondstrand, High Impedance, 525 Hz	A55	\$	703.00
NYK:6E00627780645	NBS, Narrow Band Shunt, Erico® Bondstrand, High Impedance, 645 Hz	A55	\$	703.00
NYK:6E00627780790	NBS, Narrow Band Shunt, Erico® Bondstrand, High Impedance, 790 Hz	A55	\$	703.00
NYK:6E00627780970	NBS, Narrow Band Shunt, Erico® Bondstrand, High Impedance, 970 Hz	A55	\$	703.00
NYK:6000627700086	NBS, Narrow Band Shunt, Copper Wire, High Power, 86 Hz	A55	\$	2,354.00
NYK:6000627700114	NBS, Narrow Band Shunt, Copper Wire, High Power, 114 Hz	A55	\$	2,354.00
NYK:6000627700156	NBS, Narrow Band Shunt, Copper Wire, High Power, 156 Hz	A55	\$	2,354.00
NYK:6000627700211	NBS, Narrow Band Shunt, Copper Wire, High Power, 211 Hz	A55	\$	2,354.00
NYK:6000627700285	NBS, Narrow Band Shunt, Copper Wire, High Power, 285 Hz	A55	\$	2,354.00
NYK:6000627700348	NBS, Narrow Band Shunt, Copper Wire, High Power, 348 Hz	A55	\$	2,354.00
NYK:6000627758621	NBS, Narrow Band Shunt, Copper Wire Bondstrand, Multi Frequency, 86 - 211 Hz	A56	\$	1,076.00
NYK:6000627751543	NBS, Narrow Band Shunt, Copper Wire Bondstrand, Multi Frequency, 156 - 430 Hz	A56	\$	1,076.00
NYK:6000627752152	NBS, Narrow Band Shunt, Copper Wire Bondstrand, Multi Frequency, 211 - 535 Hz	A56	\$	1,076.00

Grade Crossing Auxiliary Systems Products			Price
NYK:6000627752879	NBS, Narrow Band Shunt, Copper Wire Bondstrand, Multi Frequency, 285 - 790 Hz	A56	\$ 1, 076.00
NYK:6000627753497	NBS, Narrow Band Shunt, Copper Wire Bondstrand, Multi Frequency, 348 - 970 Hz	A56	\$ 1,076.00
NYK:6E00627758621	NBS, Narrow Band Shunt, Erico® Bondstrand, Multi Frequency, 86 - 211 Hz	A56	\$ 1,076.00
NYK:6E00627751543	NBS, Narrow Band Shunt, Erico® Bondstrand, Multi Frequency, 156 - 430 Hz	A56	\$ 1,076.00
NYK:6E00627752152	NBS, Narrow Band Shunt, Erico® Bondstrand, Multi Frequency, 211 - 535 Hz	A56	\$ 1,076.00
NYK:6E00627752879	NBS, Narrow Band Shunt, Erico® Bondstrand, Multi Frequency, 285 - 790 Hz	A56	\$ 1,076.00
NYK:6E00627753497	NBS, Narrow Band Shunt, Erico® Bondstrand, Multi Frequency, 348 - 970 Hz	A56	\$ 1,076.00
NYK:80008A0760001	WBS, Wide Band Shunt, Single Band, 3V, 10ft leads, Copper Wire	A60	\$ 438.00
NYK:80008A0760002	WBS, Wide Band Shunt, Single Band, 3V, 14ft leads, Copper Wire	A60	\$ 438.00
NYK:80008A0760011	WBS, Wide Band Shunt, Single Band, 20V, 10ft leads, Copper Wire	A60	\$ 438.00
NYK:80008A0760012	WBS, Wide Band Shunt, Single Band, 20V, 14ft leads, Copper Wire	A60	\$ 438.00
NYK:8E008A0760001	WBS, Wide Band Shunt, Single Band, 3V, 10ft leads, Erico® Bondstrand	A60	\$ 449.00
NYK:8E008A0760002	WBS, Wide Band Shunt, Single Band, 3V, 14ft leads, Erico® Bondstrand	A60	\$ 585.00
NYK:8E008A0760011	WBS, Wide Band Shunt, Single Band, 20V, 10ft leads, Erico® Bondstrand	A60	\$ 438.00
NYK:8E008A0760012	WBS, Wide Band Shunt, Single Band, 20V, 14ft leads, Erico® Bondstrand	A60	\$ 438.00
NYK:80008A0770001	WBS, Wide Band Shunt, Dual Band, 3V, 10ft leads, Copper Wire	A60	\$ 1,165.00
NYK:80008A0770002	WBS, Wide Band Shunt, Dual Band, 3V, 14ft leads, Copper Wire	A60	\$ 1,165.00
NYK:80008A0770011	WBS, Wide Band Shunt, Dual Band, 20V, 10ft leads, Copper Wire	A60	\$ 827.00
NYK:80008A0770012	WBS, Wide Band Shunt, Dual Band, 20V, 14ft leads, Copper Wire	A60	\$ 836.00
NYK:8E008A0770001	WBS, Wide Band Shunt, Dual Band, 3V, 10ft leads, Erico® Bondstrand	A60	\$ 585.00
NYK:8E008A0770002	WBS, Wide Band Shunt, Dual Band, 3V, 14ft leads, Erico® Bondstrand	A60	\$ 593.00
NYK:8E008A0770011	WBS, Wide Band Shunt, Dual Band, 20V, 10ft leads, Erico® Bondstrand	A60	\$ 827.00
NYK:8E008A0770012	WBS, Wide Band Shunt, Dual Band, 20V, 14ft leads, Erico® Bondstrand	A60	\$ 836.00
NYK:6000627850086	TJC, Tunable Joint Coupler, 86 Hz, Copper Wire	A62	\$ 1,446.00
NYK:6000627850114	TJC, Tunable Joint Coupler, 114 Hz, Copper Wire	A62	\$ 1,482.00
NYK:6000627850156	TJC, Tunable Joint Coupler, 156 Hz, Copper Wire	A62	\$ 1,446.00
NYK:6000627850211	TJC, Tunable Joint Coupler, 211 Hz, Copper Wire	A62	\$ 1,446.00
NYK:6000627850285	TJC, Tunable Joint Coupler, 285 Hz, Copper Wire	A62	\$ 1,446.00
NYK:6000627850348	TJC, Tunable Joint Coupler, 348 Hz, Copper Wire	A62	\$ 1,446.00
NYK:6000627850430	TJC, Tunable Joint Coupler, 430 Hz, Copper Wire	A62	\$ 1,446.00
NYK:6000627850525	TJC, Tunable Joint Coupler, 535 Hz, Copper Wire	A62	\$ 1,446.00
NYK:6000627850645	TJC, Tunable Joint Coupler, 645 Hz, Copper Wire	A62	\$ 1,482.00
NYK:6000627850790	TJC, Tunable Joint Coupler, 790 Hz, Copper Wire	A62	\$ 1,446.00
NYK:6000627850970	TJC, Tunable Joint Coupler, 970 Hz, Copper Wire	A62	\$ 1,446.00
NYK:6E00627850086	TJC, Tunable Joint Coupler, 86 Hz, Erico® Bondstrand	A62	\$ 1,446.00
NYK:6E00627850114	TJC, Tunable Joint Coupler, 114 Hz, Erico® Bondstrand	A62	\$ 1,482.00
NYK:6E00627850156	TJC, Tunable Joint Coupler, 156 Hz, Erico® Bondstrand	A62	\$ 1,482.00
NYK:6E00627850211	TJC, Tunable Joint Coupler, 211 Hz, Erico® Bondstrand	A62	\$ 1,482.00
NYK:6E00627850285	TJC, Tunable Joint Coupler, 285 Hz, Erico® Bondstrand	A62	\$ 1,482.00
NYK:6E00627850348	TJC, Tunable Joint Coupler, 348 Hz, Erico® Bondstrand	A62	\$ 1,482.00
NYK:6E00627850430	TJC, Tunable Joint Coupler, 430 Hz, Erico® Bondstrand	A62	\$ 1,482.00
NYK:6E00627850525	TJC, Tunable Joint Coupler, 535 Hz, Erico® Bondstrand	A62	\$ 1,482.00
NYK:6E00627850645	TJC, Tunable Joint Coupler, 645 Hz, Erico® Bondstrand	A62	\$ 1,482.00
NYK:6E00627850790	TJC, Tunable Joint Coupler, 790 Hz, Erico® Bondstrand	A62	\$ 1,482.00
NYK:6E00627850970	TJC, Tunable Joint Coupler, 970 Hz, Erico® Bondstrand	A62	\$ 1,482.00
NYK:6000626640086	Bi-Directional Simulation Coupler, 86 Hz	A66	\$ 3,084.00
NYK:6000626640114	Bi-Directional Simulation Coupler, 114 Hz	A66	\$ 3,084.00
NYK:6000626640156	Bi-Directional Simulation Coupler, 156 Hz	A66	\$ 3,084.00
NYK:6000626640211	Bi-Directional Simulation Coupler, 211 Hz	A66	\$ 3,084.00
NYK:6000626640285	Bi-Directional Simulation Coupler, 285 Hz	A66	\$ 3,084.00

Grade Crossing Auxiliary Systems Products			Price
NYK:6000626640348	Bi-Directional Simulation Coupler, 348 Hz	A66	\$ 3,084.00
NYK:6000626640430	Bi-Directional Simulation Coupler, 430 Hz	A66	\$ 3,084.00
NYK:6000626640525	Bi-Directional Simulation Coupler, 525 Hz	A66	\$ 3,084.00
NYK:6000626640645	Bi-Directional Simulation Coupler, 645 Hz	A66	\$ 3,084.00
NYK:6000626640790	Bi-Directional Simulation Coupler, 790 Hz	A66	\$ 3,084.00
NYK:6000626640970	Bi-Directional Simulation Coupler, 970 Hz	A66	\$ 3,023.00
NYK:70007A4220156	PSO Insulated Joint Bypass Coupler, 156 Hz	A67	\$ 6,275.00
NYK:70007A4220211	PSO Insulated Joint Bypass Coupler, 211 Hz	A67	\$ 6,275.00
NYK:70007A4220285	PSO Insulated Joint Bypass Coupler, 285 Hz	A67	\$ 6,275.00
NYK:70007A4220348	PSO Insulated Joint Bypass Coupler, 348 Hz	A67	\$ 6,275.00
NYK:70007A4220430	PSO Insulated Joint Bypass Coupler, 430 Hz	A67	\$ 6,275.00
NYK:70007A4220525	PSO Insulated Joint Bypass Coupler, 525 Hz	A67	\$ 6,275.00
NYK:70007A4220645	PSO Insulated Joint Bypass Coupler, 645 Hz	A67	\$ 6,275.00
NYK:70007A4220790	PSO Insulated Joint Bypass Coupler, 790 Hz	A67	\$ 6,275.00
NYK:70007A4220970	PSO Insulated Joint Bypass Coupler, 970 Hz	A67	\$ 6,275.00
NYK:70007A4221180	PSO Insulated Joint Bypass Coupler, 1180 Hz	A67	\$ 6,275.00
NYK:70007A4221450	PSO Insulated Joint Bypass Coupler, 1450 Hz	A67	\$ 6,275.00
NYK:70007A4221770	PSO Insulated Joint Bypass Coupler, 1770 Hz	A67	\$ 6,275.00
NYK:70007A4222140	PSO Insulated Joint Bypass Coupler, 2140 Hz	A67	\$ 6,275.00
NYK:70007A4222630	PSO Insulated Joint Bypass Coupler, 2630 Hz	A67	\$ 6,275.00
NYK:70007A4223240	PSO Insulated Joint Bypass Coupler, 3240 Hz	A67	\$ 6,275.00
NYK:70007A4224000	PSO Insulated Joint Bypass Coupler, 4000 Hz	A67	\$ 6,275.00
NYK:70007A3550156	Receiver Coupler, Standard Impedance, 156 Hz	A68	\$ 1,060.00
NYK:70007A3550211	Receiver Coupler, Standard Impedance, 211 Hz	A68	\$ 1,019.00
NYK:70007A3550285	Receiver Coupler, Standard Impedance, 285 Hz	A68	\$ 1,019.00
NYK:70007A3550348	Receiver Coupler, Standard Impedance, 348 Hz	A68	\$ 1,024.00
NYK:70007A3550430	Receiver Coupler, Standard Impedance, 430 Hz	A68	\$ 1,060.00
NYK:70007A3550525	Receiver Coupler, Standard Impedance, 525 Hz	A68	\$ 999.00
NYK:70007A3550645	Receiver Coupler, Standard Impedance, 645 Hz	A68	\$ 999.00
NYK:70007A3550790	Receiver Coupler, Standard Impedance, 790 Hz	A68	\$ 999.00
NYK:70007A3550970	Receiver Coupler, Standard Impedance, 970 Hz	A68	\$ 999.00
NYK:70007A3551180	Receiver Coupler, Standard Impedance, 1180 Hz	A68	\$ 1,082.00
NYK:70007A3551450	Receiver Coupler, Standard Impedance, 1450 Hz	A68	\$ 999.00
NYK:70007A3551770	Receiver Coupler, Standard Impedance, 1770 Hz	A68	\$ 1,082.00
NYK:70007A3552140	Receiver Coupler, Standard Impedance, 2140 Hz	A68	\$ 999.00
NYK:70007A3552630	Receiver Coupler, Standard Impedance, 2630 Hz	A68	\$ 999.00
NYK:70007A3553240	Receiver Coupler, Standard Impedance, 3240 Hz	A68	\$ 999.00
NYK:70007A3554000	Receiver Coupler, Standard Impedance, 4000 Hz	A68	\$ 999.00
NYK:70007A3660156	Receiver Coupler, High Impedance, 156 Hz	A69	\$ 1,062.00
NYK:70007A3660211	Receiver Coupler, High Impedance, 211 Hz	A69	\$ 1,062.00
NYK:70007A3660285	Receiver Coupler, High Impedance, 285 Hz	A69	\$ 1,062.00
NYK:70007A3660348	Receiver Coupler, High Impedance, 348 Hz	A69	\$ 1,062.00
NYK:70007A3660430	Receiver Coupler, High Impedance, 430 Hz	A69	\$ 1,019.00
NYK:70007A3660525	Receiver Coupler, High Impedance, 525 Hz	A69	\$ 1,062.00
NYK:70007A3660645	Receiver Coupler, High Impedance, 645 Hz	A69	\$ 1,062.00
NYK:70007A3660790	Receiver Coupler, High Impedance, 790 Hz	A69	\$ 1,062.00
NYK:70007A3660970	Receiver Coupler, High Impedance, 970 Hz	A69	\$ 1,062.00
NYK:70007A3661180	Receiver Coupler, High Impedance, 1180 Hz	A69	\$ 1,062.00
NYK:70007A3661450	Receiver Coupler, High Impedance, 1450 Hz	A69	\$ 1,062.00
NYK:70007A3661770	Receiver Coupler, High Impedance, 1770 Hz	A69	\$ 1,062.00
NYK:70007A3662140	Receiver Coupler, High Impedance, 2140 Hz	A69	\$ 1,062.00
NYK:70007A3662630	Receiver Coupler, High Impedance, 2630 Hz	A69	\$ 1,062.00
NYK:70007A3663240	Receiver Coupler, High Impedance, 3240 Hz	A69	\$ 1,062.00
NYK:70007A3664000	Receiver Coupler, High Impedance, 4000 Hz	A69	\$ 1,062.00

Grade Crossing Auxiliary Systems Products			Price
NYK:70007A3990156	Line to Rail Transmitter Coupler, Standard Impedance, 156 Hz	A70	\$ 712.00
NYK:70007A3990211	Line to Rail Transmitter Coupler, Standard Impedance, 211 Hz	A70	\$ 712.00
NYK:70007A3990285	Line to Rail Transmitter Coupler, Standard Impedance, 285 Hz	A70	\$ 712.00
NYK:70007A3990348	Line to Rail Transmitter Coupler, Standard Impedance, 348 Hz	A70	\$ 712.00
NYK:70007A3990430	Line to Rail Transmitter Coupler, Standard Impedance, 430 Hz	A70	\$ 712.00
NYK:70007A3990525	Line to Rail Transmitter Coupler, Standard Impedance, 525 Hz	A70	\$ 712.00
NYK:70007A3990645	Line to Rail Transmitter Coupler, Standard Impedance, 645 Hz	A70	\$ 712.00
NYK:70007A3990790	Line to Rail Transmitter Coupler, Standard Impedance, 790 Hz	A70	\$ 712.00
NYK:70007A3990970	Line to Rail Transmitter Coupler, Standard Impedance, 970 Hz	A70	\$ 712.00
NYK:70007A3991180	Line to Rail Transmitter Coupler, Standard Impedance, 1180 Hz	A70	\$ 712.00
NYK:70007A3991450	Line to Rail Transmitter Coupler, Standard Impedance, 1450 Hz	A70	\$ 712.00
NYK:70007A3991770	Line to Rail Transmitter Coupler, Standard Impedance, 1770 Hz	A70	\$ 712.00
NYK:70007A3992140	Line to Rail Transmitter Coupler, Standard Impedance, 2140 Hz	A70	\$ 712.00
NYK:70007A3992630	Line to Rail Transmitter Coupler, Standard Impedance, 2630 Hz	A70	\$ 712.00
NYK:70007A3993240	Line to Rail Transmitter Coupler, Standard Impedance, 3240 Hz	A70	\$ 712.00
NYK:70007A3994000	Line to Rail Transmitter Coupler, Standard Impedance, 4000 Hz	A70	\$ 712.00
NYK:70007A3770156	Line to Rail Receiver Coupler, Standard Impedance, 156 Hz	A71	\$ 830.00
NYK:70007A3770211	Line to Rail Receiver Coupler, Standard Impedance, 211 Hz	A71	\$ 830.00
NYK:70007A3770285	Line to Rail Receiver Coupler, Standard Impedance, 285 Hz	A71	\$ 830.00
NYK:70007A3770348	Line to Rail Receiver Coupler, Standard Impedance, 348 Hz	A71	\$ 830.00
NYK:70007A3770430	Line to Rail Receiver Coupler, Standard Impedance, 430 Hz	A71	\$ 830.00
NYK:70007A3770525	Line to Rail Receiver Coupler, Standard Impedance, 525 Hz	A71	\$ 830.00
NYK:70007A3770645	Line to Rail Receiver Coupler, Standard Impedance, 645 Hz	A71	\$ 830.00
NYK:70007A3770790	Line to Rail Receiver Coupler, Standard Impedance, 790 Hz	A71	\$ 830.00
NYK:70007A3770970	Line to Rail Receiver Coupler, Standard Impedance, 970 Hz	A71	\$ 830.00
NYK:70007A3771180	Line to Rail Receiver Coupler, Standard Impedance, 1180 Hz	A71	\$ 830.00
NYK:70007A3771450	Line to Rail Receiver Coupler, Standard Impedance, 1450 Hz	A71	\$ 830.00
NYK:70007A3771770	Line to Rail Receiver Coupler, Standard Impedance, 1770 Hz	A71	\$ 851.00
NYK:70007A3772140	Line to Rail Receiver Coupler, Standard Impedance, 2140 Hz	A71	\$ 830.00
NYK:70007A3772630	Line to Rail Receiver Coupler, Standard Impedance, 2630 Hz	A71	\$ 830.00
NYK:70007A3773240	Line to Rail Receiver Coupler, Standard Impedance, 3240 Hz	A71	\$ 830.00
NYK:70007A3774000	Line to Rail Receiver Coupler, Standard Impedance, 4000 Hz	A71	\$ 830.00
NYK:8V617-0100	Simulated Track Inductor, 100'	A74	\$ 106.00
NYK:8V617-0200	Simulated Track Inductor, 200'	A74	\$ 106.00
NYK:8V617-0400	Simulated Track Inductor, 400'	A74	\$ 106.00
NYK:8V617-0600	Simulated Track Inductor, 600'	A74	\$ 106.00
NYK:8V617-0800	Simulated Track Inductor, 800'	A74	\$ 106.00
NYK:8V617-1000	Simulated Track Inductor, 1000'	A74	\$ 106.00
NYK:8V617-1200	Simulated Track Inductor, 1200'	A74	\$ 106.00
NYK:8V617-1400	Simulated Track Inductor, 1400'	A74	\$ 106.00
NYK:8V617-1600	Simulated Track Inductor, 1600'	A74	\$ 106.00
NYK:8V617-1800	Simulated Track Inductor, 1800'	A74	\$ 106.00
NYK:8V617-2000	Simulated Track Inductor, 2000'	A74	\$ 106.00
NYK:8V617-2200	Simulated Track Inductor, 2200'	A74	\$ 106.00
NYK:8V617-2400	Simulated Track Inductor, 2400'	A74	\$ 106.00
NYK:8V617-2600	Simulated Track Inductor, 2600'	A74	\$ 106.00
NYK:8V617-2800	Simulated Track Inductor, 2800'	A74	\$ 106.00
NYK:8V617-3000	Simulated Track Inductor, 3000'	A74	\$ 106.00
NYK:8V617-4000	Simulated Track Inductor, 4000'	A74	\$ 106.00
NYK:8V617-4400	Simulated Track Inductor, 4400'	A74	\$ 106.00
NYK:8V617-5200	Simulated Track Inductor, 5200'	A74	\$ 106.00
NYK:021500-5X	Test Shunt, TS-1	A76	\$ 290.00
NYK:021500-5VGX	Test Shunt, TS-1	A76	\$ 502.00
NYK:021500-6X	Test Shunt, TS-1B	A76	\$ 300.00
NYK:021500-6VGX	Test Shunt, TS-1	A76	\$ 502.00
NYK:021500-25X	Super Shunt	A76	\$ 482.00

Grade Crossing Auxiliary Systems Products			Price	
NYK:021500-25VGX	Super Shunt	A76	\$	402.00
NYK:021500-40X	Test Shunt, TS-1B	A76	\$	361.00
NYK:021500-40VGX	Test Shunt, TS-1	A76	\$	502.00
NYK:021500-42X	Test Shunt, TS-1	A76	\$	310.00
NYK:021500-56X	Test Shunt, TS-1	A76	\$	674.00
NYK:021500-57X	Test Shunt, TS-4	A76	\$	706.00

Grade Crossing Signaling Systems Products			Price
NYK:9000255270001	S60, Entrance Gate Printed Circuit Board	A78	\$ 875.00
NYK:9000255310001	S60, Exit Gate Printed Circuit Board	A78	\$ 622.00
NYK:8000802860002	S60, MTSS Printed Circuit Board	A78	\$ 578.00
NYK:9000255280001	S60, Barrier Arm Light Printed Circuit Board	A78	\$ 101.00
NYK:074007-X001	S60, Entrance Gate Mechanism, 4 Cam, 12VDC Defroster, w/o MTSS	A79	\$ 5,737.00
NYK:074007-X001A1	S60, Entrance Gate Mechanism, 4 Cam, 12VDC Defroster, w/o MTSS	A79	\$ 5,778.00
NYK:074007-X001B1	S60, Entrance Gate Mechanism, 4 Cam, 12VDC Defroster, w/ MTSS	A79	\$ 6,293.00
NYK:074007-X001A2	S60, Entrance Gate Mechanism, 4 Cam, 24VDC Defroster, w/o MTSS	A79	\$ 5,737.00
NYK:074007-X001B2	S60, Entrance Gate Mechanism, 4 Cam, 24VDC Defroster, w/ MTSS	A79	\$ 6,293.00
NYK:074007-X001A3	S60, Entrance Gate Mechanism, 4 Cam, 115VAC Defroster, w/o MTSS	A79	\$ 5,737.00
NYK:074007-X001B3	S60, Entrance Gate Mechanism, 4 Cam, 115VAC Defroster, w/ MTSS	A79	\$ 5,830.00
NYK:074007-X002	S60, Entrance Gate Mechanism, 5 Cam, 12VDC Defroster, w/o MTSS	A79	\$ 5,789.00
NYK:074007-X002A1	S60, Entrance Gate Mechanism, 5 Cam, 12VDC Defroster, w/o MTSS	A79	\$ 5,830.00
NYK:074007-X002B1	S60, Entrance Gate Mechanism, 5 Cam, 12VDC Defroster, w/ MTSS	A79	\$ 6,345.00
NYK:074007-X002A2	S60, Entrance Gate Mechanism, 5 Cam, 24VDC Defroster, w/o MTSS	A79	\$ 5,830.00
NYK:074007-X002B2	S60, Entrance Gate Mechanism, 5 Cam, 24VDC Defroster, w/ MTSS	A79	\$ 6,345.00
NYK:074007-X002A3	S60, Entrance Gate Mechanism, 5 Cam, 115VAC Defroster, w/o MTSS	A79	\$ 5,830.00
NYK:074007-X002B3	S60, Entrance Gate Mechanism, 5 Cam, 115VAC Defroster, w/ MTSS	A79	\$ 6,345.00
NYK:074007-X003	S60, Entrance Gate Mechanism, 6 Cam, 12VDC Defroster, w/o MTSS	A80	\$ 5,840.00
NYK:074007-X003A1	S60, Entrance Gate Mechanism, 6 Cam, 12VDC Defroster, w/o MTSS	A80	\$ 5,881.00
NYK:074007-X003B1	S60, Entrance Gate Mechanism, 6 Cam, 12VDC Defroster, w/ MTSS	A80	\$ 6,396.00
NYK:074007-X003A2	S60, Entrance Gate Mechanism, 6 Cam, 24VDC Defroster, w/o MTSS	A80	\$ 5,881.00
NYK:074007-X003B2	S60, Entrance Gate Mechanism, 6 Cam, 24VDC Defroster, w/ MTSS	A80	\$ 6,396.00
NYK:074007-X003A3	S60, Entrance Gate Mechanism, 6 Cam, 115VAC Defroster, w/o MTSS	A80	\$ 5,157.00
NYK:074007-X003B3	S60, Entrance Gate Mechanism, 6 Cam, 115VAC Defroster, w/ MTSS	A80	\$ 6,396.00
NYK:074007-X004	S60, Entrance Gate Mechanism, 7 Cam, 12VDC Defroster, w/o MTSS	A80	\$ 5,892.00
NYK:074007-X004A1	S60, Entrance Gate Mechanism, 7 Cam, 12VDC Defroster, w/o MTSS	A80	\$ 5,933.00
NYK:074007-X004B1	S60, Entrance Gate Mechanism, 7 Cam, 12VDC Defroster, w/ MTSS	A80	\$ 6,448.00
NYK:074007-X004A2	S60, Entrance Gate Mechanism, 7 Cam, 24VDC Defroster, w/o MTSS	A80	\$ 5,933.00
NYK:074007-X004B2	S60, Entrance Gate Mechanism, 7 Cam, 24VDC Defroster, w/ MTSS	A80	\$ 6,396.00
NYK:074007-X004A3	S60, Entrance Gate Mechanism, 7 Cam, 115VAC Defroster, w/o MTSS	A80	\$ 5,933.00
NYK:074007-X004B3	S60, Entrance Gate Mechanism, 7 Cam, 115VAC Defroster, w/ MTSS	A80	\$ 5,275.00
NYK:074008-X001	S60, Exit Gate Mechanism, 4 Cam, 12VDC Defroster, w/o MTSS	A81	\$ 7,303.00
NYK:074008-X001A1	S60, Exit Gate Mechanism, 4 Cam, 12VDC Defroster, w/o MTSS	A81	\$ 7,344.00
NYK:074008-X001B1	S60, Exit Gate Mechanism, 4 Cam, 12VDC Defroster, w/ MTSS	A81	\$ 7,859.00
NYK:074008-X001A2	S60, Exit Gate Mechanism, 4 Cam, 24VDC Defroster, w/o MTSS	A81	\$ 7,344.00
NYK:074008-X001B2	S60, Exit Gate Mechanism, 4 Cam, 24VDC Defroster, w/ MTSS	A81	\$ 7,859.00
NYK:074008-X001A3	S60, Exit Gate Mechanism, 4 Cam, 115VAC Defroster, w/o MTSS	A81	\$ 7,344.00
NYK:074008-X001B3	S60, Exit Gate Mechanism, 4 Cam, 115VAC Defroster, w/ MTSS	A81	\$ 7,859.00
NYK:074008-X002	S60, Exit Gate Mechanism, 5 Cam, 12VDC Defroster, w/o MTSS	A81	\$ 7,354.00
NYK:074008-X002A1	S60, Exit Gate Mechanism, 5 Cam, 12VDC Defroster, w/o MTSS	A81	\$ 7,395.00
NYK:074008-X002B1	S60, Exit Gate Mechanism, 5 Cam, 12VDC Defroster, w/ MTSS	A81	\$ 7,910.00
NYK:074008-X002A2	S60, Exit Gate Mechanism, 5 Cam, 24VDC Defroster, w/o MTSS	A81	\$ 7,395.00
NYK:074008-X002B2	S60, Exit Gate Mechanism, 5 Cam, 24VDC Defroster, w/ MTSS	A81	\$ 7,910.00
NYK:074008-X002A3	S60, Exit Gate Mechanism, 5 Cam, 115VAC Defroster, w/o MTSS	A81	\$ 7,395.00
NYK:074008-X002B3	S60, Exit Gate Mechanism, 5 Cam, 115VAC Defroster, w/ MTSS	A81	\$ 7,910.00
NYK:074008-X003	S60, Exit Gate Mechanism, 6 Cam, 12VDC Defroster, w/o MTSS	A82	\$ 7,406.00
NYK:074008-X003A1	S60, Exit Gate Mechanism, 6 Cam, 12VDC Defroster, w/o MTSS	A82	\$ 7,457.00
NYK:074008-X003B1	S60, Exit Gate Mechanism, 6 Cam, 12VDC Defroster, w/ MTSS	A82	\$ 7,972.00
NYK:074008-X003A2	S60, Exit Gate Mechanism, 6 Cam, 24VDC Defroster, w/o MTSS	A82	\$ 7,457.00
NYK:074008-X003B2	S60, Exit Gate Mechanism, 6 Cam, 24VDC Defroster, w/ MTSS	A82	\$ 7,972.00
NYK:074008-X003A3	S60, Exit Gate Mechanism, 6 Cam, 115VAC Defroster, w/o MTSS	A82	\$ 7,457.00

Grade Crossing Signaling Systems Products			Price
NYK:074008-X003B3	S60, Exit Gate Mechanism, 6 Cam, 115VAC Defroster, w/ MTSS	A82	\$ 7,972.00
NYK:074008-X004	S60, Exit Gate Mechanism, 7 Cam, 12VDC Defroster, w/o MTSS	A82	\$ 7,406.00
NYK:074008-X004A1	S60, Exit Gate Mechanism, 7 Cam, 12VDC Defroster, w/o MTSS	A82	\$ 7,447.00
NYK:074008-X004B1	S60, Exit Gate Mechanism, 7 Cam, 12VDC Defroster, w/ MTSS	A82	\$ 7,962.00
NYK:074008-X004A2	S60, Exit Gate Mechanism, 7 Cam, 24VDC Defroster, w/o MTSS	A82	\$ 7,447.00
NYK:074008-X004B2	S60, Exit Gate Mechanism, 7 Cam, 24VDC Defroster, w/ MTSS	A82	\$ 7,962.00
NYK:074008-X004A3	S60, Exit Gate Mechanism, 7 Cam, 115VAC Defroster, w/o MTSS	A82	\$ 7,447.00
NYK:074008-X004B3	S60, Exit Gate Mechanism, 7 Cam, 115VAC Defroster, w/ MTSS	A82	\$ 7,962.00
NYK:074018-X	Hold Clear Wheel Assembly	A83	\$ 2,245.00
NYK:9000255330001	24 V - 12 V S60 Power Supply	A83	\$ 1,705.00
NYK:8000803010001	EBell, Loud Tone, Fast Pulse Rate, w/ Micraphone Sensor	A86	\$ 595.00
NYK:8000803010002	EBell, Loud Tone, Slow Pulse Rate, w/ Micraphone Sensor	A86	\$ 595.00
NYK:8000803010003	EBell, Soft Tone, Fast Pulse Rate, w/ Micraphone Sensor	A86	\$ 595.00
NYK:8000803010004	EBell, Soft Tone, Slow Pulse Rate, w/ Micraphone Sensor	A86	\$ 608.00
NYK:8000803011001	EBell, Loud Tone, Fast Pulse Rate, w/o Micraphone Sensor	A86	\$ 450.00
NYK:8000803011002	EBell, Loud Tone, Slow Pulse Rate, w/o Micraphone Sensor	A86	\$ 450.00
NYK:8000803011003	EBell, Soft Tone, Fast Pulse Rate, w/o Micraphone Sensor	A86	\$ 381.00
NYK:8000803011004	EBell, Soft Tone, Slow Pulse Rate, w/o Micraphone Sensor	A86	\$ 442.00
NYK:035048-500X	Adapter Mount - From 4" pipe to 8" pipe	A88	\$ 110.00
NYK:035063-X	Adapter Mount - From 4" pipe to 10" pipe	A88	\$ 142.00
NYK:035062-X	Adapter Mount - From 4" pipe to 12" pipe	A88	\$ 146.00
NYK:040290-X100	Adapter Mount - Mast Offset Bracket	A88	\$ 178.00
NYK:035045-502	Pinnacle, Cast Aluminum w/o Hardware	A90	\$ 24.29
NYK:035045-11X	Pinnacle, Cast Aluminum w/ Hardware	A90	\$ 25.24
NYK:035045-502B	Pinnacle, Cast Aluminum w/o Hardware, Black	A90	\$ 79.31
NYK:035045-502XEB	Pinnacle, Cast Aluminum w/ Hardware, Black	A90	\$ 79.00
NYK:035044-501	Pinnacle, Cast Aluminum w/o Hardware and Wire Chase	A91	\$ 79.31
NYK:035044-501X	Pinnacle, Cast Aluminum w/ Hardware and Wire Chase	A91	\$ 79.31
NYK:041442-70X	Sidelight Cantilevered Mount 4" Mast 36" Offset 1 Way Version	A94	\$ 766.00
NYK:041442-26X	Sidelight Cantilevered Mount 5" Mast 36" Offset 1 Way Version	A94	\$ 845.00
NYK:041442-27X	Sidelight Cantilevered Mount 4" Mast 42" Offset 1 Way Version	A94	\$ 898.00
NYK:041442-55X	Sidelight Cantilevered Mount 5" Mast 36" Offset 2 Way Version, 45°	A94	\$ 968.00
NYK:041442-53X-1	Sidelight Cantilevered Mount 5" Mast 36" Offset 2 Way Version, 90°	A95	\$ 812.00
NYK:041442-53X-2	Sidelight Cantilevered Mount 5" Mast 36" Offset 2 Way Version, 135°	A95	\$ 832.00
NYK:041442-53X-3	Sidelight Cantilevered Mount 5" Mast 36" Offset 2 Way Version, 150°	A95	\$ 812.00
NYK:041442-25X	Sidelight Cantilevered Mount 4" Mast 36" Offset Extension	A96	\$ 174.00
NYK:041442-515	Sidelight Cantilevered Mount Boot	A96	\$ 80.32
NYK:259371-T10128	Tubular Sweep High Wind Bracket 4" mounting	A98	\$ 155.00
NYK:076203-47X	Tubular Sweep High Wind Bracket 5" mounting	A98	\$ 163.00
NYK:076203-28X	Structural High Wind Bracket 4" mounting	A98	\$ 350.00
NYK:076203-518X	Structural High Wind Bracket 5" mounting	A98	\$ 299.00
NYK:076203-59X	High Wind Bracket, 27"	A99	\$ 237.00
NYK:076203-67X	High Wind Bracket, 25 3/4"	A99	\$ 255.00
NYK:042003-18	Crossarm Junction Box w/ Control Box Vents	A102	\$ 114.00
NYK:042041	Crossarm Junction Box Cover Plate	A102	\$ 5.53
NYK:042041-X	Crossarm Junction Box Cover Plate Kit	A102	\$ 14.47
NYK:041291	Crossarm Junction Box Gasket	A103	\$ 0.53

Grade Crossing Signaling Systems Products			Price
NYK:041279-7	Crossarm Junction Box 90° Lamp Mounting Extension Arm	A103	\$ 54.80
NYK:041279-500	Crossarm Junction Box 90° Lamp Mounting Extension Arm	A103	\$ 61.45
NYK:041279-19	Crossarm Junction Box 90° Lamp Mounting Extension Arm	A103	\$ 82.52
NYK:042027-4	Crossarm Junction Box Offset Lamp Mounting Extension Arm	A104	\$ 47.17
NYK:042027-3	Crossarm Junction Box Offset Lamp Mounting Extension Arm	A104	\$ 47.17
NYK:041279-501	Crossarm Junction Box 90° Transition	A104	\$ 133.00
NYK:042006-X	Crossarm Control Box Cover	A104	\$ 37.15
NYK:042073-4BX	Crossarm Junction Box Terminal Box Assembly, 4" mounting	A105	\$ 484.00
NYK:042073-4X01	Crossarm Junction Box Terminal Box Assembly, 4" mounting	A105	\$ 493.00
NYK:042073-4X02	Crossarm Junction Box Terminal Box Assembly, 4" mounting	A105	\$ 493.00
NYK:042073-7BX	Crossarm Junction Box Terminal Box Assembly, 5" mounting	A106	\$ 484.00
NYK:042073-7X01	Crossarm Junction Box Terminal Box Assembly, 5" mounting	A106	\$ 493.00
NYK:042073-7X02	Crossarm Junction Box Terminal Box Assembly, 5" mounting	A106	\$ 493.00
NYK:042950-X	FLX-12 Housing	A108	\$ 381.00
NYK:040405-4730	FLX RED 12" Lens 20° / 32° Bullseye	A108	\$ 69.00
NYK:040405-5230	FLX RED 12" Lens 30° / 15° Bullseye	A108	\$ 69.00
NYK:040405-5030	FLX RED 12" Lens 70° / 0° Bullseye	A108	\$ 69.00
NYK:042000-000180	FLX-12 Housing w/ RED 12" Lens 30° / 15° Bullseye, 10V-25W Bulb	A108	\$ 411.00
NYK:042000-000601	FLX-12 Housing w/ RED 12" Lens 30° / 15° Bullseye, 10V-25W Gem Bulb	A108	\$ 411.00
NYK:042000-000250	FLX-12 Housing w/ RED 12" Lens 30° / 15° Bullseye, 10V-18W Bulb	A108	\$ 411.00
NYK:042000-000689	FLX-12 Housing w/ RED 12" Lens 30° / 15° Bullseye, 10V-18W Gem Bulb	A108	\$ 411.00
NYK:042975-LX	FLX-4000 Housing	A108	\$ 245.00
NYK:042975-9X	FLX-4000 Housing w/ RED 12" Gelcore® LED Module	A108	\$ 773.00
NYK:042975-15X	FLX-4000 Housing w/ RED 12" RDG® LED Module	A108	\$ 804.00
NYK:042975-8X	FLX-4000 Housing w/ RED 12" Dialight® LED Module	A108	\$ 706.00
NYK:042005-103	FLX Aluminum 12" Long Visor w/o Hardware	A109	\$ 41.09
NYK:042005-103X	FLX Aluminum 12" Long Visor w/ Hardware	A109	\$ 41.09
NYK:042005-80	FLX Polycarbonate 16" Long Visor w/o Hardware	A109	\$ 26.86
NYK:042005-80X	FLX Polycarbonate 16" Long Visor w/ Hardware	A109	\$ 67.55
NYK:042005-30	FLX Steel 12" Long Visor w/o Hardware	A109	\$ 33.48
NYK:042005-30AX	FLX Steel 12" Long Visor w/ Hardware	A109	\$ 33.48
NYK:042004-32	FLX (1) Aspect Aluminum Background w/o Hardware	A109	\$ 62.83
NYK:042004-32X	FLX (1) Aspect Aluminum Background w/ Hardware	A109	\$ 64.89
NYK:042004-41	FLX (1) Aspect Polycarbonate Background w/o Hardware	A109	\$ 26.86
NYK:042004-41AX	FLX (1) Aspect Polycarbonate Background w/ Hardware	A109	\$ 26.86
NYK:042004-30	FLX (1) Aspect Steel Background w/o Hardware	A109	\$ 43.26
NYK:042004-30X	FLX (1) Aspect Steel Background w/ Hardware	A109	\$ 50.47
NYK:042003-M121W	FLX-12, One Way Incandescent Main Mast Assembly	A110	\$ 1,429.00
NYK:042003-A121W	FLX-12, One Way Incandescent Arm Assembly	A110	\$ 1,389.00
NYK:042003-GM12	FLX-12, One Way Incandescent Gate Assembly	A110	\$ 1,429.00
NYK:042003-SL121W	FLX-12, One Way Incandescent Main Mast w/ Sidelight Assembly	A110	\$ 2,647.00
NYK:042003-M122W	FLX-12, Two Way Incandescent Main Mast Assembly	A110	\$ 2,595.00
NYK:042003-A122W	FLX-12, Two Way Incandescent Arm Assembly	A110	\$ 2,555.00
NYK:042003-SL122W	FLX-12, Two Way Incandescent Main Mast w/ Sidelight Assembly	A110	\$ 4,058.00
NYK:042003-MLED121W	FLX-4000, One Way Incandescent Main Mast Assembly	A110	\$ 2,494.00
NYK:042003-ALED121W	FLX-4000, One Way Incandescent Arm Assembly	A110	\$ 2,454.00
NYK:042003-GM12	FLX-4000, One Way Incandescent Gate Assembly	A110	\$ 1,429.00

Grade Crossing Signaling Systems Products			Price
NYK:042003-SLLED121W	FLX-4000, One Way Incandescent Main Mast w/ Sidelight Assembly	A110	\$ 2,547.00
NYK:042003-MLED122W	FLX-4000, Two Way Incandescent Main Mast Assembly	A110	\$ 3,378.00
NYK:042003-ALED122W	FLX-4000, Two Way Incandescent Arm Assembly	A110	\$ 3,338.00
NYK:042003-SLLED122W	FLX-4000, Two Way Incandescent Main Mast w/ Sidelight Assembly	A110	\$ 3,378.00
NYK:035200-X	English, "Railroad Crossing", Standard Intensity, Single Sided w/o Mast Hardware	---	\$ 123.00
NYK:035200-3BX	English, "Railroad Crossing", Standard Intensity, Single Sided w/ 4" Mast Hardware	---	\$ 201.00
NYK:035200-17BX	English, "Railroad Crossing", Standard Intensity, Single Sided w/ 5" Mast Hardware	---	\$ 201.00
NYK:035200-DXD	English, "Railroad Crossing", Standard Intensity, Double Sided w/o Mast Hardware	---	\$ 304.00
NYK:035200-3DXD	English, "Railroad Crossing", Standard Intensity, Double Sided w/ 4" Mast Hardware	---	\$ 381.00
NYK:035200-17DXD	English, "Railroad Crossing", Standard Intensity, Double Sided w/ 5" Mast Hardware	---	\$ 381.00
NYK:035200-523X	English, "Railroad Crossing", High Intensity, Single Sided w/o Mast Hardware	---	\$ 155.00
NYK:035200-3HBX	English, "Railroad Crossing", High Intensity, Single Sided w/ 4" Mast Hardware	---	\$ 242.00
NYK:035200-17HBX	English, "Railroad Crossing", High Intensity, Single Sided w/ 5" Mast Hardware	---	\$ 242.00
NYK:035200-HDXD	English, "Railroad Crossing", High Intensity, Double Sided w/o Mast Hardware	---	\$ 355.00
NYK:035200-3HDXD	English, "Railroad Crossing", High Intensity, Double Sided w/ 4" Mast Hardware	---	\$ 400.00
NYK:035200-17HDXD	English, "Railroad Crossing", High Intensity, Double Sided w/ 5" Mast Hardware	---	\$ 525.00
NYK:070755-34G	Short Counterweight Plate	A112	\$ 96.16
NYK:070755-4G	Long Counterweight Plate	A112	\$ 155.00
NYK:070756-7X	Counterweight Mounting Plate	A112	\$ 160.00
NYK:070925-X	Clamp and Roller Assembly	A112	\$ 45.02
NYK:070923-3	Barrier Arm Support Arm Hub	A112	\$ 142.00
NYK:070920-L	Barrier Arm Left Hand Support Arm, Long	A113	\$ 571.00
NYK:070920-LX	Barrier Arm Left Hand Support Arm Assembly, Long	A113	\$ 725.00
NYK:070920-R	Barrier Arm Right Hand Support Arm, Long	A113	\$ 571.00
NYK:070920-RX	Barrier Arm Right Hand Support Arm Assembly, Long	A113	\$ 725.00
NYK:070921-L	Barrier Arm Left Hand Support Arm, Short	A114	\$ 447.00
NYK:070921-LX	Barrier Arm Left Hand Support Arm Assembly, Short	A114	\$ 554.00
NYK:070921-R	Barrier Arm Right Hand Support Arm, Short	A114	\$ 447.00
NYK:070921-RX	Barrier Arm Right Hand Support Arm Assembly, Short	A114	\$ 554.00
NYK:076227-7X1	Coverison Bracket, Complete Assembly w/ Cast Adapter	A116	\$ 619.00
NYK:076203-510X	Coverison Bracket, Cast Adapter Mount w/ Mounting Pin	A116	\$ 240.00
NYK:076227-22X1	Coverison Bracket, Complete Assembly w/ Fabricated Adapter	A117	\$ 758.00
NYK:076203-501X	Coverison Bracket, Fabricated Adapter Mount w/ Mounting Pin	A117	\$ 399.00
NYK:076215-X	Coverison Bracket, Shear Bolt Assembly	A117	\$ 6.63
NYK:076203-506X	Coverison Bracket, Replacement Mounting Pin	A117	\$ 62.92
NYK:076260-8AHX	Barrier Arm Base Seciton 8' Long, Aluminum, High Intensity Tape	A118	\$ 261.00
NYK:076260-8AHD	Barrier Arm Base Seciton 8' Long, Aluminum, Diamond Grade Tape	A118	\$ 261.00
NYK:076260-16AHX	Barrier Arm Base Seciton 16' Long, Aluminum, High Intensity Tape	A118	\$ 484.00
NYK:076260-16AHD	Barrier Arm Base Seciton 16' Long, Aluminum, Diamond Grade Tape	A118	\$ 307.00
NYK:076260-16HX	Barrier Arm Base Seciton 16' Long, Fiberglass, High Intensity Tape	A118	\$ 221.00
NYK:076260-16HDX	Barrier Arm Base Seciton 16' Long, Fiberglass, Diamond Grade Tape	A118	\$ 258.00
NYK:076261-8HX	Barrier Arm 2nd Section 8' Long, Aluminum, High Intensity Tape	A118	\$ 213.00
NYK:076261-8HDX	Barrier Arm 2nd Section 8' Long, Aluminum, Diamond Grade Tape	A118	\$ 145.00
NYK:076261-12HX	Barrier Arm 2nd Section 16' Long, Aluminum, High Intensity Tape	A118	\$ 259.00
NYK:076261-12HDX	Barrier Arm 2nd Section 16' Long, Aluminum, Diamond Grade Tape	A118	\$ 182.00
NYK:076261-16HX	Barrier Arm 2nd Section 16' Long, Fiberglass, High Intensity Tape	A118	\$ 213.00

Grade Crossing Signaling Systems Products			Price
NYK:076261-16HDX	Barrier Arm 2nd Section 16' Long, Fiberglass, Diamond Grade Tape	A118	\$ 396.00
NYK:076262-8HX	Barrier Arm 3rd Section 8' Long, Aluminum, High Intensity Tape	A118	\$ 130.00
NYK:076262-8HDX	Barrier Arm 3rd Section 8' Long, Aluminum, Diamond Grade Tape	A118	\$ 108.00
NYK:076262-12HX	Barrier Arm 3rd Section 16' Long, Aluminum, High Intensity Tape	A118	\$ 210.00
NYK:076262-12HDX	Barrier Arm 3rd Section 16' Long, Aluminum, Diamond Grade Tape	A118	\$ 210.00
NYK:076262-16HX	Barrier Arm 3rd Section 16' Long, Fiberglass, High Intensity Tape	A118	\$ 215.00
NYK:076262-16HDX	Barrier Arm 3rd Section 16' Long, Fiberglass, Diamond Grade Tape	A118	\$ 229.00
NYK:076203-6	Barrier Arm Adapter Sleeve 1' to 11' Sleeve, Aluminum	A118	\$ 31.14
NYK:076203-4	Barrier Arm Adapter Sleeve 12' to 24' Sleeve, Aluminum	A118	\$ 51.87
NYK:076203-5	Barrier Arm Adapter Sleeve 25' to 40' Sleeve, Aluminum	A118	\$ 142.00
NYK:8000802810001	Barrier Arm Tip Sensor	A119	\$ 402.00
NYK:8000802810002	Barrier Arm Tip Sensor Assembly	A119	\$ 464.00
NYK:075955-XM694	Barrier Arm Tip Sensor Mounting Bracket	A119	\$ 49.17
NYK:075970-AX	Barrier Arm Light Assembly	A119	\$ 65.00
NYK:041901-AX	Split Bases w/o Junction Boxes for Light Loading for 4" Masts	A122	\$ 783.00
NYK:041902-AX	Split Bases w/o Junction Boxes for Heavy Loading For 4" Masts	A122	\$ 1,006.00
NYK:041933-X	Split Bases w/o Junction Boxes for Heavy Loading For 5" Masts	A122	\$ 732.00
NYK:041918-X	Split Bases w/o Junction Boxes for Heavy Loading For 8" Masts	A122	\$ 975.00
NYK:041931-1X	Split Bases w/ Junction Boxes for 4" Masts	A122	\$ 1,391.00
NYK:041931-2X	Split Bases w/ Junction Boxes for 5" Masts	A122	\$ 1,000.00

Wayside Control Systems Products			Price
NYK:9000535110001	GEO®, Empty Two Track Extended	B2	\$ 1,744.00
NYK:9112535102000	GEO®, Comprehensive Two Track Extended	B2	\$ 14,958.00
NYK:9000535140001	GEO®, Empty Three Track Extended	B2	\$ 3,236.00
NYK:93125351323003	GEO®, Comprehensive Three Track Extended	B2	\$ 24,898.00
NYK:8000804030002	Non Appliance CPU II+ Module	B3	Call For Pricing
NYK:8000804030003	Appliance CPU II+ Module	B3	Call For Pricing
NYK:9000532850001	Track Module, Standard Power	B3	\$ 1,873.00
NYK:9000532850003	Track Module, High Power	B3	\$ 2,808.00
NYK:8000804130001	Relay Input /Output (RIO) Module	B4	\$ 2,187.00
NYK:9000532840001	Colorlight Lamp Module	B4	\$ 2,335.00
NYK:8000804380001	External Configuration Device (ECD Plus) Module	B5	\$ 231.00
NYK:8000804380002	External Configuration Device (ECD Plus) Module	B5	\$ 199.00
NYK:9000506920002	Universal Local Control Panel	B6	\$ 4,085.00
NYK:Z610395850001	GEO®, Top Mounting Bracket, Keyhole	B7	\$ 160.00
NYK:Z610395850002	GEO®, Bottom Mounting Bracket, Keyhole	B7	\$ 160.00
NYK:Z610395850003	GEO®, Top Mounting Bracket, Slotted	B8	\$ 160.00
NYK:Z610395850004	GEO®, Bottom Mounting Bracket, Slotted	B8	\$ 160.00
NYK:80008055000100	VIU 8i Module w/o Relay I/O Module, w/o Mounting Plate	B10	\$ 4,288.00
NYK:80008055000110	VIU 8i Module w/ Relay I/O Module, w/o Mounting Plate	B10	\$ 6,225.00
NYK:80008055000101	VIU 8i Module w/o Relay I/O Module, w/ Mounting Plate	B10	\$ 4,288.00
NYK:80008055000111	VIU 8i Module w/ Relay I/O Module, w/ Mounting Plate	B10	\$ 6,225.00
NYK:80008055000102	VIU 8i Module w/o Relay I/O Module, w/ Mounting Plate	B11	\$ 4,288.00
NYK:80008055000112	VIU 8i Module w/ Relay I/O Module, w/ Mounting Plate	B11	\$ 6,225.00
NYK:80008055500100	VIU 16i Module w/o Relay I/O Module, w/o Mounting Plate	B12	\$ 4,948.00
NYK:80008055500110	VIU 16i Module w/ Relay I/O Module, w/o Mounting Plate	B12	\$ 6,886.00
NYK:80008055500101	VIU 16i Module w/o Relay I/O Module, w/ Mounting Plate	B12	\$ 4,948.00
NYK:80008055500111	VIU 16i Module w/ Relay I/O Module, w/ Mounting Plate	B12	\$ 6,886.00
NYK:80008055500102	VIU 16i Module w/o Relay I/O Module, w/ Mounting Plate	B13	\$ 4,948.00
NYK:80008055500112	VIU 16i Module w/ Relay I/O Module, w/ Mounting Plate	B13	\$ 6,886.00
NYK:80008051500100	VIU 20 Module w/o Relay I/O Module, w/o Mounting Plate	B14	\$ 8,954.00
NYK:80008051500110	VIU 20 Module w/ Relay I/O Module, w/o Mounting Plate	B14	\$ 10,891.00
NYK:80008051500101	VIU 20 Module w/o Relay I/O Module, w/ Mounting Plate	B14	\$ 8,954.00
NYK:80008051500111	VIU 20 Module w/ Relay I/O Module, w/ Mounting Plate	B14	\$ 10,891.00
NYK:80008051500102	VIU 20 Module w/o Relay I/O Module, w/ Mounting Plate	B15	\$ 8,954.00
NYK:80008051500112	VIU 20 Module w/ Relay I/O Module, w/ Mounting Plate	B15	\$ 10,891.00
NYK:80008054000100	VIU 20e Module w/o Relay I/O Module, w/o Mounting Plate	B16	\$ 8,406.00
NYK:80008054000110	VIU 20e Module w/ Relay I/O Module, w/o Mounting Plate	B16	\$ 10,343.00
NYK:80008054000101	VIU 20e Module w/o Relay I/O Module, w/ Mounting Plate	B16	\$ 8,406.00
NYK:80008054000111	VIU 20e Module w/ Relay I/O Module, w/ Mounting Plate	B16	\$ 10,343.00
NYK:80008054000102	VIU 20e Module w/o Relay I/O Module, w/ Mounting Plate	B17	\$ 8,406.00
NYK:80008054000112	VIU 20e Module w/ Relay I/O Module, w/ Mounting Plate	B17	\$ 10,343.00
NYK:8000805260000	VIU-CAT Module w/o Relay I/O Module, w/o Mounting Plate	B18	\$ 13,582.00
NYK:8000805260001	VIU-CAT Module w/o Relay I/O Module, w/ Mounting Plate	B18	\$ 13,582.00
NYK:8000805260002	VIU-CAT Module w/o Relay I/O Module, w/ Mounting Plate	B18	\$ 13,582.00
NYK:8000806720000	PTC Condole Unit w/o GPS, w/o Mounting Plate	B22	\$ 4,679.00
NYK:8000806720001	PTC Condole Unit w/o GPS, w/ Mounting Plate	B22	\$ 4,797.00
NYK:8000806720010	PTC Condole Unit w/ GPS, w/o Mounting Plate	B22	\$ 5,320.00

Wayside Control Systems Products			Price
NYK:8000806720011	PTC Condole Unit w/ GPS, w/ Mounting Plate	B22	\$ 5, 295.00
WayConnex	Trackguard® WayConnex Wayside Signaling System	B24	Call For Pricing
WayTraX	Clearguard® WayTraX Module	B24	Call For Pricing
Wayside Communications Systems Products			
	Siemens offers a wide variety of Wayside Communication equipment. Please call for additional details and pricing		

Wayside Signaling Systems Products			Price
NYK:044600-01X	CLS-20R Housing	B44	\$ 342.00
NYK:044620-L12G	Pharos Wayside LED Module, Long Range Green	--	Call for Pricing
NYK:044620-L12Y	Pharos Wayside LED Module, Long Range Yellow	--	Call for Pricing
NYK:044620-L12R	Pharos Wayside LED Module, Long Range Red	--	Call for Pricing
NYK:044620-L12L	Pharos Wayside LED Module, Long Range Lunar White	--	Call for Pricing
NYK:044620-M12G	Pharos Wayside LED Module, Medium Range Green	--	Call for Pricing
NYK:044620-M12Y	Pharos Wayside LED Module, Medium Range Yellow	--	Call for Pricing
NYK:044620-M12R	Pharos Wayside LED Module, Medium Range Red	--	Call for Pricing
NYK:044620-M12L	Pharos Wayside LED Module, Medium Range Lunar White	--	Call for Pricing
NYK:044036-1	Locking Rod (1) Aspect	B44	\$ 33.95
NYK:044036-2	Locking Rod (2) Aspect	B44	\$ 33.95
NYK:044036	Locking Rod (3) Aspect	B44	\$ 33.95
NYK:044006-1X	Clamp On Sighting Tool	B44	\$ 557.00
NYK:044004	Lampholder Post	B44	\$ 3.33
NYK:044005	Lampholder Slide	B44	\$ 0.93
NYK:042019-10	Bulb Socket	B44	\$ 8.96
NYK:042005-107	Aluminum 6 3/8" Long Visor w/o Hardware	B45	\$ 27.58
NYK:042005-107X	Aluminum 6 3/8" Long Visor w/ Hardware	B45	\$ 28.27
NYK:044018	Aluminum 12" Long Visor w/o Hardware	B45	\$ 35.15
NYK:044018-X	Aluminum 12" Long Visor w/ Hardware	B45	\$ 35.15
NYK:042005-19	Polycarbonate 6 3/8" Long Visor w/o Hardware	B45	\$ 22.66
NYK:042005-19X	Polycarbonate 6 3/8" Long Visor w/ Hardware	B45	\$ 34.69
NYK:042005-147	Polycarbonate 16" Long Visor w/o Hardware	B45	\$ 31.36
NYK:042005-147X	Polycarbonate 16" Long Visor w/ Hardware	B45	\$ 31.36
NYK:042005-35	Steel 6 3/8" Long Visor w/o Hardware	B45	\$ 21.36
NYK:042005-35X	Steel 6 3/8" Long Visor w/ Hardware	B45	\$ 21.36
NYK:042005-130	(1) Aspect Aluminum Snowshields w/o Hardware	B46	\$ 256.00
NYK:042005-130X	(1) Aspect Aluminum Snowshields w/ Hardware	B46	\$ 315.00
NYK:042005-131	(2) Aspect Aluminum Snowshields w/o Hardware	B46	\$ 318.00
NYK:042005-131X	(2) Aspect Aluminum Snowshields w/ Hardware	B46	\$ 377.00
NYK:042005-132	(3) Aspect Aluminum Snowshields w/o Hardware	B46	\$ 380.00
NYK:042005-132X	(3) Aspect Aluminum Snowshields w/ Hardware	B46	\$ 439.00
NYK:042005-128	(1) Aspect Steel Snowshields w/o Hardware	B46	\$ 338.00
NYK:042005-128X	(1) Aspect Steel Snowshields w/ Hardware	B46	\$ 397.00
NYK:042005-125	(2) Aspect Steel Snowshields w/o Hardware	B46	\$ 415.00
NYK:042005-125X	(2) Aspect Steel Snowshields w/ Hardware	B46	\$ 474.00
NYK:042005-115	(3) Aspect Steel Snowshields w/o Hardware	B46	\$ 492.00
NYK:042005-115X	(3) Aspect Steel Snowshields w/ Hardware	B46	\$ 551.00
NYK:044021-5	(1) Aspect Aluminum Background w/o Hardware	B47	\$ 211.00
NYK:044021-X	(1) Aspect Aluminum Background w/ Hardware	B47	\$ 211.00
NYK:044020-7	(2) Aspect Aluminum Background w/o Hardware	B47	\$ 253.00
NYK:044020-X	(2) Aspect Aluminum Background w/ Hardware	B47	\$ 253.00
NYK:044019-11	(3) Aspect Aluminum Background w/o Hardware	B47	\$ 296.00
NYK:044019-X	(3) Aspect Aluminum Background w/ Hardware	B47	\$ 296.00
NYK:044021-4	(1) Aspect Polycarbonate Background w/o Hardware	B47	\$ 64.89
NYK:044021-1X	(1) Aspect Polycarbonate Background w/ Hardware	B47	\$ 64.89
NYK:044020-6	(2) Aspect Polycarbonate Background w/o Hardware	B47	\$ 157.00
NYK:044020-1X	(2) Aspect Polycarbonate Background w/ Hardware	B47	\$ 157.00
NYK:044019-10	(3) Aspect Polycarbonate Background w/o Hardware	B47	\$ 217.00
NYK:044019-1X	(3) Aspect Polycarbonate Background w/ Hardware	B47	\$ 217.00

Wayside Signaling Systems Products			Price
NYK:044021-6	(1) Aspect Steel Background w/o Hardware	B47	\$ 124.00
NYK:044021-2X	(1) Aspect Steel Background w/ Hardware	B47	\$ 124.00
NYK:044020-8	(2) Aspect Steel Background w/o Hardware	B47	\$ 176.00
NYK:044020-2X	(2) Aspect Steel Background w/ Hardware	B47	\$ 176.00
NYK:044019-12	(3) Aspect Steel Background w/o Hardware	B47	\$ 282.00
NYK:044019-2X	(3) Aspect Steel Background w/ Hardware	B47	\$ 282.00
NYK:042005-134	CLS-20R, Visor Brace	B48	\$ 40.71
NYK:042005-135	CLS-20R, Visor Brance Angle	B48	\$ 17.32
NYK:042077-500X	Hardware Kit for Visors, Snowshields and Backgrounds	B48	\$ 7.37
NYK:044603-9GX	CLS-20R, Lens Bracket	B48	\$ 217.00
NYK:044008-1X	CLS-20R, Module Lifting Bracket	B49	\$ 33.39
NYK:044603-1RX	CLS-20R, Lens Bracket Assembly	B49	\$ 192.00
NYK:042258-2	CLS Anti Phantom Screen Lens	B49	\$ 19.96
NYK:044607-BX	CLS Blackout Lens Kit	B49	\$ 88.26
NYK:044011-4X	Top of Mast Bracket	B50	\$ 545.00
NYK:044011-5X	Top of Mast Bracket	B50	\$ 621.00
NYK:044011-14X	Top of Mast Bracket	B50	\$ 1,232.00
Wayside Wireless Pole Line Products			Price
NYK:9000534570002	Wayside Access Gateway	B52	\$ 2,531.00
NYK:9000533550001	ESSR, 2.4 GHz, DES 56, TDD	B54	\$ 3,594.00
NYK:9000533550002	ESSR, 2.4 GHz, DES 56, ATC	B54	\$ 3,811.00
NYK:9000533550003	ESSR, 2.4 GHz, DES 56, ATC, Channel Blocking	B54	\$ 3,811.00
NYK:9000533550004	ESSR, 2.4 GHz, DES 56, TDD	B54	\$ 3,811.00
NYK:9000533550005	ESSR, 2.4 GHz, DES 56, Cluster Hub	B54	\$ 3,811.00
NYK:9000533550006	ESSR, 2.4 GHz, DES 56, Cluster Hub	B54	\$ 2,973.00
NYK:9000533550007	ESSR, 2.4 GHz, DES 56, Cluster Hub, Channel Blocking	B54	\$ 3,811.00
NYK:9000533550008	ESSR, 2.4 GHz, AES 128, TDD, Channel Blocking	B54	\$ 3,811.00
NYK:9000533550013	ESSR, 2.4 GHz, AES 128, Cluster Hub	B54	\$ 3,811.00
NYK:9000533550014	ESSR, 2.4 GHz, AES 128, TDD	B54	\$ 3,811.00
NYK:9000533550015	ESSR, 2.4 GHz, AES 128, Cluster Hub, Channel Blocking	B54	\$ 3,811.00
NYK:9000533550016	ESSR, 2.4 GHz, DES 56, Cluster Hub, Channel Blocking	B54	\$ 3,811.00
NYK:9000533550009	ESSR, 2.4 GHz, AES 128, ATC	B54	\$ 3,811.00
NYK:9000533550010	ESSR, 2.4 GHz, AES 128, ATC	B54	\$ 3,811.00
NYK:9000533550011	ESSR, 2.4 GHz, AES 128, TDD	B54	\$ 3,811.00
NYK:9000533550012	ESSR, 2.4 GHz, AES 128, Cluster Hub	B54	\$ 3,811.00
NYK:9000533550017	ESSR, 2.4 GHz, AES 128, Cluster Hub	B54	\$ 3,811.00
NYK:9000533550018	ESSR, 2.4 GHz, AES 128, TDD	B54	\$ 3,811.00
NYK:9000533550019	ESSR, 2.4 GHz, AES 128, TDD, Channel Blocking	B54	\$ 3,811.00
NYK:9000533550020	ESSR, 2.4 GHz, AES 128, Cluster Hub, Channel Blocking	B54	\$ 3,811.00
NYK:9000533550021	ESSR, 2.4 GHz, AES 128, Cluster Hub	B54	\$ 3,811.00
NYK:9000533550022	ESSR, 2.4 GHz, AES 128, Cluster Hub	B54	\$ 3,811.00
NYK:9000533550023	ESSR, 2.4 GHz, AES 128, Cluster Hub	B54	\$ 3,811.00
NYK:9000533550024	ESSR, 2.4 GHz, AES 128, Cluster Hub	B54	\$ 3,811.00
NYK:9000532010004	HD Link Module, 4 I/O Circuits, w/o EPROM	B56	\$ 3,549.00
NYK:9000532010008	HD Link Module, 8 I/O Circuits, w/o EPROM	B56	\$ 5,067.00
NYK:9000532010014	HD Link Module, 4 I/O Circuits, w/ EPROM	B56	\$ 3,340.00
NYK:9000532010018	HD Link Module, 8 I/O Circuits, w/ EPROM	B56	\$ 4,592.00

Track Circuit Systems Products			Price
NYK:70007A4710001	PSO 4000 Transmitter Module	C2	\$ 2,704.00
NYK:70007A4730001	PSO 4000 Receiver Module	C2	\$ 2,758.00
NYK:70007A4750001	PSO 4000 Transceiver Module	C2	\$ 4,097.00
NYK:70007A4740001	PSO 4000 Crossing Module	C2	\$ 8,234.00
NYK:7000711500001	IPITC Track Circuit Module	C5	Call for Pricing
NYK:400044926060X	SE-3 60Hz Receiver Module	C10	\$ 5,693.00
NYK:400044926060RX	SE-3 60 Hz Receiver Module with Code Reset	C10	\$ 5,693.00
NYK:400044904833X	SE-3 83.3Hz Receiver Module	C10	\$ 5,693.00
NYK:400044904833RX	SE-3 83.3Hz Receiver Module with Code Reset	C10	\$ 5,693.00
NYK:400044930917X	SE-3 91.7Hz Receiver Module	C11	\$ 10,261.00
NYK:400044930917RX	SE-3 91.7Hz Receiver Module with Code Reset	C11	\$ 10,757.00
NYK:400044901100X	SE-3 100Hz Receiver Module	C11	\$ 5,852.00
NYK:400044901100RX	SE-3 100Hz Receiver Module with Code Reset	C11	\$ 5,852.00
NYK:400044903000X	ST-7 Track Feed Reactor	C14	\$ 1,450.00
NYK:400044909000X	ST-8 Track Feed Reactor	C14	\$ 1,734.00
NYK:400044906000X	ST-9 Track Feed Reactor	C14	\$ 1,700.00

Foundation Products			Price
NYK:131702-4X Anchor Bolt 3/4"-10 x 9" Long D2 Call For Pricing NYK:131702-18X Anchor Bolt 3/4"-10 x 9 1/2" Long D2			Call For Pricing
NYK:131702-1X	Anchor Bolt 1/2"-13 x 12" Long	D2	Call For Pricing
NYK:131702-2X	Anchor Bolt 3/4"-10 x 12" Long	D2	Call For Pricing
NYK:131702-3X	Anchor Bolt 1"-8 x 12" Long	D2	Call For Pricing
NYK:131702-6X	Anchor Bolt 3/4"-10 x 16" Long	D2	Call For Pricing
NYK:131702-7X	Anchor Bolt 1"-8 x 12" Long	D2	Call For Pricing
NYK:131702-15X	Anchor Bolt 3/4"-10 x 18" Long	D2	Call For Pricing
NYK:131702-10X	Anchor Bolt 1/2"-13 x 20" Long	D2	Call For Pricing
NYK:131702-14X	Anchor Bolt 3/4"-10 x 24" Long	D2	Call For Pricing
NYK:131702-26X	Anchor Bolt 1"-8 x 36" Long	D2	Call For Pricing
NYK:131702-19X	Anchor Bolt 1 1/4"-7 x 36" Long	D2	Call For Pricing
NYK:131702-11X	Anchor Bolt 1 1/4"-7 x 42" Long	D2	Call For Pricing
NYK:131702-48X	Anchor Bolt 1 1/2"-6 x 42" Long	D2	Call For Pricing
NYK:131702-96X	Anchor Bolt 1 1/2"-6 x 54" Long	D2	Call For Pricing
NYK:131702-16X	Anchor Bolt 1"-8 x 60" Long	D2	Call For Pricing
NYK:131702-13X	Anchor Bolt 1"-8 x 60" Long	D2	Call For Pricing
NYK:131702-22X	Anchor Bolt 1 1/4"-7 x 74" Long	D2	Call For Pricing
NYK:131702-23X	Anchor Bolt 1 1/4"-7 x 74" Long	D2	Call For Pricing
NYK:131702-21X	Anchor Bolt 1 1/4"-7 x 87" Long	D2	Call For Pricing
NYK:131702-20X	Anchor Bolt 1"-8 x 120" Long	D2	Call For Pricing
NYK:035903-911-1X	Pier Foundation 48" Tall w/ Riser	D6	\$ 1,051.00
NYK:035903-911-3X	Pier Foundation 60" Tall w/ Riser	D7	\$ 2,149.00
NYK:035903-200X	Pyramid Foundation 48" Tall w/ Riser	D8	\$ 2,858.00
NYK:035903-500X	Pyramid Foundation 60" Tall w/ Riser	D9	\$ 2,128.00
NYK:035800-2X	Triangle Pier Foundation 48" Tall	D10	\$ 331.00
NYK:035900-X	Block Pier Foundation 48" Tall	D11	\$ 919.00

Electromechanical Power Products			Price
NYK:400044350006X	CXP-3 Track Circuit Uninterruptible Power Supply	E1	\$ 2,372.00
NYK:400044562001X	ST-200-1 Track Transformer (SE-3/CE-3 Track Circuits)		\$ 1,300.00
NYK:400044560021X	ST-400-1 Track Transformer (Feed End)	E3	\$ 1,910.00
NYK:010560-X	ST-400 Signal / Track Transformer 396 VA (Receiver End)	E6	\$ 2,320.00
NYK:010560-X-1	ST-400 Signal / Track Transformer 396 VA (Receiver End)	E6	Call For Pricing
NYK:010560-X-2	ST-400 Signal / Track Transformer 400 VA (Receiver End)	E6	\$ 2,472.00
NYK:400044520020X	SLT Fixed Signal Lighting Transformer 20 A	E8	Call For Pricing
NYK:400044520050X	SLT Fixed Signal Lighting Transformer 50 A	E8	\$ 1,702.00
NYK:400044599101X	LT Lighting Transformer 5 A, 115 VAC	E10	Call For Pricing
NYK:400044599103X	LT Lighting Transformer 5 A, 230 VAC	E10	Call For Pricing
NYK:400044599106X	LT Lighting Transformer 5 A, 115 VAC	E10	Call For Pricing
NYK:400044599110X	LT Lighting Transformer 50 VA, 115 VAC	E10	Call For Pricing

Electromechanical Stabilization Products			Price	
NYK:052619-1	Lagdown Brace	E12	\$	18.54
NYK:3250775319	Temperature probe with 12' cable	E12	\$	63.00
NYK:3250775328	Temperature probe with 15' cable	E12	\$	80.00
NYK:Z820000140000	Clear Air Gap Arrester Cover	E14	\$	1.03
NYK:400044485036X	Air Gap Arrester Basic Assembly w/o Cover w/ Buss Connector	E14	\$	23.79
NYK:40004448528AX	Air Gap Arrester Basic Assembly w/ Cover	E14	\$	23.79
NYK:400044485028X	Air Gap Arrester Basic Assembly w/ Cover and Buss Connector	E14	\$	23.79
NYK:40004448528X1	Air Gap Arrester Basic Assembly w/ Cover and Buss Connector	E15	\$	23.79
NYK:400044485031X	Air Gap Arrester Basic Assembly w/ (2) Post Bakelite Base	E15	\$	30.36
NYK:400044485032X	Air Gap Arrester Basic Assembly w/ (2) Post Porcelain Base	E15	\$	61.90
NYK:400044485033X	Air Gap Arrester Basic Assembly w/ (3) Post Porcelain Base	E15	\$	68.51
NYK:400044585001X	Air Gap Arrester Heavy Duty Assembly w/ Cover	E18	\$	69.01
NYK:400044585003X	Air Gap Arrester Heavy Duty Assembly w/ (2) Post Bakelite Base	E18	\$	74.55
NYK:400044585004X	Air Gap Arrester Heavy Duty Assembly w/ Hardware	E18	\$	84.59
NYK:400044585005X	Air Gap Arrester Heavy Duty Assembly w/ Hardware	E18	\$	88.33
NYK:400044485054X	Air Gap Arrester Basic Assembly w/o Cover (Communications)	E20	\$	60.00
NYK:400044485050X	Air Gap Arrester Basic Assembly w/ Cover and Buss Connector (Communications)	E20	\$	38.00
NYK:40004448550X1	Air Gap Arrester Basic Assembly w/ Cover and Buss Connector (Communications)	E20	\$	25.00
NYK:400044485051X	Air Gap Arrester Basic Assembly w/ (2) Post Bakelite Base (Communications)	E20	\$	40.00
NYK:400044485052X	Air Gap Arrester Basic Assembly w/ (2) Post Porcelain Base (Communications)	E21	\$	41.96
NYK:400044485053X	Air Gap Arrester Basic Assembly w/ (3) Post Porcelain Base (Communications)	E21	\$	64.89
NYK: Z820000280000	Clear Air Gap Equalizer Cover	E24	\$	1.03
NYK:400044700007X	Air Gap Equalizer Basic Assembly w/o Cover w/ Hardware	E24	\$	30.08
NYK:40004470001AX	Air Gap Equalizer Basic Assembly w/ Cover	E24	\$	30.08
NYK:400044700001X	Air Gap Equalizer Basic Assembly w/ Cover and Hardware	E24	\$	30.08
NYK:40004470001X1	Air Gap Equalizer Basic Assembly w/ Cover and Hardware	E25	\$	36.05
NYK:400044700005X	Air Gap Equalizer Basic Assembly w/ (2) Post Bakelite Base	E25	\$	37.01
NYK:400044700002X	Air Gap Equalizer Basic Assembly w/ (2) Post Porcelain Base	E25	\$	58.30
NYK:400044700030X	Rope Equalizer 3 1/2"	E25	\$	19.81
NYK:400044700033X	Rope Equalizer 3 5/8"	E26	\$	34.26
NYK:400044700032X	Rope Equalizer 3 3/4"	E26	\$	46.00
NYK:400044700031X	Rope Equalizer 8 1/2"	E26	\$	46.00
NYK:400044700021X	Blade Equalizer 2 1/2"	E26	\$	30.39
NYK:400044700046X	Blade Equalizer 2 1/2"	E27	\$	37.61
NYK:400044700047X	Blade Equalizer 2 1/2" w/ Cover	E27	\$	47.90
NYK:4000447010000	701-1 Discharge Unit	E32	\$	78.57
NYK:400044701001X	701-1 Discharge Unit w/ Cover	E32	\$	107.00
NYK:400044701002X	701-1 Discharge Unit w/ Cover and (2) Post Bakelite Base	E32	\$	123.00
NYK:400044701029X	701-1 Discharge Unit w/ Cover	E32	\$	104.00
NYK:400044817000X	SSP-11 Surge Protector 20 V	E36	\$	142.00
NYK:400044817001X	SSP-11 Surge Protector 30 V	E36	\$	145.00
NYK:400044817002X	SSP-11 Surge Protector 40 V	E36	\$	142.00
NYK:400044817003X	SSP-11 Surge Protector 50 V	E36	\$	145.00
NYK:400044817004X	SSP-11 Surge Protector 100 V	E36	\$	142.00
NYK:400044817005X	SSP-11 Surge Protector 200 V	E36	\$	118.00
NYK:400044817006X	SSP-11 Surge Protector 300 V	E36	\$	118.00
NYK:400044817007X	SSP-11 Surge Protector 400 V	E36	\$	129.00
NYK:400044818000X	SSP-11 Surge Protector 20 V w/ Bakelite Base	E36	\$	155.00

Electromechanical Stabilization Products			Price	
NYK:400044818001X	SSP-11 Surge Protector 30 V w/ Bakelite Base	E36	\$	175.00
NYK:400044818002X	SSP-11 Surge Protector 40 V w/ Bakelite Base	E36	\$	129.00
NYK:400044818003X	SSP-11 Surge Protector 50 V w/ Bakelite Base	E36	\$	155.00
NYK:400044818004X	SSP-11 Surge Protector 100 V w/ Bakelite Base	E36	\$	155.00
NYK:400044818005X	SSP-11 Surge Protector 200 V w/ Bakelite Base	E36	\$	149.00
NYK:400044818006X	SSP-11 Surge Protector 300 V w/ Bakelite Base	E36	\$	160.00
NYK:400044818007X	SSP-11 Surge Protector 400 V w/ Bakelite Base	E36	\$	175.00
NYK:40004480400AX	SP17-1A Battery System Model	E40	\$	82.92
NYK:40004480400BX	SP17-1B Battery System Model	E40	\$	82.92
NYK:40004480405AX	SP17-2A Battery System Model	E40	\$	221.00
NYK:40004480405BX	SP17-2B Battery System Model	E40	\$	221.00
NYK:40004480500AX	SP18-1A Battery System Model	E42	\$	244.00
NYK:40004480500BX	SP18-1B Battery System Model	E42	\$	244.00
NYK:40004480504AX	SP18-2A Battery System Model	E42	\$	235.00
NYK:40004480504BX	SP18-2B Battery System Model	E42	\$	235.00
NYK:40004480600AX	SP19-1A Battery System Model	E44	\$	234.00
NYK:40004480600BX	SP19-1B Battery System Model	E44	\$	129.00
NYK:40004480603AX	SP19-2A Battery System Model	E44	\$	234.00
NYK:40004480603BX	SP19-2B Battery System Model	E44	\$	234.00
NYK:40004480700AX	SP20-2 AC Line Model	E46	\$	200.00
NYK:40004480700BX	SP20-3 AC Line Model	E46	\$	200.00
NYK:40004480706AX	SP20-2A AC Line Model	E46	\$	245.00
NYK:40004480707AX	SP20-3A AC Line Model	E46	\$	379.00
NYK:40004481105AX	SP20-2A AC Line Model	E47	\$	334.00
NYK:40004481105BX	SP20-2B AC Line Model	E47	\$	334.00
NYK:400044808000X	SP21-1 Code Line Model	E50	\$	122.00
NYK:400044808005X	SP21-2 Code Line Model	E50	\$	319.00
NYK:400044808006X	SP21-3 Code Line Model	E50	\$	319.00
NYK:400044808010X	SP21-5 Code Line Model	E50	\$	319.00
NYK:40004481104AX	SP24-1A Battery System Model	E52	\$	311.00
NYK:40004481104BX	SP24-1B Battery System Model	E52	\$	311.00
NYK:400044802000X	SP15-1 Track Circuit Model	E54	\$	109.00
NYK:400044802014X	SP15-2 Track Circuit Model	E54	\$	104.00
NYK:400044814000X	SP26-1 Track Circuit Model	E54	\$	304.00
NYK:400044814006X	SP26-2 Track Circuit Model	E54	\$	349.00
NYK:400044814007X	SP26-2-50 Track Circuit Model	E55	\$	308.00
NYK:400044814008X	SP26-2 Track Circuit Model	E55	\$	350.00
NYK:029602-1X	Resistance Unit, Adjustable, 8.89 A	E58	\$	66.46
NYK:029602-2X	Resistance Unit, Adjustable, 3.97 A	E58	\$	66.46
NYK:029602-3X	Resistance Unit, Adjustable, 3.87 A	E58	\$	66.46
NYK:029602-4X	Resistance Unit, Adjustable, 3.40 A	E58	\$	66.46
NYK:029602-5X	Resistance Unit, Adjustable, 3.06 A	E58	\$	66.46
NYK:029602-6X	Resistance Unit, Adjustable, 2.74 A	E58	\$	66.46
NYK:029602-7X	Resistance Unit, Adjustable, 2.45 A	E58	\$	66.46
NYK:029602-8AX	Resistance Unit, Adjustable, 2.24 A	E58	\$	66.46
NYK:029602-51X	Resistance Unit, Adjustable	E58	\$	66.46
NYK:029603-1X	Resistance Unit, Adjustable, 1.94 A	E58	\$	71.33
NYK:029603-2X	Resistance Unit, Adjustable, 1.73 A	E58	\$	71.33
NYK:029603-3X	Resistance Unit, Adjustable, 1.54 A	E58	\$	71.33

Electromechanical Stabilization Products			Price
NYK:029603-4X	Resistance Unit, Adjustable, 1.37 A	E58	\$ 71.33
NYK:029603-5X	Resistance Unit, Adjustable, 1.22 A	E58	\$ 71.33
NYK:029603-6X	Resistance Unit, Adjustable, 1.09 A	E58	\$ 71.33
NYK:029603-7X	Resistance Unit, Adjustable, 0.97 A	E58	\$ 71.33
NYK:029603-8X	Resistance Unit, Adjustable, 0.94 A	E58	\$ 71.33
NYK:029603-9X	Resistance Unit, Adjustable, 0.83 A	E58	\$ 71.33
NYK:029603-10X	Resistance Unit, Adjustable, 0.73 A	E59	\$ 71.33
NYK:029603-11X	Resistance Unit, Adjustable, 0.65 A	E59	\$ 71.33
NYK:029603-12X	Resistance Unit, Adjustable, 0.58 A	E59	\$ 71.33
NYK:029603-13X	Resistance Unit, Adjustable, 0.52 A	E59	\$ 66.46
NYK:029603-14X	Resistance Unit, Adjustable, 0.46 A	E59	\$ 47.79
NYK:029603-15X	Resistance Unit, Adjustable, 0.42 A	E59	\$ 71.33
NYK:029603-16X	Resistance Unit, Adjustable, 0.37 A	E59	\$ 66.46
NYK:029603-22X	Resistance Unit, Adjustable, 1.58 A	E59	\$ 71.33
NYK:029603-23X	Resistance Unit, Adjustable, 0.87 A	E59	\$ 71.33
NYK:029603-25X	Resistance Unit, Adjustable, 0.26 A	E59	\$ 71.33
NYK:029603-26X	Resistance Unit, Adjustable, 0.22A	E59	\$ 71.33
NYK:029604-1X	Resistance Unit, Fixed, 8.89 A	E59	\$ 45.04
NYK:029604-2X	Resistance Unit, Fixed, 5.48 A	E59	\$ 45.04
NYK:029604-3X	Resistance Unit, Fixed, 3.87 A	E59	\$ 45.04
NYK:029604-4X	Resistance Unit, Fixed, 3.54 A	E59	\$ 45.04
NYK:029604-5X	Resistance Unit, Fixed, 2.74 A	E59	\$ 45.04
NYK:029604-6X	Resistance Unit, Fixed, 2.45 A	E59	\$ 45.04
NYK:029604-7X	Resistance Unit, Fixed, 2.24 A	E59	\$ 45.04
NYK:029604-8X	Resistance Unit, Fixed, 1.58 A	E59	\$ 45.04
NYK:029604-9X	Resistance Unit, Fixed, 1.34 A	E59	\$ 45.04
NYK:029604-10X	Resistance Unit, Fixed, 2.07 A	E59	\$ 55.62
NYK:029604-11X	Resistance Unit, Fixed, 5.26 A	E59	\$ 45.04
NYK:400044883152X1	General Purpose Panel (Blank)	E62	\$ 254.00
NYK:400044883149X1	General Purpose Panel (12 Positions)	E62	\$ 500.00
NYK:400044883199X1	General Purpose Panel (16 Positions)	E62	\$ 500.00
NYK:400044883201X1	General Purpose Panel (Signal Panel)	E62	\$ 1,330.00
NYK:400044883145X	General Purpose Panel (20 Positions)	E63	\$ 979.00
NYK:400044883170X1	General Purpose Panel (Blank w/ Slotted Duct)	E63	\$ 607.00
NYK:400044883177X1	General Purpose Panel (14 Positions w/ Slotted Duct)	E63	\$ 1,173.00
NYK:400044700176X1	General Purpose Panel (24 Positions w/ Slotted Duct)	E63	\$ 1,089.00
NYK:8000800260031	Battery and (1) Track Panel	E64	\$ 769.00
NYK:8000800260003	Battery and (1) Track Panel	E64	\$ 2,485.00
NYK:8000800260022	Track Panel	E64	\$ 478.00
NYK:8000800490001	DC Enhancer Panel	E64	\$ 6,042.00
NYK:9000911700001	Common Gate Control Panel	E65	\$ 1,396.00
NYK:9000911700002	Common Gate Control Panel	E65	\$ 1,435.00
NYK:9000911810001	Isolated Gate Control Panel	E65	\$ 1,757.00
NYK:9000911810002	Isolated Gate Control Panel	E65	\$ 1,547.00
NYK:40004421712X1	Type 217 Block Porcelain Terminal Block 1" Post Center to Center	E66	\$ 22.62
NYK:400044217012X	Type 217 Block Porcelain Terminal Block 1" Post Center to Center	E66	\$ 22.62
NYK:40004421708X1	Type 217 Block Porcelain Terminal Block 2 3/8" Post Center to Center	E66	\$ 29.55
NYK400044217008X	Type 217 Block Porcelain Terminal Block 2 3/8" Post Center to Center	E66	\$ 29.55
NYK40004421703X1	Type 217 Block Porcelain Terminal Block 5 1/8" Post Center to Center	E66	\$ 29.55
NYK400044217003X	Type 217 Block Porcelain Terminal Block 5 1/8" Post Center to Center	E66	\$ 29.55

Electromechanical Stabilization Products			Price	
NYK:023390-5-2X	Type 390 1" Square Terminal Block 2" Overall Length	E66	\$	9.27
NYK:023390-5-3X	Type 390 1" Square Terminal Block 3" Overall Length	E66	\$	13.91
NYK:023390-5-4X	Type 390 1" Square Terminal Block 4" Overall Length	E66	\$	22.15
NYK:023390-5-5X	Type 390 1" Square Terminal Block 5" Overall Length	E66	\$	23.69
NYK:023390-5-6X	Type 390 1" Square Terminal Block 6" Overall Length	E66	\$	27.81
NYK:023390-5-7X	Type 390 1" Square Terminal Block 7" Overall Length	E66	\$	32.45
NYK:023390-5-8X	Type 390 1" Square Terminal Block 8" Overall Length	E66	\$	37.08
NYK:023390-5-9X	Type 390 1" Square Terminal Block 9" Overall Length	E66	\$	41.72
NYK:023390-5-10X	Type 390 1" Square Terminal Block 10" Overall Length	E66	\$	46.35
NYK:023390-5-11X	Type 390 1" Square Terminal Block 11" Overall Length	E66	\$	50.99
NYK:023374-24X	Type 274 Rounded (2) Post Wide Terminal Block	E66	\$	11.01
NYK:023374-23X	Type 274 Rounded (2) Post Wide Terminal Block	E66	\$	14.92
NYK:023374-40X	Type 274 Rounded (2) Post Wide Terminal Block	E66	\$	12.94
NYK:023374-503X	Type 274 Rounded (2) Post Wide Terminal Block	E66	\$	20.76
NYK:023374-501X	Type 274 Rounded (2) Post Wide Terminal Block	E66	\$	38.76
NYK:023374-21X	Type 274 Rounded (2) Post Wide Terminal Block	E66	\$	53.53
NYK:051883-26X1	13 Way Terminal Block w/o Hardware	E66	\$	147.00
NYK:051883-26X2	13 Way Terminal Block w/ Hardware	E66	\$	175.00
NYK:051883-18X2	14 Way Terminal Block w/o Hardware	E66	\$	151.00
NYK:051883-18X1	14 Way Terminal Block w/ Hardware	E66	\$	165.00

Relay Products			Price
US2:400000	ST1, Neutral Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F2	\$ 1,131.00
US2:400001	ST1, Neutral Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F2	\$ 1,510.00
US2:400002	ST1, Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F2	\$ 1,219.00
US2:400003	ST1, Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F2	\$ 1,121.00
US2:400004	ST1, Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F2	\$ 1,174.00
US2:400005	ST1, Neutral Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F2	\$ 1,174.00
US2:400006	ST1, Neutral Relay, Regular Release and Regular Pickup, 4F - 2B, 4 A @ 30 V, Standard Duty	F2	\$ 1,242.00
US2:400007	ST1, Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F2	\$ 1,659.00
US2:400008	ST1, Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F2	\$ 1,396.00
US2:400010	ST1, Neutral Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F3	\$ 1,788.00
US2:400011	ST1, Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F3	\$ 1,373.00
US2:400012	ST1, Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F3	\$ 1,727.00
US2:400013	ST1, Neutral Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F3	\$ 1,433.00
US2:400015	ST1, Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F3	\$ 1,548.00
US2:400017	ST1, Neutral Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F3	\$ 1,550.00
US2:400020	ST1, Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 15 A @ 30 V, Heavy Duty	F3	\$ 1,129.00
US2:400022	ST1, Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 15 A @ 30 V, Heavy Duty	F3	\$ 1,401.00
US2:400023	ST1, Neutral Relay, Regular Release and Regular Pickup, 6FB, 15 A @ 30 V, Heavy Duty	F3	\$ 1,174.00
US2:400026	ST1, Neutral Relay, Regular Release and Regular Pickup, 6FB, 15 A @ 30 V, Heavy Duty	F4	\$ 2,369.00
US2:400027	ST1, Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 15 A @ 30 V, Heavy Duty	F4	\$ 1,620.00
US2:400028	ST1, Neutral Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F4	Call for Pricing
US2:400029	ST1, Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 15 A @ 30 V, Heavy Duty	F4	\$ 1,326.00
US2:400030	ST1, Neutral Relay, Regular Release and Regular Pickup, 2FB - 3F - 3B, 4 A @ 30 V, Standard Duty	F4	\$ 1,495.00
US2:400031	ST1, Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F4	\$ 2,013.00
NYK:400070	ST1, Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F4	\$ 1,329.00
NYK:450000	ST2, Neutral Relay, Regular Release and Regular Pickup, 12FB, 4 A @ 30 V, Standard Duty	F4	\$ 2,816.00
NYK:450001	ST2, Neutral Relay, Regular Release and Regular Pickup, 8FB - 2F, 4 A @ 30 V, Extra Heavy Duty	F4	\$ 2,816.00

Relay Products			Price
US2:400100	ST1, Neutral Relay, Regular Release and Slow Pickup, 6FB, 4 A @ 30 V, Standard Duty	F5	\$ 1,844.00
US2:400101	ST1, Neutral Relay, Regular Release and Slow Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F5	\$ 2,025.00
US2:400014	ST1, Neutral Relay, Slow Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F6	\$ 1,750.00
US2:400200	ST1, Neutral Relay, Slow Release and Regular Pickup, 4FB, 4 A @ 30 V, Standard Duty	F6	\$ 1,558.00
US2:400210	ST1, Neutral Relay, Slow Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F6	\$ 1,788.00
US2:400211	ST1, Neutral Relay, Slow Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F6	\$ 1,373.00
US2:400212	ST1, Neutral Relay, Slow Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F6	\$ 1,727.00
US2:400213	ST1, Neutral Relay, Slow Release and Regular Pickup, 2FB, 4 A @ 30 V, Standard Duty	F6	\$ 1,433.00
US2:400220	ST1, Neutral Relay, Slow Release and Regular Pickup, 2F - 4B, 4 A @ 30 V, Standard Duty	F6	\$ 1,735.00
US2:400221	ST1, Neutral Relay, Slow Release and Regular Pickup, 2FB, 4 A @ 30 V, Standard Duty	F6	\$ 1,827.00
NYK:450200	ST2, Neutral Relay, Slow Release and Regular Pickup, 12FB, 4 A @ 30 V, Standard Duty	F6	\$ 4,119.00
US2:400016	ST1, Neutral Lamp Control Relay, Regular Release and Regular Pickup, 2FB - 5F - 1B, 20 A @ 16 V, Heavy Duty	F7	\$ 1,986.00
US2:400021	ST1, Neutral Lamp Control Relay, Regular Release and Regular Pickup, 2B, 15 A @ 30 V, Heavy Duty, 2FB, 4 A @ 30 V Standard Duty	F7	\$ 1,382.00
US2:400300	ST1, Neutral Light Out Relay, Regular Release and Regular Pickup, 4FB, 4 A @ 30 V, Standard Duty	F8	\$ 1,347.00
US2:400301	ST1, Neutral Light Out Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F8	\$ 1,354.00
US2:400302	ST1, Neutral Light Out Relay, Regular Release and Regular Pickup, 4FB, 4 A @ 30 V, Standard Duty	F8	\$ 1,710.00
US2:400303	ST1, Neutral Light Out Relay, Regular Release and Regular Pickup, 4FB, 4 A @ 30 V, Standard Duty	F8	\$ 1,710.00
US2:400305	ST1, Neutral Light Out Relay, Regular Release and Regular Pickup, 4FB, 4 A @ 30 V, Standard Duty	F8	\$ 1,502.00
NYK:400300-1X	External rectifier stack assembly for Neutral Light Out Relay assemblies (Includes hardware)	F8	\$ 264.00
NYK:400500	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F9	\$ 1,174.00
NYK:400500-1	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F9	\$ 1,240.00
NYK:400501	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F9	\$ 1,482.00
NYK:400502	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F9	\$ 1,174.00
NYK:400503	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 2FB - 4F - 2B, 4 A @ 30 V, Standard Duty	F9	\$ 1,410.00
NYK:400504	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F9	\$ 1,467.00
NYK:400505	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 6FB, 15 A @ 30 V, Heavy Duty	F9	\$ 1,653.00

Relay Products			Price
NYK:400506	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 15 A @ 30 V, Heavy Duty	F9	\$ 1,436.00
NYK:400506-1	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 15 A @ 30 V, Heavy Duty	F9	\$ 1,240.00
NYK:400507	ST1, Neutral Light Out Relay, Regular Release and Regular Pickup, 5F - 4B, 4 A @ 30 V, Standard Duty	F10	\$ 1,431.00
NYK:400508	ST1, Neutral Light Out Relay, Regular Release and Regular Pickup, 5F - 4B, 4 A @ 30 V, Standard Duty	F10	\$ 1,642.00
NYK:400509	ST1, Neutral Light Out Relay, Regular Release and Regular Pickup, 2FB - 4F - 2B, 4 A @ 30 V, Heavy Duty	F10	\$ 1,174.00
NYK:400509M	ST1, Neutral Light Out Relay, Regular Release and Regular Pickup, 2FB - 4F - 2B, 4 A @ 30 V, Heavy Duty	F10	\$ 1,174.00
NYK:400510	ST1, Neutral Light Out Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Heavy Duty	F10	\$ 1,174.00
NYK:400511	ST1, Neutral Light Out Relay, Regular Release and Regular Pickup, 4FB, 4A @ 30 V, Heavy Duty	F10	\$ 1,381.00
NYK:400512	ST1, Neutral Light Out Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Heavy Duty	F10	\$ 1,631.00
NYK:400513	ST1, Neutral Light Out Relay, Regular Release and Regular Pickup, 2FB - 3F - 3B, 4 A @ 30 V, Heavy Duty	F10	\$ 1,177.00
NYK:400515	ST1, Neutral Light Out Relay, Regular Release and Regular Pickup, 5F - 4B, 4 A @ 30 V, Heavy Duty	F10	\$ 1,682.00
NYK:400600	ST1, Neutral Switch Overload Relay, Regular Release and Regular Pickup, 2B, Extra Heavy Duty, Magnetic Blowout	F11	\$ 1,623.00
NYK:400601	ST1, Neutral Switch Overload Relay, Regular Release and Regular Pickup, 2CBO, 4 A @ 30 V, Standard Duty	F11	\$ 1,883.00
NYK:400602	ST1, Neutral Switch Overload Relay, Regular Release and Regular Pickup, 2CBO, 4 A @ 30 V, Standard Duty	F11	\$ 1,627.00
NYK:400604	ST1, Neutral Switch Overload Relay, Regular Release and Regular Pickup, 2CBO, 4 A @ 30 V, Standard Duty	F11	\$ 1,435.00
NYK:400605	ST1, Neutral Switch Overload Relay, Regular Release and Regular Pickup, 2CBO, 4 A @ 30 V, Standard Duty	F11	\$ 2,083.00
NYK:400605-1	ST1, Neutral Switch Overload Relay, Regular Release and Regular Pickup, 2CBO, 4 A @ 30 V, Standard Duty	F11	\$ 1,206.00
NYK:400527	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F12	\$ 1,122.00
NYK:400528	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F12	\$ 1,438.00
NYK:400529	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 4FB, 15 A @ 30 V, Heavy Duty, 2FB, 4 A @ 30 V, Standard Duty	F12	\$ 1,438.00
NYK:400531	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F12	\$ 1,378.00
NYK:400532	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F12	\$ 1,438.00
NYK:400533	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F12	\$ 1,136.00
NYK:400534	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F12	\$ 1,532.00
NYK:400535	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F12	\$ 1,518.00
NYK:400559	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 2FB - 6F, 4 A @ 30 V, Heavy Duty	F12	\$ 1,458.00

Relay Products			Price
NYK:400516	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F13	\$ 1,620.00
NYK:400517	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 4FB, 4 A @ 30 V, Standard Duty	F13	\$ 1,320.00
NYK:400518	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 4FB, 4 A @ 30 V, Standard Duty	F13	\$ 1,468.00
NYK:400519	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 2FB - 4F - 2B, 4 A @ 30 V, Standard Duty	F13	\$ 1,439.00
NYK:400521	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F13	\$ 1,730.00
NYK:400522	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F13	\$ 1,613.00
NYK:400524	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F13	\$ 1,842.00
NYK:400525	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 4FB - 2F - 1B, 4 A @ 30 V, Standard Duty	F13	\$ 1,410.00
NYK:400526	ST1, Biased Neutral Relay, Regular Release and Regular Pickup, 2FB - 4F - 2B, 4 A @ 30 V, Standard Duty	F13	\$ 1,160.00
NYK:400540	ST1, Biased Neutral Relay, Regular Release and Slow Pickup, 6FB, 4 A @ 30 V, Standard Duty	F14	\$ 1,506.00
NYK:400530	ST1, Biased Neutral Relay, Slow Release and Regular Pickup, 6FB, 4 A @ 30 V, Standard Duty	F14	\$ 1,523.00
NYK:400520	ST1, Biased Neutral Switch Control Relay, Regular Release and Regular Pickup, 2F - 2B, 15 A @ 30 V, Extra Heavy Duty Magnetic Blowout	F14	\$ 1,174.00
NYK:400520-1	ST1, Biased Neutral Switch Control Relay, Regular Release and Regular Pickup, 2F - 2B, 15 A @ 30 V, Extra Heavy Duty Magnetic Blowout	F14	\$ 1,129.00
NYK:400523	ST1, Biased Neutral Switch Control Relay, Regular Release and Regular Pickup, 2F, 15 A @ 30 V, Extra Heavy Duty Magnetic Blowout	F14	\$ 1,551.00
NYK:400700	ST1, Flasher, 60 Ohm	F14	\$ 1,056.00
NYK:400700-X	ST1, Flasher, 240 Ohm	F14	\$ 1,432.00
NYK:400700-1X	ST1, Flasher, 240 Ohm	F14	\$ 382.00
NYK:400700-7X	ST1, Flasher, 60 Ohm	F14	\$ 1,385.00
NYK:400950	ST1, Code Responsive Relay, 200 Ohm	F15	\$ 5,174.00
NYK:400951	ST1, Code Responsive Relay, 22 Ohm	F15	\$ 5,563.00
NYK:400952	ST1, Code Responsive Relay, 80 Ohm	F15	\$ 4,689.00
NYK:400953	ST1, Code Responsive Relay, 80 Ohm	F15	\$ 5,249.00
NYK:400954	ST1, Code Responsive Relay, 80 Ohm	F15	\$ 5,016.00
NYK:400955	ST1, Code Responsive Relay, 80 Ohm	F15	\$ 4,820.00
NYK:400956	ST1, Code Responsive Relay, 80 Ohm	F15	\$ 4,498.00
NYK:400957	ST1, Code Responsive Relay, 80 Ohm	F15	\$ 5,333.00
NYK:450992	ST2, Vane Track Relay	F16	\$ 4,917.00
NYK:450993	ST2, Vane Track Relay	F16	\$ 4,917.00
NYK:450994	ST2, Vane Track Relay	F16	\$ 4,917.00
NYK:450994-N	ST2, Vane Track Relay	F16	\$ 4,917.00
NYK:400800	ST1, Power Transfer Relay	F16	\$ 1,461.00
NYK:400800-X	ST1, Power Transfer Relay	F16	\$ 1,375.00
NYK:400801	ST1, Power Transfer Relay	F16	\$ 1,519.00
NYK:400801-X	ST1, Power Transfer Relay	F16	\$ 1,629.00
NYK:400802	ST1, Power Transfer Relay	F16	\$ 1,461.00
NYK:400802-X	ST1, Power Transfer Relay	F16	\$ 1,518.00
NYK:400900	ST1, Magnetic Stick Relay	F16	\$ 4,650.00
NYK:400901	ST1, Magnetic Stick Relay	F16	\$ 4,673.00
NYK:400904	ST1, Magnetic Stick Relay	F16	\$ 4,917.00

Relay Products			Price	
NYK:27E805	Relay Socket Base	F18	\$	10.30
NYK:27E809	Relay Socket Base Basic Assembly	F18	\$	40.17
NYK:420000-40X	Relay Socket Base Assembly	F18	\$	87.67
NYK:420000-41X	Relay Socket Base Assembly	F18	\$	100.00
NYK:420000-43X	Relay Socket Base Assembly	F19	\$	94.95
NYK:420000-75X	Relay Socket Base Assembly	F19	\$	93.99
NYK:420000-77X	Relay Socket Base Assembly	F19	\$	98.55
NYK:420000-78X	Relay Socket Base Assembly	F19	\$	126.00
NYK:420000-61	Socket Terminal Insert	F20	\$	2.95
NYK:420000-48	Terminal Solder Tab	F20	\$	2.10
NYK:420000-49	Terminal Crimping Tab	F20	\$	2.20
NYK:420000-50	Terminal Crimping Tab	F20	\$	2.12

Locomotive Systems Products			Price
NYK:V3465/R	Full Size HOT Console Unit	G2	\$ 4,378.00
NYK:VK-3465/R	Full Size HOT Console Unit w/ Setup Kit	G2	\$ 5,121.00
NYK:V3467/R	Compact HOT Console Unit	G3	\$ 4,498.00
NYK:VK-3467/R	Compact HOT Console Unit w/ Setup Kit	G3	\$ 5,265.00
V3451/R2	Integrated HOT Unit	G4	\$ 3,410.00
V3452/R2	Integrated HOT Unit	G4	\$ 3,126.00
NYK:QK-3920-01	EOT with EOT Phone Home Included (Red Standard Model)	G6	Call for Pricing
NYK:QK-3920-02	EOT with EOT Phone Home Included (Orange Standard Model)	G6	Call for Pricing
NYK:QK-3920-03	EOT with EOT Phone Home Included (Red Smart Charge Model)	G6	Call for Pricing
NYK:QK-3920-04	EOT with EOT Phone Home Included (Orange Smart Charge Model)	G6	Call for Pricing
NYK:QP-35056	Dump Pilot Valve	G7	\$ 55.22
NYK:QP-35057	APG Control Valve	G7	Call for Pricing
NYK:59208	APG Assembly	G7	\$ 316.00
NYK:52616	Clamp Nut Bar	G7	\$ 26.05
NYK:59062	Latch Handle	G7	\$ 57.01
NYK:61013	Electronic Interface Module	G7	\$ 1,062.00
NYK:62174	Power Module	G7	\$ 494.00
NYK:62176/PC	Clamp Assembly	G7	\$ 729.00
NYK:65105/ORD	Orange Enclosure\\	G7	\$ 191.00
NYK:65105/RED	Red Enclosure	G7	\$ 190.00
NYK:65106/ORD	Orange Enclosure Cover	G7	\$ 75.00
NYK:65106/RED	Red Enclosure Cover	G7	\$ 65.92
NYK:QP-52516	Mounting Bracket	G7	\$ 53.05
NYK:QP-70312	Chassis Harness	G7	\$ 335.00
EOT Phone Home Service	EOT Phone Home Service	G9	Call For Pricing
NYK:Q3440/R	Integrated Repeater Unit	G12	\$ 4,489.00
NYK:Q3442	Integrated Repeater Unit for General Electric® IFC, EMD/Rockwell® ICEtm or FIREtm systems.	G12	\$ 4,778.00
NYK:Q1230	Basic Recorder / Tester Unit	G14	\$ 1,939.00
NYK:Q1400	Speed Test Unit	G14	\$ 4,678.00
NYK:Q3431/NB	EOT / HOT Testing Unit	G14	\$ 5,230.00
NYK:Q3433/NB	EOT / HOT Testing Unit	G14	\$ 8,409.00
NYK:D3005H15-A01	ATC Tester Unit	G15	\$ 19,691.00
NYK:D3883H32-A01	ACSES transponder simulator control portable tester	G15	Call For Pricing
NYK:Q1123	Axle Drive 20 Pulses Per Minute	G18	\$ 1,280.00
NYK:Q1124	Axle Drive 20 Pulses Per Minute w/ Paddle Axle Drive Assembly	G18	\$ 1,460.00
NYK:Q1126	Axle Drive 20 Pulses Per Minute w/ PEG Drive Assembly	G18	\$ 1,117.00
NYK:Q1127	Axle Drive 20 Pulses Per Minute w/ PEG Drive Assembly	G18	\$ 1,131.00
NYK:Q1163	Axle Drive 60 Pulses Per Minute	G19	\$ 1,148.00
NYK:Q1164	Axle Drive 60 Pulses Per Minute w/ Paddle Axle Drive Assembly	G19	\$ 1,460.00
NYK:52508/20P	Axle Drive Shaft Assembly for 20 Pulses Per Minute	G20	\$ 163.00
NYK:52508/60P	Axle Drive Shaft Assembly for 60 Pulses Per Minute	G20	\$ 207.00
NYK:52170	Paddle Axle Drive Shaft Assembly for 20 Pulses Per Minute	G20	\$ 163.00
NYK:52272	PEG Drive Shaft Assembly for 20 Pulses Per Minute	G20	\$ 51.50

Locomotive Systems Products			Price
NYK:D600001-A01	Axle Generator	G21	\$ 3, 019.00
NYK:D1365H01-A12	Junction box	G21	\$ 510.00
NYK:B600010-A01	Spline assembly	G21	\$ 736.00
NYK:D243H01-A01	Code Rate Generator	G24	\$ 1,416.00
NYK:D887H01-A01	Code Rate Decoder	G24	\$ 5,349.00
NYK:Q1860	Odometer (English)	G26	\$ 1,845.00
NYK:Q1860/M	Odometer (Metric)	G26	\$ 1,977.00
NYK:Q1810	Speed Indicator No Preset	G28	\$ 2,590.00
NYK:Q1810-74	Speed Indicator 74 mph Preset	G28	\$ 2,447.00
NYK:Q1810/M-120	Speed Indicator 120 kph Preset	G28	\$ 2,447.00
NYK:Q1812	Speed Indicator No Preset	G28	\$ 2,965.00
NYK:Q1812-69	Speed Indicator 69 mph Preset	G28	\$ 4,763.00
NYK:Q1818-74	Speed Indicator 74 mph Preset	G28	\$ 2,521.00
NYK:Q1818-80	Speed Indicator 80 mph Preset	G28	\$ 2,922.00
NYK:Q1820	Speed Indicator No Preset	G28	\$ 2,645.00
NYK:Q1820-45	Speed Indicator 45 mph Preset	G28	\$ 2,643.00
NYK:Q1820-71	Speed Indicator 71 mph Preset	G28	\$ 2,645.00
NYK:Q1820-74	Speed Indicator 74 mph Preset	G28	\$ 2,643.00
NYK:Q1820-80	Speed Indicator 80 mph Preset	G28	\$ 2,257.00
NYK:Q1821	Speed Indicator No Preset	G28	\$ 2,286.00
NYK:Q1830	Speed Indicator No Preset	G28	\$ 2,674.00
NYK:Q1830-10	Speed Indicator 10 mph Preset	G28	\$ 2,674.00
NYK:Q1830-69	Speed Indicator 69 mph Preset	G28	\$ 2,674.00
NYK:Q1830-74	Speed Indicator 74 mph Preset	G28	\$ 2,286.00
NYK:Q9011/10B	Speed Indicator Power Cable (20) Pole, 10' (3 m) long, 90° "B" Break	G29	\$ 310.00
NYK:Q9011/10C	Speed Indicator Power Cable (20) Pole, 10' (3 m) long, 90° "C" Break	G29	\$ 279.00
NYK:Q9011/15B	Speed Indicator Power Cable (20) Pole, 15' (4.5 m) long, 90° "B" Break	G29	\$ 310.00
NYK:Q9011/15C	Speed Indicator Power Cable (20) Pole, 15' (4.5 m) long, 90° "C" Break	G29	\$ 290.00
NYK:Q9011/20B	Speed Indicator Power Cable (20) Pole, 20' (6 m) long, 90° "B" Break	G29	\$ 331.00
NYK:Q9011/20C	Speed Indicator Power Cable (20) Pole, 20' (6 m) long, 90° "C" Break	G29	\$ 301.00
NYK:Q9012/10B	Speed Indicator Power Cable (60) Pole, 10' (3 m) long, 90° "B" Break	G29	\$ 310.00
NYK:Q9012/10C	Speed Indicator Power Cable (60) Pole, 10' (3 m) long, 90° "C" Break	G29	\$ 310.00
NYK:Q9012/15B	Speed Indicator Power Cable (60) Pole, 15' (4.5 m) long, 90° "B" Break	G29	\$ 332.00
NYK:Q9012/15C	Speed Indicator Power Cable (60) Pole, 15' (4.5 m) long, 90° "C" Break	G29	\$ 304.00
NYK:Q9012/20B	Speed Indicator Power Cable (60) Pole, 20' (6 m) long, 90° "B" Break	G29	\$ 310.00
NYK:Q9012/20C	Speed Indicator Power Cable (60) Pole, 20' (6 m) long, 90° "C" Break	G29	Call for Pricing
NYK:Q9038/15C	Speed Indicator / Alerter Interface Cable, 15' (4.5 m) long, 90° "C" Break	G29	\$ 117.00
NYK:Q9038/25C	Speed Indicator / Alerter Interface Cable, 25' (7.5 m) long, 90° "C" Break	G29	\$ 310.00

Locomotive Systems Products			Price
NYK:Q9038/30C	Speed Indicator / Alerter Interface Cable, 30' (9 m) long, 90° "C" Break	G29	\$ 310.00
NYK:Q1250	Universal Interface Panel No Preset	G32	\$ 2,172.00
NYK:Q1251	Universal Interface Panel 128 PPWR Preset	G32	\$ 3,039.00
NYK:Q1253	Universal Interface Panel 249 PPWR Preset	G32	\$ 1,891.00
NYK:Q1254	Universal Interface Panel 128 PPWR Preset	G32	\$ 2,628.00
NYK:Q1260	Universal Interface Panel 249 PPWR Preset	G32	\$ 1,520.00
NYK:Q2014/30V	Ditch Light, Type 1, 30 V	G34	\$ 460.00
NYK:Q2014/75V	Ditch Light, Type 1, 75 V	G34	\$ 460.00
NYK:Q2015/30V	Ditch Light, Type 1, 30 V	G35	\$ 855.00
NYK:Q2015/75V	Ditch Light, Type 1, 75 V	G35	\$ 897.00
NYK:Q2030C	Ditch Light Controller, 8 mph trigger	G36	\$ 814.00
NYK:Q2032C	Ditch Light Controller, 5 mph trigger	G36	\$ 814.00
NYK:D1582H01	Heater Ground Relay, 600 VDC	G38	\$ 1,949.00
NYK:D3676H01	Heater Ground Relay, 750 VDC	G38	\$ 2,253.00
NYK:D17715H03-A01	Penalty Brake Cutout Switch	G40	Call For Pricing
NYK:D17715H04-A01	Brake Penalty Indicator	G40	Call For Pricing
NYK:D17715H03-A01	Brake Penalty Interface Module	G40	Call For Pricing
NYK:C655H01-A02	Maintenance Key Switch	G41	\$ 1,026.00
NYK:D1563H18-A01	GPS Onboard Monitoring Unit	G42	\$ 3,125.00
NYK:D1365H01-A01	Track Receiver Junciton Box	G43	\$ 873.00
ADU	ADU, Aspect Display Units	G44	Call For Pricing
NYK:D1517H01-A01	Locomotive Power Supply, 13.6 VDC (ACSES Radio)	G46	\$ 1,908.00
NYK:D5600H01-A01	Locomotive Power Supply, 32 VDC	G46	\$ 2,328.00
NYK:D1567H08-A01	Locomotive Power Supply, 36 VDC	G46	\$ 3,180.00
NYK: D5600H01-A02	Locomotive Power Supply, 12 VDC (CTV)	G46	\$ 1,932.00
NYK:D177H01-A01	Decelerometer (0.05 mph increments)	G50	\$ 5,665.00
NYK:D177H01-A02	Decelerometer (0.10 mph increments)	G50	\$ 5,665.00
NYK:Q1602	Crash Hardenend Memory Module	G52	\$ 4,565.00
NYK:Q1603-02	Crash Hardenend Memory Module w/ Handle	G52	\$ 4,211.00
NYK:Q1040E	Locomotive Event Recorder, Type 40 Enclosure	G54	\$ 5,763.00
NYK:Q1044E	Locomotive Event Recorder, Type 44 Enclosure	G54	\$ 4,138.00
NYK:Q1046E	Locomotive Event Recorder, Type 46 Enclosure	G54	\$ 3,438.00
NYK:Q1048E	Locomotive Event Recorder, Type 48 Enclosure	G54	\$ 3,005.00
NYK:Q1050E	Locomotive Event Recorder, Type 50 Enclosure	G55	\$ 4,380.00
NYK:Q1067E	Locomotive Event Recorder, Type 67 Enclosure	G55	\$ 4,042.00
NYK:Q1029	Locomotive Event Recorder, Type 29 Enclosure	G55	\$ 7,142.00
Cab Signaling Systems	Cab Signaling Systems	G56	Call For Pricing
Scanner Antenna	Scanner Antenna	G56	Call For Pricing
Intermittent Train Stop Systems	Intermittent Train Stop Systems	G56	Call For Pricing
Variable Timers	Variable Timers	G56	Call For Pricing

Locomotive Systems Products			Price
Mini, Midi and Maxi	Mini, Midi and Maxi	G56	Call For Pricing
Track Receivers	Track Receivers	G56	Call For Pricing
Crew Alerters	Crew Alerters	G56	Call For Pricing

Instrument Housing Products			Price
NYK:058400-44-XX	4' x 4' House	H2	Call For Pricing
NYK:051600-44-XX	4' x 4' House	H2	Call For Pricing
NYK:058400-46-XX	4' x 6' House	H2	Call For Pricing
NYK:051600-46-XX	4' x 6' House	H2	Call For Pricing
NYK:058400-66-XX	6' x 6' House	H2	Call For Pricing
NYK:051600-66-XX	6' x 6' House	H2	Call For Pricing
NYK:058400-68-XX	6' x 8' House	H2	Call For Pricing
NYK:051600-68-XX	6' x 8' House	H2	Call For Pricing
NYK:058400-88-XX	8' x 8' House	H2	Call For Pricing
NYK:051600-88-XX	8' x 8' House	H2	Call For Pricing
NYK:545210-410000	41" Wide Case	H4	Call For Pricing
NYK:567200-410000	41" Wide Case	H4	Call For Pricing
NYK:545110-410000	41" Wide Case	H4	Call For Pricing
NYK:567100-410000	41" Wide Case	H4	Call For Pricing
NYK:545210-600000	60" Wide Case	H4	Call For Pricing
NYK:567200-600000	60" Wide Case	H4	Call For Pricing
NYK:545110-600000	60" Wide Case	H4	Call For Pricing
NYK:567100-600000	60" Wide Case	H4	Call For Pricing
NYK:545210-810000	81" Wide Case	H4	Call For Pricing
NYK:567200-810000	81" Wide Case	H4	Call For Pricing
NYK:545110-810000	81" Wide Case	H4	Call For Pricing
NYK:567100-810000	81" Wide Case	H4	Call For Pricing
NYK:093313-7	Series One Pedestal 14 1/2" Long	H6	\$ 135.00
NYK:093463-11	Series One Pedestal 20" Long	H6	\$ 124.00
NYK:093463-89	Series One Pedestal 20" Long w/ Junction Box	H6	\$ 358.00
NYK:093463-X3	Series One Pedestal 30" Long	H6	\$ 378.00
NYK:091313-BX	Series One Junction Box	H7	\$ 214.00
NYK:091463-BX	Series One Junction Box	H7	Call For Pricing
NYK:091626-BX	Series One Junction Box	H7	\$ 708.00
NYK:091463-224X	Series One Junction Box	H7	\$ 438.00
NYK:093374-4	Series Four Pedestal 14 1/2" Long	H8	\$ 153.00
NYK:093374-26	Series Four Pedestal 20 3/4" Long	H8	\$ 174.00
NYK:093374-28	Series Four Pedestal 14 3/4" Long w/ Junction Box	H8	\$ 688.00
NYK:093374-27	Series Four Pedestal 26 3/4" Long w/ Junction Box	H8	\$ 785.00
NYK:091428-CBX	Series Four Junction Box	H9	\$ 765.00
NYK:091428-223BX	Series Four Junction Box	H9	\$ 802.00
NYK:091428-1ABX	Series Four Junction Box	H9	\$ 1,045.00
NYK:091608-BX	Series Four Junction Box	H9	\$ 1,909.00
NYK:170999-2	Battery Tray 8 1/8" x 38"	H12	\$ 240.00
NYK:170999-1	Battery Tray 8 1/8" x 44"	H12	\$ 253.00
NYK:170999-3	Battery Tray 8 3/8" x 48"	H12	\$ 627.00
NYK:170999-4	Battery Tray 8 3/8" x 55"	H12	\$ 648.00
NYK:170999-7	Battery Tray 9 1/2" x 26"	H13	\$ 627.00
NYK:170999-6	Battery Tray 9 1/2" x 68"	H13	\$ 627.00
NYK:051639-78X	Battery Rack 1 Tier 10 1/4" x 30 1/4"	H14	\$ 638.00
NYK:051640-52X1	Battery Rack 1 Tier 10 1/4" x 60 1/4"	H14	\$ 954.00
NYK:151504-201A	Appartus Box 5" x 6" (Empty)	H16	\$ 2,553.00
NYK:151504-201X	Appartus Box 5" x 6" (Empty w/ Pushbutton)	H16	\$ 2,776.00
NYK:151504-204X	Appartus Box 5" x 6" (Empty w/ Pushbutton and 2 Position Lever Switch)	H16	\$ 3,843.00
NYK:151504-X258	Appartus Box 5" x 6" (Empty w/ Pushbutton and 2 Position Signal Switch)	H16	\$ 3,192.00

Instrument Housing Products			Price
NYK:151504-X261	Appartus Box 5" x 6" (Empty w/ 3 Position Key Switch)	H17	\$ 1,468.00
NYK:151504-X260	Appartus Box 5" x 6" (Empty w/ 2 Position Key Switch)	H17	\$ 1,264.00
NYK:560024-1	Relay Bar for 41" Wide Cases	H20	\$ 41.20
NYK:560024-1X	Relay Bar for 41" Wide Cases w/ Hardware	H20	\$ 49.08
NYK:560024-2	Relay Bar for 60" Wide Cases	H20	\$ 33.99
NYK:560024-2X	Relay Bar for 60" Wide Cases w/ Hardware	H20	\$ 55.00
NYK:560024-3X	Relay Bar for 41" Wide Cases w/ Hardware	H21	\$ 47.00
NYK:560024-4X	Relay Bar for 60" Wide Cases w/ Hardware	H21	\$ 55.00
NYK:420000-54X	Relay Shelf, (1) ST-1 Relay	H22	\$ 78.02
NYK:420000-55X	Relay Shelf, (2) ST-1 Relay	H22	\$ 105.00
NYK:420000-56X	Relay Shelf, (4) ST-1 Relay	H22	\$ 125.00
NYK:051894-281	Air Conditioner 230V 6,000 BTU/HR	H24	Call For Pricing
NYK:051894-282	Air Conditioner 230V 19,000 BTU/HR	H24	Call For Pricing
NYK:051620-38X	Heater 240V, 1,500W, w/ fan and frame	H24	\$ 411.00
NYK:051620-X	Heater 240V, 4,000W, w/ fan and frame	H24	\$ 825.00
NYK:051894-35AX	Ventilation Fan	H25	\$ 218.00
NYK:035035-7X	Ventilation Fan 110 VAC, w/ Aerial Inlet	H25	\$ 714.00
NYK:035035-503X	Ventilation Fan 220 VAC, w/ Aerial Inlet	H25	\$ 714.00
NYK:050971-26X	Cable Riser 36"	H26	\$ 150.00
NYK:035908-1X	Cable Riser 18" w/ Foot Mount	H26	\$ 99.00
NYK:050971-X	Cable Riser 24" w/ Foot Mount	H26	\$ 63.86
NYK:035035-X	Aerial cable inlet	H26	\$ 44.70
NYK:051151-1	Cable support	H26	\$ 56.65
NYK:051128-AX	Door handle	H26	\$ 23.69
NYK:035049-X	Ground terminal	H26	\$ 19.47
NYK:051154-500X	Lamp socket	H26	\$ 60.84

Tools and Accessories			Price	
NYK:030399-19X	Padlock, Zamak w/ Chain and Standard Hex Key	J2	\$	46.11
NYK:030399-15X	Padlock, Zamak w/ Chain and Small Triangle Key	J2	\$	52.19
NYK:030399-X	Padlock, Zamak w/ Chain and Standard Triangle Key	J2	\$	46.11
NYK:030399-87X	Padlock, Zamak w/ Chain and Modified D Key	J2	\$	67.26
NYK:030399-13X	Padlock, Zamak w/o Chain and Standard Triangle Key	J3	\$	43.63
NYK:030399-75X	Padlock, Zamak w/o Chain and Modified D Key	J3	\$	58.89
NYK:030399-16X	Padlock, Zamak w/o Chain and Slotted Hex Key	J3	\$	45.41
NYK:030399-24X	Padlock, Zamak w/o Chain and Slotted Hex Key	J4	\$	46.56
NYK:030399-84X	Padlock, Zamak w/o Chain and Small Hex Key	J4	\$	51.20
NYK:030399-31X	Padlock, Zamak w/o Chain and Standard Hex Key	J4	\$	58.26
NYK:030399-14X	Padlock, Zamak w/o Chain and Small Triangle Key	J4	\$	52.02
NYK:030399-51X	Padlock, Brass w/ Chain and Hex Key	J5	\$	111.00
NYK:030399-1X	Padlock, Brass w/ Chain and Standard Triangle Key	J5	\$	111.00
NYK:032400-X	Semaphonre Oil 1 qt	J7	\$	72.71
NYK:032401-X	NO Oxide Grease 1 pt	J8	\$	50.70
NYK:032619-1X	AAR Terminal Wrench 4 1/2" Long Uninsulated	J10	\$	32.36
NYK:032619-5X	AAR Terminal Wrench 4 1/2" Long Insulated	J10	\$	32.36
NYK:032619-3X	AAR Terminal Wrench 6 1/2" Long Uninsulated	J10	\$	31.95
NYK:032619-6X	AAR Terminal Wrench 6 1/2" Long Insulated	J10	\$	41.63
NYK:032619-8X	AAR Terminal Wrench 11" Long Uninsulated	J11	\$	47.04
NYK:032619-9X	AAR Terminal Wrench 11" Long Insulated	J11	\$	47.04
NYK:032619-28X	AAR Terminal Wrench 5 1/2" Long Uninsulated w/ Triangle Key	J11	\$	61.29
NYK:032619-35X	AAR Terminal Wrench 7 1/2" Long Uninsulated w/ Triangle Key	J11	\$	63.02
NYK:032619-24X	AAR Terminal Wrench 5 1/2" Long Uninsulated w/ Modified D Key	J12	\$	76.81
NYK:032619-34X	AAR Terminal Wrench 7 1/2" Long Uninsulated w/ Modified D Key	J12	\$	78.30
NYK:032619-28	Triangle Key	J12	\$	14.33
NYK:032619-23	Modified D Key	J12	\$	28.64
NYK:032619-22X	Test Nut Wrench 11" Long Insulated w/ Modified D Key	J13	\$	80.03
NYK:032619-30X	Folding Hex Wrench	J13	\$	49.40
NYK:032249-1	Double End Box Wrench	J16	\$	733.00
NYK:032249-2	Switch Adjustment Wrench	J16	\$	401.00
NYK:032249-4	Switch Adjustment Wrench	J16	\$	489.00
NYK:070981-X	Torque Wrench Kit	J17	\$	381.00
NYK:420000-85	Crimping Pliers	J18	\$	110.00
NYK:080600-7	Starting Punch	J20	\$	58.00
NYK:080305-1	Bond Punch	J20	\$	61.53
NYK:080305-2	Bond Punch	J20	\$	58.00
NYK:080090-7	Bond Installation Punch	J20	\$	61.53
NYK:023834	AAR beveled washer	J21	\$	0.30
NYK:023832	AAR clamp nut	J21	\$	1.64
NYK:023831	AAR binding shoulder nut	J21	\$	1.64
NYK:023833-X	2" Ground Stud Post Assembly	J21	\$	4.70
NYK:023833	2" Ground Stud Post	J22	\$	1.15
NYK:023833-4X	1 5/8" Ground Stud Post Assembly	J22	\$	7.96
NYK:023833-4	1 5/8" ground stud post	J22	\$	5.27
NYK:023408-1X	Insulated #14-24 nut	J22	\$	10.03

Tools and Accessories			Price	
NYK:023837	Terminal Connector Clip	J24	\$	2.71
NYK:023839-2	Connector Buss	J24	\$	1.28
NYK:023839-3	Connector Buss	J24	\$	1.69
NYK:023836	Connector Buss	J24	\$	7.64
NYK:023408-5X	Shield and Cap, Bakelite	J23	\$	10.39
NYK:023408-6X	Shield and Cap, Bakelite	J23	\$	10.39
NYK:023408-7X	Shield and Cap, Bakelite	J23	\$	10.39
NYK:023408-8X	Shield and Cap, Bakelite	J23	\$	10.39
NYK:023839-1	Connector Buss	J25	\$	3.72
NYK:023839-5	Connector Buss	J25	\$	4.10
NYK:023839-21	Connector Buss	J25	\$	8.30
NYK:024620-3X	Straight Insulated Link	J26	\$	3.35
NYK:024620-13	Gold Colored Test Nut	J26	\$	3.59
NYK:024620-2X	Straight Insulated Link Assembly	J26	\$	4.02
NYK:024620-1X	Straight Insulated Link Assembly	J26	\$	7.34
NYK:024620-15	Offset Test Link	J27	\$	1.38
NYK:024620-19X	Offset Insulated Link	J27	\$	8.78
NYK:024620-11X	Offset Insulated Link Assembly	J27	\$	10.25
NYK:024620-7X	Offset Insulated Link Assembly	J27	\$	10.25
NYK:024620-14	Straight Link	J28	\$	6.07
NYK:024620-6X	Straight Insulated Link	J28	\$	6.90
NYK:024620-5X	Straight Insulated Link Assembly	J28	\$	6.41
NYK:024620-4X	Straight Insulated Link Assembly	J28	\$	7.31
NYK:024620-16	Offset Link	J29	\$	2.12
NYK:024620-20X	Offset Insulated Link	J29	\$	3.34
NYK:024620-12X	Offset Insulated Link Assembly	J29	\$	3.90
NYK:024620-8X	Offset Insulated Link Assembly	J29	\$	8.37