



## TRANSIENT VOLTAGE SURGE SUPPRESSOR (TVSS)



**DRY CONTACT  
OPTIONAL**



**CUSTOMER  
CONNECTIONS**

INSTALLATION NOTES:

1. RECOMMENDED WIRE SIZE: #6 AWG (15MM ) COPPER WIRE FOR PHASE, NEUTRAL AND GROUND CONNECTIONS.
2. RECOMMENDED BREAKER SIZE: 30-60 AMP CIRCUIT BREAKER.

MODEL NUMBER	VOLTAGE CODE	SERVICE VOLTAGE	Schematic Diagram
TPSMCCA	A	120/240V, 1 PHASE, 3 WIRE	A
TPSMCCB	B	240/120V, 3 PHASE, 4 WIRE	B
TPSMCCC	C	208Y/120V, 3 PHASE, 4 WIRE	C
TPSMCCD	D	240V, 3 PHASE, 3 WIRE	D
TPSMCC E	E	480Y/277V, 3 PHASE, 4 WIRE	C
TPSMCCF	F	480V, 3 PHASE, 3 WIRE	D
TPSMCCG	G	600V, 3 PHASE, 3 WIRE	D
TPSMCCK	K	380Y/220V, 3 PHASE, 4 WIRE	C
TPSMCCL	L	600Y/347V, 3 PHASE, 4 WIRE	C
TPSMCCM	M	240V, 3 PHASE CORNER, GRD	E

<b>SIEMENS</b>
SERIES XTE/XGA TPS MCC