

A man in a white t-shirt and blue overalls is working on a car in a workshop. He is using a power tool on the roof of the car. The background shows a typical workshop environment with various tools and equipment.

SIEMENS

Totally Integrated Power – SIVACON 8PS

Flexible power supply for workshops and production

BD01 and BD2 busbar trunking systems

[siemens.com/busbar](https://www.siemens.com/busbar)




Totally Integrated Power

Totally Integrated Power (TIP) stands for integrated power supply solutions for industries, buildings, and facilities. Siemens' comprehensive electrification portfolio enables a reliable, safe, and efficient power supply using software and hardware products, systems, and solutions for all voltage levels. TIP comprises everything it takes to supply power for challenging environments. Smart interfaces to industrial and building automation systems are the key to tapping the full potential offered by an integrated power supply solution. The portfolio is rounded out by comprehensive support throughout the entire lifecycle – from planning to maintenance.

Purpose-designed for workshops and production – flexible SIVACON 8PS busbar trunking systems

The most important requirement placed on a workshop or production is to be able to tap small volumes of power as near as possible to the consumer load location. The solution: BD01 and BD2 busbar trunking systems from SIVACON 8PS product family. These systems use standardised tap-off units that can be flexibly changed, and are economical as well as safe and reliable.



SIVACON 8PS
busbar trunking systems:
For safe power flows

SIVACON 8PS busbar trunking systems

Versatile power supply in workshops and production

In contrast to conventional cable installation, BD01 and BD2 busbar trunking systems combine cost-effectiveness, flexibility, reliability and safety – and thus deliver real benefits over your competition.

Economic planning and installation

Thanks to simple planning and fast installation of the power distribution network, the SIVACON 8PS busbar trunking systems enable reliable, efficient power supply throughout buildings.

Flexible system when expansions are needed

Both systems are comprised of straight busbar trunking units measuring up to 3.25 m in length, either with or without tap-off points, as well as feeding units, flexible junction units, tap-off units and ancillary equipment units that allow the system to be adjusted or expanded as needed.

High reliability and safety of every module

The design verified switchgear and control-gear assemblies in compliance with IEC 61439-1/-6 allow hazard-free plug-in disconnected from load while energized¹⁾ thanks to a contact apparatus in the tap-off units. Supplementary coding of the modules reduces the risk of operating errors.

SIVACON 8PS Benefits at a glance

Economic advantages

- Simple planning, less time and effort
- Clearly arranged installation
- High level of flexibility for planning and operation
- Power transparency through communication-capable measuring and switching devices

System and operational safety

- Design verified low-voltage busbar trunking systems
- Low fire load

Reliability

- High short-circuit rating
- Easy troubleshooting and error correction


Innovation

- Flexible and safe solution compared to cable

One-stop shop

- Support from planning via installation to operation

1) In accordance with EN 50110-1 (VDE 0105-1); please always observe all national regulations/standards



Modular system for complete freedom in planning and operation


Right from the start, SIVACON 8PS lowers installation and operating costs over the long term because the planning phase goes quickly and thus saves costs.



BD2 system, 160A to 1250A

It's simple with SIMARIS

The SIMARIS planning tools and our local Siemens contacts provide all necessary support, from planning and network calculation to generating line routing plans. Among other tools, SIMARIS sketch can be used to intuitively route busbar runs, visualising the busbar routing, including accessories, in 3D display.



BD01 system, 40A to 160A


Flexible adaptation using BD2

The BD2 system is particularly well suited to applications in the 160A to 1250A range with increased safety requirements. Available in two sizes and in aluminium or copper design, the system covers seven current ratings. Junction units allow flexible adjustments to building structures. Power distribution can be individually adjusted thanks to variable mounting positions and flexible end fittings. The

system can configure standard lengths of 1.25 m, 2.25 m and 3.25 m as well as freely selectable lengths ranging from 0.5 m to 3.24 m, fitting with tap-off points spaced at 0.50 m on either side or offset on both sides every 0.25 m.

Equipping systems with flexible tap-off units using BD01

The BD01 system designed in a single size for 40A to 160A applications can be individually supplemented with protection devices as well further components (Schuko and CEE sockets). The tap-off units can be flexibly positioned without having to de-energise the system¹⁾. Standard lengths of 2 m and 3 m fitted with tap-off points at 0.5 m or 1 m spacing and junction units round out the system features.



from left:

SIMARIS sketch:
Intuitive 3D line routing plans

SIVACON 8PS:
Space-saving and
flexible solution

SIVACON 8PS:
Individually equipped tap-off units

Reducing the time needed for installation

Even during production operations, busbar trunking systems allow simple, fast installation of power runs offering facility-wide power supply. Mounted on the building superstructure, the mechanical and electrical connections can be completed in a single work step. Thanks to the numerous tap-off points available, the system can be installed without precise division of the production hall into sections, or any final machinery arrangement drawing – which saves additional time.

Optimum use in operation

Laying new power cables often entails having to shut down production work. With SIVACON 8PS, however, systems can be changed over quickly. Modular tap-off units and system components simplify system expansion and ensure power supply is maintained. In this way, a facility's entire machinery inventory can be flexibly changed over by plugging and removing tap-off units while energised¹⁾. Another advantage is the clearly arranged configuration of the overall power supply system.

1) In accordance with EN 50110-1 (VDE 0105-1); please always observe all national regulations/standards



Enhanced safety in all areas

Tested safety

The design verified low-voltage switchgear and controlgear assemblies in compliance with IEC 61439-1/-6 make it possible to achieve a high level of safety for people and buildings. Compared to cable installations, the busbars offer a high short-circuit rating and a low fire load.

Reliable in every operational phase

These busbar trunking systems also offer a high degree of protection. Installation of additional machinery will consequently diminish the easy comprehensibility of power cable installation arrangements, for example, while such additions in facilities served by busbar trunking systems will be accommodated by installing switching devices near to the power consumer loads, thus reducing the risk of operating errors.

Protection for personnel

The mechanically guided dismantling and installation of the system, which uses coding of the tap-off units to prevent mix-up errors, ensures a high level of safety.

More areas of application, more orders

Compared to cable installations, these highly flexible busbar trunking systems are more economical in terms of overall cost. Whether for an automotive workshop, a bakery or a manufacturing plant – an innovative power supply system design can be prepared at your premises with the support of expert advisors, starting with initial planning and covering the facility's entire lifecycle. You benefit from a future-proof power supply system that is adaptable for future expansion at low cost.

Support

Time optimization with Siemens as your expert partner at your side

SIVACON 8PS busbar trunking systems on the Internet

Our website offers you a wide range of promotional and technical information as well as helpful tools for the SIVACON 8PS busbar trunking systems.

[siemens.com/busbar](https://www.siemens.com/busbar)



Convenient planning using SIMARIS tools

Planning of electrical power distribution for industrial plants, infrastructure and buildings is increasingly complex. Innovative SIMARIS software tools provide effective support for your planning process enabling you, the electrical designer, to work better and faster under the given conditions.

- **SIMARIS design**

Dimensioning electricity networks and selecting components automatically

- **SIMARIS project**

Calculating space requirements and budgeting for power distribution

- **SIMARIS sketch**

Creating 3D line routing plans for the BD01, BD2, LD and LI busbar trunking systems

[siemens.com/simaris](https://www.siemens.com/simaris)

Technical documentation on the Internet

An up-to-the-minute overview of the available technical documentation of the SIVACON 8PS busbar trunking systems is available on the Internet at

[siemens.com/lowvoltage/product-support](https://www.siemens.com/lowvoltage/product-support)

Tender specifications

We offer you a comprehensive range of tender specification texts to assist at

[siemens.com/specifications](https://www.siemens.com/specifications)

Building on a sound foundation

Our training courses provide you with a solid foundation for your business success.

Experts provide the theoretical and practical knowledge you need for our SIVACON 8PS busbar trunking systems.

[siemens.com/lowvoltage/training](https://www.siemens.com/lowvoltage/training)

Reliable on-site support

Our local experts are there for you worldwide. They help you develop power supply solutions and offer you support with their specialist knowledge in project management and financial services, while always taking important aspects such as safety, logistics, and environmental protection into account.

Expert staff from our TIP Consultant Support unit will provide you with targeted support for the planning and design of electrical power supply systems.

[siemens.com/tip-cs](https://www.siemens.com/tip-cs)

Siemens AG

Energy Management
Mozartstraße 31 c
91052 Erlangen, Germany
siemens.com/busbar

For more information, please contact
our Customer Support Center.
Phone: +49 (0) 180 524 70 00
Fax: +49 (0) 180 524 24 71
(Charges depending on provider)
E-mail: support.energy@siemens.com

Article No. EMMS-B10030-00-7600
Printed in Germany
hl 15111554 | WS | 02161.0
Subject to change

© 2016 Siemens. All rights reserved.
The information provided in this brochure contains
descriptions or characteristics of performance which
in case of actual use do not always apply as described,
or which may change as a result of further development
of the products. An obligation to provide the respective
characteristics shall only exist if expressly agreed in the
terms of contract.

Read the
QR Code with
the QR Code
Reader!

