



Model	
Product brand name	SENTRON
Product designation	accessories





Connections according IEC	
Connectable conductor cross-section	
<ul style="list-style-type: none"> • for copper cable / finely stranded / minimum 	50 mm ²
<ul style="list-style-type: none"> • for copper cable / finely stranded / maximum 	240 mm ²
<ul style="list-style-type: none"> • for copper cable / stranded / minimum 	50 mm ²
<ul style="list-style-type: none"> • for copper cable / stranded / maximum 	300 mm ²
<ul style="list-style-type: none"> • for aluminum cable / stranded / minimum 	50 mm ²
<ul style="list-style-type: none"> • for aluminum cable / stranded / maximum 	300 mm ²
Wire stripping length	28 mm
Tightening torque / when using copper cables	
<ul style="list-style-type: none"> • stranded 	42
<ul style="list-style-type: none"> • finely stranded 	42

Connections according UL	
Wire stripping length	1.1 in
Connectable conductor cross-section	

- for copper cable / stranded / minimum 1 AWG
- for copper cable / stranded / maximum 600 kcmil
- for copper cable / finely stranded / minimum 1 AWG
- for copper cable / finely stranded / maximum 600 kcmil
- for aluminum cable / stranded / minimum 1 AWG
- for aluminum cable / stranded / maximum 600 kcmil

Tightening torque / when using copper cables	
• stranded	370 lb-in
• finely stranded	370 lb-in

Certificates

General Product Approval	EMC	Declaration of Conformity	other
 UL		 RCM	 EG-Konf.
			Miscellaneous

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9373-0JB13>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9373-0JB13>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9373-0JB13

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

11/20/2017