

SIEMENS

Ingenuity for life

SIPROTEC 7SJ82

Feeder and overcurrent protection

www.siemens.com/siprotec

Description

The SIPROTEC 7SJ82 overcurrent protection has been designed specifically for a cost-effective and compact protection of feeders and lines in medium-voltage and high-voltage systems. With its flexibility and the high-performance DIGSI 5 engineering tool, the SIPROTEC 7SJ82 device offers future-oriented solutions for protection, control, automation, monitoring, and Power Quality – Basic.

Main function	Feeder and overcurrent protection for all voltage levels
Inputs and outputs	4 current transformers, 4 voltage transformers (optional), 11 or 23 binary inputs, 9 or 16 binary outputs, or 8 current transformers, 7 binary inputs, 7 binary outputs
Hardware flexibility	Different hardware quantity structures for binary inputs and outputs are available in the 1/3 base module. Adding 1/6 expansion modules is not possible; available with large or small display.
Housing width	1/3 × 19 inches

Applications

- Detection and selective 3-pole tripping of short circuits in electrical equipment of star networks, lines with infeed at one or two ends, parallel lines and open-circuited or closed ring systems of all voltage levels
- Detection of ground faults in isolated or arc-suppression-coil-ground power systems in star, ring, or meshed arrangement
- Backup protection for differential protection devices of all kind for lines, transformers, generators, motors, and busbars
- Protection and monitoring of simple capacitor banks
- Phasor Measurement Unit (PMU)
- Reverse-power protection
- Load shedding applications
- Automatic switchover



SIPROTEC 7SJ82

- Regulation or control of power transformers (two-winding transformers)
- Detection and recording of power-quality data in the medium-voltage and subordinate low-voltage power system

Functions

DIGSI 5 permits all functions to be configured and combined as required.

- Directional and non-directional overcurrent protection with additional functions
- Optimized tripping times due to directional comparison and protection data communication
- Detection of ground faults of any type in compensated or isolated electrical power systems using the following functions: 3I0>, V0>, transient ground-fault function, $\cos \phi$, $\sin \phi$, dir. detection of intermittent ground faults, harmonic detection, and admittance measurement
- Ground-fault detection using the pulse-detection method
- Detection of intermittent ground faults with automatic blocking of statically measuring functions to avoid message and fault-record flooding
- Fault locator plus for accurate fault location with inhomogeneous line sections and targeted automatic overhead-line section reclosing (AREC)

Compact and flexible

- Arc protection
- Overvoltage and undervoltage protection
- Frequency protection and frequency change protection for load shedding applications
- Automatic frequency relief for underfrequency load shedding, taking changed infeed conditions due to decentralized power generation into consideration
- Power protection, configurable as active or reactive power protection
- Protection functions for capacitor banks, such as overcurrent, overload, current unbalance, peak overvoltage, or differential protection
- Directional reactive power undervoltage protection (QU protection)
- Control, synchrocheck and switchgear interlocking protection, circuit-breaker failure protection
- Circuit-Breaker Failure Protection
- Circuit breaker reignition monitoring
- Graphical logic editor to create powerful automation functions in the device
- Detection of current and voltage signals up to the 50th harmonic with high accuracy for selected protection functions (such as peak overvoltage protection for capacitors) and operational measured values
- PQ - Basic: Voltage unbalance; voltage changes: overvoltage, dip, interruption; TDD, THD, and harmonics
- Single-line representation in small or large display
- Integrated electrical Ethernet RJ45 for DIGSI 5 and IEC 61850 (reporting and GOOSE)
- 2 optional, pluggable communication modules, usable for different and redundant protocols (IEC 61850-8-1, IEC 60870-5-103, IEC 60870-5-104, Modbus TCP, DNP3 serial and TCP, PROFINET IO)
- Serial protection data communication via optical fibers, two wire connections and communication networks (IEEE C37.94, and others), including automatic switchover between ring and chain topology
- Reliable data transmission via PRP and HSR redundancy protocols
- Extensive cybersecurity functionality, such as role-based access control (RBAC), logging of security-related events, signed firmware, or authenticated IEEE 802.1X network access
- Simple, fast, and secure access to the device via a standard Web browser to display all information and diagnostic data, vector diagrams, single-line and device display pages Whitepaper Phasor Measurement Unit (PMU) for synchrophasor measured values and IEEE C37.118 protocol
- Time synchronization using IEEE 1588
- Control of Power Transformers
- Powerful fault recording (buffer for a max. record time of 80 sec. at 8 kHz or 320 sec. at 2 kHz)
- Auxiliary functions for simple tests and commissioning

Benefits

- Compact and low-cost overcurrent protection
- Safety due to powerful protection functions
- Purposeful and easy handling of devices and software thanks to a user-friendly design
- Cybersecurity according to NERC CIP and BDEW Whitepaper requirements (for example, logging security-related events and alarms)
- Highest availability even under extreme environmental conditions by standard coating of the modules
- Full compatibility between IEC 61850 Editions 1, 2.0, and 2.1



Siemens 2020
Smart Infrastructure
Digital Grid
Humboldtstrasse 59
90459 Nuremberg,
Germany

For the U.S. published by
Siemens Industry Inc.

100 Technology Drive
Alpharetta, GA 30005
United States

Customer Support: <http://www.siemens.com/csc>

© Siemens 2020. Subject to changes and errors.
SIPROTEC 7SJ82_Profile V1.docx_12.20

For all products using security features of OpenSSL, the following shall apply:

This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (www.openssl.org), cryptographic software written by Eric Young (eay@cryptsoft.com) and software developed by Bodo Moeller.