

SIEMENS

Ingenuity for life

SIPROTEC 7UM85

Generator protection

www.siemens.com/siprotec

Description

The generator protection device SIPROTEC 7UM85 has been designed specifically for the protection of generators and power units. It contains all necessary main protection functions and a large number of other protection and monitoring functions. With its modular structure, flexibility, and the high-performance DIGSI 5 engineering tool, SIPROTEC 7UM85 offers future-oriented solutions for protection, control, automation, monitoring, and Power Quality – Basic. For motors in explosive environments, the SIPROTEC 7UM85 is also available with EN 60079-14 or VDE 0165, Part 1, ATEX (Verband der Elektrotechnik, Elektronik und Informationstechnik) certification

Main function	Typical generator protection functions
Inputs and outputs	5 predefined standard variants with up to 16 current transformers and 8 voltage transformers, 7 to 15 binary inputs, 9 to 20 binary outputs 4 fast measuring transducer inputs (10 V or 20 mA)
Hardware flexibility	Flexibility adjustable and expandable I/O quantity structure within the scope of the modular SIPROTEC 5 system; 1/6 expansion modules can be added, available with large or small display, or without display
Housing width	1/3 × 19 inches to 2 × 19 inches

Applications

- Protection of generators in busbar connection of different power, with directional stator ground-fault protection.
- Protection of generators in unit connection of different power (using the 100 % stator ground fault (20 Hz) with larger generators)
- Protection of power units with one device per protection group. In the generator transformer variant, the 7UM85 implements both generator and transformer protection.



SIPROTEC 7UM85 Generator Protection (width: 1/3 × 19" to 2 × 19")

- In more complex power units (unit connection with generator circuit breaker and several auxiliary transformers), additional SIPROTEC 5 devices are used, for example, 7UT8x, 7SJ82, or 7SJ85 and 7SA, SD, SL86, at the upper-voltage side of the generator transformer.
- Using motor and generator protection functions (for example, underexcitation protection) to protect synchronous motors
- Detection and recording of power-quality data in the medium-voltage and subordinate low-voltage power system

Functions

DIGSI 5 permits all functions to be configured and combined as required.

- Short-circuit protection (overcurrent protection, impedance protection, differential protection)
- Stator ground-fault protection (90% non-directional or directional, 100% with 3rd harmonic, real 100% protection with 20-Hz voltage interference)
- Rotor ground-fault protection with different measuring methods (ground current or ground-resistance monitoring)
- Underexcitation and overexcitation protection

Efficient and modular

- High-precision reverse-power protection and universal power protection
- Unbalanced-Load Protection
- Overload protection and temperature supervision via external RTD unit (with PT 100, for example)
- Universal overvoltage and undervoltage protection with different measuring methods
- Overfrequency and underfrequency protection, frequency change protection and monitoring of dwell time in frequency bands as turbine protection (protection against abnormal frequencies)
- Protection functions for network decoupling (voltage and frequency protection, directional reactive power undervoltage protection (QU protection) and vector-jump protection)
- Inadvertent energization protection to detect incorrect activation of the circuit breaker
- Circuit-breaker failure protection
- Circuit breaker reignition monitoring
- Single-channel parallel connection function (synchronization) with adjustment commands for rotational speed (frequency) and voltage
- Graphical logic editor to create powerful automation functions in the device
- Integrated electrical Ethernet RJ45 for DIGSI 5 and IEC 61850 (reporting and GOOSE)
- Up to 4 pluggable communication modules, usable for different and redundant protocols (IEC 61850-8-1, IEC 61850-9-2 Client, IEC 60870-5-103, IEC 60870-5-104, Modbus TCP, DNP3 serial and TCP, PROFINET IO, PROFINET IO S2 redundancy)
- Virtual network sharing (IEEE 802.1Q - VLAN)
- Reliable data transmission via PRP and HSR redundancy protocols
- PQ-Basic: voltage unbalance; voltage changes: over-voltage, dip, interruption; TDD, THD and Harmonics
- Extensive cybersecurity functionality, such as role-based access control (RBAC), protocolling security-related events, signed firmware or authenticated network access IEEE 802.1X
- Simple, fast and secure access to the device via a standard Web browser to display all information and diagnostic data, as well as vector diagrams, single-line and device display pages
- Phasor Measurement Unit (PMU) for synchrophasor measured values and IEEE C37.118 protocol
- Time synchronization using IEEE 1588
- Capturing operational measured variables and protection function measured values for the evaluation of the system, to support commissioning, and to analyze faults
- Frequency tracked protection functions over a wide frequency range (10 Hz to 80 Hz) and the option to assign the protection functions in a single device to different frequency tracking groups.
- Powerful fault recording (buffer for a max. record time of 80 sec. at 8 kHz or 320 sec. at 2 kHz)
- Flexibly adjustable I/O quantity structure within the scope of the SIPROTEC 5 modular system

Benefits

- Safe and reliable automation and control of your systems
- Purposeful and easy handling of devices and software thanks to a user-friendly design
- Cybersecurity in accordance with NERC CIP and BDEW Whitepaper requirements
- Highest availability even under extreme environmental conditions by standard coating of the populated printed circuit boards



Siemens 2020
Smart Infrastructure
Digital Grid
Humboldtstrasse 59
90459 Nuremberg,
Germany

For the U.S. published by
Siemens Industry Inc.

100 Technology Drive
Alpharetta, GA 30005
United States

Customer Support: <http://www.siemens.com/csc>

© Siemens 2020. Subject to changes and errors.
SIPROTEC_Profile V1.docx_12.20

For all products using security features of OpenSSL, the following shall apply:

This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (www.openssl.org), cryptographic software written by Eric Young (eay@cryptsoft.com) and software developed by Bodo Moeller.