



IF IN DOUBT ASK
DO NOT SCALE

**NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED**



Ø4.4-2 HOLES

TYPICAL OVERALL DIMENSIONS AND MOUNTING DETAILS FOR THE 2435H90000 SERIES OF RESISTOR ASSEMBLIES

**PRINTED ON 18/10/2012
ENSURE CORRECT REVISION
DESTROY AFTER USE**

MATERIAL:

Copyright © 2012 Siemens Protection Devices Ltd. Hebburn

1	17/10/12	CHANGE	△
ISSUE	DATE	NOTED	

Dimensions in millimetres : Surface texture in micrometres.
Machine where marked ✓
For explanation of dimensions, tolerances, notes etc. see B.S.308.
Limit on untoleranced unmachined dimensions ± _____
Limits on untoleranced machined dimensions to B.S.4500;
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
over 6 to 30±0.2; over 120 to 315±0.5;
General unmachined angular tolerance ± _____

Finish:

Treatment:

Title:
**OVERALL DIMENSION, WIRING AND MOUNTING
FOR DROPPER RESISTOR ASSEMBLIES**

SIEMENS PROTECTION DEVICES LTD.

Original Scale:
1:2

First used on:
Similar Articles:
Supersedes:
Drg.No.
2435X90000

DRAWN: J.BURNETT	CHECKED:RD.WATSON	APPROVED:RD.WATSON	DATE: 18/10/2012	I.E.	OPS.	PCP.	Purch. Spec.	TQ.	EAC	CE.	STD.	A4h
------------------	-------------------	--------------------	------------------	------	------	------	--------------	-----	-----	-----	------	-----