

# SIEMENS

## Indoor Load Center

Catalog Number	Series	Enclosure
<b>E0204ML1060S</b>	<b>A</b>	<b>Type 1</b>
<b>E0204ML1060F</b>	<b>A</b>	<b>Type 1</b>

**RATINGS:** 60 AMPS. MAX.  
120/240 VOLTS ~ 1 PHASE 3 WIRE  
208Y/120 VOLTS ~ 1 PHASE 3 WIRE

FOR INSTALLATION BY A QUALIFIED PERSON IN ACCORDANCE WITH ALL LOCAL ELECTRICAL CODES AND/OR THE NATIONAL ELECTRICAL CODE®.

SHORT CIRCUIT CURRENT RATING - SEE ADJACENT LABEL 4810268.

TO RESET BREAKERS WITH TRIPPED HANDLE POSITION BETWEEN "ON" AND "OFF", MOVE HANDLE TO "OFF" THEN TO "ON".

### ACCESSORIES:

1" FILLER PLATE - CAT. NO. QF3  
GROUND BAR: CAT. NO. ECGB5, 5 TAPS

**USE CU/AL WIRE** AT PANELBOARD LINE AND NEUTRAL TERMINALS. SEE MARKINGS ON BREAKERS FOR THEIR WIRING AND TORQUE REQUIREMENTS.

LINE TERMINALS A AND B SUITABLE FOR 60°/75° C CONDUCTORS.  
WIRE SIZE: #14-#2 AWG.  
TORQUE TERMINALS TO 35 LB-IN FOR #14-#10 AWG, 40 LB-IN FOR 8 AWG AND 45 LB-IN FOR #6-2 AWG.

Tighten neutral bar terminals as shown below

Wire Size/Range	14-10 AWG	8 AWG	6 AWG	4-2 AWG
Small Terminals:	20 LB-IN	25 LB-IN	35 LB-IN	---
Large Terminals:	35 LB-IN	40 LB-IN	45 LB-IN	45 LB-IN

® The National Electrical Code is a registered trademark of the National Fire Protection Association.


© 2010 Copyright Siemens Industry, Inc.

Assembled in Mexico

Siemens Industry, Inc., Norcross, Georgia U.S.A.

J2 4094869-1 Rev.A

**IMPORTANT:** DO NOT ALLOW PETROLEUM BASED (HYDROCARBON) SPRAYS, CHEMICALS, SOLVENTS OR ANY PAINT TO CONTACT INTERIOR COMPONENTS. PETROLEUM BASED CHEMICALS CAN CAUSE DEGRADATION OF ELECTRICAL INSULATING MATERIALS.



### SUITABLE FOR USE AS SERVICE EQUIPMENT

WHEN NOT USED AS A LIGHTING AND APPLIANCE BRANCH CIRCUIT PANELBOARD (SEE ARTICLE 408.14 OF THE NATIONAL ELECTRICAL CODE®). WHEN USED AS SERVICE EQUIPMENT, APPLY "SERVICE DISCONNECT" LABEL(S) TO FRONT NEXT TO APPROPRIATE BREAKER HANDLE(S).

NOT FOR USE AS SERVICE EQUIPMENT IN CANADA

WHEN REQUIRED, BOND THE NEUTRAL TO THE ENCLOSURE WITH BONDING STRAP PROVIDED. FOLLOW INSTRUCTIONS PRINTED ON BAG.

### GROUND BAR WIRE SIZE

COPPER: ONE #14-#4 AWG OR TWO OR THREE #14-#10 AWG  
ALUMINUM: ONE #12-#4 AWG OR TWO OR THREE #12-#10 AWG