

[Siemens.com/mobility](https://www.siemens.com/mobility)

QEECF1 Relay

A twin dc operated tractive armature lamp proving relay

General data

Contact Arrangement: 2 x 2F
Nominal Rated Current: 1.5 A
Approximate Weight: 1.3 kg

Note: Refer to the following data sheets:

- 7-1-1 for general information and contact ratings.
- 7-2-1 for dimensions.
- 8.2 for tools.
- 8.3 for plugboard and connector details.

Refer overleaf for specific data.




Typical Twin Coil Relay

Description

Designed specifically for use with level crossing flashing road signals. It comprises two electrically independent relays mounted side-by-side on a single base. This relay supersedes the QEECF1.

Contact layout viewed from rear



Packaging

Q-Relays are packed in a carton holding ten relays; the same container is used for quantities of four to nine relays. Quantities less than four are packed individually in cardboard boxes, as are all train-carried relays. Each container has a bar-coded label affixed to the outside, stating details of the packaged relay(s) and the quantity therein.

EMC Compliance

Q-Relays comply with the relevant emission requirements of EN 55014. It is considered that these relays have inherent immunity to in-service electromagnetic disturbance.


A Technical Certificate for EU Directive on EMC (89/336/EEC) has been obtained.

Technical data

SIEMENS Part No. (PAD No.)	CONTACT ARRANGEMENT	RATED CURRENT (A dc)	PIN CODE	COIL RES (OHMS)	WDG SPEC 1/108/-	MAX FULL OP. (mA dc)	MIN REL (mA dc)	PLUGBOARD	REQD No. OF CONNECTORS J4137/3	REMARKS
B18568/1 (85/001730)	2F LH & RH	1.5	030	0.4	170	1310	650	J4138/386	12	BRB SPEC 966F8



Un-drilled plugboard
Part No. E7218/1



Representation of Relay,
Plugboard and Retaining clip
(Clip Part No. J4136/1)

Siemens Mobility Limited
Rail Automation
PO Box 79
Pew Hill
Chippenham
Wiltshire SN15 1JD
UK
www.siemens.com/mobility

Printed in the United Kingdom

Data Sheet 7-2-28

X342/55/000047 Revision 06

SIEMENS
Ingenuity for life

The information within this document contains general descriptions of the technical options available, which do not always have to be present in individual cases. The required features should therefore be specified in each individual case at the time of closing the contract.