

Siemens Switzerland Ltd., DI, CH-8047 Zürich

Name Fernando Granados  
 Department Digital Industries  
 Business Development and Marketing  
 Phone +41 585 585 595  
 E-Mail fernando.granados@siemens.com  
 Date September 16<sup>th</sup>, 2021

### Delivery situation for products of Digital Industries (DI) and Smart Infrastructure (SI EP) (Status as of September 16<sup>th</sup>, 2021)

#### Factory Automation:

Product family	Actual delivery time	Standard delivery time
SIMATIC S7-1500 CPUs Modular	60 WD - 95 WD*	1 WD*
SIMATIC S7-1500 Compact CPU <sup>1)</sup>	180 WD	1 WD
SIMATIC S7-1500 I/Os	35 WD - 100 WD	1 WD
SIMATIC ET200 MP (IM)	45 WD	1 WD
SIMATIC S7-300 CPUs	50 WD - 95 WD	1 WD
SIMATIC S7-300 I/Os	50 WD - 95 WD	1 WD
SIMATIC ET200 M	50 WD - 75 WD	1 WD
SIMATIC ET200 SP CPUs	50 WD - 65 WD	1 WD
SIMATIC ET200 SP Open Controller (2. Gen.)	30 WD	1 WD
SIMATIC ET200 SP Heads (IM)	75 WD	1 WD
SIMATIC ET200 SP Base Units	50 WD - 80 WD	1 WD
SIMATIC ET200 SP I/Os	55 WD - 100 WD	1 WD
SIMATIC ET200 ecoPN	35 WD	1 WD
SIMATIC ET200 Pro	35 WD	1 WD
SIMATIC ET200 AL	35 WD	1 WD
SIMATIC S7-1200 CPUS	40 WD	1 WD
SIMATIC S7-1200 Modules	20 WD	1 WD
LOGO! Modules (EM)	25 WD	1 WD
SIMATIC HMI Comfort Panels 4"-22"	50 WD - 95 WD	1 WD
SIMATIC HMI Mobile Panels	40 WD - 55 WD	1 WD
SIMATIC HMI Basic Panels 12"	30 WD	1 WD
SIMATIC HMI Comfort Panels PRO / INOX **	1 WD - 70 WD	1 WD
SIMATIC HMI Industrial Flat Panels V2 **	1 WD - 70 WD	1 WD
SIMATIC HMI Industrial Thin Clients V3 **	1 WD - 70 WD	1 WD
SIMATIC HMI Accessories **	1 WD - 70 WD	1 WD
SIMATIC IPC 2x7X / 4x7D, E(PRO)** <sup>2)</sup>	60 WD	15 WD
SIMATIC IPC 6x7D, E / 8x7D, E** <sup>2)</sup>	80 WD	15 WD
SIMATIC IPC 547G, J ** <sup>2)</sup>	80 WD	15 WD
SIMATIC IPC 127E / 3x7E ** <sup>2)</sup>	100 WD	1 WD
SIMATIC IOT2040**	80 WD	1 WD
SIMATIC IPC Tablet/Field PG	45 WD	15 WD
SIMOTION D410-2	80 WD	1 WD
SIMOTION D425-2/D435-2/D445-2/D455-2	80 WD	1 WD
SIMOTION D CX32-2	80 WD	1 WD
SIMATIC Drive Controller	80 WD	1 WD

\* WD = Working days

\*\* Standard and Customized

1) These products are currently not available. Please contact your local salesperson for more information.

2) New orders will be confirmed according to material availability.

## Motion Control Products:

Product family	Actual delivery time	Standard delivery time
SINAMICS G120/G130/S120 chassis	30 - 45 WD*	15 WD*
SINAMICS S120 booksize (GWE)	70 WD	10 WD
SINAMCIS S120M	45 WD	25 WD
SINAMICS S210-3ph	30 WD	15 WD
SINAMICS G120 blocksize FSD-F	20 WD	5 - 15 WD
SINUMERIK 840D	80 WD	10 WD
SINAMICS Accessories (e.g. chokes, encoders, CU's)	60 - 95 WD	10 - 15 WD
SINUMERIK Accessories (e.g. TCU, Panels, MCPs)	70 - 80 WD	15 WD
SINUMERIK ONE	80 WD	15 WD
Motion Connect Signal Cables (Drive CLiQ)	70 WD	5 WD
Motion Connect Power Cables M23	70 WD	15 WD
Motion Connect Cables M17	70 WD	5 WD
Motion Connect	70 WD	5 WD
828D packages w/o 1PH8 or S120 booksize	45 - 65 WD	20 WD
828D packages with 1PH8 / S120 booksize	70 / 80 WD	20 WD
828D packages w/o 1PH8 or S120 booksize <b>(SNC)</b>	45 - 65 WD	20 WD
828D packages with 1PH8 / S120 booksize <b>(SNC)</b>	70 / 80 WD	20 WD
SINAMICS V20 (7,5 - 15 kW) (ordered by CN, Asia)	35 WD	< 5 WD
SINAMICS V20 (7,5 - 15 kW) (ordered by others)	20 - 25 WD	
SINAMICS V90 (3,5 - 7 kW) (ROW)	50 WD	
SINAMICS G120/G130/S120 chassis	30 - 45 WD	15 WD
S120 Combi <b>(SNC)</b>	40 WD	5 WD
SINAMICS G120 <b>(SNC)</b>	45 WD	5 - 15 WD
SINAMICS G120XA (0,75-250kW) <b>(SNC)</b>	45 WD	15 WD
G115D	35 WD	15 WD
SINAMICS G120C	40 WD	< 5 WD
SINAMICS G120X / PN	15 / 20 WD	10 WD
SINAMICS G110M	20 WD	3 WD
SINAMICS G120 PM240-2 / PM230-2 <b>(CON)</b>	55 WD	5 WD
SINAMICS G120 D <b>(CON)</b>	25 WD	< 5 WD
SINAMICS Accessories (e.g. chokes, encoders, CUs, BOP, IOP, ET200 pro) <b>(CON)</b>	20 - 55 WD	5 WD
SINAMICS G180 compact	100 WD	75 WD
SINAMICS G180 compact cabinet	100 WD	75 WD
SINAMICS G180 cabinet air (6 - 12 pulse)	100 WD	75 WD
SINAMICS G180 cabinet water (6 - 12 pulse)	100 WD	75 WD
Dynavert L	100 WD	75 WD
Dynavert I	100 WD	75 WD
SIMODRIVE	40 WD	30 WD
SIMOTICS GP/SD FS 140-250 (Small Frames)	60 - 70 WD	20 WD
SIMOTICS GP/SD FS 280-440 (Large Frames)	60 - 70 WD	30 WD
SIMOTICS SD IEEE/XP FS 140-250 (Small Frames)	60 - 70 WD	20 WD
S120 Combi <b>(SNC)</b>	40 WD	5 WD
SIMOTICS SD IEEE/XP FS 280-440 (Large Frames)	60 - 70 WD	30 WD
SIMOTICS SD FS 509 to FS 513	80 WD	40 WD
SIMOTICS SD/GP – Standard motors 1LE0 (CN)	25 WD	10 WD

# SIEMENS

Product family	Actual delivery time	Standard delivery time
SIMOTICS Servo – Standard motors 1FL6 (CN, stock)	35 WD	5 WD
SIMOTICS Servo – Standard motors 1FL6 (ROW)	50 WD	5 WD
SIMOTICS 1FK7	45 - 60 WD	10 - 15 WD
SIMOTICS 1FK2	35 WD	15 WD
1FK2 >= AH40	25 WD	15 WD
SIMOTICS 1FK7 Gen. 2 (w/o SMI / w SMI)	50 / 60 WD	10 - 15 WD
SIMOTICS 1FK701* & 1FK702* Gen. 1 (w/o SMI / w SMI)	15 / 60 WD	20 WD
1FT7	50 WD	20 WD
SIMOTICS 1FG1	70 WD	15/15/40/50/90
SIMOTICS 1PH8 Asynchron 80/100	60 WD	20 WD
SIMOTICS 1PH8 Asynchron 130/160	60/100 WD	20 WD
SIMOTICS 1PH8 shed	60 WD	40 WD
SIMOTICS 1PH8 Synchron	60 WD	40 WD
1FE1	80 WD	30 WD
1FW3	45 WD	30 WD
1FW6	50 WD	25 WD
1FN3	50 WD	20 WD
SIMOTICS SD IEEEX/XP FS 280-440 (Large Frames)	60 - 70 WD	30 WD
SIMOTICS 1PH7	60 WD	40 WD
SIMOTICS SD 1LE5 FS 400/450	45 WD	
Simogear 2KJ8 (G115D) A+B	50 WD	25 WD
SIMOGEAR (Kat. A/B/C/D)	25/25/30/55 WD	15/15/30/40 WD
SIMOTICS GP/SD/DP 1LE1 / 1FP1 / 1PC1 FS 63-90	50 WD	2/5/10 WD
SIMOTICS GP/SD/DP 1LE1 / 1FP1 / 1PC1 FS 100	70 WD	2/5/10 WD
SIMOTICS GP/SD/DP 1LE1 / 1FP1 / 1PC1 FS 112	70 WD	2/5/10 WD
SIMOTICS GP/SD/DP 1LE1 / 1FP1 / 1PC1 FS 132	80 WD	2/5/10 WD
SIMOTICS GP/SD/DP 1LE1 / 1FP1 / 1PC1 FS 160	80 WD	2/5/10 WD
SIMOTICS GP/SD/DP 1LE1 / 1FP1 / 1PC1 FS 180-200	85 WD	2/5/10 WD
SIMOTICS XP 1MB1 FS 63-200	50 - 85 WD	25 WD
SIMOTICS SD/DP 1LE1/ 1FP1 / 1PC1 FS 225-315	50 - 60 WD	20 WD
SIMOTICS SD 1LE5 FS 315/355	50 WD	20 WD
SIMOTICS XP 1MB1/1MB5 (ex*) FS 225-355	50 - 60 WD	30 WD
SIMOTICS 1PH8 (FS180/225/280)	60 WD	30/30/45 WD

\* WD = Working days

## Process Automation:

Product family	Actual delivery time	Standard delivery time
PCS 7 SIMATIC IPC Family	45 - 80 WD*	15 WD*
Y-LINK for 1Channel DP-SLAVES	15 WD	1 WD
ET 200M IM, Field Device Coupler	25 WD	1 WD
S7-400 Family S7-400 CPU + I/O Signals	15 WD	1 WD
ET200 iSP Family	35 WD	15 WD
ET200SP HA	5 - 15 WD	15 WD
ET 200SP HA Ex und Pot Isol.	20 WD	30 WD
SIWAREX WP (WAEGELEKTRONIK)	40 WD	1 WD
SCALANCE X 000/100/200/300	1 - 60 WD <sup>2)</sup>	1 WD
SCALANCE Plugable Transceiver	5 - 30 WD <sup>2)</sup>	1 WD
SCALANCE M	30 WD - on request <sup>2)</sup>	1 WD
SCALANCE W	order stop <sup>5)</sup>	1 - 5 WD
SCALANCE S	15 - on request <sup>2)</sup>	1 WD
Product family	Actual delivery time	Standard delivery time

# SIEMENS

SIMATIC RF200R / RF300R	1 - 30 WD <sup>2)</sup>	1 WD
SIMATIC RF600R / MV540 H	on request	1 - 15 WD
Transponder MDS D1xx/4xx, RF600, RF300	1 WD - on request <sup>2)</sup>	1 WD
SIMATIC CP1623/1616/1604	15 - 60 WD	1 WD
SIMATIC CP1542/1543/1545, CM1542	5 - 95 WD	1 WD
SIMATIC CP443/1242/1243, CSM1277	5 - 40 WD <sup>2)</sup>	1 WD
IE FC RJ45 plug / IE FC M12 plug	1 - 10 WD <sup>2)</sup>	1 WD
RCOAX / IWLAN cable	on request	1 WD
SIMATIC RF120C/166C/188C	1 - 15 WD <sup>2)</sup>	1 WD
SITOP SEL1200 / SEL1400	10 WD	1 WD
SIMATIC ET200PRO PS	20 WD	1 WD
SITOP PSU8200 (3AC 20 A / 40 A)	50 WD / 100 WD	1 WD
SITOP PSU200M 10 A / PSU300S 20 A, 40 A	20 WD	1 WD
SITOP UPS1600	20 WD	1 WD

\* WD = Working days

2) Depending on MLFB

## Electrical Products (SI EP):

Product family		Actual delivery time	Standard delivery time
5SV1	- SENTRON RCBO compact	15 WD*	2 - 5 WD*
5SM2	- SENTRON RC unit	10 WD	2 - 5 WD
5SL30, 5SL60	- SENTRON MCB compact	50 WD	2 - 5 WD
5SL4,6	- SENTRON MCB	30 WD	2 - 5 WD
5SU1	- SENTRON RCBO	40 WD	2 - 5 WD
3RW3	- SIRIUS Soft Starter	25 WD	2 - 5 WD
3RW4	- SIRIUS Soft Starter	50 WD	2 - 5 WD
3RW5	- SIRIUS Soft Starter	50 WD	2 - 5 WD
3SU1 LED	- SIRIUS ACT	30 WD	2 - 5 WD
3SU1 ASI / IO Link	- SIRIUS ACT	80 WD	2 - 5 WD
3SU1 others	- SIRIUS ACT	25 WD	2 - 5 WD
3RK (some types)	- AS-i K20+K45 module	80 WD	2 - 5 WD
3VA9***J***	- SENTRON MCCB lug	40 WD	2 - 5 WD
3VM9***J***	- SENTRON MCCB lug	40 WD	2 - 5 WD
3WL	- SENTRON ACB	35 WD	2 - 5 WD
3RT2 S00	- SIRIUS Contactor	30 WD	2 - 5 WD
3RT2 S0/S2	- SIRIUS Contactor	45/20 WD	2 - 5 WD
3RV S2/S3 & 3RV20	- SIRIUS MSP	20/30 WD	2 - 5 WD
3LD	- SENTRON LBS	60 WD	2 - 5 WD
3NB/3NC/3NE/3NW	- Fuses (some)	25 WD	2 - 5 WD
5SV3-5 (Type A, F, AC, G w/o Typ B)	- SENTRON RCBO	70 WD	2 - 5 WD
5SV3 Typ B	- SENTRON RCBO	80 WD	2 - 5 WD
5SY (w/o 5SY...CC)	- SENTRON MCB	40 WD	2 - 5 WD
5SJ4...HG...UL489			
3RM	- SIRIUS Motor Starter	120 WD	2 - 5 WD

\* WD = Working days

Most orders we are still confirming with our communicated standard lead times. However, due to the very high demand in recent weeks and the tight capacity situation at some of our plants as a result of Covid19, we have extended standard delivery times for a few products.

# SIEMENS

## **Spare Parts and their necessity for performing services:**

In principle, we have a stock of spare parts in stock and can therefore provide the related service, but the delivery times for repeat orders depend on the standard delivery time and availability of the products. This can therefore also (occasionally) affect service delivery. We ask you to clarify the extent of the impact with us in individual cases. You find our contact details on the internet at [www.siemens.ch/industry/kontakt/fr](http://www.siemens.ch/industry/kontakt/fr).