

SIEMENS

Ingenuity for life

Project6 ▶ Control device_1 [SIMOCODE pro V] ▶ Traces ▶ Trace

Status: Recording completed



Take a step into the future
with SIMOCODE pro

The motor management system for safety,
transparency and efficiency. Connected to the Cloud.

usa.siemens.com/simocode



SIMOCODE pro – synonymous with motor management.

People today use the word SIMOCODE to mean “motor management and control devices” because SIMOCODE is easy to use, reliable, and the most advanced motor management system on the market, and as the technology leader, has developed an interface to the cloud.

Flexible, modular, integrated – the way modern motor management should be.

For 30 years, SIMOCODE pro has been controlling and monitoring low-voltage, constant-speed motors all over the world. For plant reliability, SIMOCODE is used to keep motors running. And with its Cloud-based connection, SIMOCODE gives you more transparency and power.

The highlights of SIMOCODE pro

- Extensive protection, monitoring and control functions, independent of the automation system
- Detailed operational, service and diagnostics data – at any time or place in new or existing systems
- Safe shutdown of motors
- Scalable, flexible solutions for all plant configurations
- Versatile, open communication via various bus systems and protocols
- Integration in process control systems such as SIMATIC PCS 7

SIMOCODE pro offers multifunctional, solid-state full motor protection. The motor management system monitors, protects and controls constant-speed motors and enables the implementation of predictive maintenance. It does not wait for a problem to occur before shutting down the motor, but establishes a level of transparency in advance to avoid shutdowns and improve productivity.

SIMOCODE pro delivers detailed operating, service and diagnostic data across the entire process.

SIMOCODE is easy to use, requires no advanced engineering, and integrates into virtually any automation system. SIMOCODE pro communicates via PROFIBUS and PROFINET, Modbus RTU, EtherNet/IP and OPC UA.

With both the SIMOCODE pro General Performance and SIMOCODE pro High Performance device classes, we offer scalable, flexible solutions for industrial controls and plant optimization in the context of Industry 4.0.

SIMOCODE pro – Modern motor management: scalable and modular

Two device series form the core of the multifunctional SIMOCODE pro motor management system: General Performance and High Performance. The devices in both series incorporate all essential motor protection, monitoring and control functions – including data transparency through the Cloud connection. SIMOCODE pro General Performance is your entry into modern motor management and addresses standard motor applications. SIMOCODE pro High Performance features up to five expansion modules, including fail-safe modules, and offers additional measured variables. Find out how you can take advantage of the two SIMOCODE pro device series in all areas of the automation industry.



SIMOCODE pro – General Performance: Ideal for the entry level

The smart and compact motor management system for direct-on-line, reversing, and star-delta (wye-delta) starters or for controlling a motor starter protector or soft starter. The basic system includes a current measuring module and the basic unit for overload or thermistor motor protection, for example. Communication with the automation level takes place via PROFIBUS/PROFINET. Optional additions include an operator panel and an expansion module that allows additional inputs/outputs, ground-fault detection and temperature measurement to be realized.

SIMOCODE pro – High Performance: The fully professional solution for every motor


The SIMOCODE pro High Performance motor management system is variable, intelligent and can be adapted individually to suit any requirement. The basic system includes a module for measuring current (and optionally also voltage), as well as a basic unit, and is suitable for removing pump blockages, for example. Communication with the automation level takes place via PROFIBUS or Modbus RTU, via Ethernet with the PROFINET or EtherNet/IP protocols, and also via OPC UA. The optional expansion modules include separate current/voltage measuring modules for dry-running protection, an operator panel with display, a ground-fault module, a temperature module, standard digital modules, fail-safe digital modules and an analog module.

SIMOCODE pro Safety: Fail-safe expansion modules

Various modules are available for SIMOCODE pro for the extended protection of personnel, machines and the environment. These guarantee the safety-related shutdown of motors and meet all the requirements of the standards.

The advantages:

- Functional switching and fail-safe shutdown without manual wiring or additional effort
- Safety function parameters can be flexibly configured
- Transfer of meaningful diagnostic data to the control system
- Logging of errors for detailed evaluation
- Fail-safe shutdown via PROFIsafe or locally



	PROFINET IO/OPC UA	ETHERNET/IP	PROFIBUS	MODBUS RTU	
High Performance	SIMOCODE pro V PN	SIMOCODE pro V EIP	SIMOCODE pro V PB	SIMOCODE pro V MR	Current/voltage measuring module
					Operator panel with display
					max. 5/7 expansion modules
					Safety
General Performance	SIMOCODE pro V PN GP		SIMOCODE pro S		Extended control functions (e.g. positioner, pole-changing starter)
					Current measuring module
					Operator panel
					1 expansion module
					Basic control functions (e.g. direct-on-line/reversing start)

Remove pump blockages and increase availability.


Say goodbye to blocked pumps with SIMOCODE pro – the modular, compact motor management system that tackles the challenge by automatically reversing the pump. SIMOCODE pro can be retrofitted in existing plants.

Every water utility operator is familiar with the problems of a blocked pump – and the possible consequences: environmental harm, damage due to flooding, and dangers to health as a result of lifting and cleaning pumps. This is compounded by the financial impact of plant downtimes. SIMOCODE pro monitors the current and active power of the pump motor – and derives the pump

status from them. If a defined threshold value is exceeded, SIMOCODE pro autonomously reverses the rotational direction of the pump in order to dislodge deposits on the impeller blades.


SIMOCODE pro – the advantages at a glance

- Minimized downtimes with less maintenance work
- Energy and cost savings over the entire plant life cycle
- Simple use
- Scalable solution
- A choice of networked or autonomous configuration




Reliable monitoring – dry-running protection redesigned.

Reliable dry-running protection is a must in many applications in the chemical industry. SIMOCODE pro reliably prevents the dry running of centrifugal pumps in order to preclude hazardous situations and completely redefines dry-running protection for pumps in hazardous areas with an innovative solution.



Conventional dry-running monitoring with a sensor



Active power-based dry-running protection

Sensors on centrifugal pumps in hazardous areas are often prone to high installation and maintenance costs. The solution: Using active power-based dry-running detection, SIMOCODE pro monitors the active electrical power consumption of the pump motor and thus the status of the pump – without the need for additional monitoring devices or sensors to be installed. The new technology ensures reliable explosion protection in accordance with ATEX and IECEx criteria and saves costs and time for commissioning and maintenance.

Your benefits through active power-based dry-running protection

Earlier fault detection

- Direct conclusions concerning the flow rate can be drawn from the active power consumption of the pump motor
- Reliable prevention of dry running of the pump and therefore less damage to the pump

Cost and time savings

- No maintenance effort due to the elimination of mechanical wear of the sensors
- No additional sensor required

Reduction of hardware

- No need for additional sensors and mechanical components
- Simplified engineering

Reliable monitoring of the system

- Compliance with ATEX and IECEx criteria
- Reliable and automatic pump shutdown in the event of unacceptable operating conditions

SIMOCODE pro speaks to everyone – including the Cloud.

With the OPC UA industrial M2M communication protocol, SIMOCODE pro provides an additional communication interface that is independent of the automation system.

Digitalization for more economical operation: SIMOCODE pro with OPC UA

The open and supplier-independent communication via OPC UA guarantees the direct exchange of data with HMI panels or SCADA systems. Motor, process and plant data is therefore available without any losses, wherever it is needed: at the device, but also in the control room for diagnostic purposes. As part of the digital revolution and the efforts to evaluate vast quantities of data even more quickly, all motor data from SIMOCODE pro can be transmitted by the most direct route to the Cloud using OPC UA.

The data can then be used more intensively and in a targeted fashion – without the need for any intervention in the motor control.

The result: Plant availability and efficiency are increased, because you can run analyses, improve energy consumption, or even optimize the entire process.



Benefits

Thanks to OPC UA, SIMOCODE facilitates simple and convenient integration into Cloud-based solutions, e.g. Siemens MindSphere with so many advantages:

- Data provision in the Cloud for cross-plant, reliable diagnostics
- Convenient and reliable process optimization
- Plant-wide access to control data, process values and readings without complex engineering effort
- Predictive maintenance, energy data management and resource optimization
- Effective protection against manipulation (security)




SIMOCODE ES Software:
For diagnostics and simple configuration, including in the TIA Portal

SIMOCODE ES provides you with the software for the configuration, startup, operation and diagnosis of SIMOCODE pro. The software is based on the central Totally Integrated Automation Portal (TIA Portal) engineering framework, providing an integrated, efficient and intuitive solution for all automation tasks. SIMOCODE ES offers you a host of advantages, including convenient configuration in the device view, graphical commissioning using drag and drop functions, online access to signal states and clear measurement curves for diagnostic purposes.

The convenient way to optimum process guidance: The integration of SIMOCODE pro into SIMATIC PCS 7

Using standardized blocks and faceplates, SIMOCODE pro can very easily be integrated into the SIMATIC PCS 7 process control system. This makes it extremely easy to integrate service and diagnostic data from the motor management system into higher-level process control systems, for example.

The result: A high level of transparency throughout the plant, enabling faults to be detected at an early stage or prevented from occurring altogether. In general, the greater density of information in the control system enables you to achieve not only greater transparency, but also higher process quality.




Benefits

SIMOCODE pro is your reliable data supplier for maximum process quality. The motor management system offers:

- Transparency into your process
- Data analysis and simulation
- Secure data storage and transmission
- Visualization and recommendation(s)
- Increased availability of components
- Optimization of energy consumption
- Maximization of process efficiency

SIMOCODE pro system overview – general performance



Basic units	
SIMOCODE pro S	
<ul style="list-style-type: none"> • 24 V DC • 110 ... 240 V AC/DC 	3UF7020-1AB01-0 3UF7020-1AU01-0
SIMOCODE pro V PN GP	
<ul style="list-style-type: none"> • 24 V DC, 2 ports • 110 ... 240 V AC/DC, 2 ports • 24 V DC, 1 port • 110 ... 240 V AC/DC, 1 port 	3UF7011-1AB00-1 3UF7011-1AU00-1 3UF7011-1AB00-2 3UF7011-1AU00-2

Expansion modules	
SIMOCODE pro S multifunction modules	
Monostable relay outputs, input voltage	
<ul style="list-style-type: none"> • 24 V DC • 110 ... 240 V AC/DC 	3UF7600-1AB01-0 3UF7600-1AU01-0


Connection cables
 3UF793x-0AA00-0 connection cables available in various versions from 0.025 m – 0.5 m

Current measuring modules			
Straight-through transformers	0.3 ... 3 A	45 mm	3UF7100-1AA00-0
	2.4 ... 25 A	45 mm	3UF7101-1AA00-0
Busbar connections	10 ... 100 A	55 mm	3UF7102-1AA00-0
	20 ... 200 A	120 mm	3UF7103-1AA00-0
Busbar connections	20 ... 200 A	120 mm	3UF7103-1BA00-0
	63 ... 630 A	145 mm	3UF7104-1BA00-0

Expansion modules		
Digital modules		
Relay outputs	Input voltage	
<ul style="list-style-type: none"> • Monostable 	24 V DC	3UF7300-1AB00-0 3UF7300-1AU00-0
	110 ... 240 V AC/DC	
Ground-fault module		3UF7510-1AA00-0
Temperature module		3UF7700-1AA00-0

Operator panel	
<ul style="list-style-type: none"> • Titanium gray 	3UF7200-1AA01-0

SIMOCODE pro system overview – high performance



Basic units			
SIMOCODE pro V PROFIBUS			
• 24 V DC			3UF7010-1AB00-0
• 110 ... 240 V AC/DC			3UF7010-1AU00-0
SIMOCODE pro V PROFINET			
• 24 V DC			3UF7011-1AB00-0
• 110 ... 240 V AC/DC			3UF7011-1AU00-0
SIMOCODE pro V Modbus RTU			
• 24 V DC			3UF7012-1AB00-0
• 110 ... 240 V AC/DC			3UF7012-1AU00-0
SIMOCODE pro V EtherNet/IP			
• 24 V DC			3UF7013-1AB00-0
• 110 ... 240 V AC/DC			3UF7013-1AU00-0
Current/voltage measuring modules			
Straight-through transformers	0.3 ... 4 A	45 mm	3UF71□0-1AA01-0
	3 ... 40 A	45 mm	3UF71□1-1AA01-0
	10 ... 115 A	55 mm	3UF71□2-1AA01-0
Busbar connection	20 ... 200 A	120 mm	3UF71□3-1BA01-0
	63 ... 630 A	145 mm	3UF71□4-1BA01-0

1 Standard version 2 Dry-running protection

Expansion modules		
Digital modules		
Relay outputs	Input voltage	
• Bistable	24 V DC 110 ... 240 V AC/DC	3UF7310-1AB00-0 3UF7310-1AU00-0
Analog module		3UF7400-1AA00-0

Fail-safe expansion modules	
DM-F Local fail-safe digital module Rated control supply voltage	
• 24 V DC	3UF7320-1AB00-0
• 110 ... 240 V AC/DC	3UF7320-1AU00-0
DM-F PROFIsafe fail-safe digital module ¹⁾ Rated control supply voltage	
• 24 V DC	3UF7330-1AB00-0
• 110 ... 240 V AC/DC	3UF7330-1AU00-0
¹⁾ Possible with SIMOCODE pro V PROFIBUS / PROFINET basic unit	

Operator panels with display	
Languages: English / German / French / Spanish / Portuguese / Italian / Polish / Finnish	3UF7210-1AA01-0
Languages: English / Chinese / Russian / Korean	3UF7210-1BA01-0

Software

SIMOCODE ES (TIA Portal) V15 Basic	
Basic functional scope including Premium Trial License	3ZS1322-6CE13-0YG8
SIMOCODE ES (TIA Portal) V15 Standard	
Floating license for one user	
• License key on USB flash drive, Class A	3ZS1322-5CC13-0YA5
• License key and software download, Class A	3ZS1322-5CE13-0YB5
Upgrade for SIMOCODE ES 2007 Standard	3ZS1322-5CC13-0YE5
Software Update Service	3ZS1322-5CC00-0YL5
SIMOCODE ES (TIA Portal) V15 Premium	
Floating license for one user	
• License key on USB flash drive, Class A	3ZS1322-6CC13-0YA5
• License key and software download, Class A	3ZS1322-6CE13-0YB5
Upgrade for SIMOCODE ES 2007 Premium	3ZS1322-6CC13-0YE5
Software Update Service	3ZS1322-6CC00-0YL5

SIMOCODE pro block library for SIMATIC PCS 7 Version V9 with Advanced Process Library (APL)	
Engineering software V9	3ZS1632-1XX03-0YA0
Runtime license V9	3ZS1632-2XX03-0YB0
Upgrade for PCS 7 block library SIMOCODE pro V8	3ZS1632-1XX03-0YE0
SIMOCODE pro block library for SIMATIC PCS 7 Version V8 with Advanced Process Library (APL)	
Engineering software V8	3ZS1632-1XX02-0YA0
Runtime license V8	3ZS1632-2XX02-0YB0
SIMOCODE pro block library for SIMATIC PCS 7 Version V7 without Advanced Process Library (APL)	
Engineering software V7	3UF7982-0AA10-0
Runtime license V7	3UF7982-0AA11-0
Engineering software for V7–V9 migration	3UF7982-0AA20-0

Siemens Industry, Inc.

5300 Triangle Parkway
Norcross, GA 30092

1-866-663-7324
info.us@siemens.com

Subject to change without prior notice
All rights reserved

Order No.: CPBR-SMPR-0219
Article No. DFCP-B10220-00-7600
Printed in USA

© 2019 Siemens Industry, Inc.

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.