

The background of the advertisement features a modern industrial setting with two men in the center. One man, wearing a light blue button-down shirt and jeans, holds a tablet. The other man, in a grey polo shirt, holds a small white electronic component. To their left, a large, complex low-voltage switchboard is shown in a semi-transparent, glowing blue wireframe style. The switchboard has multiple levels of components, including circuit breakers and busbars. In the upper right corner, there is a vertical stack of five yellow icons: a line graph with an upward arrow, a stack of coins, a speedometer, crossed wrench and screwdriver, and a hard hat. The overall scene is overlaid with a blue hexagonal grid pattern and glowing lines, suggesting a digital or smart factory environment.

SIEMENS

Ingenuity for life

The plus for your business:
Intelligent. Flexible. Safe.

Low-voltage switchboard SIVACON S8^{plus}

[siemens.com/sivacon-S8plus](https://www.siemens.com/sivacon-S8plus)

Contents

SIVACON S8^{plus} at a glance

Intelligent infrastructure for your success	3
Many applications – one single power distribution	4
The plus for real added value	5
Innovative by tradition	8

Safety and digitalization

Safety without any ifs or buts	12
Tested under worst-case conditions	14
SIMARIS control – the digital intelligence for your SIVACON S8 ^{plus}	18
SIVACON S8 ^{plus} in practice	22

Technology

Frame, enclosure, and busbars	24
Circuit-breaker design	26
Universal mounting design	28
Frequency converter design	32
In-line design, plug-in	34
In-line design, fixed-mounted	35
Fixed-mounted design with front covers	36
Reactive power compensation	37

Service

Competent support for your switchboard	38
--	----

Technical data & project checklist

Technical data	40
Project checklist – Part 1	42
Project checklist – Part 2	43

SIVACON S8^{plus} – intelligent infrastructure for your success

Benefit from the options of SIVACON S8^{plus} – supported by the know-how of Siemens experts

Work successfully – with SIMARIS control, the digital twin of the switchboard

- Easy local operation and diagnostics
- Flexible adaptation to changes in operation
- Support for predictive maintenance via Health Index
- High power flow transparency and energy efficiency to optimize your energy costs
- Seamless integration in energy management and automation solutions or cloud-based analysis systems (IoT)

Optimum safety for personnel and switchboard


- Design verification according to IEC 61439-2
- Arc fault test according to IEC/TR 61641
- Extended, active, and resettable arc fault protection
- Targeted monitoring via built-in sensors (e.g. temperature sensors)
- Consistently design verified connection to SIVACON 8PS busbar trunking systems

High level of flexibility for new possibilities – today und tomorrow

- Easily adaptable or expandable thanks to the innovative modular design
- Space-saving, compact withdrawable design
- Powerful motor management systems for flexible adaptations to new tasks



Many applications – one single power distribution: SIVACON S8^{plus}



*Reliable and future-oriented
power distribution for industries
and infrastructure*

+ SIVACON S8^{plus} – the plus for real added value

Power distribution matters

Whether complex tasks with special requirements in the process industry, in data centers, or in critical infrastructure facilities – with SIVACON S8^{plus} you will master the power supply for these applications. With this safe, flexible, and intelligent electrical power distribution system you can not only distribute power, but also manage the efficiency and reliability of your processes.

Your success starts in our production facility!

The SIVACON S8^{plus} quality is based on long years of experience in the engineering and manufacture of switchboards at our Center of Competence in Leipzig, Germany. Beyond just offering a high-quality product, it also includes all services and functions which are planned and developed for each SIVACON S8^{plus} switchboard individually.

Siemens SIVACON S8^{plus} production facilities, strategically distributed worldwide, complement the Center of Competence in Leipzig and support the high SIVACON S8^{plus} quality with uniform CAD systems, software tools, and production standards.

The result: sustainably constructed switchboards with an optimized use of materials and durable components.

Your advantages

- Engineered in Germany: developed, planned, and produced according to your specific requirements
- Support by qualified experts in all project phases
- Research and development teams as well as local experts work hand in hand
- High system quality thanks to a proven and consistent process chain



Digital from the very beginning

Digitalization already starts in the planning process of your power distribution. **SIMARIS Suite** is the platform for your uniform access to all SIMARIS planning tools:

- **SIMARIS design** for network calculation and dimensioning
- **SIMARIS curves** for visualizing characteristic tripping curves, let-through current curves, and let-through energy curves
- **SIMARIS project** for determining the space requirements of the distribution system, and for creating tender specifications and **BIM** files (Building Information Modeling). BIM data support the monitoring of the interaction of all installations in complex infrastructure.



Your advantages

- Efficient planning
- Safe dimensioning – from the medium-voltage level down to the consumer
- Easy and fast determination of space requirements
- Clearly designed planning documentation

Tested safety for every application


SIVACON S8^{plus} is design verified according to IEC 61439-2, including the connection of the SIVACON 8PS busbar trunking systems. You thus get to create a coordinated and safe power distribution for your production or infrastructure. It has proven physical properties under operating and fault conditions.

With the modular arc fault protection system tested according to IEC/TR 61641, you go one step further for a higher level of personnel and switchboard safety, and for more availability. SIVACON S8^{plus} can also be used in demanding applications, like on ships and in regions at risk from earthquakes.



Your advantages

- Personnel and switchboard safety tested under conditions of internal arcing according to IEC/TR 61641
- Optional, active, and resettable arc fault protection system
- Seismic upgrade and certification for ships and offshore platforms
- Consistently design verified connection to SIVACON 8PS busbar trunking systems





Digital intelligence for operation

Make use of all system advantages for efficient commissioning and cost-efficient operation – no matter whether as a Motor Control Center (MCC) or a mere power distribution board. With SIMARIS control, SIVACON S8^{plus} offers you an entirely new perspective. SIMARIS control simplifies the commissioning of the switchboard as well as the parameterization of the installed devices. It offers more transparency regarding power flows as well as switchboard and device conditions, and enables quicker fault diagnostics and predictive maintenance. Furthermore, SIMARIS control supports flexible operation, offering interfaces for the integration in other systems such as overall automation systems as well as cloud-based analysis systems.

Flexibility, today and tomorrow

Flexibility starts with planning, and extends through efficient operation up to service. SIVACON S8^{plus} adapts to your requirements. Different mounting designs can easily be combined in one cubicle. Thanks to flexible modules – the space-saving, small withdrawable units, among others –, functional units can be easily replaced or extended. Powerful motor management systems complement the offer for the flexible adaptation to special tasks.

Your advantages



- High level of flexibility for new tasks
- Predictive maintenance thanks to Health Index
- Easy system overview and diagnostics – on site, in higher-level automation or energy management systems, as well as in the cloud
- Optimized power flows; higher switchboard availability and efficiency on the basis of sound data across the entire lifecycle

Your advantages



- Customized switchboard thanks to the modular system of different mounting designs
- Easy adaptation of operation thanks to exchangeable functional units
- Continuous technical further development

SIVACON S8^{plus} – innovative by tradition

- + Design verification by means of tests according to IEC 61439-2, arc resistance by means of tests according to IEC 61641, earthquake upgrade, certification for application on ships and offshore platforms according to DNV GL, LR, and ABS
- + Consistently design verified connection to SIVACON 8PS busbar trunking systems
- + Active arc fault protection system with reusability
- + Two standard heights and two base heights permit a perfect adaptation to structural conditions
- + Innovative locking system with multiple designs allows to change the door hinge at any time
- + Installation of two independent main busbar runs possible in one switchboard (up to 4,000 A)
- + Variable busbar positions (top, rear) with rated current up to 7,010 A
- + Modular and compact frequency converter cubicle, tested according to IEC 61439
- + SIMARIS control – diagnostics station: visualizing, monitoring, parameterization, and connection to overall systems
- + Combination of different mounting designs (fixed-mounted feeders, plug-in design, withdrawable design)
- + Easy exchange or addition of functional units
- + High packing density with up to 48 feeders in withdrawable design in one outgoing feeder cubicle
- + Arc-resistant distribution busbar embedding
- + Shutter with double-action for normal and small withdrawable units
- + Patented low-wear withdrawable unit contact system for long service life
- + Normal withdrawable units up to 630 A and small withdrawable units up to 63 A
- + Mechanical coding of withdrawable units and compartments with up to 9,216 options
- + Operating-error-proof and uniform operating concept throughout all sizes of withdrawable units
- + Lockable disconnected position for safe commissioning and maintenance



Circuit-breaker design

Arc fault protection design

Universal mounting design

Frequency converter design

In-line design, plug-in



New ideas, new concepts

- Decades of experience in engineering and construction for modern system architecture
- High level of flexibility and versatile innovation
- Quickly available new solutions for new tasks

Tested safety

- Design verification by means of test according to IEC 61439-2
- Test under conditions of internal arcing according to IEC/TR 61641
- Test evidence of behavior during earthquakes
- Certification for ships and offshore applications

Increasing performance systematically

- Digitize now with SIMARIS control, and operate efficiently
- An overall system with perfect interaction of all used devices for maximum system performance
- Sustainable, cost-efficient design, lower power demand, improved CO₂ footprint



*In-line design,
fixed-mounted*

*Fixed-mounted
design*

*Reactive power
compensation*

Innovation straight from our Siemens production facilities

The special functionalities of SIVACON S8^{plus} support you in making the operation of your switchboard even more reliable and future-proof.

Active arc fault protection for extended safety

The active arc fault protection system developed for SIVACON S8^{plus} complements the proven conventional protection measures. Detecting and extinguishing an arc fault within a few milliseconds extends the protection of personnel and switchboard. Continuous self-monitoring, testability, and up to two arc quenching operations without component exchange make the difference.

Space-saving small withdrawable units

Small withdrawable units from 150 x 150 mm allow for a high packing density in your SIVACON S8^{plus}.

SIMARIS control – use energy data in a smart way

SIMARIS control increases the flexibility and transparency of your switchboard. For new requirements and commissioning, simply parameterize your devices through SIMARIS control. Perform you maintenance predictively with the Health Index function. Collect the data of all communication-capable devices of the switchboard and analyze it – on site, in higher-level energy management and automation solutions, or in the cloud.

Intelligent sensor technology – high switchboard availability


The continuous temperature monitoring of all on-site made busbar interconnections and cable connections monitors and alerts before a failure can create damages.

Frequency converter design – fit for the digital age

SINAMICS frequency converters of the G120 series with Modbus, PROFIBUS, or PROFINET communication form the centerpiece of the standardized modules with design verification according to IEC 61439. This way, continuously operating or highly dynamic pumps, fans, and compressors can be supplied even more cost-efficiently and safely.

Higher performance thanks to highly efficient cooling technology

For switchboard cubicles in circuit-breaker design and universal mounting design, we have developed an energy-efficient cooling with forced ventilation which reduces the derating. Speed-controlled fans and a redundant design ensure a low temperature profile in every cubicle – for more performance and longer service life of the components.



	1	2	3	4	5	6	7	8
	Circuit-breaker design	Arc fault protection design	Universal mounting design	Frequency converter design	In-line design, plug-in	In-line design, fixed-mounted	Fixed-mounted design	Reactive power compensation
Mounting design	Fixed-mounted design, withdrawable design	Fixed-mounted design	Withdrawable design, fixed-mounted design with compartment doors, plug-in design	Fixed-mounted design	Plug-in design	Fixed-mounted design	Fixed-mounted design with front covers	Fixed-mounted design
Functions	Incoming feeder, outgoing feeder, bus coupler	Extended arc fault protection	Cable feeders, motor feeders (MCC)	Regulation of pumps, fans, compressors	Cable feeders	Cable feeders	Cable feeders	Central reactive power compensation
Rated values	up to 6,300 A	Short-circuit withstand strength up to 100 kA at 690 V	up to 630 A up to 250 kW	up to 132 kW	up to 630 A	up to 630 A	up to 630 A	up to 500 kvar choked/unchoked
Type of connection	front or rear	–	front or rear	front	front	front	front	front
Cubicle width (mm)	400, 600, 800, 1,000, 1,400	400	600, 1,000, 1,200	600, 800, 1,000	1,000, 1,200	600, 800, 1,000	1,000, 1,200	800
Internal separation	Form 1, 2b, 3a, 4b, 4 type 7 (BS)	4b	Form 2b, 3b, 4a, 4b, 4 type 6, 4 type 7 (BS)	Form 1, 2b	Form 3b, 4b	Form 1, 2b	Form 1, 2a, 4a, 4b	Form 1, 2b
Busbar position	top, rear	top, rear	top, rear	without, top, rear	top, rear	rear	top, rear	without, top, rear

SIVACON S8^{plus} – safety without any ifs or buts

*SIVACON S8^{plus} – integral safety
for personnel and switchboard*

Safety as an integral part

For us, there are no compromises in questions of safety, only clear regulations. Our low-voltage switchboards are developed, manufactured, and tested according to the stipulations of IEC 61439-2 for power switchgear and controlgear assemblies. Quality is not a luxury here, but the precondition for the cost-efficient operation of your switchboard and a high level of reliability of your production or infrastructure.

Your advantages

- Safety for personnel and switchboard by means of tests according to IEC 61439-2
- High level of process safety thanks to SIVACON S8^{plus} quality and integrated system approach
- Consideration of national regulations
- Safe power supply in earthquake-tested version for higher seismic requirements
- Certifications for application on ships and offshore platforms



The SIVACON S8^{plus} quality ensures your success

IEC 61439-2 requires two main pieces of evidence that the switchboard is fit for purpose: design verifications and routine verifications. Siemens provides the design verifications during the basic development of SIVACON S8^{plus} by means of tests accompanying the development process. The routine verifications are performed on every manufactured low-voltage switchboard prior to delivery. These two verifications together are a decisive part of quality assurance, and a prerequisite for CE marking according to the EU directives and laws. They are evidence for the high level of safety SIVACON S8^{plus} provides for personnel and switchboard.

With SIVACON S8^{plus}, you are not only investing in standard-compliant technology, but also in technology that is especially reliable. Whether you intend to use your SIVACON S8^{plus} for applications in the chemical industry, for a data center, or for a critical infrastructure – it offers you specific advantages in any case.

Required verifications to be performed according to IEC 61439-1/2 standard

	Verification by means of test	Verification by means of calculation	Verification by means of design rules
1. Strength of materials and parts	■	–	–
2. Degree of protection of enclosures	■	–	■
3. Clearances and creepage distances	■	■	■
4. Protection against electric shock and consistency of protective conductor circuits	■	■ ¹⁾	■ ¹⁾
5. Installation of operational equipment	–	–	■
6. Internal electrical circuits and connections	–	–	■
7. Connections for conductors inserted from outside	–	–	■
8. Insulation properties	■	–	■ ²⁾
9. Temperature-rise limits	■	up to 1,600 A	up to 630 A ³⁾
10. Short-circuit withstand strength	■	conditionally ³⁾	conditionally ³⁾
11. Electromagnetic compatibility (EMC)	■	–	■
12. Mechanical function	■	–	–

1) Effectiveness of the switchgear and controlgear assembly in case of external faults

2) Only impulse strength 3) Comparison with an already tested design

Seismic upgrade with tested safety

For application in seismically critical locations, we deliver SIVACON S8^{plus} switchboards in vibration-resistant, earthquake-tested versions. The test results are summarized and disclosed in three categories:

- Operability of the switchboard during the earthquake
- Operability of the switchboard after the earthquake
- Stability

Certification for ships and offshore platforms

The application on the high seas also poses a special challenge for switchboards. Among these challenges are, above all, the saline atmosphere with high air humidity (risk of corrosion) and the higher vibration load of the switchboard due to the swell or ship propulsion. SIVACON S8^{plus} switchboards are perfectly set to meet these challenges. For application on ships and offshore platforms, SIVACON S8^{plus} was given the necessary certifications from renowned classification societies (DNV GL, LR, ABS) under hand and seal.

Tested under worst-case conditions

Arc fault protection with SIVACON S8^{plus}

Even though arc faults rarely occur in design verified low-voltage switchboards, their effects are still grave, as they can cause severe personal injuries and equipment damages, and produce high downtime costs.

Caused, for example, by foreign objects, pollution, animals, or incorrect operations, an arc fault releases a high amount of energy with extreme heat development and a pressure wave within a short period of time.

To minimize these risks, SIVACON S8^{plus} provides a comprehensive, modular arc fault protection concept. The following principles apply to all measures defined for the protection of personnel and switchboard:

- Preventing arc faults
- Keeping the effects of residual risks from an arc fault as low as possible

Basic arc fault protection

Low-voltage switchboards SIVACON S8^{plus} already offer a high level of protection against arc faults thanks to the switchboard design. The design verification by means of tests, the high-quality system components, the device and switchboard dimensioning using the engineering tools from the SIMARIS family, and the uniform operation with integrated operating error protection all serve to avoid arc faults.



Proven conventional protection measures mitigate the effects of arc faults. They include arc-resistant hinge and locking systems, pressure-relieving roof plates, protection measures on the ventilation openings at the front, and arc barriers.

They are further expanded by designing the busbar systems or cable connections as an arc ignition protected zone.

Verification of functionality in the event of an arc fault

The test under conditions of arcing due to an internal fault is done according to IEC/TR 61641. For the evaluation of test results, criteria are applied which are summarized in arcing classes.

Your advantages

- Modular arc fault protection concept for every customer requirement
- Personnel safety by testing the switchboard under conditions of arcing
- Switchboard safety by mitigating the effects of the arc fault within the switchboard
- Higher personnel and switchboard safety thanks to extended arc fault protection
 - Design of the busbar systems or cable connections as an arc ignition protected zone
 - Active arc fault protection system

Characteristics under conditions of arcing


Criteria	Arcing class A Personnel protection	Arcing class B Personnel and switchboard protection	Arcing class C Personnel and switchboard protection
1 Doors and covers do not open	A	B	C
2 No parts of the switchgear and controlgear assembly are ejected			
3 No holes as a result of an arc fault burning through the external parts of the enclosure declared to be freely accessible			
4 The indicators do not ignite. Limited access for authorized personnel in work clothes (cretonne 150 g/m ²) The indicators do not ignite; unlimited access for untrained or unskilled persons in light summer clothes (batiste 40 g/m ²)			
5 The protective conductor circuit for accessible parts of the enclosure is still effective			
6 The arc fault is limited to the defined area of the switchgear and controlgear assembly			
7 Emergency operation of the remaining switchgear and controlgear assembly is possible after the fault has been cleared and/or affected functional units have been disconnected or removed			

Active protection at a high level

The active arc fault protection system specifically developed for SIVACON S8^{plus} reduces the energy converted during an arc fault, and thus additionally mitigates the effects on the low-voltage switchgear and controlgear assemblies.

The integration and testing of the active arc fault protection system of SIVACON S8^{plus} is done according to IEC/TS 63107 with the following objectives:

- Correct functioning of all components of the active arc fault protection system within the low-voltage switchgear and controlgear assembly
- Prevention of false tripping, e.g. by switching arcs from open circuit breakers
- Test of the lower and maximum tripping threshold (smallest and maximum residual current)
- Behavior of the system immediately after switching on



Mode of operation of an active protection system

Current transformer



How active arc fault protection works

An arc fault causes a flash of light which is detected by an optical sensor. At the same time, the current transformers register a quick current increase. Both events are reported to an internal arc fault control device (IACD) and, if they occur simultaneously, they are recognized as an arc fault. The energy converted in an internal arc fault is reduced by tripping the arc quenching device (AQD) and the incoming circuit breaker. By tripping the AQD, a low-impedance current path is established. The residual current/short-circuit current flows along this path and withdraws energy from the arc. This current path is maintained until the incoming circuit breaker interrupts the short-circuit current.

Technical data

- Integrated in SIVACON S8^{plus} and tested up to 690 V/100 kA
- No pyrotechnical operating mechanism of the arc quenching device
- Continuous self-monitoring of all system components
- Testability for detecting devices and the arc quenching device – up to 100 test cycles
- Two arc quenching operations without exchange of the quenching device (resettable)

SIVACON S8^{plus} – modular arc fault protection concept

Arcing class A with limitation to the area of the switchgear and controlgear assembly

Personnel protection; the arc fault is confined to the area within the switchgear and controlgear assembly.

Arcing class C with limitation to the area of the cubicle

Personnel and switchboard protection; the arc fault is confined to a defined area within the switchgear and controlgear assembly. Limited operation is possible after the arc fault.

Arcing class C with limitation to the area of the compartment

Personnel and switchboard protection; the arc fault is confined to a defined area within the switchgear and controlgear assembly. Limited operation is possible after the arc fault.

Extended arc fault protection by means of insulation

Design of the busbar systems or cable connections as an arc ignition protected zone

Extended arc fault protection by means of an active arc fault protection system (resettable)

With optical sensors, current transformers, and evaluation units. Reducing the energy converted in an internal arc fault by:

- Shutdown of the incoming circuit breaker, or
- Shutdown by means of an arc quenching device and the incoming circuit breaker


SIMARIS control – the digital intelligence for your SIVACON S8^{plus}

Manage your energy data – with SIMARIS control

Accelerate and simplify your operational diagnostics – on the basis of your energy data. Define your threshold values for early signaling – for monitoring, control, and diagnostics – and transparency down to each individual feeder. Use the data on switching rates and runtimes or temperatures to increase the switchboard availability through predictive maintenance and optimized energy management – and to reduce your costs as well as the power demand of your application. The software application SIMARIS control creates one integrated system from many individual devices, and supports you with five basic functions.

Your advantages

- Simplified diagnostics: All tools on board!
- More overview: Operational and diagnostic data perfectly visualized!
- Higher switchboard availability: Continuous monitoring and diagnostic information for predictive maintenance!
- Higher efficiency: Perfect energy transparency!
- Optimal connectivity: To higher-level automation and energy management systems, and to the cloud!



Consistent acquisition of device status, measured values, and sensor data

Temperature sensors, communication-capable measuring and switching devices, such as the measuring devices SENTRON 7KT/7KM PAC, the circuit breakers 3WA/3VA, or the intelligent motor management system SIMOCODE pro, as well as the frequency converters provide comprehensive diagnostic, status, measurement, statistical, and service data. They form the basis on which the intelligent switchboard can show its advantages. After all, it is only with actual operational data that savings potentials can be detected and predictive maintenance can be planned in a targeted manner.



Record data – make the most of communication-capable devices

SIMARIS control – the digital twin of your switchboard

Acquiring switchboard data is one thing; visualizing it, another. SIMARIS control implements this in a way that is structured, clear, and oriented towards your information requirements. At a central location, you can see all that you need to know about the condition of the switchboard, sensor data, measured values, and power demand in your system – intuitively operable via touch control. Always on board: different bus systems, a standardized data model for the Motor Control Center, and a central message list for the latest diagnostics information of the entire switchboard, all in one system.




Visualize data – get a quick and sound overview

Continuous data analysis – the foundation for your decisions

Receive your operational diagnostics locally or via remote access more quickly, more flexibly, more easily – and above all independently of the higher automation level. The Health Index function indicates the status of your switchboard and individual feeders on the basis of the operational data up to now. This way, you can act with foresight! Your personnel can easily and quickly perform important diagnostics and analyses on their own, and initiate required measures in a timely and targeted manner in order to support a reliable operation.



Analyze data – easily recognize correlations



Generating a competitive advantage from data – efficient switchboard management

Optimize your switchboard management with sound data and analyses from SIMARIS control. Change your operational parameters without additional parameterization software, and modify your feeder designations and comment information – according to the user authorizations. Make changes to the digital twin regarding runtime in order to adapt your switchboard easily and quickly to new operational requirements. The achievement: a high level of flexibility and, thanks to the Health Index, always sound information on the condition of your switchboard and individual feeders.



Manage systems – experience your advantages live

For an ideal system overview – integration in overall systems

Integrate SIVACON S8^{plus} in existing IT structures, a comprehensive energy management system, or your overall predictive maintenance strategy – via the integrated LAN interface of the SIMARIS control hardware and the web interface (also for mobile devices). SENTRON powermanager connects your SIVACON S8^{plus} to overall energy management systems. Alternatively, you can use interfaces such as OPC UA or Modbus TCP to integrate your switchboards in overall systems and benefit from the advantages of cloud-based analysis systems (e.g. in MindSphere).



Transfer data – effectively use the potentials of information exchange

Technical features

- Reliable industrial PC system
- Independent of higher automation levels
- Uses the communication system of the switchboard
- Compatible with various communication systems and network topologies
- Interfaces for PROFIBUS, PROFINET, Modbus, OPC UA, Ethernet, and others
- Flexible and extendable
- Operation e.g. via web client or mobile devices
- Structured alarm and error display
- Integrated user group administration with differentiated authorizations
- Configuration changes possible during ongoing operation (number, positioning, designation, and description of feeders)



Planning maintenance



Parameterization of components



Switching feeders on and off




Data analysis in the cloud




Consistent communication across all levels



Efficient energy management




View – alarm signals



View – individual cubicle



View – entire switchboard



View – Health Index

SIMARIS control, the digital twin of your switchboard



View – single line SIMOCODE pro



View – SIMOCODE pro

SIVACON S8^{plus} in practice

The SIVACON S8^{plus} switchboard supports complex applications with high requirements regarding the safety and reliability as well as the cost-efficiency of the power supply. You can find typical applications in the process industry, but also in data centers and critical infrastructure facilities.

Industrial applications

Safe, reliable, and cost-efficient – even under demanding conditions: SIVACON S8^{plus} offers ideal preconditions for low-voltage power distribution in industrial applications.

Specific requirements

- Safety for personnel and switchboard
- Reliable power supply
- Minimized risk of downtime
- Customer-specific, flexible, and extendable design

Versatile solutions

Thanks to the universal mounting design (ideal for Motor Control Centers), the withdrawable design (for a high level of personnel and operational safety and/or flexibility), and the connection of communication-capable devices to the overall automation and energy management systems, SIVACON S8^{plus} is especially versatile.

Further advantages

- Clear visualization and control via SIMARIS control
- Integration in the world of TIA with the prevalent process control system PCS 7, and use of the motor management system SIMOCODE pro
- Seamless interaction with the protection devices of the SIPROTEC family frequently used in the oil and gas industry is another plus.



Benefit and added value

- Reliable operation thanks to safety for personnel and switchboard with design verification according to IEC 61439-2
- High level of protection of personnel and switchboard in the event of an arc fault
- Certification for offshore applications by renowned classification societies
- Operational reliability even under high seismic stress (optional: earthquake-tested version)
- Future-proof system thanks to the cost-efficient, flexible, and modularly extendable switchboard
- Cost-benefit optimization by integrating the power distribution into automation and energy management

Data centers/infrastructures

Consistent and intelligent for very high availability: Low-voltage power distribution with SIVACON S8^{plus} for data centers and critical infrastructures ensures a reliable and cost-efficient operation.

Specific requirements

- For IT infrastructures and hospitals: high level of supply reliability
- For exhibition and production halls: Flexibility
- High level of planning and project management expertise
- Financially strong partner for long-term projects

Custom solutions

SIVACON S8^{plus} meets every demand optimally – whether as an especially reliable, compact double-fronted version for data centers, or as a flexible version with in-line design for infrastructure applications. It fits into almost any building structure, economically and fast. If necessary, it can be adapted and expanded if the needs change frequently, for example, in exhibition halls or hospitals. In combination with the SIVACON 8PS busbar trunking systems, it forms one consistent and design verified power distribution. And: Siemens supports you comprehensively – across the entire service life of the infrastructure – with the appropriate technology and the required project management skills.

Benefit and added value

- Reliable operation thanks to safety for personnel and switchboard with design verification according to IEC 61439-2
- High level of protection of personnel and switchboard in the event of an arc fault
- Operational reliability even under high seismic stress (optional: earthquake-tested version)
- Cost-efficient, flexible, and extendable switchboard with space-saving design
- Cost-benefit optimization by integrating the power distribution into energy management systems
- Comprehensive support by Siemens experts



Frame, enclosure, and busbars

SIVACON S8^{plus} – a perfect combination of cost-efficient design and high quality

The objective is clear: a perfect equipment for all of your demands – versatile, safe, user-friendly, and easy to operate. The intelligent and flexible, modular design of SIVACON S8^{plus} is our answer to these requirements.

Enclosure


- 1** Roof plate
- 2** Rear wall
- 3** Design side wall
- 4** Frame
- 5** Base cover
- 6** Base
- 7** Base compartment cover, ventilated
- 8** Cubicle door, ventilated
- 9** Compartment door
- 10** Head compartment door

Busbars

- 11** Main busbar (L1 ... L3, N) – top
- 12** Main busbar (L1 ... L3, N) – rear-top
- 13** Main busbar (L1 ... L3, N) – rear-bottom
- 14** Main busbar (PE) – bottom
- 15** Distribution busbar (L1 ... L3, N) – device compartment
- 16** Distribution busbar (PE) – cable compartment
- 17** Distribution busbar (N) – cable compartment

Internal separation

- 18** Device compartment/ busbar compartment
- 19** Cubicle to cubicle
- 20** Compartment to compartment
- 21** Cross-wiring compartment



Your advantages

- Personnel safety thanks to patented door locking system
- Arrangement of the busbar positions suitable for the application
- High level of flexibility thanks to variable busbar systems
- Robust version with high surface quality

Function with safety

The doors of SIVACON S8^{plus} are available with either simple or central locking (door locks or rotary handle locks are possible). The patented door locking system with universal door hinge allows for the hinge side to be changed with ease. Additional safety is provided by the pressure relief for the roof plates. The cubicles consist of separate functional compartments.

Systematic flexibility

The well thought-out design of the switchboard allows it to be integrated perfectly into a modern room concept. The cubicles, either single- or double-fronted, can be installed with a common main busbar system (MBB system), or back-to-back with separate MBB systems.

If required, two busbar systems can also be integrated in one switchboard, thus providing a high level of flexibility. For a higher current demand in so-called Power Centers (4,000 A and more), a double busbar system installed at the rear or top is used.

Technical data

Frame

Door opening angle	125°, 180° with stand-alone installation
Frame height (without base)	2,000, 2,200 mm
Base height (optional)	100, 200 mm
Cubicle depth	500 mm, 600 mm, 800 mm for single front 1,000 mm, 1,200 mm for double front
Degree of protection acc. to IEC 60529	IP30, IP31, IP40, IP41, IP43, IP54
Material of the switchboard	Sendzimir-galvanized sheet steel
Side walls and covers	Powder-coated
Type of installation	Single- or double-fronted with a common main busbar system (MBB system); back-to-back with separate MBB system
Connection position of cable and busbar trunking system connection	from front, from rear, from top, from bottom

Main busbars

Rated currents	up to 7,010 A
Rated peak withstand current I_{pk}	up to 330 kA
Rated short-time withstand current I_{cw}	up to 150 kA
Horizontal busbar system	top, rear-top, and/or rear-bottom



Locking system for simple or central locking

Circuit-breaker design

Safe, efficient, and compact – wherever more current is needed

SIVACON S8^{plus} incoming feeder cubicles, outgoing feeder cubicles, and coupling cubicles of circuit-breaker design use 3WA air circuit breakers in withdrawable or fixed-mounted design for the power supply of consumers with high power ratings, or, alternatively, 3VA molded case circuit breakers. Since there are generally many consumer loads downstream from these cubicles, the personnel safety and operational reliability of these is of particular importance.

Technical data





One circuit breaker per cubicle (FCB1)

Two circuit breakers per cubicle (FCB2)

Three circuit breakers per cubicle (FCB3)

	One circuit breaker per cubicle (FCB1)	Two circuit breakers per cubicle (FCB2)	Three circuit breakers per cubicle (FCB3)
Mounting design	Fixed-mounted design, withdrawable design	Withdrawable design	Fixed-mounted design, withdrawable design
Functions	Incoming feeder, outgoing feeder, transverse or longitudinal coupler	Incoming feeder, outgoing feeder, longitudinal coupler, bypass	Incoming feeder, outgoing feeder
Circuit breaker/ rated current of the circuit breaker	3WA air circuit breakers (ACB), from 630 A to 6,300 A, 3- and 4-pole 3VA molded case circuit breakers (MCCB), from 630 to 1,000 A	3WA air circuit breakers (ACB), from 630 A to 2,500 A (3,200 A bypass), 3- and 4-pole size 2	3WA air circuit breakers (ACB), from 630 A to 1,600 A, 3- and 4-pole size 1
Type of connection	Cable/busbar connection at the front or rear	Cable/busbar connection at the front	Cable connection at the rear
Connection position	top or bottom, depending on the position of the cable or busbar connection compartment		
Cubicle width (mm)	400 up to $I_n = 2,000$ A 600 up to $I_n = 3,200$ A 1,000 up to $I_n = 6,300$ A	600, 800, 1,000	600
Internal separation	Form 1, 2b, 3a, 4b, 4 type 7 (BS)	Form 1, 3a, 3b	Form 1, 3a, 3b
Busbar position	top, rear-top rear-bottom	rear-top, rear-bottom	top





Safety with design verification

With its circuit-breaker design, SIVACON S8^{plus} meets the requirements of personnel safety and operational reliability in a compact and safe manner. Moving to the connected, test, or disconnected position with the 3WA air circuit breaker takes place with the door closed. Design verification by means of tests in accordance with IEC 61439-2 also ensures a high level of safety for all sizes.

Space-saving solutions

The design with 3WA air circuit breaker and a cubicle width of only 400 mm is perfectly suitable for current ratings up to 2,000 A and minimized space requirements. The circuit-breaker cubicle with a width of 600 mm offers enough space for up to three circuit breakers (with rear connection).

Flexibility for every size

In the cable or busbar connection compartment which can be positioned at the top or bottom, the circuit-breaker design offers optimal connection conditions for every size. There, cables or SIVACON 8PS busbar trunking systems can be connected through a design verified connection, while the switching devices for control and monitoring can be kept in the auxiliary device compartment.

Energy-efficient cooling at any time



SIVACON S8^{plus} optionally offers a patented forced ventilation technology for cubicles in circuit-breaker design. It cools reliably, reduces the derating, and thus allows for a safe operation and a long service life. The fans are designed redundantly and – for a long service life – speed monitored.

Your advantages

- Cost-efficient technology for applications with higher current demand
- Safety thanks to connected, test, and disconnected position with the door closed
- Optimum cubicle width for every circuit breaker size
- Ideal space conditions for cable connection, for every size
- Design verified connection to SIVACON 8PS busbar trunking systems



Continuous power supply by means of design verified connection to SIVACON 8PS busbar trunking systems



Forced cooling for circuit-breaker design

- | | |
|--------------------------|-------------------|
| 1 Filter (only for IP54) | 4 Fan |
| 2 Heat sink | 5 Circuit breaker |
| 3 Air duct | |



Cooling system with fans underneath the 3WA circuit breaker

Universal mounting design



Combination of withdrawable design, fixed-mounted design, and plug-in design

Safe, flexible, and cost-efficient – if there is little space available





The universal mounting design allows you to combine different mounting designs – withdrawable, fixed-mounted with compartment doors, plug-in – in one and the same cubicle of your SIVACON S8^{plus} switchboard. As a version in withdrawable design, it is the ideal solution for Motor Control Centers in industrial plants, where a high availability of feeders and quick adjustments of the power supply are required.

Your advantages

- High level of flexibility and efficiency by combinable functional assemblies in one cubicle
- Space-optimized modular design
- Personnel safety, even in the event of a fault, thanks to closed front doors in all withdrawable unit positions (connected, test, disconnected positions)
- Long service life thanks to patented low-wear contact system

Technical data

Mounting design	Withdrawable design, fixed-mounted design with compartment doors, plug-in design
Functions	Cable feeders up to 630 A, motor feeders up to 250 kW (at 400 V)
Type of connection	front and rear
Cubicle width (mm)	600, 1,000, 1,200
Internal separation	Form 2b, 3b, 4a, 4b, 4 type 6, 4 type 7 (BS)



Technology basics for fixed-mounted design – plug-in design – withdrawable design

Code letters:

F for fixed connections *D* for detachable connections *W* for guided connections

Flexible and space-saving

The SIVACON S8^{plus} technology allows for a space-saving installation. The lateral connection compartment with cable brackets for propping up the cables can be 400 or 600 mm wide. Since the cables can also be connected at the rear in the universal mounting design, the cubicle width can be reduced to 600 mm. The rear-left vertical distribution busbars are executed as profile busbar or flat copper for tap-offs without any need for drilling or punching – optimal flexibility for later extensions.

Fixed-mounted design – modular and cost-efficient


The fixed-mounted switching devices are installed on modular device holders. These can be equipped with circuit breakers or switch disconnectors with fuses. Cable connection is made directly at the device or, in cases of higher requirements, at special connection terminals in the cable compartment. For individual equipping, the system offers device holders for free arrangement of components.

Plug-in design – flexible modifications

3NJ63 switch disconnectors with fuses can be installed in the bottom 600 mm of the device compartment. They are equipped with a plug-in contact on the supply/line side. This means that the switch disconnector can be replaced or retrofitted without de-energizing the cubicle.

Withdrawable design – ergonomic and compact

When requirements are frequently changing, e.g. modifications in motor rating or the connection of new consumer loads, the withdrawable design offers the flexibility needed. Withdrawable units can be retrofitted or exchanged with ease and without de-energizing the cubicle, thus avoiding downtimes. The withdrawable design is therefore the solution if a very high switchboard availability is required.



Withdrawable units of all sizes are equipped with integrated operating error protection

Arc-resistant distribution busbar embedding



Shutter with double-action for normal and small withdrawable units



Operating-error-proof and uniform operating concept throughout all sizes of withdrawable units



Mechanical coding of withdrawable units and compartments with up to 9,216 options



Withdrawable design – ergonomic and compact

Regardless of whether small or normal withdrawable units are used, the size is optimally adapted to the required power rating, thus allowing to reduce the size of the switchboard to a minimum. The compact small withdrawable units are particularly useful here. With small withdrawable units of size 1/4 (up to four withdrawable units per compartment) and 1/2 (up to two withdrawable units per compartment), as well as with normal withdrawable units with heights starting from 100 mm, very high packing densities can be achieved, with up to 48 withdrawable units per cubicle for space-optimized installation.


Distribution with safety

In the withdrawable design, the distribution busbar system is arranged at the rear. It offers test finger safety (IP20B) to live parts even without additional shutters. Optionally, the plug-in busbar system can be embedded in a way that is arc-resistant, and equipped with a shutter with double-action system. The tap-off openings are arranged in a 50 mm modular grid. This ensures maximum flexibility, even for later extensions. Optionally, a withdrawable unit coding (up to 9,216 options) can be used for the unambiguous assignment of withdrawable units.


Safe operation of the withdrawable units

Withdrawable units of all sizes are equipped with integrated operating error protection and a uniform, clear indication of the withdrawable unit positions. Moving to the connected, disconnected, or test position takes place with the door closed and without eliminating the degree of protection. In addition to the main switch, the disconnected position of the withdrawable units can also be locked for additional safety. A coding of the withdrawable unit prevents any mix-up of withdrawable units of the same size. The patented withdrawable unit contact system has been conceived to be user-friendly and particularly wear-resistant. In order to protect against damage, in the disconnected position all parts of the withdrawable units are located within the contours of the withdrawable units. No connection work is required inside the withdrawable unit compartments.


In the connected position, both the power and the control contacts are closed.



Withdrawable units in disconnected position have maximum isolating distances on the incoming, outgoing, and control sides.



The test position allows for no-load testing of the withdrawable units.



Moving to the withdrawable unit positions behind closed door

Energy-efficient cooling at any time

Like for cubicles in circuit-breaker design, the redundantly designed forced ventilation technology (optional) enables cost-efficient operation of cubicles in universal mounting design. The system reduces the derating and provides a low temperature profile inside the cubicle to ensure the safe operation and long service life of sensitive electronic equipment. The temperature is monitored at all critical spots, ensuring an energy-efficient cooling at any time. Speed-controlled fans optimize the service life and power demand.

Motor management and motor control devices

As a flexible, modular motor management system for motors in the low-voltage range, SIMOCODE pro optimizes the link between control system and motor feeder. The system increases the switchboard availability, and offers at the same time considerable savings during construction, commissioning, operation, and maintenance of a switchboard.

- Extensive protection, monitoring, safety, and control functions between the motor feeder and the automation system in just one compact system
- Independent of the controller
- Connection to process control systems using the most important communication protocols: PROFIBUS, PROFINET, Modbus RTU, and OPC UA
- SIMOCODE ES: for diagnostics and easy configuration, also in the TIA portal
- Integration in process control systems, such as SIMATIC PCS 7



*SIMOCODE pro –
the flexible and modular
motor management system*

Frequency converter design

Ideal for cost-efficient and safe power supply to continuously operating or highly dynamic pumps, fans, and compressors

The modular and compact frequency converter cubicle, as an integral part of SIVACON S8^{plus}, is supplied via the common busbar – or can optionally be delivered as an independent cubicle.

Your advantages

- Higher cost-efficiency thanks to the flexible solution for your switchboard with standardized modules
- More safety thanks to design verification according to IEC 61439, and test according to IEC/TR 61641
- Saved space in comparison with a conventional design

Technical data

Mounting design	Fixed mounting of modules with SINAMICS frequency converters of the G120 series
Functions	Control of continuously operating or highly dynamic pumps, fans, and compressors
Rated values of the module	from 0.55 kW to 132 kW
Type of connection	front
Cubicle width (mm)	600, 800, 1,000
Internal separation	Form 1, 2b




Fit for industrial applications – the frequency converter module

Specialized in the requirements of industrial applications

The cubicle contains up to nine standardized frequency converter modules, which integrate all required functions in a very small space. It is possible to use feeders either in design with fuses or without fuses. In terms of power rating, six tested frequency converter modules are available within the power range from 0.55 kW to 132 kW – modular, and flexibly convertible and expandable.

Fit for the digital age

A converter of the SINAMICS G120 series is the centerpiece of each module, and its IOP (Intelligent Operator Panel) is plugged onto the control unit of the frequency converter itself or installed in the cubicle door to ensure perfect access. With integrated communication modules, the frequency converters can easily be integrated in higher-level automation and energy management systems as well as in cloud-based analysis systems. Configuration is done via the proven TIA portal.



Frequency converter
module size FSA

Frequency converter
module size FSF

In-line design, plug-in

High packing density and possible exchange without de-energizing the cubicle entirely

The cubicles for cable feeders in in-line design with plug-in contact on the supply/line side can be equipped with up to 35 horizontal 3NJ63 switch disconnectors with fuses.

Variable with plug-in design

The 3NJ63 in-line switch disconnectors with fuses are suitable for cable feeders up to 630 A. The cable compartment has a width of either 400 or 600 mm and contains cable brackets which prop up the cables.

Safe and flexible

The distribution busbar system at the rear of the in-line design cubicle offers test finger safety (IP20B) to live parts. The tap-off openings are arranged in a 50 mm modular grid. This ensures maximum flexibility, even for later extensions.

Compact with high functionality

The cable is connected directly at the device, which also forms the front closure. Alternatively, SASILplus (JEAN MÜLLER) can also be executed in plug-in design on the load side. The plug-in in-line switch disconnectors are operated directly at the device. Up to three required current transformers can be installed in the in-line system within the device contours – auxiliary switches, measuring devices, and communication connections can also be integrated. Device compartments are available for individual equipping.



Up to 35 feeders per cubicle for 3NJ63 switch disconnectors with fuses

Your advantages

- High level of switchboard availability thanks to modification or replacement under operating conditions
- Simple and cost-efficient mounting thanks to plug-in contact on the supply/line side
- High packing density with up to 35 feeders per cubicle
- Flexible expansion possibilities

Technical data

Mounting design	Plug-in design
Functions	Cable feeders up to 630 A
Type of connection	front
Cubicle width (mm)	1,000, 1,200
Internal separation	Form 3b, 4b

In-line design, fixed-mounted

Cost-efficient choice if replacement of components under operating conditions is not required

The cubicles for cable feeders in the fixed-mounted design up to 630 A are equipped with vertically installed 3NJ4 fuse switch disconnectors.

Compact and safe

Depending on the cubicle width, there is room for several switch disconnectors of size 00 to 3 in order to build compact, economically optimized infrastructure applications. Additional auxiliary devices can be installed on a mounting plate or with ALPHA fast mounting kits.

Cost-efficient and adaptable

The distribution busbar system located horizontally at the rear inside the cubicle offers various cross-sections. The PE, PEN, or neutral conductor bars are installed separately from the phase conductors in the cable compartment, either at the top or the bottom of the cubicle, depending on the connection.

Flexible design

The switch disconnectors are fixed-mounted on the horizontal distribution busbar system and operated directly at the device. For each switch disconnector, up to three current transformers enable feeder-related measurements. The cables can be routed into the cubicle from the top or the bottom, and are connected directly at the switch disconnectors.

A cubicle-height door provides the front closure, optionally fitted with a cutout area, which allows to operate the switching devices when the door is closed.



Your advantages

- Space-saving thanks to compact design for up to 18 feeders per cubicle
- Consistently cost-efficient installation
- Optional installation of device holders for free arrangement of components, or ALPHA fast mounting kits for modular installation devices
- Optional door cutout for operation with closed front

Technical data

Mounting design	Fixed-mounted design
Functions	Cable feeders up to 630 A
Type of connection	front
Cubicle width (mm)	600, 800, 1,000
Internal separation	Form 1, 2b

Up to 18 feeders per cubicle with fixed-mounted 3NJ4 fuse switch disconnectors

Fixed-mounted design with front covers

Take advantage of the benefits of the fixed-mounted design and the easy operation through the cover

If short downtimes are acceptable for the replacement of devices, the fixed-mounted design with front covers offers advantages. Individual functional assemblies can be flexibly combined with it, and the functional compartments can be subdivided by means of additive modules as required (up to form 4b).

Safe, space-saving, and flexible

The design verified standard modules of the fixed-mounted design with front covers offer a high level of safety. The connection compartment on the right side of the cubicle has a width of either 400 or 600 mm; cable brackets are provided to prop up the cables. The rear-left vertical distribution busbars are designed as profile busbar or flat copper for tap-offs in the smallest of grids. Cables, wires, or busbars are connected without any need for drilling or punching – optimal flexibility for later extensions.

Multifunctional modules

The switching devices are installed on modular device holders of graduated depth. These can be equipped with circuit breakers, switch disconnectors with fuses, or modular installation devices. They are attached to the device holder and directly connected to the distribution busbar. Cable connection is made directly at the device or, in cases of higher requirements, at special connection terminals. Thanks to the cover, simple operation is possible directly at the device. The cubicle can be optionally closed with a glass door.



Easy installation of front covers, and uniform front level in the fixed-mounted design cubicle

Your advantages

- Cost-efficient arrangement of devices as single or multiple feeders
- Device holders of graduated depth
- More safety thanks to design verified standard modules
- High level of flexibility through the combination of high-rating feeders and modular installation devices

Technical data

Mounting design	Fixed-mounted design with front covers
Functions	Cable feeders up to 630 A
Type of connection	front
Cubicle width (mm)	1,000, 1,200
Internal separation	Form 1, 2b, 4a, 4b

Reactive power compensation

Cubicles for the central reactive power compensation make your power supply more cost-efficient and more energy-efficient

Reactive power from inductive, linear, and non-linear consumers (e.g. motors, transformers, reactors, converters, or UPS systems) burden transformers and cables/lines in the power grid, thus leading to transmission losses and causing avoidable costs.

Cost-efficient overall system

For reactive power compensation, SIVACON S8^{plus} switchboards are equipped with unchoked or choked capacitor assemblies depending on the consumer load structure. The controller assembly has an electronic reactive power controller for door installation. The multifunction display is used to set the desired target $\cos \phi$ from 0.8 ind to 0.8 cap. Network parameters such as U, I, f, $\cos \phi$, P, S, Q, and harmonics are displayed.

The capacitor assemblies (up to 200 kvar) comprise a fuse switch disconnecter, capacitor contactors, discharge devices, and filter reactors. A central switch-disconnector assembly can optionally be used for the safety isolation of the integrated capacitor assemblies. In this way, the central reactive power compensation of SIVACON S8^{plus} enables an economically optimized power supply with efficient network dimensioning. If required, the compensation cubicle can also be installed separately.



Cubicle for the central reactive power compensation

Your advantages

- Increased cost-efficiency thanks to lower energy costs
- Efficient network dimensioning thanks to low reactive power
- Design verified integration, either directly in the switchboard or as a separate cubicle

Technical data

Mounting design	Fixed-mounted design
Functions	Central reactive power compensation
Capacitor power	up to 500 kvar unchoked/choked
Degree of choking	without, 5.67%, 7%, 14%
Type of connection	front
Cubicle width (mm)	800
Internal separation	Form 1, 2b

Competent support for your SIVACON S8^{plus} switchboard

Our qualified and experienced experts assist you worldwide, from planning to maintenance.

Your advantages

- Development "Made in Germany"
- Bundled competence at the Center of Competence in Leipzig, Germany
- Comprehensive support locally and online
- Comfortable and time-saving planning with SIMARIS tools



Reliable local support, worldwide

Siemens experts assist you worldwide in all matters related to SIVACON S8^{plus}. They provide ideas and solutions for your power supply, and specific expertise on project management and financial services. Important aspects of safety, logistics, and environmental protection are also considered. Every region is attended by specifically trained promoters, who are responsible for assisting Siemens customers. Technical experts from TIP Consultant Support are available, too, especially for the planning and conception of electrical power distribution systems.

[siemens.com/tip-cs](https://www.siemens.com/tip-cs)

Your local contact partners

Through our contact database you can easily identify the S8^{plus} contact partner or service provider in your region.

[siemens.com/sivaconS8plus-contact](https://www.siemens.com/sivaconS8plus-contact)

SIVACON S8^{plus} low-voltage switchboards online

Our website offers you a broad range of promotional and technical information as well as helpful tools for the SIVACON S8^{plus} low-voltage switchboards.

[siemens.com/sivacon-S8plus](https://www.siemens.com/sivacon-S8plus)

SIVACON S8^{plus} in moving images

Various videos on the advantages of the low-voltage switchboard SIVACON S8^{plus} are available on the Siemens YouTube channel under power distribution – SIVACON.



Comfortable planning with the SIMARIS tools

Planning electric power distribution for industrial plants, infrastructure, and buildings is becoming more and more complex. To help you work faster and better under existing conditions, the innovative SIMARIS software tools effectively support your planning process:

- SIMARIS design – dimensioning electric grids, and automatically selecting components
- SIMARIS project – determining space requirements and budget for power distribution systems

[siemens.com/simaris](https://www.siemens.com/simaris)

Efficiency from planning to maintenance – with BIM data

Within the scope of digitalization, Building Information Modeling (BIM) offers great benefits already in the planning process. Easy exchange of all relevant building data from planning to facility management ensures quality and saves both time and money. For this reason, BIM also plays an increasingly important part in electrical planning.

[siemens.com/bim-eplanning](https://www.siemens.com/bim-eplanning)

Technical documentation online

You will find an overview of the latest technical documentation available for SIVACON S8^{plus} on our website (updated daily) at

[siemens.com/lowvoltage/product-support](https://www.siemens.com/lowvoltage/product-support)

First-hand know-how

Our courses offer you solid foundations for your business success. Expert lecturers provide you with the necessary theoretical and practical information relating to our SIVACON S8^{plus} low-voltage switchboards.



Technical data



Standards and approvals

Standards and regulations	Power switchgear and controlgear assembly (design verification)	IEC 61439-2 DIN EN 61439-2 VDE 0660-600-2
	Testing under conditions of internal fault (arc faults)	IEC/TR 61641 DIN EN 61439-2 Supplement 1 VDE 0660-600-2 Supplement 1
	Integration and testing of active arc fault protection systems	IEC/TS 63107
	Induced vibrations	IEC 60068-3-3 IEC 60068-2-6 IEC 60068-2-57 IEC 60980 KTA 2201.4 Uniform Building Code (UBC), Edition 1997 Vol. 2, Ch. 19, Div. IV
	Protection against electric shock	EN 50274 (VDE 0660-514)
Approvals and certifications	Europe Russia, Belarus Kazakhstan China	CE Marking and EC Declaration of Conformity EAC (Eurasian Conformity)
	Det Norske Veritas Lloyds Register of Shipping	CCC DNV GL Type Approval Certificate LR Type Approval Certificate ABS American Bureau of Shipping
	Shell Conformity	"DEP Shell"

Technical data

Rated operational voltage U_e	Main circuit	up to 690 V (rated frequency f_n 50 Hz)
Clearances and creepage distances	Rated impulse withstand current I_{imp}	8 kV
	Rated insulation voltage U_i	1,000 V
	Pollution degree	3
Main busbars, horizontal	Rated current	up to 7,010 A
	Rated peak withstand current I_{pk}	up to 330 kA
	Rated short-time withstand current I_{cw}	up to 150 kA, 1s
	Busbar position	top, rear-top, rear-bottom
Rated currents of devices	Circuit breakers	up to 6,300 A
	Cable feeders	up to 630 A
	Motor feeders	up to 250 kW
Internal separation	IEC 61439-2	Form 1 to form 4
	BS EN 61439-2	up to form 4 type 7
IP degree of protection	In accordance with IEC 60529	ventilated up to IP43 non-ventilated IP54 forced ventilated up to IP54
Mechanical strength	IEC 62262	up to IK10
Dimensions	Height (without base)	2,000, 2,200 mm
	Height of base (optional)	100, 200 mm
	Cubicle width	200, 350, 400, 600, 800, 850, 1,000, 1,200, 1,400 mm
	Depth	single front 500, 600, 800 double front 1,000, 1,200 mm
Installation conditions	Indoor installation, ambient air temperature in the 24-h mean	+35° C (-5° C up to +40° C)

Project checklist – Part 1

Customer	
<hr/>	
Author	
<hr/>	
Project	Tel./mobile
<hr/>	
Project no.	E-mail
<hr/>	
Delivery date	Date

Standards and regulations

<input checked="" type="checkbox"/> IEC 61439-1/2/ EN 61439-1/2 VDE 0660 Part 600-1/2	IEC/TR 61641, testing under conditions of arcing	
	<input type="checkbox"/> Arcing class A	
	<input type="checkbox"/> Arcing class C with limitation to the area of the cubicle	<input type="checkbox"/> Arcing class C with limitation to the area of the compartment
	IEC/TR 61641, arc ignition protected zone	
	<input type="checkbox"/> Main busbar	<input type="checkbox"/> Neutral conductor
	<input type="checkbox"/> Cable connection, FCB cubicles	
	IEC/TS 63107, integration and testing of active arc fault protection systems	
	<input type="checkbox"/> Arc detection system, quenching by circuit breaker	<input type="checkbox"/> Arc detection system, quenching by arc quenching device (AQD) and circuit breaker

Communication, sensors, and power monitoring

Preferred bus system	<input type="checkbox"/> PROFINET	<input type="checkbox"/> PROFIBUS DP	<input type="checkbox"/> Modbus RTU
	<input type="checkbox"/> MODBUS TCP	<input type="checkbox"/> Others	
Power monitoring	<input type="checkbox"/>		
Temperature supervision	<input type="checkbox"/> Wired with PT100 or PT1000	<input type="checkbox"/> Wireless with IR sensors	
Position of the sensors	<input type="checkbox"/> On the main busbar at the joints of the transport unit <input type="checkbox"/> Customer connections of the circuit-breaker cubicles <input type="checkbox"/> Connection to the main busbar in universal mounting design cubicle <input type="checkbox"/> Others:		
SIMARIS control	<input type="checkbox"/> System software for customer PC	<input type="checkbox"/> With central touch display at the switchboard	
	<input type="checkbox"/> With industry PC in the switchboard		

Environmental conditions

Operating conditions	<input type="checkbox"/> Standard (indoor climate 3K4)	<input type="checkbox"/> Corrosive gases (for example, H ₂ S)
	<input type="checkbox"/> Special	
Ambient air temperature (24-h mean)	<input type="checkbox"/> 20° C <input type="checkbox"/> 25° C <input type="checkbox"/> 30° C <input type="checkbox"/> 35° C <input type="checkbox"/> 40° C <input type="checkbox"/> 45° C <input type="checkbox"/> 50° C	
Site altitude above sea level	<input type="checkbox"/> ≤ 2,000 m	<input type="checkbox"/> Others: m
Adverse operating conditions	<input type="checkbox"/> None <input type="checkbox"/> Earthquake-proof <input type="checkbox"/> Ship/Offshore <input type="checkbox"/> Others:	

Layout and installation

Type of installation	<input type="checkbox"/> Single-fronted	<input type="checkbox"/> Double-fronted	<input type="checkbox"/> Back-to-back
Connection inside the cubicle	<input type="checkbox"/> Front	<input type="checkbox"/> Rear	
Restriction of total length	<input type="checkbox"/> Without	<input type="checkbox"/> Yes	mm
Max. net length per transport unit	<input type="checkbox"/> 2,400 mm	<input type="checkbox"/> Others	mm

Cable/busbar entry

Incoming feeder cubicles	<input type="checkbox"/> From bottom	<input type="checkbox"/> From top
Outgoing feeder cubicles	<input type="checkbox"/> From bottom	<input type="checkbox"/> From top

Degree of protection

Ventilated cubicle	<input type="checkbox"/> IP30	<input type="checkbox"/> IP31	<input type="checkbox"/> IP40	<input type="checkbox"/> IP41	<input type="checkbox"/> IP43
Non-ventilated cubicle	<input type="checkbox"/> IP54				
Towards the cable floor	<input type="checkbox"/> IP00	<input type="checkbox"/> IP30	<input type="checkbox"/> IP40	<input type="checkbox"/> IP54	
	<input type="checkbox"/> Provided by the factory		<input type="checkbox"/> Provided by the customer		

Project checklist – Part 2

Project:

Network data/infeed data

Network type	<input type="checkbox"/> TN-C <input type="checkbox"/> IT	<input type="checkbox"/> TN-S <input type="checkbox"/> TT	<input type="checkbox"/> TN-C-S
Transformer rated power S_T	kVA	Rated impedance voltage U_z	%
Rated operational voltage U_e	V	Frequency f	Hz
Rated short-time withstand current I_{cw}	kA	Short-circuit withstand current I_k at DC	kA
Design of external connection	<input type="checkbox"/> L1, L2, L3, PEN <input type="checkbox"/> Others: <input type="checkbox"/> 3-pole switchable	<input type="checkbox"/> L1, L2, L3, PE + N <input type="checkbox"/> 4-pole switchable	<input type="checkbox"/> CEP (PEN + PE)

Horizontal busbar system

Position	<input type="checkbox"/> Top	<input type="checkbox"/> Rear-top	<input type="checkbox"/> Rear-bottom
Rated current I_n	A	A	A
Cu surface treatment	<input type="checkbox"/> Bare	<input type="checkbox"/> Silver-plated	<input type="checkbox"/> Tinned
Design L1, L2, L3 + ...	<input type="checkbox"/> PEN <input type="checkbox"/> PEN, N = 50% <input type="checkbox"/> Others:	<input type="checkbox"/> PE <input type="checkbox"/> PEN, N = 100%	<input type="checkbox"/> N

Vertical busbar system/distribution bars

Cu surface treatment	<input type="checkbox"/> Bare	<input type="checkbox"/> Silver-plated	<input type="checkbox"/> Tinned
Design L1, L2, L3 + ...	<input type="checkbox"/> PEN <input type="checkbox"/> PEN, N = 50%	<input type="checkbox"/> PE <input type="checkbox"/> PEN, N = 100%	<input type="checkbox"/> N

Internal separation

Circuit-breaker design	<input type="checkbox"/> Form 1	<input type="checkbox"/> Form 2b <input type="checkbox"/> Form 4b	<input type="checkbox"/> Form 3a <input type="checkbox"/> Form 4 type 7
Universal mounting design	<input type="checkbox"/> Form 4a	<input type="checkbox"/> Form 4b	<input type="checkbox"/> Form 4 type 6 <input type="checkbox"/> Form 4 type 7
Frequency converter design	<input type="checkbox"/> Form 1	<input type="checkbox"/> Form 2b	
In-line design, plug-in		<input type="checkbox"/> Form 4b	<input type="checkbox"/> Form 3b
In-line design, fixed-mounted	<input type="checkbox"/> Form 1	<input type="checkbox"/> Form 2b	
Fixed-mounted design	<input type="checkbox"/> Form 1 <input type="checkbox"/> Form 4a	<input type="checkbox"/> Form 2b <input type="checkbox"/> Form 4b	<input type="checkbox"/> Form 3b
Reactive power compensation	<input type="checkbox"/> Form 1	<input type="checkbox"/> Form 2b	

Assumed load of the consumer feeders

Values for assumed loading for motor-operated consumers	<input type="checkbox"/> 1	<input type="checkbox"/> 0.8		
Values for assumed loading for power distribution	<input type="checkbox"/> 1 <input type="checkbox"/> 0.6	<input type="checkbox"/> 0.9	<input type="checkbox"/> 0.8	<input type="checkbox"/> 0.7

Notes

Published by
Siemens AG

Smart Infrastructure
Distribution Systems
Mozartstrasse 31c
91052 Erlangen
Germany

For further information,
please contact our
Customer Support Center.
Tel.: +49 180 524 70 00
(Charges depending on provider)
E-mail: support.energy@siemens.com

Article No. SIDS-B10031-00-7600
Dispo 30407 TH 260-191070 BR 1120
© Siemens 2020

Subject to changes and errors.
The information given in this document only contains general, non-comprehensive descriptions and/or performance features which may not always specifically or completely reflect those described, is used for noncommittally information purpose or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract. Therefore, nor warranties nor guarantees for the accuracy, completeness or up-to-dateness of the given information is assumed and the document does not constitute advice on correct application and implementation of the given standards.

All product designations may be trademarks or other rights of Siemens AG, its affiliated companies or other companies whose use by third parties for their own purposes could violate the rights of the respective owner.

