

The Siemens logo is displayed in a bold, white, sans-serif font against a dark blue background. The letters are evenly spaced and have a clean, modern appearance.

SIEMENS

PROCESS INSTRUMENTATION

Motion monitoring in the digital age - with SITRANS WM300 MFA

usa.siemens.com/wm300

Compact, rugged and reliable

A rugged early warning system for your plant, motion failure alarms (MFA) alert you to potential problems in your operations before they occur or develop into something more serious. Introducing SITRANS WM300 MFA, detecting changes in the motion and speed of your rotating, reciprocating, or conveying equipment. It warns of machinery malfunction and signals to shut down processes in case of a slowdown or failure. This versatile unit excels in a variety of applications: tail pulley shafts, driven pulleys, motor shaft sensing, belt or drag conveyors, and fans and machines. In the mining, aggregates and cement industry, for example, SITRANS WM300 MFA monitors bucket elevators and screw conveyors for continuous conveying. And in the food and beverage or chemical industries, the alarm monitors mixers to ensure non-stop operation. This space-saving device replaces many older MFA style controllers, reducing both your wiring time and the space required in cabinets. In fact, four SITRANS WM300s can fit in the same footprint as older motion failure alarms!



Space-saving

- Reduction in size of cabinets and in wiring time
- DC power supply

Economical

- Short commissioning time
- Reduced stocks
- Precise set point control

New Functions

- Differential speed detection
- Non-contacting tachometer
- Over/under speed alarming
- Four relays

**Motion probes**

- Backward compatible
- Direct connection with MSP-7

Easy to handle

- Intuitive programming
- Can be used without specific training courses

With intuitive, easy-to-configure digital programming, you get precise set point control of machines or processes for accurate alarming that prevents potentially costly down-time or damage. Monitor multiple machines at once with twin, independent probe inputs as well as an additional two inputs for differential speed detection. No longer requiring separate MFAs for over- and under-speed alarming, you can now monitor both values with the same SITRANS WM300 MFA. Another valuable feature is the optional

analog output module, which can convert the device into a non-contacting tachometer with two mA outputs. And with its adjustable 0- to 60-second time delay, this intelligent alarm allows the monitored equipment to accelerate to normal running speed before monitoring begins. Compact, rugged and reliable motion failure alarms from Siemens are economical investments with a large impact - ensuring peace of mind and protecting your processes.

	SITRANS WM300 MFA
Applications	Tail pulleys, motor shaft sensing, screw conveyor flights, bucket elevators
Measurement range	Up to 100mm (4")
Outputs	4 relays, 2, 4 ... 20 mA outputs (NCT)
Input speed	30 - 300,000 ppm
Process connections	2" NPSL motion probes
Options	• Remote display • High temp probes • mA output card • WM300 RMA module
Order number	7MH7701-0AA00-0A

Legal Manufacturer

Siemens Industry, Inc.
100 Technology Drive
Alpharetta, GA 30005
United States of America
Telephone: +1 (800) 365-8766
usa.siemens.com/pi
Order No.: PIFL-00178-0223

This document contains a general description of available technical options only, and its effectiveness will be subject to specific variables including field conditions and project parameters. Siemens does not make representations, warranties, or assurances as to the accuracy or completeness of the content contained herein. Siemens reserves the right to modify the technology and product specifications in its sole discretion without advance notice.