



SIEMENS

Ingenuity for life




IO-Link – continuous communication through to the last metre

Integrate sensors and actuators seamlessly into the automation pyramid

[siemens.com/io-link](https://www.siemens.com/io-link)

IO-Link – the point-to-point connection ...



Consistent cost reduction, high system availability and transparency – the requirements for a continuous industrial communication are rising.

At the same time, actuators and sensors are becoming increasingly intelligent. To be equipped for the requirements of the future, data transparency and communication must therefore extend deeper than only to the control level. However, how can the growing intelligence of sensors and actuators be integrated and used optimally in the automation system?

Easily integrating sensors and actuators in the data flow

Siemens provides the answer with the open communication standard IO-Link. Here, you benefit not only from the simple, standardised and favourable point-to-point connection with which sensors and actuators can be connected to the control level, but also from the systematic diagnosis concepts and efficient handling of parameter data on all levels of automation technology.


Lay the ideal basis for efficient transparency – with IO-Link both in the control cabinet and on the field level.

IO-Link – fully integrated in TIA

In every production facility, IO-Link solutions from Siemens ensure maximum precision and economy. Thus data access through to the sensor/actuator level, e.g. for central fault diagnosis and localisation, increase installation availability and reduce engineering outlay.

Through seamless integration in the Totally Integrated Automation (TIA) concept, the full potential of this communication standard emerges properly for the first time – both in the switchboard and on the field. Consequently, it allows simple, uninterrupted and open engineering. Furthermore, the inclusion in energy management becomes simpler and the commissioning of actuators sensors and switching devices becomes faster.

The IO-Link master modules and IO-Link devices can be parameterised conveniently using the PC-based STEP 7 port configuration tool (PCT) – and this can be done even with integration in the TIA portal. You can also select, configure and order all IO-Link products quickly and easily using the TIA selection tool.



IO-Link – all the products you need

As an open interface, IO-Link can be integrated in all current fieldbus and automation systems: the open communication standard was developed by the IO-Link company collective, in which leading suppliers of automation products have joined forces to support the concept in all areas of control, sensor and actuator technology.

The consistent interoperability ensures high investment protection – even in the context of existing machine concepts for the further use of sensors that have no IO-Link interface. Furthermore, through the interoperability, you have a free choice of products and can benefit from guaranteed development.

	<p>IO-Link master To connect IO-Link devices with your automation system, Siemens offers you IO-Link master for decentralised peripheral SIMATIC ET 200 and the SIMATIC S7-1200 and SIMATIC S7-1500 controls. These master modules integrate the IO-Link communication with sensors and actuators into the established fieldbus systems – PROFIBUS and PROFINET – and thus into Totally Integrated Automation.</p>	<ul style="list-style-type: none"> • SIMATIC S7-1200 • SIMATIC S7-1500 • SIMATIC ET 200eco PN • SIMATIC ET 200AL • SIMATIC ET 200pro • SIMATIC ET 200SP
	<p>Industrial switching technology Industrial switching technology from Siemens offers you everything you need to integrate actuators into your automation network easily, efficiently and reliably via IO-Link.</p>	<ul style="list-style-type: none"> • SIRIUS 3RS2 temperature monitoring relay • SIRIUS 3RR24 and SIRIUS 3UG48 monitoring relays • SIRIUS 3RB24 electronic monitoring relay • SIRIUS 3RA6 compact • SIRIUS 3RA27 functional modules for attachment to contactors
	<p>Commanding and signaling devices The SIRIUS ACT commanding and signaling devices can also be connected to IO-Link. This includes the electronic SIRIUS ACT ID key switch with the latest RFID technology. Via special electronics modules for IO-Link, the SIRIUS ACT push buttons and signaling devices can be connected quickly to IO-Link. The signaling columns 8WD 44 can be integrated via IO link using an adapter element.</p>	<ul style="list-style-type: none"> • SIRIUS ACT ID key • SIRIUS ACT electronics modules • Signaling columns 8WD 44



	<p>RFID reader The SIMATIC RF 200 RFID system IO-Link is designed for identification tasks, such as reading identification numbers. It consists of space-saving HF readers, which are particularly suited to applications in intralogistics or in small assembly lines.</p>	<ul style="list-style-type: none"> • SIMATIC RF200 IO-Link
	<p>IO modules The compatibility of IO-Link modules also allows an easy connection of standard sensors and actuators. Signals and energy is transmitted through IO-Link (IO-Link master). The IO-Link modules can be connected to any IO-Link master and thus enable a set-up of distributed I/O module units that are field-bus-independent.</p>	<ul style="list-style-type: none"> • IO-Link modules
	<p>Software IO-Link software tools and functional modules ensure standardised and efficient engineering and visualisation of diagnostic information. Thus the PC-based S7 port configuration tool simplifies parameterisation. Moreover, Siemens provides both IODD device description files and functional modules and UDTs for all IO-Link devices from the Siemens portfolio.</p>	<ul style="list-style-type: none"> • S7 port configuration tool • IO-Link functional modules • IODD device description files

IO-Link – in every industry in the field

With its very fast and cost-saving cabling as well as the simple engineering, IO-Link has long since arrived in practice. In many applications and industries, the standard ensures a transparent data flow to the sensors

and actuators – and thus more transparent, more reliable machines, installations and processes.

IO-Link in the steel industry



Duisburg steel production is dependent upon the reliable supply of processed coal to the furnace. At Emscher Aufbereitung GmbH, automation specialist EAS GmbH modernised the conveyor belts together with all auxiliary components, with new electrical engineering and automation.

Our solution

The group formation of SIRIUS motor starters with IO-Link significantly reduced the outlay for parallel wiring: the motor starters combine circuit breaker, contactor and electronic overload relay in one compact housing. SIRIUS power monitoring relays improve data collection and communicate with the control via IO-Link. By measuring the active current, conclusions can also be drawn about the efficient operation of the drives.

The benefit

- significantly less cabling, due to motor starter with IO-Link
- Optimised plant operation due to many diagnostic options
- Detection of faults in the control centre and targeted troubleshooting

Production machines for grinding discs



Davide Maternini SPA uses the ET 200AL and ET200SP IO system to simplify the production process and to save costs and time. Use of the ET 200AL allows engineers to save time during the planning and implementation phase of the projects through the option of installing the modules flexibly, which reduces the number of switch boxes required. The diagnostic capability of the ET 200SP modules and the IO-Link sensor technology allow faster installation and a shorter debugging phase during commissioning on the customer site.

The benefit

- Reduction of installation and wiring time by 15% due to the flexible installation options of the ET 200AL directly on the machine
- Increase in availability as a result of the detailed diagnoses of the ET 200SP and information from intelligent IO-Link sensors
- Reduction of switchboard size due to the small footprint of the ET 200SP and installation of the ET 200AL outside the switchboard

... For greater efficiency on all levels

The IO-Link solution from Siemens allows communication with sensors and closes the last metre in the process with continuous data transparency.

1

Fast diagnosis

- Detection and reporting of relevant diagnostic events
- Reduced effort in troubleshooting
- Minimisation of downtimes

2

Efficient engineering

- Fast, fault-free IO-Link engineering with the SIMATIC S7-PCT configuration tool integrated in STEP 7
- Reparameterisation in ongoing operation and reading of additional information
- Fast, simple commissioning of the IO-Link devices thanks to an existing library with device-specific function blocks

3

Standardised wiring

- Manufacturer-independent and cost-effective wiring technology
- Fast, fault-free switch from conventional wiring to IO-Link technology
- Simplified storage
- Increased productivity for service staff

4

Automatic parameterisation

- Parameterisation of a new sensor or actuator through IO-Link master or by means of IOL_DEVICE functional module
- Avoidance of incorrect settings
- Minimisation of downtimes and simplification of device replacement

5


Reduced wiring cost

- Faster installation and lower wiring fault rate
- Reduced number of I/O modules and cables due to use of up to 16 motor starters from Siemens per IO-Link master

6

High process transparency

- Transfer of measuring data, e.g. energy data, through the IO-Link devices to the higher level controller
- Optimisation of the energy demand
- Avoidance of cost-intensive peak loads
- Longer product lifetime



**Published by
Siemens AG 2020**

Siemens AG Digital Factory
Postfach 48 48
90026 Nuremberg
Germany

Article-No. DFFA-B10447-01-7600
Printed in Germany
Dispo 06334
gB170157 BR 09200.0

Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.

To protect installations, systems, machines and networks from cyber threats, it is necessary to implement (and continuously maintain) a holistic industrial security concept that corresponds to the latest technology. The products and solutions from Siemens form only one element of such a concept. Further information about industrial security can be found at [siemens.com/industrialsecurity](https://www.siemens.com/industrialsecurity).

