

Dodatak 3.1.1 Preneta osnovna sredstva

Dodatak 3.1.1 Preneta osnovna sredstva	
Inventarni broj	Opis / naziv
11000064	Licence za radnu stanicu Wartnugsplaner v6
11000065	Licence za radnu stanicu Wartnugsplaner v6
11000066	Licence za radnu stanicu Wartnugsplaner v6
11000068	Licenca za Wartungsplaner
11000069	Licenca za Wartungsplaner
11000070	Licenca za Wartungsplaner
40000097	Goodwill
40000122	Goodwill
40000048	Izrada elektricne instalacije
40000049	Rekonstrukcija i prenamena magacinskog prost.
40000050	Ulaganje u halu
40000051	Hala 1
40000052	Hala 2
40000053	Refundacija elektroradova na trafostanici
40000055	Adaptacija proizvodne hale u malom
40000056	Adaptacija proizvodne hale
40000057	Adaptacija proizvodne hale
40000058	Adaptacija proizvodne hale
40000059	Adaptacija proizvodne hale u ml.baj
40000060	Adaptacija proizvodne hale u mal baj
40000073	Radovi za rashladni sitem
40000080	Soba za pusenje na galeriji Hala 1
40000082	Soba za pusenje u nivou prizemlja Hala 1
40000083	Soba za pusenje u nivou prizemlja Hala 2
40000085	Kontrolna soba za pec u Hali 1
40000088	Rekonstruk. i pretvar. Hale 2 u halu za proizvod.
40000093	Revizioni saht za kanalizaciju u prizemlju-Hala 1
40000094	Kancelarija za REFU na spratu Hale 1
40000095	Kancelarija za QM na spratu Hale 1
40000096	Kancelarija kod montaze u Hali 1
40000098	Sistem za snagu - Trafo stanica III
40000101	Kancelarija za sindikat - Hala 1
40000102	Jednokrilna vrata u hali 4.1
40000103	Betonska platforma - hala 2
40000104	Efaflex rolo vrata - hala 2

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

40000105	Efaflex rolo vrata - hala 2
40000106	Efaflex rolo vrata - hala 2
40000107	Prostorije recepcije,soba za posetioce i SAP kanc.
40000108	Pomocne prostorije-social room 2, Hala 2
40000109	Nadstresnica za otpad iza Hale 4.1
40000110	Pregradni zid sa aluminijum. rolo vratima u Hali 2
40000110	Adaptacij.pregrad. zid sa ugradnjom brzo pod.vrata
40000111	Pomocne prostorije, Hala 2
40000114	Kancelarija na liniji A Hala 1
40000115	Kancelarija na liniji A Hala 1
40000116	Kancelarija na liniji A Hala 1
40000117	Kancelarija na liniji A Hala 1
40000118	Trafo stanica za visokonaponsko ispitivanje
40000119	Pomocne prostorije 3a,Hala 2 (toalet,kantina,gard)
40000119	Adaptacija Pomocne prostorije hala 3a,hala2
40000120	Pregradni zid 2 sa brzo podizucim vratima u Hali 2
40000121	Kancelarija za smenovodje na liniji 2 i 3
40000123	Izrada parking prostora za fabriku, 56 mesta
40000125	Rolo vrata brzopodizna - hala 3
40000126	Rolo vrata brzopodizna - hala 3
40000127	Betonska platforma - hala 3
40000128	Soba za pusenje severni deo, Hala 3
40000129	Soba za prvu pomoc severni deo, Hala1
40000130	Soba za prvu pomoc juzna strana, Hala 2
40000132	Kancelarija za montažu u hali 1
40000133	Radionica za doradu generatora u Hali 1
40000134	Soba za pusenje u hali 1
40000135	Trpezarija za radnike juzna strana Hala1
40000136	Ucionica u okviru Hale 3
40000138	Tipaska Portirinca
40000139	Kancelarija u hali 1 Stator
40000140	Kancelarija u hali 1 2 Stator
40000141	Kancelarija u hali 1 Rotor
40000143	Klizna Automatizovana Kapija Glavni Ulaz Logistick
40000144	Rolo Vrata Hala 3 Efaflex (roto door Hall 3)
40000146	Klima Uredjaj 18 BTU 2017
40000147	Laboratorija
40000155	Čista soba
40000156	Izgradnja zaustavnog predprostora
40000157	Objekat za mašinsku opremu
40000158	Ograda I kapija kod skladista otpada

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

40000161	Raskladna komora hala3
40000162	Vetrobran hala I
40000163	Nadstresnice za odmor zaposlenih
40000164	Nadstresnice za odmor zaposlenih
40000165	Nadstresnice za odmor zaposlenih
40000166	Nadstresnice za odmor zaposlenih
40000167	Nadstresnice za odmor zaposlenih
40000168	Punionice baterija
40000169	Kuhinja sa elementima
40000170	Zaštitna ograda Hala 1
40000171	Prostorija za proizvodnju protofera
40000173	Eflex rolo vrata
40000174	Klizna kapija na izlazu ka novoj hali
40000099	Sistem za teh.vent.i klim.za impr.DDW seg.Hala 4.1
40000100	Sistem za napajanje opreme el. energ. u hali 4.1.
40000112	Sistem za klimatizaciju u Hali 1
40000112	Sistem za klimatizaciju u Hali 1
40000113	Sistem za klimatizaciju u Hali 2
40000113	Sistem za klimatizaciju u Hali 2
40000124	Sistem ventilacije kuhinje u soc. delu 3,Hala 2
40000145	Sistem LED rasvete
40000148	Sistem akvizicije i merenja potrošnje energenata
50000293	Nosac statora za namotavanje 9
50000294	Nosac statora za namotavanje 8
50000321	Jedinica za namotavanje sa elektromotorom i redukt
50000322	Jedinica za namotavanje sa elektromotorom i redukt
50000323	Jedinica za namotavanje sa elektromotorem i redukt
50000324	Jedinica za namotavanje sa elektromotorem i redukt
50000327	Hidraulicna masina -schymann
50000329	Hidraulicni agregat
50000330	Hidraulicni agregat
50000333	Masina za secenje
50000334	Pec za polimerizaciju
50000334	Pec za polimerizaciju-premestanje peci
50000334	Pec za polimerizaciju-ugrad. sina i ventilac.kanal
50000334	Pec za polimerizaciju-izrada elektric. instalacije
50000354	Uredaj za montazu magneta
50000355	Uredaj za montazu magneta
50000373	Masina za izravnvanje krajeva namotaja
50000374	Masina za izravnvanje krajeva namotaja
50000393	Susara 15

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

50000409	Pec za polimerizaciju
50000415	Hidraulicna presa za namotaje
50000416	Hidraulicna presa za namotaje
50000417	Hidraulicna presa za namotaje
50000418	Hidraulicna presa za namotaje
50000420	Pec za toplotno tretiranje drveta
50000422	Impregnacioni sistem 3
50000423	Susara 17
50000424	Susara 18
50000424	Nadogradnja peći
50000438	Nosac statora za namotavanje 4
50000439	Nosac statora za namotavanje 5
50000440	Nosac statora za namotavanje 6
50000441	Nosac statora za namotavanje 7
50000446	Nosac statora za namotavanje 1
50000447	Nosac statora za namotavanje 2
50000705	Pec za polimerizaciju
50000711	Komora za grejanje statora
50000712	Hidraulicna presa rm123
50000713	Hidraulicna presa rm124
50000714	Hidraulicna presa rm135, 138 i 139
50000715	Hidraulicna presa rm119
50000716	Hidraulicna presa rm130
50000717	Hidraulicna presa rm146
50000718	Hidraulicna presa rm150
50000719	Hidraulicna presa rm133
50000720	Hidraulicna presa rm145
50000721	Presa rm131 4 glave
50000722	Masina za bandaziranje
50000722	Masina za bandaziranje-dodatno postolje
50000723	Hidraulicna presa rm148
50000724	Hidraulicna presa rm134
50000725	Hidraulicna presa rm128
50000726	Hidraulicna presa rm129
50000727	Hidraulicna presa rm100
50000728	Hidraulicna presa rm125
50000729	Hidraulicna presa rm147
50000730	Nosac statora za namotavanje 25
50000731	Nosac statora za namotavanje 26
50000732	Nosac statora za namotavanje 27
50000733	Nosac statora za namotavanje 28

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

50000734	Nosac statora za namotavanje 29
50000735	Nosac statora za namotavanje 33
50000736	Hidraulicna presa rm120
50000737	Hidraulicna presa rm139
50000738	Hidraulicna presa rm132
50000739	Hidraulicna presa rm136
50000740	Hidraulicna presa rm144
50000741	Hidraulicna presa rm154
50000742	Masina za bandaziranje
50000744	Nosac statora za namotavanje 34
50000745	Nosac statora za namotavanje 35
50000747	Hidraulicna presa rm115
50000748	Hidraulicna presa rm127
50000749	Hidraulicna presa rm141
50000750	Hidraulicna presa rm102
50000751	Hidraulicna presa rm121
50000752	Nosac statora za namotavanje 13
50000753	Nosac statora za namotavanje 56
50000754	Hidraulicna presa rm142
50000755	Pila za secenje tega kod balans masine
50000756	Hidraulicna presa rm143
50000757	Hidraulicna presa rm155
50000758	Hidraulicna presa rm149
50000759	Hidraulicna presa rm122
50000760	Hidraulicna presa rm101
50000761	Hidraulicna presa rm156
50000762	Nosac statora za namotavanje 14
50000763	Nosac statora za namotavanje 15
50000764	Nosac statora za namotavanje 16
50000765	Nosac statora za namotavanje 17
50000766	Nosac statora za namotavanje 18
50000767	Nosac statora za namotavanje 19
50000768	Nosac statora za namotavanje 20
50000769	Nosac statora za namotavanje 21
50000770	Nosac statora za namotavanje 22
50000771	Nosac statora za namotavanje 23
50000772	Nosac statora za namotavanje 24
50000773	Nosac statora za namotavanje 40
50000774	Nosac statora za namotavanje 43
50000775	Nosac statora za namotavanje 44
50000776	Nosac statora za namotavanje 45

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

50000777	Nosac statora za namotavanje 54
50000778	Nosac statora za namotavanje 55
50000779	Hidraulicna presa rm140
50000780	Hidraulicna presa rm153
50000781	Hidraulicna presa rm160
50000782	Hidraulicna presa rm151
50000783	Hidraulicna presa rm152
50000784	Hidraulicna presa rm157
50000785	Hidraulicna presa rm158
50000786	Hidraulicna presa rm159
50000787	Hidraulicna presa rm162
50000788	Hidraulicna presa rm163
50000789	Hidraulicna presa rm164
50000790	Nosac statora za namotavanje 31
50000791	Nosac statora za namotavanje 32
50000792	Nosac statora za namotavanje 57
50000793	Nosac statora za namotavanje 58
50000794	Nosac statora za namotavanje 59
50000795	Nosac statora za namotavanje 60
50000796	Nosac statora za namotavanje 30
50000797	Hidraulicna presa rm161
50000798	Nosac statora za namotavanje 46
50000799	Nosac statora za namotavanje 47
50000800	Nosac statora za namotavanje 48
50000801	Nosac statora za namotavanje 49
50000802	Nosac statora za namotavanje 50
50000803	Nosac statora za namotavanje 51
50000804	Nosac statora za namotavanje 52
50000806	Hidraulicna presa rm165
50000807	Hidraulicna presa rm166
50000813	Uredjaj za razvlacenje i pozicioniranje spulne
50000815	Uredjaj za savijanje krajeva namotaja DDW
50000816	Masina za ciscenje namotaja EMT 1005001
50000817	Postrojenje za impregnaciju sa vakumom i pritiskom
50000817	Impregnacioni sud za NG5 DDW segment generatora
50000817	Huebers prosireni sistem za prihvatanje 2 DDW segmenta
50000819	Masina-uredjaj za razvlacenje i pozic. spulne NG5
50000822	Masina za secenje
50000824	Uredjaj za savijanje glave namotaja NG5-DDW
50000824	Uredjaj za savijanje glave nam. NG5-DDW - del.za BE2265
50000834	Pec za polimerizaciju DDW segmenta

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

50000835	Pec za polimerizaciju DDW segmenta
50000844	Cetvorost. hidraul.uredjaj za presovanje limpaketa
50000852	Dizel agregat ADG 132 C Comfort
50000859	Uredjaj za presovanje protofer mase u utor statora
50000861	Masina za namotavanja DDW namotaja mod.Selekta 245
50000862	Masina za namotavanja DDW namotaja mod.Selekta 245
50000889	Postrojenje za predzagrev. i polimer.DDW stat.seg.
50000890	Postrojenje za predzagrev. i polimer.DDW stat.seg.
50000891	Postrojenje za predzagrev. i polimer.DDW stat.seg.
50000892	Postrojenje za predzagrev. i polimer.DDW stat.seg.
50000901	Cetverostubni hidraulicni uredj.za presov.limp.DD
50000902	Cetverostubni hidraulicni uredj.za presov.limp.DD
50000916	VPI-Postrojenje za impregnaciju DD stator. segmen.
50000917	Stalak za okretanje limpaketa statora
50000923	Postrojenje za peskarenje DDW statorskih segmenata
50000924	Masina za namotavanje DDW namotaja
50000925	Masina za namotavanje DDW namotaja
50000952	Srednje frekventni spec.aparat za tackasto zavar.
50000960	Postrojenje za farbanje i susenje DDW stat. segm.
50000969	Masina za indukciono zavarivanje MFG150
50000976	Obradni centar za glodanje i busenje
50000980	Masina za secenje i savijanje utorne izolacije
50001019	Masina za graviranje natpisnih tablica
50001052	Masina za bandaziranje
50001066	Masina za savijanje utorne izolacije K 080x040x040
50001067	Masina za savijanje utorne izolacije K 080x040x040
50001084	Elektricna masina za vucu Baka EGZ 20
50001085	Elektricna masina za vucu Baka EGZ 20
50001101	Univerzalna masina za savijanje glave DDW namotaja
50001135	Masina za namotavanje DDW namotaja
50001136	Masina za namotavanje DDW namotaja
50001187	Postrojenje za farbanje i susenje DDW stat. segm.
50001188	Postrojenje za farbanje i susenje ddw stat. segm.
50001265	Pec za polimerizaciju DDW segmenata
50001266	Pec za susenje farb. rot. i stat. sa protof. SF31
50001271	Pec za polimerizaciju DDW segmenata
50001290	Mašina za savijanje, razvlačenje i formiranje namo
50001300	Mašina za namotavanje DDW namotaja Selekt 245
50001314	Peć za zagrevanje kućišta generatora SF-34-H
50001330	Univerzalna masina za savijanje glave DDW namotaja
50001332	Univerzalna masina za savijanje glave DDW namotaja

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

50001333	Univerzalna masina za savijanje glave DDW namotaja
50001353	Peć za sušenje generatora D-KT 38/2-2
50001354	Kabina za pripremu generatora za farbanje D-VK 16
50001356	Peć za polimerizaciju DDW segmenta
50001357	Peć za polimerizaciju DDW segmenta
50001380	Mašina za savij. i ravnanje krajeva namot.statora
50001396	Weiler bušilica VOM 50 sa okretljivim stolom
50001401	Mašina za tačkasto zavarivanje PMP6-2/100MF
50001413	Uređaj za tačkasto označavanje Markator
50001414	Uređaj za tačkasto označavanje Markator
50001420	Glava pneumatske blankerice
50001421	Glava pneumatske blankerice
50001422	Glava pneumatske blankerice
50001423	Glava pneumatske blankerice
50001424	Uređaj za ispitivanje udara na limpaketima i osovi
50001426	VPI Sistem za impregnaciju segmenata
50001426	VPI Sistem za impregnaciju segmenata upgade
50001431	Mašina za namotavanje Selektta 245, srednji šablon
50001432	Mašina za namotavanje Selektta 245, srednji šablon
50001433	VPI Sistem za impregnaciju Traction DDW
50001434	Radijalna bušilica MAS/CSFR VO 50 (bela bušilica)
50001436	2-K sistem za mešanje Cyclomix Multi
50001438	Mašina za balansiranje HM60U
50001439	2-K sistem za mešanje Cyclomix Multi
50001440	Hidraulična presa tip 456
50001442	Hidraulična presa
50001444	Mašina za balansiranje
50001445	Hidraulična presa
50001446	Masina za namotavanje namotaja
50001446	Masina za namotavanje namotaja
50001448	Masina za graviranje natpisnih tablica
50001449	Mašina za balansiranje HM7U
50001456	Ispitni sto sa pretvaračem za serijsko ispitivanje
50001457	Mašina za udružno i poprečno sečenje izolacionog m
50001463	Kabina za peskarenje PressoBlast3 HD
50001464	Mašina za sečenje Labotom 15
50001465	Mašina za poliranje Labopol 30
50001466	Testera trakasta S350 DG
50001467	Trakasta testera ARG 300 Plus F
50001468	Hidraulicna masina za razvlacenje namota
50001469	ABUS stubski kran VS 2000kg/5000mm/VS558

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

50001470	ABUS stubski kran VS 2000kg/6000mm/VS558
50001471	Presa za namotaje 458-2500-061
50001472	Udarne makaze za sečenje izolacionog materijala
50001473	Dvogredna mosna dizalica nosivosti 3200 kg
50001480	Univerzalni strug
50001481	Mašina za žljeb i pofiliranje
50001482	Univerzalni strug 900x380 KERN
50001483	Digitalni pozicionirač
50001486	Preklopna presa sa dodatkom
50001487	Hidraulična presa
50001502	Presa za namotaje GROSS
50001505	Gasna grejna komora BALZER Type KLG
50001506	Stubni kran
50001507	Zidni kran
50001510	Brusilica AKU ETSC 125/3
50001511	Usisivač CTM 26 E Cleantec
50001514	Mašina za izolovanje namotaja
50001515	Presa za namotaje sa duzinom metala do 1500 mm
50001516	Presa za namotaje sa duzinom metala do 1500 mm
50001517	Hidraulicna visespratnapresa Model S32
50001518	Masina za izoliranje namotaja Mi338-3000
50001518	Masina za izoliranje namotaja Mi338-3000
50001519	Hidraulicna masina za razvlacenje namotaja 2015-2P
50001521	Masina za namotavanje namotaja C / H: 245-029
50001524	Masina za izoliranje namotaja Ridgeway B
50001525	Oprema za lemljenje - Optorno
50001526	Oprema za lemljenje - Induktivno
50001527	Oprema za lemljenje - Induktivno
50001529	C kuka 1900 mm / 8t
50001530	Presa za presovanje namotaja - delovi
50001531	Uredaj za ispitivanje impulsnim naponom
50001532	Abus stubni kran 2 t
50001534	Neprekidni izvor napajanja (UPS)
50001535	Senzor za vibraciju
50001536	Senzor za vibraciju
50001537	Senzor za vibraciju
50001538	Senzor za vibraciju
50001540	Masina za namotavanje namotaja Selekt 245
50001541	Mašina za izolovanje namotaja Micamation MI-339
50001542	Klimatizacioni sistem u cistoj sobi
50001544	Vertikalni strug Dörries VCE2400/220SM, SN: V-8002

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

50001553	Kabina za farbanje Durst
50001554	Oprema za električno testiranje
50001555	Oprema za električno testiranje
50001556	Oprema za električno testiranje i ulaganje namotaj
50001557	Oprema za električno testiranje, delovi ćelije
50001558	Oprema za električno testiranje, delovi ćelije
50001559	Oprema za električno testiranje, delovi ćelije
50001560	Oprema za električno testiranje
50001561	Komplet opreme za indukciono lemljenje
50001562	Komplet opreme za indukciono lemljenje
50001563	Komplet opreme za indukciono lemljenje
50001564	Strothmann kolica/nosač
50001565	Strothmann kolica/nosač
50001566	Strothmann kolica/nosač
50001567	Strothmann kolica/nosač
50001568	Strothmann kolica/nosač
50001569	Strothmann kolica/nosač
50001570	Strothmann kolica/nosač
50001571	Strothmann kolica/nosač
50001572	Strothmann kolica/nosač
50001573	Oprema za rotiranje segmenta
50001574	Oprema za rotiranje segmenta
50001575	Oprema za manipulaciju segmentima
50001576	Oprema za manipulaciju segmentima
50001577	Oprema za manipulaciju segmentima
50001578	Oprema za manipulaciju segmentima
50001579	Oprema za manipulaciju segmentima
50001580	Alat za kran (prihvat: H profil, manipulacija segm
50001581	Strothmann kolica/nosač
50001582	Alat za kran (manipulacija segmenta)
50001593	Masina za razvljacenje namotaja
50001594	Monforts CNC - 2 strug sa dve ose/RNC 700
50001596	Masina za indukciono zavarivanje Mico-S 18MFDA
50001597	Masina za indukciono zavarivanje Mico-S 18MFDA
50001598	Masina za indukciono zavarivanje Mico-S 18MFDA
50001611	Glodalica Alzmetall GS1000/5 br.36585
50001612	Masina za mesanje protofera F/N 2482
50001613	Mosna dizalica jednogredna 10t
50001614	Mosna dizalica jednogredna 10t
50001623	Mašina Alzmetall GS 1000_5
50000297	Delovi za balans masinu

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

50000326	Uredaj za doziranje dvokomponentnog araldita i far
50000362	Telo grejaca
50000363	Telo grejaca
50000364	Telo grejaca
50000365	Hibridni apsopcioni filter
50000369	Telo grejaca
50000370	Telo grejaca
50000371	Telo grejaca
50000375	Telo grejaca
50000376	Telo grejaca
50000377	Telo grejaca
50000378	Telo grejaca
50000379	Telo grejaca
50000380	Telo grejaca
50000381	Telo grejaca
50000382	Telo grejaca
50000383	Telo grejaca
50000384	Telo grejaca
50000389	Aparat za testiranje namotaja za visoki napon
50000390	Merac za merenje unutrasnjeg precnika otvora kucis
50000391	Merac za merenje unutrasnjeg precnika otvora kucis
50000392	Merac za merenje unutrasnjeg precnika otvora kucis
50000394	Telo grejaca
50000395	Telo grejaca
50000396	Telo grejaca
50000397	Telo grejaca
50000398	Telo grejaca
50000399	Telo grejaca
50000400	Telo grejaca
50000401	Telo grejaca
50000402	Telo grejaca
50000403	Telo grejaca
50000404	Telo grejaca
50000405	Telo grejaca
50000406	Telo grejaca
50000407	Telo grejaca
50000410	Grejac za predgrevanje namotaja sa postoljem
50000419	Aparat za varenje za novu balans masinu
50000421	Razvodni orman sa alatima za veliku balans masinu
50000425	Visokofrekventni uredaj za ispitivanje izolacije
50000453	Telo grejaca 950

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

50000454	Telo grejaca 950
50000455	Telo grejaca 900
50000456	Telo grejaca 900
50000457	Telo grejaca 850
50000458	Telo grejaca 850
50000459	Telo grejaca 800
50000460	Telo grejaca 800
50000479	Grejac balansn. ploce
50000493	Rotacioni kompresor typ:ac18h
50000503	Telo grejaca 950-125
50000504	Telo grejaca 950-126
50000505	Telo grejaca 950-127
50000506	Telo grejaca 950-128
50000507	Telo grejaca
50000508	Telo grejaca
50000509	Telo grejaca
50000510	Telo grejaca
50000558	Aparat za zavarivanje citronix tig-400a-dc
50000569	Aparat za zavarivanje citronix tig-400a-dc
50000583	Vibrometar
50000631	Ispitni uredaj za vis. napon.merenje
50000658	Telo grejaca
50000659	Telo grejaca
50000660	Telo grejaca
50000661	Telo grejaca
50000662	Telo grejaca
50000663	Telo grejaca
50000664	Telo grejaca
50000665	Telo grejaca
50000666	Telo grejaca
50000667	Telo grejaca
50000668	Telo grejaca
50000669	Telo grejaca 1200*89*45
50000670	Telo grejaca 1200*89*45
50000671	Telo grejaca 1200*89*45
50000672	Telo grejaca 1200*89*45
50000673	Telo grejaca
50000674	Telo grejaca
50000675	Telo grejaca
50000676	Telo grejaca
50000677	Telo grejaca

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

50000678	Telo grejaca
50000679	Telo grejaca
50000680	Telo grejaca
50000681	Telo grejaca
50000682	Telo grejaca
50000683	Industrijski usisivac keper
50000684	Industrijski usisivac keper
50000685	Telo grejaca
50000686	Telo grejaca
50000687	Telo grejaca
50000688	Telo grejaca
50000689	Telo grejaca
50000690	Telo grejaca
50000691	Telo grejaca
50000692	Telo grejaca
50000693	Telo grejaca
50000694	Telo grejaca
50000695	Telo grejaca
50000696	Telo grejaca
50000697	Telo grejaca
50000698	Telo grejaca
50000699	Telo grejaca
50000700	Telo grejaca
50000703	Rucni digitalni obrtomer
50000704	Schalalnalysator
50000821	Sistem za merenje temperature i vlage na liniji F
50000827	Kada za impregnaciju namotaja rotora i statora
50000829	Multimetar Metrahit27m
50000830	Multimetar Metrahit27m
50000833	Aparat za zavarivanje Citronix 400 Mig-Mag kompakt
50000843	Industrijski grejac TIH 220M/MV
50000845	Laserski uredjaj za mer. oblika i poloz.segm. DDW
50000846	Mig-Mag aparat za impulsno zavar.nosaca DDW seg.
50000847	Mig-Mag aparat za impulsno zavar.nosaca DDW seg.
50000848	Razvodni orman 201 u lim.kuc. sa prip.kabl.-Hala 2
50000849	Razvodni orman 202 u lim.kuc. sa prip.kabl.-Hala 2
50000853	Instrument za mer. vremena zeliranja smole za DDW
50000854	Sistem za kontrolu pristupa SiePass
50000855	Elektro-magnet za podizanje DDW segmenta
50000856	Sprava za dizanje lezaja pri zagrevanju
50000867	Aparat za impulsno zavarivanje Phonix 351Puls DW

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

50000868	Aparat za impulsno zavarivanje Phonix 351Puls DW
50000872	Merni uredjaj Fluke CableIQ
50000876	Uredjaj za razvlacenje i pozicion. spulne DDW-NG2
50000879	Strug za obradu metala sa siljcima
50000888	Uredjaj za savijanje glave namotaja DDW NG2
50000897	Impregnaciona kada
50000904	Aparat za impulsivno zavarivanje Phonix351 Puls DW
50000905	Uredjaj za susenje izolacionih materijala FD 115
50000918	Uredjaj za podmazivanje struga masine pri radu
50000928	Hidraulicna presa Maxico 10-M
50000929	Hidraulicna presa Maxico 10-M
50000936	Hidraulicna presa Maxico 10-M
50000946	Uredjaj za prevrtanje DDW segmenata
50000947	Internet hot-spot sistem
50000948	Elektricni uredjaj za secenje izolacionog materij.
50000951	Uredjaj za rucno skidanje izolacije Karcher TTE301
50000954	Projektor Panasonic PT-LX26HE
50000955	Uredjaj za sortiranje lima
50000961	Orman-uredjaj za susenje izolacionih materijala
50000962	Uredjaj za prevrtanje DDW segmenata
50000965	Mig-Mag mobilni impulsni aparat za zavarivanje
50000966	Masina za secenje izolacionog materijala K500
50000967	Mig-Mag mobilni impulsni aparat za zavarivanje
50001021	Tracna brusilica sa postoljem i ruckom
50001025	Mig-Mag mobilni impulsni aparat za zavarivanje
50001026	Mig-Mag mobilni impulsni aparat za zavarivanje
50001040	Mig-Mag aparat za zavarivanje Phonix 351Puls DW
50001041	Mig-Mag aparat za zavarivanje Phonix 351Puls DW
50001042	Mig-Mag aparat za zavarivanje Phonix 351Puls DW
50001050	Rucni hidraulicni alat za ravn. i savij. namotaja
50001051	Uredjaj za secene izolacionog materijala RGM
50001053	Pneum.uredjaj za presovanje-form.glave namot.DD22
50001054	Dvokomponentni uredjaj za mesanje farbe PU3000
50001055	Dvokomponentni uredjaj za mesanje farbe PU3000
50001056	Dvokomponentni uredjaj za mesanje farbe PU3000
50001057	Pec za zagrevanje lim paketa rotora S32
50001069	Pneumatski uredjaj sa cilindrom fi 125, DD22, DD64
50001070	Pneumatski uredjaj sa cilindrom fi 125, DD22, DD64
50001072	Presa za wg proizvodnju statora i rotora
50001097	KRAUS Specijalni sto za podizanje DD segmenata
50001100	Uredjaj za rastezanje i pozicioniranje namotaja

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

50001116	Cetvorostubni hidraulični uređaj za presovanje
50001117	Srednje-frekventni spec. aparat za tac.zavarivanje
50001119	Portabilni uređaj za uklanjanje slomljenog alata
50001121	Postrojenje za peskarenje ddw statorskih segmenata
50001127	Uređaj za ostrenje burgija 3-40mm
50001137	Kraus specijalni sto za podizanje DD segmenta
50001138	Kraus specijalni sto za podizanje DD segmenta
50001139	Kraus specijalni sto za podizanje DD segmenta
50001140	Kraus specijalni sto za podizanje DD segmenta
50001141	Kraus specijalni sto za podizanje DD segmenta
50001142	Kraus specijalni sto za podizanje DD segmenta
50001143	Kraus specijalni sto za podizanje DD segmenta
50001144	Kraus specijalni sto za podizanje DD segmenta
50001145	Kraus specijalni sto za podizanje DD segmenta
50001146	Kraus specijalni sto za podizanje DD segmenta
50001147	Kraus specijalni sto za podizanje DD segmenta
50001148	Kraus specijalni sto za podizanje DD segmenta
50001153	Uređaj za zavarivanje MIG/MAG
50001154	Uređaj za zavarivanje MIG/MAG
50001155	Uređaj za zavarivanje MIG/MAG
50001156	Uređaj za zavarivanje MIG/MAG
50001157	Uređaj za zavarivanje MIG/MAG
50001158	Uređaj za zavarivanje MIG/MAG
50001159	Uređaj za zavarivanje MIG/MAG
50001164	Hidrocilindar sa pumpom za svlačenje ležaja
50001165	Uređaj za zavarivanje
50001166	Uređaj za zavarivanje
50001167	Uređaj za zavarivanje
50001170	Uređaj za zavarivanje MIG/MAG
50001171	Uređaj za zavarivanje MIG/MAG
50001172	Uređaj za zavarivanje MIG/MAG
50001173	Uređaj za zavarivanje MIG/MAG
50001174	Uređaj za zavarivanje MIG/MAG
50001177	Uređaj za zavarivanje TIG
50001178	Uređaj za zavarivanje TIG
50001179	Uređaj za zavarivanje TIG
50001185	Uređaj za sečenje izolacionog materijala RGM2050-3
50001186	Supra dvostubna dizalica Consul 2.35
50001205	Stona bušilica Alzotronic sa prikazom dub. provrta
50001219	Akumulatorska hidraulična presa Weitkowitz AP10
50001220	Akumulatorska hidraulična presa Weitkowitz AP10

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

50001221	Akumulatorska hidraulična presa Weitkowitz AP10
50001222	Akumulatorska hidraulična presa Weitkowitz AP10
50001226	Akumulatorska hidraulična presa Weitkowitz AP10
50001227	Akumulatorska hidraulična presa Weitkowitz AP10
50001228	Akumulatorska hidraulična presa Weitkowitz AP10
50001229	Akumulatorska hidraulična presa Weitkowitz AP10
50001230	Akumulatorska hidraulična presa Weitkowitz AP10
50001238	Uređaj za zavarivanje Citronix TIG 500 A DC 5-500A
50001239	Uređaj za zavarivanje MIG/MAG Lorch S8 Standard
50001240	Uređaj za zavarivanje MIG/MAG Lorch S8 Standard
50001241	Uređaj za zavarivanje MIG/MAG Lorch S8 Standard
50001242	Uređaj za zavarivanje MIG/MAG Lorch S8 Standard
50001243	Uređaj za zavarivanje MIG/MAG Lorch S8 Standard
50001247	Aparat za zavarivanje Citronix MMA-REL 350A
50001248	Aparat za zavarivanje Citronix 400 Mig Mag
50001258	Uređaj za sečenje izolacionog materijala RGM
50001273	Sto za podizanje ddw segmenta 6t
50001281	Hidrocilindar sa pumpom Enerpac
50001282	Mašina za sečenje bužira
50001284	Aparat za zavarivanje TIG 500A-DC
50001285	Aparat za zavarivanje TIG 500A-DC
50001302	Uređaj za ručno skidanje izolacije
50001303	Uređaj za ručno skidanje izolacije
50001304	Uređaj za ručno skidanje izolacije
50001317	Mešać farbe komplet PU 3000 Airmix
50001318	Hidraulični sto Flachformhühtisch U-oblik TUL 2000
50001321	Hidraulični sto Flachformhühtisch U-oblik TUL 2000
50001325	Hidraulične makaze za sečenje bakra HB 2 V Alarm
50001326	Hidraulične makaze za sečenje bakra HB 2 V Alarm
50001327	Hidraulične makaze za sečenje bakra HB 2 V Alarm
50001328	Hidraulične makaze za sečenje bakra HB 2 V Alarm
50001334	Univerzalni uređaj za rastezanje i pozicioniranje
50001335	Uređaj za okretanje statora Neumuller
50001337	Dvokomponentni uređaj za mešanje farbe PU3000 Airm
50001338	Dvokomponentni uređaj za mešanje farbe PU3000 Airm
50001339	Dvokomponentni uređaj za mešanje farbe PU3000 Airm
50001340	Dvokomponentni uređaj za mešanje farbe PU3000 Airm
50001341	Dvostubna dizalica Consul 2.35 Premium
50001342	Sto za podizanje ddw segmenta 7t
50001343	Sto za podizanje ddw segmenta 7t
50001344	Sto za podizanje ddw segmenta 7t

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

50001345	Sto za podizanje ddw segmenta 7t
50001346	Sto za podizanje ddw segmenta 7t
50001347	Sto za podizanje ddw segmenta 7t
50001348	Sto za podizanje ddw segmenta 7t
50001349	Sto za podizanje ddw segmenta 7t
50001350	Sto za podizanje ddw segmenta 7t
50001358	TIG aparat za zavarivanje Tetrix 351
50001359	TIG aparat za zavarivanje Tetrix 351
50001360	TIG aparat za zavarivanje Tetrix 351
50001361	TIG aparat za zavarivanje Tetrix 351
50001362	TIG aparat za zavarivanje Tetrix 351
50001363	MIG/MAG aparat za zavarivanje Alpha Q 351
50001364	MIG/MAG aparat za zavarivanje Alpha Q 351
50001365	MIG/MAG aparat za zavarivanje Alpha Q 351
50001368	Magnetni uređaj za podizanje i transport segmenata
50001373	Pumpa za tečnost drum angel mod 35011S
50001381	Magnetna bušilica BDS Maschinen MAB 825 1800W
50001384	Uređaj za zavarivanje S8 SpeedPulse-XT 500 BW
50001385	Uređaj za zavarivanje S8 SpeedPulse-XT 500 BW
50001386	Uređaj za zavarivanje S8 SpeedPulse-XT 500 BW
50001387	Uređaj za zavarivanje S8 SpeedPulse-XT 500 BW
50001389	Mala hidraulična presa
50001390	Mala hidraulična presa
50001391	Mala hidraulična presa
50001392	Velika hidraulična presa
50001393	Velika hidraulična presa
50001394	Velika hidraulična presa
50001395	Velika hidraulična presa
50001406	Uređaj za mešanje farbe D50 ST 16C
50001407	Presa za skidanje alata sa lim paketa statora
50001408	Ručni hidraulični uređaj za ravnanje i savijanje
50001409	Ručni hidraulični uređaj za ravnanje i savijanje
50001410	Univerzalni uređaj za rastezanje i pozic.namotaja
50001411	Univerzalni uređaj za rastezanje i pozic.namotaja
50001412	Faro merna ruka sa bluetooth tehnologijom
50001450	Mosna dizalica (kran)
50001451	Mosna dizalica (kran)
50001452	Dodatni kranski most
50001453	Nadogradjeni kranski most 10t
50001454	Obnova i produženje krana 3,2T
50001484	Ručna mašina za peskarenje Typ Problast 60 SV

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

50001485	Kopresor za snabdevanje pogonskih mašina vazduhom
50001501	Induktivna oprema za lemljenje MICO-M 30
50001503	Induktor za klešta za lemljenje 21 * 14 sa kontrom
50001504	Induktor za klešta za lemljenje 21 * 14 sa kontrom
50001513	Uređaj za varenje vakum vreća
50001583	Strothmann mašina za automatsko pakovanje limova
50001584	Schumann masina za izradu namotaja
50001587	Schumann masina za izradu namotaja
50001590	Presa za pakovanje DD segmenata
50001591	Kada za VPI
50001592	Sistem za farbanje Graco XP50 sa mešaćem
50001595	Alat-pistolj za pranje Oltrogge, Bielefeld
50001599	Kada za impregnacioni sistem Hubers
50001602	Komora za brušenje
50001603	Monitoring prese za limove na statoru
50001604	Monitoring prese za limove na statoru
50001606	Monitoring prese za limove na statoru
50001607	Shumann mašina za savijanje glava namotaja
50001608	Kran za manipulaciju namotajima Erfurt
50001609	Shumann mašina za savijanje glava namotaja
50001610	Kran za manipulaciju namotajima Erfurt
50001615	Kada za impregnaciju za DD9 segmente za VPI 3 sist
50001618	Neutralizator emisije štetnih materija RTO
61100125	Teretno vozilo Skoda RoomsterPraktik1.4 BG-210-NV
61100136	Autoprikolica Stema M/AN750OE reg. AČ-563-BG
61100220	Skoda Octavia A7 Ambition 1.6TDI reg. BG 795-TU
61100241	Skoda Octavia A7 reg. BG 901-LČ
61100242	Skoda Octavia A7 Ambition 2.0 reg. BG 901-LČ
61100248	Skoda Octavia A7 Ambition 2.0TDI CR 110kw BG924 BT
61100260	Škoda Octavia A7 Style 1.6 TDI reg. BG 1031-GJ
61100261	Škoda Octavia A7 Style 1.6 TDI reg. BG 1031-GH
61100262	ASTRA K enjoy ST B16DTH reg. BG 1035-XC
61100274	Regalni viljuskar Linde R25S S/N:SYSF003963
61100275	Škoda Octavia A7 Style 1.6 TDI reg. BG 1140-RF
61100329	Skoda Octavia A7 Style 1.6 TDI BG1786-CS DGTA21709
61100330	Skoda Octavia A7 Style 1.6 TDI BG1786-CX DGTA21795
61100335	VW Tiguan Highline Dizel 2.0 TDI BG 1852 XE
61400002	Vucno vozilo Linde P50C sa 30 prikolica
61400003	Viljuskar H 80 D 8,0t, izvedba 396-00
61400004	Viljuskar H 160 D/1200 16,0t - Izvedba 1401-00
61400005	Viljuskar na elektricni pogon, Linde R20

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

61400006	Viljuškar na električni pogon, Linde R20
61400011	Viljuškar na elektromotorni pogon, Linde E50/600HL
61400012	Viljuškar na elektromotorni pogon, Linde E50/600HL
61400013	Elektro vučno vozilo Linde P250 sa punjacom
61400015	Dizel viljuškar Linde H 80 D /600
61400016	Viljuškar Still FM-X 25
61400017	Elektro skladišni viljuškar STILL FM-X 25
61400018	Elektro viljuškar STILL RX60-50
61400021	Elektro viljuškar Toyota s br. 8FBMT50-10798
61400022	Elektroviljuškar Toyota s b. 8FBMT50-10801
61400023	El.regalni viljuškar Toyota RRE250H s. b.6530708
61400024	El.regalni viljuškar Toyota RRE250H s. b.6531034
61400026	Elektro viljuškar STILL RX 60-80, serijski br.5163
61400027	Baka viljuškar 8t EGU8000 (d.v.1500mm) 33560
61400028	Baka viljuškar 8t EGU8000(d.v.1800mm) br.33561
61400029	Viljuškar STILL RX60-50, 80V Elektro
61400030	Viljuškar STILL FM-X25, 48V Elektro
61400031	Viljuškar STILL, model RX60-80
62100004	Mobilni telefon Iphone 11 128gb black1
62201196	Hp desktop dc7600 p4 630
62201200	Hp procure
62201201	Hp procure
62201202	Hp procure
62201203	Hp procure
62201204	Hp procure
62201205	Hp procure
62201206	Hp procure
62201207	Hp procure
62201208	Hp procure
62201209	Hp procure
62201210	Hp procure
62201211	Hp procure
62201213	Hp destop dc5100
62201214	Hp destop dc5100
62201215	Hp destop dc5100
62201255	Lifebook FSC S710
62201278	Racunar MSI Windbox Atom N270 sa monitorom
62201280	Server Primergy RX300S6 Xeon 5620 6x3.5 gold PSU
62201283	Racunar MSI Windbox Atom N270 sa mon. i oper.sist.
62201299	Lifebook Celsius H700
62201326	Skener Fujitsu fi-6130

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

62201358	Lifebook FSC S751
62201359	Lifebook FSC S751
62201361	Skener Fujitsu 600dpi, fi-6130
62201362	Skener Fujitsu 600dpi, fi-6130
62201377	Lifebook S751
62201387	Lifebook S751
62201389	Lifebook S751
62201390	Lifebook S751
62201393	Lifebook S751
62201394	Lifebook S751
62201395	Lifebook S751
62201398	Lifebook S751
62201402	Fujitsu Lifebook E751
62201406	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201407	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201408	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201409	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201410	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201413	Lifebook S751
62201415	Lifebook S751
62201416	Lifebook S751
62201417	Lifebook S751
62201421	Lifebook E751
62201422	Lifebook E751
62201423	Lifebook E751
62201424	Fujitsu Lifebook E751
62201425	Lifebook S751
62201429	Lifebook S751
62201433	Lifebook S751
62201436	Lifebook E751
62201440	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201441	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201442	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201443	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201444	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201445	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201446	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201447	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201448	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201449	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201468	Lifebook FTS S751

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

62201469	Lifebook FTS S751
62201470	Lifebook FTS E751
62201473	Lifebook FTS E751
62201475	Lifebook S751
62201477	Lifebook S751
62201478	Lifebook S751
62201481	Lifebook S751
62201482	Lifebook S751
62201484	Lifebook E751
62201485	Lifebook E751
62201488	Lifebook E751
62201490	Notebook Fujitsu Celsius H910
62201496	Desktop racunar Dell OpiPlex 390DT sa monitorom
62201498	Lifebook S752
62201500	Lifebook S752
62201506	Lifebook S752
62201508	Lifebook E752
62201511	Lifebook E752
62201514	Desktop Fujitsu Celsius R920
62201515	Desktop Fujitsu Celsius R920
62201516	Desktop Fujitsu Celsius R920
62201517	Notebook Fujitsu Celsius H720
62201518	Notebook Fujitsu Celsius H720
62201519	Notebook Fujitsu Celsius H720
62201520	Notebook Fujitsu Celsius H720
62201523	Notebook Fujitsu S752
62201529	Notebook Fujitsu S752
62201530	Notebook Fujitsu S752
62201532	Notebook Fujitsu S752
62201533	Notebook Fujitsu S752
62201534	Notebook Fujitsu S752
62201535	Notebook Fujitsu S752
62201536	Notebook Fujitsu S752
62201537	Notebook Fujitsu S752
62201538	Notebook Fujitsu S752
62201540	Notebook Fujitsu E752
62201541	Notebook Fujitsu E752
62201544	Skener Fujitsu fi-6130Z
62201545	Infopult ELO 3200L racunar sa stalkom Inox
62201547	Notebook Fujitsu Celsius H910
62201548	Lifebook FTS S752

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

62201550	Lifebook FTS S752
62201552	Lifebook FTS S752
62201557	Lifebook FTS S752
62201561	Lifebook FTS S752
62201564	Lifebook FTS S752
62201566	Lifebook FTS S752
62201568	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201569	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201570	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201571	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201572	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201573	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201574	Racunar MSI Windbox II Atom N270 sa monitorom 17"
62201605	Lifebook S752
62201606	Lifebook S752
62201607	Lifebook S752
62201608	Lifebook S752
62201609	Lifebook S752
62201610	Lifebook S752
62201611	Lifebook S752
62201612	Lifebook S752
62201613	Lifebook S752
62201630	Desktop Fujitsu Celsius R920
62201631	Notebook Fujitsu Celsius H720
62201632	Notebook Fujitsu Celsius H720
62201651	Notebook Fujitsu Celsius H720
62201659	Desktop Fujitsu Celsius R920
62201660	Stampac HP Designjet T520 36" ploter A0
62201661	Stampac HP Designjet T520 24" ploter A1
62201664	Notebook Fujitsu Celsius H720
62201665	Desktop Fujitsu Celsius R920
62201666	Notebook Fujitsu Celsius H720
62201669	Notebook Fujitsu Celsius H920
62201670	Notebook Fujitsu Celsius R930
62201671	Notebook Fujitsu Celsius R930
62201672	Notebook Fujitsu Celsius R930
62201673	Notebook Fujitsu Celsius R930
62201675	Termopreslikavajući stampac za materijal u rolni
62201679	Racunar MSI Windbox II Atom 1,6GHz sa monitorom
62201680	Racunar MSI Windbox II Atom 1,6GHz sa monitorom
62201681	Racunar MSI Windbox II Atom 1,6GHz sa monitorom

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

62201682	Racunar MSI Windbox II Atom 1,6GHz sa monitorom
62201683	Racunar MSI Windbox II Atom 1,6GHz sa monitorom
62201684	Racunar MSI Windbox II Atom 1,6GHz sa monitorom
62201685	Racunar MSI Windbox II Atom 1,6GHz sa monitorom
62201686	Skener Fujitsu fi-5530C2
62201687	Racunar MSI Windbox II Atom 1,6GHz sa monitorom
62201688	Racunar MSI Windbox II Atom 1,6GHz sa monitorom
62201689	Racunar MSI Windbox II Atom 1,6GHz sa monitorom
62201690	Termostampac za kartasti materijal Phonix contact
62201700	Tablet mobilni telefon Samsung Galaxy Note P901
62201703	Tablet mobilni telefon Samsung Galaxy Note
62201704	Tablet racunar Samsung Galaxy Note SM-P901
62201706	Tablet mobilni telefon Samsung Galaxy Note
62201707	Notebook racunar Dell Precision M6800
62201708	Notebook racunar Dell Precision M6800
62201721	Laptop računar - Fujitsu Lifebook E744
62201722	Lifebook E744
62201723	Lifebook E744
62201724	Lifebook E744
62201726	Lifebook E744
62201727	Lifebook E744
62201728	Lifebook E744
62201729	Lifebook E744
62201730	Lifebook E744
62201731	Notebook Fujitsu Celsius H730
62201732	Desktop racunar Fujitsu Celsius M730
62201733	Desktop racunar Fujitsu Celsius M730
62201734	Desktop racunar Fujitsu Celsius M730
62201735	Desktop racunar Fujitsu Celsius M730
62201736	Desktop racunar Fujitsu Celsius M730
62201737	Desktop racunar Fujitsu Celsius M730
62201738	Desktop racunar Fujitsu Celsius M730
62201739	Desktop racunar Fujitsu Celsius M730
62201740	Desktop racunar Fujitsu Celsius M730
62201741	Desktop racunar Fujitsu Celsius M730
62201742	Desktop racunar Fujitsu Celsius M730
62201764	Lifebook E744
62201765	Lifebook E744
62201766	Lifebook E744
62201767	Lifebook E744
62201768	Lifebook E744

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

62201769	Lifebook E744
62201770	Lifebook E744
62201771	Lifebook E744
62201772	Lifebook E744
62201773	Lifebook E744
62201774	Lifebook E744
62201779	Lifebook E752
62201780	Lifebook E752
62201781	Štampač Zebra ZT230 D,dpi GP
62201792	Prenosni računar Lifebook S935
62201793	Prenosni računar lifebook E734
62201794	Prenosni računar lifebook E734
62201795	Fujitsu Lifebook E734
62201796	Fujitsu Lifebook E734
62201797	Fujitsu Lifebook E734
62201798	Fujitsu Lifebook E734
62201799	Fujitsu Lifebook E734
62201800	Prenosni računar lifebook E734
62201801	Prenosni računar lifebook E734
62201802	Laptop računar - Fujitsu Lifebook E734
62201848	Prenosni racunar Li feBook E734
62201849	Prenosni racunar Li feBook E734
62201850	Prenosni racunar Li feBook E734
62201851	Prenosni racunar Li feBook E734
62201852	Prenosni racunar Li feBook E734
62201856	Prenosni računar FUJITSU Lifebook S936
62201859	Prenosni računar Celsius H730
62201860	Prenosni računar lifebook E736
62201861	Prenosni računar lifebook E736
62201863	Prenosni računar lifebook E736
62201864	Prenosni računar lifebook E736
62201865	Prenosni računar lifebook E736
62201867	Prenosni računar lifebook E736
62201868	Prenosni računar lifebook E736
62201869	Prenosni računar lifebook E736
62201875	Prenosni računar lifebook E736
62201876	Prenosni računar lifebook E736
62201877	Prenosni računar lifebook E736
62201878	Prenosni računar lifebook E736
62201879	Prenosni računar lifebook E736
62201880	Prenosni računar lifebook E736

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

62201881	Prenosni računar lifebook E736
62201882	Prenosni računar lifebook E736
62201883	Prenosni računar lifebook E736
62201884	Prenosni računar lifebook E736
62201887	Prenosni računar lifebook E736
62201888	Prenosni računar lifebook E736
62201889	Prenosni računar lifebook E736
62201896	Prenosni računar ProBook 640
62201899	Apple Ipad Air 2Cellular 128GB-Space Grey
62201914	Prenosni racunar lifebook E736
62201915	Prenosni racunar lifebook E736
62201916	Prenosni racunar lifebook E736
62201917	Prenosni racunar lifebook E736
62201918	Prenosni racunar lifebook E736
62201919	Prenosni racunar lifebook E736
62201920	Prenosni racunar lifebook E736
62201921	Prenosni racunar lifebook E736
62201927	Prenosni racunar lifebook E736
62201928	Prenosni racunar lifebook E736
62201938	Mobilni telefon Iphone 7
62201940	Notebook računar Celsius H760 SAG 15.6` FHD LED
62201941	Notebook računar Celsius H760 SAG 15.6` FHD LED
62201942	Notebook računar Celsius H760 SAG 15.6` FHD LED
62201943	Notebook računar Celsius H760 SAG 15.6` FHD LED
62201944	Notebook računar Celsius H760 SAG 15.6` FHD LED
62201945	Notebook računar Celsius H760 SAG 15.6` FHD LED
62201946	Notebook računar Celsius H760 SAG 15.6` FHD LED
62201947	Notebook računar Celsius H760 SAG 15.6` FHD LED
62201948	Notebook računar Celsius H760 SAG 15.6` FHD LED
62201949	Notebook računar Celsius H760 SAG 15.6` FHD LED
62201984	UPS 3UIEC 309 32A HV INTL KIT
62201985	UPS 3UIEC 309 32A HV INTL KIT
62201986	UPS 3UIEC 309 32A HV INTL KIT
62201989	Scanner Fujitsu fi-5530C2
62201990	Notebook racunar HP Probook 640 G2
62201993	Notebook racunar HP Probook 640 G2
62201994	Notebook racunar HP Probook 640 G2
62201995	Notebook racunar HP Probook 640 G2
62201996	Notebook racunar HP Probook 640 G2
62201997	Notebook racunar HP Probook 640 G2
62201998	Notebook racunar HP Probook 640 G2

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

62202000	Notebook racunar HP Probook 640 G2
62202001	Notebook racunar HP Probook 640 G2
62202010	Notebook racunar HP Probook 640 G2
62202015	Fujitsu fi-6130Z Workgroup Scanner
62202035	HP probook 640 G2
62202036	HP probook 640 G2
62202037	HP probook 640 G2
62202038	HP probook 640 G2
62202039	HP probook 640 G2
62202040	HP probook 640 G2
62202041	HP probook 640 G2
62202042	HP probook 640 G2
62202044	HP probook 640 G2
62202077	HP Probook 640 G2
62202078	HP Probook 640 G2
62202079	HP Probook 640 G2
62202080	HP Probook 640 G2
62202081	HP Probook 640 G2
62202082	HP Probook 640 G2
62202083	HP Probook 640 G2
62202084	HP Probook 640 G2
62202085	HP Probook 640 G2
62202086	HP Probook 640 G2
62202087	HP Probook 640 G2
62202088	HP Probook 640 G2
62202089	HP Probook 640 G2
62202090	HP Probook 640 G2
62202091	HP Probook 640 G2
62202092	HP Probook 640 G2
62202093	HP Probook 640 G2
62202094	HP Probook 640 G2
62202095	HP Probook 640 G2
62202103	Racunar HP Probook 640G2w/o ODD
62202104	Racunar HP Probook 640G2w/o ODD
62202105	Racunar HP Probook 640G2w/o ODD
62202106	Racunar HP Probook 640G2w/o ODD
62202107	Racunar HP Probook 640G2w/o ODD
62202132	Laptop racunar HP model ZBook 17 G3
62202133	Laptop racunar HP model ZBook 17 G3
62202134	Laptop racunar HP model ZBook 17 G3
62202135	Laptop racunar HP model ZBook 17 G3

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

62202136	Laptop racunar HP model ZBook 17 G3
62202137	Laptop racunar HP model ZBook 17 G3
62202138	Laptop racunar HP model ZBook 17 G3
62202139	Laptop racunar HP model ZBook 17 G3
62202140	WIN7 Probook 640 G2 (Variant 14", 8GB, 512GB SSD,
62202141	WIN7 Probook 640 G2 (Variant 14", 8GB, 512GB SSD,
62202142	WIN7 Probook 640 G2 (Variant 14", 8GB, 512GB SSD,
62202143	WIN7 Probook 640 G2 (Variant 14", 8GB, 512GB SSD,
62202144	WIN7 Probook 640 G2 (Variant 14", 8GB, 512GB SSD,
62202145	WIN7 Probook 640 G2 (Variant 14", 8GB, 512GB SSD,
62202146	WIN7 Probook 640 G2 (Variant 14", 8GB, 512GB SSD,
62202147	WIN7 Probook 640 G2 (Variant 14", 8GB, 512GB SSD,
62202148	WIN7 Probook 640 G2 (Variant 14", 8GB, 512GB SSD,
62202149	WIN7 Probook 640 G2 (Variant 14", 8GB, 512GB SSD,
62202150	WIN7 Probook 640 G2 (Variant 14", 8GB, 512GB SSD,
62202151	WIN7 Probook 640 G2 (Variant 14", 8GB, 512GB SSD,
62202176	Notebook racunar HP 650 G2
62202177	Ploter HP DesignJet T520 ePrinter 36" (edicija 201
62202178	Ploter HP DesignJet T520 ePrinter 36" (edicija 201
62202180	Racunar HP ZBook 15G4 i7
62202181	HP Elitebook 830 G5 4DU06E
62202225	WIN10 HP Zbook 17 G4
62202226	HP Zbook 15 G4
62202227	WIN10 HP Elitebook 830 G5
62202228	WIN10 HP Elitebook 830 G5
62202229	WIN10 HP Elitebook 830 G5
62202230	WIN10 HP Probook 640 G4
62202231	WIN10 HP Probook 640 G4
62202232	WIN10 HP Probook 640 G4
62202233	WIN10 HP Probook 640 G4
62202234	WIN10 HP Probook 640 G4
62202235	WIN10 HP Probook 640 G4
62202237	WIN10 HP Probook 640 G4
62202238	WIN10 HP Probook 640 G4
62202239	WIN10 HP Probook 640 G4
62202240	WIN10 HP Probook 640 G4
62202241	WIN10 HP Probook 640 G4
62202242	WIN10 HP Probook 640 G4
62202243	WIN10 HP Probook 640 G4
62202244	WIN10 HP Probook 640 G4
62202245	WIN10 HP Probook 640 G4

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

62202246	WIN10 HP Probook 640 G4
62202247	WIN10 HP Probook 640 G4
62202248	WIN10 HP Probook 640 G4
62202249	WIN10 HP Probook 640 G4
62202252	WIN10 HP Probook 640 G4
62202253	WIN10 HP Probook 640 G4
62202254	WIN10 HP Probook 640 G4
62202255	WIN10 HP Probook 640 G4
62202256	WIN10 HP Probook 640 G4
62202257	WIN10 HP Probook 640 G4
62202258	WIN10 HP Probook 640 G4
62202259	WIN10 HP Probook 640 G4
62202271	WIN10 HP Probook 640 G5
62202272	WIN10 HP Probook 640 G5
62202273	WIN10 HP Probook 640 G5
62202274	WIN10 HP Probook 640 G5
62202275	WIN10 HP Probook 640 G5
62202276	WIN10 HP Probook 640 G5
62202277	WIN10 HP Probook 640 G5
62202278	WIN10 HP Probook 640 G5
62202279	WIN10 HP Probook 640 G5
62202280	WIN10 HP Probook 640 G5
62202281	HP 17.3" TFT7600 G2 KVM Console Rac.Keyboard
62202295	HP Zbook 15 G5+Dock
62202299	5HE67EC, WIN10 HP Zbook 17 G5 and dock
62202300	5HE49EC, WIN10 HP Zbook 17 G5 and dock
62202301	4DU06EC, WIN10 HP Elitebook 830 G5
62202302	4DU06EC, WIN10 HP Elitebook 830 G5
62202338	MOBILE Workstation HP Zbook 17 G5+HP TB Dock G2230
62202339	MOBILE Workstation HP Zbook 17 G5+HP TB Dock G2230
62202340	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202341	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202342	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202343	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202344	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202345	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202346	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202347	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202348	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202349	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202350	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

62202351	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202352	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202353	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202354	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202355	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202356	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202357	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202358	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202359	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202360	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202361	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202362	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202363	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202364	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202365	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202366	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202367	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202368	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202369	WIN10 HP Probook 640 G4 + HP UltraSlim Dock 2013
62202372	5HE54EC WIN10 HP Zbook 15 G5+Memory+Dock G2 230W
62202373	5HE54EC WIN10 HP Zbook 15 G5+Memory+Dock G2 230W
62202374	5HE54EC WIN10 HP Zbook 15 G5+Memory+Dock G2 230W
62202422	WIN10 HP Probook 640 G4 Standard 14", 8GB, 512GB
62202423	WIN10 HP Probook 640 G4 Standard 14", 8GB, 512GB
62202424	WIN10 HP Probook 640 G4 Standard 14", 8GB, 512GB
62202425	WIN10 HP Probook 640 G4 Standard 14", 8GB, 512GB
62202426	WIN10 HP Probook 640 G4 Standard 14", 8GB, 512GB
62202427	WIN10 HP Probook 640 G4 Standard 14", 8GB, 512GB
62202428	WIN10 HP Probook 640 G4 Standard 14", 8GB, 512GB
62202429	WIN10 HP Probook 640 G4 Standard 14", 8GB, 512GB
62202430	WIN10 HP Probook 640 G4 Standard 14", 8GB, 512GB
62202431	WIN10 HP Probook 640 G4 Standard 14", 8GB, 512GB
62202432	MOBILE Workstation HPZbook 17G5 +HP TBDock G2 230W
62202433	MOBILE Workstation HPZbook 17G5 +HP TBDock G2 230W
62202434	MOBILE Workstation HPZbook 17G5 +HP TBDock G2 230W
62202435	MOBILE Workstation HPZbook 17G5 +HP TBDock G2 230W
62202436	MOBILE Workstation HPZbook 17G5 +HP TBDock G2 230W
62202437	WIN10 HP Elitebook 830 G5+UltraSlim Dock 2013
62202438	WIN10 HP Elitebook 830 G5+UltraSlim Dock 2013
62202439	5HE64EC WIN10 HP Zbook 15 G5 (Variant 15"),+Memory
62202466	HP Probook 640 G4 sa memorijom

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

62202468	HP Probook 640 G4 sa memorijom
62202472	Fujitsu skener fi-7160 A33AJ60716
62202473	5HE54EC WIN10 HP Zbook 15 G5
63000779	Nadzorno upravljacki sistem
63000780	Sistem za merenje nivoa vode u rezervoaru rashl. c
63000781	Nadzorni sistem
63000782	Akvic.sistem temp.sa 3 linija presa
63000783	Akvic.sistem temp.sa 3 linija presa
63000784	Akvic.sistem temp.sa 3 linija presa
63000788	Akvizionni softver pracenja potrosnje el. energij
63000851	Softver za mere.vrem.traj.proiz.proc.sa sig.kljuc.
63001018	PolyWorks Inspector Probing licenca za dimen. mer.
63001023	PolyWorks Inspector Probing licenca za dimen. mere
63001059	Softver za monitoring presa
63001081	Software DxSurveyor - CMEM 18-DXSURVSW
63001082	Software DxSurveyor - CMEM 18-DXSURVSW
63001083	Software DxSurveyor - CMEM 18-DXSURVSW
63001084	Software DxSurveyor - CMEM 18-DXSURVSW
63001089	Software DxSurveyor - CMEM 18-DXSURVSW
63001106	Baker mta
63001110	Softver Xnet Starter set
63001152	Postprocesor za FPT glodalicu
63000854	Backup uredjaj ET LT40
63000900	Server PY RX300S7, 8x2.5
63000901	Server PY RX300S7, 8x2.5
63000938	Server Primergy RX350S8
63000939	Server Primergy RX350S8
63000963	Server Proliant DL 160 Gen9
63000986	Server S26361-K1566-V401
63001015	S26361_K1566-V101 Server
63001066	NetApp.Storage-uredjaj za skladištenje podataka
63001067	Server za virtualizaciju (ESXi)
63001068	Server za virtualizaciju (ESXi)
63001076	PY RX2520 M4
63001077	Urtdjaj za Back up LT60S2KNXU
63001078	PY RX2530 M4 4x 3.5" Server
63001100	NetApplication disk shelf,12G,12X4TB
63000786	Oprema za telefonsku centralu
63000787	Oprema za telefonsku centralu
63000823	Cisci SW 2960 sa dva opt. modula
63000824	Cisci SW 2960 sa dva opt. modula

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

63000825	Cisci SW 2960 sa dva opt. modula
63000826	Cisci SW 2960 sa dva opt. modula
63000827	Cisci SW 2960 sa dva opt. modula
63000828	Cisci SW 2960 sa dva opt. modula
63000840	Switch Catalyst 2960
63000841	Switch Catalyst 2960
63000842	Switch Catalyst 2960
63000843	Switch Catalyst 2960
63000844	Switch Catalyst 2960
63000845	Switch Catalyst 2960
63000849	Telekomunikacioni sklop u Hali 2
63000868	Switch Cisco WS-C2960-24TC-L
63000869	Switch Cisco WS-C2960-24TC-L
63000870	Switch Cisco WS-C2960-24TC-L
63000871	Switch Cisco WS-C2960-24TC-L
63000872	Switch Cisco WS-C2960-24TC-L
63000878	Switch Cisco Catalyst 2960 sa dva opticka modula
63000882	Telefonska centrala HiPath 4000 V6 - Subotica
63000904	Ruter za enkripciju linkova Cisco 2921
63000910	Switch Catalyst 3750X12 Port GE SFP IP Base
63000911	Switch Catalyst 3750X12 Port GE SFP IP Base
63000912	Switch Catalyst 3750X24 Port Data IP Base
63000913	Switch Catalyst 3750X24 Port Data IP Base
63000922	Switch Cisco Catalyst WS-C2960X-24TD-L sa modulom
63000923	Switch Cisco Catalyst WS-C2960X-24TD-L sa modulom
63000924	Switch Cisco Catalyst WS-C2960X-24PD-L sa modulom
63000925	Switch Cisco Catalyst WS-C2960X-24PD-L sa modulom
63000926	Switch Cisco Catalyst WS-C2960X-24PD-L sa modulom
63000927	Switch Cisco Catalyst WS-C2960X-24PD-L sa modulom
63000931	Bazna stanica BS4, Hala 3
63000943	Switch Cisco Catalyst WS-C2960X-24PD-L
63000944	Switch Cisco Catalyst WS-C2960X-24PD-L
63000945	Switch Cisco Catalyst WS-C2960X-24PD-L
63000946	Switch Cisco Catalyst WS-C2960X-24PD-L
63000947	Switch Cisco Catalyst WS-C2960X-24PD-L
63000948	Switch Cisco Catalyst WS-C2960X-24PD-L
63000961	Switch Cisco WS-C2960X-48PD-L
63000962	Switch Cisco WS-C2960X-48PD-L
63000967	Switch Cisco WS-C2960X-48 LPD-L
63000970	Mrezni uredjaj SCALANCE w788c-2 RJ45
63000971	Mrezni uredjaj SCALANCE w788c-2 RJ45

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

63000972	Mrezni uredjaj SCALANCE w788c-2 RJ45
63000973	FIRENALL CPAP-SG1120-FW
63000974	FIRENALL CPAP-SG1120-FW
63000975	Mrezni uredjaj Catalyst 2960-X48 LP D-L
63000985	mrezni uredjaj Cisco WS-C2960+48PST-L
63001063	6GK5786-2HC00-1AA0Access Point, SCALANCE W786C-2IA
63001064	6GK5786-2HC00-1AA0Access Point, SCALANCE W786C-2IA
63001065	6GK5786-2HC00-1AA0Access Point, SCALANCE W786C-2IA
63001075	Cisco WS-C2960X-48TS-L switch
63001080	HP server concole Switch
63001101	WS-C2960L-48TS- Catalyst 2960L 48 port-switch
63001102	WS-C2960L-48TS- Catalyst 2960L 48 port-switch
63001103	WS-C2960L-24TS-Catalyst 2960L 24 port-switch
63001107	Radio stanica digitalna
63001117	Wireless point - AIR-CT3504-K9 Cisco 3504 sa hardw
63001118	Wireless point - AIR-CT3504-K9 Cisco 3504 sa hardw
63001119	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001120	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001121	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001122	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001123	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001124	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001125	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001126	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001127	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001128	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001129	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001130	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001131	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001132	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001133	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001134	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001135	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001136	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001137	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001138	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001139	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001140	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001141	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001142	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA
63001143	Access point -AIR-AP2802E-E-K9 802.11ac W2 AP w/CA

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

63001144	Mrežni komunikator C9500-24X-A-24 port
63001145	Mrežni komunikator C9500-24X-A-24 port
63001146	Mrežni komutator C9300-24port data sa licencama
63001147	Mrežni komutator C9300-24port data sa licencama
63001148	Mrežni komutator C9300-24port data sa licencama
63001149	Mrežni komutator C9300-24port data sa licencama
63001002	Sistem za kontrolu pristupa na parking
63001003	Sistem IP video nadzora hale I,hale II i hale 4.1
63001003	Racunar HP Envy Phoenix 860-002 NY P3H19A
63001003	Televizor Sharp 55 LC55 CFE6242E Smart Full HD
63001003	CCTV System Upgrade Fujitsu
63001006	Sistem Video Nadzora Server Sala HALA 1 SU
63001007	Sistem za kontrolu pristupa u Hali 1 menadžment
63001007	Sistem za kontrolu pristupa menadžment - upgrade
63001008	Sistem kontrole pristupa Hala 1
63001009	Sistem kontrole pristupa Hala 2
63001009	ASL 5100 DE SiPass Licenca software
63001010	Sistem video nadzora H3
63001010	Sistem video nadzora H3 - upgrade
63001011	Sistem kontrole pristupa Hala 3
63001012	Sistem za kontrolu službe obezbeđenja
63001019	Sistem za dojavu nikotinskog dima H2
63001020	Sistem za dojavu nikotinskog dima H1
63001022	Sistem za kontrolu brzine viljuškara
63001024	Sistem za kontrolu pristupa viljuškarima M.E.K.mod
63001088	Kontrola pristupa ispitnim stanicama
63001095	Sistem video nadzora
63001096	Sistem za dojavu provale
64000023	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000024	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000025	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000026	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000027	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000028	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000029	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000030	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000031	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000032	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000033	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000034	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000035	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

64000036	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000037	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000038	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000039	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000040	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000041	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000042	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000043	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000044	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
64000045	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E
65000001	Instrument za merenje kap i dielektričnih gubitaka
65000006	Uredjaj za snimanje procesnih vremena Multidata S
65000007	Uredjaj za snimanje procesnih vremena Multidata S
65000009	Uredjaj za ultrazvucno ispitivanje zav. spojeva
65000010	Uredjaj za ultrazvucno ispitivanje zavar.spojeva
65000011	Uredaj za vizuelni pregled i skeniranje Wiki-Scan
65000012	Uredaj za vizuelni pregled i skeniranje Wiki-scan
65000013	Uredaj za vizuelni pregled i skeniranje Wiki-scan
65000014	Uredaj za vizuelni pregled i skeniranje Wiki-scan
65000015	Uredaj za vizuelni pregled i skeniranje Wiki-scan
65000018	Dvostruki sistem za uzorkovanje i merenje
65000019	Uredjaj za vizuelni pregled i skeniranje zavarenih
65000020	Multimetar GMC Metrahit Extra
65000021	Multimetar GMC Metrahit 27M
65000026	Dvostrani mikrometar za untrasnja merenja HARTIG
65000027	Merac hrapavosti Surtronic Duo 5 plus
65000028	Uredjaj za merenje hrapavosti MAHR, M300
65000029	Garnitura mikrometra za merenje rupa Mitutoyo
65000030	Uredjaj za merenje vibracija Vibscanner
65000031	Multimetar Fluke 28II sa etaloniranjem
65000032	Digitalni sat sa štopericom
65000033	Aparat za merenje tvrdoće bakarne žice BYH-52
65000034	Aparat za merenje tvrdoće bakarne žice BYH-52
65000035	Analizator digitalnog signala
65000038	Instrument za mer.otpornosti izolac. Metriso 5000A
65000039	Instrument za mer.otpornosti izolac. Metriso 5000A
65000040	Instrument za mer.otpornosti izolac. Metriso 5000A
65000041	Termo kamera T420 320x240px sa objektivom 45°
65000046	Instrument za isp.izolacije visokim nap. Hippe OHG
65000047	Instrument za merenja debljine farbe sa sondom
65000048	Aparat za merenje vlaznosti vazduha tipa TESTO 645

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

65000049	Ispitni pult za serijsko elektric.merenje DDW segm
65000050	Uredjaj za merenje udarnog napona Baker
65000051	Elektricni uredjaj za kalibriranje CAL 542D
65000053	Instrument za ispitivanje udarnog napona
65000054	Termalna kamera Flir T440
65000055	Merac hrapavosti Mahr M300
65000056	Ispitna stanica sa Faraday-ovim kavezom
65000057	Digitalni osiloskopTetronix DP05104B s.b. 050886
65000058	Uredaj za proveru zavarenih spojeva WIKI SCAN
65000059	Analizator snage Yokogawa
65000060	Inverter za ispitivanje pod opterecenjem
65000061	Visokonaponska pasivna sonda za osciloskop 1000:1
65000062	Sonda za merenje debljine farbe
65000063	Sonda za merenje debljine farbe
65000064	Sonda za merenje debljine farbe
65000065	Sonda za merenje debljine farbe
65000066	Uredaj za merenje debljine farbe Elcometar 456
65000067	Uredaj za merenje debljine farbe Elcometar 456
65000068	Digitalna libela pro 3600
65000069	Garnitura planparalelnih granicnih merila 47kom
65000070	Digitalni uredjaj za merenje tvrdoce HH-411
65000071	Digitalni mikrometar sa zastitom IP65
65000072	Digitalni mikrometar sa zastitom IP65
65000073	Digitalni mikrometar sa zastitom IP65
65000074	Digitalni mikrometar sa zastitom IP65
65000075	Digitalni mikrometar sa izmenjivim umetcima
65000076	Mikrometar 1000-1200/0.01mm
65000077	Digitalni stapni mikrometar sa rezerv. baterijom
65000078	Digitalni merni sat sa rezervnom baterijom
65000079	Digitalni dubinomer 0-450/0.01mm
65000080	Uredaj za merenje tvrdoce Equotip 550 portable Roc
65000081	Uredaj za merenje kruznosti obrtanja osovine
65000083	Uredaj za merenje debljine farbe ELCOMETER 456
65000084	Instrument za ispitivanje udarnim naponom-Baker
65000086	Baker DXR ispitivač namotaja
65000087	Uredaj za merenje debljine farbe Elcometer 456
65000088	Uredaj za merenje debljine farbe Elcometer 456
65000089	Instrument Eurot.61557 MI2086 EU
65000090	Sistem akvizicije i merenja potrosnje energenata
65000094	Uredaj za merenje Q data
65000095	Uredaj za merenje Q data

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

65000096	Uređaj za merenje Q data
65000097	Uređaj za merenje Q data
65000098	Uređaj za merenje Q data
65000099	Laserski uređaj za mer. oblika i poloz. segm. DDW
65000103	Laserski uređaj za merenje oblik.i poloz.DDW seg.
65000104	Elektricna vaga sa napajanjem RL-WEX15, do 15kg
65000107	Laserski uređaj za merenje dimenzija 'Faro
65000108	Laserski uređaj za merenje dimenzija 'Faro
65000110	Laserski uređaj za merenje dimenzija 'Faro
65000111	Laserski uređaj za mer. oblika i poloz.segm. DDW
65000112	Uređaj za merenje i namestanje reznog ugla VG1
65000114	Merni instrument FARO za geometrijsko merenje
65000115	Uređaj za snimanje podataka sa uređaja za zavar.
65000116	Uređaj za snimanje podataka sa uređaja za zavar.
65000117	Uređaj za snimanje podataka sa uređaja za zavar.
65000118	Uređaj za snimanje podataka sa uređaja za zavar.
65000119	Uređaj za snimanje podataka sa uređaja za zavar.
65000120	Uređaj za snimanje podataka sa uređaja za zavar.
65000121	Uređaj za snimanje podataka sa uređaja za zavar.
65000122	Uređaj za snimanje podataka sa uređaja za zavar.
65000123	Uređaj za snimanje podataka sa uređaja za zavar.
65000124	Uređaj za snimanje podataka sa uređaja za zavar.
65000125	Uređaj za snimanje podataka sa uređaja za zavar.
65000126	Uređaj za snimanje podataka sa uređaja za zavar.
65000128	Instrument za merenja debljine farbe sa sondom
65000129	Uređaj za merenje otpornosti izolacije MetrISO
65000130	Uređaj za merenje otpornosti izolacije MetrISO
65000131	Uređaj za merenje otpornosti izolacije MetrISO
65000132	Urdjaj za merenje debljine farbe Elcometar
65000133	Urdjaj za merenje debljine farbe Elcometar
65000134	Urdjaj za merenje debljine farbe Elcometar
65000135	Merač hrapavosti Mahr M300
65000136	Uređaj za merenje hrapavosti Mahr kalibrisan
65000141	Digitalno pomicno merilo sa zastitom IP66
65000143	Merni most za digitalni merni sat 50-100mm
65000144	Merni most za digitalni merni sat 100-200mm
65000145	Uređaj za kontorlu pomicnih merila i visinomera
65000146	Uređaj za kontolu mikrometara za unutrašnje mer.
65000147	Surftest SJ 310 sa dodatnom iglom
65000149	Garnitura subitora sa rezervnom baterijom
65000153	Instrument za merenje debljine farbe sa sondom

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

65000154	Instrument za ispitivanje udarnim naponom Baker
65000157	Visokonaponski ispitni uređaj dielektrične čvrstoće
65000157	Nadogradnja visokonaponske ispitne stanice
65000159	Merna igla PHT 6-3500
65000160	Merna igla PHT 6-3500
65000161	Merna igla PHT 6-3500
65000162	Merač intenziteta magnetskog polja sa tangentalnom
65000163	Merač intenziteta magnetskog polja sa tangentalnom
65000164	Merač intenziteta magnetskog polja sa tangentalnom
65000165	Analizator snage Yokagawa WT-1800
65000166	Visokonap. instrum. za mer. el. otp. MetrISO Prime
65000167	Visokonap. instrum. za mer. el. otp. MetrISO Prime
65000168	Naponski merni transformator za unut.montazu DNT36
65000169	Naponski merni transfor. za unut.montazu DNT24/12
65000170	Uređaj za ispitivanje namotaja Baker Dx12 Res/Dc
65000171	Uređaj za merenje hrapavosti MAHR M300
65000172	Merna sonda za MAHR M300 kalibrisana
65000173	Uređaj za visokonaponsko ispitivanje HP-12.6
65000174	Uređaj za visokonaponsko ispitivanje HP-12.6
65000175	Instrument za merenje temperature Testo 645
65000176	Ispitni ormar za SiDrive Test
65000177	Automatski digitalni pull off tester Positest AT-A
65000180	Faro laser tracker
65000181	Ispitna stanica
65000183	Faro ruka Quantum za geometrijsko merenje; 2,4m;/6
65000183	Pomoćni alat(ručka) za merenje faro rukom(Quantum)
65000184	Baker Digitalni tester napona tip D12R
65000185	Baker Digitalni tester napona tip D12R
65000186	Baker Digitalni tester napona tip D12R
65000187	Merni sto 2500 x 1500 x 350 mm
65000189	Uređaj za merenje zatezne sile Quasar 600 kN
65000190	Merni sistem Faro Laser Tracker Vantage
65000191	Merna oprema Faro EDGER Arm 3,7
65000193	Ultrazvučna kada 5800H-E
65000194	Uređaj za kontrolu varova StructureExpert Weld-5
65000195	Presna za toplo zatapanje uzoraka
65000196	Makroskop Car Zeiss Stemi 508
65000197	Ručni infracrveni spektrometar FTIR 4300
65000198	Automatski digitalni Pull Off Tester Positest AT-A
65000199	Automatski digitalni Pull Off Tester Positest AT-A
65000200	Uređaj za testiranje tvrdoće Durascan DS70G5

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

65000201	Merač hrapavosti TQC Positector SPG-1
65000203	Uređaj za ispitivanje zavarenih spojeva UT metodom
65000205	Alat za pakotiranje rotora EP 301
65000207	Bočni regalni viljuškar 2500kg RRB8/958722(180)
65000208	Baka električna vučna kolica SYSA001008 (182)
65000209	Bočni regalni viljuškar 2500kg RRB8/962719(181)
65000210	Aluminijumska rasklapajuća pokretna skela
65000211	Cev za podizanje tereta nosivosti 2500 kg
65000212	Kružna pila
65000213	Mašina za namotavanje 115 G
65000214	Zaštitna vrata za balans mašinu Typ C 15 H
65000215	El. paletar sa platformom 3000 kg S/N:6061801(185)
65000216	El.paletar sa platformom 2500 kg SYSF004179(187)
65000217	El. paletar sa platformom 2500kg SYSF004180(188)
65000218	Vibexpert II Data Collector - uređaj za merenje i
65000219	Set mikrometara za unutrašnje merenje sa prstenom
65000220	Sto za visokonaponsko ispitivanje namotan
65000221	Visokonaponski ispitni uređaj - SHV 05 E
65000222	Visokonaponsko DC napajanje - DC-HV
65000223	Orman za ispitne uređaje
65000224	Napajanje za laboratoriju
65000225	Sto sa valjcima 3t Ø 550 - 1000 / 830x83
65000226	Sto sa valjcima 3t Ø 550 - 1000 / 830x83
65000227	Sto sa valjcima 3t Ø 550 - 1000 / 830x83
65000228	Sto sa valjcima 3t Ø 550 - 1000 / 925x83
65000229	Stara glava za izoliranje Ridgeway
65000230	Presavna mašina za presovanje namotaja(hladna) - 1
65000231	Barovi(sipke) za presovanje namotaja 29
65000232	Sto sa valjcima 3t Ø 550 - 1000 / 815x82
65000233	Sto sa valjcima 3t Ø 550 - 1000 / 815x82
65000234	Sto sa valjcima 3t Ø 550 - 1000 / 820x82
65000235	Sto sa valjcima 3t Ø 550 - 1000 / 830x82
65000236	Sto sa valjcima 3t Ø 550 - 1000 / 925x83
65000237	Postolje za izoliranje (6kom)
65000238	Kolica za namotaje
65000239	Radni sto sa fiokama 2000 x 750
65000240	Horizontalni uređaj za podešavanje i ispitivanje
65000241	Alat za fiksiranje 1054-01
65000242	Alat za fiksiranje 1054-01
65000243	Alat za fiksiranje 1054-02
65000244	Alat za fiksiranje 1054-02

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

65000245	Uređaj za merenje debljine farbe PosiTector 6000 z
65000246	Uređaj za merenje debljine farbe-PosiTector 6000
65000247	Uređaj za merenje otpora izolacije
65000248	Uređaj za merenje otpora izolacije
65000249	Uređaj za merenje oscilacija
65000250	Uređaj za merenje debljine izolacije pr
65000251	Uređaj za merenje debljine izolacije pr
65000252	Mikrometar-Micrometer 700-800 mm MITUTOYO
65000254	Merni uređaj Testo 645
65000255	Uređaj za merenje hrapavosti Surfctest SJ 210
65000256	Reometar MCR302 Anton Paar
65000257	Digitalni uglomer sina 300mm
65000258	Uređaj za merenje debljine prevlake
65000259	Oprema za merenje Hioki RM3545
65000260	Mikrometar
65000261	Mikrometar
65000262	Mikrometar
65000263	Mikrometar analogni Mitutoyo 1200-1300mm
65000264	Ispitna oprema -Agilent 34970A sa pripad. modulima
65000265	Mikrometar Mitutoyo 0-25mm
65000267	Analogni instrument za merenje
65000268	Analogni instrument za merenje
65000269	Analogni instrument za merenje
65000270	Analogni instrument za merenje
65000273	Merni sto Stolle (3500x2200x300)
65000275	12-kanalni OROS Analizator dinamičkih signala
65000276	Visokonaponski kablovi
65000278	Digitalni merni uređaj GARANT
65000279	Merac debljine namotaja W840511010
65000280	Ispitna oprema za merenje el. Otpora
65000281	Ispitna oprema za merenje el. Otpora
65000282	MIKROMETAR, DIGITALNI 340-520
65000283	DIGITALNO POMICNO MERILO 500-501-10
65000284	DIGITALNO POMICNO MERILO 551-207-10
65000285	DIGITALNO POMICNO MERILO 552-305-10
65000286	DIGITALNO POMICNO MERILO 552-306-10
65000287	DIGITALNI DUBINOMER 571-205-10
65000288	Merni alat za Faro instrument SMR 1.5"
65000289	Merni alat za Faro instrument SMR 1.5"
65000290	MIKROMETAR 105-410
65000291	MIKROMETAR 105-411

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

65000293	Vaga za merenje
65000294	Uredjaj za podizanje spulni bakra
65000295	Radni sto za izoliranje namotaja
65000296	Radni sto za izoliranje namotaja
65000297	Polica za odlaganje izolacionog materijala
65000298	Polica za odlaganje alata za presovanje namotaja
65000299	Tiede Magnetni jaram TWM 220N AC 230V/50Hz
65000300	Tiede Magnetni jaram TWM 220N AC 230V/50Hz
65000301	Multimetar Mahr 610-1015mm
65000302	Multimetar Mahr 610-1015mm
65000303	Merač debljine farbe PosiTector 6000 Advance
65000304	Merni sto STOLLE ARP 2500mmx1500mm
65000305	Multimetar Mahr 844 T 260-615mm u kutiji
65000306	Digitalni MITUTOYO stapni mikrometar opseg 200-200
65000307	Visokonaponska ispitna oprema HSV918/30-1 / Wurmb
65000308	Digitalno pomicno merilo Mitutoyo 1500mm
65000309	Digitalno pomicno merilo Mitutoyo 1500mm
65000310	Digitalno pomicno merilo Mitutoyo 1500mm
65000311	Termo kamera FLIRT T530
65000312	Adapter za merenje alata SK50/VDI60
65000313	BAKER DX12 kontoler sa sertifikatom o etaloniranju
65000314	Kada za čelične kugle
65000315	Mikrometar 800-900/0,01mm sa izmenjivim umetcima
65000316	Mikrometar 1300-1400/0,01mm sa izmenjivim umetcima
65000318	OMP60 Wireless Sensore Optical touch probe
65000319	Amper klesta Fluke i3000s flex -24
65000320	Magnetni jaram MR51 230V
65000321	Magnetni jaram MR51 230V
65000322	Digitalni automatski penetrometar
65000323	Uredaj za merenje debljine farbe Elcometer 456
65000324	Uredaj za merenje debljine farbe PosiTector 6000
65000325	MicroGraph System uredaj za merenje krimp uzoraka
65000326	Subitor MaraMeter 844N 100-250mm Mahr
65000327	Subitor MaraMeter 844N 250-400mm Mahr
65000328	Univerzalni merni uredaj MAHR 844T
65000329	Baker uredjaj za merenje sa kontrolerom DX12
65000330	Digitalni Mikrometar 300-400mm Mitutoyo
65000331	Digitalni Mikrometar 150-300mm Mitutoyo
65000332	Digitalni mikrometarski dubinomer 0-300m Mitutoyo
65000333	Digitalno pomicno merilo MAHR 0-500/0,01
65000334	Mini Test 735FN1,5 sa sertifikatom

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

65000335	Mini Test 735FN1,5 sa sertifikatom
65000336	Digitalni mikrometar 150-175mm
65000337	Set mikrometara sa dodirom u 3 tacke
65000338	Univerz.merni instrument Multimar 844T
66000114	Radijalna busilica
66000120	Rucna hidraulicna makaza za secenje
66000121	Rucna hidraulicna makaza za secenje
66000122	Alat za drzanje rotora u vertikalnom poloazaju
66000130	Komplet kalibarskih merila
66000131	Izmenljivi specijalni alat za mont. i demont. leza
66000132	Izmenljivi specijalni alat za montazu i demontazu
66000133	Izmenljivi spec..alat za montazu i demontazu rotor
66000134	Izmenljivi spec.alat za montazu i demontazu rotora
66000135	Alat za ubacivanje statora
66000140	Kalibarsko merilo za kontrolu velicina kod montaze
66000141	Alat za formiranje razvoj namotaja statora ddw gen
66000245	Rucni hiraulicni alat za ravnanje namotaja
66000246	Rucni hidraulicni alat za savijanje kraja namotaja
66000252	Alat za manipulaciju namotaja
66000256	Pneumatski alat za formiranje glave namotaja
66000265	Akumulat. klesta za presov. Weitkowitz-s.br.100749
66000266	Akumulat. klesta za presov. Weitkowitz-s.br.100763
66000267	Akumulat. klesta za presov. Weitkowitz-s.br.100826
66000271	Alat za upustanje limpaketa u kuciste statora
66000278	Alat za drzanje rotora u vertikalnom poloazaju
66000279	Alat za drzanje rotora u vertikalnom poloazaju
66000282	Hidro alat za savijanje kraja namotaja
66000300	Alat za paketiranje limpaketa DDW segmenta V1644
66000301	Alat za paketiranje limpaketa DDW segmenta V1644
66000302	Alat za paketiranje limpaketa DDW segmenta V1644
66000303	Alat za paketiranje limpaketa DDW segmenta V1644
66000304	Alat za paketiranje limpaketa DDW segmenta V1644
66000305	Alat za paketiranje limpaketa DDW segmenta V1644
66000306	Alat za paketiranje limpaketa DDW segmenta V1644
66000307	Alat za paketiranje limpaketa DDW segmenta V1644
66000315	Alat za presovanje i polimerizaciju
66000319	Hidro alat za savijanje kraja namotaja,velika verz
66000323	Alat za paketiranje limpaketa DDW stator. segm.NG2
66000325	Alat za manipulaciju namotaja DDW NG2
66000327	Kombinovani trn za dinamicno balans. ventilatora
66000343	Alat za merenje dimenzije namotanih DDW stat.segm.

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66000346	Alat za pakotiranje limpaketa DDW segm. V1644-04
66000347	Alat za pakotiranje limpaketa DDW segm. V1644-04
66000348	Alat za pakotiranje limpaketa DDW segm. V1644-06
66000349	Alat za pakotiranje limpaketa DDW segm. V1644-06
66000350	Alat za pakotiranje limpaketa DDW segm. V1644-06
66000351	Alat za pakotiranje limpaketa DDW segm. V1644-06
66000352	Traverza nosivosti 6t sa stalkom
66000353	Traverza nosivosti 6t sa stalkom
66000357	Alat za dizanje i nosenje lezaja kucista generat.
66000365	Traverza prema crtezu BE 2265-103
66000366	Traverza prema crtezu BE 2265-74
66000367	Metalna traverza dizalice TV 5/2
66000369	Marametar za merenje osovine rotora, 150-200mm
66000370	Elektricna busilica Fein KBM 65 Q sa setom burgija
66000374	Sablon za proveru mere bakarnih lukova
66000378	Sablon za izradu riba namotaja DD64, 0st
66000379	Sablon za izradu riba namotaja DD64, 37st
66000380	Sablon za izradu riba namotaja DD64, 92st
66000387	Centralni alat za masinu za izradu riba namotaja
66000390	Traverza za kransku dizalicu nosivosti 20t
66000394	Traverza sa nosacem za kransku dizalicu 10t
66000395	Alat za presovanje limpaketa rotora PR865
66000396	Alat za presovanje limpaketa rotora PR865-07
66000397	Alat za presovanje limpaketa rotora PR865-07
66000398	Alat za presovanje limpaketa rotora PR865
66000399	Alat za presovanje limpaketa rotora PR865
66000400	Alat za presovanje limpaketa rotora PR865
66000401	Alat za presovanje limpaketa rotora PR865
66000402	Alat za presovanje limpaketa rotora PR865
66000403	Alat za presovanje limpaketa rotora PR865
66000404	Alat za presovanje limpaketa rotora PR865
66000405	Alat za presovanje limpaketa rotora PR865
66000406	Alat za presovanje limpaketa rotora PR865
66000407	Alat za presovanje limpaketa rotora PR865
66000408	Alat za presovanje limpaketa rotora PR865
66000409	Centralni alat za masinu za izradu riba namotaja
66000410	Moment kljuc 3/4"
66000414	Alat za pakotiranje segmenata V1644-06
66000415	Alat za pakotiranje segmenata V1644-06
66000416	Alat za pakotiranje segmenata V1644-06
66000417	Alat za pakotiranje segmenata V1644-06

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66000418	Indukcijski grejac lezajeva TIH 220M/MV
66000419	Centralni alat za masinu za izradu riba namotaja
66000420	Centralni alat za masinu za izradu riba namotaja
66000421	Centralni alat za masinu za izradu riba namotaja
66000422	Alat za pakovanje segmenata V1644-06
66000423	Alat za pakovanje segmenata V1644-06
66000424	Alat za pakovanje segmenata V1644-06
66000425	Alat za pakovanje segmenata V1644-06
66000426	Pneumatski udarni pistolj sa prigusivacem MD
66000428	Hidraulicne makaze za secenje bakra HB 1V
66000429	Hidraulicne makaze za secenje bakra HB 1V
66000432	Aku alat za presovanje kablskih stopica AP 10
66000434	Alat za dizanje i upustanje statora BE 1900-112
66000435	Noseca ploca sa plocom za centr. upustanja statora
66000436	Pomocni alat za ubacivanje rotora u generator
66000440	Pomicno kljunasto merilo sa dugim kljunom 1000mm
66000441	Pomocni prsten za pakovanje statora
66000442	Pomocni prsten za pakovanje statora
66000443	Pomocni prsten za pakovanje statora
66000444	Pomocni prsten za pakovanje statora
66000445	Pomocni prsten za pakovanje statora
66000446	Pomocni prsten za pakovanje statora
66000465	Alat za podesavanje merne letve 1195mm
66000466	Alat za podesavanje merne letve 965mm
66000467	Noseca ploca sa plocom za centr. fi 720-575-660
66000468	Pistolj za farbanje sa diznom i crevima
66000470	Mikrometar podesavajuci 900-1000 mm
66000471	Mikrometar podesavajuci 1000-1100 mm
66000472	Mikrometar podesavajuci 1100-1200 mm
66000473	Alat za podizanje rotora
66000474	Alat za podizanje rotora
66000475	Kalibar za kontrolisanje i kalibraciju mikrometara
66000476	Alat za zatezanje trake
66000477	Alat za prevrtanje segmenata DDW
66000478	Alat za prevrtanje segmenata DDW
66000479	Metalni prsten fi 1080mm
66000480	Metalni prsten fi 1080mm
66000483	Ploca za merenje Messplatte BE-2265
66000484	Ploca za merenje Messplatte BE-2265
66000485	Bakarni prsten za indukciono lemljenje
66000486	Bakarni prsten za indukciono lemljenje

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66000487	Bakarni prsten za indukciono lemljenje
66000488	Bakarni prsten za indukciono lemljenje
66000489	Bakarni prsten za indukciono lemljenje
66000490	Bakarni prsten za indukciono lemljenje
66000491	Sablon za izradu riba namotaja BE_2265-95C
66000492	Prsten za presovanje za EP-262
66000493	Prsten za presovanje za EP-262
66000494	Prsten za presovanje za EP-262
66000495	Prsten za presovanje za EP-262
66000496	Prsten za presovanje za EP-262
66000497	Prsten za presovanje za EP-262
66000498	Prsten za presovanje limpaketa rotora 950/300
66000499	Prsten za presovanje limpaketa rotora 950/300
66000501	Prsten za presovanje limpaketa rotora 950/300
66000502	Prsten za presovanje limpaketa rotora 950/300
66000503	Prsten za presovanje limpaketa rotora 950/300
66000504	Prsten za presovanje limpaketa rotora 950/300
66000505	Prsten za presovanje limpaketa rotora 950/300
66000506	Prsten za presovanje limpaketa rotora 950/300
66000507	Pneumatske makaze
66000509	Prsten za presovanje statora EP-259
66000510	Prsten za presovanje statora EP-259
66000511	Prsten za presovanje statora EP-259
66000512	Prsten za presovanje statora EP-259
66000513	Alat za pakovanje statora EP-259
66000514	Alat za pakovanje statora EP-259
66000515	Pomocni prsten za pakovanje statora EP-150/-181
66000516	Pomocni prsten za pakovanje statora EP-150/-181
66000517	Pomocni prsten za pakovanje statora EP-150/-181
66000518	Pomocni prsten za pakovanje statora EP-150/-181
66000519	Pomocni prsten za pakovanje statora EP-150/-181
66000520	Pomocni prsten za pakovanje statora EP-150/-181
66000521	Pomocni prsten za pakovanje statora EP-150/-181
66000522	Pomocni prsten za pakovanje statora EP-150/-181
66000523	Alat za merenje radijusa na TS-u segmenta KL688
66000524	Sablon Alu BE 2265-166 D3 Mark II 90 (par)
66000525	Sablon Alu BE 2265-166 D3 Mark II 0 (par)
66000526	Sablon Alu BE 2265-166 D3 Mark II 37 (par)
66000527	Pomicno kljunasto merilo 2000mm sa kalibracijom
66000528	Pomocni prsten za presovanje statora EP 269
66000529	Pomocni prsten za presovanje statora EP 269

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66000530	Pomocni prsten za presovanje statora EP 277
66000531	Pomocni prsten za presovanje statora EP 277
66000532	Pomocni prsten za presovanje statora EP 277
66000533	Pomocni prsten za presovanje statora EP 277
66000543	Aku udarni odvijač GDS 18
66000544	Aku udarni odvijač GDS 18
66000547	Alat za pakovanje segmenta statora DD30
66000548	Alat za pakovanje segmenta statora DD30
66000549	Magnetna bušilica KBM 65 U
66000550	Mikrometar za merni sat sa ručicom 100-150 mm MAHR
66000551	Snažna ručna bušilica Fein 1200 W
66000552	Alat za pakovanje segmenta DD64 V1644-04
66000553	Alat za pakovanje segmenta DD64 V1644-04
66000554	Alat za pakovanje segmenta DD64 V1644-04
66000555	Alat za pakovanje segmenta DD64 V1644-04
66000556	Alu šablon DD64 v.2 45
66000557	Grejna tela 124 x 1060 mm
66000558	Grejna tela 124 x 1060 mm
66000559	Grejna tela 124 x 1060 mm
66000560	Grejna tela 124 x 1060 mm
66000561	Grejna tela 124 x 1060 mm
66000562	Grejna tela 124 x 1060 mm
66000563	Alu šablon DD64 v.2 90
66000564	Alat za merenje radijusa na TS-u segmenta
66000565	Alat za merenje radijusa na TS-u segmenta
66000566	Alat za merenje radijusa na TS-u segmenta
66000567	Alat za merenje radijusa na TS-u segmenta
66000568	Alat za merenje radijusa na TS-u segmenta
66000569	Alat za merenje radijusa na TS-u segmenta
66000570	Pomocni alat za rastavljanje rotora PR 914
66000571	Alat za pakovanje EP 256
66000572	Alat za pakovanje rotora PR 865-05
66000573	Alat za pakovanje segmenta DD64 V1644-04
66000574	Alat za pakovanje segmenta DD64 V1644-04
66000581	Magnetna klešta (MY-2 Yoke)
66000582	Češalj za namotavanje DD22 V.3. BE 2265-95
66000583	Češalj za namotavanje DD22 V.3. BE 2265-95
66000584	Češalj za namotavanje DD22 V.3. BE 2265-95
66000585	Češalj za namotavanje DD22 V.3. BE 2265-95
66000586	Češalj za namotavanje DD22 V.3. BE 2265-95
66000587	Češalj za namotavanje DD22 V.3. BE 2265-95

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66000588	Alat za paketiranje segmenta DD22 V1644-06
66000589	Alat za paketiranje segmenta DD22 V1644-06
66000590	Alat za paketiranje segmenta DD22 V1644-06
66000591	Alat za paketiranje segmenta DD22 V1644-06
66000592	Alat za paketiranje segmenta DD22 V1644-06
66000593	Alat za paketiranje rotora PR 865-05
66000594	Alat za paketiranje rotora PR 865-05
66000595	Aku mešač mase DB2 400-50-300- 400ml 4:1
66000596	Češalj za namotavanje DD64 V.2 BE 2265-98 B1
66000597	Češalj za namotavanje DD64 V.2 BE 2265-98 B1
66000598	Hidraulična akumulatorska presa
66000599	Hidraulična akumulatorska presa
66000600	Pištolj za farbanje Airmix Xcite Gun 200
66000601	Pištolj za farbanje Airmix Xcite Gun 200
66000602	Pištolj za farbanje Airmix Xcite Gun 200
66000603	Glodalica ručna Assfalg basis SMA50-E
66000604	Zaštitni prsten za stator
66000605	Zaštitni prsten za stator
66000606	Hidraulične glave za prese
66000607	Hidraulične glave za prese
66000608	Hidraulične glave za prese
66000609	Brusilica ugaona KNSE 12-150
66000611	Digitalno pomično merilo od Inox-a 1000 mm kalibri
66000612	Motalica za trapez rotirajući deo
66000613	Digitalno pomično merilo 1500mm, KERN
66000618	Prsten za indukciono zavarivanje rotora 221
66000619	Grejno telo za prese 124x890 mm
66000620	Grejno telo za prese 124x890 mm
66000621	Grejno telo za prese 124x890 mm
66000622	Grejno telo za prese 124x890 mm
66000623	Grejno telo za prese 124x890 mm
66000624	Grejno telo za prese 124x890 mm
66000625	Akumulatorska presa Api 30
66000626	Akumulatorska presa Api 30
66000627	Garnitura mernih pinova 1,00-10,00 mm korak 0,10mm
66000629	Šablon 37 stepeni za izradu namotaja
66000630	Šablon 92 stepena za izradu namotaja
66000631	Šablon 0 stepeni za izradu namotaja
66000632	Prsten za indukciono zavarivanje rotora 221
66000633	Merni alat za Faro instrument SMR 1.5"
66000634	Merni alat za Faro instrument SMR 1.5"

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66000635	Merni alat za Faro instrument SMR 1.5"
66000636	Plastični paralelni šablon za centr. namotaja 45st
66000637	Plastični paralelni šablon za centr. namotaja 90st
66000638	Pomoćni alat za osnovnu cev za ubacivanje rotora
66000639	Pomoćni alat za osnovnu cev za ubacivanje rotora
66000640	Pomoćni alat za osnovnu cev za ubacivanje rotora5t
66000641	Cev za ubacivanje rotora nosivost 5t
66000642	Zaštitni prsten za stator fi995
66000643	Zaštitni prsten za stator fi995
66000644	Zaštitni prsten za rotor fi716
66000645	Zaštitni prsten za rotor fi716
66000652	Šablon za centriranje namotaja 45st
66000653	Šablon za centriranje namotaja 90st
66000654	Grejač prese 1100x89x45mm
66000655	Grejač prese 1100x89x45mm
66000656	Grejač prese 1100x89x45mm
66000657	Grejač prese 1100x89x45mm
66000658	Grejač prese 1100x89x45mm
66000659	Grejač prese 1100x89x45mm
66000660	Rotirajući alat ST 294-02
66000661	Rotirajući alat ST 294-02
66000662	Hidraulična glava male prese
66000663	Hidraulična glava male prese
66000664	Hidraulična glava velike prese
66000665	Hidraulična glava velike prese
66000666	Hidraulična glava velike prese
66000667	Moment ključ Stahlwille 650 Nm
66000672	Alat za bušilicu BE 2265-209 manji alat
66000673	Alat za bušilicu BE 2265-210 veći alat
66000674	Alat za pneumatski skidač 7x50mm
66000675	Alat za pneumatski skidač 7x50mm
66000676	Obrtni šiljak Bruckner MK 6 tip MGM
66000677	Pomoćni alat za podizanje rotora, nosivosti 4t
66000678	Pomoćni alat za podizanje rotora, nosivosti 4t
66000679	Moment ključ Stahlwille 650 Nm
66000680	Moment ključ Stahlwille 650 Nm
66000681	Gvozdeni alat za zatezanje elemenata na strugu
66000682	Stranica alata za pakotiranje, desna
66000683	Stranica alata za pakotiranje, leva
66000684	Magnetna bušilica FEIN KBM 65U 770W
66000685	Alat za pakotiranje limpaketa DD22

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66000686	Alat za pakiranje limpaketa DD22
66000687	Alat za pakiranje limpaketa DD22
66000688	Alat za pakiranje limpaketa DD22
66000689	Alat za pakiranje limpaketa DD22
66000690	Alat za pakiranje limpaketa DD22
66000691	Spec. alat za Faro merenja sa staklenom zaštitom
66000692	Spec. alat za Faro merenja sa staklenom zaštitom
66000693	Staklena prizma za merenje geometrijskih veličina
66000694	Staklena prizma za merenje geometrijskih veličina
66000695	Digitalni mikrometar 225-250/0.001mm
66000696	Digitalni mikrometar 250-275/0.001mm
66000697	Digitalni mikrometar 275-300/0.001mm
66000698	Digitalni visinomer 0-1000mm
66000701	Digitalni mikrometar 200-225/0.001mm
66000702	Spitz za strug K116H MK6
66000703	Spitz za strug K116H MK6
66000704	Pomoćni merni alat za Faro laserski uređaj KL688AA
66000705	Pomoćni merni alat za Faro laserski uređaj KL688AA
66000706	Zaštitni prsten za rotor
66000707	Zaštitni prsten za rotor
66000708	Alat za pakiranje statorskih segmenata DD30
66000711	Pištalj za farbanje Airmix Xcite Gun 200
66000712	Pištalj za farbanje Airmix Xcite Gun 200
66000713	Pištalj za farbanje Airmix Xcite Gun 200
66000714	Grejno telo dim. 124x900mm
66000715	Grejno telo dim. 124x900mm
66000716	Grejno telo dim. 124x900mm
66000717	Grejno telo dim. 124x900mm
66000718	Grejno telo dim. 124x900mm
66000719	Grejno telo dim. 124x900mm
66000726	Zaštitni prsten za stator 272
66000727	Zaštitni prsten za stator 272
66000728	Zaštitni prsten za stator 221
66000729	Zaštitni prsten za stator 221
66000730	Elcometar 319 merač tačke rošenja
66000731	Elcometar 319 merač tačke rošenja
66000732	Plastični šablon za centriranje namotaja DD76 45st
66000733	Plastični šablon za centriranje namotaja DD76 90st
66000734	Plastični šablon za centriranje namotaja DD22 90st
66000735	Plastični šablon za centriranje namotaja DD64 45st
66000736	Plastični šablon za centriranje namotaja DD64 90st

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66000737	Plastični šablon za centriranje namotaja DD22 45st
66000738	Šablon za namotavanje D10-45-12 navoja, komplet
66000739	Šablon za namotavanje D10-45-23 navoja, komplet
66000740	Alat za paketiranje statorskih segmenata DD30-1
66000741	Alat za paketiranje statorskih segmenata DD30-1
66000742	Alat za paketiranje statorskih segmenata DD30-2
66000743	Alat za paketiranje statorskih segmenata DD30-2
66000744	Pneumatski snažni čekić Chicago Pneumatics GV5
66000745	Pneumatski snažni čekić Chicago Pneumatics GV5
66000746	Komplet pločica za vizuelno testiranje delova gene
66000747	Pištalj za farbanje Xcite Airmix 200 bar
66000748	Pištalj za farbanje Xcite Airmix 200 bar
66000749	Pištalj za farbanje Xcite Airmix 200 bar
66000750	Pištalj za farbanje Xcite Airmix 200 bar
66000751	Alat za paketiranje statorskih segmenata DD30-2
66000752	Alat za paketiranje statorskih segmenata DD30-2
66000753	Alat za paketiranje statorskih segmenata DD30-2
66000754	Alat za paketiranje statorskih segmenata DD30-2
66000755	Alat za paketiranje statorskih segmenata DD30-2
66000756	Alat za podizanje rotora
66000757	Kontrolna šipka L=1350mm
66000758	Kontrolna šipka L=1950mm
66000759	Alat za paketiranje za DD64, DD76, DD83
66000760	Alat za paketiranje za DD64, DD76, DD83
66000761	Alat za paketiranje za DD64, DD76, DD83
66000762	Alat za paketiranje statorskih segmenata DD30-1
66000763	Alat za paketiranje statorskih segmenata DD30-1
66000764	Alat za paketiranje statorskih segmenata DD30-1
66000765	Alat za paketiranje statorskih segmenata DD30-1
66000766	Alat za paketiranje statorskih segmenata DD30-1
66000767	Grejna tela hidrauličnih presa 1000mm
66000768	Grejna tela hidrauličnih presa 1000mm
66000769	Grejna tela hidrauličnih presa 1000mm
66000770	Grejna tela hidrauličnih presa 1000mm
66000771	Grejna tela hidrauličnih presa 1000mm
66000772	Grejna tela hidrauličnih presa 1000mm
66000773	Grejna tela hidrauličnih presa 1000mm
66000774	Grejna tela hidrauličnih presa 1000mm
66000775	Grejna tela hidrauličnih presa 1000mm
66000776	Grejna tela hidrauličnih presa 1000mm
66000777	Grejna tela hidrauličnih presa 1000mm

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66000778	Grejna tela hidrauličnih presa 1000mm
66000779	Bakarni prsten za indukciono lemljenje tip 129
66000780	Bakarni prsten za indukciono lemljenje tip 129
66000781	Digitalni štapni mikrometar 200-2000/ 0.001 mm
66000782	Set alata za namotavanje DD10
66000783	Hidraulična glava male prese
66000784	Hidraulična glava male prese
66000785	Hidraulična glava male prese
66000786	Hidraulična glava male prese
66000787	Plastični šablon 45st., Plastični šablon 90st.
66000788	Šablon za namotavanje DD37
66000791	Alat za paketiciranje DD30 A5E39156320A
66000792	Alat za paketiciranje DD30 A5E39156320A
66000793	Alat za paketiciranje DD30 A5E39156320A
66000794	Alat za paketiciranje DD30 A5E39156320A
66000795	Alat za paketiciranje DD30 A5E39156320A
66000796	Alat za paketiciranje DD30 A5E39156320A
66000797	Alat za paketiciranje DD30 A5E39156320A
66000798	Set alata za namotavanje i razvlačenje DD 76-83
66000799	Kalibar za izvode DD64
66000800	Pomoćni alat za mašinu za razvlačenje
66000801	Alat za paketiciranje rotora EP271
66000806	Zahvatna naprava Tigrip TR
66000810	Alat za impregnaciju Statora 221
66000811	Alat za impregnaciju Rotora fi 750 x 700 mm
66000812	Aku udarna bušilica odvijač DeWalt
66000813	Aku udarna bušilica odvijač DeWalt
66000814	Aku udarna bušilica odvijač DeWalt
66000815	Aku udarna bušilica odvijač DeWalt
66000816	Aku udarna bušilica odvijač DeWalt
66000817	Aku udarna bušilica odvijač DeWalt
66000818	Aku udarna bušilica odvijač DeWalt
66000819	Aku udarna bušilica odvijač DeWalt
66000820	Aku udarna bušilica odvijač DeWalt
66000821	Aku udarna bušilica odvijač DeWalt
66000822	Alat za paketiciranje limpaketa DD30-2 sa delovima
66000823	Alat za paketiciranje limpaketa DD30-2 sa delovima
66000824	Alat za paketiciranje limpaketa DD30-2 sa delovima
66000825	Alat za paketiciranje limpaketa DD30-2 sa delovima
66000826	Alat za paketiciranje limpaketa DD30-2 sa delovima
66000827	Alat za paketiciranje limpaketa DD30-2 sa delovima

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66000828	Alat za pakiranje limpaketa DD30-2 sa delovima
66000829	Kompozitni disk MD Largo
66000830	Radionički šubler opseg merenja 1200 mm
66000831	Radionički šubler opseg merenja 1200 mm
66000832	Set šablona za namotavanje DD 30
66000833	Alat za balansiranje ventilatora A5E42725160A
66000834	Prizma za merenje 1.5" Heavy Duty BR SMR
66000835	Prizma za merenje 1.5" Heavy Duty BR SMR
66000836	Akumulatorska presa Weitkowitz AP 10
66000837	Akumulatorska presa Weitkowitz AP 10
66000838	Akumulatorska presa Weitkowitz AP 10
66000839	Akumulatorska presa Weitkowitz AP 10
66000840	Akumulatorska presa Weitkowitz AP 10
66000841	Akumulatorska presa Weitkowitz AP 10
66000842	Akumulatorska presa Weitkowitz AP 10
66000843	Akumulatorska presa Weitkowitz AP 10
66000844	Akumulatorska presa Weitkowitz AP 10
66000845	Akumulatorska presa Weitkowitz AP 10
66000846	Akumulatorska presa Weitkowitz AP 10
66000847	Akumulatorska presa Weitkowitz AP 10
66000848	Akumulatorska presa Weitkowitz AP 10
66000849	Akumulatorska presa Weitkowitz AP 10
66000850	Akumulatorska presa Weitkowitz AP 10
66000851	Šablon za razvlačenje namotaja
66000852	Univerzalni alat za pakiranje DD64/76/83
66000853	Univerzalni alat za pakiranje DD64/76/83
66000854	Univerzalni alat za pakiranje DD64/76/83
66000855	Stranica alata DD37 - leva
66000856	Stranica alata DD37 - desna
66000857	Moment ključ HAZET sa računom prihvata 1`1600 Nm
66000858	Šablon za namotavanje namotaja DD10, set od 12 kom
66000859	Alat za presovanje lim paketa DD37PT2
66000861	Mikrometri za unutrašnja merenja ORION-set 20-50mm
66000862	Akumulatorska presa za stopiciranje Weitkowitz APW
66000863	Alat za presovanje limpaketa DD76
66000871	Magnetna bušilica BDS MAB 825
66000873	Alat za limpaketiranje DD 64 76 83
66000874	Alat za limpaketiranje DD 64 76 83
66000875	Alat za limpaketiranje DD 64 76 83
66000876	Alat za pakiranje DD 64 76 83 V 1644-04
66000877	Alat za pakiranje DD 64 76 83 V 1644-04

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66000878	Dorna prema crtežu A5E43745588A
66000879	Stranica alata za pakotiranje DD 76 leva
66000880	Stranica alata za pakotiranje DD 76 leva
66000881	Stranica alata za pakotiranje DD 76 leva
66000882	Stranica alata za pakotiranje DD 76 leva
66000883	Stranica alata za pakotiranje DD 76 leva
66000884	Stranica alata za pakotiranje DD 76 leva
66000885	Stranica alata za pakotiranje DD 76 leva
66000886	Stranica alata za pakotiranje DD 76 leva
66000887	Stranica alata za pakotiranje DD 76 desna
66000888	Stranica alata za pakotiranje DD 76 desna
66000889	Stranica alata za pakotiranje DD 76 desna
66000890	Stranica alata za pakotiranje DD 76 desna
66000891	Stranica alata za pakotiranje DD 76 desna
66000892	Stranica alata za pakotiranje DD 76 desna
66000893	Stranica alata za pakotiranje DD 76 desna
66000894	Stranica alata za pakotiranje DD 76 desna
66000895	Set alata za razvlačenje i namotavanje A5E43775059
66000896	Set alata za razvlačenje i namotavanje A5E43775059
66000897	Set alata za razvlačenje i namotavanje A5E43525630
66000899	Pozicioner izvoda DD 76
66000900	Alat za ulaganje statora u kućište
66000902	Dorna za pakotiranje
66000903	Trakasta brusilica Fein GIS 150 3x400/440V 50/60HZ
66000906	Aku. Hidraulične makaze fi 32mm
66000907	Dorna za EP 307
66000908	Alat za grejanje lim paketa
66000909	Presa za stopiciranje
66000910	Presa za stopiciranje
66000911	Šablon za bušenje lim paketa statora EP302
66000912	Alat za fiksiranje lim-paketa statora EP302 na buš
66000913	Alat za presovanje namotaja pre ulaganja
66000914	Alat za presovanje namotaja pre ulaganja
66000915	Busilica Ruko RSH 1300
66000916	Šablon za DD83-1S
66000917	Šablon za DD83-1S
66000920	Šipke za motalicu DD 22
66000921	Šipke za motalicu DD 22
66000922	Aku presa Weotkowitz
66000923	Plastični šablon za centriranje DD83-1S
66000924	Šablon za DD83-1S komplet

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66000928	Dorna
66000929	Alat za pakiranje statora EP 318
66000930	Alat za pakiranje statora EP 318
66000933	Hidraulicne makaze 235150 HB-1
66000934	Hidraulicne makaze 235150 HB-1
66000935	Moment kljuc 657094 650 STAHLWILLE od 130 -650
66000936	Alat multi A5E45755990A_001AA EP318
66000937	Alat multi A5E45755990A_001AA EP318
66000938	Alat multi A5E45755990A_001AA EP318
66000939	Alat multi A5E45755990A_001AA EP318
66000940	Alat multi A5E45755990A_001AA EP318
66000941	Alat multi A5E45755990A_001AA EP318
66000942	Alat multi A5E45755990A_001AA EP318
66000943	Alat za DD3
66000944	Alat za kidalicu Quasar 600
66000945	Plasticni šablon za centriranje namotaja DD83-1S
66000946	Prsten za dornu EP 307
66000947	Prsten za dornu EP 307
66000948	Prsten za dornu EP 307
66000949	Prsten za dornu EP 307
66000954	Prsten za okretanje rotora
66000955	Alat za pakiranje DD37
66000956	Alat za pakiranje DD37
66000957	Alat za pakiranje DD37
66000958	Alat za pakiranje DD37
66000959	Alat za pakiranje DD37
66000960	Alat za pakiranje DD37
66000961	Alat za pakiranje DD37
66000962	Alat za pakiranje DD37
66000963	Alat za pakiranje DD37
66000964	Alat za pakiranje DD37
66000965	Plasticni sablon
66000966	Aluminijumski sablon za namotavanje
66000967	Aku hidraulicne makaze Fi32mm Klauke
66000968	Pritisni alat za pakiranje statora
66000969	Sablon za namotaje DD CW
66000970	Sablon za namotaje DD CW
66000971	Alat za limpakiranje segmenta DD76
66000972	Alat za limpakiranje segmenta DD76
66000973	Alat za limpakiranje segmenta DD76
66000974	Alat za limpakiranje segmenta DD76

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66000975	Univerzalne stranice
66000976	Univerzalne stranice
66000977	Univerzalne stranice
66000978	Univerzalne stranice
66000979	Univerzalne stranice
66000980	Univerzalne stranice
66000981	Univerzalne stranice
66000982	Univerzalne stranice
66000983	Univerzalne stranice
66000984	Univerzalne stranice
66000985	Univerzalne stranice
66000986	Univerzalne stranice
66000987	Alat za VPI A5E46068931A - 318
66000988	Alat za dizanje statora A5E45876196A
66000989	Alat za dizanje statora A5E45876196A
66000990	Alat za dizanje statora A5E45876196A
66000991	Alat za dizanje statora A5E45876196A
66000992	Slajferica rotaciona baterijska - set
66000993	Sekac hidraulicni
66000994	Univerzalni alat za paketiranje EP 307
66000995	Alat za VPI A5E46068931A - 318
66000996	Alat za paketiranje statora Dorna
66000997	Alat za paketiranje statora Dorna
66000998	Alat za paketiranje DD37-2
66000999	Alat za paketiranje DD37-2
66001000	Alat za paketiranje DD37-2
66001001	Alat za paketiranje DD37-2
66001002	Alat za paketiranje DD37-2
66001003	Alat za paketiranje DD37-2
66001004	Alat za paketiranje DD9
66001005	Alat za paketiranje DD9
66001006	Pomocni alat za prihvat 3*6mm
66001007	Alat za dizanje statora
66001008	Alat za dizanje statora
66001009	Sablon plasticni za centriranje namotaja
66001010	Alat za VPI
66001011	Alat za VPI
66001012	Alat za savijanje štapova rotora
66001013	Alat DD83-2
66001014	Alat DD83-2
66001015	Zaštitni prsten EP318

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66001016	Alat za dizanje rotora
66001017	Alat za dizanje rotora
66001018	Zastitni prsten za impregnaciju EP 307
66001019	Alat za limpaketiranje segmenta DD76
66001020	Alat za limpaketiranje segmenta DD76
66001021	Alat za limpaketiranje segmenta DD76
66001023	Alat za dizanje statora
66001024	Alat za dizanje statora
66001025	Alat za paketiranje statora EP318
66001026	Zastitni prsten za impregnaciju EP 307
66001027	Alat za pecenje namotaja
66001028	Alat pomocni za dizanje rotora EP 318
66001029	Alat za savijanje EP318
66001030	Alat za sestougaone rupe
66001031	Potisni prsten A5E53000327240 (TVL38)
66001032	Potisni prsten A5E53000327240 (TVL38)
66001033	Potisni prsten A5E53000327240 (TVL80)
66001034	Potisni prsten A5E53000327240 (TVL140)
66001035	Alat za pozicioniranje DD37
66001036	Alat za dizanje statora
66001055	Alata za pozicioniranje I stezanje flansni FI 1160
66001056	Alata za pozicioniranje I stezanje flansni FI 1400
66001057	Zastitna stranica za DD3
66001058	Zastitna stranica za DD3
66001059	Sekac kablova AKU hidraulicni
66001060	Sekac kablova AKU hidraulicni
66001061	Busilica magnetna MAB 845, 1800w
66001062	Kljunasto pomicno merilo digitalno Mahr 18EWR 500m
66001063	Kljunasto pomicno merilo digitalno Mahr 18EWR 500m
66001064	Kljunasto pomicno merilo digitalno Mahr 18EWR 1000
66001065	Kljunasto pomicno merilo digitalno Mahr 18EWR 1000
66001067	Alati za pecenje namotaja EP 337
66001068	Prsten potisni za dornu EP318
66001069	Prsten potisni za dornu EP318
66001070	Prsten potisni za dornu EP318
66001071	Prsten potisni za dornu EP318
66001072	Zastitni prsten A5E47026450A
66001073	Zastitni prsten A5E47026450A
66001074	Zastitni prsten A5E46774354A
66001075	Zastitni prsten A5E46774354A
66001076	Kljunasto pomicno merilo digitalno Mahr18EWR 1000m

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66001077	Kljunasto pomicno merilo digitalno Mahr18EWR 500mm
66001078	Bušilica magnetna MAB 845
66001079	Zaštitni prstenovi
66001080	Zaštitni prstenovi
66001081	Alat za merenje FARO ba
66001082	Alat za merenje FARO ba
66001083	Alat za savijanje štapova EP334
66001084	Alat za savijanje štapova EP318
66001085	Dorna univerzalna za EP318
66001086	Alat za savijanje štapova EP334 komplet
66001087	Dorna za pakiranje A5E47654515A_001_AA
66001088	Trn za centriranje Ø420/Ø680x145
66001089	Alat za samostalno savijanje EP318
66001090	Alat za samostalno savijanje EP334
66001091	Zaštitni prsten A5E46911048A
66001092	Zaštitni prsten A5E46911048A
66001093	Zaštitni prsten A5E47026450A
66001094	Zaštitni prsten A5E47026450A
66001095	Zaštitni prsten A5E46911048A
66001096	Zaštitni prsten A5E46911048A
66001097	BUSILICA MAGNETNA MAB 825
66001098	Zastitni prsten za stator EP 337
66001115	Alat sa pipcima za prihvatanje limova/gnezdo za slagan
66001116	Alat sa pipcima za prihvatanje limova/gnezdo za slagan
66001117	Zastitni prsten za EP 337
66001118	Zastitni prsten za stator EP 337
66001119	Zastitni prsten za stator EP 337
66001120	Zastitni prsten za EP 337
66001121	Zastitni prsten za EP 337
66001122	Moment ključ sa sertifikatom Stahlwille
66001123	Baterijske makaze za secenje bakra
66001124	Alat za ulaganje statora u kuciste EP337
66001125	Prsten za presovanje rotorkih lim pak. A5E3645243A
66001126	Alat za samostalno savijanje EP318
66001127	Alat za samostalno savijanje EP337
66001128	Alat za samostalno savijanje EP323
66001129	Alat za samostalno savijanje EP308
66001130	Alat za samostalno savijanje EP334
66001131	Aku presa Api 130-H
66001132	Podizni alat za rotore - 5t nosivost
66001133	Podizni alat za rotore - 5t nosivost

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66001134	Podizni alat za rotore - 5t nosivost
66001136	Podizni alat za rotore - 5t nosivost
66001137	Podizni alat za rotore - 5t nosivost
66001138	Podizni alat za rotore - 5t nosivost
66001139	Podizni alat za rotore - 5t nosivost
66001140	Podizni alat za rotore - 5t nosivost
66001141	Alat za paketiranje multi-A5E4797536A_00
66001142	Aku. hidraul. makaze fi32mm ES32ML Klauk
66001143	Aku. hidraul. makaze fi32mm ES32ML Klauk
66001144	Aku. hidraul. makaze fi32mm ES32ML Klauk
66001145	Aku. hidraul. makaze fi32mm ES32ML Klauk
66001146	Aku. hidraul. makaze fi32mm ES32ML Klauk
66001147	Pritisni prsten A5E48860422A003AC
66001148	Pritisni prsten A5E48860422A003AC
66001149	Alat za kontrolu ispravnosti limova 1
66001153	Stalak za rotore u vertikalnom poloazju
66001154	Stalak za rotore u vertikalnom poloazju
66001155	Stalak za rotore u vertikalnom poloazju
66001156	Stalak za rotore u vertikalnom poloazju
66001157	Stalak za rotore u vertikalnom poloazju
66001158	Stalak za rotore u vertikalnom poloazju
66001159	Stalak za rotore u vertikalnom poloazju
66001160	Stalak za rotore u vertikalnom poloazju
66001161	Stalak za rotore u vertikalnom poloazju
66001162	Stalak za rotore u vertikalnom poloazju
66001163	Stalak za rotore u vertikalnom poloazju
66001164	Stalak za rotore u vertikalnom poloazju
66001165	Zastitni prsten za rotor prema crtezu
66001166	Zastitni prsten za rotor prema crtezu
66001167	Zastitni prsten za rotor prema crtezu
66001168	Zastitni prsten za rotor prema crtezu A5E49537730A
66001169	Zastitni prsten za stator prema crtezu A5E49559073
66001170	Sekac kablova na baterije Stil oCut 50
66001171	Sekac kablova na baterije Stil oCut 50
66001172	Sekac kablova na baterije Stil oCut 50
66001173	Presa na baterije APW30
66001174	Presa na baterije APW30
66001175	Presa na baterije APW30
66001176	Presa na baterije APW30
66001177	Presa na baterije APW30
66001181	Moment kljuc 130-650 Nm sa

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66001182	Grejac lezajeva SKF TIH 220M/V
66001183	Grejac lezajeva SKF TIH 220M/V
66001184	Grejac lezajeva SKF TIH 220M/V
66001186	Digitalni visinomer 814 Sr Digimar 0-600
66001187	Digitalni visinomer 814 Sr Digimar 0-600
66001188	Digitalno pomicno merilo MarCal 18 EWR 0
66001189	Digitalno pomicno merilo MarCal 18 EWR 0
66001190	Alat za proveru pritiska u presama
66001198	Alat za ulaganje statora u kuciste EP328
66001200	Presna za konektore WIETKOWITZ APW30 240mm
66001203	Aku presa Api 130-H
66001204	Potisni prstenovi za dornu EP342/320
66001205	Potisni prstenovi za dornu EP342/320
66001206	Potisni prstenovi za dornu EP342/320
66001207	Potisni prstenovi za dornu EP342/320
66001211	Okretni prsten za EP252
66001212	Okretni prsten za EP252
66001213	Okretni prsten za EP252
66001214	Okretni prsten za EP252
66001215	Blok celjusti postavljen za stezne vijke
66001216	Dorna za paketiranje
66001217	Zastitni prsten EP321
66001218	Trn i stopa za trn A5E49210864A
66001219	Blok celjusti postavljen za stezne vijke 315mm
66001220	Blok celjusti postavljen za stezne vijke 315mm
66001221	Alat za kidalicu - Bending test
66001222	Potisni prsten za dornu EP157
66001223	Potisni prsten za dornu EP157
66001224	Pomocni alat rotorske prese W1G00003073
66001225	Pomocni alat rotorske prese W1G00003073
66001226	Pomocni alat rotorske prese W1G00003073
66001227	Pomocni alat rotorske prese W1G00003073
66001228	Pomocni alat statorske prese W1G0000264
66001229	Pomocni alat statorske prese W1G0000264
66001230	Pomocni alat statorske prese W1G0000264
66001231	Pomocni alat statorske prese W1G0000264
66001232	Zastitni prsten za stator W1G00003659
66001233	Standarna Dorna EP320-1305840_S77_001AA
66001234	Aku presa Hidraulicna 130kN Weitkowi
66001235	Ugaoni precizni zatvarač Milwaukee M12ONEFTR12
66001236	Ugaoni precizni zatvarač Milwaukee M12ONEFTR12

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

66001237	Prsten (fi670xfi627)x30 Ploca (C45) - 1
66001238	Dig.visinomer Mahr814SR Digimar 0-350mm
66001239	Dig.visinomer Mahr814SR Digimar 0-350mm
66001240	Dig.visinomer Mahr814SR Digimar 0-600mm
66001241	Dig.visinomer Mahr814SR Digimar 0-600mm
66001242	Dig.visinomer Mahr814SR Digimar 0-600mm
66001243	Zastitni prsten za rotor crtez 5E49502037A
66001244	Zastitni prsten za rotor crtez 5E49502037A
66001245	Zastitni prsten za rotor crtez 5E49502037A
66001246	Zastitni prsten za stator crtez 5E49502037A
66001247	Zastitni prsten za stator crtez 5E49502037A
66001248	Zastitni prsten za stator crtez 5E49502037A
66001249	Statorska potisna ploca alat - EP301280-3
66001250	Statorska potisna ploca alat - EP301280-3
66001251	Statorska potisna ploca alat - EP301280-3
66001252	Statorska potisna ploca alat - EP301280-3
66001253	Alat za navlacenje kliznog prstena
66001150	Sablon za razvlacenje namotaja DD64
66001151	Sablon za razvlacenje namotaja DD76
66001152	Sablon za razvlacenje namotaja DD76
66001178	Sablon za razvlacenje namotaja DD83
66001179	Sablon za razvlacenje namotaja DD83
66001180	Sablon za razvlacenje namotaja DD30
66001185	Drzac kablova za stator EP328
66001191	Podizni alat za rotore - 5t nosivost
66001192	Podizni alat za rotore - 5t nosivost
66001193	Podizni alat za rotore - 5t nosivost
66001194	Podizni alat za rotore - 5t nosivost
66001195	Podizni alat za rotore - 5t nosivost
66001196	Podizni alat za rotore - 5t nosivost
66001197	Podizni alat za rotore - 5t nosivost
66001199	Alati za krimpovanje CU C8 50mm2 WEITKOW
66001201	Alata za samostalno savijanje Typ A5E
66001202	Dorna za pakiranje rotora EP320
66001208	Drzac kablova za stator EP321/EP342 prototip
66001209	Gornja vilica postavljena za stezne vijk sa 3
68002629	Kolica 12 to
68002630	Kolica 12 to
68002631	Kolica 12 to
68002632	Kolica 12 to
68002633	Kolica 12 to

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68002644	Kolica 12 to
68002645	Kolica 12 to
68002646	Kolica 12 to
68002647	Kolica 12 to
68002648	Kolica 12 to
68002670	Vodomer dn65 wpd
68002671	Metalna ograda kod ispitne stanice
68002675	Kucica za blankovanje
68002676	Gasna stanica
68002701	Delovi krana
68002702	Delovi krana
68002703	Delovi krana
68002704	Delovi krana
68002705	Delovi krana
68002706	Delovi krana
68002707	Delovi krana
68002708	Delovi krana
68002712	Kuhinjski elementi
68002717	Metalne tende za bic
68002718	Metalne tende za bic
68002719	Metalne tende za bic
68002720	Metalne tende za bic
68002722	Konfekcioni sto za video salu
68002723	Dupli antistik
68002727	Delovi krana (oslonci, stubovi sa vijcima upravljac
68002730	Celicna ploca-deo krana
68002731	Celicna ploca-deo krana
68002732	Celicna ploca-deo krana
68002733	Celicna ploca-deo krana
68002746	Transformator za ispitivanje
68002747	Ormani za odlaganje repromaterijala
68002748	Kolica 12to
68002749	Kolica 12to
68002750	Kolica 12to
68002751	Kolica 12to
68002752	Kolica 12to
68002753	Kolica 12to
68002754	Kolica 12to
68002755	Kolica 12to
68002756	Kolica 12to
68002757	Kolica 12to

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68002758	Rezistomat za merenje otpora
68002760	Metalna tenda
68002761	Metalna tenda
68002768	Ugrada masina za sudove
68002769	Ugrada masina za sudove
68002776	Hidraulicna pumpa
68002777	Hidraulicna pumpa
68002778	Hidraulicne bolcne
68002779	Hidraulicne bolcne
68002787	Metalna kolica za montazu rotora
68002790	Upravljacki orman za peci za polimerizaciju
68002791	Citronix aparat za zavarivanje
68002792	Pneumatski cekic za ljustenje farbe u farbari
68002795	Kolica 12tona za montazu generatora
68002796	Kolica 12tona za montazu generatora
68002797	Kolica 12tona za montazu generatora
68002798	Kolica 12tona za montazu generatora
68002799	Kolica 12tona za montazu generatora
68002800	Kolica 12tona za montazu generatora
68002801	Kolica 12tona za montazu generatora
68002802	Kolica 12tona za montazu generatora
68002803	Kolica 12tona za montazu generatora
68002804	Kolica 12tona za montazu generatora
68002805	Nosac kotura 1 komplet
68002808	Ispitni pult za ispitivanje generatora
68002815	Kolica od 12 t za montazu
68002816	Kolica od 12 t za montazu
68002817	Kolica od 12 t za montazu
68002818	Kolica od 12 t za montazu
68002819	Kolica od 12 t za montazu
68002820	Kolica od 12 t za montazu
68002821	Upravljacki orman za peci za polimerizaciju
68002822	Postolje za utiskivanje magneta prototip
68002826	Metalna tenda sa drzecem za bicikle
68002827	Stalak za rotor
68002828	Stalak za rotor
68002829	Stalak za rotor
68002830	Stalak za rotor
68002831	Stalak za rotor
68002832	Stalak za rotor
68002834	Stalak za rotor

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68002835	Stalak za rotor
68002836	Stalak za rotor
68002837	Stalak za rotor
68002838	Stalak za rotor
68002839	Stalak za rotor
68002840	Stalak za rotor
68002841	Stalak za rotor
68002842	Stalak za rotor
68002843	Stalak za rotor
68002844	Stalak za rotor
68002845	Stalak za rotor
68002846	Stalak za rotor
68002855	Sto sa drzacem namotaja statora
68002856	Sto sa drzacem namotaja statora
68002857	Sto sa drzacem namotaja statora
68002858	Sto sa drzacem namotaja statora
68002861	Kontejner od metala za smestaj htz opreme
68002862	Upravljacki orman za peci za polimerizaciju
68002906	Elektricni viljuskar
68002938	Viljuskar
68002942	Viljuskar;lpe 240;bt
68002961	Vakum sud
68002972	Transportna kolica
68002973	Transportna kolica
68002974	Transportna kolica
68002975	Transportna kolica
68003065	Vakum pumpa busch
68003079	Os1449zidni kran
68003088	Prufrotor
68003094	Industrijski usisivac za usisavanje opiljaka pri b
68003095	Konzole sa povezivanjem sistema za vazduh
68003096	Konzole sa povezivanjem sistema za vazduh
68003097	Konzole sa povezivanjem sistema za vazduh
68003098	Konzole sa povezivanjem sistema za vazduh
68003099	Konzole sa povezivanjem sistema za vazduh
68003101	Most kрана
68003102	Delovi kрана
68003115	Pokretni regal za vijcanu robu
68003116	Pokretni regal za vijcanu robu
68003117	Pokretni regal za vijcanu robu
68003118	Pokretni regal za vijcanu robu

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68003119	Pokretni regal za vijcanu robu
68003120	Pokretni regal za vijcanu robu
68003125	Pogonska rasveta
68003129	Uredjaj za termicko obelezavanje zica
68003130	Konzolna dizalica 270
68003131	Konzolna dizalica 270
68003132	Konzolna dizalica 360
68003133	Konzolna dizalica 360
68003135	Filterska jedinica
68003136	Kontejner za cuvanje zapaljivih materijala
68003137	Skladiste tehnickih gasova otvorenog tipa
68003138	Metalna polica za skladistenje robe na prip. gener
68003139	Metalni radni sto sa met. orman. za skladist.alata
68003141	Sine za kran 11,972m
68003142	Sigurnosni ormar za zapaljive materijale120x62x205
68003143	Sigurnosni ormar za zapaljive materijale120x62x205
68003144	Sigurnosni ormar za zapaljive materijale120x62x205
68003145	Sigurnosni ormar za zapaljive materijale120x62x205
68003146	Sigurnosni ormar za zapaljive materijale120x62x205
68003147	Sigurnosni ormar za zapaljive materijale 60x60x205
68003148	Filter za filtrir. i apsorpciju zapaljivih gasova
68003149	Filter za filtrir. i apsorpciju zapaljivih gasova
68003150	Filter za filtrir. i apsorpciju zapaljivih gasova
68003151	Filter za filtrir. i apsorpciju zapaljivih gasova
68003156	Rezervoar za impregnaciono sredstvo
68003179	Nosac kotura sa kocnicama
68003182	Klima uredjaj Mitsubishi Heavy Indus.SRK71ZE/SRC71
68003183	Klima uredjaj Mitsubishi Heavy Indus.SRK71ZE/SRC71
68003185	Klima uredjaj Mitsubishi Heavy Indus.SRK71ZE/SRC71
68003188	Ormaric za garderobu
68003193	Produzetak kranske staze
68003202	Metalno postolje za ciscenje DDW segmenta
68003207	Pomocni stalak za montazu hladnjaka za generator
68003208	Pomocni stalak za montazu hladnjaka za generator
68003209	Montazni kontejner za skladistenje opreme i alata
68003212	Metalno postolje za ciscenje DDW segmenta
68003213	Zastitna komora dim. 2mx2mx2m
68003217	Mobilna vakum. jedinica P30 I 400V-Industi.usisiv.
68003221	Viljuskar BT Reflex RRE 250
68003222	Zastitna ograda na metal. policama 3315x2000x1200
68003223	Zastitna ograda na metal. policama 3000x2000x1200

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68003224	Zastitna ograda na metal. policama 3000x2000x1200
68003225	Metalna polica sa komb.univer ploce 2x1,2x8m
68003229	Kolica od 25t za montazu generatora
68003230	Kolica od 25t za montazu generatora
68003231	Kolica od 25t za montazu generatora
68003233	Frizider Liebherr za sklad. protofer mase za stat.
68003234	Klima uredjaj Mitsubishi SRK35XG-X
68003237	Sto za ulaganje namotaja-pozicion. segmen. DDW gen
68003238	Sto za ulaganje namotaja-pozicion. segmen. DDW gen
68003243	Razvodni orman 203 u lim. kucistu sa prip.kabl.
68003244	Razvodni orman IT01
68003250	Zastitna ograda sa vratima 8500x2000
68003251	Metalna zastitna ograda sa vratima 10mx2m
68003254	Metalni kran nosivosti 50 kg
68003255	Metalni kran nosivosti 50 kg
68003256	Razvodni orman 206 u lim. kuc. sa prip.kabl.-Hala2
68003257	Razvodni orman 207 u lim. kuc. sa prip.kabl.-Hala2
68003258	Razvodni orman 205 u lim. kuc. sa prip.kabl.-Hala2
68003259	Lestve aluminijumske sa platformom
68003266	Razvodni orman 204 u lim. kucistu.-Hala2
68003267	Postolje za montazu i unutr.transp. SWP generatora
68003268	Postolje za montazu i unutr.transp. SWP generatora
68003270	Montazni sistem sa kruznim sinama za nam. DDW segm
68003271	Laki portalni kran nosivosti 500kg
68003272	Laki portalni kran nosivosti 500kg
68003275	Metalni sto za DDW segmente 1000x2300
68003278	Zastitna komora 3200x3200x3000
68003280	Kabina za varenje DDW segmenata
68003282	Kolica od 25t za montazu generatora
68003283	Kolica od 25t za montazu generatora
68003284	Kolica od 25t za montazu generatora
68003285	Rampa za parking prostor
68003286	Rampa za parking prostor
68003301	Metalno postolje za montazu DDW segmenata
68003305	Razvodni orman 401 u lim.kuc.sa prip.kabl.-Hala4.1
68003306	Stub nosaca kotura
68003307	Kranski sistem nosivosti 160kg ABUS HB
68003309	Laki kran nosivosti 320 kg
68003310	Jednomostni kran ABUS EHB za ulag. DDW namotaja
68003311	Kolica za transport strugotine, kiper sist.FAL5012
68003312	Kolica za transport strugotine, kiper sist.FAL5012

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68003313	Metalni orman BOX 3/15 Grey sa bravicama
68003314	Seckalica Fellowes MS-460 CS
68003315	Seckalica Fellowes MS-460 CS
68003317	Metalno postolje za montazu DDW segmenta
68003318	Metalno postolje za montazu DDW segmenta
68003319	Metalno postolje za montazu DDW segmenta
68003321	Zastitna ograda oko ispitne stanice
68003323	Metalni orman BOX 3/15 Grey sa bravicama
68003324	Metalni orman BOX 3/15 Grey sa bravicama
68003325	Kranska staza 55m sa mostom od 10t i 5t u Hali 2
68003326	Kranska staza 65m sa dva mosta od 15t u Hali 4.1
68003328	Razvodni orman 209 u lim. kuc. sa prip.kabl.-Hala2
68003330	Informacioni pult Info - Point
68003331	Informacioni pult Info - Point
68003332	Informacioni pult Info - Point
68003333	Informacioni pult Info - Point
68003336	Metalni orman BOX 3/15 Grey sa bravicama
68003337	Metalni orman BOX 3/15 Grey sa bravicama
68003338	Metalni orman BOX 3/15 Grey sa bravicama
68003339	Kranska vaga do 10t
68003341	Samohodna elektricna vucna kolica EGU,spec.izvedba
68003342	Samohodni el. viljuskar za dizanje DDW stat. segm.
68003349	Samohodni elektro viljuskar Linde E50HL-BR 388-00
68003351	POM-plasticna podloga za sto za obrtanje statora
68003352	POM-plasticna podloga za sto za obrtanje statora
68003353	POM-plasticna podloga za sto za obrtanje statora
68003354	POM-plasticna podloga za sto za obrtanje statora
68003355	Ormar za opasne materije
68003357	Okretni sto za statore generatora
68003359	Klima uredjaj Mitsubishi SRK35ZJ-S
68003360	Metalna univerzalna paleta
68003361	Metalna univerzalna paleta
68003362	Metalna univerzalna paleta
68003363	Metalna univerzalna paleta
68003364	Metalna univerzalna paleta
68003365	Metalna univerzalna paleta
68003366	Metalna univerzalna paleta
68003367	Metalna univerzalna paleta
68003368	Metalna univerzalna paleta
68003369	Metalna univerzalna paleta
68003370	Metalna univerzalna paleta

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68003371	Metalna univerzalna paleta
68003372	Metalna univerzalna paleta
68003373	Metalna univerzalna paleta
68003374	Metalno postolje za montazu DDW segmenata
68003375	Metalno postolje za montazu DDW segmenata
68003376	Metalno postolje za montazu DDW segmenata
68003377	Metalno postolje za montazu DDW segmenata
68003378	Metalno postolje za potrebe impregnacije-Hala 4.1.
68003379	Metalno postolje za potrebe impregnacije-Hala 4.1.
68003380	Orman za alate HSK 100 CNC - 971320
68003381	Metalno postolje za DDW segmente DDG - Hala 4.1.
68003382	Metalno postolje za DDW segmente DDG - Hala 4.1.
68003383	Metalno postolje za DDW segmente DDG - Hala 4.1.
68003384	Metalno postolje za DDW segmente DDG - Hala 4.1.
68003385	Razvodni orman 210 u lim. kuc. sa prip.kabl.-Hala2
68003388	Kranska vaga nosivosti 10t
68003389	Kranska vaga nosivosti 10t
68003390	Informacioni panel za pracenje proizvod. DDW segm.
68003391	Platforma za pranje kada
68003392	Montazna ograda sa stepenistem
68003393	Kranska staza 19,8m sa 4 most.diz. od 8t u Hali 2
68003394	Univerzalni ram za namotaje , DDW GEN
68003404	Industrijski usisivac DTX70 1-30 EX
68003407	Metalni ormar sa 15 boksova za drzanje vrednosti
68003415	Skladiski kontejner 2991x2438x2591
68003418	Radni sto za tvrdo lemljenje kaveza rotora gener.
68003419	Drzac rotora za hladjenje
68003420	Metalni skladiski kontejner 4550x2200x2260
68003424	Paletni regal za odlaganje materijala i delova
68003425	Paletni regal za odlaganje materijala i delova
68003427	Masina za tanjire Aristarco, model AP 50.35
68003434	Nosac koturova sa 6kom.diskova fi430 i vaz.kocnica
68003435	Radni sto za bandaziranje glave namot. BE 2265-12A
68003441	Spratna paleta (stalak) za impregnaciju 2 segm.DDW
68003442	Spratna paleta (stalak) za impregnaciju 2 segm.DDW
68003445	Rucni elektricni viljuskar Linde, Tip L20
68003448	Masina za ciscenje tvrdih podova Karcher BD 140 R
68003451	Radni kuhinjski element - kantina Hala 1
68003452	Metalno postolje za potreb.impregnacije u Hali 4.1
68003453	Metalno postolje za potreb.impregnacije u Hali 4.1
68003454	Obrtni sto za namotavanje 8t

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68003455	Vratilo za kalup za paketiciranje rotora tip 150
68003456	Vratilo za kalup za paketiciranje rotora tip 150
68003457	Vratilo za kalup za paketiciranje rotora tip 181
68003458	Podna ploca za paketiciranje rotora
68003459	Podna ploca za paketiciranje rotora
68003464	MikroTik Hotspot stampac
68003465	Razvodni orman RO212
68003466	Razvodni orman RO213
68003467	Kombinovani trn za balansiranje ventilatora EP221
68003468	Elektricni rostilj Ghn-75 RL
68003469	Friteza fr.6+6lt
68003470	Metalni sto za DDW segmente 1000x2300x80
68003471	Metalni sto za DDW segmente 1000x2300x80
68003472	Razvodni orman RO214
68003473	Univerzalne palete DDW BE 2265-69A var1
68003474	Univerzalne palete DDW BE 2265-69A var1
68003475	Univerzalne palete DDW BE 2265-69A var1
68003476	Univerzalne palete DDW BE 2265-69A var1
68003477	Univerzalne palete DDW BE 2265-69A var1
68003478	Univerzalne palete DDW BE 2265-69A var1
68003479	Univerzalne palete DDW BE 2265-69A var1
68003480	Univerzalne palete DDW BE 2265-69A var1
68003481	Univerzalne palete DDW BE 2265-69A var1
68003482	Univerzalne palete DDW BE 2265-69A var1
68003483	Univerzalne palete DDW BE 2265-69A var1
68003484	Univerzalne palete DDW BE 2265-69A var1
68003485	Univerzalne palete DDW BE 2265-69A var1
68003486	Univerzalne palete DDW BE 2265-69A var1
68003487	Univerzalne palete DDW BE 2265-69A var1
68003488	Vatrootporni orman za dokumentaciju nis
68003501	Metalno postolje za farbanje segmenata(BE 2265-91)
68003502	Metalni boks za potrebe mesanja blata
68003503	Metalna ograda za obrtanje WG statora i rotora
68003504	Metalna komora sa providnom ceradom 2500x1700x2000
68003505	Metalno postolje za potrebe impregnaije-Hala 4.1.
68003506	Metalno postolje za potrebe impregnaije-Hala 4.1.
68003507	Metalni orman Box 3/15 Grey old
68003508	Metalni orman Box 3/15 Grey old
68003509	Laki kran BE 2265-88A 7700mm x 3280 x 3400
68003510	Montazni kontejner za skladistenje opasnog otpada
68003511	LCD TV LG 47LN5400 3D

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68003512	Stepenisno aluminijumsko postolje sa dva rukohvata
68003513	Metalna konstrukcija sa paravanima za obuku zavari
68003514	Metalni orman BOX 3/15 sa bravicama
68003515	Metalni orman BOX 3/15 sa bravicama
68003517	Razvodni orman R0216
68003518	Metalno postolje za DDW segmente, BE 2265-91A
68003519	Metalno postolje za DDW segmente, BE 2265-91A
68003520	Metalno postolje za DDW segmente, BE 2265-91A
68003521	Metalno postolje za DDW segmente, BE 2265-91A
68003522	Radni sto za ispitivanje hladnjaka
68003523	Kolica za ispunu
68003526	Razvodni ormar RO215
68003527	Metalni kontejner za reciklazu
68003529	Metalni okvir sa aluminijumskim plocama BE2265-101
68003530	Metalni okvir sa aluminijumskim plocama BE2265-101
68003531	Metalni okvir sa aluminijumskim plocama BE2265-101
68003532	Metalni okvir sa aluminijumskim plocama BE2265-101
68003533	Metalni paravan oko kontejnera za otpad
68003534	Metalni stalak za montiranje kranske staze
68003535	Metalni stalak za montiranje kranske staze
68003536	Metalni orman BOX 3/15 sa bravicama
68003537	Metalni paravan sa pokretnim vratima
68003538	Metalni stalak BE 2265-91C
68003539	Metalni stalak BE 2265-91C
68003540	Metalni stalak BE 2265-91C
68003541	Metalni stalak BE 2265-91C
68003543	Prijemni pult u sobi recepcije dim. 2,20m*110cm
68003544	Metalno postolje za montazu DDW segmenata
68003545	Metalno postolje za montazu DDW segmenata
68003546	Metalno postolje za montazu DDW segmenata
68003547	Metalno postolje za montazu DDW segmenata
68003548	Paravan sa pokretnim kliznim vratima
68003549	Metalni paravan sa kombinacijom leksana
68003555	Razvodni ormar RO 217
68003556	Razvodni ormar RO 218
68003557	Razvodni ormar RO 219
68003558	Maketa vetrenjace model SWT 6.0-154
68003562	Paleta za drzanje boca za gasove
68003563	Metalni drzac rotora za hladjenje wg
68003564	Metalni drzac rotora za hladjenje wg
68003566	Kuhinjski elementi - Social room 2, hala 2

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68003568	Dvostubna dizalica za dizanje segmenata Consul2.35
68003569	Kontejner ABROL otvoreni sa ceradom
68003570	Kontejner ABROL otvoreni sa ceradom
68003571	Kontejner ABROL otvoreni sa ceradom
68003572	Kontejner ABROL otvoreni sa ceradom
68003573	Hidraulicni sto za podizanje U-Forma tip TUL 2000
68003574	Hidraulicni sto za podizanje U-Forma tip TUL 2000
68003575	Hidraulicni sto za podizanje U-Forma tip TUL 2000
68003576	Hidraulicni sto za podizanje U-Forma tip TUL 2000
68003578	Metalna polica za odlaganje poklopca alata
68003580	Radna stolica - Please Task
68003582	Radna stolica - Please Task
68003583	Tabla Whiteboard sa dodatnim elementima
68003584	TV LCD Philips 50" 50PFL3008H/12 LED full HD
68003586	Ventilacija varilackog mesta sa rekuperacijom
68003587	Ventilacija varilackog mesta sa rekuperacijom
68003588	Ventilacija varilackog mesta sa rekuperacijom
68003589	Ventilacija varilackog mesta sa rekuperacijom
68003590	Ventilacija varilackog mesta sa rekuperacijom
68003591	Ventilacija varilackog mesta sa rekuperacijom
68003592	Ventilacija varilackog mesta sa rekuperacijom
68003593	Ventilacija varilackog mesta sa rekuperacijom
68003594	Elektronska bela tabla CleverBoard 3 105"
68003597	Metalni orman BOX 3/15 blue sa bravicama
68003599	Noseci prsten rotora sa 6 lamela i 4 vezna lima
68003600	Noseci prsten rotora sa 6 lamela i 4 vezna lima
68003601	Metalni orman BOX 3/15 blue sa bravicama
68003603	Dvokrilni sigurnosni ormar za opasne materije
68003606	Univerzalne palete DDW BE 2265-69A
68003607	Univerzalne palete DDW BE 2265-69A
68003608	Univerzalne palete DDW BE 2265-69A
68003609	Univerzalne palete DDW BE 2265-69A
68003610	Univerzalne palete DDW BE 2265-69A
68003611	Univerzalne palete DDW BE 2265-69A
68003612	Univerzalne palete DDW BE 2265-69A
68003613	Univerzalne palete DDW BE 2265-69A
68003614	Univerzalne palete DDW BE 2265-69A
68003615	Univerzalne palete DDW BE 2265-69A
68003616	Razvodni orman RO 220 za pripremu segmenata
68003617	Metalni paravan sa ceradom 9750x3000 mm
68003618	Ormar za procesni racunar za susaru SF31

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68003619	Dvokrilini sigurnosni ormar za opasne materije
68003620	Polica sa soskama za malu farbaru u Hali 1
68003621	Metalni paravan sa kombinacijom leksana
68003624	Kran sa duplim gredama 10tn CXTD, raspon od 14,30m
68003625	Kranska staza 22m
68003625	Produzetak postojece kranske staze za kran od 20t
68003626	Noseci prsten statora O1195/O1035
68003627	Noseci prsten statora O1195/O1035
68003628	Laki portalni kran ABUS za celiju za namotavanje
68003629	Laki portalni kran ABUS za manipulaciju DDW nam.
68003632	Metalni orman BOX 3/15 sa bravicama
68003633	Metalna konstrukcija za zvuenu izolaciju
68003634	Metalni nosac za transport boca za tehnicke gasove
68003635	Metalni nosac za transport boca za tehnicke gasove
68003636	Metalni nosac za transport boca za tehnicke gasove
68003642	Metalni orman BOX 3/30 sa bravicama
68003643	Metalni orman BOX 3/15 sa bravicama
68003645	Noseci prstenovi rotora 0844/0964 - komplet
68003646	Teleskopska dizalica HA 12 IP Haulotte
68003647	Stepenik sa dva rukohvata visine 168cm
68003652	Radni sto za bandaziranje glave namot. BE 2265-12A
68003653	Radni sto za bandaziranje glave namot. BE 2265-12A
68003654	Radni sto za bandaziranje glave namot. BE 2265-12A
68003657	Razvodni orman RO 222
68003659	META-Paletno regalni sistem sa montazom
68003661	META-Paletno regalni sistem sa montazom
68003662	Rucna kolica za palete sa LCD ekranom
68003663	Pokretna masina za usisavanje poda Karcher
68003686	Metalna paleta za grundiranje segmenata BE2265-154
68003687	Razvodni ormar RO221
68003689	Grejno telo 124x62x950 mm
68003690	Grejno telo 124x62x950 mm
68003691	Grejno telo 124x62x950 mm
68003694	Rzvodni orman RO 223
68003695	Susac za ruke Dyson Airblade dB AB14
68003696	Susac za ruke Dyson Airblade dB AB14
68003697	Susac za ruke Dyson Airblade dB AB14
68003698	Susac za ruke Dyson Airblade dB AB14
68003699	Susac za ruke Dyson Airblade dB AB14
68003700	Susac za ruke Dyson Airblade dB AB14
68003701	Susac za ruke Dyson Airblade dB AB14

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68003702	Susac za ruke Dyson Airblade dB AB14
68003703	Susac za ruke Dyson Airblade dB AB14
68003704	Susac za ruke Dyson Airblade dB AB14
68003705	Susac za ruke Dyson Airblade dB AB14
68003706	Susac za ruke Dyson Airblade dB AB14
68003707	Susac za ruke Dyson Airblade dB AB14
68003708	Susac za ruke Dyson Airblade dB AB14
68003709	Susac za ruke Dyson Airblade dB AB14
68003710	Susac za ruke Dyson Airblade dB AB14
68003711	Susac za ruke Dyson Airblade dB AB14
68003712	Susac za ruke Dyson Airblade dB AB14
68003713	Susac za ruke Dyson Airblade dB AB14
68003714	Susac za ruke Dyson Airblade dB AB14
68003715	Susac za ruke Dyson Airblade dB AB14
68003716	Susac za ruke Dyson Airblade dB AB14
68003717	Susac za ruke Dyson Airblade dB AB14
68003718	Susac za ruke Dyson Airblade dB AB14
68003719	Susac za ruke Dyson Airblade dB AB14
68003720	Susac za ruke Dyson Airblade dB AB14
68003721	Susac za ruke Dyson Airblade dB AB14
68003722	Susac za ruke Dyson Airblade dB AB14
68003723	Susac za ruke Dyson Airblade dB AB14
68003724	Susac za ruke Dyson Airblade dB AB14
68003725	Susac za ruke Dyson Airblade dB AB14
68003726	Susac za ruke Dyson Airblade dB AB14
68003727	Susac za ruke Dyson Airblade dB AB14
68003728	Susac za ruke Dyson Airblade dB AB14
68003729	Susac za ruke Dyson Airblade dB AB14
68003730	Susac za ruke Dyson Airblade dB AB14
68003731	Susac za ruke Dyson Airblade dB AB14
68003732	Susac za ruke Dyson Airblade dB AB14
68003733	Susac za ruke Dyson Airblade dB AB14
68003734	Susac za ruke Dyson Airblade dB AB14
68003735	Susac za ruke Dyson Airblade dB AB14
68003736	Susac za ruke Dyson Airblade dB AB14
68003737	Susac za ruke Dyson Airblade dB AB14
68003738	Susac za ruke Dyson Airblade dB AB14
68003739	Susac za ruke Dyson Airblade dB AB14
68003740	Susac za ruke Dyson Airblade dB AB14
68003741	Razvodni orman RO224
68003742	Kranski most 8t

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68003743	Metalni stubni kran nosivosti 50kg
68003749	Kuhinjski elementi, za konstrukciju Hala 3
68003750	TV LCD Philips 50" 50PFL3008H/12 LED full HD
68003751	TV LCD Philips 50" 50PFL3008H/12 LED full HD
68003752	Razvodni orman RO225
68003753	Metalna konstrukcija za zvuenu izolaciju
68003755	Univerzalni radni sto sa radnom plocom 1500x700m
68003756	Univerzalni radni sto sa radnom plocom 1500x700m
68003757	Klima uredjaj Midea za kancelarije
68003758	Klima uredjaj Midea za kancelarije
68003759	Klima uredjaj Midea za kancelarije
68003760	Klima uredjaj Midea za kancelarije
68003761	Kuhinja 2 u prizemlju, Hala 3
68003762	Kuhinja 3 na spratu, Hala 3
68003763	Metalna ograda sa montazom ispod nadstresnice
68003764	PD ispitna stanica
68003765	Metalna konstrukcija za zvuenu izolaciju
68003766	Metalni paravan sa kombinacijom leksana
68003767	Grejno telo 89x45x400mm
68003768	Grejno telo 89x45x400mm
68003770	Grejno telo 124x62x950 mm
68003771	Grejno telo 124x62x950 mm
68003772	Grejno telo 124x62x950 mm
68003774	Grejno telo 124x62x1100 mm
68003775	Metalna polica za balans ploce 4000x1540x500mm
68003776	Metalna soska za odlaganje Eurotransport paleta
68003777	Metalna konstrukcija za odsisne uredjaje
68003778	Metalna konstrukcija za odsisne uredjaje
68003779	Ventilacija varilackog mesta sa rekuperacijom
68003780	Ventilacija varilackog mesta sa rekuperacijom
68003781	Noseci prsten rotora fi 814,6
68003782	Noseci prsten rotora fi 814,6
68003783	Sto Fliptop twin table 140x70
68003784	Sto Fliptop twin table 140x70
68003785	Sto Fliptop twin table 140x70
68003786	Sto Fliptop twin table 140x70
68003787	Sto Fliptop twin table 140x70
68003788	Sto Fliptop twin table 140x70
68003789	Sto Fliptop twin table 140x70
68003790	Sto Fliptop twin table 140x70
68003791	Sto Fliptop twin table 140x70

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68003792	Sto Fliptop twin table 140x70
68003793	Sto Fliptop twin table 140x70
68003794	Tabla Whiteboard WB W 1480xH950 sa dod.elementima
68003795	Elektronska bela tabla CleverBoard 3 105"
68003796	Dorna za pakiranje statora, tip EP-262
68003797	Dorna za pakiranje statora, tip EP-262
68003798	Masivni radni sto
68003799	Metalni paravan sa kliznim i fiksnim vratima
68003800	Metalni radni sto za tackasto zavarivanje
68003801	Polica za grund sa fiokama
68003802	Polica za grund sa fiokama
68003803	Metalno postolje stepenastog oblika 2000x860x1205
68003804	Dorna za pakiranje rotora tip EP-254
68003805	Dorna za pakiranje rotora tip EP-254
68003806	Prikolica za transport materijala,Pefra Modell4000
68003807	Prikolica za transport materijala,Pefra Modell4000
68003808	Garant radni sto Kompakt sa 4 fioke
68003809	Garant ormar za alat sa fiokama 1431x1325x725mm
68003810	Metalna zastitna ograda oko ispitne stanice
68003811	Prikolica za transport materijala,Pefra Modell4000
68003812	Prikolica za transport materijala,Pefra Modell4000
68003813	Prikolica za transport materijala,Pefra Modell4000
68003814	Prikolica za transport materijala,Pefra Modell4000
68003815	Defibrilator Aed Plus Zoll automatski externi
68003816	Defibrilator Aed Plus Zoll automatski externi
68003817	Defibrilator Aed Plus Zoll automatski externi
68003818	Nosac segmenta BE2265-78, za segment DD22 i DD64
68003819	Metalno postolje za farbanje segmenata(BE 2265-91)
68003820	Merna racva 125-150mm
68003822	Metalno postolje sa proizecima za farbanje segm.
68003823	Samoposlužna linija
68003824	Neutralni sto sa kliznim vratima, dim.1800x700x900
68003825	Trodelna sudopera, Inox AISI304 dim.1600x700x900mm
68003826	Orman sa kliznim vratima, Inox dim.1400x700x2000mm
68003827	Zidna hauba sa lamel. filter. i osvetlj.bez motora
68003829	Dorna za pakiranje rotora tip EP-250/262/264
68003830	Dorna za pakiranje rotora tip EP-250/262/264
68003831	Kuhinjski elementi - Social room 2,prizemlje Hala2
68003832	Susac za ruke Dyson Airblade AB14
68003833	Susac za ruke Dyson Airblade AB14
68003834	Susac za ruke Dyson Airblade AB14

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68003835	Susac za ruke Dyson Airblade AB14
68003836	Susac za ruke Dyson Airblade AB14
68003837	Susac za ruke Dyson Airblade AB14
68003838	TNG Instalacija za hale 1,2,3,4.1
68003839	Televizor Philips Led Full HD digital LCD, 50"
68003842	Montazni sistem sa kruznim sinama za nam. DDW segm
68003843	Pokretni nosac namotaja
68003844	Pokretni nosac namotaja
68003845	Pokretni nosac namotaja
68003846	Pokretni nosac namotaja
68003847	Pokretni nosac namotaja
68003848	Pokretni nosac namotaja
68003853	Pokretni nosac namotaja
68003854	Pokretni nosac namotaja
68003855	Nosac bandazkotura i zatezaca
68003858	Kombinovani sto
68003859	Radna stolica - Please Task
68003862	Metalna ograda oko nove peskare sa montazom
68003863	Tabla Whiteboard sa dodatnim elementima
68003864	Metalni sto za DDW segmente 1000x2300x80mm
68003865	Metalni sto za DDW segmente 1000x2300x80mm
68003866	Set za zatezanje sipki statora EP-259
68003867	Noseca ploca i ploca za centriranje fi 790
68003868	Celicna paleta za okretanje rotora
68003869	Celicna paleta za okretanje rotora
68003870	Celicna paleta za okretanje rotora
68003871	Celicna paleta za okretanje rotora
68003872	Celicna paleta za okretanje rotora
68003874	Klima uredjaj LG P24 Advance Plus-za server saluH1
68003875	Metalni paravan sa kliznim vratima oko struga
68003876	Metalna polica za kajle WG
68003878	Metalna soska za alate kod presa (rotor)
68003879	Metalna soska za alate kod presa (stator)
68003880	Metalna soska za alate kod presa (stator)
68003881	Merdevine dvokrake sa radnom platformom
68003882	Dorna za paketiranje statora EP-256/259
68003883	Elektricni viljuskar Linde L20
68003884	Metalna ograda za prostoriju 16 x 7,5m
68003885	Laki portalni kran ABUS, visine dizanja do 5000mm
68003886	Metalno postolje stepenastog oblika
68003887	Metalno postolje stepenastog oblika

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68003888	Elektricni niski paletni viljuskar, Linde T30
68003889	Viljuskar na elektricni pogon, Linde L20
68003891	Elektricni viljuskar Baka EGV 3000
68003892	Server rek ormar Rittal
68003894	Montazni sistem sa kruznim sinama i pok. kolicima
68003895	Laki portalni kran ABUS za celiju za namotavanje
68003896	Prsten (fi 615) za rotor bez AKZ
68003897	Prsten (fi 716) za rotor bez AKZ
68003898	Prsten (fi 766) za rotor bez AKZ
68003899	Radni sto sa ugradjenim odsisom prasine A2080
68003900	Radni sto sa ugradjenim odsisom prasine A2080
68003901	Metalni sto za tačkasto zavarivanje sa fiokama
68003902	Televizor LG 55LB650V
68003903	Dorna za paketiranje rotora tip EP
68003911	Razvodni orman RO-ISP
68003912	Dorna za paketiranje rotora EP272
68003913	Dorna za paketiranje rotora EP272
68003914	Dvostubni kranski most 14,30 m
68003915	Rezervoar TNG
68003916	Klima uredjaj Dalkin
68003917	Klima uredjaj Dalkin
68003918	Metalna soška za odlaganje eurotransportne palete
68003919	Sistem za kabliranje niskog napona na galeriji
68003920	Klima uredjaj Dalkin
68003921	Klima uredjaj Dalkin
68003922	Konferencijski sto
68003923	Metalni sto za ulaznu kontrolu
68003924	Polica metalna za bakarne prstenove
68003925	Metalna zaštitna ograda oko ispitne stanice 22,785
68003926	Please - radna stolica
68003927	Dorna za paketiranje rotora tip PR839L
68003933	Dorna za paketiranje rotora tip PR918b
68003934	Radni sto za ispravljanje krajeva namotaja statora
68003935	Radni sto za ispravljanje krajeva namotaja statora
68003936	Metalno postolje sa izdignutim nosačima
68003937	Metalno postolje sa izdignutim nosačima
68003938	Metalno postolje sa izdignutim nosačima
68003939	Metalno postolje sa izdignutim nosačima
68003940	Nadstresnica za bicikle pored Hale 3
68003941	Metalni paravan oko radnog mesta za čišćenje kraje
68003942	Metalni paravan oko radnog mesta za čišćenje kraje

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68003943	Metalno postolje sa valjcima za okretanje segmenat
68003944	Metalno postolje sa valjcima za okretanje segmenat
68003945	Metalno postolje sa valjcima za okretanje statora
68003946	Metalno postolje sa valjcima za okretanje statora
68003947	Metalno postolje sa valjcima za okretanje statora
68003948	Metalno postolje sa valjcima za okretanje statora
68003949	META-regalni sistem sa uvodnicom na svim nivoima
68003950	META-regalni sistem sa uvodnicom na svim nivoima
68003951	META-regalni sistem sa uvodnicom na svim nivoima
68003952	META-regalni sistem sa uvodnicom na svim nivoima
68003953	META-regalni sistem sa uvodnicom na svim nivoima
68003954	META-regalni sistem sa uvodnicom na svim nivoima
68003955	META-regalni sistem sa uvodnicom na svim nivoima
68003956	META-regalni sistem sa uvodnicom na svim nivoima
68003957	Pokretni radni sto Tooltruck sa8 fioka
68003958	Kolica od 25t za montazu generatora
68003959	Kolica od 25t za montazu generatora
68003960	Kolica od 25t za montazu generatora
68003961	Kolica od 25t za montazu generatora
68003962	Televizor 48 Led Philips 1920x1080
68003963	Radni sto za bandaziranje glave namot. BE 2265-12A
68003964	Radni sto za bandaziranje glave namot. BE 2265-12A
68003965	Radni sto za bandaziranje glave namot. BE 2265-12A
68003966	Radni sto za bandaziranje glave namot. BE 2265-12A
68003967	Radni sto za bandaziranje glave namot. BE 2265-12A
68003968	Radni sto za bandaziranje glave namot. BE 2265-12A
68003969	Radni sto za bandaziranje glave namot. BE 2265-12A
68003970	Radni sto za bandaziranje glave namot. BE 2265-12A
68003971	Radni sto za bandaziranje glave namot. BE 2265-12A
68003972	Radni sto za bandaziranje glave namot. BE 2265-12A
68003975	Radni sto za bandaziranje glave namot. BE 2265-12A
68003976	Radni sto za bandaziranje glave namot. BE 2265-12A
68003977	Radni sto za bandaziranje glave namot. BE 2265-12A
68003978	Radni sto za bandaziranje glave namot. BE 2265-12A
68003979	Radni sto za bandaziranje glave namot. BE 2265-12A
68003980	Radni sto za bandaziranje glave namot. BE 2265-12A
68003981	Radni sto za bandaziranje glave namot. BE 2265-12A
68003982	Radni sto za bandaziranje glave namot. BE 2265-12A
68003983	Radni sto za bandaziranje glave namot. BE 2265-12A
68003984	Radni sto za bandaziranje glave namot. BE 2265-12A
68003985	Radni sto za bandaziranje glave namot. BE 2265-12A

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68003986	Radni sto za bandaziranje glave namot. BE 2265-12A
68003987	Radni sto za bandaziranje glave namot. BE 2265-12A
68003988	Metalni paravan sa leksanom sa kliznim vratima
68003989	Čelične palete za okretanje rotora
68003990	Čelične palete za okretanje rotora
68003991	Čelične palete za okretanje rotora
68003992	Čelične palete za okretanje rotora
68003993	Čelične palete za okretanje rotora
68003994	Pritisni prsten za rotor 221,250,254,260,264
68003995	Skladište zatvoreno za odlaganje otpada
68003996	Metalna ograda oko otpadnog materijala
68004006	Univerzalna paleta Be 2265-69A
68004007	Univerzalna paleta Be 2265-69A
68004008	Univerzalna paleta Be 2265-69A
68004009	Univerzalna paleta Be 2265-69A
68004010	Univerzalna paleta Be 2265-69A
68004011	Univerzalna paleta Be 2265-69A
68004012	Univerzalna paleta Be 2265-69A
68004013	Univerzalna paleta Be 2265-69A
68004014	Univerzalna paleta Be 2265-69A
68004015	Univerzalna paleta Be 2265-69A
68004016	Univerzalna paleta Be 2265-69A
68004017	Univerzalna paleta Be 2265-69A
68004018	Univerzalna paleta Be 2265-69A
68004019	Univerzalna paleta Be 2265-69A
68004020	Univerzalna paleta Be 2265-69A
68004021	Pokretni radni sto za DDW segmente
68004022	Pokretni radni sto za DDW segmente
68004023	Pokretni radni sto za DDW segmente
68004024	Pokretni radni sto za DDW segmente
68004025	Pokretni radni sto za DDW segmente
68004026	Pokretni radni sto za DDW segmente
68004027	Pokretni radni sto za DDW segmente
68004028	Pokretni radni sto za DDW segmente
68004029	Pokretni radni sto za DDW segmente
68004030	Pokretni radni sto za DDW segmente
68004036	Metalni boks sa staklom za tocilo sa montazom
68004037	Metalna soška za stubove dupli tip 2
68004038	Soška metalna za silirit dupli
68004041	Paletno regalna konstrukcija 2700x1100x85 mm
68004042	Tankvani dimenzija 2650x110x450 mm

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004043	Tankvani dimenzija 2650x110x450 mm
68004044	Tankvani dimenzija 2650x110x450 mm
68004045	Tankvani dimenzija 2650x110x450 mm
68004046	Tankvani dimenzija 2650x110x450 mm
68004047	Antimagnetne uške za dizanje segmenta BE 2265-72 D
68004048	Antimagnetne uške za dizanje segmenta BE 2265-72 D
68004049	Antimagnetne uške za dizanje segmenta BE 2265-72 D
68004050	Antimagnetne uške za dizanje segmenta BE 2265-72 D
68004051	Antimagnetne uške za dizanje segmenta BE 2265-72 D
68004052	Antimagnetne uške za dizanje segmenta BE 2265-72 D
68004053	Antimagnetne uške za dizanje segmenta BE 2265-72 D
68004054	Antimagnetne uške za dizanje segmenta BE 2265-72 D
68004055	Klima Uredjaj Galanz AUS 18-Hala 2
68004056	Klima Uredjaj Galanz AUS 18-Hala 2
68004057	Klima Uredjaj Galanz AUS 18-Hala 2
68004064	Antimagnetne uške atestirane BE 2265-72 D (VAR 4)
68004065	Antimagnetne uške atestirane BE 2265-72 D (VAR 4)
68004066	Antimagnetne uške atestirane BE 2265-72 D (VAR 4)
68004067	Antimagnetne uške atestirane BE 2265-72 D (VAR 4)
68004068	Antimagnetne uške atestirane BE 2265-72 D (VAR 4)
68004069	Antimagnetne uške atestirane BE 2265-72 D (VAR 4)
68004070	Antimagnetne uške atestirane BE 2265-72 D (VAR 4)
68004071	Antimagnetne uške atestirane BE 2265-72 D (VAR 4)
68004072	Radionička kolica sa radnim stolom i pet fioka Gar
68004073	Radionička kolica sa radnim stolom i pet fioka Gar
68004074	Radionička kolica sa radnim stolom i pet fioka Gar
68004075	Radionička kolica sa radnim stolom i pet fioka Gar
68004076	Radionička kolica sa radnim stolom i pet fioka Gar
68004077	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004078	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004079	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004080	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004081	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004082	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004083	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004084	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004085	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004086	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004087	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004088	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004089	Antimagnetne uške atestirane BE 2265-72 (VAR 3)

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004090	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004091	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004092	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004093	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004094	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004095	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004096	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004097	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004098	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004099	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004100	Antimagnetne uške atestirane BE 2265-72 (VAR 3)
68004101	Podpultna Maisina za pranje casa ATA AL 402 sa pos
68004102	Dvodelna Sudopera sa ocedjivacem
68004104	Stalak za hladenje rotora
68004105	Stalak za hladenje rotora
68004106	Traverza 6t
68004107	Traverza 6t
68004108	Stubna konzolna dizalica nosivosti 500 kg
68004109	Dorna za pakovanje EP 256
68004110	Dorna za pakovanje EP 256
68004111	Metalna ograda za magacin EHS opreme 3x28 m
68004112	Metalni Abrol kontejner sa ciradom
68004115	Ručni mehanički viljuškar za podizanje tereta
68004117	Metalna ograda za otpadni bakar sa kliznim vratima
68004118	Metalna paleta sa valjcima za farbanje
68004119	Metalna paleta sa valjcima za farbanje
68004120	Metalna paleta sa valjcima za farbanje
68004121	Metalna paleta sa valjcima za farbanje
68004123	Čelična platforma 40x1000x1000 mm
68004124	Čelična platforma 40x1000x1000 mm
68004125	Zaštitna ograda oko radnog mesta za tvrdo lemljenj
68004126	Polični regal 2x10 m
68004127	Polični regal 2x10 m
68004128	Zidni sistem sa pokretnim I statičkim tablama High
68004129	Aluminijumska pokretna platforma sa točkovima
68004130	Aluminijumska pokretna platforma sa točkovima
68004131	Aluminijumska pokretna platforma sa točkovima
68004132	Aluminijumska pokretna platforma sa točkovima
68004133	Aluminijumska pokretna platforma sa točkovima
68004136	Kuhinjski Elementi u Hali 1
68004137	UV LED lampa baterijsko napajanje 24V/2300mAh

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004138	UV LED lampa baterijsko napajanje 24V/2300mAh
68004139	UV LED lampa baterijsko napajanje 24V/2300mAh
68004141	Pokretni metalni nosaš kalema
68004142	Metalni orman za odlaganje kalmike
68004143	Aluminijumsko postolje ZARGES sa stepenicama
68004144	Kondenzatorska Baterija CFQ 46/50
68004145	Radni sto Kompakt 930x1100x630 mm
68004146	Radni sto Kompakt 930x1100x630 mm
68004147	Radni sto Kompakt 930x1100x630 mm
68004148	Radni sto Kompakt 930x1100x630 mm
68004149	Radni sto Kompakt 930x1100x630 mm
68004150	Radni sto Kompakt 930x1100x630 mm
68004151	Radni sto Kompakt 930x1100x630 mm
68004152	Radni sto Kompakt 930x1100x630 mm
68004153	Radni sto Kompakt 930x1100x630 mm
68004154	Radni sto Kompakt 930x1100x630 mm
68004155	Ventilacija varilačkog mesta sa rekuperacijom
68004156	Ventilacija varilačkog mesta sa rekuperacijom
68004157	Ventilacija varilačkog mesta sa rekuperacijom
68004158	Ventilacija varilačkog mesta sa rekuperacijom
68004159	Ventilacija varilačkog mesta sa rekuperacijom
68004160	Ventilacija varilačkog mesta sa rekuperacijom
68004171	Sto za zavarivanje Siegmund Basic 1200x1200x50
68004172	Stalak za Faro Uredaj
68004173	Stalak za montažu 1316537_S77
68004174	Set paralelnih graničnih merila kalibrisan 87 kom.
68004175	Set paralelnih graničnih merila Mitutoyo 8 kom.
68004176	Kranski most 5t CXTS
68004177	Orman za držanje vrednosti 21 odeljak BOX 3/21
68004178	Orman za držanje vrednosti 21 odeljak BOX 3/21
68004179	Orman za držanje vrednosti 21 odeljak BOX 3/21
68004180	Uške za dizanje prema crtežu BE 2265-190
68004181	Uške za dizanje prema crtežu BE 2265-190
68004182	Uške za dizanje prema crtežu BE 2265-190
68004183	Uške za dizanje prema crtežu BE 2265-190
68004184	Uške za dizanje prema crtežu BE 2265-190
68004185	Uške za dizanje prema crtežu BE 2265-190
68004186	Uške za dizanje prema crtežu BE 2265-190
68004187	Uške za dizanje prema crtežu BE 2265-190
68004188	Uške za dizanje prema crtežu BE 2265-190
68004189	Uške za dizanje prema crtežu BE 2265-190

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004190	Uške za dizanje prema crtežu BE 2265-190
68004191	Uške za dizanje prema crtežu BE 2265-190
68004192	Uške za dizanje prema crtežu BE 2265-190
68004193	Uške za dizanje prema crtežu BE 2265-190
68004194	Uške za dizanje prema crtežu BE 2265-190
68004195	Uške za dizanje prema crtežu BE 2265-190
68004196	Kolica za transport generatora nosivosti 25 tona
68004197	Kolica za transport generatora nosivosti 25 tona
68004198	Kolica za transport generatora nosivosti 25 tona
68004199	Kolica za transport generatora nosivosti 25 tona
68004200	Kolica za transport generatora nosivosti 25 tona
68004201	Kolica za transport generatora nosivosti 25 tona
68004202	Vaga Vibra GZII B60K Ex
68004203	Pritisna ploča za presovanje lim paketa
68004204	Dorne za pakiranje statora EP 272
68004205	Dorne za pakiranje statora EP 272
68004206	Kiper paleta KP-100
68004207	Kiper paleta KP-100
68004210	Merni sto za proveru neobrađenih nosača DD22
68004213	Klizna polica za alate za kantiranje i savijanje
68004215	Metalno kućište za visokonaponsku opremu
68004219	Paralelni plastični uložak DD64 A5E35590223A
68004220	Paralelni plastični uložak DD64 A5E35590223A
68004221	Paralelni plastični uložak DD64 A5E35590223A
68004222	Pokretni radni sto za upravljačku jedinicu VN opre
68004224	Orman za držanje vrednosti 15 odeljaka
68004225	Dorna za pakiranje statora EP 272 PR 926
68004226	Dorna za pakiranje statora EP 272 PR 926
68004227	Traverza za kran nosivosti 6t
68004229	Pokretni stalak za Faro laserski uređaj
68004234	Čelična paleta za okretanje rotora
68004235	Čelična paleta za okretanje rotora
68004236	Stalak za polimerizaciju ddw segmenata
68004237	Stalak za polimerizaciju ddw segmenata
68004238	Stalak za polimerizaciju ddw segmenata
68004239	Stalak za polimerizaciju ddw segmenata
68004241	Traverza za kran HV4 sa podesivim kukama
68004242	Traverza za kran HV4 sa podesivim kukama
68004243	Traverza za kran HV4 sa podesivim kukama
68004244	Traverza za kran nosivosti 6t
68004245	Platformska vaga H520, 3t

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004246	Platformaska vaga H520, 3t
68004253	Orman za držanje vrednosti, 15 odeljaka
68004254	Varilačko radno mesto
68004255	Varilačko radno mesto
68004256	Varilačko radno mesto
68004257	Radni sto za ubacivanje rotora u generator
68004259	Ventilacioni sistem kod ulaganje protofera u Hali1
68004261	Defibrilator fred easy manual schiller
68004262	Defibrilator fred easy manual schiller
68004263	Defibrilator fred easy manual schiller
68004264	Paravan između presa
68004265	Sigurnosni orman EN30 170 litara
68004266	Digitalna vaga 'EHP typ BR C3'
68004268	Zaštitni paravan oko novog struga
68004269	Skladišni elektro viljuškar STILL EXU-S 22
68004270	Skladišni elektro viljuškar STILL EXU-S 22
68004271	Polični regal SI1230x1972x1574mm
68004272	Dvokrake merdevine Zarges sa 5 stepenika
68004273	Sistem osvetljenja radnog mesta na ulaznoj kontrol
68004274	Rotorska dorna PR 839P
68004277	Postolje za okretanje LPS i LPR
68004278	Postolje za okretanje LPS i LPR
68004279	Postolje za okretanje LPS i LPR
68004280	Postolje za okretanje LPS i LPR
68004281	Postolje za okretanje LPS i LPR
68004282	Postolje za okretanje LPS i LPR
68004283	Postolje za okretanje LPS i LPR
68004284	Postolje za okretanje LPS i LPR
68004285	Postolje za okretanje LPS i LPR
68004286	Postolje za okretanje LPS i LPR
68004287	Postolje za okretanje LPS i LPR
68004288	Postolje za okretanje LPS i LPR
68004289	Postolje za okretanje LPS i LPR
68004290	Postolje za okretanje LPS i LPR
68004291	Postolje za okretanje LPS i LPR
68004293	Postolje za okretanje LPS i LPR (roler)
68004294	Kompletan sistem za podmazivanje mašću za burad
68004295	Postolje za okretanje LPS i LPR (roler)
68004296	Postolje za okretanje LPS i LPR (roler)
68004297	Postolje za okretanje LPS i LPR (roler)
68004298	Postolje za okretanje LPS i LPR (roler)

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004299	Met. paravan oko r.m. za čišćenje krajeva namotaja
68004300	Met. paravan oko r.m. za čišćenje krajeva namotaja
68004301	Zaštitna ograda kod OCH bušilice 6x2m
68004302	Otvoreni metalni kontejner 30M3
68004303	Otvoreni metalni kontejner 30M3
68004304	Viljuškar na elek.pogon Pro-lift nosivost 200kg
68004305	Viljuškar na elek.pogon Pro-lift nosivost 200kg
68004307	Sistem jednostranih regala poz.30
68004308	Sistem jednostranih regala poz.20
68004309	Sistem jednostranih regala poz.20
68004310	Sistem jednostranih regala poz.10
68004311	Sistem jednostranih regala poz.10
68004312	Paletni regal poz.70
68004313	Paletni regal poz.70
68004314	Sistem jednostranih regala poz.50
68004315	Paletni regal poz.60
68004316	Paletni regal poz.60
68004317	Sistem jednostranih regala poz.40
68004318	Kompletan sistem za podmazivanje mašću za burad
68004319	Kompletan sistem za podmazivanje mašću za burad
68004320	Kompletan sistem za podmazivanje mašću za burad
68004321	Kompletan sistem za podmazivanje mašću za burad
68004322	Kompletan sistem za podmazivanje mašću za burad
68004323	Komplet audio opreme za komunikaciju
68004324	Komplet audio opreme za komunikaciju
68004325	Kabina za farbanje i sušenje statora i rotora
68004326	Aluminijumske merdevine podest Z600 sa ogradom
68004328	Sto kod izrade štavpova
68004329	Sto kod izrade štavpova
68004330	Sto kod izrade štavpova
68004331	Sto kod izrade štavpova
68004332	Soška za alate
68004333	Soška za alate
68004334	Soška za alate
68004335	Soška za alate
68004336	Polica prema crtežu A5E38409115A
68004337	Sistem za ispiranje pištolja za farbanje
68004338	Sistem za ispiranje pištolja za farbanje
68004339	Zaštita segmenta prilikom grundiranja
68004340	Prenosna paleta
68004341	Mašina za pranje poda Karcher B 150 R Advance

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004342	Mašina za pranje poda Karcher B 150 R Advance
68004343	Uške za dizanje tereta Thepa Point M24x45mm
68004344	Uške za dizanje tereta Thepa Point M24x45mm
68004345	Uške za dizanje tereta Thepa Point M24x45mm
68004346	Uške za dizanje tereta Thepa Point M24x45mm
68004347	Radna stolica Please
68004349	Klizna polica za kantiranje i savijanje
68004350	Kolica za DD22
68004351	Kolica za DD64
68004352	Ograda oko prese i okretalice
68004353	Skladišni elektro viljuškar STILL EXV 20
68004354	Sto za izolaciju izvoda
68004355	Komplet plastičnih držača za statorsku okretalicu
68004356	Brzopodizuća rolo industrijska vrata Efaflex
68004357	Brzopodizuća rolo industrijska vrata Efaflex
68004358	Ventilacija zavarivačkih mesta
68004359	Prenosivi stalak za flanše
68004360	Pokretni radni sto za računar Garant 1000x725mm
68004361	Pokretni radni sto za računar Garant 1000x725mm
68004362	Aluminijumske merdevine platforma Z600
68004364	Paleta 002-17062016
68004365	Paleta 002-17062016
68004366	Paleta 002-17062016
68004367	Paleta 002-17062016
68004368	Paleta 002-17062016
68004369	Paleta 002-17062016
68004370	Paleta 002-17062016
68004371	Paleta 002-17062016
68004372	Paleta 002-17062016
68004373	Paleta 002-17062016
68004374	Paleta 002-17062016
68004375	Paleta 002-17062016
68004376	Paleta 002-17062016
68004377	Paleta 002-17062016
68004378	Paleta 002-17062016
68004379	Paleta 002-17062016
68004380	Mašina za pranje poda Karcher B 250 R + D 100
68004382	Radna korpa viljuškara za rad na visini - 65002
68004383	Televizor LG 49LH6047 LED TV49` Full HD
68004384	Sistem programiranog automatskog aktiviranja zvona
68004385	Sistem programiranog automatskog aktiviranja zvona

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004386	Sistem programiranog automatskog aktiviranja zvona
68004387	Metalni orman za hemikalije model VO-K
68004388	Metalni orman za hemikalije model VO-K
68004389	Digitalni multifunkc. uređaj za merenje Mitutoyo
68004390	Digitalni multifunkc. uređaj za merenje Mitutoyo
68004408	Ur.za merenje rel.vlažnosti i temperature Testo 64
68004409	Prenosivi stalak za flanšne
68004410	Mašina za pranje poda B 150 R Advance 1.246-020.2
68004411	Adapter za Baka viljuškar
68004412	Postolje za okretanje LPS i LPR (roler) po specifi
68004413	Postolje za okretanje LPS i LPR (roler) po specifi
68004414	Postolje za okretanje LPS i LPR (roler)
68004415	Postolje za okretanje LPS i LPR (roler)
68004416	Postolje za okretanje LPS i LPR (roler)
68004417	Postolje za okretanje LPS i LPR (roler)
68004418	Postolje za okretanje LPS i LPR (roler)
68004424	Pumpa za ispiranje PU3000
68004425	Televizor VIVAX LED TV-65LE74T2
68004426	Usisivač za mokro i suvo usisavanje ATTIX 961-01
68004427	Usisivač za mokro i suvo usisavanje ATTIX 961-01
68004428	Dvokrilni sigurnosni orman ASECOS S-Classic tip 90
68004429	Dvokrilni sigurnosni orman ASECOS S-Classic tip 90
68004430	Postolje za okretanje LPS i LPR (roler) po specifi
68004431	Postolje za okretanje LPS i LPR (roler) po specifi
68004432	Postolje za okretanje LPS i LPR (roler) po specifi
68004433	Postolje za okretanje LPS i LPR (roler) po specifi
68004434	Postolje za okretanje LPS i LPR (roler) po specifi
68004435	Postolje za okretanje LPS i LPR (roler) po specifi
68004436	Postolje za okretanje LPS i LPR (roler) po specifi
68004437	Postolje za okretanje LPS i LPR (roler) po specifi
68004438	Viljuškar BAKA EGU5020 ser.br.33120(1,00)
68004439	Jednokrilni sigurnosni orman ASECOS S-Classic tip
68004440	Jednokrilni sigurnosni orman ASECOS S-Classic tip
68004441	C okvir sa kolicima STILL C-FRAME
68004442	C okvir sa kolicima STILL C-FRAME
68004443	C okvir sa kolicima STILL C-FRAME
68004444	C okvir sa kolicima STILL C-FRAME
68004445	C okvir sa kolicima STILL C-FRAME
68004446	C okvir sa kolicima STILL C-FRAME
68004447	C okvir sa kolicima STILL C-FRAME
68004448	C okvir sa kolicima STILL C-FRAME

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004449	Viljuškar BAKA EGU5020 ser.br.33119(1,00)
68004450	Tegljač STILL R07-25L
68004451	Tegljač STILL R07-25L
68004452	Zavesa za Durst kabinu za lakiranje
68004453	Baker Tester DXR Power 30 Zero starter
68004454	Baker Tester DXR Power 30 Zero starter
68004455	Dupla kranska staza raspona 19,80m 16t I+II CXTD
68004456	Mrežni sklop projektora i usluga realizacije
68004457	Specijalno merilo za Faro ruku zakrivljeno 90st
68004458	Viljuškar BAKA EGU5020 ser.br.33145(1,00)
68004459	Uređaj za merenje mehanič. svojstava tragstrukture
68004460	Mobilni prečistač vazduha MobilePro 400V/3ph/50Hz
68004461	Mobilni prečistač vazduha MobilePro 400V/3ph/50Hz
68004462	Mobilni prečistač vazduha MobilePro 400V/3ph/50Hz
68004463	Mobilni prečistač vazduha MobilePro 400V/3ph/50Hz
68004464	Mobilni prečistač vazduha MobilePro 400V/3ph/50Hz
68004465	Mobilni prečistač vazduha MobilePro 400V/3ph/50Hz
68004466	Uređaj za zavarivanje S8 SpeedPulse-XT 500 B/W
68004467	Uređaj za zavarivanje S8 SpeedPulse-XT 500 B/W
68004468	Kolica sa kočnicom za šine kod proizv.trake za seg
68004469	Kolica sa kočnicom za šine kod proizv.trake za seg
68004470	Kolica sa kočnicom za šine kod proizv.trake za seg
68004471	Kolica sa kočnicom za šine kod proizv.trake za seg
68004472	Kolica sa kočnicom za šine kod proizv.trake za seg
68004473	Kolica sa kočnicom za šine kod proizv.trake za seg
68004474	Kolica sa kočnicom za šine kod proizv.trake za seg
68004475	Kolica sa kočnicom za šine kod proizv.trake za seg
68004476	Kolica sa kočnicom za šine kod proizv.trake za seg
68004477	Kolica sa kočnicom za šine kod proizv.trake za seg
68004478	Kolica za šine kod proizvodne trake za segmente
68004479	Kolica za šine kod proizvodne trake za segmente
68004480	Kolica za šine kod proizvodne trake za segmente
68004481	Kolica za šine kod proizvodne trake za segmente
68004482	Kolica za šine kod proizvodne trake za segmente
68004483	Kolica za šine kod proizvodne trake za segmente
68004484	Kolica za šine kod proizvodne trake za segmente
68004485	Kolica za šine kod proizvodne trake za segmente
68004486	Kolica za šine kod proizvodne trake za segmente
68004487	Kolica za šine kod proizvodne trake za segmente
68004488	Dvostubna dizalica Consul Z360
68004489	Dvostubna dizalica Consul Z360

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004492	Dvokrilni sigurnosni orman sa filtracijom
68004493	Spec.alat 0,875` SMR za merenje standardne preciz
68004494	Spec.alat 0,875` SMR za merenje standardne preciz
68004495	Usisivač za mokro i suvo usisavanje ATTIX 961-01
68004496	Pritisna ploča za DD22
68004497	Zaštitno stepenište VPI 3 sistema sa ogradom
68004500	Kancelarijski prostor škole zavarivanja 1800x3000x
68004501	Ormar sa policama ORSY crveni 1170x1555
68004502	Ormar sa policama ORSY crveni 1170x1555
68004503	Ormar sa policama ORSY crveni 1170x1555
68004504	Metalni sto za secenje kablova
68004506	Dvokrilni sigurnosni orman sa filtracijom
68004507	Televizor Vivax LED TV-65LE74T2
68004508	Jednokrilni ormar sa policama Orsy
68004509	Jednokrilni ormar sa policama Orsy
68004510	Jednokrilni ormar sa policama Orsy
68004511	Jednokrilni ormar sa policama Orsy
68004512	Radni sto Orsy WUG12-1500-RAL3020
68004513	Radni sto Orsy WUG12-1500-RAL3020
68004514	Stabilni vijčani vazduhom hlađeni kompresor GA75VS
68004515	Postolje za vizuelnu kontrolu sa urezanim navojima
68004516	Postolje za vizuelnu kontrolu sa urezanim navojima
68004517	Postolje za vizuelnu kontrolu sa urezanim navojima
68004518	Postolje za vizuelnu kontrolu sa urezanim navojima
68004519	Postolje za vizuelnu kontrolu sa urezanim navojima
68004520	Postolje za vizuelnu kontrolu sa urezanim navojima
68004521	Sistem polica
68004522	Radna korpa viljuškara za rad na visini - 65003
68004523	Kalibrator 0micron CAL 542 Verzija D
68004524	Kalibrator 0micron CAL 542 Verzija D
68004525	Orman za merne instrumente
68004526	Viljuškar Linde L20 ser.1173
68004527	Viljuškar Linde L20 ser.1173
68004528	Merni sto za prijemnu kontrolu STOLLE
68004530	Televizor Vivax Imago TV-65LE74T2 sa nosačem
68004531	Kompletan ugradni sistem ASECOS 305x555x210mm
68004532	Laserski uređaj za merenje dimenzija Faro
68004533	Dispenzer paleta
68004534	Postolje za TS prema crtežu A5E4137198A
68004535	Ventilacija zavarivačkih mesta na DDW liniji
68004536	Ventilacija zavarivačkih mesta na DDW liniji

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004537	Ventilacija zavarivačkih mesta na DDW liniji
68004538	Ventilacija zavarivačkih mesta na DDW liniji
68004560	Pregrada na MGD liniji
68004561	Merni pipak PHT 6-350/2
68004562	Merni pipak PHT 6-350/2
68004563	Merni pipak PHT 6-350/2
68004564	Set mikrometara za unutrašnja merenja 20-50mm Orion
68004565	Alu merdevine platforma sa rukohvatima
68004566	Alu. Radna platforma
68004567	Alu. Radna platforma
68004568	Alu. Radna platforma
68004569	Digitalno kljunasto pomično merilo Orion 0-1500mm
68004570	Uređaj za ispitivanje visokog napona HP E12
68004571	Stalak za fino merenje segmenta
68004572	Transportni radni sto GARANT 1100x1030x630mm
68004573	Transportni radni sto GARANT 1100x1030x630mm
68004574	Kolica za izvode
68004575	Kolica za izvode
68004576	Kolica za izvode
68004577	Kolica za izvode
68004578	Kolica za izvode
68004579	Kolica za izvode
68004580	Kolica za izvode
68004581	Kolica za izvode
68004582	Kolica za izvode
68004583	Kolica za izvode
68004584	Telo grejaca
68004585	Telo grejaca
68004586	Telo grejaca
68004588	Telo grejaca
68004590	Telo grejaca
68004591	Telo grejaca
68004592	Telo grejaca
68004593	Telo grejaca
68004597	Pomerajući stalak za
68004598	Sistem distribucije tačnog vremena
68004609	Projektor Vivitek dw868 sa nosačem
68004610	Audio - video sistem u Video sali hala 1
68004611	Audio - video sistem u učionici hala 1
68004612	Električna friteza na postolju, dim. 800x700x900mm
68004613	Električni roštilj na postolju, dim. 800x700x900mm

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004614	Frižider kapaciteta 700lit, Technodom, d800x800x2050
68004615	Elektricni sporet sa pecnicom na postolju
68004616	Masina za pranje sudja dim. 600x600x780mm
68004617	Zamrzivac 700 lit, Inox AISI 304
68004618	Stona ljustilica krompira FIMAR PPN 5
68004619	Elektricni sporet sa pecnicom na postolju
68004620	Projektor EPSON EB X 20
68004627	Uredjaj za odvod i filtrir.dima pri zavar. Kemper
68004628	Uredjaj za odvod i filtrir.dima pri zavar. Kemper
68004629	Uredjaj za odvod i filtrir.dima pri zavar. Kemper
68004630	Masina za ciscenje poda Karcher KM 75/40W
68004631	Masina za ciscenje/glacanje poda Karcher KM 70/30C
68004636	Uredjaj za stampanje natpisnih tablica Hellermann
68004637	Industrijski usisivac Karcher NT 65/2 Tact
68004638	Industrijski usisivac Karcher NT 65/2 Tact
68004639	Kompaktna dvostruka jedinica za aparat
68004640	Mokro suvi usisivač Karcher NT 65/2 tact 2
68004641	Mokro suvi usisivač Karcher NT 65/2 tact 2
68004642	Mokro suvi usisivač Karcher NT 65/2 tact 2
68004643	Mokro suvi usisivač Karcher NT 65/2 tact 2
68004644	Projektor Epson EB-X27 LCD
68004645	Uredjaj za filtriranje vazd.za orm. za opasne mat.
68004646	Aparat za pranje HD10/25-4sx+
68004647	Projektor Epson EB-1410Wi
68004649	Kompresor AC 55 H
68004650	Agregat za hidrauličnu presu
68004651	Agregat za hidrauličnu presu
68004654	Klima Uredjaj Fujitsu AOY24LFCC
68004655	Klima Uredjaj Fujitsu AOY24LFCC
68004663	Elektricna pumpa za burad Typ ME II 3-230
68004664	Projektor Epson EB-1410Wi
68004665	Mobilni industrijski aspirator Kemper
68004666	Mobilni industrijski aspirator Kemper
68004667	Uredjaj za odsis prasine sa radnog stola Dustomat
68004668	Uredjaj za odsis prasine sa radnog stola Dustomat
68004669	Usisivač za mokro i suvo čišćenje Kracher NT75/2
68004670	Usisavač Kracher NT/65 2 tact
68004671	Usisavač Kracher NT/65 2 tact
68004672	Usisavač Kracher NT/65 2 tact
68004673	Usisavač Kracher NT/65 2 tact
68004674	Uredaj za odsis zaprljanog vazduha Dustomat P20

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004675	Kompresor za vazduh ACS 7 H Plus
68004676	Kompresor za vazduh ACS 7 H Plus
68004677	Dizel agregat Aggretech AGS0630M E43 S71
68004678	Kompresor AC 55 H
68004679	Uredjaj za filtriranje vazd.za orm. za opasne mat.
68004680	Automatski turbo agregat sa elektricnim pogonom
68004681	Uredjaj za preciscavanje emulzije sa separatorom
68004682	Industrijski samohodni usisivac Karcher B150
68004683	Industrijski usisivac Karcher NT 65/2 Tact
68004684	Industrijski cistac podova Karcher KM 70/30 C'
68004685	Mobilni industrijski aspirator Kemper
68004686	Mobilni industrijski aspirator Kemper
68004687	Mobilni industrijski aspirator Kemper
68004688	Mobilni industrijski aspirator Kemper
68004689	Mobilni industrijski aspirator Kemper
68004690	Mobilni industrijski aspirator Kemper
68004691	Mobilni industrijski aspirator Kemper
68004692	Mobilni industrijski aspirator Kemper
68004693	Mobilni industrijski aspirator Kemper
68004694	UPS uredaj Masterguard D-serie 200 kVa
68004696	Razvodni orman
68004697	Alkotest AlcoQuant® 6020 plus
68004698	Alkotest AlcoQuant® 6020 plus
68004699	Uredaj za zavarivanje Lorch S8 SpeedPulse-XT 500 B
68004700	Uredaj za zavarivanje Lorch S8 SpeedPulse-XT 500 B
68004701	Uredaj za zavarivanje Lorch S8 SpeedPulse-XT 500 B
68004702	Uredaj za zavarivanje Lorch S8 SpeedPulse-XT 500 B
68004703	Uredaj za zavarivanje Lorch S8 SpeedPulse-XT 500 B
68004704	Uredaj za zavarivanje Lorch S8 SpeedPulse-XT 500 B
68004705	Induktor GETEMP0006
68004706	Uredaj za tackasto označavanje Markator
68004707	Uredaj za tackasto označavanje Markator
68004708	Poklopac alata DD37 sa pripadajućim delovima
68004709	Pritisna ploča A5E412515055A
68004710	Pritisna ploča A5E412515055A
68004711	Pritisna ploča A5E412515055A
68004712	Pritisna ploča A5E412515055A
68004713	Pritisna ploča A5E412515055A
68004714	Aparat za zavarivanje Alpha Q 351
68004715	Aparat za zavarivanje Alpha Q 351
68004716	Aparat za zavarivanje Alpha Q 351

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004717	Aparat za zavarivanje Alpha Q 351
68004718	Uređaj za tačkasto označavanje Markator
68004719	Hidraulični agregat H1608010-1 za hidrauličnu pres
68004720	Hidraulični agregat H1608011-1 za hidrauličnu pres
68004721	Hidraulični agregat H1608011-1 za hidrauličnu pres
68004722	Hidraulični agregat H1608011-1 za hidrauličnu pres
68004723	Hidraulični agregat H1608011-1 za hidrauličnu pres
68004724	Hidraulični agregat H1608011-1 za hidrauličnu pres
68004725	Hidraulični agregat H1608011-1 za hidrauličnu pres
68004726	Hidraulični agregat H1608011-1 za hidrauličnu pres
68004727	Hidraulični agregat H1608011-1 za hidrauličnu pres
68004728	Hidraulični agregat H1608011-1 za hidrauličnu pres
68004729	Hidraulični agregat H1608011-1 za hidrauličnu pres
68004730	Hidraulični agregat H1608011-1 za hidrauličnu pres
68004731	Hidraulični agregat H1608011-1 za hidrauličnu pres
68004732	Cilindar HHJ 60 S 7.5
68004733	Cilindar HHJ 60 S 7.5
68004734	Cilindar HHJ 60 S 7.5
68004735	Cilindar HHJ 60 S 7.5
68004736	Cilindar HHJ 60 S 7.5
68004737	Cilindar HHJ 60 S 7.5
68004738	Sistem konzolnih regala
68004739	Sistem regala za skladištenje teških tereta
68004740	Sistem standardnih paletnih regala
68004744	Prihvatna kada čelična pocink. sa 2 bureta 200l
68004745	Set zavesa Durst za kabinu za lakiranje segmenata
68004746	Postolje za TS
68004747	Postolje za TS
68004748	Postolje za TS
68004749	Predfilter Atlas Copco DD310+
68004750	Stacionarna kertridž filter jed, usisna ruka 2m
68004751	Stacionarna kertridž filter jed, usisna ruka 2m
68004752	Uništivač papira Šreder Fellowes Automax 500C
68004753	Gravitacioni regal 600 paletnih mesta
68004754	Gravitacioni regal 600 paletnih mesta
68004755	Dorna za pakovanje PR 918
68004756	Dorna za pakovanje PR 918
68004757	Dorna za pakovanje PR 897A
68004758	Dorna za pakovanje
68004759	Dorna za pakovanje PR 880B
68004760	Dorna za pakovanje PR 942

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004761	Dorna za pakiranje PR 942 T2
68004762	Dorna za pakiranje PR 942 T2
68004763	Dorna za pakiranje PR 918
68004764	Dorna za pakiranje
68004765	Dorna za pakiranje
68004766	Dorna za pakiranje
68004767	Dorna za pakiranje
68004768	Kabina za otprašivanje sa ventilatorom JETBLACK
68004769	Postolje za Faro merenje
68004770	Poklopac alata DD64
68004771	Poklopac alata DD64
68004772	Poklopac alata DD64
68004773	Poklopac alata DD64
68004774	Poklopac alata DD64
68004775	Poklopac alata DD64
68004776	Poklopac alata DD64
68004777	Poklopac alata DD64
68004778	Poklopac alata DD64
68004779	Poklopac alata DD64
68004780	Radni sto sa točkicama RWB2-3F/18
68004781	Postolje za okretanje LPS i LPR
68004783	Postolje za okretanje LPS i LPR
68004784	Rashladna komora Viessmann
68004785	Metalni orman za opterećenja sa pregradom
68004786	Farbara WA-LA90 (velika farbara), Farbara WA-LA22
68004787	Mašina za pranje i odmašćivanje delova "GLOGAR"
68004788	Visokopritisna pumpa H 06 07 013-1
68004789	Visokopritisna pumpa H 06 07 013-1
68004790	Visokopritisna pumpa H 06 07 013-1
68004791	Sigurnosni orman za opasne materije
68004792	Rolo vrata tip "SST-S"
68004793	Rolo vrata tip "SST-S"
68004794	Rolo vrata tip "SST-S"
68004795	Rolo vrata tip "SST-S"
68004796	Rolo vrata tip "SST-S"
68004797	Rolo vrata tip "SST-S"
68004798	Aparat za zavarivanje Tetrix 350 AC/DC Serien-Nr.
68004799	Frižider + rashladni agregat Viessmann
68004800	Postolje za okretanje LPS i LPR
68004801	Postolje za okretanje LPS i LPR
68004802	Postolje za okretanje LPS i LPR

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004803	Postolje za okretanje LPS i LPR
68004804	Kompresorski sistem
68004805	Frižider bez poda
68004806	Rucna kolica za manipulaciju kotura sa bakarnom zi
68004807	Rucna kolica za manipulaciju kotura sa bakarnom zi
68004808	Rucna kolica za manipulaciju kotura sa bakarnom zi
68004809	Ograda prostora odeljenja održavanja H1
68004810	Niskonaponski transformator
68004811	Brodski kontejner 40' korišten
68004812	Brodski kontejner 40' korišten
68004813	Brodski kontejner 40' korišten
68004814	Brodski kontejner 40' korišten
68004815	Brodski kontejner 40' korišten
68004816	Brodski kontejner 40' korišten
68004817	Brodski kontejner 40' korišten
68004818	Brodski kontejner 40' korišten
68004819	Pumpa za farbu PU3000
68004820	Pumpa za farbu PU3000
68004822	Klima Uredjaj 12 BTU
68004823	Sistem osvetljenja varilačkih kabina
68004825	Postolje za serijsko ispitivanje hibrid generatora
68004826	Jednogredna mosna dizalica nosivosti 5t
68004827	Peć za izolacioni materijal
68004828	Peć za izolacioni materijal
68004829	Jednostrane merdevine Zarges sa jednom platformom
68004830	Jednostrane merdevine Zarges sa jednom platformom
68004831	Jednostrane merdevine Zarges sa jednom platformom
68004832	Mosni kran Abus / EHB
68004832	Dizalica mosna EHB ABUS
68004833	El.platformska vaga 1000x2200mm 300kg
68004834	Radni sto sa točkicama RWB2-3F/1B
68004851	Viljuškar Baka Egu 5020 s. br. SO E 33323
68004852	Viljuškar Baka Egu 5020 s. br. SO E 33322
68004853	Viljuškar Baka Egu 5020 s. br. SO E 33324
68004854	Baka viljuškar 5t EGU-5020 MPEL s b. E 033099
68004855	Uredaj za smirglanje Herkules T2 Mobil
68004856	Uredaj za smirglanje Herkules T2 Mobil
68004857	Sto za zavarivanje
68004858	Sto za zavarivanje
68004859	Sto za zavarivanje
68004860	Sto za zavarivanje

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004861	Sto za zavarivanje
68004862	Sto za zavarivanje
68004863	Sto za zavarivanje
68004864	Sto za zavarivanje
68004865	Horizontalni stalak za merenje i transport
68004866	Horizontalni stalak za merenje i transport
68004867	Horizontalni stalak za merenje i transport
68004868	Horizontalni stalak za merenje i transport
68004869	Horizontalni stalak za merenje i transport
68004870	Horizontalni stalak za merenje i transport
68004871	Horizontalni stalak za merenje i transport
68004872	Horizontalni stalak za merenje i transport
68004873	Horizontalni stalak za merenje i transport
68004874	Horizontalni stalak za merenje i transport
68004875	Elek. paletni viljuškar Toyota LPE220 sbr. 6525453
68004876	Viljuškar BAKA EGU EL SO s. b. 33321 SO E
68004877	Viljuškar BAKA EGU 8000 EL SO s b.33320 SO E
68004878	Viljuškar BAKA EGU 8000 EL SO s b.33319 SO E
68004879	Viljuškar BAKA EGU 8000 ser.br.SO E 33293(1,00)
68004880	Viljuškar BAKA EGU 8000 ser.br.SO E 33297(1,00)
68004881	Uredaj za peskarenje TZP 200 SX
68004882	Viljuškar BAKA EGU 8000 ser.br.SO E 33294(1,00)
68004883	Viljuškar BAKA EGU 8000 ser.br.SO E 33296(1,00)
68004884	Viljuškar BAKA EGU 8000 ser.br.SO E 33295(1,00)
68004885	Čelična ograda za proširenje škole zavarivača
68004886	Švedski atlas ISO 8501-1 + Standard ISO 8501-3
68004887	Merač klimatskih uslova TQC Positector DPM-1
68004888	Merač klimatskih uslova TQC Positector DPM-1
68004889	Vertikalno skladište visina 4,7 m Modula MX75
68004890	Vertikalno skladište visina 6,3 m Modula MX75
68004891	Vertikalno skladište visina 6,3 m Modula MX75
68004892	Vertikalno skladište visina 4,7 m Modula MX75
68004893	Vertikalno skladište visina 6,3 m Modula MX75
68004894	Strugarska stezna glava
68004895	Metalna tankvana sa ogradom za 4 bureta
68004896	Metalna tankvana sa ogradom za 4 bureta
68004897	Metalna tankvana sa ogradom za 4 bureta
68004898	Metalna tankvana sa ogradom za 4 bureta
68004899	Metalna tankvana sa ogradom za 4 bureta
68004900	Metalna tankvana sa ogradom za 4 bureta
68004901	Metalna tankvana sa ogradom za 4 bureta

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004902	Metalna tankvana sa ogradom za 4 bureta
68004903	Metalna tankvana sa ogradom za 4 bureta
68004904	Metalna tankvana sa ogradom za 4 bureta
68004905	Klima uredjaj GREE
68004906	Klima Uredjaj 12
68004907	Univerzalna sušnica, 58l do 300st. France Etuves
68004913	UPS uređaj za FARO 230V
68004914	UPS uređaj za FARO 230V
68004915	UPS uređaj za FARO 230V
68004916	Univerzalni Kombi radni sto Garant sa pločom od El
68004917	Univerzalni Kombi radni sto Garant sa pločom
68004918	Platforma za brodski kontejner
68004919	Seckalica -Fellows Powerschred 125Ci
68004920	Seckalica -Fellows Powerschred 125Ci
68004921	Postolje za montažu za JXRA-800LA-12A
68004923	Oštrač Wolfram elektrode TGM 40230 PORTA
68004924	Kparat za sečenje metala plazmom tip Powermax 125
68004925	Sistem zatvaranja farbara
68004935	Stalaža MDDW proizvodne linije
68004936	Stalaža MDDW proizvodne linije
68004942	Držač za dizanje rotora u vertikalu 4000kg
68004943	Držač za dizanje rotora u vertikalu 4000kg
68004944	Magnetni stalak za FARO ruku
68004945	C-kuka za dizanje tereta nosivosti 6t
68004952	Alat za montažu V1695-03 (Hybrid-Drive)
68004953	Alat za ubacivanje magneta V1628-9 (Hybrid-Drive)
68004954	Postolje za merenje i transport segmenta
68004955	Merač debljine prevlaka Elcometer 456 F model B
68004956	Laboratorijski jednodelni sudoper 120x75x90cm
68004957	Ormar sa fiokama
68004958	Ormar sa fiokama
68004959	Ormar sa fiokama
68004960	Radni sto 930 mm visok sa 4+1 fioke und 1 vrata
68004961	Ormar sa fiokama
68004962	Alat za žljeb ASP 1050-7-085
68004963	Alat za žljeb. ASP 1050-6-216 anf.
68004964	Alat za žljeb. ASP 1050-6-230 anf.
68004965	Alat za žljeb. ASP 1050-6-260 anf.
68004966	Alat pričvršćivanje (za strug)
68004967	Komplet za usisavanje (Torit)
68004968	Ormar za alat 717 mm sa 9 fioke i

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68004969	Sto sa mogucnosti dizanja TA 4000
68004970	Velika radna klupa/sto sa 3 ladice, 1 vrata
68004971	Ormar za alate sa 1+1+2+2 razlicita
68004972	Velika radna klupa/sto sa 2 ladice, 2 vrata
68004973	Velika radna klupa/sto sa 2 ladice, 2 vrata
68004974	Ormar za alte sa 9 fioka za izvlačenjem
68004975	Ormar sa kliznim vratima, sa 10 + 4 police
68004976	Niskoprofilna kolica za palete nosivost 1500kg
68004977	Elektro razvodni orman u hali br.3
68004978	Radni sto Garant Kompakt - Lserije 9 fioka, polica
68004980	Orman za skladištenje mape 10
68004981	Orman za skladištenje mape 10
68004982	Orman za skladištenje mape 10
68004983	Orman za skladištenje mape 10
68004984	Orman za skladištenje mape 10
68004985	Orman za skladištenje mape 10
68004986	Orman za skladištenje mape 10
68004987	Orman za skladištenje mape 10
68004988	Hidraulična dizalica za burad
68004989	Hidraulična dizalica za burad
68004990	Sto sa šablonom za kontrolu namotaja
68004991	E-dizalica EXD-S20 dupli štap sa fiksnim
68004992	Rotatori za zavarivanje
68004993	Ekstra duboki orman za odlaganje sa 4 police sv.si
68005032	Magacin za opasan otpad
68005034	Aparat za zavarivanje EWM Tetrix 351AC/DC Synergic
68005035	Jedinica za prečišćavanje vazduha
68005036	VAGA DIGITALNA CRANE SCALE 09-2011 110904
68005037	Stubna bušilica ALZMETALL AB 50/SV
68005038	Nosač namotaja za manuelno izoliranje
68005039	Nosač namotaja za manuelno izoliranje
68005040	Nosač namotaja za manuelno izoliranje
68005041	Nosač namotaja za manuelno izoliranje
68005042	Nosač namotaja za manuelno izoliranje
68005043	Nosač namotaja za manuelno izoliranje
68005044	Nosač namotaja za manuelno izoliranje
68005045	Nosač namotaja za manuelno izoliranje
68005046	Nosač namotaja za manuelno izoliranje
68005047	Nosač namotaja za manuelno izoliranje
68005048	Nosač namotaja za manuelno izoliranje
68005049	Nosač namotaja za manuelno izoliranje

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68005050	Seckalica za papir Fellowes AutoMax 500C
68005051	Pomoćni alat C hook (dizalica sa atestom)
68005052	Aku.hidraul. Makaze fi32mm
68005053	Mokro-suvi usisivač NT 70/2 * EU 1.667-269.0
68005054	Mokro-suvi usisivač NT 70/2 * EU 1.667-269.0
68005055	Mokro-suvi usisivač NT 70/2 * EU 1.667-269.0
68005056	Skladiste varilackih materijala
68005065	Industrijski usisivač IVS 100/55 M
68005066	Brusilica stubna dvostruka 2HP 1400rpm LTF
68005067	Paleta za montažu EP 302
68005068	Paleta za montažu EP 302
68005069	Paleta za montažu EP 302
68005070	Paleta za montažu EP 302
68005071	Paleta za montažu EP 302
68005072	Filterska jedinica sa ventilatorom
68005073	Filterska jedinica sa ventilatorom
68005074	Sigurnosni orman za zapaljive hemikalije T90 Class
68005075	Sigurnosni orman za zapaljive hemikalije T90 Class
68005076	Sigurnosni orman za zapaljive hemikalije T90 Class
68005077	Sigurnosni orman za zapaljive hemikalije T90 Class
68005078	Digestor za hemikalije sa ventilacijom dim 120x90x
68005079	Kiper paleta KP 66
68005080	Kiper paleta KP 66
68005081	Kiper paleta KP 100
68005082	Sigurnosni orman za zapaljive hemikalije T90 Class
68005083	Mašina za pranje B 40 C Bp Pack 9.502-335.0
68005084	Sigurnosni orman za zapaljive hemikalije T90 Class
68005085	Mašina za metenje KM 100/100
68005086	Alat za fiksiranje ASP1054-16
68005087	Centralni gasni sistem GD linije
68005088	Centralni gasni sistem DD linije
68005089	Radni sto sa fiokama 2000x880x700 sa multiplex rad
68005090	Radni sto sa fiokama 2000x880x700 sa multiplex rad
68005091	Klima uredjaj Gree 12
68005092	Klima uredjaj Gree 12
68005093	Klima uredjaj Gree 12
68005094	Klima uredjaj Polar
68005095	Hidraulična pumpa TMJL100
68005096	Hidraulične snažne kandže TMHP 60/600X
68005097	Ručna presa za spojnice za kablove i konektore AP
68005098	Ručna presa za spojnice za kablove i konektore AP

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68005103	Stalak za unutrašnji transport
68005104	Induktor za lemljenje
68005115	Sigurnosni orman za zapaljive hemikalije T90 Class
68005116	FLUKE 568 Infracrveni merac temperature
68005117	Električno vučno vozilo TPT HL 250 AC-EVO 70937
68005118	Zaštitna ograda oko male sačmare i testere 28x2 m
68005120	Aparat za zavarivanje Titan XQ350 puls D Expert XQ
68005121	Aparat za zavarivanje Titan XQ350 puls D Expert XQ
68005122	X button starter set za autorizaciju pristupa zava
68005123	Multiplikator momenta Walter Mx28, max. output 280
68005125	Barkod skener
68005126	C-kuka za dizanje tereta nosivosti 6t
68005128	Barkod skener
68005129	Barkod skener
68005130	Zastitna ograda kod viskoko naponske stanice
68005132	Gravitacioni regal
68005133	Nosac za FARO 4 merenje
68005134	Nosac za FARO 4 merenje
68005135	Nosac za FARO 4 merenje
68005136	Nosac za FARO 4 merenje
68005139	Televizor TOSHIBA 55" TV LED 55U6763DG
68005140	Stalak za C kuku
68005141	Stalak za C kuku
68005142	Barkod skeneri
68005143	Podizni sto ELS 8-13-G-SO
68005144	Podizni sto ELS 8-13-G-SO
68005145	Podizni sto ELS 8-13-G-SO
68005146	Podizni sto ELS 8-13-G-SO
68005147	Podizni sto ELS 8-13-G-SO
68005148	Podizni sto ELS 8-13-G-SO
68005150	Regal za DD skladište
68005151	Zastitini paravan za skolu zavarivanja
68005152	Laminator MLB 650 A1 format
68005153	Stubni kran
68005154	Stubni kran
68005155	Stubni kran
68005156	Mašina za pranje pištolja SATA
68005157	Mašina za sečenje izolacionih materijala
68005158	Uredjaj za ispitivanje smeru magnetnog polja
68005159	Uredjaj za ispitivanje smeru magnetnog polja
68005160	Uredjaj za ispitivanje smeru magnetnog polja

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68005161	Alu platforma Z600 jednostrana
68005162	Električna lančana dizalica
68005163	Električna lančana dizalica
68005164	Električna lančana dizalica
68005165	Laser sistem L Box
68005166	Platforma za ispitivanje generatora
68005167	Vertikalno skladište MX 75
68005168	Vertikalno skladište MX 75
68005169	Televizor Thoshiba 75U6763DG LED TV
68005185	Uredjaj za merenje otpadnih voda
68005190	Klima Tesla inv.
68005192	Kolica Fetra Etazna sa 4 utovarne povrsi
68005193	Kolica Fetra Etazna sa 4 utovarne povrsi
68005195	Industrijski ventilator KAISER KRAFT 800mm
68005196	Akumulatorske hidraulične makaze fi32mm
68005197	Akumulatroske hidraulične makaze fi 32mm
68005198	Akumulatroske hidraulične makaze fi 32mm
68005199	Akumulatroske hidraulične makaze fi 32mm
68005200	Zastitna ograda za laboratoriju
68005201	Zastitna ograda na liniji montaze
68005202	Set diskova za ulaganje stator
68005208	Podloga za hidraulični i hidrostatik sistem
68005209	Podloga za hidraulični sistem i agregat
68005210	Ormar za alat 717 mm sa 6 polica
68005211	Ormar sa kliznim vratima sa 10 polica
68005212	Kontejner za metalne opiljke 1,5cbm
68005213	Ormar sa običnim vratima
68005214	Sto za sastanke FlipTop Twin 140*70
68005215	Sto za sastanke FlipTop Twin 140*70
68005216	Sto za sastanke FlipTop Twin 140*70
68005217	Sto za sastanke FlipTop Twin 140*70
68005218	Sto za sastanke FlipTop Twin 140*70
68005219	Sto za sastanke FlipTop Twin 140*70
68005220	Sto za sastanke FlipTop Twin 140*70
68005221	Sto za sastanke FlipTop Twin 140*70
68005222	Sto za sastanke FlipTop Twin 140*70
68005223	Sto za sastanke FlipTop Twin 140*70
68005224	Industrijski orman za punjenje baterija GARANT dup
68005225	Industrijski orman za punjenje baterija GARANT dup
68005226	Industrijski orman za punjenje baterija GARANT dup
68005227	Industrijski orman za punjenje baterija GARANT dup

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68005228	Garant radni sto Kompakt sa tri fioke i vratima 11
68005229	Garant radni sto Kompakt sa tri fioke i vratima 11
68005230	Garant radni sto Kompakt sa tri fioke i vratima 11
68005231	Garant radni sto Kompakt sa tri fioke i vratima 11
68005232	Brusilica aku ETSC 125,Li3.1
68005233	Aksijalni ventilator WM8T 24 qteck
68005234	Aksijalni ventilator WM8T 24 qteck
68005235	Aluminijumska radna platforma sa čeličnom rešetkom
68005236	Aluminijumska radna platforma sa čeličnom rešetkom
68005237	Uređaj za lemljenje BV WLA25 Compact 25kVA
68005238	Pokretni radni sto za računar
68005239	ZARGES jednostrane merdevine sa radnom platformom
68005240	ZARGES jednostrane merdevine sa radnom platformom
68005241	ZARGES jednostrane merdevine sa radnom platformom
68005242	Sonda Elcometer 456 pod uglom
68005243	Sonda Elcometer 456 pod uglom
68005244	Mokro suvi usisivač NT 70/2
68005245	Police za alate
68005246	Regali za rashladnu komoru u hali 3
68005248	Zaštitna ograda za ispitnu stanicu, Stator
68005249	Aku presa Weitkowitz APW18
68005250	Aku presa Weitkowitz APW18
68005251	Aku presa Weitkowitz APW18
68005252	Vertikalno skladiste MX75
68005253	Dodavač žice WM tigspeed drive 12P 4M flex 94.5001
68005254	Stalak za busenje kucista
68005255	Visokonaponski DC Generator-Heinzinger s.385215121
68005256	Vertikalno skladiste MX75
68005257	Klima 18
68005258	Platforma-stanica
68005263	Ormar sigurnosni Halex tip 90 sa tri police 1200x6
68005264	Usisivac
68005265	Sto sa stegama
68005266	Sto sa stegama
68005267	Sto sa stegama
68005268	Celicna paleta
68005269	Celicna paleta
68005270	Celicna paleta
68005271	Celicna paleta
68005272	Celicna paleta
68005273	Celicna paleta

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68005274	Ormar za punjenje baterija
68005275	Razvodni ormar
68005276	Zavarivacke kabine sa zavesama
68005277	Oprema za napajanje
68005278	Nosac namotaja
68005279	Industrijski ormar
68005280	Zastitni prsten za rotor
68005281	Susara sa ventilatorom
68005282	Ploce za medjupresovanje DD9 alata
68005283	Šablon za namotaje DD3CW
68005284	Šablon za namotavanje DD9
68005287	Alat za simuliranje priključivanja kablova EP 318
68005288	Alat za limpaketiranje segmenta DD76
68005289	Alat za limpaketiranje segmenta DD76
68005290	Ostrilica za burgije Darex V-3
68005291	Kranska vaga
68005292	Ormar za ulaznu kontrolu
68005293	Gravitacioni regali
68005294	Kolica za limpaketiranje DD37
68005295	Kolica za limpaketiranje DD37
68005296	Kolica za limpaketiranje DD37
68005297	Kolica za limpaketiranje DD37
68005298	Kolica za limpaketiranje DD37
68005299	Kolica za limpaketiranje DD37
68005300	Kolica za limpaketiranje DD37
68005301	Kolica za limpaketiranje DD37
68005302	Kolica za limpaketiranje DD37
68005303	Kolica za limpaketiranje DD37
68005304	Kolica za limpaketiranje DD37
68005305	Kolica za limpaketiranje DD37
68005306	Kolica za limpaketiranje DD37
68005307	Kolica za limpaketiranje DD37
68005308	Kolica za limpaketiranje DD37
68005310	Grejac Indukcioni 400 FAG
68005311	Blankerica
68005312	Blankerica
68005313	Roleri za ciscenje statora
68005314	Roleri za ciscenje statora
68005315	Roleri za ciscenje statora
68005316	MICRON set baterija MPP 600
68005317	MICRON set baterija MPP 600

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68005318	Uredjaj za tackasto oznacavanje
68005319	Uredjaj za tackasto oznacavanje
68005320	Stalak sa točkicama (tronozac) 36"-54"
68005322	Alat za paketiranje EP 314
68005323	Ulazna rampa
68005324	Uredjaj za napajanje UPS
68005325	Uredjaj za napajanje UPS
68005326	Kolica za transport generatora 25t
68005327	Kolica za transport generatora 25t
68005328	Kolica za transport generatora 25t
68005329	Kolica za transport generatora 25t
68005330	Kolica za transport generatora 25t
68005331	Kolica za transport generatora 25t
68005332	Kolica za transport generatora 25t
68005333	Kolica za transport generatora 25t
68005334	Kolica za transport generatora 25t
68005335	Kolica za transport generatora 25t
68005336	Kolica za transport generatora 25t
68005337	Kolica za transport generatora 25t
68005353	Zastitna stranica za DD3
68005354	Zastitna stranica za DD3
68005355	Zastitna stranica za DD3
68005356	Zastitna stranica za DD3
68005357	Mobilna dizalica HYWEMA-Axle Stand AV 7,5 KF
68005358	Mobilna dizalica HYWEMA-Axle Stand AV 7,5 KF
68005359	Mobilna dizalica HYWEMA-Axle Stand AV 7,5 KF
68005360	Mobilna dizalica HYWEMA-Axle Stand AV 7,5 KF
68005361	Usisivac 575298 CTM 48 E LE EC
68005362	Mašina za ispravljanje i sečenje
68005365	Ventilator aksijalni sa postoljem
68005366	Ventilator aksijalni sa postoljem
68005367	Ventilator aksijalni sa postoljem
68005368	Ventilator aksijalni sa postoljem
68005369	Televizor Tesla 55S903SUS 55 inca slim smart HD
68005373	Metalna paleta sa tankom 1400* 1400mm
68005374	Metalna paleta sa tankom 1400* 1400mm
68005375	Metalna paleta sa tankom 1400* 1400mm
68005376	Metalna paleta sa tankom 1400* 1400mm
68005377	Metalna paleta sa tankom 1400* 1400mm
68005378	Metalna paleta sa tankom 1400* 1400mm
68005379	Metalna paleta sa tankom 1400* 1400mm

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68005380	Metalna paleta sa tankom 1400* 1400mm
68005381	Metalna paleta sa tankom 1400* 1400mm
68005382	Metalna paleta sa tankom 1400* 1400mm
68005383	Metalna paleta sa tankom 1400* 1400mm
68005384	Metalna paleta sa tankom 1400* 1400mm
68005385	Metalna paleta sa tankom 1400* 1400mm
68005386	Metalna paleta sa tankom 1400* 1400mm
68005387	Metalna paleta sa tankom 1400* 1400mm
68005389	Sigurnosni orman jednokrilni ASECOS "SC tip 90"
68005390	Rucni paletar sa elektronskom vagom
68005393	Merdevine pokretne sa 7 gazišta
68005394	Merdevine pokretne sa 7 gazišta
68005395	Oprema za manipulaciju segmentima
68005396	Oprema za mesto paketiranja
68005397	Stalak opreme za hidraulično presovanje segmenta
68005398	Nosač za izrađene namotaje
68005399	Nosač za izrađene namotaje
68005400	Nosač za izrađene namotaje
68005401	Nosač za izrađene namotaje
68005402	Nosač za izrađene namotaje
68005403	Nosač za izrađene namotaje
68005404	Nosač za izrađene namotaje
68005405	Nosač za izrađene namotaje
68005406	Nosač za izrađene namotaje
68005407	Nosač za izrađene namotaje
68005408	Nosač za izrađene namotaje
68005409	Nosač za izrađene namotaje
68005410	Nosač za izrađene namotaje
68005411	Nosač za izrađene namotaje
68005412	Nosač za izrađene namotaje
68005415	Mikser za mesanje malih kanti GRACO
68005416	Sigurnosni orman FWF 30, 1115*55*1950mm250l filter
68005417	Usisivac kompaktni za tecnosti IVL 50/24-2
68005419	Zaštitna ograda oko vertikalnog struga
68005422	Set steznih celjusti ST 346-13
68005423	Orman sa fiokama
68005424	Police za alat
68005425	Police za alat
68005426	Police za alat
68005427	Orman sa fiokama
68005429	Fleksibilni nosač LED svetiljke

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68005430	Fleksibilni nosač LED svetiljke
68005431	C Kuka za podizanje statora
68005432	Projektor
68005434	Stalak za hladjenje sa prstenom za EP318
68005435	Stalak za hladjenje sa prstenom za EP318
68005436	Stalak za hladjenje sa prstenom za EP318
68005437	Stalak za hladjenje sa prstenom za EP318
68005438	Orman GARANT stubni za racunar 1620x750x550cm
68005439	Orman GARANT stubni za racunar 1620x750x550cm
68005440	Orman GARANT stubni za racunar 1620x750x550cm
68005441	Merdevine pokretne sa 7 gazista Zarges
68005442	Merdevine pokretne sa 3 gazista Zarges
68005443	Koordinatni sto 650250mm
68005444	Paletar rucni sa elektronskom vagom Liftex Gravity
68005445	Tankvan sa resetkama i policama za magacin opasnog
68005446	Termalni stampac za markere na rolni sa sekacem
68005447	Radni sto za paketiranje
68005448	Radni sto za paketiranje
68005449	Radni sto za paketiranje
68005450	Radni sto za paketiranje
68005451	Radni sto za paketiranje
68005452	Radni sto za paketiranje
68005453	Radni sto za paketiranje
68005454	Radni sto za paketiranje
68005455	Radni sto za paketiranje
68005456	Radni sto za paketiranje
68005457	Radni sto za paketiranje
68005458	Radni sto za paketiranje
68005459	Radni sto za paketiranje
68005460	Radni sto za paketiranje
68005461	Radni sto za paketiranje
68005462	Radni sto za paketiranje
68005463	Radni sto za paketiranje
68005464	Radni sto za paketiranje
68005465	Radni sto za paketiranje
68005466	Radni sto za paketiranje
68005468	Aluminijumske platforme za zavarivanje
68005469	Aluminijumske platforme za zavarivanje
68005470	Aluminijumske platforme za zavarivanje
68005471	Aluminijumske platforme za zavarivanje
68005472	Aluminijumske platforme za zavarivanje

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68005473	Aluminujumske platforme za zavarivanje
68005474	Aluminujumske platforme za zavarivanje
68005475	Aluminujumske platforme za zavarivanje
68005476	Aluminujumske platforme za zavarivanje
68005477	Aluminujumske platforme za zavarivanje
68005478	Aluminujumske platforme za zavarivanje
68005479	Aluminujumske platforme za zavarivanje
68005480	Aluminujumske platforme za zavarivanje
68005481	Aluminujumske platforme za zavarivanje
68005482	Aluminujumske platforme za zavarivanje
68005483	Aluminujumske platforme za zavarivanje
68005484	Aluminujumske platforme za zavarivanje
68005485	Aluminujumske platforme za zavarivanje
68005486	Aluminujumske platforme za zavarivanje
68005487	Aluminujumske platforme za zavarivanje
68005488	Postolje za hladjenje
68005489	Gvozdena paleta za u.transport A5E47101192A_002_AB
68005490	Usisivač 26 l - CTL 26 E, Festool sa adapterom
68005491	Usisivač 26 l - CTL 26 E, Festool sa adapterom
68005492	Stalkovi za DD9
68005493	Stalkovi za DD9
68005494	Stalkovi za DD9
68005495	Stalkovi za DD9
68005496	Stalkovi za DD9
68005497	Stalkovi za DD9
68005498	Stalkovi za DD9
68005499	Stalkovi za DD9
68005500	Stalkovi za DD9
68005501	Stalkovi za DD9
68005502	Stalkovi za DD9
68005503	Stalkovi za DD9
68005504	Stalkovi za DD9
68005505	Stalkovi za DD9
68005506	Stalkovi za DD9
68005507	Stalkovi za DD9
68005508	Radni sto model 933452 2000/6
68005509	Permanentni magnetni lift 600kg
68005510	Permanentni magnetni lift 600kg
68005511	Metalna tankvana sa ogradom za 4 bureta
68005512	Metalna tankvana sa ogradom za 4 bureta
68005513	Ormar za odlaganje buradi

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68005514	Ormar za odlaganje buradi
68005515	Ormar za ulaznu kontrolu
68005517	Odvijač udarni akumulatorski Milwaukee
68005518	Radna platforma ZARGES Z600
68005519	Radna platforma ZARGES Z600
68005520	Kontejner - kiper mode TIPPO HD900
68005521	Kontejner - kiper mode TIPPO HD900
68005522	Kontejner - kiper mode TIPPO HD900
68005523	Kontejner - kiper mode TIPPO HD900
68005524	Kontejner - kiper mode TIPPO HD900
68005525	Kontejner - kiper mode TIPPO HD900
68005526	Kontejner - kiper mode TIPPO HD900
68005527	Kontejner - kiper mode TIPPO HD900
68005528	Kontejner - kiper mode TIPPO HD900
68005529	Kontejner - kiper mode TIPPO HD900
68005530	Kontejner - kiper mode TIPPO HD900
68005531	Kontejner - kiper mode TIPPO HD900
68005532	Paletni regal F15
68005533	Magacinski kontejner 6058x2438x2591mm
68005534	Magacinski kontejner 6058x2438x2591mm
68005535	Grejac lezajeva SKF TIH 220M/V
68005536	Kontejner - kiper mode TIPPO HD900
68005537	Kontejner - kiper mode TIPPO HD900
68005538	Kontejner - kiper mode TIPPO HD900
68005539	Kontejner - kiper mode TIPPO HD900
68005540	Štampač za termo bužire THERMOMARK ROLL 2.0
68005542	Hilma- Linearna masinska stega sa svom propr.oprem
68005543	Hilma- Linearna masinska stega sa svom propr.oprem
68005544	Linerana letva za zatvaranje vrata DGP-40-1100-PPV
68005545	Sigurnosna laserska barijera S/N: 07210392
68005546	Sigurnosna laserska barijera S/N: 07210392
68005547	Stezna glava od sivog liva sa tri stezne celjusti
68005548	Palet police za 11 dela BE 2239-01
68005549	Podizni sto ELS 8-13-G-SO
68005550	El. vaga HERCULES 1200x800 A12 1500Kg
68005551	Stega masinska hidraulicna 160 mm
68005552	Stega masinska hidraulicna 160 mm
68005553	Kranska vaga 10t sa obrtnom rukom i daljinskim
68005554	Radni sto za proizvodnju Garant visina 850mm 1500
68005555	Kocke celicne za merni sto
68005556	Kocke celicne za merni sto

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68005557	Kocke celicne za merni sto
68005558	Kocke celicne za merni sto
68005559	Kiper paleta KP100
68005560	Stubna dizalica
68005561	Prsten za presovanje rot.lim paketa A5E3645243A
68005562	Prsten za presovanje rot.lim paketa A5E3645243A
68005563	Prsten za presovanje rot.lim paketa A5E3645243A
68005564	Prsten za presovanje rot.lim paketa A5E3645243A
68005565	Prsten za presovanje rot.lim paketa A5E3645243A
68005566	Prsten za presovanje rot.lim paketa A5E3645243A
68005567	Prsten za presovanje rot.lim paketa A5E3645243A
68005568	Televizor 65 inca sa nosacem
68005569	Televizor 65 inca sa nosacem
68005570	Stalak za hladjenje rotora A5E49285508A
68005571	Stalak za hladjenje rotora A5E49285508A
68005572	Stalak za hladjenje rotora A5E49285508A
68005573	CrimpLamb Vacuum cleaner-Convac 3000-PQ
68005574	Projektor
68005575	Jednokrilni sigurnosni orman FWF 90 130l
68005576	Jednokrilni sigurnosni orman FWF 90 130l
68005581	Sreder za papir Fellowes Automax 550C
68005582	Samoistovarujući kiper kontejner TIPPO HD900
68005583	Samoistovarujući kiper kontejner TIPPO HD900
68005584	Uredaj za varenje vakum vreća
68005585	Uredaj za varenje vakum vreća
68005586	Duboki orman sa 4 police,extra
68005587	Duboki orman sa 4 police,extra
68005588	Metalni sto za Einrich mixer-protofer
68005589	Inustrijski orman za punjenje baterija Garant
68005590	Osnovni orman Gridline s 2000
68005591	Osnovni orman Gridline s 2000
68005592	Mikser Planetarni Italy line 20 L
68005593	Prenosni detektor gasa O2 Hoynewell
68005594	Nosila za vertikalni transport DX030
68005595	Vodeno kupatilo za kontrolu smole
68005596	Sreder za papir Fellowes 125 CI
68005597	Sreder za papir Fellowes 125 CI
68005598	Radnicki sto 2000 Garant Gridiline
68005599	Metalne palete za odlaganje DD alata
68005600	Metalne palete za odlaganje DD alata
68005601	Metalne palete za odlaganje DD alata

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

68005602	Metalne palete za odlaganje DD alata
68005603	Metalne palete za odlaganje DD alata
68005604	Metalne palete za odlaganje DD alata
68005605	Metalne palete za odlaganje DD alata
68005606	Metalne palete za odlaganje DD alata
68005607	Metalne palete za odlaganje DD alata
68005608	Metalne palete za odlaganje DD alata
68005609	Paletni regal
68005610	Aksijalni ventilator sa postpljem
68005611	Aksijalni ventilator sa postpljem
68005612	Aksijalni ventilator sa postpljem
68005613	Aksijalni ventilator sa postpljem
68005614	Transportne grede
68005615	Transportne grede
68005616	Mixer EL10 Profi plus 031693 za mesanje protofera
68005617	Traverzni nosac 2m 10T-Lifting Beam
68005618	Traverzni nosac 2m 10T-Lifting Beam
68005619	Paletni regal-Meta
68005621	Nosač namotaja bakarnih traka-stator
68005623	Aparat za zavarivanje Tetrix 451 synergic FW
68005541	Klima Viola 12k btu
68005428	Svetleća reklama SIEMENS
68005622	Prenosni RFID čitač HS9 bluetooth HF 13.56MHz
99001865	Neutralizator emisije štetnih materija
99002075	Oprema za merenje faktora gubitka Tando 700 Tan+D
99002083	Računar 6AV7241-5RB07-0DA2 SIMATIC IPC 477E 100kom
99002125	R-ISE-VMS-K9= Cisco ISE Virtual Machine sa licenca
99002126	R-ISE-VMS-K9= Cisco ISE Virtual Machine sa licenca
99002127	FPR2110-NGFW-K9 Cisco Firepower2110 NG sa licencam
99002128	FPR2110-NGFW-K9 Cisco Firepower2110 NG sa licencam
99002190	Alat FPT
99002191	Alat DORRIES
99002291	Modernizacija Balans mašine HM7U
68005620	Epson projektor EH-TW650
62201991	Notebook racunar HP Probook 640 G2
62202236	WIN10 HP Probook 640 G4
5255100000001	BG 1210-BV OPEL INSIGNIA INNOVATION D20DTR/1345016
5255100000008	BG 1024-RL SKODA SUPERB STYLE 2.0TDI/1509217
5255400000010	Hala 1 – 8819/11 Hala 2 – 8820/11 Hala 4.1 – 8818/11

UGOVOR O STATUSNOJ PROMENI IZDVAJANJA UZ PRIPAJANJE

Siemens doo Beograd / Flender doo Subotica

Dodatak 3.1.1 Preneta osnovna sredstva

525540000010	Sladiste opasnih materija – 13940/16 Parking - 12277/15
525540000011	Hala 3 – 10493/13
525540000012	16555/19