
SIEMENS



S7-200 SMART

Programmable Controllers

siemens.com



Siemens has been committed to the R&D, promotion and application of industrial automation technology. In the past 160 years, we have have brought reliable and efficient automation products and perfect automation solutions to industrial customers, improving the production efficiency of customers and enhancing customer's market competitiveness.

A vast number of industrial customers have brought reliable and efficient automation products and perfect automation solutions, which have improved the customer's Production efficiency enhances the customer's market competitiveness.

The Siemens SIMATIC controller family is a complete product portfolio, including from the basic intelligent logic controller LOGO! And S7 series high-performance programmable controller, and then to PC-based automation control system. No matter how Strict requirements, it can be flexibly combined and customized according to specific application needs and budget, and meet them one by one.

SIMATIC S7-200 SMART is a cost-effective small PLC product tailored for customers after extensive market research by Siemens. Combined with Siemens SINAMICS drive products and SIMATIC man-machine interface products, the small automation solution with S7-200 SMART as the core will create more value for Indian customers.




Table of Contents

Product Highlights4	Analog Input/Output Module Specifications2
CPU module6	Digital input / output signal board technical specifications2
Signal board8	Analog input signal board specification2
Telecommunication9	Analog output signal board specification2
Motion control10	RS485/232 signal board technical specifications2
Programming software12	Battery signal board technical specification2
Small automation solution14	Thermal resistance module specification2
Specifications16	Thermocouple Module Specifications2
CPU SR20/ST20 Technical Specifications16	PROFIBUS-DP slave communication module2
CPU SR30/ST30 Technical Specifications18	Power module2
CPU SR40/ST40 Technical Specifications20	Installation dimension drawing2
CPU SR60/ST60 Technical Specifications22	Order number description2
Digital input module technical specification24	Module and signal board wiring diagram3
Digital output module technical specification24	Economical CPU overview3
Digital Input / Output Module Specifications25	Economic CPU specification3
Analog input module specification26	Economical CPU wiring diagram3
Analog Output Module Specifications26	Ordering data

SIMATIC S7-200 SMART

Product Highlights



More models, more choices

It provides CPU modules that have a large number of I/O points onboard (up to 60 points.) The CPU module has a standard type and compact type for the users to choose, which can meet the different needs of customers.



Extension options, accurate customization

The new signal boards are designed with scalable communication ports, digital or analog channels, that are closely fitting to the user's application requirements, and lower the user's costs for expansion.



High speed chip, excellent performance

It is equipped with Siemens dedicated processor chip, the basic instruction execution time is up to 0.15 μ s, it has the leading performance compared to the micro PLC of the same level, it can easily deal with complex and fast processes.



Ethernet interconnectivity, economic and convenient

The standard Ethernet interface of the CPU supports various industrial Ethernet communication protocols such as PROFINET, TCP, UDP, Modbus TCP. Through this interface, it can also communicate with other PLCs, touch screens, inverters, servo drives, host computers and so on. The program can be downloaded to the PLC using a common network cable, eliminating the need for dedicated Programming cable, economical and fast

Multi-axis operation control, flexible and free


The CPU module body integrates up to 3 high-speed pulse outputs with a frequency up to 100 KHz, supports PWM/PTO output mode, and supports up to 3-axis linear interpolation. Multiple motion modes drive the servo drive easily.

The integrated PROFINET interface of the CPU can connect multiple servo drives, and with the convenient and easy-to-use SINAMICS motion library instructions, it can quickly realize the operation and control functions such as equipment speed regulation and positioning.



Common SD card, fast update

This PLC integrates Micro SD card slot, supports common Micro SD card, can be used to update the program or device firmware, and can provide great convenience to the engineer who conducts the field service.



Friendly software, efficient programming

Based on the powerful functions inherited from the Siemens programming software, it has absorbed more humanized design which has enhanced the user friendliness of the software greatly. Improved the efficiency in developing the program.

The **SMART Web Editor** tool can customize the Web page, relying on the **PLC Web server** function, Provide customers with flexible custom pages.



Perfect integration, seamless integration

The perfect integration of SIMATIC S7-200 SMART, Basic HMI and SINAMICS V20/V90, forms the micro automation solutions that is cost-effective; meeting the OEM customer's full range of demand.



SR/ST CPU Module

The new S7-200 SMART CPU module can meet the needs of different industries, different customers and different equipment. The SR/ST standard CPU can expand 6 expansion modules and 1 signal board for applications with more I/O points and more complex logic control.



Туре	CR40	CR60	SR20	SR30	SR40	SR60	ST20	ST30	ST40	ST60
High speed counter	4 at 100 single					6 💐	Vew			
High speed pulse output			_	_			2 at 100 kHz		3 at 100 kHz	
Number of communication ports	2	2				2 -	~ 4			
Number of Expansion modules	-	_					5			
Maximum I/O handling capacity ³⁾	40	60	216	226	236	256	216	226	236	256
Maximum analogue I/O 3)	-	_				4	9			

 $^{^{\}rm 3)}$ The maximum I/O handling capacity is considering I/O expansion with Signal boards.

SR/ST CPU module



Signal Board

The signal board is mounted directly on the front of the CPU body; without occupying the cabinet space, its installation and disassembly are convenient and quick. For a small amount of I/O points extension and more demand for communication ports, the signal board with new design can provide more economical and flexible solutions.



Basic information of the signal board

Model	Specification	Description
SB DT04	2DI/2DO transistor output	It provides additional digital I/O extensions, and support 2 digital inputs and 2 digital transistor outputs.
SB AQ01	1AO	It provides additional analogue I/O extension, and support 1 analogue output, with a precision 12 bits.
SB CM01	RS232/RS485	It provides additional RS232 or RS485 serial communication interface, the conversion can be realized via simple configuration in the software.
SB BA01	Battery module	It supports the generic CR1025 cell (battery), which can drive the clock for about 1 year.
SB AE01	1AI	It Provides additional analog I/O expansion to support 1. Al with 12 bits of precision



Signal board configuration

When the standard CPU module is selected in the system block, the aforementioned four signal boards will display the SB options:

- When SB DT04 is selected, the system can automatically distribute I7.0 and Q7.0 as the beginning of the I/O image area
- When SB AE01 is selected, the system automatically assigns AIW12 as the I/O image area.
- When SB AQ01 is selected, the system can automatically allocates AQW12 as the I/O image area
- When SB CM01is selected, it can be done via selecting the RS232 or RS485 in the port type setting box.
- When SB BA01 is selected, the low power consumption alarm can be initialized or the power consumption state can be monitored via I7.0.

Installation steps



Remove the cover board of terminal



Remove the cover board with Screw driver



No fastening screw is required, gently insert it



The installation is complete

SR/ST CPU Network communication

The S7-200 SMART SR/ST CPU module body integrates 1 PROFINET interface and 1 RS485 interface. By expanding the CM01 signal board or EM DP01 module, the number of communication ports can be increased to up to 4, which can meet small automation devices and touch screens. Inverters, servo drives and third-party devices



Ethernet communication

SR/ST CPU integrated PROFINET interface, supports multiple protocols, and efficiently connects various devices:

- PROFINET communication: communication with the drive or servo drive, supporting up to 8 devices
- Can be used as a program download port, supports web server function, & customers can customize the web interface
- Can be used as a program download port (using a normal network cable)
- Supports Ethernet communication between multiple PLCs: Supports 8 active and 8 passive PUT/GET connections
- Open Ethernet communication: supports various communication protocols such as TCP, UDP, ISO_on_TCP, Modbus TCP, etc. Support 8 active and 8 passive connections



The S7-200 SMART SR/ST CPU can be connected as a PROFIBUS-DP slave to the PROFIBUS communication network using the EM DP01 expansion module. The PROFIBUS-DP slave address can be set via the rotary switch on the module. The module Supports any PROFIBUS baud rate between 9600 baud and 12 M baud, allowing up to 244 input bytes and 244 output bytes.

The following protocols are supported:

- MPI slave
- PROFIBUS-DP slave

Serial communication

The S7-200 SMART CPU modules are integrated with one RS485 interface and can communicate with third-party devices such as inverters and touch screens. If an additional serial port is required, it can be realized by extending the CM01 signal board, and the signal board supports RS232/RS485 free conversion.


The serial port supports the following protocols:


- Modbus RTU
- USS
- Free port communication


Communication with the host computer


Using Siemens PC Access tool, it is possible to read the data from S7-200 SMART on to the host computer. This can be used for simple GUI requirements for data monitoring or data archiving.

(PC Access is an OPC server protocol specifically developed for S7-200 series PLC, an OPC software dedicatedly developed for interaction between the micro PLC and host computer)











Motion Control

The S7-200 SMART transistor output type CPU module body provides up to three-axis 100 KHz high-speed pulse output, which can be configured as PWM output or motion control output through a powerful and flexible setup wizard, and supports up to 3-axis linear interpolation function. Provides a unified solution for speed and position control of stepper motors or servo motors.

The S7-200 SMART SR/ST CPU uses the integrated PROFINET interface to control the servo drive by means of communication, The wiring between devices is further reduced, and the response time of the devices is shortened, so as to meet the positioning requirements of small mechanical devices.





Basic functions of motion control

The S7-200 SMART CPU provides four open-loop motion control methods:


- Pulse Train Output (PTO): Speed and position control built into the CPU.
 This function onlyTo provide pulse train output, direction and limit control must be provided by the application program using I/O integrated in the PLC or provided by expansion modules.
- Pulse Width Modulation (PWM): Speed, position, or duty cycle control
 built into the CPU. If PWM output is configured, the CPU will fix the cycle time of the output, and control the pulse duration or duty cycle
 through the program. The speed or position of the application can be
 controlled by varying the pulse duration.
- Motion axes: built into the CPU for speed and position control. This feature provides a single pulse train output with integrated direction control and disable outputs, also includes a programmable input, and offers multiple modes of operation including automatic reference point search
- Motion axis group: supports PTO-based open-loop axis group function, some support 2-axis or 3-axis linear interpolation function, and can support the Move_Path function through the motion control wizard Multi-segment path planning is possible.

PWM and Motion Control Wizard Setup

In order to simplify the use of the position control function in your application program, the position control wizard provided by STEP 7- Micro/WIN SMART can help you complete the configuration of PWM and PTO within a few minutes. The wizard can generate position control instructions that you can use in your Dynamically control speed and position in your application.

The PWM wizard setting generates the corresponding PWMx_RUN subroutine frame for editing according to the number of PWM pulses selected by the user.

Use the Motion Wizard to configure axes groups and generate POUs (Program Organizational Units) to command 2D/3D linear interpolation movements of axes groups from actual positions to absolute or relative target positions




Control of SINAMICS servo drives with PROFINET

In order to simplify the control program and programming steps, STEP 7- Micro/WIN SMART integrates two sets of SINAMICS library instructions for easy PROFINET control servo positioning:

- SINAMICS_Control:
 - SINA_POS: Controls drive position via 8 different operating modes
 - SINA_SPEED: Control drive speed
- SINAMICS Parameter:
 - SINA_PARA_S: read drive parameters or modify drive parameters

Note: Supported by STEP 7-Micro/WIN SMART V2.4 and above



PROFINET wizard and SINAMICS library make programming easier

Steps for connecting the S7-200 SMART CPU to the SINAMICS V90 PN servo drive:

- The SINAMICS V90 PN drive and servo motor are ready
- The drive and the S7-200 SMART CPU are connected to the PROFINET network
- The V-assistant software is connected to the SINAMICS V90 PN and has been configured for the V90PN Set relevant parameters (V-assistant software is V90PN debugging software)
- Add the GSDML file of the corresponding device to the STEP 7-Micro/WIN SMART software. Use the PROFINET wizard to set drive related parameters and configuration
- Call the SINAMICS library program and write the relevant program according to the control requirements



User-friendly & Efficient Software

STEP 7- Micro/WIN SMART is the programming configuration software of S7-200 SMART, which can run smoothly on Windows 7 SP1 or Windows 10 operating system, supports LAD (ladder diagram), STL (statement list), FBD (function block diagram)Programming languages, some languages can be freely converted. More user-friendly designs make programming easier to learn and development more efficient. The SMART Web Editor tool assists customers in creating a user-defined Web page project and downloading the project to a Web server

Full support for Windows 7 and Windows 10 operating systems

- Operating system: Windows 7 or Windows 10 (both 32-bit and 64-bit versions)
- At least 350 Mbytes of free hard disk space

New menu design


It has no more traditional drop-down menu. It has adopted the band-type menu design, all menu options can be seen completely. The image of the icon display makes the operation more convenient.


By double clicking on the menu, it can be hidden so as to provide more space for a visual programming window.

Fully movable window design

All windows in the software interface can move freely, and provide eight kinds of drag and drop methods.

The main window, the program editor, the output window, variable table, state diagram etc. windows can be combined according to the user's habits, maximally improve the programming efficiency.






The definitions of variables and program notes

The users can define the variable name according to the process flow, and can call through the variable name directly, allowing users to fully enjoy the convenience of high-level programming language. A special function registers the address call, automatically naming the variable, which can now be called directly the next time.

Micro/WIN SMART provides a perfect function for annotation, can add annotations to program block, programming network and variables, with its readability greatly improved. When the mouse is moved to the instruction block, data types supported by each pin are automatically displayed.



STEP 7-Micro/WIN SMART Software features:

- 1. New menu design 2. Fully movable window design
- 3. Variable definitions and notes 4. Novel wizard setting
- 5. Status monitoring 6. Convenient command Library
- 7. Powerful password protection functions

For detailed information about the software, consult the S7-200 SMART System Manual.



Setup wizard

Micro/WIN SMART integrates the quick and easy wizard setup function, just follow the wizard prompts to set the parameters of each step to complete the complex function settings. The new wizard feature allows the user to directly set the function of one of the steps, and the modified wizard does not need to reset each step.

The wizard settings support the following features:

- HSC (High Speed Counting)
- sport control
- PID
- PWM (Pulse Width Modulation)
- Text display
- GET/PUT
- Data log
- PROFINET

Status monitoring

In the Micro/WIN SMART status graph, it can monitor the current values of each input / output channel of PLC, at the same time, it can conduct the mandatory input operation to test the program logic for each channel.

Status monitoring value can be displayed in numerical form, and can also be directly displayed in the waveform, the aforementioned two can also be switched each other.

In addition, the Micro/WIN SMART system can monitor the PID and motion control operation, equipment operation status through the dedicate operation panel.


Convenient command Library


In PLC programming, the same tasks that are repetitively executed will be generally included in a subprogram, which can be directly used in the future. The use of subroutines can better organize the program structure, facilitate the debugging and reading.


Micro/WIN SMART provides the command library functions, converting the subroutine into a block of instructions, as a common block of instructions, which will be directly dragged and dropped into the programming interface to complete the call. The command library function provides password protection function, preventing the database files from being randomly reviewed or modified.

The Micro/WIN SMART software automatically integrates the Modbus RTU communication library, the Modbus TCP communication library, the open user communication library, the PN Read Write Record library, the SINAMICS library, and the USS communication library.

In addition, Siemens offers a large instruction library to complete a variety of functions, which can be easily added into the software.








SMART Automation Solution

The combination of Siemens SIMATIC automation products and SINAMICS drive products, the cost-effective SIMATIC S7-200 SMART PLC, SIMATIC Basic touch screen, SINAMICS V20 inverter and SINAMICS V90 servo system bring perfect machine builders

A small automation solution that covers the full range of user needs for human-computer interaction, automation and drive. This solution helps users improve the performance of machinery and equipment, reduce development costs, significantly reduce the time-to-market of machinery and equipment, and effectively



For any information about SMART's small automation solutions, please visit www.siemens.co.in/automation/in/en/automation-systems/industrialautomation/ s7-200-smart-plc/pages/default.aspx

S7-200 SMART Recommendations:

- When programming and debugging, it is recommended to have one ordinary switch to connect related equipment (including PLC, touch screen, computer, inverter, servo drive, etc.) to the switch. After downloading the PLC or touch screen program, you can directly perform the touch test on the touch screen to check the working status of the PLC without connecting the PLC and the touch screen with cables.
- Quick and batch download of PLC programs using the Micro SD card. The produced source card can be sent to the end user via courier. When the customer puts forward various urgent needs on site, the source files in the card are directly sent to the on-site users via Email. After receiving, the source files can be copied to the Micro SD card for use.

C Р

M

N

М

C

9

0

S

N

M

C

٧



SIMATIC S7-200 SMART





SIMATIC Basic Panels 2nd Generation

- SR/ST CPU module with 20I/O, 30I/O, 40I/O, 60I/O configurations
- Expandable communication port, analog channel, digital channel and clock hold function via signal board
- SR/ST CPU module body integrates PROFINET interface and RS485 serial port, supports PN interface download program
- Supports communication such as PN, TCP, Modbus TCP, UDP, Modbus RTU, USS, PROFIBUS-DP
- •The body integrates up to 3 channels of 100KHz high-speed pulse output, supporting up to 3axis linear interpolation
- PN devices such as servo drives and inverters can be connected via the PROFINET network



- •The device family offers Panels with 4", 7", 9" and 12" displays, as well as combined key and touch operation.
- The innovative high-resolution widescreen displays with 64 000 colors are also suitable for upright installation, and they can be dimmed down to 100%
- Efficient engineering -Create your visualization faster and more easily than ever before!
- •Innovative design and operation-Make visualizing the calling card for your machine!
- •Brilliant HMI devices-Use the right HMI device for your application!
- •Safe and secure-Protect your investment, your know-how and ensure reliable operation!
- •Commissioning in the fast lane-Waste no time with testing and servicing!
- •Openness with PC-based-You and your applications remain flexible and independent!



SINAMICS V90 SIMOTICS S-1FL6

- 1/3 phase 220V power supply, covering power range from 0.05 kW to 2 kW
- 3-phase 380 V power supply covering power ranges from 0.4 kW to 7 kW
- One drive system for external pulse position control, internal set point position control, speed control and torque control System, accurate and efficient
- USS, Modbus RTU communication & Full power standard brake resistor
- Real-time automatic optimization and harmonic suppression
- Supports high speed pulse input up to 1 MHz & 20 bit high precision encoder
- · Powerful and convenient debugging software, user-friendly design, rich debugging functions, and more efficient development



SINAMICS V20

- Single-phase 230 V power range from 0.12 to 3 kW, three-phase 400 V power range from 0.37 to 30 kW, integrated V/f, V2/f, FCC control mode
- ECO energy saving mode, energy saving effect is visible in real time through parameters & Integrated USS, Modbus RTU communication
- Built-in common connection macros and application macros
- · Parameter cloning and version upgrade without power supply
- Special features such as frost protection, hibernation, capture restart, auto restart
- 7.5 ~ 30 kW integrated brake module, other power supply brake options SINAMICS V20
- V20 with the same power supports a common DC busbar connection, energy sharing

Technical specifications

Technical specification for CPU SR20/ST20

CPU SR20 AC/DC/RLY	CPU ST20 DC/DC/DC
6ES7 288-1SR20-0AA1	6ES7 288-1ST20-0AA1
90 x 100 x 81	
	320 q
-	20W
	Max. 1110 mA (5 V DC)
Max. 300 mA (sensor power source)	
4mA for each input point used	
12 KB program memory /8 KB data memory /max 10 KB retentive memory	
56 words input (AI) / 56 words output (AQ)	
256 bits	
The main program has 64 bytes, each subroutine and interrupt program ha	s 64 bytes
6 extension modules	
Max 1 signal hoard	
• .	
Quadrature phase: 2 of 100 kHz	
-	2 of 100 kHz
12	
2 in total, resolution is of 1ms,	
	are 6 edges each)
	are o eages each,
`	
In general 7 days, or min. 6 days when 25 °C (Maintenance free super capa	citor)
0.15 µs/instruction	
1.2 us/instruction	
•	
•	
sub-program: 128 (0 to 127) interrupt program: 128 (0 to 127) Nesting depth from main program: 8 sub-program level from interrupt program: 4 sub-program level	
non-holding (or not retained) (TON, TOF): 192 holding (or retained) (TONR): 64	
256	
1 PROFINET port/ 1 serial (RS485) /1 additional serial (optional RS232/485 s	ignal hoard) port
	ighar board, port
·	
PROFINET (LAN): 8 clients and 8 server connections	
Yes/No	
Yes/No 8	
8	
8 64	
8 64 PROFINET (LAN): 8 active and 8 passive connections	
8 64 PROFINET (LAN): 8 active and 8 passive connections Profinet: 10/100 Mb/s RS485 system protocol: 9600, 19200 and 187500 b/s	
8 64 PROFINET (LAN): 8 active and 8 passive connections Profinet: 10/100 Mb/s	
8 64 PROFINET (LAN): 8 active and 8 passive connections Profinet: 10/100 Mb/s RS485 system protocol: 9600, 19200 and 187500 b/s RS485 free port: 1200 to 115200 b/s Profinet: Transformer isolation, 1500 V AC	
8 64 PROFINET (LAN): 8 active and 8 passive connections Profinet: 10/100 Mb/s RS485 system protocol: 9600, 19200 and 187500 b/s RS485 free port: 1200 to 115200 b/s Profinet: Transformer isolation, 1500 V AC RS485: none Profinet: CAT5e shielded cable	
8 64 PROFINET (LAN): 8 active and 8 passive connections Profinet: 10/100 Mb/s RS485 system protocol: 9600, 19200 and 187500 b/s RS485 free port: 1200 to 115200 b/s Profinet: Transformer isolation, 1500 V AC RS485: none Profinet: CAT5e shielded cable RS485: PROFIBUS network cable	20.4 ~ 28.8 V DC
8 64 PROFINET (LAN): 8 active and 8 passive connections Profinet: 10/100 Mb/s RS485 system protocol: 9600, 19200 and 187500 b/s RS485 free port: 1200 to 115200 b/s Profinet: Transformer isolation, 1500 V AC RS485: none Profinet: CAT5e shielded cable RS485: PROFIBUS network cable	20.4 ~ 28.8 V DC
8 64 PROFINET (LAN): 8 active and 8 passive connections Profinet: 10/100 Mb/s RS485 system protocol: 9600, 19200 and 187500 b/s RS485 free port: 1200 to 115200 b/s Profinet: Transformer isolation, 1500 V AC RS485: none Profinet: CAT5e shielded cable RS485: PROFIBUS network cable 85 ~ 264 V AC 47 ~ 63 Hz – When the maximum load is reached, only CPU is included 210 mA when voltage is 120 V AC (with a 300 mA sensor power output) 90 mA when voltage is 120 V AC (without a 300 mA sensor power output) 120 mA when voltage is 240 V AC (with a 300 mA sensor power output)	20.4 ~ 28.8 V DC When the maximum load is reached, only CPU is included 160 mA when voltage is 24 V DC (without a 300 m sensor power output) 430 mA when voltage is 24 V DC (with a 300 mA sensor power output) When the max load is reached, CPU and all the scalable extensions are included
	90 x 100 x 81 367.3 g 14 W Max. 740 mA (5 V DC) Max. 300 mA (sensor power source) 4mA for each input point used 12 KB program memory /8 KB data memory /max. 10 KB retentive memory 12 input points / 8 output points 256 bits input (I) / 256 bits output (Q) 56 words input (AI) / 56 words output (AQ) 256 bits The main program has 64 bytes, each subroutine and interrupt program ha 6 extension modules Max. 1 signal board 4 in total Single phase: 4 of 200 kHz Quadrature phase: 2 of 100 kHz - 12 2 in total, resolution is of 1ms, 4 rising edges and 4 falling edges (when using optional signal board, there Micro SDHC card (optional) 120 seconds/month In general 7 days, or min. 6 days when 25 °C (Maintenance free super capa 0.15 µs/instruction 1.2 µs/instruction 1.2 µs/instruction 1.9 us/instruction 1.9 whe 57-200 SMART type/quantity • main program: 128 (0 to 127) • interrupt program: 128 (0 to 127) Nesting depth • from main program: 8 sub-program level • from interrupt program: 4 sub-program level • from interrupt program: 7 sub-program level • from interrupt program: 8 sub-program level

Model	CPU SR20 AC/DC/RLY	CPU ST20 DC/DC/DC
Inrush current (max)	9.3 A when voltage is 264 V AC	11.7 A when voltage is 28.8 DC
Isolation (input power with the logic side)	1500 V AC	-
Leakage current, AC line for functional earthing	Max 0. 5 mA	-
Hold time (power off)	30 ms when voltage is 120 V AC 200 ms when voltage is 240 V AC	20 ms when voltage is 24 V DC
Internal fuse (cannot be replaced by the	3 A, 250 V, Slow-blow fuse	3 A, 250 V, Slow-blow fuse
user)		
Sensor power source		
Voltage range	20.4 ~ 28.8 V DC	
Rated output current (max)	300 mA (short circuit protection)	
Maximum ripple noise (<10 MHz)	<1 V peak-peak value	
Isolation (CPU logic side and sensor power source)	Not isolated	
Digital input		
Number of input points	12	
Туре	The sinking / sourcing type (IEC type 1 sinking)	The sinking/sourcing type (IEC type 1 sinking excluding I0.0 to I0.3)
Rated voltage	It is 24V DC when the current is 4 mA, nominal value	,
Allowable continuous voltage	Max 30 V DC	
Surge voltage	35 V DC, lasting 0.5 s	
Logic 1 signal (min)	It is 15 V DC when the current is 2.5 mA	The voltage is 4 V DC when it ranges from I0.0 to I0.3, I0.6 to I0.7: 8 mA
Logic 0 signal (min)	It is 5 V DC when the current is 1 mA	Other input: 15 V DC when it is 2.5 mA The voltage is 1 V DC when it ranges from I0.0 to I0.3, I0.6 to I0.7: 1 mA Other input: 5 V DC when it is 1 mA.
Isolation (field side and logic side)	500 V AC, lasting 1 min	other input. 5 v be whell it is I link.
Isolation group	1	
Filter time	Each channel can be separately selected (point I0.0 to 11.3) : 0.2, 0.4, 0.8, 1.6, 3.2, 6.4 and 12.8 µs 0.2, 0.4, 0.8, 1.6, 3.2, 6.4 and 12.8 ms	
HSC clock input frequency (max)	Single phase: 4 200 KHz + 2 30 KHz	
(Logic 1 battery = $15 \sim 26 \text{ V DC}$) Number of inputs that connect at the same	Quadrature phase: 2 100 KHz + 2 20 KHz	
time	'-	
Cable length (max), its unit is meter	Shielded: 500m (normal input), 50m (HSC input); non shielded: 300m (normal input)	10.0 to 10.3, shielded (only limited to this category): 500 m (normal input), 50 m (HSC input) 10.6 to 10.7, shielded (only limited to this category): 500 m (normal input), All other inputs: shielded: 500 m (normal input); non shielded: 300 m (normal input)
Digital output		non sinciaca. 500 m (normal mpat)
	8	
Number of output		C-lid -t-t- MOCEET (
Туре	Relay, dry contact	Solid state-MOSFET (source-type)
Voltage range	5 ~ 30 V DC or 5 ~ 250 V AC	20.4 ~ 28.8 V DC
Logic 1 signal when the current is max.	-	Min. 20 V DC
Logic 0 signal when the load is KG	-	Max. 0.1 V DC
Rated current at each point (max)	2.0 A	0.5 A
Rated current at each public end (max)	10.0 A	6 A
Lamp load	30 W DC/200 W AC	5 W
On state resistance	New equipment is 0.2 Ω maximally	Max. 0.6 Ω
Leakage current at each point	-	Max. 10 μ A
Surge current	It is 7A when the contact is closed	8 A, max. lasting 100 ms
Overload protection	none	
Isolation (field side and logic side)	1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side)	500 V AC, lasting 1 min
Isolation resistance	New equipment is 100 MΩ minimally	-
Disconnect the insulation between the contacts	750 V AC, lasting 1 min	-
Isolated group	1	2
Inductive voltage clamp	Not recommended	L+ - 48 V DC, 1 W loss
Relay max. on/off frequency	Not recommended	,
Switching delay (Qa.0-Qa.3)	Max. 10 ms	From the disconnection to connection max.1 µs from the connection to disconnection is 3 µs max.
Switching delay (Qa.0-Qa.7)	Max. 10 ms	From the disconnection to connection max. 50 µs from the connection to disconnection is 200 µs max.
Mechanical life (no load)	10,000,000 break/close cycles	-
Contact life under the rated load	100,000 break/close cycles	-
Output state under the STOP mode Number of output that are connected at the	Last value or replicable value (The default value is 0)	
same time	CI. II 200	
Cable length	Shielded: 500 m; non shielded: 300 m	

Technical specification for CPU SR30/ST30

Model	CPU SR30 AC/DC/RLY	CPU ST30 DC/DC/DC
Order No.: (MLFB)	6ES7 288-1SR30-0AA1	6ES7 288-1ST30-0AA1
Standard		
Dimension W x H x D (mm)	110 x 100 x 81	
Weight	435 g	375 g
Power consumption	14 W	12W
Available current (EM bus)	Max. 740 mA (5 V DC)	
Available current (24 V DC)	Max. 300 mA (sensor power source)	
Digital input current consumption	4mA for each input point used	
(24 V DC)		
CPU features		
User memory	18 KB program memory /12 KB data memory /max. 10 KB retentive memory	
On board digital I/O	18 input points / 12 output points	
Process image size	256 bits input (I) / 256 bits output (Q)	
Analog image	56 words input (AI) / 56 words output (AQ)	
Bit memory (M)	256 bits	
Temporary (local) memory	The main program has 64 bytes, each subroutine and interrupt program has 6	4 bytes
I/O module extension	6	
Signal board extension	Max. 1 signal board	
High speed counters	4 in total	
	Single phase: 4 of 200 kHz Quadrature phase: 2 of 100 kHz	
Pulse output	-	3 of 100 kHz
Pulse capture input	12	
Cycle interrupt	2 in total, resolution is of 1ms,	
Interrupt Edge	4 rising edges and 4 falling edges (when using optional signal board, there are	e 6 edges each)
Memory	Micro SDHC card (optional)	
Precision of real-time clock	120 seconds/month	
Real-time clock hold time	In general 7 days, or min. 6 days when 25 °C (Maintenance free super capacito	or)
Performance/ Processing Time		,
Boolean	0.15 μs/instruction	
Moving word operations	1.2 µs/instruction	
Real mathematical operations	3.6 µs/instruction	
The user's program elements supported	•	
POUs	type/quantity	
	 interrupt program: 128 (0 to 127) Nesting depth from main program: 8 sub-program level from interrupt program: 4 sub-program level 	
Accumulators	4	
Timer	type/quantity • non-holding (or not retained) (TON, TOF) : 192 • holding (or retained) (TONR) : 64	
Counters	256	
Communications		
Number of ports	1 PROFINET port/ 1 serial (RS485) /1 additional serial (optional RS232/485 sign	al board) port
HMI equipment	max. 4 connection on serial port & max. 8 connection on PROFINET port	, , , , , , , , , , , , , , , , , ,
Programming equipment (PG)	PROFINET: 1 & Serial Port: 1	
CPU (PUT/GET)	PROFINET (LAN): 8 clients and 8 server connections	
PROFINET communication	(E. inj. o silents and o server confidences	
PROFINET controller/device	Yes/No	
Maximum number of PROFINET devices	8	
that can be connected to RT		
Maximum number of modules	64	
Open user communication	PROFINET (LAN): 8 active and 8 passive connections	
Data transmission rate	PROFINET: 10/100 Mb/s RS485 system protocol: 9600, 19200 and 187500 b/s RS485 free port: 1200 to 115200 b/s	
Isolation (external signal and PLC logic side)	PROFINET: Transformer isolation, 1500 V AC RS485: none	
Type of cable	PROFINET: CAT5e shielded cable RS485: PROFIBUS network cable	
Power source		
Voltage range	85 ~ 264 V AC	20.4 ~ 28.8 V DC
Power supply frequency	47 ~ 63 Hz	-
Input current	When the maximum load is reached, only CPU is included 92 mA (including power source of the sensor) when the voltage is 120 V AC 40 mA (excluding power source of the sensor) when the voltage is 120 V AC 52 mA (including power source of the sensor) when the voltage is 240 V AC 27 mA (excluding power source of the sensor) when the voltage is 240 V AC When the max load is reached, it CPU and all the scalable extensions are included 136 mA when voltage is 120 V AC 72 mA when voltage is 240 V AC	When the maximum load is reached, only CPU is included 64 mA when voltage is 24 V DC (without a 300 mA sensor power output) 365 mA when voltage is 24 V DC (with a 300 mA sensor power output) When the max load is reached, CPU and all the scalable extensions are included 624 mA when voltage is 24 V DC
Inrush current (max)	8.9 A when voltage is 240 V AC	6 A when voltage is 28.8 V DC

Model	CPU SR30 AC/DC/RLY	CPU ST30 DC/DC/DC
Isolation (input power with the logic side)	1500 V AC	-
Leakage current, AC line for functional earthing	Max 0. 5 mA	-
Hold time (power off)	30 ms when voltage is 120 V AC 200 ms when voltage is 240 V AC	20 ms when voltage is 24 V DC
Internal fuse (cannot be replaced by the user)	3 A, 250 V, Slow-blow fuse	
Sensor power source		
Voltage range	20.4 ~ 28.8 V DC	
Rated output current (max)	300 mA (short circuit protection)	
Maximum ripple noise (<10 MHz)	<1 V peak-peak value	
Isolation (CPU logic side and sensor	Not isolated	
power source)		
Digital input Number of input points	18	
Туре	The sinking / sourcing type (IEC type 1 sinking)	The sinking/sourcing type (IEC type 1 sinking
		excluding 10.0 to 10.3)
Rated voltage	It is 24 V DC when the current is 4 mA, rated value	
Allowable continuous voltage	Max 30 V DC	
Surge voltage Logic 1 signal (min)	35 V DC, lasting 0.5 s It is 15 V DC when the current is 2.5 mA	The voltage is 4 V DC when it ranges from I0.0 to
Logic i Signal (IIIIII)	It is 13 V DC when the current is 2.3 min	10.3, 10.6 to 10.7: 8 mA Other input: 15 V DC when it is 2.5 mA
Logic 0 signal (min)	It is 5 V DC when the current is 1 mA	The voltage is 1 V DC when it ranges from I0.0 to I0.3, I0.6 to I0.7: 1 mA Other input: 5 V DC when it is 1 mA.
Isolation (field side and logic side)	500 V AC, lasting 1 min	
Isolation group	1	
Filter time	Each channel can be separately selected (point I0.0 to I1.5): 0.2, 0.4, 0.8, 1.6, 3.2, 6.4 and 12.8 µs 0.2, 0.4, 0.8, 1.6, 3.2, 6.4 and 12.8 ms Each channel can be separately selected (I0.6): 0, 6.4, 12.8 ms	
HSC clock input frequency (max)	Single phase: 5 200 KHz + 1 30 KHz	
(Logic 1 battery = 15 ~ 26 V DC) Number of inputs that connect at the	Quadrature phase: 3 100 KHz + 1 20 KHz	
same time		
Cable length (max), its unit is meter	Shielding: 500m (normal input), 50m (HSC input); non shielding: 300m (normal input)	I0.0 to I0.3, shielding (only limited to this category): 500 m (normal input), 50 m (HSC input) I0.6 to I0.7, shielding (only limited to this category): 500 m (normal input), All other inputs: shielding: 500 m (normal input); non shielding: 300 m (normal input)
Digital output		
Number of output	12	
Type	Relay, dry contact	Solid state-MOSFET (source-type)
Voltage range	5 ~ 30 V DC or 5 ~ 250 V AC	20.4 ~ 28.8 V DC
Logic 1 signal when the current is max. Logic 0 signal when the load is 10 K Ω	-	Min. 20 V DC Max. 0.1 V DC
Rated current at each point (max)	2.0 A	0.5 A
Rated current at each public end (max)	10.0 A	6 A
Lamp load	30 W DC/200 W AC	5 W
On state resistance	New equipment is 0.2 Ω maximally	Max. 0.6 Ω
Leakage current at each point	-	Max. 10 μ A
Surge current	It is 7A when the contact is closed	8 A, max. lasting 100 ms
Overload protection	none	
Isolation (field side and logic side)	1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side)	500 V AC, lasting 1 min
Isolation resistance Disconnect the insulation between the	New equipment is 100 M Ω minimally 750 V AC, lasting 1 min	-
contacts Isolated group	1	
Inductive voltage clamp	Not recommended	L+ - 48 V DC, 1 W loss
Switching delay (Qa.0-Qa.3)	Max. 10 ms	From the disconnection to connection max.1 µs from the connection to disconnection is 3 µs max
Switching delay (Qa.4-Qb.7)	Max. 10 ms	From the disconnection to connection max. 50 μ s from the connection to disconnection is 200 μ s max.
Mechanical life (no load)	10,000,000 break/close cycles	-
Contact life under the rated load	100,000 break/close cycles	-
Output state under the STOP mode Number of output that are connected at the same time	Last value or replicable value (The default value is 0) 12	

Technical specification for CPU SR40/ST40/CR40

Model		CPU SR40 AC/DC/RLY	CPU ST40 DC/DC/DC	CPU CR40 AC/DC/RLY		
Order No.: (MLFB)		6ES7 288-1SR40-0AA1	6ES7 288-1ST40-0AA1	6ES7 288-1CR40-0AA1		
Standard	B ()	105 100 0				
Dimension W x H x	(D (mm)	125 x 100 x 81		1		
Weight 		441.3 g	410.3 g	440 g		
Power consumptio		23 W	18 W	18 W		
Available current (Max. 740 mA (5 V DC)		-		
Available current (Max. 300 mA (sensor power source)				
	nt consumption (24 V DC)	4mA for each input point used				
CPU features						
User memory		24 KB program memory /16 KB data mer	24 KB program memory /16 KB data memory /max. 10 KB retentive memory 12 KB program memory /8 KB memory /max. 10 KB retentive memory /max. 10 KB retentive			
On board digital I/0		24 input points / 16 output points				
Process image size		256 bits input (I) / 256 bits output (Q)				
Analog image		56 words input (AI) / 56 words output (A	Q)			
Bit memory (M)		256 bits				
Temporary (local)			broutine and interrupt program has 64 by	tes		
/O module extensi		6 extension modules		-		
Signal board exten		Max. 1 signal board		-		
High speed counte	ers	4 in total Single phase: 4 of 200 kHz Quadrature phase: 2 of 100 kHz		4 in total Single phase: 4 of 100 kHz Quadrature phase: 2 of 50 kHz		
Pulse output		3, 100 kHz		-		
Pulse capture inpu	t	14				
Cycle interrupt		2 in total, resolution is of 1ms,				
Interrupt Edge		4 rising edges and 4 falling edges (when 6 edges each)	using optional signal module, there are	4 rising edges and 4 falling edges		
Memory		Micro SDHC card (optional)				
Precision of real-ti	me clock	120 seconds/month		-		
Real-time clock ho	ld time	In general 7 days, or min. 6 days when 2	5 °C (Maintenance free super capacitor)	-		
Performance/ Pro	cessing Time					
Boolean		0.15 µs/instruction				
Moving word oper	ations	1.2 µs/instruction				
Real mathematical	l operations	3.6 µs/instruction				
The user's progra	m elements supported by	the S7-200 SMART				
		 interrupt program: 128 (0 to 127) Nesting depth from main program: 8 sub-program lev from interrupt program: 4 sub-program 				
Accumulators		4				
Timer		type/quantity • non-holding (or not retained) (TON, TO • holding (or retained) (TONR): 64	DF): 192			
Counters		256				
Communications						
Number of ports		1 PROFINET port/ 1 serial (RS485) /1 add	itional serial (optional RS232/485 signal b	oard) port		
HMI equipment		max. 4 connection on serial port & max.	8 connection on PROFINET port			
Programming equi	ipment (PG)	PROFINET: 1 & Serial Port: 1				
CPU (PUT/GET)		PROFINET (LAN): 8 clients and 8 server of	onnections			
PROFINET commu	nication					
PROFINET controll	er/device	Yes/No				
Maximum number can be connected	r of PROFINET devices that to RT	8				
Maximum number		64				
Open user commu Data transmission		PROFINET (LAN): 8 active and 8 passive of PROFINET: 10/100 Mb/s RS485 system protocol: 9600, 19200 an				
Isolation (external	signal and PLC logic side)	RS485 free port: 1200 to 115200 b/s PROFINET: Transformer isolation, 1500 V	AC			
Type of cable		RS485: none PROFINET: CAT5e shielded cable RS485: PROFIBUS network cable				
Power source		103.1 NOT IDOS NEWVOIR CADIC				
Voltage range		85 ~ 264 V AC	20.4 ~ 28.8 V DC	85 ~ 264 V AC		
Power supply frequ	uency	47 ~ 63 Hz		47 ~ 63 Hz		
Input current	Only includes the CPU	130 mA when voltage is 120 V AC (without a 300 mA sensor power output 250 mA when voltage is 120 V AC (with a 300 mA sensor power output)	190 mA when voltage is 24 V DC (without a 300 mA sensor power output) 470 mA when voltage is 24 V DC (with a 300 mA sensor power output)	130 mA when voltage is 120 V AC (without a 300 mA sensor power output) 250 mA when voltage is 120 V AC (with a 300 mA sensor power output) 80 mA when voltage is 240 V AC		
		80 mA when voltage is 240 V AC (without a 300 mA sensor power output 150 mA when voltage is 240 V AC (with a 300 mA sensor power output)		(without a 300 mA sensor power output) 150 mA when voltage is 240 V AC		
	Includes CPU and all	(without a 300 mA sensor power output		(without a 300 mA sensor power output)		

Model	CPU SR40 AC/DC/RLY	CPU ST40 DC/DC/DC	CPU CR40 AC/DC/RLY
nrush current (max)	16.3 A when voltage is 264 V AC	11.7 A when voltage is 28.8 V DC	7.3 A when voltage is 264 V AC
solation (input power with the logic side)	1500 V AC	-	1500 V AC
Leakage current, AC line for functional earthing	Max 0. 5 mA	-	Max 0. 5 mA
Hold time (power off)	30 ms when voltage is 120 V AC 200 ms when voltage is 240 V AC	20 ms when voltage is 24 V DC	50 ms when voltage is 120 V AC 400 ms when voltage is 240 V AC
nternal fuse (cannot be replaced by the user)	3 A, 250 V, Slow-blow fuse		
ensor power source			
/oltage range	20.4 ~ 28.8 V DC		
Rated output current (max)	00 mA (short circuit protection)		
Maximum ripple noise (<10 MHz)	<1 V peak-peak value		
solation (CPU logic side and sensor power	Not isolated		
source)	Not Bolated		
Digital input			
Number of input points	24		
Гуре	The sinking / sourcing type (IEC type 1	The sinking/sourcing type (IEC type 1	The sinking / sourcing type (IEC type 1
урс	sinking)	sinking excluding I0.0 to I0.3)	sinking)
Rated voltage	It is 24 V DC when the current is 4 mA, no		,g,
Allowable continuous voltage	Max 30 V DC	milar value	
Surge voltage	35 V DC, lasting 0.5 s	The voltage is 4 V DC where it was	Other inputs 15 V DC selver it is 2.5
Logic 1 signal (min)	It is 15 V DC when the current is 2.5 mA, 10.0 to 10.4 V DC at 8 mA	The voltage is 4 V DC when it ranges from I0.0 to I0.3 : 8 mA Other input: 15 V DC when it is 2.5 mA	Other input: 15 V DC when it is 2.5 m
Logic 0 signal (min)	It is 5 V DC when the current is 1 mA	The voltage is 1 V DC when it ranges from I0.0 to I0.3: 1 mA Other input: 5 V DC when it is 1 mA	Other input: 5 V DC when it is 1 mA
solation (field side and logic side)	500 V AC, lasting 1 min		
solation group	1		
Filter time	Each channel can be separately selected (only first 14 input loads on board, includi	ng the digital input of the signal board
nter time	0.2, 0.4, 0.8, 1.6, 3.2, 6.4 and 12.8 µs 0.2, 0.4, 0.8, 1.6, 3.2, 6.4 and 12.8 ms	orny mst 14 mput loads on board, melddi	ing the digital input of the signal board
HSC clock input frequency (max)	Single phase: 4 200 KHz + 2 30 KHz		
(Logic 1 battery = 15 ~ 26 V DC)			
	Quadrature phase: 2 100 KHz + 2 20 KHz		
Number of inputs that connect at the same	24		
Number of inputs that connect at the same time	24		
Number of inputs that connect at the same time		out), 50m (HSC input); All other inputs: sl	nielding 500m (normal input);
Number of inputs that connect at the same time Cable length (max)	10.0 to 10.3: Shielding: 500m (normal inpos shielding: 300m (normal input)	out), 50m (HSC input); All other inputs: sl	nielding 500m (normal input);
Number of inputs that connect at the same time Cable length (max) Digital output	10.0 to 10.3: Shielding: 500m (normal inp	out), 50m (HSC input); All other inputs: sl	nielding 500m (normal input);
Number of inputs that connect at the same time Cable length (max) Digital output Number of output	10.0 to 10.3: Shielding: 500m (normal inpos shielding: 300m (normal input)	out), 50m (HSC input); All other inputs: sl Solid state-MOSFET (source-type)	nielding 500m (normal input); Relay, dry contact
Number of inputs that connect at the same ime Cable length (max) Digital output Number of output Type	10.0 to 10.3: Shielding: 500m (normal inponshielding: 300m (normal input)		
Number of inputs that connect at the same ime Cable length (max) Digital output Number of output Type Voltage range	10.0 to 10.3: Shielding: 500m (normal inpons shielding: 300m (normal input) 16 Relay, dry contact	Solid state-MOSFET (source-type)	Relay, dry contact
Number of inputs that connect at the same ime Cable length (max) Digital output Number of output Type Voltage range Logic 1 signal when the current is max.	10.0 to 10.3: Shielding: 500m (normal inpons shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC	Relay, dry contact
Number of inputs that connect at the same ime Cable length (max) Digital output Number of output Type Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG	10.0 to 10.3: Shielding: 500m (normal inpons shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC
Number of inputs that connect at the same ime Cable length (max) Digital output Number of output Type Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Rated current at each point (max)	10.0 to 10.3: Shielding: 500m (normal inpons shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC -	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC Max. 0.1 V DC	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC 2.0 A
Number of inputs that connect at the same ime Cable length (max) Digital output Number of output Type Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Rated current at each point (max) Lamp load	24 10.0 to 10.3: Shielding: 500m (normal inpun non shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC 2.0 A 30 W DC/200 W AC
Number of inputs that connect at the same ime Cable length (max) Digital output Number of output Type Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Rated current at each point (max) Lamp load On state resistance	10.0 to 10.3: Shielding: 500m (normal inponshielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC 2.0 A	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W Max. 0.6 Ω	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC 2.0 A
Number of inputs that connect at the same ime Cable length (max) Digital output Number of output Type Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Rated current at each point (max) Lamp load On state resistance Leakage current at each point	24 10.0 to 10.3: Shielding: 500m (normal inpons shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally	Solid state-MOSFET (source-type) 20.4 \sim 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W Max. 0.6 Ω Max. 10 μ A	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally
Number of inputs that connect at the same time Cable length (max) Digital output Number of output Type Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Rated current at each point (max) Lamp load On state resistance Leakage current at each point Surge current	24 10.0 to 10.3: Shielding: 500m (normal inpons shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W Max. 0.6 Ω	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC 2.0 A 30 W DC/200 W AC
Number of inputs that connect at the same time Cable length (max) Digital output Number of output Type Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Rated current at each point (max) Lamp load On state resistance Leakage current at each point Surge current Diverload protection	24 10.0 to 10.3: Shielding: 500m (normal inpons shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally It is 7A when the contact is closed none	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W Max. 0.6 Ω Max. 10 μ A 8 A, max. lasting 100 ms	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed
Number of inputs that connect at the same time Cable length (max) Digital output Number of output I/Oltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Rated current at each point (max) Lamp load On state resistance Leakage current at each point Surge current Diverload protection	24 10.0 to 10.3: Shielding: 500m (normal inponent inponent input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed none 1500 V AC, lasting 1 min (coil and	Solid state-MOSFET (source-type) 20.4 \sim 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W Max. 0.6 Ω Max. 10 μ A	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed
Number of inputs that connect at the same time Cable length (max) Digital output Number of output Type Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Rated current at each point (max) Lamp load On state resistance Leakage current at each point Surge current Coverload protection solation (field side and logic side)	24 10.0 to 10.3: Shielding: 500m (normal inpons shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed none 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side)	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W Max. 0.6 Ω Max. 10 μ A 8 A, max. lasting 100 ms	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side)
Number of inputs that connect at the same time Cable length (max) Digital output Number of output Number of output Type Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Rated current at each point (max) Lamp load On state resistance Leakage current at each point Surge current Diverload protection solation (field side and logic side)	24 10.0 to 10.3: Shielding: 500m (normal inpons shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed none 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 MΩ minimally	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W Max. 0.6 Ω Max. 10 μ A 8 A, max. lasting 100 ms	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 MΩ minimally
Number of inputs that connect at the same time Cable length (max) Digital output Number of output Type Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Rated current at each point (max) Lamp load On state resistance Leakage current at each point Diverload protection solation (field side and logic side) solation resistance Disconnect the insulation between the	24 10.0 to 10.3: Shielding: 500m (normal inponent shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed none 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side)	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W Max. 0.6 Ω Max. 10 μ A 8 A, max. lasting 100 ms	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side)
Number of inputs that connect at the same time Cable length (max) Digital output Number of output Type Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Rated current at each point (max) Lamp load On state resistance Leakage current at each point Surge current Diverload protection Solation (field side and logic side) Solation resistance Disconnect the insulation between the	10.0 to 10.3: Shielding: 500m (normal inpons shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed none 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 MΩ minimally 750 V AC, lasting 1 min	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W Max. 0.6 Ω Max. 10 μ A 8 A, max. lasting 100 ms 500 V AC, lasting 1 min -	Relay, dry contact $5\sim30\text{V}$ DC or $5\sim250\text{V}$ AC $-$ 2.0 A 30 W DC/200 W AC New equipment is 0.2Ω maximally $-$ It is 7A when the contact is closed 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is $100\text{M}\Omega$ minimally 750V AC, lasting 1 min
Number of inputs that connect at the same time Cable length (max) Digital output Number of output Type Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Rated current at each point (max) Lamp load On state resistance Leakage current at each point Surge current Diverload protection Solation (field side and logic side) solation resistance Disconnect the insulation between the contacts Solated group	10.0 to 10.3: Shielding: 500m (normal inpons shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed none 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 MΩ minimally 750 V AC, lasting 1 min	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W Max. 0.6 Ω Max. 10 μ A 8 A, max. lasting 100 ms 500 V AC, lasting 1 min -	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 MΩ minimally
Number of inputs that connect at the same time Cable length (max) Digital output Number of output Type Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Rated current at each point (max) Lamp load On state resistance Leakage current at each point Surge current Overload protection Isolation (field side and logic side) Isolation resistance Disconnect the insulation between the contacts Isolated group Inductive voltage clamp	10.0 to 10.3: Shielding: 500m (normal inpon shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed none 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 MΩ minimally 750 V AC, lasting 1 min	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W Max. 0.6 Ω Max. 10 μ A 8 A, max. lasting 100 ms 500 V AC, lasting 1 min 2 L+ - 48 V DC, 1 W loss	Relay, dry contact $5\sim30$ V DC or $5\sim250$ V AC $ 2.0$ A $ 30$ W DC/200 W AC New equipment is 0.2 Ω maximally $-$ It is 7A when the contact is closed $ 1500$ V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 M Ω minimally $ 100$ New equipment is 100 M Ω minimally 100 New AC, lasting 1 min 100 M Ω
Number of inputs that connect at the same time Cable length (max) Digital output Number of output Type Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Rated current at each point (max) Lamp load On state resistance Leakage current at each point Surge current Diverload protection solation (field side and logic side) solation resistance Disconnect the insulation between the contacts solated group nductive voltage clamp	10.0 to 10.3: Shielding: 500m (normal inpons shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed none 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 MΩ minimally 750 V AC, lasting 1 min	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W Max. 0.6 Ω Max. 10 μ A 8 A, max. lasting 100 ms 500 V AC, lasting 1 min -	Relay, dry contact $5\sim30$ V DC or $5\sim250$ V AC $ 2.0$ A $ 30$ W DC/200 W AC New equipment is 0.2 Ω maximally $-$ It is 7A when the contact is closed $ 1500$ V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 M Ω minimally $ 100$ NC, lasting 1 min $ 100$ NC
Number of inputs that connect at the same time Cable length (max) Digital output Number of output Type Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Rated current at each point (max) Lamp load On state resistance Leakage current at each point Surge current Diverload protection solation (field side and logic side) solation resistance Disconnect the insulation between the contacts solated group nductive voltage clamp Switching delay (Qa.0-Qa.3)	10.0 to 10.3: Shielding: 500m (normal inpon shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed none 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 MΩ minimally 750 V AC, lasting 1 min	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W Max. 0.6 Ω Max. 10 μ A 8 A, max. lasting 100 ms 500 V AC, lasting 1 min 2 L+ - 48 V DC, 1 W loss From the disconnection to connection max.1 μs from the connection to disconnection	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 MΩ minimally 750 V AC, lasting 1 min 4 - Max. 10 ms
Number of inputs that connect at the same time Cable length (max) Digital output Number of output Type Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Rated current at each point (max) Lamp load On state resistance Leakage current at each point Surge current Diverload protection solation (field side and logic side) solation resistance Disconnect the insulation between the contacts solated group Inductive voltage clamp Switching delay (Qa.0-Qa.3)	10.0 to 10.3: Shielding: 500m (normal inpons shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed none 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 MΩ minimally 750 V AC, lasting 1 min 4 Not recommended Max. 10 ms	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W Max. 0.6 Ω Max. 10 μ A 8 A, max. lasting 100 ms 500 V AC, lasting 1 min 2 L+ - 48 V DC, 1 W loss From the disconnection to connection max.1 μs from the connection to disconnection is 3 μs max. From the disconnection to connection max.50 μs from the connection to disconnection	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 MΩ minimally 750 V AC, lasting 1 min 4 - Max. 10 ms
Number of inputs that connect at the same	10.0 to 10.3: Shielding: 500m (normal inpon shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed none 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 MΩ minimally 750 V AC, lasting 1 min 4 Not recommended Max. 10 ms	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W Max. 0.6 Ω Max. 10 μ A 8 A, max. lasting 100 ms 500 V AC, lasting 1 min 2 L+ - 48 V DC, 1 W loss From the disconnection to connection max.1 μs from the connection to disconnection is 3 μs max. From the disconnection to connection max.50 μs from the connection to disconnection	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 MΩ minimally 750 V AC, lasting 1 min 4 - Max. 10 ms
Number of inputs that connect at the same time Cable length (max) Digital output Number of output Type Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Rated current at each point (max) Lamp load On state resistance Leakage current at each point Surge current Overload protection Isolation (field side and logic side) Isolation resistance Disconnect the insulation between the contacts Isolated group Inductive voltage clamp Switching delay (Qa.0-Qa.3) Switching delay (Qa.4-Qb.7) Mechanical life (no load) Contact life under the rated load	10.0 to 10.3: Shielding: 500m (normal inpon shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed none 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 MΩ minimally 750 V AC, lasting 1 min 4 Not recommended Max. 10 ms Max. 10 ms	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W Max. 0.6 Ω Max. 10 μ A 8 A, max. lasting 100 ms 500 V AC, lasting 1 min 2 L+ - 48 V DC, 1 W loss From the disconnection to connection max.1 μs from the connection to disconnection is 3 μs max. From the disconnection to connection max. 50 μs from the connection to disconnection is 200 μs max.	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 MΩ minimally 750 V AC, lasting 1 min 4 - Max. 10 ms Max. 10 ms
Number of inputs that connect at the same time Cable length (max) Digital output Number of output Number of output Number of output Stype Voltage range Logic 1 signal when the current is max. Logic 0 signal when the load is KG Nated current at each point (max) Lamp load On state resistance Leakage current at each point Surge current Diverload protection solation (field side and logic side) solation resistance Disconnect the insulation between the contacts solated group Inductive voltage clamp Switching delay (Qa.0-Qa.3) Switching delay (Qa.4-Qb.7) Mechanical life (no load)	10.0 to 10.3: Shielding: 500m (normal inpon shielding: 300m (normal input) 16 Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed none 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 MΩ minimally 750 V AC, lasting 1 min 4 Not recommended Max. 10 ms Max. 10 ms	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC Min. 20 V DC Max. 0.1 V DC 0.5 A 5 W Max. 0.6 Ω Max. 10 μ A 8 A, max. lasting 100 ms 500 V AC, lasting 1 min 2 L+ - 48 V DC, 1 W loss From the disconnection to connection max.1 μs from the connection to disconnection is 3 μs max. From the disconnection to connection max. 50 μs from the connection to disconnection is 200 μs max.	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC - 2.0 A 30 W DC/200 W AC New equipment is 0.2 Ω maximally - It is 7A when the contact is closed 1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side) New equipment is 100 MΩ minimally 750 V AC, lasting 1 min 4 - Max. 10 ms

Technical specification for CPU SR60/ST60/CR60

Order No.: (MLFB)		CPU SR60 AC/DC/RLY	CPU ST60 DC/DC/DC	CPU CR60 AC/DC/RLY	
		6ES7 288-1SR60-0AA1	6ES7 288-1ST60-0AA1	6ES7 288-1CR60-0AA1	
Standard					
Dimension W x H x	D (mm)	175 x 100 x 81			
Weight		611.5 g	528.2 g	620 g	
Power consumption	n	25 W	20 W		
Available current (E	-M bus)	Max. 740 mA (5 V DC)		_	
Available current (2		Max. 300 mA (sensor power source)			
	nt consumption (24 V DC)	4 mA for each input point used			
CPU features	it consumption (24 v DC)	4 IIIA for each input point used			
		20.1/2	40.00	10 1/0	
User memory		30 KB program memory /20 KB data memory /max. 10 KB retentive memory 12 KB program memory / 8 KB memory / max. 10 KB retentive memory / max. 10 KB retentive			
On board digital I/C)	36 input points / 24 output points			
Process image size		256 bits input (I) / 256 bits output (Q)			
Analogue image		56 words input (AI) / 56 words output (AQ))		
Bit memory (M)		256 bits			
Temporary (local) n	memory (L)	The main program has 64 bytes, each sub	routine and interrupt program has 64 by	tes	
I/O module extension	The state of the s	6 extension modules		_	
Signal board extens		Max. 1 signal board		_	
•				4 in total	
High speed counter	15	4 in total Single phase: 4 of 200 kHz Quadrature phase: 2 of 100 kHz		Single phase: 4 of 100 kHz Quadrature phase: 2 of 50 kHz	
ulse output		3, 100 kHz		-	
Pulse capture input		14			
Cycle interrupt		2 in total, resolution is of 1ms,			
nterrupt Edge		4 rising edges and 4 falling edges (when u	sing optional signal module, there are	4 rising edges and 4 falling edges	
		6 edges each)	sang optional signal filodule, there are	Thisting cages and + failing eages	
Memory		Micro SDHC card (optional)			
Precision of real-tim		120 seconds/month		-	
Real-time clock hold	d time	In general 7 days, or min. 6 days when 25	°C (Maintenance free super capacitor)	-	
Performance/ Proc	essing Time				
Boolean		0.15 µs/instruction			
Moving word opera	ations	1.2 µs/instruction			
Real mathematical of		3.6 µs/instruction			
	n elements supported by				
POUs	il elements supported by	type/quantity			
		 interrupt program: 128 (0 to 127) Nesting depth from main program: 8 sub-program leve from interrupt program: 4 sub-program leve 			
			evei		
Accumulators		4	evei		
Accumulators Timer					
Гimer		4 type/quantity non-holding (or not retained) (TON, TOF			
Fimer Counters		4 type/quantity • non-holding (or not retained) (TON, TOF • holding (or retained) (TONR) : 64			
Fimer Counters Communications		4 type/quantity • non-holding (or not retained) (TON, TOF • holding (or retained) (TONR) : 64 256):192	pard) nort	
Timer Counters Communications Number of ports		4 type/quantity • non-holding (or not retained) (TON, TOF • holding (or retained) (TONR) : 64 256 1 PROFINET port/ 1 serial (RS485) /1 additi) : 192 onal serial (optional RS232/485 signal bo	pard) port	
Counters Communications Number of ports HMI equipment	amout (RC)	4 type/quantity • non-holding (or not retained) (TON, TOF • holding (or retained) (TONR) : 64 256 1 PROFINET port/ 1 serial (RS485) /1 additi max. 4 connection on serial port & max. 8) : 192 onal serial (optional RS232/485 signal bo	oard) port	
Timer Counters C ommunications Number of ports HMI equipment Programming equip	oment (PG)	4 type/quantity • non-holding (or not retained) (TON, TOF • holding (or retained) (TONR) : 64 256 1 PROFINET port/ 1 serial (RS485) /1 additi max. 4 connection on serial port & max. 8 PROFINET: 1 & Serial Port: 1) : 192 onal serial (optional RS232/485 signal be connection on PROFINET port	pard) port	
Counters Communications Number of ports HMI equipment Programming equip CPU (PUT/GET)	, ,	4 type/quantity • non-holding (or not retained) (TON, TOF • holding (or retained) (TONR) : 64 256 1 PROFINET port/ 1 serial (RS485) /1 additi max. 4 connection on serial port & max. 8) : 192 onal serial (optional RS232/485 signal be connection on PROFINET port	pard) port	
Counters Communications Number of ports HMI equipment Programming equip CPU (PUT/GET) PROFINET communi	ication	type/quantity non-holding (or not retained) (TON, TOF holding (or retained) (TONR): 64 256 1 PROFINET port/ 1 serial (RS485) /1 additi max. 4 connection on serial port & max. 8 PROFINET: 1 & Serial Port: 1 PROFINET (LAN): 8 clients and 8 server con) : 192 onal serial (optional RS232/485 signal be connection on PROFINET port	pard) port	
Counters Communications Number of ports HMI equipment Programming equip CPU (PUT/GET) PROFINET communi	ication	4 type/quantity • non-holding (or not retained) (TON, TOF • holding (or retained) (TONR) : 64 256 1 PROFINET port/ 1 serial (RS485) /1 additi max. 4 connection on serial port & max. 8 PROFINET: 1 & Serial Port: 1) : 192 onal serial (optional RS232/485 signal be connection on PROFINET port	oard) port	
Counters Communications Number of ports HMI equipment Programming equip CPU (PUT/GET) PROFINET communi	ication	type/quantity non-holding (or not retained) (TON, TOF holding (or retained) (TONR): 64 256 1 PROFINET port/ 1 serial (RS485) /1 additi max. 4 connection on serial port & max. 8 PROFINET: 1 & Serial Port: 1 PROFINET (LAN): 8 clients and 8 server con) : 192 onal serial (optional RS232/485 signal be connection on PROFINET port	oard) port	
Counters Communications Number of ports HMI equipment Programming equip CPU (PUT/GET) PROFINET communi PROFINET controller Maximum number of	ication r/device of PROFINET devices that	type/quantity non-holding (or not retained) (TON, TOF holding (or retained) (TONR): 64 256 1 PROFINET port/ 1 serial (RS485) /1 additi max. 4 connection on serial port & max. 8 PROFINET: 1 & Serial Port: 1 PROFINET (LAN): 8 clients and 8 server con) : 192 onal serial (optional RS232/485 signal be connection on PROFINET port	oard) port	
Counters Communications Number of ports HMI equipment Programming equip CPU (PUT/GET) PROFINET communi PROFINET controller Maximum number of the control of the connected to	ication r/device of PROFINET devices that o RT	type/quantity non-holding (or not retained) (TON, TOF holding (or retained) (TONR): 64 256 1 PROFINET port/ 1 serial (RS485) /1 additi max. 4 connection on serial port & max. 8 PROFINET: 1 & Serial Port: 1 PROFINET (LAN): 8 clients and 8 server con) : 192 onal serial (optional RS232/485 signal be connection on PROFINET port	oard) port	
Counters Communications Number of ports HMI equipment Programming equip CPU (PUT/GET) PROFINET communi PROFINET controller Maximum number of the control to the connected to the connected to the controller of the controller of the connected to the connec	ication r/device of PROFINET devices that o RT of modules	type/quantity non-holding (or not retained) (TON, TOF holding (or retained) (TONR): 64 256 1 PROFINET port/ 1 serial (RS485) /1 additi max. 4 connection on serial port & max. 8 PROFINET: 1 & Serial Port: 1 PROFINET (LAN): 8 clients and 8 server contyes/No 8) : 192 onal serial (optional RS232/485 signal be connection on PROFINET port	pard) port	
Counters Communications Number of ports HMI equipment CPU (PUT/GET) PROFINET communi PROFINET controller Maximum number of Can be connected to Maximum number of Open user communi	ication r/device of PROFINET devices that o RT of modules nication	type/quantity non-holding (or not retained) (TON, TOF holding (or retained) (TONR): 64 256 1 PROFINET port/ 1 serial (RS485) /1 additimax. 4 connection on serial port & max. 8 PROFINET: 1 & Serial Port: 1 PROFINET (LAN): 8 clients and 8 server con Yes/No 8 64 PROFINET (LAN): 8 active and 8 passive con PROFINET: 10/100 Mb/s RS485 system protocol: 9600, 19200 and	onal serial (optional RS232/485 signal be connection on PROFINET port nnections	pard) port	
Counters Communications Number of ports HMI equipment Programming equip CPU (PUT/GET) PROFINET communi PROFINET controller Maximum number of Can be connected to Maximum number of Open user communi Data transmission re	ication r/device of PROFINET devices that o RT of modules nication	4 type/quantity • non-holding (or not retained) (TON, TOF • holding (or retained) (TONR) : 64 256 1 PROFINET port/ 1 serial (RS485) /1 additi max. 4 connection on serial port & max. 8 PROFINET: 1 & Serial Port: 1 PROFINET (LAN): 8 clients and 8 server contyes/No 8 64 PROFINET (LAN): 8 active and 8 passive control profiners: 10/100 Mb/s	onal serial (optional RS232/485 signal be connection on PROFINET port nnections nnections	oard) port	
Counters Communications Number of ports HMI equipment Programming equip CPU (PUT/GET) PROFINET communi PROFINET controller Maximum number of Maximum number of Den user communicate transmission re- solation (external s	ication r/device of PROFINET devices that o RT of modules nication rate	type/quantity non-holding (or not retained) (TON, TOF holding (or retained) (TONR): 64 256 1 PROFINET port/ 1 serial (RS485) /1 additi max. 4 connection on serial port & max. 8 PROFINET: 1 & Serial Port: 1 PROFINET (LAN): 8 clients and 8 server con yes/No 8 64 PROFINET (LAN): 8 active and 8 passive con PROFINET: 10/100 Mb/s RS485 system protocol: 9600, 19200 and RS485 free port: 1200 to 115200 b/s PROFINET: Transformer isolation, 1500 V A	onal serial (optional RS232/485 signal be connection on PROFINET port nnections nnections	pard) port	
Counters Communications Number of ports HMI equipment CPU (PUT/GET) PROFINET communi PROFINET controller Maximum number of Maximum number of Den user communi Data transmission re solation (external s	ication r/device of PROFINET devices that o RT of modules nication rate	type/quantity non-holding (or not retained) (TON, TOF holding (or retained) (TONR): 64 256 1 PROFINET port/ 1 serial (RS485) /1 additi max. 4 connection on serial port & max. 8 PROFINET: 1 & Serial Port: 1 PROFINET (LAN): 8 clients and 8 server con Yes/No 8 64 PROFINET (LAN): 8 active and 8 passive con PROFINET: 10/100 Mb/s RS485 system protocol: 9600, 19200 and RS485 free port: 1200 to 115200 b/s PROFINET: Transformer isolation, 1500 V ARS485: none PROFINET: CAT5e shielded cable	onal serial (optional RS232/485 signal be connection on PROFINET port nnections nnections	pard) port	
Counters Communications Number of ports HMI equipment CPU (PUT/GET) PROFINET communi PROFINET controller Maximum number of Communication be connected to Maximum number of Den user communication re Counter transmission re Solation (external sections)	ication r/device of PROFINET devices that o RT of modules nication rate	type/quantity non-holding (or not retained) (TON, TOF holding (or retained) (TONR): 64 256 1 PROFINET port/ 1 serial (RS485) /1 additi max. 4 connection on serial port & max. 8 PROFINET: 1 & Serial Port: 1 PROFINET (LAN): 8 clients and 8 server con Yes/No 8 64 PROFINET (LAN): 8 active and 8 passive con PROFINET: 10/100 Mb/s RS485 system protocol: 9600, 19200 and RS485 free port: 1200 to 115200 b/s PROFINET: Transformer isolation, 1500 V ARS485: none PROFINET: CAT5e shielded cable	onal serial (optional RS232/485 signal be connection on PROFINET port nnections nnections	pard) port	
Counters Communications Number of ports HMI equipment CPU (PUT/GET) PROFINET communi PROFINET controller Maximum number of can be connected to Maximum number of Den user communi Oata transmission re solation (external s Type of cable Power source Voltage range	ication r/device of PROFINET devices that o RT of modules nication rate	type/quantity non-holding (or not retained) (TON, TOF holding (or retained) (TONR): 64 256 1 PROFINET port/ 1 serial (RS485) /1 additimax. 4 connection on serial port & max. 8 PROFINET: 1 & Serial Port: 1 PROFINET (LAN): 8 clients and 8 server contyes/No 8 64 PROFINET (LAN): 8 active and 8 passive contyes/No 8 64 PROFINET: 10/100 Mb/s RS485 system protocol: 9600, 19200 and RS485 free port: 1200 to 115200 b/s PROFINET: Transformer isolation, 1500 V ARS485: none PROFINET: CAT5e shielded cable RS485: PROFIBUS network cable	onal serial (optional RS232/485 signal be connection on PROFINET port nnections nnections 187500 b/s		
Counters Communications Number of ports HMI equipment Programming equip CPU (PUT/GET) PROFINET communi PROFINET controller Maximum number of can be connected to Maximum number of Data transmission re Isolation (external s Type of cable Power source Voltage range Power supply frequence	ication r/device of PROFINET devices that o RT of modules nication rate	type/quantity non-holding (or not retained) (TON, TOF holding (or retained) (TONR): 64 256 1 PROFINET port/ 1 serial (RS485) /1 additi max. 4 connection on serial port & max. 8 PROFINET: 1 & Serial Port: 1 PROFINET (LAN): 8 clients and 8 server cores. Yes/No 8 64 PROFINET (LAN): 8 active and 8 passive cores. PROFINET: 10/100 Mb/s RS485 system protocol: 9600, 19200 and RS485 free port: 1200 to 115200 b/s PROFINET: Transformer isolation, 1500 V ARS485: none PROFINET: CAT5e shielded cable RS485: PROFIBUS network cable 85 ~ 264 V AC 47 ~ 63 Hz 160 mA when voltage is 120 V AC (without a 300 mA sensor power output) 280 mA when voltage is 120 V AC (without a 300 mA sensor power output) 90 mA when voltage is 240 V AC (without a 300 mA sensor power output) 160 mA when voltage is 240 V AC (without a 300 mA sensor power output)	onal serial (optional RS232/485 signal be connection on PROFINET port nnections 187500 b/s	85 ~ 264 V AC 47 ~ 63 Hz 160 mA when voltage is 120 V AC (without a 300 mA sensor power outpu 280 mA when voltage is 120 V AC (with a 300 mA sensor power output) 90 mA when voltage is 240 V AC (without a 300 mA sensor power outpu 160 mA when voltage is 240 V AC	
Counters Communications Number of ports HMI equipment Programming equip CPU (PUT/GET) PROFINET communi PROFINET controller Maximum number of Communication of the controller Maximum number of M	ication r/device of PROFINET devices that o RT of modules nication rate signal and PLC logic side)	type/quantity non-holding (or not retained) (TON, TOF holding (or retained) (TONR): 64 256 1 PROFINET port/ 1 serial (RS485) /1 additi max. 4 connection on serial port & max. 8 PROFINET: 1 & Serial Port: 1 PROFINET (LAN): 8 clients and 8 server con Yes/No 8 64 PROFINET (LAN): 8 active and 8 passive con PROFINET: 10/100 Mb/s RS485 system protocol: 9600, 19200 and RS485 free port: 1200 to 115200 b/s PROFINET: Transformer isolation, 1500 V ARS485: none PROFINET: CAT5e shielded cable RS485: PROFIBUS network cable 85 ~ 264 V AC 47 ~ 63 Hz 160 mA when voltage is 120 V AC (without a 300 mA sensor power output) 90 mA when voltage is 240 V AC (without a 300 mA sensor power output) 90 mA when voltage is 240 V AC (without a 300 mA sensor power output)	onal serial (optional RS232/485 signal be connection on PROFINET port nnections nnections 187500 b/s C 20.4 ~ 28.8 V DC — 220 mA when voltage is 24 V DC (without a 300 mA sensor power output) 500 mA when voltage is 24 V DC	85 ~ 264 V AC 47 ~ 63 Hz 160 mA when voltage is 120 V AC (without a 300 mA sensor power outpu 280 mA when voltage is 120 V AC (with a 300 mA sensor power output) 90 mA when voltage is 240 V AC (without a 300 mA sensor power output)	

Model	CPU SR60 AC/DC/RLY	CPU ST60 DC/DC/DC	CPU CR60 AC/DC/RLY
Inrush current (max)	16.3 A when voltage is 264 V AC	11.5 A when voltage is 28.8 V DC	7.3 A when voltage is 264 V AC
Isolation (input power with the logic side)	1500 V AC	none	1500 V AC
Leakage current, AC line for functional	none		
earthing			
Hold time (power off)	30 ms when voltage is 120 V AC 200 ms when voltage is 240 V AC	20 ms when voltage is 24 V DC	50 ms when voltage is 120 V AC 400 ms when voltage is 240 V AC
Internal fuse (cannot be replaced by the user)	3 A, 250 V, Slow-blow fuse		
Sensor power source			
Voltage range	20.4 ~ 28.8 V DC		
Rated output current (max)	300 mA (short circuit protection)		
Maximum ripple noise (<10 MHz)	<1 V peak-peak value		
Isolation (CPU logic side and sensor power	Not isolated		
source) Digital input			
Number of input points	36		
Туре	The sinking / sourcing type (IEC type 1	The sinking/sourcing type (IEC type 1	The sinking/ sourcing type (IEC type 1
	sinking)	sinking excluding I0.0 to I0.3)	sinking)
Rated voltage	It is 24 V DC when the current is 4 mA, rate	ed value	
Allowable continuous voltage	Max 30 V DC		
Surge voltage	35 V DC, lasting 0.5 s	10.0 to 10.3 . 0	Other input: 15 VDC when it is 2.5 mA
Logic 1 signal (min)	The voltage is 4 V DC when it ranges from Other input: 15 V DC when it is 2.5 mA	10.0 to 10.3 : 8 mA	Other input: 15 V DC when it is 2.5 mA
Logic 0 signal (min)	It is 5 V DC when the current is 1 mA	The voltage is 1 V DC when it ranges	Other input: 5 V DC when it is 1 mA
		from I0.0 to I0.3: 1 mA Other input: 5 V DC when it is 1 mA	
Isolation (field side and logic side)	500 V AC, lasting 1 min		
Isolation group	1		
Filter time	Each channel can be separately selected (II 0.2, 0.4, 0.8, 1.6, 3.2, 6.4 and 12.8 µs 0.2, 0.4, 0.8, 1.6, 3.2, 6.4 and 12.8 ms Each channel can be separately selected (II		
HSC clock input frequency (max)	Single phase: 4 200 KHz + 2 30 KHz & Qua		
(Logic 1 battery = 15 ~ 26 V DC)	, ·		
Number of inputs that connect at the same time	36		
Cable length (max)	Shielded: 500m (normal input), 50m (HSC input) ; non shielded: 300m (normal input)	50 m (HSC input) All other inputs: shielded: 500 m (normal input) ; non shielded: 300 m	Shielded: 500m (normal input), 50m (HSC input) ; non shielded: 300m (normal input)
		(normal input)	
Digital output	24		
Number of output	24	Calidatata MOCEET (account to the	Dalass dans a see at
Type Voltage range	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC	Solid state-MOSFET (source-type) 20.4 ~ 28.8 V DC	Relay, dry contact 5 ~ 30 V DC or 5 ~ 250 V AC
Logic 1 signal when the current is max.	- 30 V DC 01 3 ~ 230 V AC	Min. 20 V DC	- 250 V DC 01 3 ~ 250 V AC
Logic 0 signal when the load is KG		Max. 0.1 V DC	_
Rated current at each point (max)	2.0 A	0.5 A	2.0 A
Lamp load	30 W DC/200 W AC	5 W	30 W DC/200 W AC
On state resistance	New equipment is 0.2 Ω maximally	Max. 0.6 Ω	New equipment is 0.2 Ω maximally
Leakage current at each point	-	Max. 10 μ A	-
Surge current	It is 7A when the contact is closed	8 A, max. lasting 100 ms	It is 7A when the contact is closed
Overload protection	none	, ,	
Isolation (field side and logic side)	1500 V AC, lasting 1 min (coil and	500 V AC, lasting 1 min	1500 V AC, lasting 1 min (coil and
	contact)		contact)
	none, (coil and logic side)		none, (coil and logic side)
Isolation resistance	New equipment is 100 MΩ minimally	-	New equipment is 100 MΩ minimally
Disconnect the insulation between the contacts	750 V AC, lasting 1 min	-	750 V AC, lasting 1 min
Isolated group	6	3	6
Inductive voltage clamp	Not recommended	L+ - 48 V DC, 1 W loss	-
Switching delay (Qa.0-Qa.3)	Max. 10 ms	From the disconnection to connection max.1 µs from the connection to disconnection is 3 µs max.	Max. 10 ms
Switching delay (Qa.4-Qb.7)	Max. 10 ms	From the disconnection to connection max. 50 μs from the connection to disconnection is 200 μs max.	
Mechanical life (no load)	10,000,000 break/close cycles	-	10,000,000 break/close cycles
Contact life under the rated load	100,000 break/close cycles	-	100,000 break/close cycles
Output state under the STOP mode	Last value or replicable value (The default	value is 0)	
Number of output that are connected at the same time	16		
Cable length	Shielded: 500 m; non shielded: 150 m		

Technical specification for digital input modules

Model	EM DE08	EM DE16	
Order No. (MLFB)	6ES7 288-2DE08-0AA0	6ES7 288-2DE16-0AA0	
Standard			
Dimension W x H x D (mm)	45 x 100 x 81		
Weight	141.4 g	176g	
Power consumption	1.5 W	2.3 W	
Current consumption (SM bus)	105 mA		
Current consumption (24 V DC)	4 mA for each input point used		
Digital input			
Number of input points	8	16	
Туре	The sinking / sourcing type	e (IEC type 1 sinking)	
Rated voltage	It is 24 V DC when the curvalue	rent is 4 mA, nominal	

Model	EM DE08	EM DE16
Allowable continuous voltage	Max 30 V DC	
Surge voltage	35 V DC, lasting 0.5 s	
Logic 1 signal (min)	It is 15 V DC when the cur	rent is 2.5 mA
Logic 0 signal (max)	It is 5 V DC when the curre	ent is 1 mA
Isolation (field side and logic side)	500 V AC, lasting 1 min	
Isolation group	2	4
Filter time	0.2, 0.4, 0.8, 1.6, 3.2, 6.4, 12.8 ms (optional 4 inputs form one group)	
Number of inputs that connect at the same time	8	16
Cable length (max)	500m (Shielded), 300m (r	non shielded)

Technical specification for digital output modules

Model	EM DR08	EM DT08	EM QR16	EM QT16
Order number (MLFB)	6ES7 288-2DR08-0AA0	6ES7 288-2DT08-0AA0	6ES7 288-2QR16-0AA0	6ES7 288-2QT16-0AA0
Standard				
Size W x H x D(mm)	45 x 100 x 81			
Weight	166.3 g	147 g	221g	186g
Power consumption	4.5 W	1.5 W	4.5W	1.7W
Current consumption (SM bus)	120 mA		110 mA	120 mA
Digital output				
Number of outputs	8		16	
Types	Relay, dry contact	Solid-MOSFET (source type)	Relay, dry contact	Solid state
MOSFET (source type) voltage range	5 ~ 30 V DC Or 5 ~ 250 V AC	20.4 ~ 28.8 V DC	5 ~ 30 V DC or 5 ~ 250 V AC	20.4 ~ 28.8 V DC
Logic 1 signal at maximum current	-	20 V	-	20 V
Logic 0 signal with 10 KΩ load	-	0.1 V	-	0.1 V
Rated current per point (maximum)	2.0 A	0.75 A	2.0 A	0.75 A
Lamp load	30 W DC/200 W AC	5 W	30 W DC/200 W AC	5 W
On-state contact resistance	New equipment is 0.2Ω maximally	0.6 Ω	New equipment is 0.2Ω maximally	0.6 Ω
Leakage current at each point	-	10 μΑ	_	10 μΑ
Inrush current	When the contact is closed 7 A	8 A, continued 100 ms	When the contact is closed 7 A	8 A, continued 100 ms
Overload protection	no			
Isolation (field side and logic side)	1500 V AC, Lasts 1 min (coil and contacts) None (coil and logic side)	500 V AC, Lasting 1 min	1500 V AC, Lasts 1 min (coil and contacts) None (coil and logic side)	500 V AC, lasting 1 min
Isolation resistance	New equipment min100M Ω	-	xNew equipment min 100 $M\Omega$	-
Disconnect the insulation between the contacts	750 V AC, Lasting 1 min	-	750 V AC,Lasting 1 min	-
Isolation group	2	2	4	4
Current of each public end (max)	8 A	3 A	8 A	3 A
Switching delay	Max10 ms	Disconnect to the maximum le	ength of 50 µs and Switch ti	switch to the max of 200 μs
Contact life at rated load	100,000 open/close cycle	-	100,000 open/close cycle	-
Output status in STOP mode	Previous value or replacement	t value (default is 0)		
Number of outputs simultaneously turned on	8		16	
cable length	Shielded: 500 m; non shielded	d: 300 m		

Technical specification for digital input/output modules

Model	EM DR16	EM DT16	EM DR32	EM DT32
Order No.: (MLFB)	6ES7 288-2DR16-0AA0	6ES7 288-2DT16-0AA0	6ES7 288-2DR32-0AA0	6ES7 288-2DT32-0AA0
Dimension W x H x D (mm)	45 x 100 x 81		70 x 100 x 81	
Weight	201.9 g	179.7 g	295.4 g	257.3 g
Power consumption	5.5 W	2.5 W	10 W	4.5 W
Current consumption (SM bus)	145 mA	145 mA	180 mA	185 mA
Current consumption (24 V DC)	4 mA for each input point use	d		
·	Each relay coil used is 11 mA	-	Each relay coil used is 11 mA	-
Digital input				
Number of input points	8		16	
Туре	The sinking / sourcing type (IE	C type 1 sinking)		
Rated voltage	It is 24V DC when the current	is 4 mA, nominal value		
Allowable continuous voltage	Max 30 V DC			
Surge voltage	35 V DC, lasting 0.5 s			
Logic 1 signal (min)	15 V DC			
Logic 0 signal (min)	5 V DC			
solation (field side and logic side)	500 V AC, lasting 1 min			
solation group	2			
Filter time	0.2, 0.4, 0.8, 1.6, 3.2, 6.4 and	l 12.8 ms (optional, 4 form or	ie group)	
Number of inputs that connect at the same time	8		16	
Cable length	500 m (Shielded), 150 m (nor	shielded)		
Digital output				
Number of output	8		16	
Туре	Relay, dry contact	Solid state-MOSFET	Relay, dry contact	Solid state-MOSFET
Voltage range	5 ~ 30 V DC or 5 ~ 250 V AC	20.4 ~ 28.8 V DC	5 ~ 30 V DC or 5 ~ 250 V AC	20.4 ~ 28.8 V DC
Logic 1 signal when the current is max.	-	Min. 20 V DC	-	Min. 20 V DC
Logic 0 signal when the load is KG	-	Max. 0.1 V DC	-	Max. 0.1 V DC
Rated current at each point (max)	2 A	0.75 A	2 A	0.75 A
Lamp load	30 W DC/200 W AC	5 W	30 W DC/200 W AC	5 W
Resistance of the contact in the ON state	New equipment is 0.2Ω maximally	Max. 0.6 Ω	New equipment is 0.2Ω maximally	Max. 0.6 Ω
Leakage current at each point	-	Max. 10 μ A	-	Max. 10 μ A
Surge current	It is 7A when the contact is closed	8 A, max. lasting 100 ms	It is 7A when the contact is closed	8 A, max. lasting 100 ms
Overload protection	none			
Isolation (field side and logic side)	1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side)	500 V AC, lasting 1 min	1500 V AC, lasting 1 min (coil and contact) none, (coil and logic side)	500 V AC, lasting 1 min
Isolation resistance	New equipment is 100 $M\Omega$ minimally	-	New equipment is 100 $M\Omega$ minimally	-
Disconnect the insulation between the contacts	750 V AC, lasting 1 min	-	750 V AC, lasting 1 min	-
solated group	2	2	4	3
Each end of the current public	8 A	3 A	8 A	6 A
Inductive voltage clamp	-	-48 V	-	-48 V
Switching delay	From the disconnection to connection max.1 µs from the connection to disconnection is 3 µs max.	Max. 10 ms	From the disconnection to connection max.1 µs from the connection to disconnection is 3 µs max.	Max. 10 ms
Mechanical life (no load)	10,000,000 break/close cycles	-	10,000,000 break/close cycles	-
Contact life under the rated load	100,000 break/close cycles	_	100,000 break/close cycles	_
Output state under the STOP mode	Last value or replicable value (
Number of output that are connected at the same time	8		16	
Cable length	Shielded: 500 m; non shielded	1. 300 m		

Technical specification for digital input modules

Model	EM AE04	EM AE08
Order No.: (MLFB)	6ES7 288-3AE04-0AA0	6ES7 288-3AE08-0AA0
Standard		
Dimension W x H x D (mm)	45 x 100 x 81	
Weight	147 g	186 g
Power consumption	1.5 W (no load)	2.0 W (no load)
Current consumption (SM bus)	80 mA	
Current consumption (24 V DC)	40 mA (no load)	70 mA (no load)
Analogue input		
No. of Inputs	4	8
Туре	Voltage or current (differ 2 can be selected as a gro	
Range	±10 V, ±5 V, ±2.5 V, or 0	~ 20 mA
Full scale range (data word)	-27, 648 ~ 27, 648	
Overshoot / undershoot range (data word)	Voltage: 27, 649 ~ 32, 511/-27, 649 ~ -32, 512 Current: 27, 649 ~ 32, 511/-4864 ~ 0	
Overflow / underflow (data word)	Voltage: 32, 51 2 ~ 32, 767/-32, 51 3 ~ -32, 768 Current: 32, 512 ~ 32, 767/-4, 865 ~ -32, 768	
Resolution	Voltage mode: 11 bits + signal bits Current mode: 11 bits	
Maximum voltage / current resistance	±35 V/±40 mA	
Smoothness	None, weak, medium or strong	
Noise suppression	400, 60, 50 or 10 Hz	
Input resistance	≥9 M Ω (voltage) / 250 Ω (current)	
Isolation (field side and logic side)	none	
Precision (25°C / 0 ~ 55°C)	Voltage mode: full range ±0.1 %/±0.2 % Current mode: full range ±0.2 %/±0.3 %	
Analogue to digital conversion time	625 μs (400 Hz inhibited)	
Common mode rejection	40 dB, DC to 60 Hz	
The working signal range	Signal plus common mode voltage must be less than +1 2 and greater than -12 V;	
The cable length (maximum)	100 m, Shielded twisted pair	
Diagnosis		
Overflow / underflow	✓	
24 V DC low voltage	✓	

Technical specification for analogue output modules

Model	EM AO02	EM AO04
Order No.: (MLFB)		6ES7 288-3AQ04-0AA0
Standard	0237 200 371002 07810	0237 200 37 100 1 070 10
Dimension W x H x D (mm)	45 x 100 x 81	
Weight	147.1 q	170.5g
Power consumption	1.5 W (no load)	2.1 W (no load)
Current consumption (SM bus)	60 mA	
Current consumption (24 V DC)	50 mA (no load)	75 mA (no load)
Analogue output		
No. of Inputs	2	4
Туре	Voltage or current	
Range	±10 V or 0 ~ 20 mA	
Resolution	Voltage mode: 10 bits + signal bits Current mode: 10 bits	
Full scale range (data word)	Voltage: -27, 648 ~ 27, 648 Current: 0 to 27, 648	
Precision (25°C/0 ~ 55°C)	Full range ±0.5 %/ ±1.0 %	
Stabilisation time (95% of the new value)	Voltage: 300 μs (R), 750 μs (R), 750 μs (1 μ F) Current: 600 μs (1 mH), 2 ms (10 mH)	
Load resistance	Voltage: $> 1000 \Omega$ Current: $< 500 \Omega$	
Output state under the STOP mode	Last value or replicable value (The default value is 0)	
Isolation (field side and logic side)	none	
Cable length (max)	100 m, shielded twisted pair	
Diagnosis		
Overflow / underflow	✓	
Short circuit to ground (only for voltage mode)	✓	
Circuit breaker (only for current mode)	✓	
24 V DC low voltage	✓	

Technical specification for analogue input/output modules

Model	EM AM06	EM AM03
Order No.: (MLFB)	6ES7 288-3AM06-0AA0	6ES7 288-3AM03-0AA0
Standard		
Dimension W x H x D (mm)	45 x 100 x 81	
Weight	173.4 g	172 g
Power consumption	2.0 W (no load) / 1.1 W (r	no load)
Current consumption (SM bus)	80 mA / 60 mA	
Current consumption (24 V DC)	60 mA (no load) / 30 mA	(no load)
Analogue input		
No. of Inputs	4	2
Туре	Voltage or current (differential): 2 can be selected as a group	
Range	±10 V, ±5 V, ±2.5 V, or 0 ~ 20 mA	
Full scale range (data word)	-27, 648 ~ 27, 648	
Overshoot / undershoot range (data word)	Voltage: 27, 649 ~ 32, 511/-27, 649 ~ -32, 512 Current: 27, 649 ~ 32, 511/-4864 ~ 0	
Overflow / underflow (data word)	Voltage: 32, 51 2 ~ 32, 767/-32, 51 3 ~ -32, 768 Current: 32, 512 ~ 32, 767/-4, 865 ~ -32, 768	
Resolution	Voltage mode: 11 bits + signal bits Current mode: 11 bits	
Maximum voltage / current resistance	±35 V/±40 mA	
Smoothness	None, weak, medium or strong	
Noise suppression	400, 60, 50 or 10 Hz	
Input resistance	\geq 9 M Ω (voltage) / 250 Ω (current)	
Isolation (field side and logic side)	none	
Precision (25°C / 0 ~ 55°C)	Voltage mode: full range Current mode: full range	
Analogue to digital conversion time	625 μs (400 Hz inhibited))

Model	EM AM06	EM AM03
Common mode rejection	40 dB, DC to 60 Hz	
Working signal range	Signal plus common mode voltage must be less than the +1 2 V is greater than -12 V	
The cable length (maximum)	100 m, Shielded twisted	pair
Analogue output		
No. of Inputs	2	1
Туре	Voltage or current	
Range	±10 V or 0 ~ 20 mA	
Resolution	Voltage mode: 10 bits + signal bits Current mode: 10 bits	
Full scale range (data word)	Voltage: -27, 648 ~ 27, 648 Current : 0 ~ 27, 648	
Precision (25°C/0 ~ 55°C)	Full range ±0.5 %/ ±1.0 %	
Stabilisation time (95% of the new value)	Voltage: 300 μs (R), 750 μs (R), 750 μs (1 μ F) Current: 600 μs (1 mH), 2 ms (10 mH)	
Load resistance	Voltage $\geq 1000 \Omega$ Current $\leq 600 \Omega$	
Output state under the STOP mode	Last value or replicable vis 0)	alue (The default value
Isolation (field side and logic side)	None	
Cable length (max)	100 m, shielded twisted pair	
Diagnosis		
Overflow / underflow	✓	
Short circuit to ground (only for voltage mode)	✓	
Circuit breaker (only for current mode)	✓	
24 V DC low voltage	✓	

Technical specification for digital input / output signal board

Model	SB DT04
Order No.: (MLFB)	6ES7 288-5DT04-0AA0
Standard	
Dimension W x H x D (mm)	35 x 52.2 x 16
Weight	18.1 g
Power consumption	1.0 W
Current consumption (SM bus)	50 mA
Current consumption (24 V DC)	Each input used 4mA
Analogue input	
No. of Inputs	2
Туре	Sinking type/sourcing type (IEC type 1 sinking)
Rated voltage	24 V DC, When the current is 4 mA, nominal value
Allowable continuous voltage	Max. 30 V DC
Surge voltage	35 V DC, lasting 0.5 s
Logic 1 signal (min)	15 V DC when the current is 2.5mA.
Logic 0 signal (max)	5 V DC when the current is 1 mA.
Isolation (field side and logic side)	500 V AC, lasting 1 min
Isolation group	1
Filter time	Each channel can be selected separately 0.2, 0.4, 0.8, 1.6, 3.2, 6.4 and 12.8 µs 0.2, 0.4, 0.8, 1.6, 3.2, 6.4 and 12.8 µs
Number of inputs connected at the same time	2
Cable length	500 m (shielded), 300 m (non shielded)
Digital output	
Number of outputs	2
Type of output	Solid state -MOSFET
Voltage range	20.4 ~ 28.8 V DC
Logic 1 signal at max current	Min 20 V DC
Logic 0 signal at max current	Max 0.1 V DC
Rated current of each point (max)	0.5 A
Lamp load	5 W
Contact resistance in the ON status	Max 0.6Ω
Current leakage at point	Max. 10 μA
Surge current	5 A, max lasting 100 ms
Overload protection	No
Isolation (field side and logic side)	500 V AC, lasting 1 min
Isolation group	1
Current of each public end	1 A
Inductive voltage clamp	L + - 48 V, 1 W loss
Switching delay	Disconnected to connected maximally 2 μs connected to disconnected maximally 10 μs
Output state under the STOP mode	Last value or replicable value (The default value is 0)
Number of inputs connected at the same time	2
Cable length (max)	500 m (shielded), 150 m (non shielded)

Technical specification for battery signal board

Model	SB BA01
Order No.: (MLFB)	6ES7 288-5BA01-0AA0
Standard	
Dimension W x H x D (mm)	35 x 52.2 x 16
Weight	20 g
Power consumption	0.6 W
Current consumption (SM bus)	18 mA
Current consumption (24 V DC)	None
Battery (need to be bought by the	user)
Hold duration	About 1 year
Type of battery	CR1025cell battery
Nominal voltage	3 V
Nominal capacity	30 mAH
Diagnosis	
Critical cell voltage	<2.5 V
Battery diagnosis	Low voltage lamp:
	Low battery voltage will cause the BA01 panel
	of the LED display in red state
	Diagnosis alarm / or low power digital output status available
Battery status	The battery status provided
	0 =battery normal
	1= Low battery
Battery status update	Battery status will be updated in the boot,
	then the CPU in RUN mode

Technical specification for analogue output signal board

Model	SB AQ01
Order No.: (MLFB)	6ES7 288-5AQ01-0AA0
Standard	
Dimension W x H x D (mm)	35 x 52.2 x 16
Weight	17.4 g
Power consumption	1.5 W
Current consumption (SM bus)	15 mA
Current consumption (24 V DC)	40 mA (no load)
Analogue output	
No. of Inputs	1
Туре	Voltage or current
Range	±10 V or 0 ~ 20 mA
Resolution	Voltage mode: 11 bits + signal bits Current mode: 11 bits
Full scale range (data word)	-27, 648 ~ 27, 648 (-10V ~ 10 V) 0 ~ 27, 648 (0 ~ 20 mA)
Precision (25°C/0 ~ 55°C)	±0.5 %/ ±1.0 %
Stabilisation time (95% of the new value)	Voltage: 300 μs (R), 750 μs (R), 750 μs (1 μ F) Current: 600 μs (1 mH), 2 ms (10 mH)
Load resistance	Voltage ≥ 1000 Ω Current ≤ 600 Ω
Output state under the STOP mode	Last value or replicable value
Isolation (field side and logic side)	none
Cable length (max)	10 m, shielded twisted pair
Diagnosis	✓
Overflow / underflow	✓
Short circuit to ground (only for voltage mode)	✓
Circuit breaker (only for current mode)	✓

Technical specification for RS485/232 signal board

Model	1 SB CM01
Order No	6ES7 288-5CM01-0AA0
Standard	
Dimension W x H x D (mm)	35 x 52.2 x 16
Weight	18.2 g
Power consumption	0.5 W
Current consumption (5 V DC)	50 mA
Current consumption (24 V DC)	Not applicable
Transmitter and receiver (RS485)	
common-mode voltage range	$-7 \text{ V} \sim +12 \text{ V}$, 1 s, 3 VRMS continuous
Transmitter differential output voltage	min 2 V when RL = 100 Ω min 1.5 V when RL = 54 Ω
Termination and bias	On TXD 4.7 K Ω for +5 V On RXD 4.7 K Ω for GND
Receiver input impedance	Min 12 KΩ
The receiver threshold / sensitivity	Minimum +/-0.2 V, the typical lag 60 mV
Isolation The RS485 signal and the shell grounding RS485 signal and CPU logic common end	None
Length of cable, shielded cable	Isolation repeaters: 1000 m, baud rate up to 187.5 K No isolation repeaters: 50 m
Transmitter and receiver (RS232)	
Transmitter output voltage	Minimum +/-5V, when RL two 3 K
Output voltage sent	MAX. +/-1 5 V DC
Receiver input resistance	Min 3 KΩ
Receiver threshold / sensitivity	Lower limit 0.8 V, top limit 2.4 V typical lag 0.5 V
Receiver input voltage	Max +/- 30 V DC
Isolation The RS232 signal and the shell grounding RS232 signal and CPU logic common end	None
Length of cable, shielded cable	Max. 10 m

Technical specification for RTD module

Model	EM AR02	EM AR04
Order No.: (MLFB)	6ES7 288-3AR02-0AA0	6ES7 288-3AR04-0AA0
Standard		
Dimension W x H x D (mm)	45 x 100 x 81	
Weight	148.7 g	150 q
Power consumption	1.5 W	
Current consumption (SM bus)	80 mA	
Current consumption (24 V DC)	40 mA	
Analogue input		
No. of Inputs	2	
Туре	RTD and resistance value ground	of module reference
Panga	Please refer to RTD senso	er coloction table in the
Range Nominal range (data word)	S7-200 SMART System M	
overshoot / undershoot range (data	37 200 SWITHT SYSTEM IV	iariaar
word)		
Overflow / underflow (data word)		
Resolution		
Temperature	0.1°C / 0.1°F	
Resistance	15 position + sign	
Maximum voltage hold	±35 V	
Noise suppression	85 dB, 10 Hz/50 Hz/60 Hz	z/400 Hz
Common mode rejection	> 120 dB	
Resistance	$>$ 10 M Ω	
isolation		
Field side and logic side	500 V AC	
Field side and 24 V DC side	500 V AC	
24 V DC side and logic side	500 V AC	
Channel to channel isolation	0	
Precision	Please refer to RTD senso	r selection table
Repeatability	±0.05 % FS	
Maximum power consumption of the sensor	0.5 m W	
Measuring principle	Sigma-Delta	
Module update time	Please refer to the noise	reduction selection table
Cable length (maximum)	The maximum length to	the sensor is 100 m
Cable resistance	Max.20 Ω, for Cu10, max	c. is 2.7 Ω
Diagnosis		
Overflow / underflow	✓	
Circuit breaker (only current mode)	✓	
24 V DC low voltage	✓	

Technical specification of thermocouple module

Model	EM AT04
Order No.: (MLFB)	6ES7 288-3AT04-0AA0
Standard	
Dimension W x H x D (mm)	45 x 100 x 81
Weight	125 g
Power consumption	1.5 W
Current consumption (SM bus)	80 mA
Current consumption (24 V DC)	40 mA
Analogue input	
No. of Inputs	4
Range Nominal range (data word) overshoot / undershoot range (data word) Overflow / underflow (data word)	Please refer to RTD sensor selection table in the S7-200 SMART System Manual
Resolution	
Temperature	0.1°C / 0.1°F
Resistance	15 position + sign
Maximum voltage hold	±35 V
Noise suppression	For the selected filter settings (10 Hz, 50 Hz, 60 Hz or 400 Hz) is 85 dB
Common mode rejection	120 V AC of, > 120 dB
Resistance	≥ 10 M Ω
isolation	
Field side and logic side	500 V AC
Field side and 24 V DC side	500 V AC
24 V DC side and logic side	500 V AC
Channel to channel isolation	-
Precision	Please refer to RTD sensor selection table
Repeatability	±0.05 % FS
Maximum power consumption of the sensor	Integral type
Module update time	Please refer to the noise reduction selection table
The cold end temperature error	± 1.5 °C
Cable length (maximum)	The maximum length to the sensor is 100 m
Cable resistance	Max. 100 Ω
Diagnosis	
Overflow / underflow	✓


General technical specifications

EN 61000-4-2 electrostatic discharge	8 kV, the air discharge to all surfaces; ±4 kV, conductive contact discharge on the exposed surface	
FN 61000-4-3	When 80 ~ 1000 MHz, 10 V/m, 1 kHz, 80 % AM	
Radiation, radio frequency, electromagnetic field immunity test	When 1.4 ~ 2.0 GHz, 3 V/m, 1 kHz, 80 % AM	
nadiation, radio frequency, electromagnetic field immunity test	When 2.0 ~ 2.7 GHz, 1 V/m, 1 kHz, 80 % AM	
EN 61000-4-4 fast transient Bursts	2 kV, 5 kHz, - a coupled network of AC and DC power supply systems ; 2 kV, 5 kHz, I/O coupling clam	
EN 61000-4-5	AC system — 2 kV Common mode, 1 kV Differential mode	
Surge immunity	DC system — 2 kV Common mode, 1 kV Differential mode	
	For the DC system (I/O signal, DC power supply system), need the external protection	
EN61000-4-6 Conducted interference	When 150 kHz ~ 80 MHz, 10 V RMS, 1 kHz, 80 % AM	
EN61000-4-11 Voltage dip	Communication systems; 60 Hz, 0% for 1 cycles, 40% for 12 cycles and 70% for 30 cycles	
Electromagnetic compatibility of a conduction and radiation in accordance with	EN 61000-6-4	
Transmission of EN55001, class A, group 1	0.15 MHz \sim 0.5 MHz $<$ 79 dB (µV) Quasi peak ; $<$ 66 dB (µV) Average value	
	0.5 MHz \sim 5 MHz $<$ 73 dB (µV) Quasi peak ; $<$ 60 dB (µV) Average value	
	5 MHz \sim 30 MHz $<$ 73 dB (μ V) Quasi peak ; $<$ 60 dB (μ V) Average value	
Radiation EN55001, Class A, Group 1	30 MHz \sim 230 MHz $<$ 40 dB ($\mu V/m$) Quasi peak ; Measured distances is 10m	
	230 MHz \sim 1 GHz $<$ 47 dB (μ V/m) Quasi peak ; Measured distances is 10m	
Environmental conditions -transport and storage		
EN60068-2-2, Bb test, EN60068-2-1 test Ab, hot and cold	-40°C~70°C	
EN60068-2-30, Db test, damp heat	25°C ~ 55°C / humidity 95 %	
EN60068-2-14 Na test, a temperature change	-40~ 70°C, residence time 3hrs, 2 cycles	
EN60068-2-32, free fall	0.3 m, 5times, product package	
Atmospheric pressure	1080 ~ 660 hPa (equivalent to altitude -1000 ~ 3500 m)	
Environment conditions -running		
Ambient temperature range (25 mm height space under the equipment for the wind		
coming in)	0°C ~ 45°C, vertical installation	
	Humidity 95 %, No condensation	
Atmospheric pressure	1080 ~ 795 hPa (equivalent to altitude 1000 ~ 2000 m)	
Pollutant concentration	SO2: < 0.5 ppm ; H2S : < 0.1 ppm ; RH < 60 %, No condensation	
EN 60068-2-14, Nb test, temperature change	5°C ~ 55°C, 3°C/min	
EN 60068-2-27 mechanical shock	15 G, 11 ms pulse, 3 axes upwards 6 impacts	
EN 60068-2-6 Sinusoidal vibration	When DIN guide rail mounting : 5 ~ 9 Hz, 3.5 mm, when 9 ~ 150 Hz, 1 G	
	Panel installation : when 5 ~ 9 Hz, 7.0 mm, when 9 ~ 150 Hz, 2 G	
	Each axis swings 10 times, each divided into 1 octave	
High voltage insulation test		
24 V/5 V nominal circuit	520 V DC (optical isolation boundary type test)	
115/230 V Ground circuit	1500 V AC routine test/1950 V DC type test	
11 5/230 V circuit for a 115/230 V circuit	1500 V AC routine test /1950 V DC type test	
11 5/230 V circuit for a 24 V/5 V circuit	1500 V AC routine test /3250 V DC type test	
Ethernet port on 24 V/5 V circuit and ground	1500 V AC (only the type testing)	


Mounting dimensions

© Side view © Horizontal mounting © Vertical mounting © Gap area Be sure to bear in mind the following guidelines, when planning the installation: The equipment shall be isolated from the thermal radiation, high voltage and electrical noise. Leave enough space for cooling and wiring. A 25mm height space above or under the equipment must be left so as to allow free air circulation. Please refer to "S7-200 SMART System Manual" for the specific requirements of installation and guidelines.


Input and output wiring diagram




Order number description




Schematic diagram of the module and the signal board wiring







CPU SR60




CPU ST60




EM DE08




EM DE16




EM DT08




EM DR08




EM QT16




EM QR16




EM DT16



EM DR16





Simple but extraordinary

The SIMATIC S7-200 SMART Compact CPU launched by Siemens in response to market demand is economical and practical, with high cost performance. Cooperating with KTP700 man-machine interface and SINAMIC V20 inverter, it can provide an ideal solution for your small automation control system.



A new generation of economical S7-200 SMART CPU S7-200 SMART Compact CPU

- Economy type CPU module has four configurations of 20 I/O, 30 I/O, 40 I/O, 60 I/O
- \bullet High-speed processor chip, bit instruction execution time can reach 0.15 μs
- Support high-speed counting function, can realize singlephase 4-way 100KHz or 2-way A/B phase 50KHz input
- Integrated power-off data retention function, no need for special batteries, just simple settings, easy Realize permanent power-off data retention
- The main body integrates an RS485 communication interface, which can be connected to a touch screen or a frequency converter
- Serial port isolation, support Modbus-RTU, USS, Freeport communication
- The input and output terminals of the CPU module are detachable and support rail or screw installation
- 220 V AC or 110 V DC power supply, relay output, support source or sink input
 Using STEP7 Micro/WIN SMART programming software, more friendly interface and easier operation 33
 Simple, full support for Windows 10 operating system

Economic CPU CR20s/CR30s/CR40s/CR60s specifications

MODEL	CPU CR20s AC/DC/RLY	CPU CR30s AC/DC/RLY	CPU CR40s AC/DC/RLY	CPU CR60s AC/DC/RLY
Order no (MLFB)	6ES7 288-1CR20-0AA1	6ES7 288-1CR30-0AA1	6ES7 288-1CR40-0AA1	6ES7 288-1CR60-0AA1
Standard				
Dimension W x H x D (mm)	90×100×81	110×100×81	125 x 100 x 81	175×100×81
Weight	367g	435g	440 g	620 g
Power consumption	14W	14W	18 W	20 W
Available current (24 V DC)	300 mA maximum (senso	or power supply)		
DI current consumption (24 V DC)	4mA per point used			
CPU feature	por point assa			
User Storage	12 KR program memory /	8 KB data memory / 2 KB re	tentive memory	
Onboard number I/O	12DI/8DO	18DI/12DO	24DI/16DO	36 DI/24DO
Process image size		256-bit input (I) / 256-bit output (Q)		
		output (Q)		
Analog image	2E6 Bit			
Bit memory (M)	256 Bit		ata a ditakan makan ma	
Temporary (partial) storage	64 bytes in the main prog	gram, 64 bytes in each subro	outine and interrupt progra	m
I/O module extension	-			
Signal board expansion	-			
High speed counter	Single phase 4, 100 KHz	4 in total Single phase 4, 100 KHz Quadrature phase 2, 50 KHz		
Pulse output	-			
Interrupted				
4 rising edges and 4 falling edges				
Storage card	-			
Real time clock accu	-			
Real time clock hold time	_			
Performance				
Boolean operation	0.15 µs/instruction			
Mobile word	1.2 µs/instruction			
Real mathematical operation	3.6 µs/instruction			
S7-200 SMART Supported user prog				
POUs	Type/quantity • Main program: 1 • Subroutine: 128 (0 to 1 • Interrupt program: 128 Nesting depth • From main program: 8 • • From interrupt program	(0 to 127) subroutine levels		
Accumulator				
Timer	4 types / quantity • Non-retentive (TON, TO • Retention: 64	Non-retentive (TON, TOF): 192		
Counter	256			
Communication				
Number of ports	Serial port: 1 (RS485)			
HMI device		Serial port: 4 connections per port		
Programming device (PG)	Serial port: 1 connection			
Data transfer rate		RS485 system protocol: 9600, 19200 and 187500 b/s RS485 free port: 1200 to 115200 b/s		
Cable type		RS485: PROFIBUS network cable		
Power Supply				
Voltage range	85 ~ 264 V AC	85 ~ 264 V AC		
Power frequency	47 ~ 63 Hz			
Input current only includes CPU	90mA at 120V AC 130 mA 90 mA at 120 V AC			
input current only includes CPO	60mA at 240V AC		240V AC 130 MA	at 150 mA 240 V AC
Inrush current (MAX)	9.3A at 264V AC		7.3 A at 264 V AC	
, ,				

MODEL	CPU CR20s AC/DC/RLY	CPU CR30s AC/DC/RLY	CPU CR40s AC/DC/RLY	CPU CR60s AC/DC/RLY
Leakage current, AC line pair functionally	0.5 mA			
Hold time (power down)	30ms at 120V AC 50 ms at 120 V AC 200ms at 240V AC 400 ms at 240 V AC			
Internal fuse (users cannot replace)	3 A, 250 V, slow blow			
Digital input				
Input Points	12	18	24	36
Types of	Sink/source (IEC Class 1 missing type)			
Rated voltage	24 V DC at 4 mA, rating			
Allowed continuous voltage	30 V DC maximum			
Surge voltage	35 V DC for 0.5 s			
Logic 1 signal (minimum)	15 V DC at 2.5 mA			
Logic 0 signal (maximum)	5 V DC at 1 mA			
Isolation (field side and logic side)	500 V AC for 1 min			
Isolation group	1			
Filtering time	Each channel can be selected individually (points I0.0 to I1.3): 0.2, 0.4, 0.8, 1.6, 3.2,6.4 and 12.8 µs0.2, 0.4, 0.8, 1.6, 3.2,6.4 and 12.8 ms	Each channel can be selected individually (points 10.0 to 11.5): 0.2, 0.4, 0.8, 1.6, 3.2, 6.4 and 12.8 µs 0.2, 0.4, 0.8, 1.6, 3.2, 6.4 and 12.8 ms Each channel can be selected individually (points 11.6 and larger): 0,6.4,12.8	Each channel can be selected individually (points 10.0 to 11.5): 0.2, 0.4, 0.8, 1.6, 3.2, 6.4 and 12.8 µs 0.2, 0.4, 0.8, 1.6, 3.2, 6.4 and 12.8 ms Each channel can be selected individually (points 11.6 and larger): 0,6.4,12.8 ms	Each channel can be selected individually (points I0.0 to I1.5): 0.2, 0.4, 0.8, 1.6, 3.2, 6.4 and 12.8 µs 0.2, 0.4, 0.8, 1.6, 3.2, 6.4 and 12.8 ms Each channel can be selected individually(points I1.6 and larger): 0,6.4,12.8
HSC clock input frequency (maximum) (logic 1 level = 15 ~ 26 V DC)	Single phase: 4, 100 KHz Quadrature phase: 2, 50 K	Hz		
Number of inputs simultaneously turned on	12	18	24	36
Cable length	Shield: 500m (normal inpu	ut), 50m (HSC input);Unshie	lded: 300m (normal input)	
Digital Output				
Output Points	8	12	16	24
Types of	Relay, dry contact			
Voltage Range	5 ~ 30 V DC or 5 ~ 250 V A	NC .		
Logic 1 signal at maximum current	-			
Logic 0 signal with 10 KΩ load	-			
Rated current per point (maximum)	2.0 A			
Lamp load	30 W DC/200 W AC			
On-state resistance	The new device is maximum 0.2 Ω			
Leakage current at each point	-			
Inrush current	When the contact is closed 7A			
Overload protection	NO			
Isolation (field side and logic side)	1500 V AC for 1 min (coil and electric shock) None (coil and logic side)			
Isolation resistance	The new device is a minimum of 100 $M\Omega$			
Disconnect insulation between contacts	750 V AC for 1 min			
Isolation group	2	3	4	6
Inductive clamping voltage	-			
Switch delay	Up to 10 ms			
Mechanical life (no load)	10,000,000 open/close cycle			
Contact life at rated load	100,000 open/close cycle			
Output status in STOP mode	Previous value or replacement value (default is 0)			
Number of outputs simultaneously turned on	8	12	16	24
cable length	500m (shielded), 150m (unshielded)			



Opening up a new era of PROFINET communication



CPU model supporting PROFINET communication

CPUTypes of	MLFB
CPU SR20, AC/DC/RLY	6ES7288-1SR20-0AA0
CPU ST20, DC/DC/DC	6ES7288-1ST20-0AA0
CPU SR30, AC/DC/RLY	6ES7288-1SR30-0AA0
CPU ST30, DC/DC/DC	6ES7288-1ST30-0AA0
CPU ST40, DC/DC/RLY	6ES7288-1SR40-0AA0
CPU SR40, AC/DC/DC	6ES7288-1ST40-0AA0
CPU SR60, AC/DC/RLY	6ES7288-1SR60-0AA0
CPU ST60, DC/DC/DC	6ES7288-1ST60-0AA0

Note: 1. The firmware version of the CPU is V2.4 and above.

2. Programming software SETP7 Micro/WIN SMART version is V2.4 and above

PROFINET communication performance

PROFINET Performance	Parameter
PROFINET Maximum number of devices	8
PROFINET Device number of the device	1 to 8
Maximum input size per PROFINET device	128 bytes
Maximum output size per PROFINET device	128 bytes
Maximum number of modules	64
Minimum cycle update time for PROFINET devices Depending on the PN communication component, the no of devices and the amount of user data	

PROFINET communication function

Function Name	Overview
PROFINET device status	Use the LEDs on the CPU panel to indicate the working status of PROFINET
Find PROFINET devices	Find PROFINET devices and assign names to PROFINET devices
PROFINET Programming Wizard	Configure, assign parameters and interconnect the functions of individual PN hardware components
PROFINET program instructions	Read and write data records using the RDREC and WRREC instructions. Read and write multiple input or output bytes of the device using the BLKMOV_BIR and BLKMOV_BIW instructions. PROFINET Network Diagnostics

PROFINET I/O address assignment

PROFINET device number	CPU input process image address	CPU output process image address
1PROFINET device process image register address	I128.0 to I255.7	Q128.0 to Q255.7
2PROFINET device process image register address	I256.0 to I383.7	Q256.0 to Q383.7
3PROFINET device process image register address	I384.0 to I511.7	Q384.0 to Q511.7
4PROFINET device process image register address	I512.0 to I639.7	Q512.0 to Q639.7
5PROFINET device process image register address	1640.0 to 1767.7	Q640.0 to Q767.7
6PROFINET device process image register address	1768.0 to 1895.7	Q768.0 to Q895.7
7PROFINET device process image register address	1896.0 to 11023.7	Q896.0 to Q1023.7
8PROFINET device process image register address	I1024.0 to I1151.7	Q1024.0 to Q1151.7

3-axis linear interpolation Enhanced Motion Control Features

- Motion axis group function supports 2D/3D linear interpolation motion
- Open-loop motion control based on PTO (Pulse Train Output)
- Override function supports modifying new position value or speed value during motion
- Configurable multi-segment motion path, fast execution of fixed path motion control
- Fully supported by ST20/ST30/ST40/ST60 CPU
- Motion axis groups can perform relative motion mode or absolute motion mode
- Simple motion guide function simplifies procedures and improves efficiency



Ordering data

SIMATIC S7-200 SMART Ordering data

EM AM03 Analog input/output module, 2 inputs / 1 output EM AM06 Analog input/output module, 4 inputs / 2 outputs EM AM06 Analog input/output module, 4 inputs / 2 outputs EM AR02 Thermal resistance input module, 2 channels EM AR04 Thermal resistance input module, 4 inputs EM AR04 Thermal resistance input module, 4 inputs EM AR04 Thermocouple input module, 4 channels EM DR01 PROFIBUS-DP slave module EM DP01 PROFIBUS-DP slave module EM DP01 PROFIBUS-DP slave module EM DR01 Communication signal board, RS485/RS232 EM CM01 Communication signal board, 2 x 24 V DC input / 2 x 24 V DC output EM AR01 Digital expansion signal board, 1 x 12-bit analog input EM AR01 Analog expansion signal board, 1 x 12-bit analog output EM AR01 Battery signal board, support CR1025 button battery (battery purchased separately) EM ES7 288-5BA01-0AA0 Acessories I/O Extension Cable S7-200 SMART I/O extension cable, 1 m in length EMS7 288-6EC01-0AA0 EMS7 288-0ED10-0AA0 EMS7 288-0ED10-0AA0 EMS7 288-0ED10-0AA0 EMS7 288-0ED10-0AA0 EMS7 288-0ED10-0AA0 EMS7 288-0ED10-0AA0			MLFB
CPU STOO Standard CPU module, transistor output, 24 V DC supply, 12 DI / 8 DO, Integrated PN port	CPU		
CPU SR30	CPU SR20	Standard CPU module, relay output, 220 V AC supply, 12 DI / 8 DO, integrated PN port	6ES7 288-1SR20-0AA0
CPU ST30 Standard CPU module, transistor output, 24 V DC supply, 18 DI / 12 DO, integrated PN port CPU ST40 Standard CPU module, relay output, 220 V AC supply, 24 DI / 16 DO, integrated PN port CPU ST40 Standard CPU module, relay output, 22 OV AC supply, 36 DI / 24 DO, integrated PN port CPU ST40 Standard CPU module, relay output, 22 OV AC supply, 36 DI / 24 DO, integrated PN port CPU ST40 Standard CPU module, relay output, 220 V AC supply, 36 DI / 24 DO, integrated PN port CPU CR20 Economical CPU module, relay output, 220 V AC supply, 12 DI / 8 DO CPU CR20 Economical CPU module, relay output, 220 V AC supply, 12 DI / 8 DO CPU CR20 Economical CPU module, relay output, 220 V AC supply, 18 DI / 12 DO CES7 288-1560-0AA0 CPU CR80 Economical CPU module, relay output, 220 V AC supply, 18 DI / 12 DO CES7 288-1560-0AA1 CPU CR80 Economical CPU module, relay output, 220 V AC supply, 36 DI / 24 DO CES7 288-1560-0AA1 CPU CR80 Economical CPU module, 8 x 24 V DC input CES7 288-2560-0AA1 CPU CR80 Economical CPU module, 8 x 24 V DC input CES7 288-2560-0AA1 CES7	CPU ST20	Standard CPU module, transistor output, 24 V DC supply, 12 DI / 8 DO, integrated PN port	6ES7 288-1ST20-0AA0
CPU SR40 Standard CPU module, relay output, 220 V AC supply, 24 D1 / 16 D0, integrated PN port 6E57 288-15R40-0AA0 CPU SR60 Standard CPU module, transistor output, 24 V DC supply, 36 D1 / 24 D0, integrated PN port 6E57 288-15T40-0AA0 6E57 288-15T40-0AA1 6E57 288-25T40-0AA1 6E57 288-25T40-0AA0 6E57 288-25T40-0	CPU SR30	Standard CPU module, relay output, 220 V AC supply, 18 DI / 12 DO, integrated PN port	6ES7 288-1SR30-0AA0
CPU ST40 Standard CPU module, transistor output, 24 V DC supply, 24 DI / 16 DO, integrated PN port CPU ST60 Standard CPU module, relay output, 220 V AC supply, 36 DI / 24 DO, integrated PN port CPU ST60 Standard CPU module, relay output, 220 V AC supply, 36 DI / 24 DO, integrated PN port CPU ST60 Standard CPU module, relay output, 220 V AC supply, 36 DI / 24 DO, integrated PN port CPU CR20s Economical CPU module, relay output, 220 V AC supply, 18 DI / 12 DO CEST 288-1CR50-0AA1 CPU CR30s Economical CPU module, relay output, 220 V AC supply, 18 DI / 12 DO CEST 288-1CR40-0AA1 CPU CR40s Economical CPU module, relay output, 220 V AC supply, 24 DI / 16 DO CEST 288-1CR40-0AA1 CPU CR60s Economical CPU module, relay output, 220 V AC supply, 36 DI / 24 DO CEST 288-1CR40-0AA1 CPU CR60s Economical CPU module, relay output, 220 V AC supply, 36 DI / 24 DO CEST 288-1CR40-0AA1 CPU CR60s Economical CPU module, relay output, 220 V AC supply, 36 DI / 24 DO CEST 288-2CR60-0AA0 CEST 288	CPU ST30	Standard CPU module, transistor output, 24 V DC supply, 18 DI / 12 DO, integrated PN port	6ES7 288-1ST30-0AA0
CPU SR60 Standard CPU module, relay output, 220 V AC supply, 36 DI J 24 DO, integrated PN port 6E57 288-1SR60-DAAD CPU ST60 Standard CPU module, transistor output, 24 V DC supply, 36 DI J 24 DO, integrated PN port 6E57 288-1ST60-DAAD CPU CR20s Economical CPU module, relay output, 220 V AC supply, 12 DI J 8 DO 6E57 288-1CR20-DAA1 CPU CR20s Economical CPU module, relay output, 220 V AC supply, 18 DI J 2 DO 6E57 288-1CR20-DAA1 CPU CR40s Economical CPU module, relay output, 220 V AC supply, 36 DI J 24 DO 6E57 288-1CR60-DAA1 CPU CR40s Economical CPU module, relay output, 220 V AC supply, 36 DI J 24 DO 6E57 288-2CR60-DAA1 END BOB Digital input module, 16 x 24 V DC input 6E57 288-2DR80-DAA0 EM DE16 Digital input module, 8 x 24 V DC input 6E57 288-2DR80-DAA0 EM D108 Digital output module, 8 x 24 V DC output 6E57 288-2DR80-DAA0 EM D108 Digital input module, 16 x 24 V DC output 6E57 288-2DR80-DAA0 EM D116 Digital input module, 16 x 24 V DC output 6E57 288-2DR80-DAA0 EM D1716 Digital input module, 16 x 24 V DC input / 8 x relay output 6E57 288-2DR80-DAA0 EM D182 Digital input module, 2 f x 24 V DC input / 8 x relay output 6E57 288-2DR80-DAA0<	CPU SR40	Standard CPU module, relay output, 220 V AC supply, 24 DI / 16 DO, integrated PN port	6ES7 288-1SR40-0AA0
CPU ST60	CPU ST40	Standard CPU module, transistor output, 24 V DC supply, 24 DI / 16 DO, integrated PN port	6ES7 288-1ST40-0AA0
CPU CR20s Economical CPU module, relay output, 220 V AC supply, 12 DI / 8 DO 6ES7 288-1CR30-0AA1 CPU CR30s Economical CPU module, relay output, 220 V AC supply, 18 DI / 12 DO 6ES7 288-1CR30-0AA1 CPU CR40s Economical CPU module, relay output, 220 V AC supply, 36 DI / 24 DO 6ES7 288-1CR30-0AA1 CPU CR60s Economical CPU module, relay output, 220 V AC supply, 36 DI / 24 DO 6ES7 288-2ER60-0AA1 Expanion Modules Expanion Modules EM DE08 Digital input module, 16 × 24 V DC input 6ES7 288-2DE16-0AA0 EM DE16 Digital output module, 16 × 24 V DC input 6ES7 288-2DE16-0AA0 EM DE08 Digital output module, 8 x relay output 6ES7 288-2DE16-0AA0 EM DT08 Digital output module, 8 x 24 V DC output 6ES7 288-2DT16-0AA0 EM QT16 Digital input module, 8 x 24 V DC output 6ES7 288-2DT16-0AA0 EM QT16 Digital input/output module, 16 x 24 V DC input / 18 x relay output 6ES7 288-2DT16-0AA0 EM DR16 Digital input/output module, 8 x 24 V DC input / 18 x relay output 6ES7 288-2DT16-0AA0 EM DT32 Digital input/output module, 16 x 24 V DC input / 18 x 24 V DC output 6ES7 288-2DT16-0AA0 EM DT32 Digital input/output module, 8 x 24 V DC inpu	CPU SR60	Standard CPU module, relay output, 220 V AC supply, 36 DI / 24 DO, integrated PN port	6ES7 288-1SR60-0AA0
CPU CR30s Economical CPU module, relay output, 220 V AC supply, 18 DI / 12 DO 6EST 288-1CR30-0AA1 CPU CR40s Economical CPU module, relay output, 220 V AC supply, 24 DI / 16 DO 6EST 288-1CR40-0AA1 CPU CR60s Economical CPU module, relay output, 220 V AC supply, 36 DI / 24 DO 6EST 288-1CR60-0AA1 Expanion Modules Expanion Modules EM DE08 Digital input module, 16 x 24 V DC input 6EST 288-2DE16-0AA0 EM DE08 Digital output module, 8 x relay output 6EST 288-2DT08-0AA0 EM DR08 Digital output module, 8 x relay output 6EST 288-2DT08-0AA0 EM DR08 Digital output module, 8 x 24 V DC output 6EST 288-2DT08-0AA0 EM DR08 Digital output module, 8 x 24 V DC output 6EST 288-2DT08-0AA0 EM DR16 Digital input/output module, 16 x 24 V DC input / 8 x relay output 6EST 288-2DT16-0AA0 EM DR16 Digital input/output module, 8 x 24 V DC input / 16 x relay output 6EST 288-2DT3-0AA0 EM DR32 Digital input/output module, 16 x 24 V DC input / 16 x relay output 6EST 288-2DT3-0AA0 EM AE04 Analog input module, 16 x 24 V DC input / 16 x 24 V DC output 6EST 288-3AE04-0AA0 EM AE04 Analog input module, 2 input s 6EST 288-3	CPU ST60		6ES7 288-1ST60-0AA0
CPU CR30s Economical CPU module, relay output, 220 V AC supply, 18 DI / 12 DO 6EST 288-1CR30-0AA1 CPU CR40s Economical CPU module, relay output, 220 V AC supply, 24 DI / 16 DO 6EST 288-1CR40-0AA1 CPU CR60s Economical CPU module, relay output, 220 V AC supply, 36 DI / 24 DO 6EST 288-1CR60-0AA1 Expanion Modules Expanion Modules EM DE08 Digital input module, 16 x 24 V DC input 6EST 288-2DE16-0AA0 EM DE08 Digital output module, 8 x relay output 6EST 288-2DT08-0AA0 EM DR08 Digital output module, 8 x relay output 6EST 288-2DT08-0AA0 EM DR08 Digital output module, 8 x 24 V DC output 6EST 288-2DT08-0AA0 EM DR08 Digital output module, 8 x 24 V DC output 6EST 288-2DT08-0AA0 EM DR16 Digital input/output module, 16 x 24 V DC input / 8 x relay output 6EST 288-2DT16-0AA0 EM DR16 Digital input/output module, 8 x 24 V DC input / 16 x relay output 6EST 288-2DT3-0AA0 EM DR32 Digital input/output module, 16 x 24 V DC input / 16 x relay output 6EST 288-2DT3-0AA0 EM AE04 Analog input module, 16 x 24 V DC input / 16 x 24 V DC output 6EST 288-3AE04-0AA0 EM AE04 Analog input module, 2 input s 6EST 288-3	CPU CR20s	Economical CPU module, relay output, 220 V AC supply, 12 DI / 8 DO	6ES7 288-1CR20-0AA1
CPU CR40s Economical CPU module, relay output, 220 V AC supply, 24 DI /16 DO 6E57 288-1CR40-0AA1 CPU CR60s Economical CPU module, relay output, 220 V AC supply, 36 DI / 24 DO 6E57 288-1CR60-0AA1 Expanion Modules Expanion Modules EM DE08 Digital input module, 8 x 24 V DC input 6E57 288-2DE08-0AA0 EM DE08 Digital output module, 8 x 24 V DC input 6E57 288-2DE08-0AA0 EM DE08 Digital output module, 8 x 24 V DC output 6E57 288-2DT08-0AA0 EM DT08 Digital output module, 16 x 24 V DC output 6E57 288-2DT16-0AA0 EM QT16 Digital output module, 16 x 24 V DC output 6E57 288-2DT16-0AA0 EM QT16 Digital input/output module, 8 x 24 V DC input / 18 x relay output 6E57 288-2DT16-0AA0 EM DR16 Digital input/output module, 16 x 24 V DC input / 18 x 24 V DC output 6E57 288-2DT16-0AA0 EM DT16 Digital input/output module, 16 x 24 V DC input / 18 x 24 V DC output 6E57 288-2DT16-0AA0 EM DT132 Digital input/output module, 8 inputs 6E57 288-2DT3-2AA0 EM AC04 Analog input module, 8 inputs 6E57 288-3AE0-0AA0 EM AC08 Analog output module, 8 inputs 6E57 288-3AE0-0AA0 EM AC09 <td></td> <td></td> <td></td>			
Expansion Modules Expansion Modules EM DEOB Digital input module, 16 x 24 V DC input EM DEOB Digital input module, 16 x 24 V DC input EM DEOB Digital input module, 16 x 24 V DC input EM DEOB Digital output module, 8 x relay output EM DEOB Digital output module, 8 x relay output EM DEOB Digital output module, 8 x relay output EM DEOB Digital output module, 8 x relay output EM DEOB Digital output module, 8 x relay output EM DEOB Digital output module, 16 x 24 V DC output EM QR16 Digital output module, 16 x 24 V DC output EM QR16 Digital output module, 16 x relay output EM DEOB Digital input/output module, 8 x 24 V DC input / 8 x relay output EM DR32 Digital input/output module, 8 x 24 V DC input / 16 x relay output EM DR32 Digital input/output module, 16 x 24 V DC input / 18 x relay output EM DR32 Digital input/output module, 8 x 24 V DC input / 18 x 24 V DC output EM DR32 Digital input/output module, 8 x 24 V DC input / 18 x 24 V DC output EM SEO		1 3 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1	
Expansion Modules EM DE08 Digital input module, 8 x 24 V DC input 6ES7 288-2DE08-0AA0 EM DE16 Digital input module, 16 x 24 V DC input 6ES7 288-2DE08-0AA0 EM DE16 Digital output module, 8 x relay output 6ES7 288-2DE08-0AA0 EM DE08 Digital output module, 8 x 24 V DC output 6ES7 288-2DT08-0AA0 EM QT16 Digital output module, 8 x 24 V DC output 6ES7 288-2DT08-0AA0 EM QT16 Digital output module, 16 x 24 V DC output 6ES7 288-2DT08-0AA0 EM QT16 Digital output module, 16 x 24 V DC output 6ES7 288-2DT16-0AA0 EM QT16 Digital input/output module, 8 x 24 V DC input / 8 x relay output 6ES7 288-2DR16-0AA0 EM DR16 Digital input/output module, 8 x 24 V DC input / 16 x relay output 6ES7 288-2DR16-0AA0 EM DR16 Digital input/output module, 8 x 24 V DC input / 16 x relay output 6ES7 288-2DR32-0AA0 EM DT16 Digital input/output module, 8 x 24 V DC input / 16 x relay output 6ES7 288-2DR32-0AA0 EM DT132 Digital input/output module, 16 x 24 V DC input / 16 x 24 V DC output 6ES7 288-2DT16-0AA0 EM AE04 Analog input module, 4 inputs 6ES7 288-3AE04-0AA0 EM AC08 Analog input module, 8 inputs 6ES7 288-3AE08-0AA0 EM AQ02 Analog output module, 2 outputs 6ES7 288-3AQ02-0AA0 EM AM03 Analog input/output module, 2 inputs / 1 output 6ES7 288-3AQ02-0AA0 EM AM03 Analog input/output module, 4 inputs / 2 outputs 6ES7 288-3AM02-0AA0 EM AR04 Thermal resistance input module, 2 channels 6ES7 288-3AR02-0AA0 EM AR04 Thermal resistance input module, 4 inputs / 2 outputs 6ES7 288-3AM04-0AA0 EM AR04 Thermal resistance input module, 4 inputs 6ES7 288-3AP02-0AA0 EM AR04 Thermal resistance input module, 4 inputs 6ES7 288-3AR02-0AA0 EM AR04 Thermal resistance input module, 4 inputs 6ES7 288-3AR02-0AA0 EM AR04 Thermal resistance input module, 4 inputs 6ES7 288-3AR04-0AA0 EM AR04 Thermal resistance input module, 4 inputs 6ES7 288-3AR04-0AA0 EM AR01 Communication signal board, 1 x 12-bit analog output 6ES7 288-5CM01-0AA0 SB BD104 Digital expansion signal board, 1 x 12-bit analog input 6ES7 288-5CM01-0AA0 AR84D1 Anal			
EM DE08 Digital input module, 8 x 24 V DC input 6ES7 288-2DE16-0AAO EM DE16 Digital input module, 16 x 24 V DC input 6ES7 288-2DE16-0AAO EM DE08 Digital output module, 8 x relay output 6ES7 288-2DE16-0AAO EM DE08 Digital output module, 8 x 24 V DC output 6ES7 288-2DT08-0AAO EM DE08 Digital output module, 8 x 24 V DC output 6ES7 288-2DT16-0AAO EM QT16 Digital output module, 16 x 24 V DC output 6ES7 288-2DT16-0AAO EM QT16 Digital output module, 16 x 24 V DC output 6ES7 288-2DT16-0AAO EM QT16 Digital input/output module, 16 x 24 V DC input / 8 x relay output 6ES7 288-2DT16-0AAO EM DE16 Digital input/output module, 8 x 24 V DC input / 16 x relay output 6ES7 288-2DR16-0AAO EM DT13 Digital input/output module, 8 x 24 V DC input / 16 x relay output 6ES7 288-2DT16-0AAO EM DT12 Digital input/output module, 8 x 24 V DC input / 16 x 24 V DC output 6ES7 288-2DT16-0AAO EM DT12 Digital input/output module, 16 x 24 V DC input / 16 x 24 V DC output 6ES7 288-2DT16-0AAO EM AD132 Digital input/output module, 16 x 24 V DC input / 16 x 24 V DC output 6ES7 288-3AE04-0AAO EM AE08 Analog input module, 8 inputs 6ES7 288-3AE04-0AAO EM AE08 Analog input module, 2 outputs 6ES7 288-3AE04-0AAO EM AE08 Analog output module, 2 outputs 6ES7 288-3AE04-0AAO EM AMO3 Analog output module, 2 outputs 6ES7 288-3AE04-0AAO EM AMO3 Analog input/output module, 2 inputs / 1 output 6ES7 288-3AE04-0AAO EM AMO3 Analog input/output module, 2 inputs / 2 outputs 6ES7 288-3AE04-0AAO EM ARO2 Thermal resistance input module, 2 channels 6ES7 288-3AE04-0AAO EM ARO4 Thermal resistance input module, 4 channels 6ES7 288-3AE04-0AAO EM ARO4 Thermal resistance input module, 4 channels 6ES7 288-3AE04-0AAO EM AEO1 PROFIBUS-DP slave module 6ES7 288-3AE04-0AAO EM ARO4 Thermal resistance input module, 4 channels 6ES7 288-3AE04-0AAO EM AEO1 PROFIBUS-DP slave module 6ES7		containing a o modulo, roley output, 220 the supply, 300 St. 2 t So	
EM DE16 Digital input module, 16 x 24 V DC input 6E57 288-2DE16-0AA0 Digital output module, 8 x relay output 6E57 288-2DR08-0AA0 Digital output module, 8 x 24 V DC output 6E57 288-2DR08-0AA0 DEM DT08 Digital output module, 16 x 24 V DC output 6E57 288-2QT16-0AA0 DEM QT16 Digital output module, 16 x 24 V DC output 6E57 288-2QT16-0AA0 DEM QT16 Digital input/output module, 16 x 24 V DC input / 8 x relay output 6E57 288-2QT16-0AA0 DEM DT16 Digital input/output module, 8 x 24 V DC input / 8 x relay output 6E57 288-2QT16-0AA0 DEM DT16 Digital input/output module, 8 x 24 V DC input / 16 x relay output 6E57 288-2DT32-0AA0 DEM DT16 Digital input/output module, 8 x 24 V DC input / 16 x relay output 6E57 288-2DT32-0AA0 DEM DT16 Digital input/output module, 8 x 24 V DC input / 16 x 24 V DC output 6E57 288-2DT32-0AA0 DEM DT13 Digital input/output module, 8 x 24 V DC input / 16 x 24 V DC output 6E57 288-2DT32-0AA0 DEM ACO Analog input module, 4 inputs 6E57 288-3AE08-0AA0 DEM ACO Analog input module, 8 inputs 6E57 288-3AE08-0AA0 DEM ACO Analog output module, 8 inputs 6E57 288-3AE08-0AA0 DEM ACO Analog output module, 2 outputs 6E57 288-3AQ02-0AA0 DEM ACO Analog output module, 2 outputs 6E57 288-3AQ02-0AA0 DEM ACO Analog output module, 2 outputs 6E57 288-3AQ04-0AA0 DEM ACO Analog input/output module, 2 inputs / 1 output 6E57 288-3AQ04-0AA0 DEM ACO Analog input/output module, 4 inputs / 2 outputs 6E57 288-3AM03-0AA0 DEM ACO Analog input/output module, 4 inputs / 2 outputs 6E57 288-3AM03-0AA0 DEM ACO Analog input/output module, 4 inputs / 2 outputs 6E57 288-3AM03-0AA0 DEM ACO Analog input/output module, 4 inputs / 2 outputs 6E57 288-3AM04-0AA0 DEM ACO Analog input output module, 4 inputs / 2 outputs 6E57 288-3AM04-0AA0 DEM ACO ANA DEM		Digital input module, 8 x 24 V DC input	6ES7 288-2DE08-0AA0
EM DR08 Digital output module, 8 x relay output EM DT08 Digital output module, 8 x 24 V DC output EM DT08 Digital output module, 16 x 24 V DC output EM CR16 Digital output module, 16 x 24 V DC output EM CR16 Digital output module, 16 x 24 V DC output EM DR16 Digital inputoutput module, 16 x 24 V DC input / 8 x relay output EM DR16 Digital inputoutput module, 8 x 24 V DC input / 8 x relay output EM DR16 Digital inputoutput module, 16 x 24 V DC input / 16 x relay output EM DR32 Digital inputoutput module, 16 x 24 V DC input / 16 x relay output EM DR32 Digital inputoutput module, 8 x 24 V DC input / 8 x 24 V DC output EM DT16 Digital inputoutput module, 8 x 24 V DC input / 8 x 24 V DC output EM ST2 SEB-ZDR16-0AA0 EM DT32 Digital inputoutput module, 8 x 24 V DC input / 16 x 24 V DC output EM AE08 Analog input module, 4 inputs EM AE08 Analog input module, 4 inputs EM AE08 Analog output module, 2 outputs EM AE08 Analog output module, 2 outputs EM AG00 Analog output module, 4 outputs EM AG01 Analog input/output module, 2 inputs / 1 output EM AR03 Analog input/output module, 2 inputs / 1 output EM AR04 Analog input/output module, 2 inputs / 1 outputs EM AR05 Analog input/output module, 4 inputs / 2 outputs EM AR06 Analog input/output module, 4 inputs / 2 outputs EM AR07 Thermal resistance input module, 2 channels EM AR08 Thermal resistance input module, 4 inputs EM AR09 Thermal resistance input module, 4 inputs EM AR04 Thermal resistance input module, 4 inputs EM AR04 Thermal resistance input module, 4 inputs EM AR04 Thermal resistance input module, 4 inputs EM AR08 Thermal resistance input module, 4 inputs EM AR09 Thermal resistance input			
EM DTO8 Digital output module, 8 x 24 V DC output 6ES7 288-2DT08-0AAO EM QT16 Digital output module, 16 x 24 V DC output 6ES7 288-2QT16-0AAO EM QR16 Digital output module, 16 x 24 V DC input / 8 x relay output 6ES7 288-2QR16-0AAO EM DR16 Digital input/output module, 8 x 24 V DC input / 8 x relay output 6ES7 288-2DR16-0AAO EM DR32 Digital input/output module, 8 x 24 V DC input / 16 x relay output 6ES7 288-2DR18-0AAO EM DR32 Digital input/output module, 8 x 24 V DC input / 16 x relay output 6ES7 288-2DR32-0AAO EM DT32 Digital input/output module, 8 x 24 V DC input / 16 x 24 V DC output 6ES7 288-2DT132-0AAO EM DT32 Digital input/output module, 16 x 24 V DC input / 16 x 24 V DC output 6ES7 288-2DT132-0AAO EM AEO4 Analog input module, 4 inputs 6ES7 288-3AE04-0AAO EM AEO8 Analog input module, 8 inputs 6ES7 288-3AE04-0AAO EM AOO2 Analog output module, 2 outputs 6ES7 288-3AQO2-0AAO EM AQO2 Analog output module, 2 inputs / 1 output 6ES7 288-3AQO2-0AAO EM AQO4 Analog input/output module, 2 inputs / 1 output 6ES7 288-3AQO4-0AAO EM ARO04 Analog input/output module, 4 inputs / 2 outputs 6ES7 288-3AMO3-0AAO EM ARO2 Thermal resistance input module, 4 inputs / 2 outputs 6ES7 288-3AMO4-0AAO EM ARO2 Thermal resistance input module, 4 inputs 6ES7 288-3AMO4-0AAO EM ARO4 Thermal resistance input module, 4 inputs 6ES7 288-3AMO4-0AAO EM ARO4 Thermal resistance input module, 4 inputs 6ES7 288-3AMO4-0AAO EM DPO1 PROFIBUS-DP slave module 6ES7 288-3AMO4-0AAO EM DPO1 PROFIBUS-DP slave module 6ES7 288-3AMO4-0AAO EM ARO4 Digital expansion signal board, 85485/RS232 6ES7 288-5CMO1-0AAO ES AGO1 Analog expansion signal board, 1 x 12-bit analog input 6ES7 288-5DP01-0AAO ES AGO1 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5DP01-0AAO ES AGO1 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5AGO1-0AAO ES AGO1 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5AGO1-0AAO ES AGO1 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5AGO1-0AAO ES AGO1 Analog expansion signal board, 1 x 12-			
EM QT16 Digital output module, 16 x 24 V DC output EM QR16 Digital output module, 16 x relay output EM QR16 Digital input/output module, 8 x 24 V DC input / 8 x relay output EM DR16 Digital input/output module, 8 x 24 V DC input / 16 x relay output EM DR32 Digital input/output module, 16x24 V DC input / 16 x relay output EM DR32 Digital input/output module, 16x24 V DC input / 16 x relay output EEST 288-2DR16-OAAO EM DR32 Digital input/output module, 16x24 V DC input / 16 x 24 V DC output EEST 288-2DR16-OAAO EM DT32 Digital input/output module, 16 x 24 V DC input / 16 x 24 V DC output EEST 288-2DT13-OAAO EM AEO4 Analog input module, 4 inputs EM AEO8 Analog input module, 8 inputs EEST 288-3AEO8-OAAO EM AQO2 Analog output module, 2 outputs EM AQO2 Analog output module, 2 inputs / 1 output EM AMO3 Analog input/output module, 2 inputs / 1 output EM AMO3 Analog input/output module, 2 inputs / 1 output EM AMO6 Analog input/output module, 2 inputs / 2 outputs EEST 288-3AMO3-OAAO EM ARO2 Thermal resistance input module, 2 thinputs / 2 outputs EEST 288-3AMO6-OAAO EM ARO4 Thermal resistance input module, 4 inputs EM ARO4 Thermal resistance input module, 4 inputs EEST 288-3ARO2-OAAO EM ARO4 Thermal resistance input module, 4 channels EM ATO4 Thermocouple input module, 4 channels EM DPO1 PROFIBUS-DP slave module EM DPO1 PROFIBUS-DP slave module EM DPO1 PROFIBUS-DP slave module EM EST 288-5ARO1-OAAO SB CMO1 Communication signal board, 2 x 24 V DC input / 2 x 24 V DC output EEST 288-5ARO1-OAAO SB ARO1 Analog expansion signal board, 1 x 12-bit analog input EEST 288-5ARO1-OAAO SB ARO1 Analog expansion signal board, 1 x 12-bit analog output EEST 288-5ARO1-OAAO EEST 288-5ARO1-OAAO SB ARO1 Analog expansion signal board, 1 x 12-bit analog output EEST 288-5ARO1-OAAO			
EM QR16 Digital output module, 16× relay output EM QR16 Digital input/output module, 8 × 24 V DC input / 8 × relay output EM DR16 Digital input/output module, 8 × 24 V DC input / 8 × relay output EM DR32 Digital input/output module, 16×24 V DC input / 16 × relay output EM DR32 Digital input/output module, 8 × 24 V DC input / 16 × 24 V DC output EM DR32 Digital input/output module, 16×24 V DC input / 16 × 24 V DC output EM DR32 Digital input/output module, 16×24 V DC input / 16×24 V DC output EM DR32 Digital input/output module, 16×24 V DC input / 16×24 V DC output EM AE04 Analog input module, 8 inputs EM AE08 Analog input module, 8 inputs EM AQ02 Analog output module, 8 inputs EM AQ02 Analog output module, 2 outputs EM AQ04 Analog output module, 2 inputs / 1 output EM AM03 Analog input/output module, 2 inputs / 1 output EM AR04 Analog input/output module, 4 inputs / 2 outputs EM AR06 Analog input/output module, 4 inputs / 2 outputs EM AR07 Thermal resistance input module, 4 inputs EM AR09 Thermal resistance input module, 4 inputs EM AR04 Thermal resistance input module, 4 inputs EM AR04 Thermocouple input module, 4 channels EM DR01 PROFIBUS-DP slave module EM DR01 PROFIBUS-DP slave module Signal board SB SE CM01 Communication signal board, RS485/RS232 EM SET 288-5AP01-OAA0 SB AR01 Analog expansion signal board, 1 × 12-bit analog output EM SE7 288-5AP01-OAA0 SB AR01 Analog expansion signal board, 1 × 12-bit analog output EM SE7 288-5AP01-OAA0 SB AR01 Analog expansion signal board, 1 × 12-bit analog output EM SE7 288-5AP01-OAA0 SB AR01 Analog expansion signal board, 1 × 12-bit analog output EM SE7 288-5AP01-OAA0 SB AR01 Analog expansion signal board, 1 × 12-bit analog output EM SE7 288-5AP01-OAA0 SB AR01 Analog expansion signal board, 1 × 12-bit analog output EM SE7 288-5AP01-OAA0 SB AR01 Analog expansion signal board, 1 × 12-bit analog output EM SE7 288-5AP01-OAA0 SB AR01 Analog expansion signal board, 1 × 12-bit analog output EM SE7 288-5AP01-OAA0 SE7 288-5AP01-OAA0 SE7			
EM DR16 Digital input/output module, 8 x 24 V DC input / 8 x relay output 6ES7 288-2DR16-0AA0 EM DR32 Digital input/output module, 16×24 V DC input / 16 x relay output 6ES7 288-2DR32-0AA0 EM DT16 Digital input/output module, 8 x 24 V DC input / 18 x 24 V DC output 6ES7 288-2DT16-0AA0 EM DT32 Digital input/output module, 16 x 24 V DC input / 16 x 24 V DC output 6ES7 288-2DT32-0AA0 EM AE04 Analog input module, 4 inputs 6ES7 288-3AE04-0AA0 EM AE08 Analog input module, 8 inputs 6ES7 288-3AE08-0AA0 EM AQ02 Analog output module, 2 outputs 6ES7 288-3AE08-0AA0 EM AQ02 Analog output module, 4 outputs 6ES7 288-3AQ02-0AA0 EM AMO3 Analog input/output module, 2 inputs / 1 output 6ES7 288-3AQ04-0AA0 EM AMO4 Analog input/output module, 2 inputs / 2 outputs 6ES7 288-3AM03-0AA0 EM AMO6 Analog input/output module, 4 inputs / 2 outputs 6ES7 288-3AM06-0AA0 EM AR02 Thermal resistance input module, 2 channels 6ES7 288-3AR02-0AA0 EM AR04 Thermal resistance input module, 4 inputs 6ES7 288-3AR04-0AA0 EM AR04 Thermal resistance input module, 4 inputs 6ES7 288-3AR04-0AA0 EM AR04 Thermal resistance input module, 4 inputs 6ES7 288-3AR04-0AA0 EM AR04 Thermal resistance input module, 4 inputs 6ES7 288-3AR04-0AA0 EM AR04 Thermal gesistance input module, 4 inputs 6ES7 288-3AR04-0AA0 EM AR04 Thermal gesistance input module, 4 inputs 6ES7 288-3AR04-0AA0 EM AR04 Thermal gesistance input module, 4 inputs 6ES7 288-3AR04-0AA0 EM AR04 Thermal gesistance input module, 4 inputs 6ES7 288-3AR04-0AA0 EM AR04 Thermal gesistance input module, 5 inputs / 2 x 24 V DC output 6ES7 288-5CM01-0AA0 EM Signal board SB EM CM01 Communication signal board, 85485/RS232 6ES7 288-5CM01-0AA0 SB DT04 Digital expansion signal board, 1 x 12-bit analog output 6ES7 288-5CM01-0AA0 SB AR01 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5CM01-0AA0 SB AR01 Battery signal board, support CR1025 button battery (battery purchased separately) 6ES7 288-5AQ01-0AA0 ACCSSORIES WO STAND STANDAR FOWER SEADOL-0AA0 ACCSSORIES WO STANDAR FOWER SEAD			·
EM DR32 Digital input/output module, 16×24 V DC input / 16 x relay output 6ES7 288-2DR32-0AA0 EM DT16 Digital input/output module, 8 x 24 V DC input / 8 x 24 V DC output 6ES7 288-2DT16-0AA0 EM DT32 Digital input/output module, 16 x 24 V DC input / 16 x 24 V DC output 6ES7 288-2DT32-0AA0 EM AE04 Analog input module, 8 inputs 6ES7 288-3AE04-0AA0 EM AE08 Analog input module, 8 inputs 6ES7 288-3AE08-0AA0 EM AQ02 Analog output module, 2 outputs 6ES7 288-3AQ02-0AA0 EM AQ04 Analog output module, 4 outputs 6ES7 288-3AQ04-0AA0 EM AM03 Analog input/output module, 2 inputs / 1 output 6ES7 288-3AQ04-0AA0 EM AM06 Analog input/output module, 2 inputs / 2 outputs 6ES7 288-3AM03-0AA0 EM AR02 Thermal resistance input module, 2 channels 6ES7 288-3AR04-0AA0 EM AR04 Thermal resistance input module, 4 inputs 6ES7 288-3AR04-0AA0 EM AR04 Thermal resistance input module, 4 inputs 6ES7 288-3AR04-0AA0 EM AT04 Thermacouple input module, 4 channels 6ES7 288-3AR04-0AA0 EM AT04 Thermacouple input module, 4 channels 6ES7 288-3AR04-0AA0 EM DP01 PROFIBUS-DP slave module 6ES7 288-3CM01-0AA0 EM DP01 PROFIBUS-DP slave module 6ES7 288-5CM01-0AA0 EM AE01 Analog expansion signal board, 8x485/RS232 6ES7 288-5CM01-0AA0 EM AE01 Analog expansion signal board, 1 x 12-bit analog input 6ES7 288-5CM01-0AA0 EM AE01 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5E0T04-0AA0 EM AE01 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5E0T04-0AA0 EM AE01 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5E0T04-0AA0 EM AE01 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5E0T04-0AA0 EM SB AE01 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5E0T04-0AA0 EM SB AE01 Battery signal board, 1 x 12-bit analog output 6ES7 288-5E0T04-0AA0 EM SB AE01 ST 288-			· ·
EM DT16 Digital input/output module, 8 x 24 V DC input / 8 x 24 V DC output 6ES7 288-2DT16-0AA0 EM DT32 Digital input/output module, 16 x 24 V DC input / 16 x 24 V DC output 6ES7 288-2DT32-0AA0 EM AE04 Analog input module, 8 inputs 6ES7 288-3AE04-0AA0 EM AE08 Analog input module, 8 inputs 6ES7 288-3AE08-0AA0 EM AQ02 Analog output module, 2 outputs 6ES7 288-3AQ02-0AA0 EM AQ04 Analog output module, 4 outputs 6ES7 288-3AQ04-0AA0 EM AM03 Analog input/output module, 2 inputs / 1 output 6ES7 288-3AM03-0AA0 EM AM06 Analog input/output module, 4 inputs / 2 outputs 6ES7 288-3AM03-0AA0 EM AR02 Thermal resistance input module, 2 channels 6ES7 288-3AR02-0AA0 EM AR04 Thermal resistance input module, 4 inputs 6ES7 288-3AR04-0AA0 EM AR04 Thermal resistance input module, 4 channels 6ES7 288-3AR04-0AA0 EM AP04 PROFIBUS-DP slave module 6ES7 288-3AT04-0AA0 EM DP01 PROFIBUS-DP slave module 6ES7 288-3AT04-0AA0 EM DP01 PROFIBUS-DP slave module 6ES7 288-7DP01-0AA0 Signal board SB SB CM01 Communication signal board, 2 x 24 V DC input / 2 x 24 V DC output 6ES7 288-5DT04-0AA0 SB AC01 Analog expansion signal board, 1 x 12-bit analog input 6ES7 288-5DT04-0AA0 SB AQ01 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5AC01-0AA0 AC0 SB BA01 Battery signal board, support CR1025 button battery (battery purchased separately) 6ES7 288-5BA01-0AA0 AC0 SP 288-5AC01-0AA0 SP 288-5A			
EM DT32 Digital input/output module, 16 x 24 V DC input / 16 x 24 V DC output EM AE04 Analog input module, 4 inputs EM AE08 Analog input module, 8 inputs EM AE08 Analog output module, 8 inputs EM AQ02 Analog output module, 2 outputs EM AQ04 Analog output module, 2 outputs EM AQ04 Analog output module, 4 outputs EM AM03 Analog input/output module, 2 inputs / 1 output EM AM03 Analog input/output module, 2 inputs / 1 output EM AM06 Analog input/output module, 2 inputs / 1 output EM AR02 Thermal resistance input module, 2 channels EM AR04 Thermal resistance input module, 4 inputs EM AT04 Thermacouple input module, 4 inputs EM AT04 Thermacouple input module, 4 channels EM DP01 PROFIBUS-DP slave module EM DP01 PROFIBUS-DP slave module EM BC1 Communication signal board, 88485/RS232 EM CM01 Communication signal board, 2 x 24 V DC input / 2 x 24 V DC output EM AE01 Analog expansion signal board, 1 x 12-bit analog input EM AE01 Analog expansion signal board, 1 x 12-bit analog output EM AE01 Analog expansion signal board, 1 x 12-bit analog output EM AE01 Analog expansion signal board, 1 x 12-bit analog output EM ES7 288-5AE01-OAA0 EM AE01 Analog expansion signal board, 1 x 12-bit analog output EM ES7 288-5BA01-OAA0 EM AE01 Analog expansion signal board, 1 x 12-bit analog output EM ES7 288-5BA01-OAA0 EM ACO1 Analog expansion signal board, 1 x 12-bit analog output EM ES7 288-5BA01-OAA0 EM AE01 Analog expansion signal board, 1 x 12-bit analog output EM ES7 288-5BA01-OAA0 EM ES7 288-6E01-OAA0 EM ES7 288-OED1-OAA0			
EM AE04 Analog input module, 4 inputs 6ES7 288-3AE04-0AA0 EM AE08 Analog input module, 8 inputs 6ES7 288-3AE08-0AA0 EM AQ02 Analog output module, 2 outputs 6ES7 288-3AQ02-0AA0 EM AQ04 Analog output module, 4 outputs 6ES7 288-3AQ04-0AA0 EM AQ04 Analog input/output module, 2 inputs / 1 output 6ES7 288-3AQ04-0AA0 EM AM03 Analog input/output module, 4 inputs / 2 outputs 6ES7 288-3AM03-0AA0 EM AM06 Analog input/output module, 4 inputs / 2 outputs 6ES7 288-3AM06-0AA0 EM AR02 Thermal resistance input module, 2 channels 6ES7 288-3AR02-0AA0 EM AR04 Thermal resistance input module, 4 inputs 6ES7 288-3AR04-0AA0 EM AT04 Thermocouple input module, 4 channels 6ES7 288-3AR04-0AA0 EM DP01 PROFIBUS-DP slave module 6ES7 288-3AT04-0AA0 EM DP01 PROFIBUS-DP slave module 6ES7 288-7DP01-0AA0 Signal board SB SB CM01 Communication signal board, 2 x 24 V DC input / 2 x 24 V DC output 6ES7 288-5DT04-0AA0 SB AE01 Analog expansion signal board, 1 x 12-bit analog input 6ES7 288-5DT04-0AA0 SB AQ01 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5AQ01-0AA0 SB BAO1 Battery signal board, support CR1025 button battery (battery purchased separately) 6ES7 288-5BA01-0AA0 Accessories WO Extension Cable 57-200 SMART I/O extension cable, 1 m in length 6ES7 288-6C01-0AA0 PM207 S7-200 SMART power supply, 24 V DC/3 A 6ES7 288-0C01-0AA0 PM207 S7-200 SMART power supply, 24 V DC/5 A 6ES7 288-0C01-0AA0			
EM AEO8 Analog input module, 8 inputs 6ES7 288-3AEO8-0AAO EM AQO2 Analog output module, 2 outputs 6ES7 288-3AQO2-0AAO EM AQO4 Analog output module, 4 outputs 6ES7 288-3AQO4-0AAO EM AQO4 Analog input/output module, 2 inputs / 1 output 6ES7 288-3AQO4-0AAO EM AMO3 Analog input/output module, 4 inputs / 2 outputs 6ES7 288-3AMO3-0AAO EM AMO6 Analog input/output module, 4 inputs / 2 outputs 6ES7 288-3AMO6-0AAO EM ARO2 Thermal resistance input module, 2 channels 6ES7 288-3ARO2-0AAO EM ARO4 Thermal resistance input module, 4 inputs 6ES7 288-3ARO4-0AAO EM ATO4 Thermocouple input module, 4 channels 6ES7 288-3ARO4-0AAO EM DPO1 PROFIBUS-DP slave module 6ES7 288-3ARO4-0AAO EM DPO1 PROFIBUS-DP slave module 6ES7 288-7DP01-0AAO EM DPO1 Digital expansion signal board, 2 x 24 V DC input / 2 x 24 V DC output 6ES7 288-5DT04-0AAO EM AEO1 Digital expansion signal board, 1 x 12-bit analog input 6ES7 288-5AEO1-0AAO EM AQO1 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5AEO1-0AAO EM BAU1 Battery signal board, 1 x 12-bit analog output 6ES7 288-5AEO1-0AAO EM ACOSSOFIES WO Extension Cable S7-200 SMART I/O extension cable, 1 m in length 6ES7 288-6ECO1-0AAO EM PM207 S7-200 SMART power supply, 24 V DC/3 A 6ES7 288-0CD10-0AAO EM PM207 S7-200 SMART power supply, 24 V DC/5 A 6ES7 288-0CD10-0AAO EM PM207 S7-200 SMART power supply, 24 V DC/5 A 6ES7 288-0CD10-0AAO EM PM207 S7-200 SMART power supply, 24 V DC/5 A			6ES7 288-2DT32-0AA0
EM AQ02 Analog output module, 2 outputs 6ES7 288-3AQ02-0AA0 EM AQ04 Analog output module, 4 outputs 6ES7 288-3AQ04-0AA0 EM AQ03 Analog input/output module, 2 inputs / 1 output 6ES7 288-3AM03-0AA0 EM AM06 Analog input/output module, 4 inputs / 2 outputs 6ES7 288-3AM06-0AA0 EM AM06 Thermal resistance input module, 2 channels 6ES7 288-3AR02-0AA0 EM AR02 Thermal resistance input module, 4 inputs 6ES7 288-3AR04-0AA0 EM AR04 Thermocouple input module, 4 channels 6ES7 288-3AR04-0AA0 EM AP09 PROFIBUS-DP slave module EM DP01 PROFIBUS-DP slave module Signal board SB SB CM01 Communication signal board, RS485/RS232 6ES7 288-5CM01-0AA0 SB DP04 Digital expansion signal board, 2 x 24 V DC input / 2 x 24 V DC output 6ES7 288-5DT04-0AA0 SB AE01 Analog expansion signal board, 1 x 12-bit analog input 6ES7 288-5AE01-0AA0 SB AQ01 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5AE01-0AA0 SB BA01 Battery signal board, 1 x 12-bit analog output 6ES7 288-5AE01-0AA0 Acessories I/O Extension Cable S7-200 SMART I/O extension cable, 1 m in length 6ES7 288-6EC01-0AA0 PM207 S7-200 SMART power supply, 24 V DC/3 A 6ES7 288-0CD10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/5 A PM207 S7-200 SMART power supply, 24 V DC/5 A PM207 S7-200 SMART power supply, 24 V DC/10 A 6ES7 288-0KD10-0AA0	EM AE04		
EM AQ04 Analog output module, 4 outputs EM AQ04 Analog input/output module, 2 inputs / 1 output EM AM03 Analog input/output module, 2 inputs / 1 output EM AM06 Analog input/output module, 4 inputs / 2 outputs EM AM06 Analog input/output module, 4 inputs / 2 outputs EM AR02 Thermal resistance input module, 2 channels EM AR04 Thermal resistance input module, 4 inputs EM AR04 Thermocouple input module, 4 channels EM AT04 Thermocouple input module, 4 channels EM DP01 PROFIBUS-DP slave module EM DP01 PROFIBUS-DP slave module Signal board SB SB CM01 Communication signal board, RS485/RS232 ESS CM01 Output GES7 288-5CM01-0AA0 EM AE01 Analog expansion signal board, 2 x 24 V DC input / 2 x 24 V DC output ESS 7 288-5CM01-0AA0 EM AE01 Analog expansion signal board, 1 x 12-bit analog input ESS 7 288-5AE01-0AA0 EM BA01 Analog expansion signal board, 1 x 12-bit analog output ESS 7 288-5AQ01-0AA0 EM BA01 Battery signal board, support CR1025 button battery (battery purchased separately) ACCESSORIES I/O Extension Cable S7-200 SMART I/O extension cable, 1 m in length ESS 7 288-6EC01-0AA0 PM207 S7-200 SMART power supply, 24 V DC/5 A ESS 7 288-0KD10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/5 A ESS 7 288-0KD10-0AA0 ESS 7 288-0KD10-0AA0	EM AE08	Analog input module, 8 inputs	6ES7 288-3AE08-0AA0
EM AM03 Analog input/output module, 2 inputs / 1 output EM AM06 Analog input/output module, 4 inputs / 2 outputs EM AM06 Analog input/output module, 4 inputs / 2 outputs EM AR02 Thermal resistance input module, 2 channels EM AR04 Thermal resistance input module, 4 inputs EM AR04 Thermal resistance input module, 4 inputs EM AR04 Thermocouple input module, 4 channels EM DR01 PROFIBUS-DP slave module EM DP01 PROFIBUS-DP slave module EM DP01 PROFIBUS-DP slave module EM DR01 Communication signal board, RS485/RS232 EM CM01 Communication signal board, 2 x 24 V DC input / 2 x 24 V DC output EM AR01 Digital expansion signal board, 1 x 12-bit analog input EM AR01 Analog expansion signal board, 1 x 12-bit analog output EM AR01 Battery signal board, support CR1025 button battery (battery purchased separately) EM ES7 288-5BA01-0AA0 Acessories I/O Extension Cable S7-200 SMART I/O extension cable, 1 m in length EMS7 288-6EC01-0AA0 EMS7 288-0ED10-0AA0 EMS7 288-0ED10-0AA0 EMS7 288-0ED10-0AA0 EMS7 288-0ED10-0AA0 EMS7 288-0ED10-0AA0 EMS7 288-0ED10-0AA0	EM AQ02	Analog output module, 2 outputs	6ES7 288-3AQ02-0AA0
EM AM06 Analog input/output module, 4 inputs / 2 outputs EM AR02 Thermal resistance input module, 2 channels EM AR04 Thermal resistance input module, 4 inputs EM AR04 Thermal resistance input module, 4 inputs EM AT04 Thermocouple input module, 4 channels EM AT04 Thermocouple input module, 4 channels EM DP01 PROFIBUS-DP slave module EM DP01 PROFIBUS-DP slave module EM ST 288-3AT04-0AA0 EM DP01 PROFIBUS-DP slave module EM ST 288-3AT04-0AA0 EM DP01 PROFIBUS-DP slave module EM ST 288-3AT04-0AA0 EM DP01 PROFIBUS-DP slave module EM ST 288-5CM01-0AA0 Signal board SB EM CM01 Communication signal board, RS485/RS232 EM ST 288-5CM01-0AA0 EM DP04 Digital expansion signal board, 2 x 24 V DC input / 2 x 24 V DC output EM ST 288-5DT04-0AA0 EM AR01 Analog expansion signal board, 1 x 12-bit analog input EM ST 288-5AE01-0AA0 EM AR01 Analog expansion signal board, 1 x 12-bit analog output EM ST 288-5AE01-0AA0 EM ST 288-5BA01-0AA0 Accessories I/O Extension Cable EM ST -200 SMART I/O extension cable, 1 m in length EM ST -200 SMART power supply, 24 V DC/3 A EM ST -200 SMART power supply, 24 V DC/5 A EM ST -200 SMART power supply, 24 V DC/5 A EM ST -200 SMART power supply, 24 V DC/10 A EM ST -200 SMART power supply, 24 V DC/10 A	EM AQ04	Analog output module, 4 outputs	6ES7 288-3AQ04-0AA0
EM AR02 Thermal resistance input module, 2 channels EM AR04 Thermal resistance input module, 4 inputs EM AR04 Thermal resistance input module, 4 inputs EM AT04 Thermocouple input module, 4 channels EM DP01 PROFIBUS-DP slave module EM DP01 PROFIBUS-DP slave module EM DP01 Communication signal board, RS485/RS232 ESB CM01 Communication signal board, RS485/RS232 ESB DT04 Digital expansion signal board, 2 x 24 V DC input / 2 x 24 V DC output ESS AE01 Analog expansion signal board, 1 x 12-bit analog input ESS AQ01 Analog expansion signal board, 1 x 12-bit analog output ESS AQ01 Analog expansion signal board, 1 x 12-bit analog output ESS AQ01 Battery signal board, support CR1025 button battery (battery purchased separately) Acessories I/O Extension Cable ESS 7-280 SMART I/O extension cable, 1 m in length ESS 7-200 SMART power supply, 24 V DC/3 A ESS 7-200 SMART power supply, 24 V DC/5 A ESS 7-280 SMART power supply, 24 V DC/10 A ESS 7-280 SMART power supply, 24 V DC/10 A	EM AM03	Analog input/output module, 2 inputs / 1 output	6ES7 288-3AM03-0AA0
EM AR04 Thermal resistance input module, 4 inputs EM AT04 Thermocouple input module, 4 channels EM DP01 PROFIBUS-DP slave module EM DP01 PROFIBUS-DP slave module Signal board SB SB CM01 Communication signal board, RS485/RS232 SB DT04 Digital expansion signal board, 2 x 24 V DC input / 2 x 24 V DC output SB AE01 Analog expansion signal board, 1 x 12-bit analog input SB AQ01 Analog expansion signal board, 1 x 12-bit analog output SB AQ01 Analog expansion signal board, 1 x 12-bit analog output SB BA01 Battery signal board, support CR1025 button battery (battery purchased separately) Acessories I/O Extension Cable S7-200 SMART I/O extension cable, 1 m in length PM207 S7-200 SMART power supply, 24 V DC/3 A PM207 S7-200 SMART power supply, 24 V DC/5 A PM207 S7-200 SMART power supply, 24 V DC/10 A 6ES7 288-0KD10-0AA0 FM207 S7-200 SMART power supply, 24 V DC/10 A 6ES7 288-0KD10-0AA0 FM207 S7-200 SMART power supply, 24 V DC/10 A 6ES7 288-0KD10-0AA0	EM AM06	Analog input/output module, 4 inputs / 2 outputs	6ES7 288-3AM06-0AA0
EM ATO4 Thermocouple input module, 4 channels EM DP01 PROFIBUS-DP slave module Signal board SB SB CM01 Communication signal board, RS485/RS232 SB CM01 Digital expansion signal board, 2 x 24 V DC input / 2 x 24 V DC output SB AE01 Analog expansion signal board, 1 x 12-bit analog input SB AQ01 Analog expansion signal board, 1 x 12-bit analog output SB BA01 Battery signal board, support CR1025 button battery (battery purchased separately) Acessories I/O Extension Cable S7-200 SMART I/O extension cable, 1 m in length PM207 S7-200 SMART power supply, 24 V DC/5 A PM207 S7-200 SMART power supply, 24 V DC/5 A PM207 S7-200 SMART power supply, 24 V DC/10 A 6ES7 288-3AT04-0AA0 6ES7 288-5CM01-0AA0 6ES7 288-5AE01-0AA0 6ES7 288-6EC01-0AA0 PM207 S7-200 SMART power supply, 24 V DC/5 A 6ES7 288-0ED10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/10 A	EM AR02	Thermal resistance input module, 2 channels	6ES7 288-3AR02-0AA0
EM DP01 PROFIBUS-DP slave module 6ES7 288-7DP01-0AA0 Signal board SB SB CM01 Communication signal board, RS485/RS232 6ES7 288-5CM01-0AA0 SB DT04 Digital expansion signal board, 2 x 24 V DC input / 2 x 24 V DC output 6ES7 288-5DT04-0AA0 SB AE01 Analog expansion signal board, 1 x 12-bit analog input 6ES7 288-5AE01-0AA0 SB AQ01 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5AQ01-0AA0 SB BA01 Battery signal board, support CR1025 button battery (battery purchased separately) 6ES7 288-5BA01-0AA0 Acessories I/O Extension Cable S7-200 SMART I/O extension cable, 1 m in length 6ES7 288-6EC01-0AA0 PM207 S7-200 SMART power supply, 24 V DC/3 A 6ES7 288-0CD10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/5 A 6ES7 288-0ED10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/10 A 6ES7 288-0KD10-0AA0	EM ARO4	Thermal resistance input module, 4 inputs	6ES7 288-3AR04-0AA0
Signal board SB Signal board SB SB CM01 Communication signal board, RS485/RS232 6ES7 288-5CM01-0AA0 SB DT04 Digital expansion signal board, 2 x 24 V DC input / 2 x 24 V DC output 6ES7 288-5DT04-0AA0 SB AE01 Analog expansion signal board, 1 x 12-bit analog input 6ES7 288-5AE01-0AA0 SB AQ01 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5AQ01-0AA0 SB BA01 Battery signal board, support CR1025 button battery (battery purchased separately) 6ES7 288-5BA01-0AA0 Acessories I/O Extension Cable S7-200 SMART I/O extension cable, 1 m in length 6ES7 288-6EC01-0AA0 PM207 S7-200 SMART power supply, 24 V DC/3 A 6ES7 288-0CD10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/5 A 6ES7 288-0ED10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/10 A 6ES7 288-0KD10-0AA0	EM AT04	Thermocouple input module, 4 channels	6ES7 288-3AT04-0AA0
SB CM01 Communication signal board, RS485/RS232 6ES7 288-5CM01-0AA0 SB DT04 Digital expansion signal board, 2 x 24 V DC input / 2 x 24 V DC output 6ES7 288-5DT04-0AA0 SB AE01 Analog expansion signal board, 1 x 12-bit analog input 6ES7 288-5AE01-0AA0 SB AQ01 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5AQ01-0AA0 SB BA01 Battery signal board, support CR1025 button battery (battery purchased separately) 6ES7 288-5BA01-0AA0 Accessories I/O Extension Cable S7-200 SMART I/O extension cable, 1 m in length 6ES7 288-6EC01-0AA0 PM207 S7-200 SMART power supply, 24 V DC/3 A 6ES7 288-0CD10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/5 A 6ES7 288-0CD10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/10 A 6ES7 288-0KD10-0AA0	EM DP01	PROFIBUS-DP slave module	6ES7 288-7DP01-0AA0
SB DT04 Digital expansion signal board, 2 x 24 V DC input / 2 x 24 V DC output 6ES7 288-5DT04-0AA0 SB AE01 Analog expansion signal board, 1 x 12-bit analog input 6ES7 288-5AE01-0AA0 SB AQ01 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5AQ01-0AA0 SB BA01 Battery signal board, support CR1025 button battery (battery purchased separately) 6ES7 288-5BA01-0AA0 Accessories I/O Extension Cable S7-200 SMART I/O extension cable, 1 m in length 6ES7 288-6EC01-0AA0 PM207 S7-200 SMART power supply, 24 V DC/3 A 6ES7 288-0CD10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/5 A 6ES7 288-0CD10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/10 A 6ES7 288-0KD10-0AA0	Signal board SB		
SB AE01 Analog expansion signal board, 1 × 12-bit analog input 6ES7 288-5AE01-0AA0 SB AQ01 Analog expansion signal board, 1 x 12-bit analog output 6ES7 288-5AQ01-0AA0 SB BA01 Battery signal board, support CR1025 button battery (battery purchased separately) 6ES7 288-5BA01-0AA0 Accessories I/O Extension Cable S7-200 SMART I/O extension cable, 1 m in length 6ES7 288-6EC01-0AA0 PM207 S7-200 SMART power supply, 24 V DC/3 A 6ES7 288-0CD10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/5 A 6ES7 288-0CD10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/10 A 6ES7 288-0KD10-0AA0	SB CM01	Communication signal board, RS485/RS232	6ES7 288-5CM01-0AA0
SB AQ01 Analog expansion signal board, 1 x 12-bit analog output SB BA01 Battery signal board, support CR1025 button battery (battery purchased separately) Accessories I/O Extension Cable S7-200 SMART I/O extension cable, 1 m in length PM207 S7-200 SMART power supply, 24 V DC/3 A PM207 S7-200 SMART power supply, 24 V DC/5 A PM207 S7-200 SMART power supply, 24 V DC/5 A S7-200 SMART power supply, 24 V DC/10 A S7-200 SMART power supply, 24 V DC/10 A GES7 288-0KD10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/10 A GES7 288-0KD10-0AA0	SB DT04	Digital expansion signal board, 2 x 24 V DC input / 2 x 24 V DC output	6ES7 288-5DT04-0AA0
SB BA01 Battery signal board, support CR1025 button battery (battery purchased separately) Accessories I/O Extension Cable S7-200 SMART I/O extension cable, 1 m in length 6ES7 288-6EC01-0AA0 PM207 S7-200 SMART power supply, 24 V DC/3 A 6ES7 288-0CD10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/5 A 6ES7 288-0ED10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/10 A 6ES7 288-0KD10-0AA0	SB AE01	Analog expansion signal board, 1 × 12-bit analog input	6ES7 288-5AE01-0AA0
Acessories I/O Extension Cable S7-200 SMART I/O extension cable, 1 m in length 6ES7 288-6EC01-0AA0 PM207 S7-200 SMART power supply, 24 V DC/3 A 6ES7 288-0CD10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/5 A 6ES7 288-0ED10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/10 A 6ES7 288-0KD10-0AA0	SB AQ01	Analog expansion signal board, 1 x 12-bit analog output	6ES7 288-5AQ01-0AA0
I/O Extension Cable S7-200 SMART I/O extension cable, 1 m in length 6ES7 288-6EC01-0AA0 PM207 S7-200 SMART power supply, 24 V DC/3 A 6ES7 288-0CD10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/5 A 6ES7 288-0ED10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/10 A 6ES7 288-0KD10-0AA0	SB BA01	Battery signal board, support CR1025 button battery (battery purchased separately)	6ES7 288-5BA01-0AA0
PM207 S7-200 SMART power supply, 24 V DC/3 A 6ES7 288-0CD10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/5 A 6ES7 288-0ED10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/10 A 6ES7 288-0KD10-0AA0	Acessories		
PM207 S7-200 SMART power supply, 24 V DC/5 A 6ES7 288-0ED10-0AA0 PM207 S7-200 SMART power supply, 24 V DC/10 A 6ES7 288-0KD10-0AA0	I/O Extension Cable	S7-200 SMART I/O extension cable, 1 m in length	6ES7 288-6EC01-0AA0
PM207 S7-200 SMART power supply, 24 V DC/10 A 6ES7 288-0KD10-0AA0	PM207	S7-200 SMART power supply, 24 V DC/3 A	6ES7 288-0CD10-0AA0
	PM207	S7-200 SMART power supply, 24 V DC/5 A	6ES7 288-0ED10-0AA0
	PM207	S7-200 SMART power supply, 24 V DC/10 A	6ES7 288-0KD10-0AA0
USB/PPI Cable S7-200 SMART Economy CPU programming cable, USB interface 6ES7 901-3DB30-0XA0	USB/PPI Cable	S7-200 SMART Economy CPU programming cable, USB interface	6ES7 901-3DB30-0XA0

XX-XXX-XXX

Siemens Ltd. Industry Sector Automation Systems Industrial Automation R&D Building, Kalwa Works Thane-Belapur Road, Airoli Thane – 400601 Tel. 022 - 33265005

Siemens Inc. All Rights Reserved

The information described hereby in the catalogue is only for the general description and characteristics of the products. The contents of this catalogue may show discrepancy with the actual application, and may change along with the product development. Only when there are clear provisions in the terms and conditions of the contract, Siemens Inc shall have the responsibility to provide the product characteristics specified in the catalogue.

All names mentioned in this brochure may be trademarks or product names of Siemens AG or its suppliers, and unauthorized use by third parties may infringe the rights of the owners.