

SIEMENS



3VA Enclosed Circuit Breaker Quick Reference

usa.siemens.com/3VA

125A TMTU Circuit Breaker Selection



| 125A, 3P \leq 25KAIC @ 480V | | | | |
|--|----------|----------|----------|--------------------|
| Amperage | ED43 | ED63 | NGG | 3VA51**4 |
| 15 | ED43B015 | ED63B015 | NGG3B015 | 3VA5195-4EC31-0AA0 |
| 20 | ED43B020 | ED63B020 | NGG3B020 | 3VA5120-4EC31-0AA0 |
| 25 | ED43B025 | ED63B025 | NGG3B025 | 3VA5125-4EC31-0AA0 |
| 30 | ED43B030 | ED63B030 | NGG3B030 | 3VA5130-4EC31-0AA0 |
| 35 | ED43B035 | ED63B035 | NGG3B035 | 3VA5135-4EC31-0AA0 |
| 40 | ED43B040 | ED63B040 | NGG3B040 | 3VA5140-4EC31-0AA0 |
| 45 | ED43B045 | ED63B045 | NGG3B045 | 3VA5145-4EC31-0AA0 |
| 50 | ED43B050 | ED63B050 | NGG3B050 | 3VA5150-4EC31-0AA0 |
| 60 | ED43B060 | ED63B060 | NGG3B060 | 3VA5160-4EC31-0AA0 |
| 70 | ED43B070 | ED63B070 | NGG3B070 | 3VA5170-4EC31-0AA0 |
| 80 | ED43B080 | ED63B080 | NGG3B080 | 3VA5180-4EC31-0AA0 |
| 90 | ED43B090 | ED63B090 | NGG3B090 | 3VA5190-4EC31-0AA0 |
| 100 | ED43B100 | ED63B100 | NGG3B100 | 3VA5110-4EC31-0AA0 |
| 110 | ED43B110 | ED63B110 | NGG3B110 | 3VA5111-4EC31-0AA0 |
| 125 | ED43B125 | ED63B125 | NGG3B125 | 3VA5112-4EC31-0AA0 |

| 125A, 3P 35KAIC @ 480V | | | |
|------------------------|----------|----------|--------------------|
| Amperage | NDG | HGG | 3VA51**5 |
| 15 | N/A | HGG3B015 | 3VA5195-5EC31-0AA0 |
| 20 | N/A | HGG3B020 | 3VA5120-5EC31-0AA0 |
| 25 | N/A | HGG3B025 | 3VA5125-5EC31-0AA0 |
| 30 | N/A | HGG3B030 | 3VA5130-5EC31-0AA0 |
| 35 | N/A | HGG3B035 | 3VA5135-5EC31-0AA0 |
| 40 | N/A | HGG3B040 | 3VA5140-5EC31-0AA0 |
| 45 | N/A | HGG3B045 | 3VA5145-5EC31-0AA0 |
| 50 | NDK3B050 | HGG3B050 | 3VA5150-5EC31-0AA0 |
| 60 | NDK3B060 | HGG3B060 | 3VA5160-5EC31-0AA0 |
| 70 | NDK3B070 | HGG3B070 | 3VA5170-5EC31-0AA0 |
| 80 | NDK3B080 | HGG3B080 | 3VA5180-5EC31-0AA0 |
| 90 | NDK3B090 | HGG3B090 | 3VA5190-5EC31-0AA0 |
| 100 | NDK3B100 | HGG3B100 | 3VA5110-5EC31-0AA0 |
| 110 | NDK3B110 | HGG3B110 | 3VA5111-5EC31-0AA0 |
| 125 | NDK3B125 | HGG3B125 | 3VA5112-5EC31-0AA0 |

| 125A, 3P \leq 65KAIC @ 480V | | | | | |
|--|----------|-----------|------------|----------|--------------------|
| Amperage | HDG | HED4 | HHED6 | LGG | 3VA51**6 |
| 15 | N/A | HED43B015 | HHED63B015 | LGG3B015 | 3VA5195-6EC31-0AA0 |
| 20 | N/A | HED43B020 | HHED63B020 | LGG3B020 | 3VA5120-6EC31-0AA0 |
| 25 | N/A | HED43B025 | HHED63B025 | LGG3B025 | 3VA5125-6EC31-0AA0 |
| 30 | N/A | HED43B030 | HHED63B030 | LGG3B030 | 3VA5130-6EC31-0AA0 |
| 35 | N/A | HED43B035 | HHED63B035 | LGG3B035 | 3VA5135-6EC31-0AA0 |
| 40 | N/A | HED43B040 | HHED63B040 | LGG3B040 | 3VA5140-6EC31-0AA0 |
| 45 | N/A | HED43B045 | HHED63B045 | LGG3B045 | 3VA5145-6EC31-0AA0 |
| 50 | HDK3B050 | HED43B050 | HHED63B050 | LGG3B050 | 3VA5150-6EC31-0AA0 |
| 60 | HDK3B060 | HED43B060 | N/A | LGG3B060 | 3VA5160-6EC31-0AA0 |
| 70 | HDK3B070 | HED43B070 | N/A | LGG3B070 | 3VA5170-6EC31-0AA0 |
| 80 | HDK3B080 | HED43B080 | N/A | LGG3B080 | 3VA5180-6EC31-0AA0 |
| 90 | HDK3B090 | HED43B090 | N/A | LGG3B090 | 3VA5190-6EC31-0AA0 |
| 100 | HDK3B100 | HED43B100 | N/A | LGG3B100 | 3VA5110-6EC31-0AA0 |
| 110 | HDK3B110 | HED43B110 | N/A | LGG3B110 | 3VA5111-6EC31-0AA0 |
| 125 | HDK3B125 | HED43B125 | N/A | LGG3B125 | 3VA5112-6EC31-0AA0 |

- 1.) Lugs are not included with 3VA circuit breakers, reference the table on next page for "standard" lug options.
- 2.) All 3VA circuit breakers are non-interchangeable trip units.
- 3.) In reference to 3VA, digits 9 and 10(-EC-) can be substituted for -ED-, this indicates non-adjustable instantaneous.
- 4.) Breakers cannot be installed in the enclosures at the factory.

250A TMTU Circuit Breaker Selection



400A TMTU Circuit Breaker Selection



250A, 3P 35KAIC @ 480V

| Amperage | FD6/FXD6 | NFG | 3VA52**5 |
|----------|----------|----------|--------------------|
| 100 | FD63B100 | NFK3B100 | 3VA5210-5EC31-0AA0 |
| 110 | FD63B110 | NFK3B110 | 3VA5211-5EC31-0AA0 |
| 125 | FD63B125 | NFK3B125 | 3VA5212-5EC31-0AA0 |
| 150 | FD63B150 | NFK3B150 | 3VA5215-5EC31-0AA0 |
| 175 | FD63B175 | NFK3B175 | 3VA5217-5EC31-0AA0 |
| 200 | FD63B200 | NFK3B200 | 3VA5220-5EC31-0AA0 |
| 225 | FD63B225 | NFK3B225 | 3VA5222-5EC31-0AA0 |
| 250 | FD63B250 | NFK3B250 | 3VA5225-5EC31-0AA0 |

400A, 3P 35KAIC @ 480V

| Amperage | JD6/JXD6 | NJG/NJX | 3VA53**5 |
|----------|--------------------|---------------------|--------------------|
| 200 | JD63B200 JXD63B200 | – | 3VA5320-5EC31-0AA0 |
| 225 | JD63B225 JXD63B225 | – | 3VA5322-5EC31-0AA0 |
| 250 | JD63B250 JXD63B250 | NJG3B250L NJX3B250L | 3VA5325-5EC31-0AA0 |
| 300 | JD63B300 JXD63B300 | NJG3B300L NJX3B300L | 3VA5330-5EC31-0AA0 |
| 350 | JD63B350 JXD63B350 | NJG3B350L NJX3B350L | 3VA5335-5EC31-0AA0 |
| 400 | JD63B400 JXD63B400 | NJG3B400L NJX3B400L | 3VA5340-5EC31-0AA0 |

250A, 3P 65KAIC @ 480V

| Amperage | HFD6/HFXD6 | HFG | 3VA52**6 |
|----------|------------|----------|--------------------|
| 100 | HFD63B100 | HFK3B100 | 3VA5210-6EC31-0AA0 |
| 110 | HFD63B110 | HFK3B110 | 3VA5211-6EC31-0AA0 |
| 125 | HFD63B125 | HFK3B125 | 3VA5212-6EC31-0AA0 |
| 150 | HFD63B150 | HFK3B150 | 3VA5215-6EC31-0AA0 |
| 175 | HFD63B175 | HFK3B175 | 3VA5217-6EC31-0AA0 |
| 200 | HFD63B200 | HFK3B200 | 3VA5220-6EC31-0AA0 |
| 225 | HFD63B225 | HFK3B225 | 3VA5222-6EC31-0AA0 |
| 250 | HFD63B250 | HFK3B250 | 3VA5225-6EC31-0AA0 |

400A, 3P 65KAIC @ 480V

| Amperage | HJD6/HJXD6 | HJG/HJX | 3VA53**6 |
|----------|----------------------|---------------------|--------------------|
| 200 | HJD63B200 HJXD63B200 | – | 3VA5320-6EC31-0AA0 |
| 225 | HJD63B225 HJXD63B225 | – | 3VA5322-6EC31-0AA0 |
| 250 | HJD63B250 HJXD63B250 | HJG3B250L HJX3B250L | 3VA5325-6EC31-0AA0 |
| 300 | HJD63B300 HJXD63B300 | HJG3B300L HJX3B300L | 3VA5330-6EC31-0AA0 |
| 350 | HJD63B350 HJXD63B350 | HJG3B350L HJX3B350L | 3VA5335-6EC31-0AA0 |
| 400 | HJD63B400 HJXD63B400 | HJG3B400L HJX3B400L | 3VA5340-6EC31-0AA0 |

250A, 3P 100KAIC @ 480V

| Amperage | HHFD6/HHFXD6 | LFG | 3VA52**7 |
|----------|--------------|----------|--------------------|
| 100 | HHFD63B100 | LFK3B100 | 3VA5210-7EC31-0AA0 |
| 110 | HHFD63B110 | LFK3B110 | 3VA5211-7EC31-0AA0 |
| 125 | HHFD63B125 | LFK3B125 | 3VA5212-7EC31-0AA0 |
| 150 | HHFD63B150 | LFK3B150 | 3VA5215-7EC31-0AA0 |
| 175 | HHFD63B175 | LFK3B175 | 3VA5217-7EC31-0AA0 |
| 200 | HHFD63B200 | LFK3B200 | 3VA5220-7EC31-0AA0 |
| 225 | HHFD63B225 | LFK3B225 | 3VA5222-7EC31-0AA0 |
| 250 | HHFD63B250 | LFK3B250 | 3VA5225-7EC31-0AA0 |

400A, 3P 100KAIC @ 480V

| Amperage | HHJD6/HHJXD6 | LJG/LJX | 3VA53**7 |
|----------|------------------------|---------------------|--------------------|
| 200 | HHJD63B200 HHJXD63B200 | – | 3VA5320-7EC31-0AA0 |
| 225 | HHJD63B225 HHJXD63B225 | – | 3VA5322-7EC31-0AA0 |
| 250 | HHJD63B250 HHJXD63B250 | LJG3B250L LJX3B250L | 3VA5325-7EC31-0AA0 |
| 300 | HHJD63B300 HHJXD63B300 | LJG3B300L LJX3B300L | 3VA5330-7EC31-0AA0 |
| 350 | HHJD63B350 HHJXD63B350 | LJG3B350L LJX3B350L | 3VA5335-7EC31-0AA0 |
| 400 | HHJD63B400 HHJXD63B400 | LJG3B400L LJX3B400L | 3VA5340-7EC31-0AA0 |

600A TMTU Circuit Breaker Selection



| 600A, 3P 35KAIC @ 480V | | | |
|------------------------|-----------------------|------------------------|--------------------|
| Amperage | LD6/LXD6 | NLK | 3VA54**5 |
| 450 | LD63B450 LXD63B450 | NLK3B450L NLX3B450L | 3VA5445-5EC31-0AA0 |
| 500 | LD63B500 LXD63B500 | NLK3B500L NLX3B500L | 3VA5450-5EC31-0AA0 |
| 600 | LD63B600 LXD63B600 | NLK3B600L NLX3B600L | 3VA5460-5EC31-0AA0 |

| 600A, 3P 65KAIC @ 480V | | | |
|------------------------|-------------------------|------------------------|--------------------|
| Amperage | HLD6/HLXD6 | HLK | 3VA54**6 |
| 450 | HLD63B450 HLXD63B450 | HLK3B450L HLX3B450L | 3VA5445-6EC31-0AA0 |
| 500 | HLD63B500 HLXD63B500 | HLK3B500L HLX3B500L | 3VA5450-6EC31-0AA0 |
| 600 | HLD63B600 HLXD63B600 | HLK3B600L HLX3B600L | 3VA5460-6EC31-0AA0 |

| 600A, 3P 100KAIC @ 480V | | | |
|-------------------------|--------------------------|------------------------|--------------------|
| Amperage | HHL6/HHLXD6 | LLX | 3VA54**7 |
| 450 | HHL63B450 HHLXD63B450 | LLX3B450L LLX3B450L | 3VA5445-7EC31-0AA0 |
| 500 | HHL63B500 HHLXD63B500 | LLX3B500L LLX3B500L | 3VA5450-7EC31-0AA0 |
| 600 | HHL63B600 HHLXD63B600 | LLX3B600L LLX3B600L | 3VA5460-7EC31-0AA0 |

800A TMTU Circuit Breaker Selection



| 800A, 3P 35KAIC @ 480V | | | |
|------------------------|--------------------------|-----------|--------------------|
| Amperage | MD6/MXD6 (50KAIC @ 480V) | NMG | 3VA55**5 |
| 500 | MD63B500 MXD63B500 | NA | NA |
| 600 | MD63B600 MXD63B600 | NMG3B600L | 3VA5560-5EC32-0AA0 |
| 700 | MD63B700 MXD63B700 | NMG3B700L | 3VA5570-5EC32-0AA0 |
| 800 | MD63B800 MXD63B800 | NMG3B800L | 3VA5580-5EC32-0AA0 |

| 800A, 3P 65KAIC @ 480V | | | |
|------------------------|----------------------|-----------|--------------------|
| Amperage | HMD6/HMXD6 | HMG | 3VA55**6 |
| 500 | HMD63B500 HXMD63B500 | NA | NA |
| 600 | HMD63B600 HXMD63B600 | HMG3B600L | 3VA5560-6EC32-0AA0 |
| 700 | HMD63B700 HXMD63B700 | HMG3B700L | 3VA5570-6EC32-0AA0 |
| 800 | HMD63B800 HXMD63B800 | HMG3B800L | 3VA5580-6EC32-0AA0 |

| 800A, 3P 100KAIC @ 480V | | | |
|-------------------------|-----------|-----------|--------------------|
| Amperage | CMD6 | LMG | 3VA**7 |
| 500 | NA | NA | NA |
| 600 | CMD63B600 | LMG3B600L | 3VA5560-7EC32-0AA0 |
| 700 | CMD63B700 | LMG3B700L | 3VA5570-7EC32-0AA0 |
| 800 | CMD63B800 | LMG3B800L | 3VA5580-7EC32-0AA0 |

Note: All 3VA 800A breakers come with nut keepers installed.

1000A TMTU Circuit Breaker Selection



| 1000A, 3P 35KAIC @ 480V | | | |
|-------------------------|--------------------------|-----------|----------------------------|
| Amperage | ND6/NXD6 (50KAIC @ 480V) | NNG | 3VA66**5 (Electronic Trip) |
| 1000 | ND63B100 NXD63B100 | NNG3B100L | 3VA6610-5HL32-0AA0 |


| 1000A, 3P 65KAIC @ 480V | | | |
|-------------------------|----------------------|-----------|----------------------------|
| Amperage | HND6/HNXD6 | HNG | 3VA66**6 (Electronic Trip) |
| 1000 | HND63B100 HNXD63B100 | HNG3B100L | 3VA6610-6HL32-0AA0 |

| 1000A, 3P 100KAIC @ 480V | | | |
|--------------------------|-----------|-----------|----------------------------|
| Amperage | CND6 | LNG | 3VA66**7 (Electronic Trip) |
| 1000 | CND63B100 | LNG3B100L | 3VA6610-7HL32-0AA0 |

Lug Selection

| | 3VA "Standard" lugs | Description | Cables Per Phase |
|--------------------|---------------------|-----------------------|------------------|
| 125A TMTU | 3VA91330JB11 | 3-POLE #14-3/0 | 1 |
| 250A TMTU | 3VA92330JB12 | 3-POLE #6-350KCMIL | 1 |
| 150A ETU | 3VA91430JB11 | 3-POLE #14-1/0 | 1 |
| 250A ETU | 3VA92430JB12 | 3-POLE #6-350KCMIL | 1 |
| 400/600A TMTU/ETU | 3VA9473-0JJ23 | 3-POLE 2/0 - 600KCMIL | 2 |
| 600/700A TMTU | 3VA9573-0JB23 | 3-POLE 4/0 - 600KCMIL | 2 |
| 800/1000A TMTU/ETU | 3VA9673-0JJ43 | 3-POLE 4/0 - 500KCMIL | 4 |

Note: For additional Lugs options reference section 7 of the online SpeedFax.



Internal Accessory Selection

| Description | Catalog No. |
|----------------------|--------------|
| Shunt Trip Flex 120V | 3VA99780BA22 |
| Shunt Trip Left 120V | 3VA99780BL32 |
| HQ Aux 1 Slot | 3VA99780AA12 |
| UVR 120V | 3VA99780BB24 |

Note: For additional accessory options, reference section 4 of the 3VA UL Catalog.




Enclosure Selection

| NEMA Type Enclosure | 125A Catalog No. | 150A/250A Catalog No. | 400/600A Catalog No. | 800/1000A Catalog No. |
|---------------------------|------------------|-----------------------|----------------------|-----------------------|
| 3VA NEMA 1 Surface | 3VAE125N1S | 3VAE250N1S | 3VAE6001S | 3VAE8001S |
| 3VA NEMA 1 Flush | 3VAE125N1F | 3VAE250N1F | 3VAE6001F | 3VAE8001F |
| 3VA NEMA 3R | 3VAE125N3R | 3VAE250N3R | 3VAE6003R | 3VAE8003R |
| 3VA NEMA 12 | 3VAE125N12 | 3VAE250N12 | 3VAE60012 | 3VAE80012 |
| 3VA NEMA 4X | 3VAE125N4X | 3VAE250N4X | 3VAE6004X | 3VAE8004X |
| 3VA NEMA 4X 316 Stainless | 3VAE125N4X316 | 3VAE250N4X316 | 3VAE6004X316 | 3VAE8004X316 |



3VA – UL molded case circuit breaker MLFB structure



**Published by
Siemens 2021**

Siemens Industry, Inc.
3617 Parkway Ln
Peachtree Corners, GA 30092

Siemens Technical Support: 1-800-333-7421
info.us@siemens.com

Printed in USA
Order No. CBFL-3ENCQ-0521
All Rights Reserved
© 2021, Siemens Industry, Inc.
usa.siemens.com/3VA

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.