

# SIEMENS

*Ingenuity for life*

## Plant asset management for smart field devices

SIMATIC PDM Maintenance Station V3.0

[usa.siemens.com/simatic-pdmms](http://usa.siemens.com/simatic-pdmms)

### Efficiently service and maintain intelligent field devices

Field devices are the eyes and ears of automation. The failure of a valve positioner, temperature, flow or pressure sensor can quickly lead to serious malfunction of the process. With SIMATIC PDM Maintenance Station V3.0, Siemens offers the right solution for efficiently monitoring the condition of smart field devices, irrespective of the automation and control systems used.

#### Applications:

- Stand-alone maintenance station for diagnostics and condition monitoring of field devices with EDD/FDI technology
- Use as stand-alone maintenance station for small and medium-sized facilities (up to 500 tags per maintenance station) in process and production automation (Additional MS's can be added to increase tag count.)
- Subsystem-specific use in large facilities
- Central data access point of plant data for cloud based apps
- Permits simultaneous access for 30 independent PDM web-clients users

No matter the architecture of the control system the maintenance station can access HART field devices and field components connected to HART multiplexers or communicate via wireless HART. The integration is based on the EDD/FDI description technology for field devices. Diagnostics, parameterization and condition data are cyclically read from the smart field devices and clearly displayed on an HMI. Field devices can be assigned to one of three groups for which a cyclic readout of the parameter and status data can be accessed. Subsequent external storage can be configured as a file in XML format. Through the export function, the data collected can also be transmitted to enterprise asset management systems or cloud-based condition monitoring systems for further processing. Version 3.0 was refined on the basis of the NAMUR recommendations NE105, 107 and 129.

The SIMATIC PDM software forms the basis for the SIMATIC PDM Maintenance Station SIMATIC PDM (process device manager) forms the basis for the data and condition acquisition of the intelligent field devices in the maintenance station.



The SIMATIC PDM Maintenance Station is the first choice when it comes to the servicing and maintenance of intelligent field devices and is employed in a wide range of industries, e.g. sewage treatment plants, biogas plants and painting lines in the automotive industry.



The SIMATIC PDM MS consists of a pre-installed industrial PC – the Microbox IPC 427E, as well as software and functional licenses

SIMATIC PDM is a universal, non-proprietary tool for the configuration, parameterization, commissioning and monitoring of smart field devices. SIMATIC PDM provides diagnostics, condition and parameter data to the SIMATIC PDM maintenance station.

#### Consistent subsequent data processing

The information from SIMATIC PDM is prepared in the SIMATIC PDM MS and supplemented by functionalities such as overview or work progress lists; overview, segment and detail screens; condition logs; parameter data archiving; global and device-specific message lists as well as cyclic functions for reading and exporting field device information such as overview displays and progress lists.

In production facilities with SIMATIC automation stations, the SIMATIC PDM MS is directly connected to the plant bus. It thus communicates with the field devices of the subordinated fieldbus systems through the automation stations. Even if it is not integrated into a SIMATIC PCS 7 project, it can utilize the existing infrastructure of a SIMATIC S7/PCS 7 project. In addition, a separate network to the field devices can be set up if direct access is not possible.

#### Standardized display of messages

In its recommendation NE 107, NAMUR has uniformly defined four status signals for all field devices including device failure, maintenance requirement, outside the specification and function control. This enables identical condition visualization for all field devices that are based on the EDD/FDI device description package – irrespective of device manufacturer. The SIMATIC MS cyclically and autonomously reads this information from the field devices and reports any maintenance requirements, requests or alarms based on the NAMUR standard. The maintenance staff is thus immediately informed and can act or respond in a timely manner.

#### Easy engineering

The engineering of the SIMATIC PDM Maintenance Station is simple to integrate and use. Network structures and field devices can be easily adopted from existing projects. Optionally, the SIMATIC PDM Maintenance Station can communicate to the field devices to be monitored in the quantity structure, as well as being enhanced, by the server/client functionality of SIMATIC PDM.

#### Ready for the cloud

Field devices are becoming ever smarter, i.e. they themselves are able to provide more and more information and transmit it via bus systems to other components in the network. With the latest version

of the SIMATIC PDM MS, field device data can be cyclically provided for transport into cloud-based applications. This opens up the way for condition monitoring functions to be realized as cloud-based applications – independent of the automation system. The cyclical acquisition of data in the SIMATIC PDM MS results in long-term data series from which the applications can develop statements on the life cycle or intelligent preventive maintenance service strategies.

#### Highlights

- Same functions and user interface as the SIMATIC PCS 7 Maintenance Station
- Possibility of data collection, analysis and processing in the cloud
- Operation is independent of the technological project and the automation system used
- Compact, flexible and expandable maintenance station
- Multiple maintenance stations per project possible
- Supports various communication types and gateways between bus systems, such as Ethernet, PROFINET, PROFIBUS DP/PA and HART
- Parameterization and detailed diagnostics of the field devices via integrated SIMATIC PDM
- One station can aggregate data of multiple automation projects

Siemens Industry, Inc.  
Process Industries and Drives  
100 Technology Drive  
Alpharetta, GA 30005  
1-800-365-8766  
info.us@siemens.com

Subject to change without prior notice  
Order No.: PIFL-B10258-1218  
All rights reserved  
Printed in USA  
© 2018 Siemens Industry, Inc.