

Catalog HA 40.6

**MEDIUM-VOLTAGE SWITCHGEAR** 

# **Switchgear Type 8DJH 24 – blue GIS** for Secondary Distribution Systems up to 24 kV, Gas-Insulated

siemens.com/8DJH24

# Application Typical uses



Application in public and industrial energy systems









Contents	Page
----------	------

MEDIUM-VOLTAGE SWITCHGE	Ν	ΛE	D	IΙ	J٨	/I-V	VO	LT	A	GΕ	S١	ΝI	Т	CH	G	E	Α	R	
-------------------------	---	----	---	----	----	------	----	----	---	----	----	----	---	----	---	---	---	---	--

# Switchgear Type 8DJH 24 – blue GIS

for Secondary Distribution Systems up to 24 kV, Gas-Insulated

Catalog HA 40.6 · 2024

siemens.com/medium-voltage-switchgear

Application	
Versions	4
Гуріcal uses, ratings, standards	5
Requirements	
Features, Safety	6
Technology	7
Digitalization, condition monitoring	
Siemens Xcelerator, available monitoring functionalities	8
Digitalization solutions from a single source	9
Sustainability	10
Technical data	
Switchgear	12
Switching devices	13
Product range	
ndividual panels	14
Panel blocks (excerpt)	17
Design	
Overview	20
Panel design (examples)	22
Outdoor enclosure	24
Components	
Busbar extension, modularity	25
Cable connection	26
Current transformers, voltage transformers	27 28
Current sensors, voltage sensors SIBushing	29
Low-voltage compartment, low-voltage niche	30
Dimensions	
Room planning	31
Pressure relief	33

# **Application** Versions





Individual circuit-breaker panel 450 mm

RRT block

### **Application**

Typical uses, ratings, standards

8DJH 24 switchgear is a factory-assembled, type-tested, 3-pole metal-enclosed single-busbar switchgear for indoor installation.

8DJH 24 switchgear is used in public and industrial energy systems of the secondary distribution level, e.g. in

- Secondary transformer substations of power supply system operators
- Utilities transfer substations for business enterprises
- Installations of building supply technologies
- Water and sewage treatment plants
- Underground railway stations, railway stations, airports
- Charging stations for electric vehicles
- Generating plants for renewable energies (biomass, hydro power, wind turbines, solar parks).

#### Electrical data (maximum values) and dimensions

		<u> </u>				
Rated voltage	kV	7.2	12	15	17.5	24
Rated frequency	Hz	50	50	50	50	50
Rated short-duration						
power-frequency						
withstand voltage	kV	20	28	36	38	50
Rated lightning impulse						
withstand voltage	kV	60	75	95	95	125
Rated peak						
withstand current	kA	50/52.5	50/52.5	50/52.5	50/52.5	50/52.5
Rated short-time						
withstand current 3 s	kA	20/21	20/21	20/21	20/21	20/21
Rated short-time						
withstand current 1 s	kA	20/21	20/21	20/21	20/21	20/21
Rated continuous current						
of the busbar	Α	630	630	630	630	630
Rated continuous current						
of feeders u	p to A	630 <sup>1)</sup>	630 <sup>1)</sup>	630 <sup>1)</sup>	630 <sup>1)</sup>	630 <sup>1)</sup>
Width (feeders)	mm	350/45	0 / 550 1) -			-
Depth						
<ul> <li>without pressure relief duct</li> </ul>	mm	775	775	775	775	775
– with pressure relief duct	mm	890	890	890	890	890
Height						
without low-voltage						
compartment and						
pressure relief duct	mm	optional	l <u>y 1200/</u> 1	400/170	0	

<sup>1)</sup> Depending on the feeder function and the selected design options

#### **Standards**

		IEC standard/ EN standard		
Switchgear		62271-1		
		62271-200		
Switching	Circuit-breakers	62271-100		
devices	Disconnectors and earthing switches	62271-102		
	Switch-disconnectors	62271-103		
	Switch-fuse combination	62271-105		
Voltage detectir	ng systems	62271-213		
HV HRC fuses		60282		
Surge arresters /	surge limiters	60099		
Degree of prote	ction	60529		
		62262		
Insulation		60071		
Instrument	General requirements	61869-1		
transformers	Current transformers	61869-2		
	Inductive voltage transformers	61869-3		
	Low-power current transformers	61869-6		
		61869-10		
	Low-power voltage transformers	61869-6		
		61869-11		
Insulating gas		62271-4		
Installation		61936-1/EN 50522		
Environmental of	conditions	60721-3-3		
Operation		EN 50110		

### Requirements

Features

#### **Environmental independence**

Hermetically tight, welded switchgear vessels made of stainless steel as well as single-pole solid insulation make the parts of the primary circuit under high voltage of 8DJH 24 switchgear

- Insensitive to certain aggressive ambient conditions, such as:
  - Saline air
  - Air humidity
  - Dust
  - Condensation
- Tight to ingress of foreign objects, such as:
  - Dust
  - Pollution
  - Small animals
  - Humidity.

#### **Compact design**

Thanks to the use of an insulation of natural gases (Clean Air), compact dimensions are possible.

- Existing switchgear rooms and substation rooms can be used effectively
- New constructions cost little
- Costly city-area space is saved.

#### Maintenance-free design

Switchgear vessels designed as sealed pressure systems, maintenance-free switching devices and enclosed cable plugs ensure:

- Maximum supply reliability
- Personnel safety
- Sealed-for-life design according to IEC 62271-200 (sealed pressure system)
- Installation, operation, extension and replacement without gas work
- Reduced operating costs
- Cost-efficient investment
- No maintenance cycles.

#### **Innovation**

The use of digital secondary systems and combined protection and control devices ensures:

- Clear integration in process control systems
- Flexible and highly simplified adaptation to new system conditions and thus to cost-efficient operation.

#### Service life

Under normal service conditions, the expected service life of gas-insulated switchgear 8DJH 24 is at least 40 years, taking the tightness of the hermetically welded switchgear vessel into account. The service life is limited by the maximum number of operating cycles of the switchgear devices installed:

- For circuit-breakers, according to the endurance class defined in IEC 62271-100
- For three-position disconnectors and earthing switches, according to the endurance class defined in IEC 62271-102
- For three-position switch-disconnectors, according to the endurance class defined in IEC 62271-103.

#### Safety

#### **Personal safety**

- Safe-to-touch and hermetically sealed primary enclosure
- Standard degree of protection IP65 for all high-voltage parts in the switchgear vessel, at least IP2X for the switchgear enclosure according to IEC 60529
- All high-voltage parts including the cable terminations, busbars and voltage transformers are metal-enclosed and/or provided with earthed layers
- Panels tested for resistance to internal faults up to 21 kA
- Capacitive voltage detecting system to verify safe isolation from supply
- Logical mechanical interlocks prevent maloperation
- HV HRC fuses and cable compartments are only accessible when outgoing feeders are earthed
- Feeder earthing via make-proof earthing switches.

#### Security of operation

- Hermetically sealed primary enclosure independent of environmental effects (pollution, humidity and small animals)
- Welded switchgear vessels, sealed for life
- Maintenance-free in an indoor environment (IEC 62271-1)
- Operating mechanisms of switching devices and auxiliary switches accessible outside the primary enclosure (switchgear vessel)
- Metal-coated, plug-in inductive voltage transformers mounted outside the switchgear vessel
- Current transformers as ring-core current transformers mounted outside the switchgear vessel
- Complete switchgear interlocking system with logical interlocks
- Mechanical position indicators integrated in the mimic diagram
- Minimum fire load
- Option: Resistance against earthquakes.

### Reliability

- Type and routine-tested
- Standardized and manufactured using numerically controlled machines
- Quality assurance in accordance with DIN EN ISO 9001
- More than 1,500,000 switchgear panels of Siemens in operation worldwide for many years.

### Requirements

Technology

#### General

- Panels 3-pole metal-enclosed
- High-voltage compartments with metal partitions
- Hermetically tight, welded switchgear vessel made of stainless steel, with welded-in bushings for electrical connections and mechanical components
- Frame made of sendzimir-galvanized sheet steel
- Front covers and doors of low-voltage compartments powder-coated in color RAL 7035 (light gray)
- Functions as individual panels or combined in a panel block with up to four functions in a common switchgear vessel
- Switching devices 3-pole, fixed-mounted, depending on the function
  - Three-position switch-disconnector
  - Three-position switch-disconnector/fuse combination
  - Vacuum circuit-breaker with three-position disconnector
  - Make-proof earthing switch
- Cable connection with outside-cone plug-in system according to DIN EN 50181
  - In ring-main and circuit-breaker feeders with bolted contact (M16)
  - In transformer feeders with plug-in contact or optionally with bolted contact (M16)
- Wall-standing or free-standing arrangement
- Pressure relief downwards, optionally upwards via pressure absorber systems.

#### Interlocks

- According to IEC 62271-200
- Logical mechanical interlocks and the constructive features
  of the three-position switches prevent maloperation as
  well as access to the cable connection of the feeders and
  HV HRC fuses under voltage
- Impermissible and undesired operations can be prevented by means of locking devices provided at the switching devices.

#### Modular design

- Individual panels and panel blocks can be lined up and optionally extended – without gas work on site
- Option: Low-voltage compartment available in 3 overall heights. Installation and removal possible on site, wiring to the panel via plug connections.

#### **Instrument transformers**

- Ring-core current transformers not subjected to dielectric stress
- Metal-coated voltage transformers, plug-in type
- In the air-insulated metering panel:
   Cast-resin insulated block-type current and voltage transformers (narrow design according to DIN 42600 Part 8 or Part 9)
- Replacement of instrument transformers without gas work, as they are located outside the switchgear vessel.

#### Sensors

- Current sensor as inductive current transformer in combination with precision shunt (voltage signal)
- Voltage sensor as resistor divider
- In combination with secondary devices such as
  - SICAM FCM
  - 7SJ81.

#### Vacuum circuit-breaker

- Maintenance-free under normal ambient conditions according to IEC 62271-1
- No relubrication or readjustment
- Up to 10,000 operating cycles
- Vacuum-tight for life.

#### **Secondary systems**

- Customary protection, measuring and control equipment
- Option: Numerical multifunction protection relay with integrated protection, control, communication, operating and monitoring functions
- Can be integrated in process control systems.

### Digitalization, condition monitoring

Siemens Xcelerator, available monitoring functionalities

#### **Siemens Xcelerator**

Siemens Xcelerator is an open digital business platform that enables customers to accelerate their digital transformation more easily, quickly, and at scale.

# Addressing key challenges in the energy sector and beyond

**Maintaining grid stability** – Increasing energy demands often clash with fluctuating generation. Balancing both is crucial for tomorrow's grid stability.

Our smart energy solutions simplify management, align OT and IT, and ensure a resilient, scalable, and adaptable grid.

**Maximizing cyber and asset security –** Power grids can be a target for cyberattacks, which may cause power outages and unpredictable results.

Our solutions incorporate security measures to remove vulnerabilities in IT components, control devices, as well as transformer substation and switchgear systems.

**Reducing expenditures** – Our solutions enhance competitiveness through optimized CAPEX and OPEX with asset optimization, digital planning, simulation, and flexible financing options.

**Integrating distributed energy resources (DERs) –** DERs are at the heart of a clean and resilient energy future. Nevertheless, a greater system flexibility is needed to consistently balance supply and demand.

Our solution offering covers the entire spectrum: from consulting through technical applications and services to tailored financing and business models.

# Available monitoring functionalities for gas-insulated switchgear

#### **Condition monitoring**

Condition monitoring serves to continuously improve the resilience, reliability, and availability of maintenance-free, gas-insulated medium-voltage switchgear with an expected service life of 40 years. These values are based on the design and empirical data for switchgear assemblies, as well as on the intended use of the switchgear under normal service conditions according to IEC 62271-1.

To protect the investment (CAPEX) and reduce operational expenditures (OPEX), the extension of switchgear functions with a condition monitoring system is the appropriate way for early indication of irregularities at the switchgear and its peripheral components. This is the premise for condition-based inspection.

#### Temperature monitoring of the cable connections

Temperature monitoring of the cable connections ensures that the maximum permissible thermal service conditions of the gas-insulated switchgear and the cable connection set are not exceeded during operation. With the help of an intelligent correlation between the ambient air temperature, the cable connection temperature, and the switchgear utilization, anomalies can already be detected and indicated before the limit temperature is reached, based also on low-load scenarios.

# Temperature and humidity monitoring of the environment (dew-point monitoring)

Ongoing condensation would lead to corrosion at the switchgear, and reduce its service life. Specific countermeasures after strong humidity at the switchgear assembly, as well as the prevention of further condensation, can remedy the situation.

#### Partial discharge monitoring

Partial discharges arise if the electrical insulation is damaged or insufficient. Partial discharge monitoring offers a pre-alarming in case of a possibly insufficient electrical insulation. In most cases, partial discharges are a long-term effect of thermal overstressing or of defective or incorrectly installed peripheral components.

#### Digital gas density monitoring

For perfect operation of a gas-insulated switchgear, the correct gas density inside the switchgear vessel is crucial. To maintain the full scope of functions of the switchgear, immediate action is required if the gas density falls below the necessary values.

#### **Circuit-breaker monitoring**

Continuous monitoring of circuit-breaker functions enables an evaluation of the actual health status of the circuit-breaker, based on both mechanical and electrical parameters. The evaluation of performed mechanical and electrical switching operations, as well as the monitoring of other components, allows to indicate at an early stage if servicing work is necessary, or if a suitable replacement switchgear should be procured.

#### Load flow monitoring

An increasing number of distributed energy resources and the growing share of e-mobility lead to ever more volatile load flows in the distribution grids. Capturing this data is an important element for identifying hotspots in the grid, and it offers planning security for the operator.

## Sustainability

#### Our contribution to a sustainable and cleaner planet

At Siemens, sustainability is not just a commitment, but a core strategy deeply ingrained in our operations. Our DEGREE framework, representing **Decarbonization**, **Ethics**, **Governance**, **Resource Efficiency**, **Equity**, and **Employability**, guides our journey towards a sustainable future. It constitutes a 360-degree approach for all stakeholders – our customers, our suppliers, our investors, our people, the societies we serve, and our planet.

Siemens aims to limit global warming to 1.5 degrees Celsius and takes action across its operations, targeting various ESG (Environmental, Social, and Governance) topics. We further contribute to decarbonization by helping our customers reduce emissions, and aim to lower our own operational emissions significantly by 2030. Additionally, we promote resource efficiency through recycling and a circular economy, incorporating sustainable design criteria into our products and increasing the use of secondary materials. Siemens focuses on sustainable materials, energy sources, and product service life optimization to minimize resource consumption and waste. Ultimately, we strive to create a better future by achieving sustainability goals and minimizing environmental impacts.

Siemens gas-insulated switchgear (GIS) systems have played a key role over the last 40 years for a reliable and safe power distribution. The new Siemens blue GIS portfolio reflects our commitment to 100% sustainable innovation, which integrates both Clean Air as an insulating medium and an eco-efficient design that reduces its CO<sub>2</sub> footprint throughout the entire life cycle. With a wide range of products covering all the needs, our blue GIS will be the core of a sustainable energy transition. The following innovative solutions offer a remarkable CO<sub>2</sub> footprint reduction:

**F-gas-free insulation:** Clean Air consists of natural-origin gases with a GWP < 1, which means it has virtually no negative impact on the environment or climate change during the entire life cycle. It can even be released into the atmosphere after reaching its end of life.

**Space efficiency:** Like the traditional GIS design, Siemens blue GIS also offer very compact solutions that save valuable space and additionally decrease the environmental impact of electrical infrastructure installations.



Material efficiency: blue GIS products are designed to have a very low CO<sub>2</sub> footprint. A prime example is SIBushing, a non-conventional instrument transformer that reduces the use of raw materials, energy consumption, and landfill waste.

**Energy efficiency:** An optimized main current path with a low ohmic resistance reduces the power loss during operation of the switchgear considerably, and thus increases the energy efficiency.

Long service life: With the right material selection and an innovative design, blue GIS have an expected service life of 40 years, thus extending the re-investment cycle and further diminishing the CO<sub>2</sub> footprint.

Maintenance-free design: No additional maintenance is necessary, and the CO<sub>2</sub> footprint can be reduced further by avoiding site visits during the operational phase of the switchgear.


**Sustainable services:** The CO<sub>2</sub> footprint can be diminished thanks to services from predictive maintenance to condition monitoring, remote FAT, CO<sub>2</sub> monitoring via NXpower monitor, the Totally Integrated Power planning tools, and paperless documentation.

### **Sustainability**

#### The complete life cycle that counts

In view of the global climate crisis and the necessity to reduce carbon emissions and preserve natural resources, Siemens aims to decrease the environmental footprint of its own business operations as well as that of its customers and supply chains. With internationally standardized approaches, we provide transparency regarding the environmental impacts of our products, systems, solutions, and services.

Robust Eco Design: Our blue GIS panels are designed as a part of the Eco Efficiency @ Siemens program, where the environmental impacts to be expected in each of the product's life cycle phases are addressed right from the design phase. The switchgear is designed not only to minimize its CO<sub>2</sub> footprint, but also to prioritize resource efficiency and circular economy.



The Siemens Environmental Product Declaration (EPD) adheres to ISO 14021 standards for environmental labels and declarations. It is based on a comprehensive Life Cycle Assessment (LCA) study conducted in accordance with ISO 14040/44, incorporating Product Category Rules (PCR) specified in EN 50693 for electronic and electrotechnical products and systems.

Product	8DJH 24 – secondary distribution blue GIS			
Technical data	$U_{\rm r} = 24$ kV, $I_{\rm k} = 21$ kA, $I_{\rm r} = 630$ A			
Product description	8DJH 24 is an F-gas-free gas-insulated load-break switchgear with Clean Air insulation for secondary distribution grids, and available as ring-main feeder (R), circuit-breaker feeder (L), transformer feeder (T), cable feeder (K), and metering panel (M); as individual panels and in panel blocks			
Functional unit	Reference 8DJH 24 – RRT block – secondary distribution blue GIS, primary part, type-tested according to IEC 62271-200. Maintenance-free, operating 24 h, 365 days/a with an expected service life of 40 years			

#### **Material composition**



#### **Resource efficiency**

The end-of-life phase of an 8DJH 24 – RRT block blue GIS was modeled with the LCA tool GaBi 9.5 by first dismantling the equipment, followed by a shredding, sorting, and material separation process, resulting in:

- An overall product recyclability of up to 82.4% mainly thanks to high metal content
- An energy recoverability of up to 16.8% from plastic materials
- A minimum disposal rate of 0.9%

The exact final values depend on the used recycling processes.

#### Use of environmentally safe materials

At Siemens, we are committed to the development and production of environmentally friendly and sustainably produced equipment. This includes avoiding hazardous substances in our products without compromising their benefits for our customers. Please visit the following website\* to learn more about how we comply with product-related environmental regulations like RoHS, REACh and others.

<sup>\*</sup> https://www.siemens.com/global/en/products/energy/ecotransparency/ ecotransparency-downloads.html

# **Technical data**

Switchgear

Electrical data of the switchgear

Rated insulation level	Rated voltage <i>U</i> <sub>r</sub>		kV	7.2	12	15	17.5	24	
	Rated short-duration power-frequency with	hstand voltage <i>և</i>	$J_{\rm d}$ :						
	– phase-to-phase, phase-to-earth, open co	ntact gap	kV	20	28	36	38	50	
	– across the isolating distance		kV	23	32	39	45	60	
	Rated lightning impulse withstand voltage	F							
	– phase-to-phase, phase-to-earth, open co	ntact gap	kV kV	60 70	75 85	95	95	125	
	– across the isolating distance	– across the isolating distance				110	110	145	
Rated frequency f <sub>r</sub>	_			50	50	50	50	50	
Rated continuous current $I_r^{(2)}$	for busbar		Α	630	630	630	630	630	
	for ring-main and cable feeders		A	630	630	630	630	630	
	for circuit-breaker feeders		Α	630	630	630	630	630	
	for transformer feeders	Depen	ding on	the HV F	HRC fuse-link →				
50 Hz Rated short-time withstand current $I_k$	for switchgear with $t_k = 1$ or 3 s <sup>1)</sup>	uŗ	to kA	20/21	1)			-	
Rated peak withstand current $I_p$		uŗ	to kA	50/52	2.51) —				
Filling level	Rated filling level $p_{re}$ (absolute)		kPa	190	190	190	190	190	
(pressure values at 20 °C)	Minimum functional level $p_{me}$ (absolute)		kPa	180	180	180	180	180	
Ambient air temperature T <sup>3)</sup>	Operation standard °C				-25 to +55				
	on request		°C	-40 to	+70 -				
	Storage / transport standard			-25 to					
		on request	°C	-40 to					
Degree of protection	for gas-filled switchgear vessel				IP65		 IP65	IP65	
g · p · ·	for switchgear enclosure				IP2X/IP3X <sup>1)</sup>				
	for low-voltage compartment	IP3X/IP4X <sup>1)</sup>							
Partition class	- Tor low voltage compartment			PM	PM			PM	
Loss of service continuity category	Feeder panels with (switch-)disconnector			LSC2	LSC2	LSC2	LSC2	LSC2	
, ,	Billing metering panel M, cable feeder K				LSC1	LSC1	LSC1	LSC1	
Accessibility to compartments	Busbar compartment			Non-a	ccessible	e ——			
(enclosure)	Switching-device compartment			Non-accessible —					
	Cable compartment/HV HRC fuse compart	ment							
	- Feeder panels with switching device				Interlock-controlled —				
	– Billing metering panel M, cable feeder K			Tool-b	ased —				
Internal arc classification 4)	IAC A								
(option)	Accessibility FL or FLR								
	Arc test current $I_{A}$	uŗ	to kA	21	21	21	21	21	
	Test duration $t_{\text{A}}$ s				1	1	1	1	

Design option
 The rated continuous currents apply to ambient air temperatures of max. 40 °C.
 The 24-hour mean value is max. 35 °C (according to IEC 62271-1)
 Minimum and maximum permissible ambient air temperature depending on the secondary equipment used 4) Description of the design options as of page 33

# **Technical data**

Switching devices

Rated voltage U <sub>r</sub>		kV	7.2	12	15	17.5	24
General-purpose switch function	Rated mainly active load breaking current $I_{load}$ A			630	630	630	630
	Rated short-circuit making current $I_{\rm ma}$ 50 Hz up t		50/52.	5 <sup>1)</sup> ———			-
	Electrical endurance	Class	E3	E3	E3	E3	E3
	Number of electrical operating cycles with $I_{ m load}$ n			100	100	100	100
	Number of short-circuit making operations with $I_{\mathrm{ma}}$	Number of short-circuit making operations with $I_{\rm ma}$ n			5	5	5
	Capacitive switching Class			C2	C2	C2	C2
	Mechanical endurance	Class	M1	M1	M1	M1	M1
	Number of mechanical operating cycles	n	1000	1000	1000	1000	1000
Disconnector function	Mechanical endurance	Class	MO	MO	M0	MO	MO
	Number of mechanical operating cycles	n	1000	1000	1000	1000	1000
Make-proof earthing switch function	Rated short-circuit making current $I_{\text{ma}}$ 50 Hz	up to kA	50/52.	51) ———		-	-
	Number of short-circuit making operations with $I_{\scriptscriptstyle{\mathrm{ma}}}$	n	5	5	5	5	5
	Mechanical endurance	Class	MO	MO	MO	MO	M0
	Number of mechanical operating cycles	n	1000	1000	1000	1000	1000

#### Three-position switch-disconnector/fuse combination

Rated voltage U <sub>r</sub>		7.2	12	15	17.5	24	
Switch function	Rated mainly active load breaking current $I_{\text{load}}$ A			200	200	200	200
	Rated short-circuit making current $I_{ma}$ 50 Hz	50/52.5	51)				
	Number of electrical operating cycles with $I_{load}$	n	100	100	100	100	100
	Number of short-circuit making operations with $I_{ m ma}$	n	5	5	5	5	5
	Mechanical endurance	Class	M1	M1	M1	M1	M1
	Number of mechanical operating cycles n			1000	1000	1000	1000
Switch-fuse combination function	Rated transfer current $I_{\text{transfer}}$	1400	1400	1400	1400	1400	
	Maximum permissible rated power S <sub>r</sub> up to kVA			1250	1250	1250	2000
	of the transformer 2)						
Disconnector function	Mechanical endurance	Class	M0	MO	MO	M0	M0
	Number of mechanical operating cycles	n	1000	1000	1000	1000	1000
Make-proof earthing switch function	Rated short-circuit making current $I_{ma}$ 50 Hz	up to kA	6.3	6.3	6.3	6.3	6.3
	Number of short-circuit making operations with $I_{ m ma}$	n	5	5	5	5	5
	Mechanical endurance Class			M1	M1	M1	M1
	Number of mechanical operating cycles	1000	1000	1000	1000	1000	

#### Vacuum circuit-breaker with three-position disconnector

Rated voltage U <sub>r</sub>		kV	7.2	12	15	17.5	24
Circuit-breaker type 1 function	Rated operating sequence		0 – 0.3	s – CO – 3	min – CC	)	
	Option		0 - 0.3	s – CO – 1	5 s – CO –		
	Rated short-circuit breaking current $I_{sc}$	up to kA	20/21 1				
	Electrical endurance	Electrical endurance Class			E2	E2	E2
	Number of short-circuit breaking operations with $I_{\rm sc}$ n			50	50	50	50
	Capacitive switching Class			C2	C2	C2	C2
	Switching of cable systems Class			S1	S1	S1	S1
	Mechanical endurance Class			M2	M2	M2	M2
	Number of mechanical operating cycles	n	10000	10000	10000	10000	10000
Disconnector function	Mechanical endurance	Class	M0	MO	MO	M0	M0
	Number of mechanical operating cycles	n	1000	1000	1000	1000	1000
Make-proof earthing switch function	Rated short-circuit making current $I_{\text{ma}}$ 50 Hz	up to kA	50/52.5	51)			
	Number of short-circuit making operations with $I_{\mathrm{ma}}$	n	5	5	5	5	5
	Mechanical endurance	Class	M0	M0	M0	M0	M0
	Number of mechanical operating cycles	n	1000	1000	1000	1000	1000

<sup>1)</sup> Design option 2) Depending on the primary voltage of the transformer and the HV HRC fuses used

# Product range Individual panels



Three-position disconnector



Vacuum circuit-breaker



Three-position switch-disconnector



Capacitive voltage detecting system



Surge arrester or limiter



Current transformer



Voltage transformer



Voltage sensor



Current sensor




Cable connection with outside cone (not included in scope of supply)



SIBushing (integrated measurement of current, voltage, and temperature)


#### Ring-main feeder (R)





#### Circuit-breaker feeder (L)







1) Only for panels with a width of 550 mm

# Product range Individual panels

#### Transformer feeder (T)





# **Product range**

Individual panels



Three-position disconnector



Vacuum circuit-breaker



Three-position switch-disconnector



Capacitive voltage detecting system



Surge arrester or limiter



Current transformer



HV HRC fuse



Voltage transformer



Voltage sensor



Current sensor



Fixed earthing points for busbar earthing



Cable connection with outside cone (not included in scope of supply)




SIBushing (integrated measurement of current, voltage, and temperature)


P1 and P2 are terminal designations of the current transformer

#### Cable feeder (K)





#### Billing metering panel (M)



# **Product range**


Panel blocks (excerpt)

### Panel blocks for 8DJH 24, 2-panel design, optionally with busbar extension

Components shown in dotted lines can be used optionally.


#### RT 1 ring-main feeder, 1 transformer feeder





#### RL 1 ring-main feeder, 1 circuit-breaker feeder





Three-position disconnector



Vacuum circuit-breaker



Three-position switch-disconnector



Capacitive voltage detecting system



Cable connection with outside cone (not included in scope of supply)



HV HRC fuse

# Product range Panel blocks (excerpt)



Three-position disconnector



Vacuum circuit-breaker



Three-position switch-disconnector



Capacitive voltage detecting system



Cable connection with outside cone (not included in scope of supply)




HV HRC fuse


### Panel blocks for 8DJH 24, 3-panel design, optionally with busbar extension

Components shown in dotted lines can be used optionally.

### RRT 2 ring-main feeders, 1 transformer feeder




#### RRL 2 ring-main feeders, 1 circuit-breaker feeder



# Panel blocks for 8DJH 24, 4-panel design, optionally with busbar extension

Components shown in dotted lines can be used optionally.


#### **RRRR 4 ring-main feeders**



Dimens	ions in	mm
Width	Denth	

Width	Depth	Height
1400	775	1200
		1400
		1700


#### RRRT 3 ring-main feeders, 1 transformer feeder



#### Dimensions in mm

Width	Depth	Height
1400	775	1200
		1400
		1700

#### RRRL 3 ring-main feeders, 1 circuit-breaker feeder



#### Dimensions in mm

Depth	Height
775	1200
	1400
	1700
	<u> </u>



Vacuum circuit-breaker



Three-position disconnector



Three-position switch-disconnector



HV HRC fuse




Capacitive voltage detecting system



Cable connection with outside cone (not included in scope of supply)



Surge arrester



#### 1 Low-voltage compartment

 Low-voltage compartments (option) in different heights of 200 mm, 400 mm or 600 mm for customer-specific secondary equipment

#### 2 Busbar extension, modularity

- Busbar extension as an ordering option
- Plug-in unit consisting of contact coupling and screened silicone coupling
- Insensitive to pollution and condensation
- Switchgear installation, extension, or panel replacement without gas work

#### 3 Indicators

 Voltage detecting systems, short-circuit/earth-fault indicators, and transformer monitors from various manufacturers

#### 4 Ring-main feeder

- Switching functions as general-purpose switch-disconnector according to IEC 62271-103 and IEC 62271-102
- Designed as a three-position switch incorporating the functions of a switch-disconnector and a make-proof earthing switch
- Switch positions: CLOSED OPEN EARTHED
- Manual operating mechanism, optionally motor operating mechanism

#### **5** Transformer feeder

- High-voltage switch-fuse combination according to IEC 62271-105
- Designed as a three-position switch
- Switch positions: CLOSED OPEN EARTHED
- Manual operating mechanism, optionally motor operating mechanism
- Mechanical "fuse tripped" indicator at the switchgear front

#### 6 HV HRC fuse assembly

- Fuse boxes, 1-pole, in the switchgear vessel
- HV HRC fuse-links according to DIN 43625 (main dimensions) with striker in "medium" version according to IEC 60282-1, for short-circuit protection of transformers

#### 7 Enclosure

- Hermetically tight, welded switchgear vessel made of stainless steel
- Enclosure made of sendzimir-galvanized sheet steel, switchgear front powder-coated

#### 8 SIBushing

 Outside-cone bushing type C with integrated sensors for current, voltage, and temperature measuring (option)

#### 9 Cable compartment

- Bushings according to DIN EN 50181 with outside cone and bolted connection M16 as interface type C (standard in cable, ring-main, and circuit-breaker feeders) or with outside cone and plug-in contact as interface type A (standard in transformer feeders)
- Adjustable cable bracket with C-rail, optionally with plastic cable clamps pre-assembled at the factory

#### Connection of:

- Cable elbow plugs or cable T-plugs
- Thermoplastic-insulated cables (1- and 3-core cables)
- Ring-core current transformers according to IEC 61869-1 and -2, around the cables
- Current sensors according to IEC 61869-10, around the cable plugs or around the cables
- Voltage sensors (resistor divider) according to IEC 61869-11, mounted on the cable plugs
- Surge arresters

#### 10 Dimension options

- Switchgear height 1400 mm (optionally 1200 m or 1700 mm)
- Deep cable compartment cover

#### 11 Pressure relief


- Pressure relief downwards
- Optionally upwards with absorber
- Up to IAC A FL 21 kA/1 s or IAC A FLR 21 kA/1 s

<u>Note:</u> More information on SIBushing, current sensor, voltage sensor can be found in the chapter "Digitalization, condition monitoring" on page 8.


# Design

Panel design (examples)


#### Ring-main feeder



#### Transformer feeder




#### Circuit-breaker feeder




- 1 Control board
- 2 Low-voltage compartment (standard)
- 3 Busbar arrangement
- 4 Three-position switch-disconnector
- 5 Pressure relief device
- **6** Wiring duct, removable, for protection cables and/or bus wires
- 7 Switchgear vessel, filled with gas
- **8** Operating mechanism of three-position switch
- **9** Bushing for cable plug with bolted contact (M16)
- 10 Cable compartment cover
- **11** Earthing busbar with earthing connection (design option)
- 12 HV HRC fuse assembly
- 13 Bushing for cable plug with plug-in contact, optionally bolted contact (M16)
- 14 Option: SIPRROTEC bay controller
- 15 Vacuum circuit-breaker
- 16 Circuit-breaker operating mechanism
- 17 SIBushing

#### Circuit-breaker feeder



- 1 Control board
- Low-voltage compartment (standard) 2
- Busbar arrangement
- Vacuum circuit-breaker
- Pressure relief device
- 6 Wiring duct, removable, for protection cables and/or bus wires
- 7 Switchgear vessel, filled with gas
- 8 Operating mechanism of switching device
- Operating mechanism of three-position switch
- 10 Bushing for cable plug with bolted contact (M16)
- 11 Cable compartment cover
- 12 Earthing busbar with earthing connection (design option)
- 13 Option: SIPROTEC bay controller
- 14 Option: Plug-in voltage transformer 4MT3 on the busbar
- 15 Bushing for connection of plug-in voltage transformers
- **16** SIBushing

#### Billing metering panel



Connection: cable – cable

- 1 Voltage transformer type 4MR
- 2 Current transformer type 4MA7
- Wiring duct, removable, for protection cables and/or bus wires
- 4 Niche for customer-side low-voltage equipment, screwed cover
- 5 Instrument transformer compartment cover
- 6 Cable connection
- Earthing busbar with earthing connection

# Design

Outdoor enclosure

#### **Outdoor enclosure**

On request, 8DJH 24 switchgear can be provided with an outdoor enclosure with the following features:

- For outdoor applications on company grounds
- Enclosure attached to standard indoor panels
- Enclosure for 1400 mm switchgear height (optionally with low-voltage compartment as a 200 mm or 400 mm high version)
- Enclosure with four different widths for freely configurable, non-extendable switchgear rows up to a switchgear width of 2200 mm
- Internal arc classification IAC A FL or FLR to 21 kA/1 s according to IEC 62271-200
- Degree of protection IP54.



Outdoor enclosure (front open)



Outdoor enclosure (front closed)

#### **Features**

- Busbar extension possible on all individual panels and panel blocks (ordering option)
- Plug-in unit consisting of contact coupling and screened silicone coupling
- Insensitive to pollution and condensation
- Switchgear installation, extension, or panel replacement without gas work.


Every panel block and every individual panel is optionally available with busbar extension on the right, on the left, or on both sides. This offers a high flexibility for the creation of switchgear configurations whose functional units can be lined up in any order. Local installation and lining up is done without gas work.

#### Lining up takes place as follows:


- By the busbar couplings on the medium-voltage side.
   Tolerances between adjacent panels are compensated by spherical fixed contacts and the movable contact coupling with degrees of freedom in all axis directions.
- By safe dielectric sealing with screened silicone couplings that are externally earthed and adjustable to tolerances.
   These silicone couplings are pressed on with a defined pressure when the panels are interconnected.
- On free busbar ends, screened dummy plugs are inserted, each of which is pressed on through a metal cover.
   A common protective cover with a warning is fixed over all three covers.
- By centering bolts for easier switchgear installation and fixing of adjacent panels.
- By bolted panel joints with defined stops for the distances between adjacent panels and the associated pressure for contact pieces and silicone couplings.

Switchgear installation, extension, or the replacement of one or more functional units requires a lateral wall distance ≥ 200 mm.

#### Interconnecting the panels



#### Surge-proof termination



- 1 Contact piece
- 2 Silicone coupling
- 3 Tension spring for earthing
- 4 Centering bolt
- 5 Silicone dummy plug with insertable sleeve
- 6 Clamping cover for dummy plugs
- 7 Busbar termination cover

Cable connection

#### **Features**

- Access to the cable compartment only if the feeder has been disconnected and earthed
- Bushings according to DIN EN 50181 with outside cone and bolted connection M16 as interface type C or plug-in contact as interface type A (for transformer feeders).

#### Connection of

- Thermoplastic-insulated cables (1- or 3-core cables) via cable elbow plug or cable T-plug
- Paper-insulated mass-impregnated cables via customary adapters.

#### Option

- Mounted cable clamps on cable bracket
- Connection of two 1-core cables per phase
- Deep cable compartment cover for a larger available mounting depth (possibly required depending on the plug or arrester combinations).

#### Cable plugs

- Numerous cable plug types from different manufacturers can be used
- Screened cable plugs (with conductive, earthed layer) particularly suitable, even in harsh ambient conditions (e.g. pollution, humidity, high site altitude).


#### Surge arresters

- Connected directly at the cable T-plug
- Compatible arrester types from the cable manufacturers' product range can be used
- · Surge arresters recommended if, at the same time,
  - the cable system is directly connected to the overhead line,
  - the protection zone of the surge arrester at the end tower of the overhead line does not cover the switchgear.


#### **Surge limiters**

- · Connected directly at the cable T-plug
- Suitable cable plug / limiter combinations on request
- Surge limiters recommended when motors with starting currents < 600 A are connected.


#### Cable compartment







Panel width 450 mm




Panel width 550 mm

#### Switchgear height without low-voltage compartment 1)


			<u> </u>
	1200	1400	1400
		without absorber base frame	with absorber base frame
			or 1700
A, B, C	375	575	875
, ,, ,, ,	373	373	07.5

<sup>1)</sup> Option: With low-voltage compartment


#### **Connection options**




Single cable (type A)



Single cable (type C)



Double cable (type C)



1 Cable T-plug

2 Cable elbow plug

3 Surge arrester

4 Coupling T-plug

### Current transformers according to IEC/EN 61869-1 and -2







Туре	Cable-type current transformer 4MC7033	Three-phase current transformer 4MC63 (3-pole)	Block-type current transformer 4MA7 (1-pole)
Features	Ring-core current transformer Inductive type Enclosure free of dielectric stress Insulation class E Secondary connection by means of cast-in was a secondary connection.	vires	Dimensions according to DIN 42600-8 (narrow design) Inductive type Cast-resin insulated Insulation class E Secondary connection by means of screw-type terminals
Installation	As current transformer at the feeder: Below the switchgear vessel, on current transformer mounting plates in the cable compartment, around the cables Installation on the cables on site  Note: Depending on the design option of the panel and the overall height of the current transformer, the current transformers may protrude from the cable compartment downwards	As current transformer at the feeder (for a panel width 550 mm): Below the switchgear vessel, around the feeder bushings in the cable compartment     Factory-assembled	<ul> <li>In the air-insulated metering panel</li> <li>Factory-assembled</li> <li>Option: Installation on site</li> </ul>

### Voltage transformers according to IEC/EN 61869-1 and -3







Туре	4MT3 and 4MT8 (1-pole)	4MR (1-pole or 2-pole)
Features	Plug-in voltage transformer for outside-cone bushing type A Inductive type Enclosure metal-coated or metal-enclosed (option) and earthed Insulation class E Secondary connection by means of system plug	<ul> <li>Dimensions according to DIN 42600-9 (narrow design)</li> <li>Inductive type</li> <li>Cast-resin insulated</li> <li>Insulation class E</li> <li>Secondary connection by means of screw-type terminals</li> </ul>
Installation	<ul> <li>As voltage transformer 4MT3 at the busbar: Above the switchgear vessel at separate outside-cone bushings, factory-assembled</li> <li>As voltage transformer 4MT8 at the feeder: Below the switchgear vessel, in the cable compartment on the symmetrical T-plug</li> </ul>	<ul> <li>In the air-insulated metering panel</li> <li>Factory-assembled</li> <li>Option: Installation on site</li> </ul>

Current sensors, voltage sensors

#### Current sensors (make Zelisko)

The current sensors are inductive current transformers whose secondary winding delivers a voltage signal through a precision shunt. At the rated primary current, this is 225 mV.

Depending on their version, the sensors have a dual accuracy class; the output signal can be equally used for measuring, protection and, if required, earth-fault detection. Suitable secondary devices with low-signal inputs can process the sensor signal directly.









Type Ring-core current sensor **SMCS-JW 1001** 

Ring-core current sensor SMCS/T-JW 1002, divisible Three-phase ring-core current sensor SMCS3-JW1004, optionally with integrated earth-fault detection sensor

Ring-core current sensor **GAE120/SENS-JW 1003** for earth-fault detection, divisible

Features

Example for available secondary devices that can be connected:

- SICAM FCM
- 7SJ81 (SIPROTEC Compact)
- 7SY82

Installation

- As current sensor at the feeder: Below the switchgear vessel, in the cable compartment. around the cables or cable plugs
- · Installation on the cables or cable plugs on site
- As current sensor at the feeder (particularly for retrofitting): Below the switchgear vessel, in the cable compartment, around the cables
- Installation on the cables on site
- As current sensor at the feeder (for a panel width of 350 mm): Below the switchgear vessel, around the feeder bushings in the cable compartment
- · Factory-assembled
- As summation current sensor at the feeder: Below the switchgear vessel, in the cable compartment, around the cables
- · Installation on the cables on site

#### Voltage sensors (make Zelisko)

The voltage sensors are resistor dividers that provide an output signal of 3.25 V/ $\sqrt{3}$  at the rated primary voltage. Suitable secondary devices with low-signal inputs can process the sensor signal directly.





#### Type

#### Voltage sensor SMVS-UW1001

Voltage sensor SMVS-UW1002

Features SICAM FCM

- Example for available secondary devices that can be connected:
- 7SJ81 (SIPROTEC Compact)
- 7SY82

Installation

- As voltage sensor at the feeder: Below the switchgear vessel, in the cable compartment, mounted on the cable plugs
- · Installation on the cable plugs on site
- Note: Voltage sensors of different design options can be selected, matching with the corresponding cable plug type

SIBushing

#### **SIBushing**

As an alternative to the conventional cable connection bushings, the bushing type SIBushing from Siemens is available for cable, ring-main and circuit-breaker feeders. It delivers current and voltage values in low-signal technology, as well as values for temperature measurement directly from the cable connection to modern protection devices and indicators.



Type C1 630 A

Туре		SIBushing
Panel types		K, R, L
Cable connection		Outside cone type C according to EN 50181, welded into the switchgear vessel
Voltage detecting and ind	icating systems	Connection for capacitive voltage detecting and indicating systems according to IEC 62271-213
Current measuring	Standard	IEC 61869-10
	Sensor principle	Rogowski coil
	Output signal	22.5 mV (at 50 A/50 Hz)
	Class	0.5
Voltage measuring	Standard	IEC 61869-11
	Sensor principle	Capacitive divider
	Ratio	10000/1
	Class	0.5
Temperature measuring	Sensor principle	Measuring resistor
	Resistor type	Pt100
Features		Examples for available secondary devices that can be connected:
		• SICAM FCM Plus (design option for SIBushing)
		• 7SY82

Low-voltage compartment, low-voltage niche

#### **Features**

- Separate selection possible for every panel (depending on the panel type and the extent of the secondary equipment)
- Available overall heights 200 mm, 400 mm and 600 mm
- Mounted on the panel. Installation/removal possible on site
- Customer-specific equipping with protection, control, measuring and metering devices
- Door with hinge on the left (standard for heights of 400 mm and 600 mm)
- Door powder-coated (same color as the switchgear front), with hinge on the left, optionally with hinge on the right, closure with rotary lock
  - Option: (for an overall height of 200 mm)
     Bolted front cover for narrow spaces, e.g. in substations without control aisle, powder-coated (same color as the switchgear front).

#### Low-voltage cables

- Control cables of the panel to the low-voltage compartment via multi-pole, coded module plug connectors
- Option: Plug-in bus wires from panel to panel in the separate wiring duct on the panel.

#### Low-voltage niche

- Integrated in the panel front of the billing metering panels type M
- · With bolted front cover
- For accommodation of options, e.g.:
  - Voltage transformer m.c.b.s
  - Small distribution fuse-box and fuse-links type DIAZED or NEOZED.

#### Wiring duct

- Metallic duct, mounted on the panel
- Overall height 60 mm
- For panel-overlapping wiring
- Can be selected for panels without low-voltage compartment.

#### Top cover

- Cover made of powder-coated sheet-metal (same color as the switchgear front), mounted on the panel
- Overall heights 200 mm, 400 mm or 600 mm
- For height adjustment of the panel front
- Can be selected for panels without low-voltage compartment.

#### Low-voltage compartment (design example)



Open low-voltage compartment with built-in equipment (option)

#### Low-voltage niche



Low-voltage niche of a billing metering panel type M, open cover

- 1 Low-voltage niche
- 2 Built-in equipment (option)

Room planning

#### **Switchgear installation**

#### Wall-standing arrangement

- 1 row
- 2 rows (for face-to-face arrangement)

Option: Free-standing arrangement.

#### Pressure relief


The type of pressure relief selected has an effect on the switchgear depth, and places requirements on the size of the cable basement and/or the room height. In case of pressure relief upwards, the room heights reproduced in the type test are decisive for the internal arc classification according to IEC 62271-200 (see table on page 33).


#### Switchgear extension or panel replacement

For switchgear extension or for panel replacement, a control aisle of at least 1000 mm is recommended in front of the switchgear. For panel replacement of lined up panels, there must be a wall distance of at least 200 mm on one side.

#### Control aisle


In front of the switchgear, a control aisle of at least 800 mm is required according to IEC 62271-200.







Room planning

### Switchgear height







Pressure relief


The following type-tested versions of the pressure relief system are available for 8DJH 24 switchgear:

- Downwards into the cable basement (for individual panels and panel blocks, internal arc classification up to IAC A FL 21 kA/1 s or IAC A FLR 21 kA/1 s, minimum cross-section of the cable basement according to the illustration below)
- Upwards through base frame and rear pressure relief duct (for individual panels and panel blocks, internal arc classification up to IAC A FL 21 kA/1 s and IAC A FLR 21 kA/1 s, minimum room heights according to the table on the right), with pressure absorber system.

# Room heights for switchgear installation with pressure relief duct at the rear

Switchgear	Room height
Without metering panel M	Switchgear height + 200 mm,
	at least 2300 mm
With metering panel M	Switchgear height + 200 mm,
	at least 2500 mm


# Switchgear installation with pressure relief downwards (standard)



Side view

- 1 Floor opening
- 2 Direction of pressure relief
- 3 Expanded metal (supplied by site)
- **4** Floor cover (divided plate for comfortable working at the cable connection)
- **5** Pressure absorber system with pressure relief duct

Switchgear installation with base frame and rear pressure relief duct (option) for switchgear with IAC A FL or FLR up to 21 kA/1 s



Side view

<sup>1)</sup> Total opening at least  $0.48\ m^2$ 


Pressure relief

For 8DJH 24 with outdoor enclosure (option), the direction of the pressure relief can be selected as follows:

- Downwards into the cable basement (internal arc classification up to IAC A FL or FLR 21 kA/1 s, minimum cross-section of the cable basement according to the illustration below)
- Upwards through rear pressure relief duct (internal arc classification up to IAC A FL or FLR 21 kA/1 s, free space above the switchgear 1000 mm as a minimum).


The dimensions for wall distances, control aisles, and cable basements correspond to those of the 8DJH 24 standard design. The outdoor enclosure is conceived for application on company grounds.

# Switchgear installation for outdoor enclosure with pressure relief downwards



- 1 Floor opening
- 2 Direction of pressure relief
- **3** Expanded metal (supplied by site)
- **4** Floor cover (divided plate for comfortable working at the cable connection)
- **5** Pressure absorber system with pressure relief duct


# Switchgear installation for outdoor enclosure with pressure relief upwards through rear duct



Side view

Jide view

1) Total opening at least 0.48 m<sup>2</sup>



Smart Infrastructure combines the real and digital worlds across energy systems, buildings and industries, enhancing the way people live and work and significantly improving efficiency and sustainability.

We work together with customers and partners to create an ecosystem that both intuitively responds to the needs of people and helps customers achieve their business goals.

It helps our customers to thrive, communities to progress and supports sustainable development to protect our planet for the next generation.

#### siemens.com/smart-infrastructure

Mediumvoltage systems



#### Published by Siemens AG

Smart Infrastructure Electrification & Automation Mozartstraße 31 C 91052 Erlangen, Germany

For further information, please contact our Customer Support Center: Phone: +49 180 524 70 00

Phone: +49 180 524 70 00 Fax +49 180 524 24 71

E-mail: support.energy@siemens.com siemens.com/medium-voltage-switchgear

Article no. SIEA-C10158-00-7600 VO 238296 en KG 03.24 0.0

# For the U.S. published by Siemens Industry Inc.

3617 Parkway Lane Peachtree Corners, GA 30092 United States

#### Status 03/2024

Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.

All product designations may be trademarks or product names of Siemens AG or other companies whose use by third parties for their own purposes could violate the rights of the owners.