



Version
1.0.6

PRODUCT INFORMATION

Sitras SCD-C – Compact short-circuiting device as voltage limiter

for DC traction power supply

[siemens.com/rail-electrification](https://www.siemens.com/rail-electrification)

SIEMENS

In DC traction systems, impermissible touch voltages may occur between the return circuit and the structure earth due to operational and short-circuit currents. The persistence of these voltages must be prevented by means of a voltage-limiting device in accordance with IEC 62128-1 / EN 50122-1.

The Sitras SCD-C reduces excessively high voltages by reliably short-circuiting the return circuit and structure earth temporarily. Furthermore, the formation of stray currents is minimized by automatic opening of the short-circuiting device.

Features

- High protection for persons – rapid response time fulfills EN 50122-1 over the entire time range down to 20 ms
- Operational safety and reliability verified by type testing in accordance with EN 50526-2
- Economic due to demand-oriented design and very high degree of standardization
- Very small space requirement due to compact design and wall mounting
- Earthquake tested version available

Application

Protection against personal injury

Impermissible touch voltages are prevented

Monitoring of the potential of the return circuit

Earth faults in the contact line are detected and so clearing by feeder substations is enabled

Design / Main components

The metal cabinet for indoor wall installation contains the following main components:

- DC contactor (NC contact) with very short response time and high short-circuit making capacity
- Measuring circuits for voltage and current with analog meters
- Control electronics with extremely fast detection of overvoltages

The external cables are brought into the cabinet through cable bushings in the floor of the cabinet.



Sitras SCD-C Design

Function

“Active” mode

In its basic state, the main contact of the DC contactor is open. The voltage between the return circuit and the equipotential bonding busbar is measured and the voltage (instantaneous value) is evaluated. If the tripping voltage set in the control electronics is exceeded, the DC contactor closes. The limit can be altered by means of plug-in jumpers in the control electronics.

Sitras SCD-C opens automatically if the current flowing through the DC contactor falls below the set maximum switching current for the set minimum closing time.

“Inactive” mode


If required, Sitras SCD-C can short-circuit both potentials without causing the contacts of the contactor to open automatically. This function can be used during maintenance work. The contacts of the contactor only open after the system has changed back to “active” mode.

Commands and messages

The short-circuiting device is intended for local operator control and monitoring as well as for link-up to a remote system.

Commands

Activate	Contactor opened
---	Contactor closed
Deactivate	Inactive (only locally)
Quit fault	Fault



Block diagram of Sitras SCD-C

Failure of the supply voltage

Sitras SCD-C works according to the closed-circuit principle. This ensures that the return circuit and the equipotential bonding busbar are short-circuited automatically if the supply voltage fails and that the system is therefore safe for persons.

Technical data

Sitras SCD-C		
Maximum system voltage U_n	[V]	1500
Rated current	[A]	800
Rated short-time current 250 ms ($I_{Ncw} = \hat{I}_{Ncw}$)	[kA]	21.8
Tripping voltage $U_{>}$ (default value)	[V]	120 / 95 / 85 / 70 / 60 / 35 (85)
Supply voltage	[V AC]	230
Mechanical lifespan	[switching operations]	150.000
Dimensions (H x B x T)	[mm]	1000 x 500 x 400
Color		RAL 7047
Degree of protection		IP40
Weight	[kg]	75

**Published by
Siemens Mobility GmbH**

Otto-Hahn-Ring 6
81739 Munich
Germany

For more information please contact:

Siemens Mobility GmbH
Rail Infrastructure
Electrification
Siemenspromenade 6
91058 Erlangen
Germany

**electrification.mobility@siemens.com
[siemens.com/rail-electrification](https://www.siemens.com/rail-electrification)**

Sitras SCD-C | Product Information
No. A6Z00007282884 | Version 1.0.6

© Siemens 2018 – 2025

**For the U.S. published by
Siemens Mobility, Inc.**

One Penn Plaza
New York City
10119
United States

Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.

All product designations may be trademarks or product names of Siemens AG, Siemens Mobility GmbH or other companies whose use by third parties for their own purposes could violate the rights of the owners.

Security information

In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial security concept. Siemens' products and solutions constitute one element of such a concept.

For more information about industrial security, please visit: [siemens.com/industrialsecurity](https://www.siemens.com/industrialsecurity).