

Connect Box – Compatibility

Check compatibility with your equipment. Connect it to a reliable, scalable and secure infrastructure.

Quickly verify if the equipment you are looking to connect is compatible with the Connect Box service. As of this moment, more than 580 devices are available to connect.

MODEL	PROTOCOL(S)	STATUS
Abb - b21	Modbus IP,Modbus Serial	Compatible
Abb - b23	Modbus Serial	Compatible
Abb - b24	Modbus Serial	Compatible
Adeunis - ARF8123AA - FIELD TEST DEVICE	LoRaWAN v1.0	Compatible
Adeunis - arf8170ba - dry contacts	LoRaWAN v1.0	Compatible
Adeunis - ARF8170BA-B02 - DOUBLE LEVEL	LoRaWAN v1.0	Compatible
Adeunis - ARF8170BA-B03 WATERLEAK CABLE	LoRaWAN v1.0	Compatible
Adeunis - ARF8170BA-B04 - WATERLEAK SPOT	LoRaWAN v1.0	Compatible
Adeunis - arf8180bca - temp - codec temp	LoRaWAN v1.0	Compatible
Adeunis - ARF8180BCA - TEMP - Codec Temp v3	LoRaWAN v1.0	Compatible
Adeunis - arf8180bca - temp - codec temp v4	LoRaWAN v1.0	Compatible
Adeunis - ARF8190BA - ANALOG	LoRaWAN v1.0	Compatible
Adeunis - ARF8230ABA - PULSE	LoRaWAN v1.0	Compatible
Adeunis - arf8230fa - pulse atex	LoRaWAN v1.0	Compatible
Adeunis - ARF8240AA - MODBUS	LoRaWAN v1.0	Compatible
Adeunis - ARF8250AA - TIC	LoRaWAN v1.0	Compatible
Adeunis - arf8275a - comfort	LoRaWAN v1.0	Compatible
Adeunis - arf8276a - motion	LoRaWAN v1.0	Compatible
Adeunis - arf8283aa - delta p	LoRaWAN v1.0	Compatible
Adeunis - ARF8373AA - Comfort CO2	LoRaWAN v1.0	Compatible
Adeunis - breath	LoRaWAN v1.0	Compatible
Adnexo - ax_dist	LoRaWAN v1.0	Compatible

Adnexo - ax_opto	LoRaWAN v1.0	Compatible
Advantech - wise2410	LoRaWAN v1.0	Compatible
Advantech - wise4610_s614	LoRaWAN v1.0	Compatible
Aermec - nrk	Modbus Serial	Compatible
Aermec - nrl	Modbus Serial	Compatible
Aldes - easyvec	Modbus Serial	Compatible
Aldes - inspirair	Modbus Serial	Compatible
Algodue - UPM209	Modbus IP,Modbus Serial	Compatible
Ambisense - ambiair_co2_04	LoRaWAN v1.0	Compatible
Antarc automation - tic master - 30.14 <= fw < 41.00 - pme pmi	Modbus IP,Modbus Serial	Compatible
Antarc automation - tic master - fw >41.00 - pme pmi	Modbus IP,Modbus Serial	Compatible
Antarc Automation - ticmaster - Compteur Bleu	Modbus IP,Modbus Serial	Compatible
Antarc Automation - ticmaster - Compteur Linky	Modbus IP,Modbus Serial	Compatible
Antarc Automation - ticmaster - Compteur PME-PMI	Modbus IP,Modbus Serial	Compatible
Antarc Automation - ticmaster - Compteur Saphir	Modbus IP,Modbus Serial	Compatible
Antarc Automation - ticmaster - Compteur Vert-ICE	Modbus IP,Modbus Serial	Compatible
Atim - acw_dind	LoRaWAN v1.0	Compatible
Atim - acw_thx	LoRaWAN v1.0	Compatible
Atim - ACW-mrx	LoRaWAN v1.0	Compatible
Atim - ACW-TH-O	LoRaWAN v1.0	Compatible
Atim - ACW-tmxd	LoRaWAN v1.0	Compatible
Atlantic - CONDENSECO	Modbus Serial	Compatible
Atlantic - condensinox	Modbus Serial	Compatible
Atlantic - LR	Modbus Serial	Compatible
Atlantic - LRK	Modbus Serial	Compatible
Atlantic - LRP NT PLUS	Modbus Serial	Compatible
Atlantic - LRR	Modbus Serial	Compatible
Atlantic - navistem b3000	Modbus Serial,LPB	Compatible
Atlantic - rotatech	Modbus Serial	Compatible
Atlantic - rubis - w 2000	Modbus Serial	Compatible
Atlantic - rubis/rubis flex - w 3000	Modbus Serial	Compatible
Atlantic - varblock	Modbus Serial	Compatible
Atlantic - varfree	Modbus Serial	Compatible

Atlantic - varino	Modbus Serial	Compatible
Atlantic - varino grande	Modbus Serial	Compatible
Atlantic - varmax	Modbus Serial	Compatible
Atlantic - varmax twin	Modbus Serial	Compatible
Awair - omni	LoRaWAN v1.0	Compatible
Axioma - qalcosonic_e3	LoRaWAN v1.0	Compatible
Axioma - qalcosonic_e4	LoRaWAN v1.0	Compatible
Axioma - qalcosonic_w1	LoRaWAN v1.0	Compatible
Babcock wanson - mae	Modbus IP	Compatible
Baelz - 6200i	Modbus IP,Modbus Serial	Compatible
Baranidesign - meteo_helix	LoRaWAN v1.0	Compatible
Baranidesign - meteo_rain	LoRaWAN v1.0	Compatible
Baranidesign - meteo_wind	LoRaWAN v1.0	Compatible
Baranidesign - meteo_wind2022	LoRaWAN v1.0	Compatible
Beijing Huakong Xingye Technology Development Co., Ltd - HSTL-10X series	Modbus Serial	Compatible
Besa - vega smart mc0101	LoRaWAN v1.0	Compatible
Bmeter - gsd8_rfm	LoRaWAN v1.0	Compatible
Bosch - Parking lot	LoRaWAN v1.0	Compatible
Calec - st ii	Modbus Serial	Compatible
Carlos gavazzi - em24_e1	Modbus IP	Compatible
Carlos gavazzi - energy management - energy analyzer - type em210	Modbus Serial	Compatible
Chauvin arnoux - ulys md-45 -m	Modbus Serial	Compatible
Chino_int - aeashwaqx	LoRaWAN v1.0	Compatible
Ciat - aquaciat caleo	Modbus Serial	Compatible
Ciat - ild	Modbus Serial	Compatible
Ciat - ildc	Modbus Serial	Compatible
Ciat - ildh	Modbus Serial	Compatible
Ciat - ld	Modbus Serial	Compatible
Ciat - ldc	Modbus Serial	Compatible
Ciat - ldh	Modbus Serial	Compatible
Ciat - lx	Modbus Serial	Compatible
Ciat - lxc	Modbus Serial	Compatible

Ciat - lxx	Modbus Serial	Compatible
Cicicom - parking_sensor_slg	LoRaWAN v1.0	Compatible
Daikin - dayn	Modbus Serial	Compatible
Danfoss - FC102	Modbus Serial	Compatible
Danfoss - MCX	Modbus Serial	Compatible
De Dietrich - Diematic m-Delta	Modbus Serial	Compatible
De dietrich - diematic m3/ 3/ 4	Modbus Serial	Compatible
De Dietrich - isystem	Modbus Serial	Compatible
Decentlab - dl_iam	LoRaWAN v1.0	Compatible
Decentlab - dl_mbx	LoRaWAN v1.0	Compatible
Decentlab - dl_ntu	LoRaWAN v1.0	Compatible
Decentlab - dl_pr26	LoRaWAN v1.0	Compatible
Delta ohm - lpphot01s	Modbus Serial	Compatible
Delta ohm - lppyra03s	Modbus Serial	Compatible
Dentt - powerscout 12 HD	Modbus IP,Modbus Serial	Compatible
Deos - sam	LoRaWAN v1.0	Compatible
Deos - teo	LoRaWAN v1.0	Compatible
Diehl - sharky 775 (armatec)	Modbus Serial,MBUS	Compatible
Dragino - cpl01	LoRaWAN v1.0	Compatible
Dragino - laq4	LoRaWAN v1.0	Compatible
Dragino - lbt1	LoRaWAN v1.0	Compatible
Dragino - ldds45	LoRaWAN v1.0	Compatible
Dragino - ldds75	LoRaWAN v1.0	Compatible
Dragino - lds	LoRaWAN v1.0	Compatible
Dragino - LDS03A - Outdoor lorawan Open/Close Door Sensor	LoRaWAN v1.0	Compatible
Dragino - lgt92	LoRaWAN v1.0	Compatible
Dragino - lht52	LoRaWAN v1.0	Compatible
Dragino - LHT65-Temperature and Humidity	LoRaWAN v1.0	Compatible
Dragino - llds12	LoRaWAN v1.0	Compatible
Dragino - lse01	LoRaWAN v1.0	Compatible
Dragino - lsn50	LoRaWAN v1.0	Compatible
Dragino - lt22222	LoRaWAN v1.0	Compatible
Dragino - lt33222	LoRaWAN v1.0	Compatible

Dragino - lwl	LoRaWAN v1.0	Compatible
Dragino - lwl03a	LoRaWAN v1.0	Compatible
Dss - ranos_db	LoRaWAN v1.0	Compatible
Eco-adapt - power-elec 3	Modbus IP,LoRaWAN v1.0	Compatible
Eco-adapt - power-elec 6	Modbus IP,LoRaWAN v1.0	Compatible
Elsys - ELT 2 HP	LoRaWAN v1.0	Compatible
Elsys - elt_lite	LoRaWAN v1.0	Compatible
Elsys - ems	LoRaWAN v1.0	Compatible
Elsys - ems_desk	LoRaWAN v1.0	Compatible
Elsys - ems_door	LoRaWAN v1.0	Compatible
Elsys - ems_lite	LoRaWAN v1.0	Compatible
Elsys - ERS	LoRaWAN v1.0	Compatible
Elsys - ers desk	LoRaWAN v1.0	Compatible
Elsys - ers_co2 lite	LoRaWAN v1.0	Compatible
Elsys - ers_eye	LoRaWAN v1.0	Compatible
Elsys - ers_voc	LoRaWAN v1.0	Compatible
Elsys - ERS-CO2	LoRaWAN v1.0	Compatible
Elsys - ERS-lite	LoRaWAN v1.0	Compatible
Elsys - ERS-sound	LoRaWAN v1.0	Compatible
Elvaco - cmi4110	LoRaWAN v1.0	Compatible
Elvaco - cmi4130	LoRaWAN v1.0	Compatible
Elvaco - cmi4140	LoRaWAN v1.0	Compatible
Elvaco - cmi4160	LoRaWAN v1.0	Compatible
Emu - professional2	LoRaWAN v1.0	Compatible
Enerbee - e_vav	LoRaWAN v1.0	Compatible
Enless - TX 600-021	LoRaWAN v1.0	Compatible
Enless - TX 600-022	LoRaWAN v1.0	Compatible
Enless - TX 600-024	LoRaWAN v1.0	Compatible
Enless - TX 600-031	LoRaWAN v1.0	Compatible
Enless - TX 600-032	LoRaWAN v1.0	Compatible
Enless - TX 600-033	LoRaWAN v1.0	Compatible
Enless - TX 600-034	LoRaWAN v1.0	Compatible
Enless - TX 600-035	LoRaWAN v1.0	Compatible
Enless - TX 600-037	LoRaWAN v1.0	Compatible

Enless - TX 600-039	LoRaWAN v1.0	Compatible
Enless - TX 600-232	LoRaWAN v1.0	Compatible
Enless - TX 600-233	LoRaWAN v1.0	Compatible
Enless - TX CO2 / VOC / T&H AMB 600-023	LoRaWAN v1.0	Compatible
Enless - TX PULSE 600-036	LoRaWAN v1.0	Compatible
Enless - TX PULSE LED 600-038	LoRaWAN v1.0	Compatible
Ethera - nemo_outdoor	LoRaWAN v1.0	Compatible
Ethera - nemo_xt	LoRaWAN v1.0	Compatible
Ewattch - ambiance	LoRaWAN v1.0	Compatible
Ewattch - ambiance-co2	LoRaWAN v1.0	Compatible
Ewattch - squid	LoRaWAN v1.0	Compatible
Ewattch - tyness_energy_tic_emeraude	LoRaWAN v1.0	Compatible
Ewattch - tyness_modular	LoRaWAN v1.0	Compatible
Ewattch - tyness-energy	LoRaWAN v1.0	Compatible
Fludia - fm432e	LoRaWAN v1.0	Compatible
Fludia - fm432g	LoRaWAN v1.0	Compatible
Fludia - fm432p	LoRaWAN v1.0	Compatible
France AIR - WALLPLAY 95 T4500 CO	Modbus IP,Modbus Serial	Compatible
Grundfos - MAGNA3-D, twin-head pump	Modbus Serial	Compatible
Hitachi - csnet manager 2	Modbus IP	Compatible
Honeywell - C7355A room IAQ monitor	Modbus Serial	Compatible
Honeywell - EEM230-D-M	MBUS	Compatible
Hoval - ultragas	Modbus IP,Modbus Serial	Compatible
Imbuildings - comfort	LoRaWAN v1.0	Compatible
Imbuildings - moodbox	LoRaWAN v1.0	Compatible
Imbuildings - people_counter	LoRaWAN v1.0	Compatible
Ime - conto d2 mid	Modbus Serial	Compatible
Ime - conto d4 pd mid	Modbus Serial	Compatible
Imi-hydronic - Compresso C200.6 (braincube)	Modbus IP	Compatible
Ineo_sense - acs_padlock	LoRaWAN v1.0	Compatible
Ineo_sense - acs_switch	LoRaWAN v1.0	Compatible
Integra - aquastream	LoRaWAN v1.0	Compatible
Integra - calec_st3	LoRaWAN v1.0	Compatible
Integra - rubin_sonic	LoRaWAN v1.0	Compatible

Integra - sonic_topas	LoRaWAN v1.0	Compatible
lotsens - iotsens_dsn00xx	LoRaWAN v1.0	Compatible
Isma - 4i4o-h	Modbus Serial	Compatible
Isma - 4i4o-h-ip	Modbus IP,Modbus Serial	Compatible
Isma - 4o-h	Modbus Serial	Compatible
Isma - 4o-h-ip	Modbus IP,Modbus Serial	Compatible
Isma - 4to-h	Modbus Serial	Compatible
Isma - 4to-h-ip	Modbus IP,Modbus Serial	Compatible
Isma - 4u4a-h	Modbus Serial	Compatible
Isma - 4u4a-h-ip	Modbus IP,Modbus Serial	Compatible
Isma - 4u4o-h	Modbus Serial	Compatible
Isma - 4u4o-h-ip	Modbus IP,Modbus Serial	Compatible
Isma - 8i	Modbus Serial	Compatible
Isma - 8i-ip	Modbus IP,Modbus Serial	Compatible
Isma - 8u	Modbus Serial	Compatible
Isma - 8u-ip	Modbus IP,Modbus Serial	Compatible
Isma - mix18	Modbus Serial	Compatible
Isma - mix18-ip	Modbus IP,Modbus Serial	Compatible
Isma - mix38	Modbus Serial	Compatible
Isma - mix38-ip	Modbus IP,Modbus Serial	Compatible
ltron - cf echo2	Modbus Serial,MBUS	Compatible
ltron - CF51	Modbus Serial,MBUS	Compatible
ltron - CF55	Modbus Serial	Compatible
ltron - CF55x	MBUS	Compatible
ltron - CF800	MBUS	Compatible
ltron - CF88	Modbus Serial	Compatible
ltron - ultramax	MBUS	Compatible
Janitza - UMG 96 RM-E	Modbus Serial	Compatible
Komfovent - DOMEKT (Unit controller: C6)	Modbus Serial	Compatible
Legrand - 412074	Modbus Serial	Compatible
Legrand - 412075	Modbus Serial	Compatible
Legrand - 412093	Modbus Serial	Compatible
Lennox - FCA 85	Modbus Serial	Compatible
Lennox - flexy	Modbus Serial	Compatible

Mcf88 - mcf_lw12met	LoRaWAN v1.0	Compatible
Mcf88 - mcf_lw12plg	LoRaWAN v1.0	Compatible
Mcf88 - mcf_lw13io	LoRaWAN v1.0	Compatible
Mcf88 - mcf_lw13mio	LoRaWAN v1.0	Compatible
Mcf88 - mcf_lwws01	LoRaWAN v1.0	Compatible
Mclimate - co2	LoRaWAN v1.0	Compatible
Mclimate - ht	LoRaWAN v1.0	Compatible
Mclimate - t_valve	LoRaWAN v1.0	Compatible
Mclimate - vicki	LoRaWAN v1.0	Compatible
Micronics - U1000MKII	Modbus Serial	Compatible
Micropelt - mlr_003	LoRaWAN v1.0	Compatible
Milesight - am103	LoRaWAN v1.0	Compatible
Milesight - am104	LoRaWAN v1.0	Compatible
Milesight - am107	LoRaWAN v1.0	Compatible
Milesight - am307	LoRaWAN v1.0	Compatible
Milesight - am319	LoRaWAN v1.0	Compatible
Milesight - em300_di	LoRaWAN v1.0	Compatible
Milesight - em300_mcs	LoRaWAN v1.0	Compatible
Milesight - em300_sld	LoRaWAN v1.0	Compatible
Milesight - em300_th	LoRaWAN v1.0	Compatible
Milesight - EM300-ZLD	LoRaWAN v1.0	Compatible
Milesight - em310_tilt	LoRaWAN v1.0	Compatible
Milesight - em310_udl	LoRaWAN v1.0	Compatible
Milesight - em320_th	LoRaWAN v1.0	Compatible
Milesight - em500_co2	LoRaWAN v1.0	Compatible
Milesight - em500_lgt	LoRaWAN v1.0	Compatible
Milesight - em500_pp	LoRaWAN v1.0	Compatible
Milesight - em500_pt100	LoRaWAN v1.0	Compatible
Milesight - em500_smtc	LoRaWAN v1.0	Compatible
Milesight - em500_swl	LoRaWAN v1.0	Compatible
Milesight - em500_udl	LoRaWAN v1.0	Compatible
Milesight - gs101	LoRaWAN v1.0	Compatible
Milesight - uc100	LoRaWAN v1.0	Compatible
Milesight - UC1114	LoRaWAN v1.0	Compatible

Milesight - UC1122	LoRaWAN v1.0	Compatible
Milesight - uc1152	LoRaWAN v1.0	Compatible
Milesight - uc300	LoRaWAN v1.0	Compatible
Milesight - uc500	LoRaWAN v1.0	Compatible
Milesight - uc51x	LoRaWAN v1.0	Compatible
Milesight - vs121	LoRaWAN v1.0	Compatible
Milesight - vs132	LoRaWAN v1.0	Compatible
Milesight - ws101	LoRaWAN v1.0	Compatible
Milesight - ws136	LoRaWAN v1.0	Compatible
Milesight - ws156	LoRaWAN v1.0	Compatible
Milesight - ws202	LoRaWAN v1.0	Compatible
Milesight - ws301	LoRaWAN v1.0	Compatible
Milesight - ws302	LoRaWAN v1.0	Compatible
Milesight - ws50x	LoRaWAN v1.0	Compatible
Milesight - ws52x	LoRaWAN v1.0	Compatible
Milesight - ws558	LoRaWAN v1.0	Compatible
Milesight - wts305	LoRaWAN v1.0	Compatible
Milesight - wts505	LoRaWAN v1.0	Compatible
Milesight - wts506	LoRaWAN v1.0	Compatible
Miro - click	LoRaWAN v1.0	Compatible
Mta - hoct	Modbus Serial	Compatible
Nanosense - aaq	LoRaWAN v1.0	Compatible
Nanosense - e4000ng	LoRaWAN v1.0	Compatible
Nanosense - qaa	LoRaWAN v1.0	Compatible
Netvox - R311A	LoRaWAN v1.0	Compatible
Netvox - R311W	LoRaWAN v1.0	Compatible
Netvox - r711	LoRaWAN v1.0	Compatible
Netvox - R718AB	LoRaWAN v1.0	Compatible
Netvox - r718ad	LoRaWAN v1.0	Compatible
Netvox - r718ck	LoRaWAN v1.0	Compatible
Netvox - r718ck2	LoRaWAN v1.0	Compatible
Netvox - r718cr	LoRaWAN v1.0	Compatible
Netvox - r718cr2	LoRaWAN v1.0	Compatible
Netvox - r718ct	LoRaWAN v1.0	Compatible

Netvox - r718ct2	LoRaWAN v1.0	Compatible
Netvox - r718db	LoRaWAN v1.0	Compatible
Netvox - r718e	LoRaWAN v1.0	Compatible
Netvox - R718F	LoRaWAN v1.0	Compatible
Netvox - R718G	LoRaWAN v1.0	Compatible
Netvox - r718h	LoRaWAN v1.0	Compatible
Netvox - r718j	LoRaWAN v1.0	Compatible
Netvox - r718j2	LoRaWAN v1.0	Compatible
Netvox - R718MA	LoRaWAN v1.0	Compatible
Netvox - R718N1	LoRaWAN v1.0	Compatible
Netvox - R718N17	LoRaWAN v1.0	Compatible
Netvox - R718n3	LoRaWAN v1.0	Compatible
Netvox - r718pa11	LoRaWAN v1.0	Compatible
Netvox - r718pa12	LoRaWAN v1.0	Compatible
Netvox - r718pa14	LoRaWAN v1.0	Compatible
Netvox - r718pa15	LoRaWAN v1.0	Compatible
Netvox - r718pa16	LoRaWAN v1.0	Compatible
Netvox - r718pa17	LoRaWAN v1.0	Compatible
Netvox - r718pa18	LoRaWAN v1.0	Compatible
Netvox - r718pa4	LoRaWAN v1.0	Compatible
Netvox - r718pa5	LoRaWAN v1.0	Compatible
Netvox - r718pa6	LoRaWAN v1.0	Compatible
Netvox - r718pa7	LoRaWAN v1.0	Compatible
Netvox - r718pa8	LoRaWAN v1.0	Compatible
Netvox - r718pa9	LoRaWAN v1.0	Compatible
Netvox - r726	LoRaWAN v1.0	Compatible
Netvox - R72615A	LoRaWAN v1.0	Compatible
Netvox - R72616A	LoRaWAN v1.0	Compatible
Netvox - RB1IE	LoRaWAN v1.0	Compatible
Nexelec - aero	LoRaWAN v1.0	Compatible
Nexelec - atmo	LoRaWAN v1.0	Compatible
Nexelec - Insafe carbon	LoRaWAN v1.0	Compatible
Nexelec - insafe origin	LoRaWAN v1.0	Compatible
Nexelec - Insafe pilot	LoRaWAN v1.0	Compatible

Nexelec - PMI	LoRaWAN v1.0	Compatible
Nexelec - sense	LoRaWAN v1.0	Compatible
Nke - bob_assistant	LoRaWAN v1.0	Compatible
Nke - flash o	LoRaWAN v1.0	Compatible
Nke - in_o	LoRaWAN v1.0	Compatible
Nke - indoor temperature	LoRaWAN v1.0	Compatible
NKE - Indoor Temperature and Humidity	LoRaWAN v1.0	Compatible
Nke - intens_o	LoRaWAN v1.0	Compatible
Nke - modbus_master	LoRaWAN v1.0	Compatible
NKE - Outdoor Temperature - ref : 50-70-164	LoRaWAN v1.0	Compatible
Nke - pilot_wire	LoRaWAN v1.0	Compatible
Nke - pulse sens'o	LoRaWAN v1.0	Compatible
Nke - remote_temp1	LoRaWAN v1.0	Compatible
Nke - remote_temp2	LoRaWAN v1.0	Compatible
Nke - smart_plug	LoRaWAN v1.0	Compatible
Nke - toran_o_atex	LoRaWAN v1.0	Compatible
Nke - triphas_o	LoRaWAN v1.0	Compatible
Nke - vaqa_o	LoRaWAN v1.0	Compatible
Nwave - parking	LoRaWAN v1.0	Compatible
Onesitu - OS110_CSM	LoRaWAN v1.0	Compatible
Oxobutton - oxobutton_q	LoRaWAN v1.0	Compatible
Parametric - PCR2	LoRaWAN v1.0	Compatible
Patlite - LA6-5DSNWB-POE	Modbus IP	Compatible
Plenom - busylight	LoRaWAN v1.0	Compatible
Polier - MM100LMOD	Modbus Serial	Compatible
Polier - MTR80LMOD	Modbus Serial	Compatible
Polysense - noise	LoRaWAN v1.0	Compatible
Produal - FLTA	Modbus Serial	Compatible
Produal - PDS 2-H	Modbus Serial	Compatible
Produal - PDS 2-V	Modbus Serial	Compatible
Produal - tex-m	Modbus Serial	Compatible
Radio bridge - door window	LoRaWAN v1.0	Compatible
Radio bridge - probless temperature	LoRaWAN v1.0	Compatible
Radio bridge - temperatura humidity	LoRaWAN v1.0	Compatible

Radio_bridge - dual_push_button	LoRaWAN v1.0	Compatible
Radio_bridge - single_push_button	LoRaWAN v1.0	Compatible
Rayleigh instruments - ri-d460	Modbus Serial	Compatible
Rayleigh instruments - ri-f384-g	Modbus Serial	Compatible
Robeau - water_monitoring	LoRaWAN v1.0	Compatible
Sakkarah - coffret multi	Modbus Serial	Compatible
Schneider - TRV00210	Modbus Serial	Compatible
Schneider Electric - A9MEM1520 - powertag A9 M63 - P 63A		Compatible
Schneider Electric - A9MEM1521 - powertag A9 M63 - IP+N 63A - amont	Modbus IP	Compatible
Schneider Electric - A9MEM1522 - powertag A9 M63 - IP+N 63A - aval	Modbus IP	Compatible
Schneider Electric - A9MEM1540 - powertag A9 M63 - IP+N 63A	Modbus IP	Compatible
Schneider Electric - A9MEM1541 - powertag A9 M63 - 3P+N 63A - amont	Modbus IP	Compatible
Schneider Electric - A9MEM1542 - powertag A9 M63 - 3P+N 63A - aval	Modbus IP	Compatible
Schneider Electric - A9MEM1560 - powertag A9 F63 - IP+N 63A	Modbus IP	Compatible
Schneider Electric - A9MEM1561 - powertag A9 P63 - IP+N 63A - amont	Modbus IP	Compatible
Schneider Electric - A9MEM1562 - powertag A9 P63 - IP+N 63A - aval	Modbus IP	Compatible
Schneider Electric - A9MEM1563 - powertag A9 P63 - IP+N 63A - aval	Modbus IP	Compatible
Schneider Electric - A9MEM1570 - powertag A9 F63 - 3P+N 63A	Modbus IP	Compatible
Schneider Electric - A9MEM1572 - powertag A9 P63 - 3P+N 63A - aval	Modbus IP	Compatible
Schneider Electric - A9MEM1573 - powertag A9 F63 - 3P+N 63A - amont/aval	Modbus IP	Compatible
Schneider Electric - A9MEM1580 - powertag F160 - 3P/3P+N	Modbus IP	Compatible
Schneider electric - aos	LoRaWAN v1.0	Compatible
Schneider electric - iaq	LoRaWAN v1.0	Compatible

Schneider electric - iem 3150	Modbus IP,Modbus Serial	Compatible
Schneider electric - iem 3155	Modbus Serial	Compatible
Schneider electric - iem 3250	Modbus Serial	Compatible
Schneider electric - iem 3255	Modbus Serial	Compatible
Schneider electric - iem 3350	Modbus Serial	Compatible
Schneider electric - iem 3355	Modbus Serial	Compatible
Schneider electric - iem 3455	Modbus Serial	Compatible
Schneider electric - iem 3555	Modbus Serial	Compatible
Schneider electric - pm3250	Modbus IP,Modbus Serial	Compatible
Schneider electric - pm51xx	Modbus Serial	Compatible
Schneider electric - pm9c	Modbus IP,Modbus Serial	Compatible
Schneider Electric - SMT10020 - heattag	Modbus IP	Compatible
Schneider electric - uniflair am cooling system	Modbus IP	Compatible
Sensitive - strip_comfort	LoRaWAN v1.0	Compatible
Sensitive - strip_drip	LoRaWAN v1.0	Compatible
Sensitive - strip_presence	LoRaWAN v1.0	Compatible
Sensitive - strips guard	LoRaWAN v1.0	Compatible
Sensgreen - sensnode	LoRaWAN v1.0	Compatible
Sensgreen - sensnode_v2	LoRaWAN v1.0	Compatible
Sensing_labs - 4MA-LAB-13NS/4MA-LAB-41NS	LoRaWAN v1.0	Compatible
Sensing_labs - PIR-LAB-41NS/PIR-LAB-13NS	LoRaWAN v1.0	Compatible
Sensing_labs - PTL-LAB-41NS	LoRaWAN v1.0	Compatible
Sensing_labs - PUL-LAB-13NS/PUL-LAB-13XS/PUL-LAB-41NS/LED-LAB-41NS	LoRaWAN v1.0	Compatible
Sensing_labs - THY-LAB-41NS/THY-LAB-14NS	LoRaWAN v1.0	Compatible
Sensing_labs - TOR-LAB-13NS/TOR-LAB-41NS/OPE-LAB-13NS/OPE-LAB-41NS/LEA-LAB-13NS	LoRaWAN v1.0	Compatible
Sensing-labs - tem-lab-41ns/tem-lab-13ns/tem-lab-14ns/tem-lab-24ns/tem-lab-44ns	LoRaWAN v1.0	Compatible
Sensing-labs - temp-lab-21ns	LoRaWAN v1.0	Compatible
Sensing-labs - thy-lab-61ns	LoRaWAN v1.0	Compatible
Sensus - sx_lw	LoRaWAN v1.0	Compatible
Siemens - 7KM PAC2200	Modbus IP,Modbus Serial	Compatible
Siemens - 7KM PAC3120	Modbus Serial	Compatible
Siemens - 7KM PAC3220	Modbus IP,Modbus Serial	Compatible

Siemens - 7KM PAC4200	Modbus IP	Compatible
Siemens - 7KM PAC5100/5200	Modbus IP	Compatible
Siemens - 7KT PAC1600 - 1 phase	Modbus Serial	Compatible
Siemens - 7KT PAC1600 - 3 phases 5A	Modbus Serial	Compatible
Siemens - 7KT PAC1600 - 3 phases 80A	Modbus Serial	Compatible
Siemens - 7kt1651 monophasé	Modbus Serial	Compatible
Siemens - GCA161.1E/MO	Modbus Serial	Compatible
Siemens - GDB111.1E/MO	Modbus Serial	Compatible
Siemens - GDB111.9E/MO	Modbus IP,Modbus Serial	Compatible
Siemens - GDB161.9E/MO	Modbus IP,Modbus Serial	Compatible
Siemens - GDB181.1E/MO	Modbus Serial	Compatible
Siemens - GEB161.1E/MO	Modbus Serial	Compatible
Siemens - GIB161.1E/MO	Modbus Serial	Compatible
Siemens - GLB111.1E/MO	Modbus Serial	Compatible
Siemens - GLB111.9E/MO	Modbus IP,Modbus Serial	Compatible
Siemens - GLB161.9E/MO	Modbus IP,Modbus Serial	Compatible
Siemens - GLB181.1E/MO	Modbus Serial	Compatible
Siemens - GLD161.9E/MO	Modbus IP,Modbus Serial	Compatible
Siemens - GMA161.1E/MO	Modbus Serial	Compatible
Siemens - GMA161.9E/MO	Modbus IP,Modbus Serial	Compatible
Siemens - iaq multi-sensor - qna2700d.ba1	LoRaWAN v1.0	Compatible
Siemens - QAE2154.010/MO	Modbus IP,Modbus Serial	Compatible
Siemens - QAM2151.040/MO	Modbus IP,Modbus Serial	Compatible
Siemens - qax903 - absences	KNX	Compatible
Siemens - qax903 - appartement	KNX	Compatible
Siemens - qax903 - défauts	KNX	Compatible
Siemens - qax903 - informations	KNX	Compatible
Siemens - qax903 - pièce 1	KNX	Compatible
Siemens - qax903 - pièce 10	KNX	Compatible
Siemens - qax903 - pièce 11	KNX	Compatible
Siemens - qax903 - pièce 12	KNX	Compatible
Siemens - qax903 - pièce 2	KNX	Compatible
Siemens - qax903 - pièce 3	KNX	Compatible
Siemens - qax903 - pièce 4	KNX	Compatible

Siemens - qax903 - pièce 5	KNX	Compatible
Siemens - qax903 - pièce 6	KNX	Compatible
Siemens - qax903 - pièce 7	KNX	Compatible
Siemens - qax903 - pièce 8	KNX	Compatible
Siemens - qax903 - pièce 9	KNX	Compatible
Siemens - QFA2050/MO	Modbus IP,Modbus Serial	Compatible
Siemens - QFA2050D/MO	Modbus IP,Modbus Serial	Compatible
Siemens - QFA3150/MO	Modbus IP,Modbus Serial	Compatible
Siemens - QFM2150/MO	Modbus IP,Modbus Serial	Compatible
Siemens - QFM3150/MO	Modbus IP,Modbus Serial	Compatible
Siemens - QMX.3P30	KNX	Compatible
Siemens - QMX3.P02	KNX	Compatible
Siemens - QMX3.P37	KNX	Compatible
Siemens - QMX3.P40	KNX	Compatible
Siemens - QMX3.P70	KNX	Compatible
Siemens - QMX3.P74	KNX	Compatible
Siemens - QPA2052/MO	Modbus IP,Modbus Serial	Compatible
Siemens - QPM2102/MO	Modbus IP,Modbus Serial	Compatible
Siemens - QPM2150/MO	Modbus IP,Modbus Serial	Compatible
Siemens - QPM2152/MO	Modbus IP,Modbus Serial	Compatible
Siemens - RVL470	LPB	Compatible
Siemens - RVL472 - Paramètre de base	LPB	Compatible
Siemens - RVL480	LPB	Compatible
Siemens - RVL482 - Paramètre de base	LPB	Compatible
Siemens - SAS61.03/MO	Modbus IP,Modbus Serial	Compatible
Siemens - SAS61.33/MO	Modbus IP,Modbus Serial	Compatible
Siemens - SAT61.008/MO	Modbus IP,Modbus Serial	Compatible
Siemens - SAT61.51/MO	Modbus IP,Modbus Serial	Compatible
Siemens - SAV61.00/MO	Modbus IP,Modbus Serial	Compatible
Siemens - SAV61P00/MO	Modbus IP,Modbus Serial	Compatible
Siemens - SAX61.03/MO	Modbus IP,Modbus Serial	Compatible
Siemens - SAX61P03/MO	Modbus IP,Modbus Serial	Compatible
Siemens - SAY61P03/MO	Modbus IP,Modbus Serial	Compatible
Siemens - SENTRON PAC3100	Modbus Serial	Compatible

Siemens - SKB62/MO	Modbus IP,Modbus Serial	Compatible
Siemens - SKC62/MO	Modbus IP,Modbus Serial	Compatible
Siemens - SKD62/MO	Modbus IP,Modbus Serial	Compatible
Siemens - synco - rmh760	KNX,KNX LTE	Compatible
Siemens - synco - rmh760b - chaudière	KNX,KNX LTE	Compatible
Siemens - synco - rmh760b - compteurs	KNX,KNX LTE	Compatible
Siemens - synco - rmh760b - défauts	KNX,KNX LTE	Compatible
Siemens - synco - rmh760b - divers	KNX,KNX LTE	Compatible
Siemens - synco - rmh760b - prérégulateur	KNX,KNX LTE	Compatible
Siemens - synco - rmh760b - régulateur principal	KNX,KNX LTE	Compatible
Siemens - synco - rmk770 - chaudière 1	KNX,KNX LTE	Compatible
Siemens - synco - rmk770 - chaudière 2	KNX,KNX LTE	Compatible
Siemens - synco - rmk770 - chaudière 3	KNX,KNX LTE	Compatible
Siemens - synco - rmk770 - chaudière 4	KNX,KNX LTE	Compatible
Siemens - synco - rmk770 - chaudière 5	KNX,KNX LTE	Compatible
Siemens - synco - rmk770 - chaudière 6	KNX,KNX LTE	Compatible
Siemens - Synco - RMK770 - Circuit de Chauffage	KNX,KNX LTE	Compatible
Siemens - synco - rmk770 - défauts	KNX,KNX LTE	Compatible
Siemens - synco - rmk770 - divers	KNX,KNX LTE	Compatible
Siemens - synco - rmk770 - pilote cascade chaudières	KNX,KNX LTE	Compatible
Siemens - synco - rmk770 - préregulateur	KNX,KNX LTE	Compatible
Siemens - synco - rmk770b - chaudière 1	KNX,KNX LTE	Compatible
Siemens - synco - rmk770b - chaudière 2	KNX,KNX LTE	Compatible
Siemens - synco - rmk770b - chaudière 3	KNX,KNX LTE	Compatible
Siemens - synco - rmk770b - chaudière 4	KNX,KNX LTE	Compatible
Siemens - synco - rmk770b - chaudière 5	KNX,KNX LTE	Compatible
Siemens - synco - rmk770b - chaudière 6	KNX,KNX LTE	Compatible
Siemens - Synco - RMK770B - Circuit de Chauffage	KNX,KNX LTE	Compatible
Siemens - synco - rmk770b - défauts	KNX,KNX LTE	Compatible
Siemens - synco - rmk770b - divers	KNX,KNX LTE	Compatible
Siemens - synco - rmk770b - pilote cascade chaudières	KNX,KNX LTE	Compatible
Siemens - synco - rmk770b - préregulateur	KNX,KNX LTE	Compatible

Siemens - synco - rms705	KNX,KNX LTE	Compatible
Siemens - synco - rmu710	KNX,KNX LTE	Compatible
Siemens - synco - rmu710b	KNX,KNX LTE	Compatible
Siemens - Synco - RMU720B - Réglage de base	KNX	Compatible
Siemens - UH50 Meter (WZU lorawan module)	LoRaWAN v1.0	Compatible
Smappee Infinity - energy meter	Modbus Serial	Compatible
Socomec - countis - e23	Modbus IP,Modbus Serial	Compatible
Socomec - countis - e43	Modbus Serial	Compatible
Socomec - digiware	Modbus IP	Compatible
Socomec - diris a20	Modbus IP,Modbus Serial	Compatible
Socomec - diris a40	Modbus IP,Modbus Serial	Compatible
Socomec - Diris Ap - Prise en compte des rapports de transformations courant et tension	Modbus IP,Modbus Serial	Compatible
Socomec - Diris Ap - Sans pris en compte des rapports de transformations courant et tension	Modbus IP,Modbus Serial	Compatible
Socomec - e53	Modbus Serial	Compatible
Sontay - RF-LW-CO2-S	LoRaWAN v1.0	Compatible
Sontay - RF-LW-RH-D	LoRaWAN v1.0	Compatible
Sontay - RF-LW-RH-O	LoRaWAN v1.0	Compatible
Sontay - RF-LW-RH-S	LoRaWAN v1.0	Compatible
Sontay - RF-LW-RH-W	LoRaWAN v1.0	Compatible
Sontay - RF-LW-RHT-CO2-D	LoRaWAN v1.0	Compatible
Sontay - RF-LW-RHT-CO2-S	LoRaWAN v1.0	Compatible
Sontay - RF-LW-T-555	LoRaWAN v1.0	Compatible
Sontay - RF-LW-T-C	LoRaWAN v1.0	Compatible
Sontay - RF-LW-T-D	LoRaWAN v1.0	Compatible
Sontay - RF-LW-T-I	LoRaWAN v1.0	Compatible
Sontay - RF-LW-T-O	LoRaWAN v1.0	Compatible
Sontay - RF-LW-T-OR	LoRaWAN v1.0	Compatible
Sontay - RF-LW-T-S	LoRaWAN v1.0	Compatible
Synetica - enlink air	LoRaWAN v1.0	Compatible
Synetica - enlink zone	LoRaWAN v1.0	Compatible
Synetica - enlink_iaq	LoRaWAN v1.0	Compatible
Synetica - enlink_oaq	LoRaWAN v1.0	Compatible

Synetica - enlink_pulse	LoRaWAN v1.0	Compatible
Synetica - enlink_status_af	LoRaWAN v1.0	Compatible
Synetica - enlink_status_dp	LoRaWAN v1.0	Compatible
Synetica - enlink_status_l	LoRaWAN v1.0	Compatible
Synetica - enlink_status_p	LoRaWAN v1.0	Compatible
Synetica - enlink_status_t	LoRaWAN v1.0	Compatible
Synetica - enlink_status_v	LoRaWAN v1.0	Compatible
Synetica - enlink_status_vc	LoRaWAN v1.0	Compatible
Talkpool - OY1110	LoRaWAN v1.0	Compatible
Talkpool - oy1210	LoRaWAN v1.0	Compatible
Talkpool - oy1310	LoRaWAN v1.0	Compatible
Talkpool - oy1320	LoRaWAN v1.0	Compatible
Talkpool - OY1700	LoRaWAN v1.0	Compatible
Tecnair LV - OHU	Modbus Serial	Compatible
Tektelic - breeze	LoRaWAN v1.0	Compatible
Tektelic - industrial	LoRaWAN v1.0	Compatible
Tektelic - kona home	LoRaWAN v1.0	Compatible
Tektelic - smart_room	LoRaWAN v1.0	Compatible
Terabee - people_counting_l_xl	LoRaWAN v1.0	Compatible
Thermokon - AGS55	LoRaWAN v1.0	Compatible
Thermokon - AKF10	LoRaWAN v1.0	Compatible
Thermokon - dpa	LoRaWAN v1.0	Compatible
Thermokon - FTA54	LoRaWAN v1.0	Compatible
Thermokon - FTK	LoRaWAN v1.0	Compatible
Thermokon - la	LoRaWAN v1.0	Compatible
Thermokon - li65	LoRaWAN v1.0	Compatible
Thermokon - lk	LoRaWAN v1.0	Compatible
Thermokon - ls02	LoRaWAN v1.0	Compatible
Thermokon - MCS	LoRaWAN v1.0	Compatible
Thermokon - MWF	LoRaWAN v1.0	Compatible
Thermokon - wk02	LoRaWAN v1.0	Compatible
Thermokon - WSA	LoRaWAN v1.0	Compatible
Thermozyklus - Unite Centrale ZE	Modbus IP,Modbus Serial	Compatible
Vega - air41	LoRaWAN v1.0	Compatible

Wavetrend - water_temperature	LoRaWAN v1.0	Compatible
Wilo - maxo	Modbus Serial	Compatible